

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999009

Luminaire Tested: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999009
REPORT IS A COMBINATION OF REPORTS P984755 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7354.0 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999009

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P999009

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	95	90	86	82	86	82	78	75	67	65	62	54	52	50	41	40	39
2	86	78	71	66	78	71	65	60	58	54	50	46	43	41	36	34	32
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	31	29	26
4	71	60	52	45	64	55	47	42	45	40	35	36	32	29	28	25	22
5	65	53	45	38	59	49	41	36	40	34	30	32	28	25	25	22	19
6	60	47	39	33	54	43	36	31	36	30	26	29	25	21	22	19	17
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15
8	51	39	31	25	46	35	28	24	29	24	20	24	20	17	19	15	13
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14470	14470	14470
5°	14536	13853	13775
10°	14438	13373	13178
15°	14234	12876	12565
20°	13977	12355	11985
25°	13723	11856	11458
30°	13368	11348	10936
35°	13007	10860	10552
40°	12629	10437	10173
45°	12268	10054	9841
50°	11880	9701	9513
55°	11474	9326	9180
60°	10976	8935	8830
65°	10455	8485	8425
70°	9870	8002	7993
75°	9118	7519	7581
80°	7936	7018	7158
85°	6738	6544	6791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12268 cd/sqm

TEST NUMBER: P999009

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	1.2
10°-20°	248.5	3.4
20°-30°	376.6	5.1
30°-40°	458.6	6.2
40°-50°	493.4	6.7
50°-60°	479.2	6.5
60°-70°	418.5	5.7
70°-80°	322.1	4.4
80°-90°	219.6	3.0
90°-100°	234.3	3.2
100°-110°	380.3	5.2
110°-120°	536.6	7.3
120°-130°	651.3	8.9
130°-140°	703.0	9.6
140°-150°	675.8	9.2
150°-160°	564.5	7.7
160°-170°	374.4	5.1
170°-180°	130.8	1.8
0°-30°	711.8	9.7
0°-40°	1170.4	15.9
0°-60°	2142.9	29.1
0°-90°	3103.1	42.2
90°-120°	1151.2	15.7
90°-150°	3181.2	43.3
90°-180°	4251.0	57.8
0°-180°	7354.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	914	914	914	914	914	
5°	917	913	905	913	912	87
15°	874	877	877	889	888	246
25°	795	804	816	832	836	366
35°	685	708	733	762	771	428
45°	562	598	644	685	698	434
55°	431	478	547	595	612	385
65°	294	359	437	492	509	292
75°	163	237	322	379	396	172
85°	48	130	215	270	289	50
90°	14	105	216	266	283	13
95°	71	145	227	277	291	76
105°	257	299	370	419	434	272
115°	472	493	550	589	600	466
125°	681	692	730	763	774	609
135°	879	892	908	934	941	680
145°	1066	1074	1081	1090	1092	666
155°	1218	1222	1225	1231	1228	561
165°	1325	1324	1324	1332	1327	374
175°	1379	1376	1373	1381	1374	131
180°	1381	1381	1381	1381	1381	

TEST NUMBER: P999009

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	914.1	914.1	914.1	914.1	914.1
2.5°	920.8	916.8	907.5	914.1	911.5
5°	916.8	912.8	904.9	912.8	911.5
7.5°	910.2	907.5	900.9	910.2	908.8
10°	902.2	899.6	895.6	906.2	904.9
12.5°	889.0	890.3	887.6	898.2	896.9
15°	874.4	877.0	877.0	889.0	887.6
17.5°	855.8	861.1	865.1	877.0	877.0
20°	837.3	843.9	849.2	863.8	863.8
22.5°	817.4	825.4	833.3	847.9	850.5
25°	794.9	804.2	816.1	832.0	836.0
27.5°	768.4	783.0	796.2	816.1	818.7
30°	741.9	759.1	776.3	797.5	801.5
32.5°	712.8	732.6	753.8	779.0	786.9
35°	684.9	707.5	732.6	761.8	771.0
37.5°	654.5	679.6	711.4	743.2	752.5
40°	624.0	653.1	688.9	723.4	735.3
42.5°	594.8	624.0	666.4	704.8	716.7
45°	561.7	597.5	643.9	684.9	698.2
47.5°	529.9	568.4	621.3	663.7	678.3
50°	496.8	537.9	597.5	642.5	657.1
52.5°	465.0	508.7	572.3	618.7	634.6
55°	430.6	478.3	547.2	594.8	612.1
57.5°	397.4	450.4	519.3	571.0	588.2
60°	361.7	418.6	494.2	544.5	563.1
62.5°	329.9	389.5	465.0	519.3	536.6
65°	294.1	359.0	437.2	491.5	508.7
67.5°	262.3	329.9	409.4	463.7	482.2
70°	227.9	296.8	378.9	435.9	451.8
72.5°	196.1	267.6	351.1	406.7	426.6
75°	163.0	237.1	321.9	378.9	396.1
77.5°	131.2	208.0	294.1	351.1	369.6
80°	99.4	180.2	266.3	321.9	340.5
82.5°	72.9	152.4	239.8	295.4	312.7
85°	47.7	129.8	214.6	270.3	288.8
87.5°	29.1	108.6	193.4	247.7	265.0
90°	14.4	105.3	215.7	266.4	283.4
92.5°	37.5	117.1	199.1	251.9	267.8
95°	71.2	145.2	227.0	277.3	290.9
97.5°	110.7	178.1	259.7	308.7	324.6
100°	157.3	215.7	293.4	342.4	355.8
102.5°	204.9	255.7	331.9	380.7	394.2
105°	257.2	299.1	370.4	419.1	433.7
107.5°	310.9	347.3	413.6	459.8	468.6
110°	360.8	394.3	459.2	501.6	512.7

TEST NUMBER: P999009

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	416.8	445.0	504.7	543.6	555.9
115°	471.6	493.2	550.5	589.0	600.1
117.5°	525.1	545.0	594.8	631.1	640.8
120°	579.9	594.5	638.2	675.3	686.3
122.5°	630.0	642.9	686.1	718.4	728.0
125°	681.0	691.5	730.4	762.7	773.5
127.5°	732.3	743.9	775.0	803.4	811.8
130°	780.1	794.0	819.5	848.9	854.9
132.5°	833.8	844.1	865.2	889.9	897.0
135°	879.1	891.9	907.5	934.2	941.3
137.5°	930.4	940.9	949.8	973.8	978.5
140°	975.8	985.0	993.5	1014.7	1018.0
142.5°	1022.5	1031.7	1035.2	1052.2	1054.2
145°	1065.5	1073.6	1080.6	1089.7	1091.7
147.5°	1105.1	1115.6	1120.3	1123.9	1123.2
150°	1145.9	1152.9	1157.6	1161.1	1157.6
152.5°	1182.0	1189.0	1194.9	1199.5	1194.9
155°	1218.2	1221.7	1225.2	1231.0	1227.5
157.5°	1249.7	1252.0	1254.3	1262.5	1256.6
160°	1277.6	1280.0	1281.1	1288.1	1283.5
162.5°	1303.3	1303.3	1304.4	1312.6	1306.8
165°	1325.4	1324.3	1324.3	1332.4	1326.6
167.5°	1345.2	1341.7	1341.7	1349.9	1344.1
170°	1360.4	1356.9	1355.7	1363.9	1356.9
172.5°	1370.9	1367.4	1366.2	1374.4	1367.4
175°	1379.0	1375.5	1373.2	1381.4	1374.4
177.5°	1383.7	1380.2	1377.9	1384.9	1377.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P999009

CATALOG NUMBER: SA2XXDIP-B865D1080UB35-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.73	14.57	14.75	15.60	16.97	16.81	17.65	17.82	18.67	20.05
	3H	15.19	15.95	16.22	16.99	18.38	19.40	20.15	20.42	21.19	22.58
	4H	15.67	16.39	16.70	17.43	18.83	20.65	21.37	21.68	22.41	23.81
	6H	15.95	16.62	16.99	17.66	19.07	21.95	22.61	22.99	23.65	25.07
	8H	16.01	16.64	17.06	17.70	19.11	22.60	23.24	23.65	24.30	25.71
	12H	16.03	16.63	17.08	17.68	19.12	23.33	23.93	24.38	24.99	26.42
4H	2H	14.78	15.50	15.82	16.54	17.94	17.14	17.86	18.18	18.90	20.30
	3H	16.49	17.10	17.54	18.16	19.58	19.93	20.54	20.97	21.60	23.02
	4H	17.11	17.67	18.16	18.73	20.16	21.34	21.90	22.40	22.96	24.40
	6H	17.52	18.01	18.59	19.09	20.52	22.81	23.30	23.87	24.38	25.81
	8H	17.63	18.09	18.70	19.16	20.61	23.57	24.02	24.63	25.10	26.54
	12H	17.67	18.09	18.76	19.18	20.63	24.39	24.81	25.48	25.90	27.35
8H	4H	17.90	18.35	18.96	19.43	20.87	21.49	21.94	22.55	23.02	24.46
	6H	18.53	18.91	19.62	20.03	21.47	23.11	23.50	24.20	24.61	26.05
	8H	18.75	19.09	19.84	20.19	21.65	24.00	24.34	25.10	25.44	26.90
	12H	18.88	19.18	19.98	20.28	21.78	25.00	25.30	26.09	26.39	27.89
12H	4H	18.10	18.51	19.18	19.60	21.05	21.46	21.87	22.54	22.96	24.41
	6H	18.86	19.20	19.96	20.30	21.76	23.14	23.48	24.23	24.57	26.04
	8H	19.17	19.47	20.26	20.56	22.06	24.07	24.37	25.16	25.46	26.96

END OF REPORT