

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997906

Luminaire Tested: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P997906
REPORT IS A COMBINATION OF REPORTS P983643 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-D4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6064.3 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997906

CATALOG NUMBER: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P997906

CATALOG NUMBER: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	98	93	88	84	91	87	82	79	75	72	69	64	62	60	54	52	51
2	89	80	73	67	82	75	69	63	65	60	56	55	52	48	46	44	41
3	80	70	62	55	74	65	58	52	56	51	46	48	44	40	41	37	34
4	73	61	53	46	68	57	50	44	50	44	39	43	38	34	36	32	29
5	67	55	46	39	62	51	43	37	44	38	33	38	33	29	32	28	25
6	62	49	40	34	57	46	38	32	40	33	29	34	29	25	29	25	22
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17
9	49	36	29	23	46	34	27	22	30	24	20	26	21	18	22	18	16
10	46	33	26	21	43	31	24	20	28	22	18	24	19	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16632	16632	16632
5°	16706	15921	15831
10°	16595	15371	15146
15°	16360	14799	14442
20°	16066	14201	13775
25°	15773	13627	13169
30°	15364	13044	12569
35°	14950	12483	12129
40°	14515	11997	11692
45°	14100	11555	11311
50°	13655	11149	10935
55°	13187	10718	10551
60°	12614	10269	10149
65°	12016	9752	9684
70°	11342	9198	9185
75°	10478	8643	8715
80°	9117	8066	8226
85°	7741	7522	7807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14100 cd/sqm

TEST NUMBER: P997906

CATALOG NUMBER: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	1.6
10°-20°	285.7	4.7
20°-30°	432.8	7.1
30°-40°	527.1	8.7
40°-50°	567.1	9.4
50°-60°	550.7	9.1
60°-70°	481.0	7.9
70°-80°	370.2	6.1
80°-90°	249.8	4.1
90°-100°	290.4	4.8
100°-110°	528.6	8.7
110°-120°	506.8	8.4
120°-130°	394.8	6.5
130°-140°	299.6	4.9
140°-150°	215.0	3.5
150°-160°	148.9	2.5
160°-170°	87.7	1.4
170°-180°	28.5	0.5
0°-30°	818.1	13.5
0°-40°	1345.2	22.2
0°-60°	2463.0	40.6
0°-90°	3564.0	58.8
90°-120°	1325.8	21.9
90°-150°	2235.3	36.9
90°-180°	2500.0	41.2
0°-180°	6064.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1051	1051	1051	1051	1051	
5°	1054	1049	1040	1049	1048	100
15°	1005	1008	1008	1022	1020	283
25°	914	924	938	956	961	420
35°	787	813	842	876	886	492
45°	646	687	740	787	802	498
55°	495	550	629	684	704	443
65°	338	413	502	565	585	336
75°	187	273	370	436	455	198
85°	55	149	247	311	332	58
90°	16	111	220	280	299	12
95°	32	132	397	317	316	30
105°	77	156	551	934	839	82
115°	128	177	443	862	994	126
125°	173	204	389	680	788	154
135°	201	239	350	542	626	156
145°	228	262	332	421	468	143
155°	259	280	322	364	379	119
165°	282	291	309	327	332	80
175°	294	294	297	300	300	28
180°	294	294	294	294	294	

TEST NUMBER: P997906

CATALOG NUMBER: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1050.7	1050.7	1050.7	1050.7	1050.7
2.5°	1058.3	1053.7	1043.1	1050.7	1047.6
5°	1053.7	1049.2	1040.0	1049.2	1047.6
7.5°	1046.1	1043.1	1035.4	1046.1	1044.6
10°	1037.0	1033.9	1029.4	1041.5	1040.0
12.5°	1021.7	1023.3	1020.2	1032.4	1030.9
15°	1005.0	1008.0	1008.0	1021.7	1020.2
17.5°	983.7	989.8	994.3	1008.0	1008.0
20°	962.4	970.0	976.1	992.8	992.8
22.5°	939.5	948.7	957.8	974.5	977.6
25°	913.6	924.3	938.0	956.3	960.8
27.5°	883.2	899.9	915.2	938.0	941.0
30°	852.7	872.5	892.3	916.7	921.2
32.5°	819.2	842.1	866.4	895.4	904.5
35°	787.2	813.1	842.1	875.6	886.2
37.5°	752.2	781.2	817.7	854.2	864.9
40°	717.2	750.7	791.8	831.4	845.1
42.5°	683.7	717.2	765.9	810.1	823.8
45°	645.6	686.7	740.0	787.2	802.5
47.5°	609.1	653.2	714.2	762.9	779.6
50°	571.0	618.2	686.7	738.5	755.3
52.5°	534.5	584.7	657.8	711.1	729.4
55°	494.9	549.7	628.9	683.7	703.5
57.5°	456.8	517.7	596.9	656.3	676.1
60°	415.7	481.2	568.0	625.8	647.2
62.5°	379.2	447.7	534.5	596.9	616.7
65°	338.0	412.7	502.5	564.9	584.7
67.5°	301.5	379.2	470.5	533.0	554.3
70°	261.9	341.1	435.5	501.0	519.2
72.5°	225.4	307.6	403.5	467.5	490.3
75°	187.3	272.6	370.0	435.5	455.3
77.5°	150.7	239.1	338.0	403.5	424.8
80°	114.2	207.1	306.1	370.0	391.3
82.5°	83.7	175.1	275.6	339.6	359.4
85°	54.8	149.2	246.7	310.6	332.0
87.5°	33.5	124.9	222.3	284.7	304.5
90°	15.8	111.2	220.3	280.3	298.9
92.5°	22.2	121.3	274.5	286.9	299.6
95°	32.0	132.4	397.1	316.8	315.8
97.5°	40.2	140.4	526.4	389.0	347.3
100°	54.3	145.8	599.8	543.6	428.2
102.5°	65.7	151.2	591.9	762.8	608.5
105°	76.7	156.0	550.7	934.4	839.3
107.5°	90.3	160.9	511.7	988.8	990.8
110°	102.4	165.9	483.3	965.9	1045.5

TEST NUMBER: P997906

CATALOG NUMBER: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	114.8	172.1	460.2	918.6	1033.7
115°	127.9	176.6	442.6	861.7	993.8
117.5°	140.0	182.6	427.3	808.4	939.7
120°	152.4	188.6	414.3	757.9	888.8
122.5°	164.3	196.1	402.8	717.4	833.1
125°	172.9	204.0	389.4	679.9	788.0
127.5°	181.4	213.0	378.5	644.8	743.5
130°	188.8	222.4	368.2	610.9	704.7
132.5°	195.6	231.4	358.6	576.2	666.3
135°	200.9	239.4	350.3	542.1	625.6
137.5°	207.1	246.2	342.7	507.6	584.5
140°	214.5	251.0	336.0	476.0	542.3
142.5°	221.8	256.0	333.0	446.8	501.7
145°	227.7	261.6	331.9	421.2	467.6
147.5°	235.6	266.2	330.2	399.1	434.9
150°	243.6	270.7	328.5	385.2	409.5
152.5°	251.5	275.2	325.7	374.6	393.1
155°	258.8	279.6	322.3	364.5	378.9
157.5°	265.1	282.9	318.9	354.8	366.5
160°	271.3	286.3	315.5	345.2	354.6
162.5°	277.5	288.8	312.7	336.2	343.2
165°	282.1	290.6	308.7	327.4	332.5
167.5°	286.0	292.2	305.3	319.5	322.3
170°	290.0	293.2	302.5	312.1	313.2
172.5°	292.3	294.0	299.1	305.6	305.9
175°	294.0	294.2	296.8	300.5	299.6
177.5°	295.1	294.5	294.5	296.8	295.1
180°	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P997906

CATALOG NUMBER: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-D4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.73	16.74	16.60	17.64	18.77	18.81	19.82	19.67	20.71	21.85
	3H	17.20	18.12	18.08	19.02	20.18	21.41	22.32	22.28	23.23	24.39
	4H	17.68	18.55	18.58	19.46	20.63	22.66	23.53	23.56	24.44	25.61
	6H	17.97	18.78	18.88	19.70	20.88	23.97	24.77	24.87	25.69	26.88
	8H	18.04	18.81	18.95	19.74	20.93	24.63	25.40	25.54	26.34	27.52
	12H	18.06	18.79	18.98	19.72	20.93	25.36	26.10	26.28	27.03	28.24
4H	2H	16.80	17.67	17.69	18.58	19.75	19.15	20.02	20.05	20.93	22.10
	3H	18.52	19.25	19.42	20.20	21.38	21.95	22.69	22.86	23.63	24.82
	4H	19.14	19.82	20.06	20.76	21.97	23.38	24.06	24.29	24.99	26.20
	6H	19.57	20.16	20.50	21.12	22.33	24.85	25.45	25.78	26.41	27.62
	8H	19.68	20.24	20.61	21.19	22.42	25.61	26.17	26.55	27.13	28.35
	12H	19.73	20.24	20.69	21.21	22.44	26.45	26.96	27.40	27.93	29.16
8H	4H	19.95	20.50	20.88	21.46	22.68	23.53	24.09	24.47	25.05	26.27
	6H	20.58	21.06	21.54	22.05	23.27	25.17	25.64	26.13	26.63	27.86
	8H	20.81	21.23	21.78	22.21	23.45	26.06	26.48	27.03	27.46	28.70
	12H	20.95	21.32	21.92	22.30	23.59	27.06	27.43	28.03	28.41	29.70
12H	4H	20.15	20.66	21.11	21.63	22.86	23.51	24.02	24.47	24.99	26.22
	6H	20.92	21.34	21.89	22.33	23.56	25.19	25.62	26.16	26.60	27.84
	8H	21.23	21.61	22.21	22.58	23.87	26.13	26.50	27.10	27.48	28.77