

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999122

Luminaire Tested: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999122
REPORT IS A COMBINATION OF REPORTS P984871 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5931.0 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	102	97	94	90	95	92	88	85	81	79	76	71	69	68	62	61	60
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	55	53	51
3	85	76	69	63	80	72	65	60	64	59	55	56	53	49	50	47	44
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34
6	67	55	47	41	63	52	45	40	47	41	36	42	37	33	37	33	30
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	32	28	25
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	22
10	51	38	31	26	48	37	30	26	33	28	24	30	26	22	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27277	27277	27277	27277
5°	27344	29085	27448	23140
10°	27026	31750	27195	19078
15°	26370	33490	26736	16069
20°	25958	31444	25958	13968
25°	25132	27013	25246	12490
30°	23771	21235	24223	11314
35°	22564	14684	22942	10351
40°	21178	11087	21419	9583
45°	19468	9111	19787	8756
50°	17990	7996	18024	8016
55°	16305	6814	16411	7211
60°	14511	5691	14711	6293
65°	12901	4629	13139	5374
70°	11299	3632	11589	4334
75°	9482	2638	9857	3143
80°	7401	1671	7928	1865
85°	4859	842	5241	623

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 28197 cd/sqm

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.1	2.8
10°-20°	477.7	8.1
20°-30°	693.3	11.7
30°-40°	730.9	12.3
40°-50°	646.8	10.9
50°-60°	516.4	8.7
60°-70°	350.8	5.9
70°-80°	179.5	3.0
80°-90°	43.7	0.7
90°-100°	23.9	0.4
100°-110°	89.2	1.5
110°-120°	236.6	4.0
120°-130°	392.4	6.6
130°-140°	416.8	7.0
140°-150°	387.4	6.5
150°-160°	311.5	5.3
160°-170°	200.7	3.4
170°-180°	69.1	1.2
0°-30°	1335.2	22.5
0°-40°	2066.1	34.8
0°-60°	3229.3	54.4
0°-90°	3803.3	64.1
90°-120°	349.8	5.9
90°-150°	1546.5	26.1
90°-180°	2128.0	35.9
0°-180°	5931.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1925	1731	1531	1725	163
15°	1620	2366	1642	1135	1620	458
25°	1456	1971	1462	911	1456	665
35°	1188	1073	1208	756	1188	743
45°	891	646	906	621	891	692
55°	612	454	616	481	612	546
65°	363	280	370	324	363	361
75°	170	138	176	164	170	182
85°	34	36	37	26	34	40
90°	0	14	0	14	0	4
95°	34	23	34	23	34	40
105°	160	40	160	40	160	171
115°	302	43	302	43	302	297
125°	427	449	427	449	427	381
135°	528	546	528	546	528	408
145°	613	622	613	622	613	383
155°	675	675	675	675	675	311
165°	711	710	711	710	711	201
175°	727	723	727	723	727	69
180°	726	726	726	726	726	

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1732.5	1736.5	1743.1	1744.4	1757.7	1768.3	1780.2	1780.2	1784.2	1782.8	1772.3
5°	1724.6	1736.5	1753.7	1768.3	1792.1	1802.7	1818.6	1830.5	1841.1	1849.1	1847.8
7.5°	1711.3	1732.5	1757.7	1785.5	1817.3	1835.8	1858.3	1879.5	1894.1	1907.4	1916.6
10°	1688.8	1724.6	1759.0	1796.1	1837.2	1862.3	1888.8	1916.6	1939.1	1964.3	1988.2
12.5°	1658.3	1710.0	1752.4	1801.4	1851.7	1879.5	1921.9	1943.1	1986.8	2050.4	2067.6
15°	1619.9	1690.1	1729.9	1792.1	1858.3	1880.9	1939.1	1973.6	2063.7	2103.4	2151.1
17.5°	1584.2	1662.3	1715.3	1786.8	1851.7	1895.4	1952.4	2022.6	2098.1	2155.0	2208.0
20°	1555.0	1630.5	1694.1	1773.6	1855.7	1911.3	1970.9	2055.7	2137.8	2196.1	2237.2
22.5°	1488.8	1585.5	1659.7	1748.4	1847.8	1924.6	1981.5	2074.3	2163.0	2198.8	2234.5
25°	1455.7	1539.1	1625.2	1725.9	1842.5	1933.8	1982.9	2086.2	2164.3	2177.6	2185.5
27.5°	1394.8	1488.8	1589.5	1704.7	1841.1	1918.0	1980.2	2074.3	2136.5	2127.2	2103.4
30°	1319.3	1434.5	1545.8	1670.3	1822.6	1906.0	1964.3	2050.4	2082.2	2034.5	1992.1
32.5°	1263.6	1372.2	1495.4	1639.8	1801.4	1880.9	1937.8	2005.4	2012.0	1925.9	1854.4
35°	1188.1	1308.7	1447.7	1600.1	1765.6	1837.2	1890.1	1931.2	1899.4	1778.9	1694.1
37.5°	1120.6	1239.8	1388.1	1543.1	1716.6	1786.8	1829.2	1835.8	1757.7	1651.7	1527.2
40°	1046.4	1169.6	1324.6	1487.5	1662.3	1723.2	1749.7	1729.9	1617.3	1494.1	1349.7
42.5°	972.2	1094.1	1261.0	1427.9	1593.4	1645.1	1655.7	1601.4	1463.6	1319.3	1152.4
45°	891.4	1018.6	1185.5	1353.7	1514.0	1543.1	1544.4	1466.3	1303.4	1152.4	997.4
47.5°	825.2	943.1	1108.7	1276.9	1412.0	1431.8	1423.9	1333.8	1156.3	986.8	851.7
50°	752.3	864.9	1029.2	1194.7	1310.0	1315.3	1295.4	1166.9	993.4	838.4	731.2
52.5°	674.2	788.1	939.1	1098.1	1201.4	1193.4	1155.0	1017.3	854.3	725.9	643.7
55°	611.9	712.6	854.3	1009.3	1082.2	1059.6	1017.3	876.9	748.4	639.8	568.2
57.5°	543.1	631.8	770.9	906.0	948.4	927.2	884.8	753.7	634.5	552.3	504.7
60°	478.2	559.0	680.8	793.4	826.5	804.0	755.0	637.1	551.0	482.1	446.4
62.5°	418.6	488.8	590.8	694.1	707.3	684.8	642.4	547.0	472.9	418.6	392.1
65°	362.9	429.2	511.3	589.4	601.3	577.5	533.8	464.9	402.7	368.2	343.1
67.5°	308.6	361.6	434.5	491.4	498.0	475.5	439.8	384.1	345.7	308.6	290.1
70°	260.9	300.7	357.6	404.0	406.6	385.4	366.9	316.6	287.4	260.9	246.4
72.5°	214.6	242.4	286.1	320.5	321.9	308.6	291.4	259.6	234.4	215.9	201.3
75°	169.5	193.4	219.9	250.3	249.0	238.4	225.2	205.3	184.1	172.2	165.6
77.5°	129.8	144.4	165.6	185.4	185.4	180.1	172.2	157.6	144.4	132.5	125.8
80°	92.7	102.0	119.2	125.8	128.5	127.2	120.5	109.9	104.6	95.4	92.7
82.5°	59.6	66.2	74.2	80.8	84.8	82.1	80.8	75.5	67.6	64.9	62.3
85°	34.4	37.1	41.1	45.0	46.4	45.0	47.7	43.7	39.7	39.7	38.4
87.5°	14.6	15.9	18.5	18.5	19.9	19.9	18.5	19.9	19.9	18.5	17.2
90°	0.5	1.8	3.1	4.4	5.7	6.3	6.8	7.7	8.6	9.6	10.5
92.5°	13.1	12.6	12.2	11.7	11.2	11.0	11.2	11.5	11.9	12.2	12.6
95°	34.1	30.3	26.4	22.6	18.7	16.8	17.2	18.0	18.9	19.7	20.5
97.5°	61.4	51.8	42.3	32.7	23.2	18.4	19.3	21.2	23.1	24.9	26.8
100°	93.0	77.0	61.0	45.0	29.0	21.0	22.0	24.0	25.9	27.9	29.9
102.5°	127.6	127.4	127.2	126.9	126.7	126.6	116.0	94.7	73.5	52.2	31.0
105°	159.6	163.1	166.6	170.1	173.6	175.4	159.5	127.6	95.7	63.9	32.0
107.5°	196.9	199.8	202.8	205.7	208.6	210.1	190.4	151.1	111.8	72.4	33.1
110°	232.6	235.1	237.5	240.0	242.5	243.7	226.8	193.1	159.4	125.6	91.9

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	266.3	268.4	270.5	272.6	274.7	275.7	274.7	272.7	270.8	268.8	266.8
115°	302.0	304.0	306.0	307.9	309.9	310.9	312.4	315.3	318.2	321.1	324.0
117.5°	333.0	335.3	337.7	340.0	342.3	343.5	344.5	346.5	348.4	350.4	352.4
120°	367.6	369.4	371.1	372.9	374.6	375.5	376.5	378.6	380.7	382.8	384.9
122.5°	397.0	398.9	400.7	402.6	404.5	405.4	406.6	408.9	411.2	413.6	415.9
125°	427.0	428.5	430.0	431.5	433.0	433.8	434.9	437.1	439.4	441.6	443.8
127.5°	454.3	455.9	457.5	459.2	460.8	461.6	462.5	464.2	466.0	467.7	469.5
130°	480.0	481.9	483.7	485.6	487.5	488.4	489.0	490.3	491.6	492.9	494.2
132.5°	506.3	507.8	509.3	510.8	512.3	513.1	513.7	515.0	516.3	517.6	518.9
135°	528.3	530.2	532.0	533.9	535.8	536.7	537.2	538.3	539.3	540.4	541.4
137.5°	551.4	552.8	554.2	555.6	557.0	557.7	558.3	559.5	560.6	561.8	563.0
140°	574.0	574.9	575.9	576.8	577.7	578.2	578.8	580.1	581.4	582.7	584.0
142.5°	592.9	593.7	594.5	595.4	596.2	596.6	597.4	598.9	600.4	601.9	603.4
145°	612.9	612.8	612.6	612.5	612.4	612.3	613.3	615.3	617.3	619.3	621.3
147.5°	630.2	629.8	629.5	629.1	628.8	628.6	629.6	631.6	633.5	635.5	637.5
150°	647.0	646.2	645.4	644.5	643.7	643.3	644.2	646.1	648.0	649.8	651.7
152.5°	661.2	660.3	659.3	658.4	657.5	657.0	657.9	659.6	661.4	663.1	664.9
155°	674.8	673.8	672.7	671.7	670.6	670.1	670.8	672.2	673.6	675.0	676.4
157.5°	685.9	685.0	684.0	683.1	682.2	681.7	682.2	683.3	684.3	685.4	686.4
160°	695.3	694.6	693.9	693.2	692.5	692.2	692.5	693.2	693.9	694.6	695.3
162.5°	703.7	703.0	702.3	701.6	700.9	700.6	700.9	701.5	702.0	702.6	703.2
165°	711.1	710.4	709.7	709.0	708.3	707.9	708.1	708.4	708.8	709.1	709.5
167.5°	716.8	716.1	715.4	714.7	714.0	713.7	713.9	714.2	714.6	714.9	715.3
170°	721.6	720.9	720.2	719.5	718.8	718.4	718.5	718.8	719.0	719.3	719.5
172.5°	724.7	724.0	723.3	722.6	721.9	721.6	721.7	721.9	722.2	722.4	722.6
175°	727.4	726.6	725.8	724.9	724.1	723.7	723.8	724.0	724.3	724.5	724.7
177.5°	728.4	727.6	726.8	725.9	725.1	724.7	724.8	724.9	725.0	725.2	725.3
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1790.8	1792.1	1794.8	1808.0	1814.6	1816.0	1810.7	1822.6	1826.6	1822.6	1819.9
5°	1875.6	1883.5	1899.4	1916.6	1915.3	1916.6	1924.6	1932.5	1935.2	1924.6	1928.5
7.5°	1949.7	1965.6	1982.9	2009.3	2009.3	2022.6	2027.9	2034.5	2050.4	2042.5	2039.8
10°	2034.5	2055.7	2087.5	2129.9	2131.2	2144.5	2157.7	2178.9	2185.5	2180.2	2182.9
12.5°	2140.5	2181.5	2184.2	2230.5	2251.7	2254.4	2275.6	2271.6	2284.9	2284.9	2307.4
15°	2186.8	2250.4	2286.2	2331.2	2344.5	2328.6	2345.8	2364.3	2365.7	2365.7	2364.3
17.5°	2270.3	2295.5	2331.2	2355.1	2360.4	2360.4	2361.7	2369.6	2364.3	2353.7	2361.7
20°	2287.5	2298.1	2311.3	2308.7	2311.3	2298.1	2284.9	2271.6	2272.9	2266.3	2286.2
22.5°	2255.7	2253.1	2222.6	2202.7	2202.7	2176.2	2151.1	2139.2	2127.2	2131.2	2137.8
25°	2176.2	2135.2	2098.1	2069.0	2062.3	2019.9	1985.5	1974.9	1955.0	1970.9	1973.6
27.5°	2049.1	2002.7	1943.1	1918.0	1883.5	1866.3	1842.5	1810.7	1769.6	1793.4	1789.5
30°	1912.7	1843.8	1794.8	1733.8	1679.5	1675.6	1630.5	1577.5	1556.3	1556.3	1568.3
32.5°	1760.3	1668.9	1597.4	1511.3	1458.3	1435.8	1381.5	1328.5	1340.4	1300.7	1315.3
35°	1582.8	1462.3	1372.2	1288.8	1249.1	1222.6	1152.4	1123.2	1091.4	1072.9	1107.3
37.5°	1413.3	1274.2	1159.0	1067.6	1053.0	1005.3	957.7	939.1	920.6	928.5	927.2
40°	1206.7	1083.5	980.2	908.6	883.5	861.0	829.2	806.7	794.7	801.4	802.7
42.5°	1019.9	916.6	839.8	789.4	768.2	752.3	736.5	717.9	713.9	713.9	719.2
45°	875.5	790.8	739.1	698.0	686.1	674.2	662.3	654.3	651.7	646.4	650.4
47.5°	760.3	692.7	661.0	630.5	617.2	614.6	604.0	600.0	594.7	593.4	594.7
50°	663.6	621.2	592.1	574.9	565.6	561.6	556.3	548.4	545.7	552.3	549.7
52.5°	596.0	556.3	540.4	523.2	517.9	512.6	504.7	506.0	504.7	502.0	502.0
55°	528.5	503.3	487.4	474.2	472.9	467.6	460.9	458.3	457.0	454.3	458.3
57.5°	474.2	454.3	439.8	427.8	422.5	422.5	415.9	410.6	410.6	409.3	410.6
60°	419.9	400.0	390.7	378.8	374.8	373.5	369.6	366.9	362.9	362.9	362.9
62.5°	369.6	353.7	343.1	332.5	333.8	327.2	321.9	319.2	319.2	320.5	320.5
65°	321.9	311.3	298.0	288.8	286.1	284.8	282.1	280.8	276.8	279.5	279.5
67.5°	278.2	263.6	255.6	251.7	247.7	246.4	243.7	241.1	239.7	238.4	241.1
70°	234.4	222.5	215.9	213.3	209.3	208.0	206.6	202.7	204.0	205.3	206.6
72.5°	194.7	184.1	182.8	174.8	174.8	174.8	169.5	172.2	170.9	168.2	170.9
75°	153.6	148.3	145.7	141.7	143.1	141.7	140.4	136.4	136.4	137.8	139.1
77.5°	121.9	116.6	115.2	111.3	108.6	111.3	108.6	107.3	107.3	108.6	108.6
80°	90.1	87.4	83.4	83.4	83.4	82.1	82.1	82.1	80.8	79.5	80.8
82.5°	59.6	59.6	58.3	57.0	58.3	55.6	57.0	57.0	57.0	57.0	57.0
85°	38.4	37.1	37.1	35.8	35.8	35.8	37.1	34.4	34.4	35.8	35.8
87.5°	17.2	17.2	17.2	18.5	17.2	17.2	17.2	18.5	17.2	17.2	17.2
90°	11.1	11.7	12.2	12.8	13.1	13.2	13.5	13.7	14.0	14.2	14.0
92.5°	12.8	13.1	13.3	13.6	13.7	13.8	13.9	14.0	14.1	14.2	14.1
95°	21.1	21.7	22.2	22.8	23.1	23.0	22.9	22.8	22.7	22.6	22.7
97.5°	27.2	27.5	27.9	28.2	28.4	28.5	28.6	28.7	28.8	28.9	28.8
100°	30.8	31.8	32.7	33.6	34.1	34.2	34.5	34.7	35.0	35.2	35.0
102.5°	32.3	33.6	34.9	36.2	36.8	37.0	37.3	37.6	38.0	38.3	38.0
105°	33.3	34.6	35.9	37.2	37.8	38.0	38.5	39.0	39.4	39.9	39.4
107.5°	34.4	35.7	37.0	38.3	38.9	39.1	39.6	40.1	40.5	41.0	40.5
110°	80.2	68.6	56.9	45.2	39.4	39.6	40.1	40.6	41.0	41.5	41.0

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	216.5	166.2	115.9	65.6	40.4	40.6	40.9	41.3	41.6	42.0	41.6
115°	270.0	216.0	161.9	107.9	80.9	76.7	68.3	59.9	51.5	43.1	51.5
117.5°	335.7	319.0	302.3	285.6	277.3	262.0	231.4	200.9	170.3	139.7	170.3
120°	386.3	387.7	389.1	390.5	391.2	383.3	367.6	351.9	336.1	320.4	336.1
122.5°	416.6	417.3	418.0	418.7	419.1	419.2	419.3	419.4	419.5	419.6	419.5
125°	444.6	445.4	446.2	447.0	447.4	447.6	447.9	448.3	448.6	449.0	448.6
127.5°	470.7	471.8	473.0	474.1	474.7	474.8	474.9	475.0	475.2	475.3	475.2
130°	495.5	496.8	498.1	499.4	500.0	499.9	499.8	499.7	499.5	499.4	499.5
132.5°	519.9	521.0	522.0	523.1	523.6	523.5	523.4	523.3	523.2	523.1	523.2
135°	542.6	543.8	544.9	546.1	546.7	546.6	546.3	546.1	545.8	545.6	545.8
137.5°	564.2	565.3	566.5	567.6	568.2	568.0	567.7	567.4	567.0	566.7	567.0
140°	585.0	586.1	587.1	588.2	588.7	588.4	587.8	587.3	586.7	586.1	586.7
142.5°	604.3	605.3	606.2	607.1	607.6	607.3	606.7	606.2	605.6	605.0	605.6
145°	622.1	622.9	623.7	624.5	624.9	624.6	624.0	623.5	622.9	622.3	622.9
147.5°	638.1	638.7	639.3	639.9	640.2	640.0	639.5	639.0	638.6	638.1	638.6
150°	652.4	653.1	653.8	654.5	654.9	654.6	654.0	653.5	652.9	652.3	652.9
152.5°	665.6	666.3	667.0	667.7	668.0	667.6	666.8	665.9	665.1	664.3	665.1
155°	677.1	677.8	678.5	679.2	679.6	679.1	678.2	677.3	676.3	675.4	676.3
157.5°	687.2	688.0	688.9	689.7	690.1	689.6	688.7	687.8	686.8	685.9	686.8
160°	696.0	696.7	697.4	698.1	698.5	698.1	697.3	696.4	695.6	694.8	695.6
162.5°	704.0	704.8	705.7	706.5	706.9	706.4	705.3	704.2	703.2	702.1	703.2
165°	710.3	711.1	712.0	712.8	713.2	712.8	712.0	711.1	710.3	709.5	710.3
167.5°	716.1	716.9	717.7	718.5	718.9	718.4	717.3	716.3	715.2	714.2	715.2
170°	720.3	721.1	722.0	722.8	723.2	722.7	721.6	720.5	719.5	718.4	719.5
172.5°	723.4	724.2	725.1	725.9	726.3	725.8	724.7	723.7	722.6	721.6	722.6
175°	725.5	726.3	727.2	728.0	728.4	727.8	726.7	725.5	724.4	723.2	724.4
177.5°	726.1	726.9	727.7	728.5	728.9	728.4	727.3	726.3	725.2	724.2	725.2
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1826.6	1817.3	1809.3	1810.7	1817.3	1812.0	1798.7	1781.5	1774.9	1767.0	1774.9
5°	1936.5	1928.5	1912.7	1914.0	1910.0	1904.7	1883.5	1857.0	1857.0	1835.8	1833.2
7.5°	2045.1	2033.2	2022.6	2019.9	2005.4	1994.8	1976.2	1939.1	1924.6	1899.4	1884.8
10°	2167.0	2157.7	2145.8	2131.2	2123.3	2104.7	2074.3	2019.9	1993.5	1959.0	1933.8
12.5°	2290.2	2288.8	2262.3	2233.2	2231.9	2202.7	2181.5	2108.7	2072.9	2026.6	1967.0
15°	2368.3	2361.7	2347.1	2332.5	2336.5	2304.7	2257.0	2170.9	2147.1	2091.5	2027.9
17.5°	2367.0	2367.0	2363.0	2360.4	2356.4	2347.1	2320.6	2263.7	2225.2	2155.0	2095.4
20°	2291.5	2308.7	2312.7	2311.3	2324.6	2331.2	2329.9	2294.1	2263.7	2201.4	2140.5
22.5°	2140.5	2180.2	2197.4	2208.0	2235.8	2250.4	2284.9	2271.6	2263.7	2217.3	2165.6
25°	2000.1	2013.3	2065.0	2067.6	2106.0	2141.8	2176.2	2198.8	2227.9	2210.7	2167.0
27.5°	1818.6	1849.1	1886.2	1914.0	1921.9	1994.8	2051.7	2094.1	2160.3	2165.6	2151.1
30°	1613.3	1627.9	1688.8	1725.9	1768.3	1821.3	1903.4	1976.2	2035.8	2090.1	2108.7
32.5°	1363.0	1422.6	1458.3	1503.4	1540.5	1634.5	1735.2	1829.2	1898.1	1989.5	2029.2
35°	1133.8	1180.2	1241.1	1259.6	1327.2	1406.7	1537.8	1658.3	1763.0	1855.7	1936.5
37.5°	944.4	981.5	1046.4	1075.5	1115.3	1217.3	1327.2	1476.9	1602.7	1716.6	1817.3
40°	814.6	842.4	891.4	900.7	933.8	1026.5	1115.3	1255.7	1422.6	1576.2	1686.2
42.5°	725.9	739.1	772.2	784.1	805.3	867.6	947.1	1079.5	1234.5	1393.4	1548.4
45°	662.3	671.5	691.4	702.0	728.5	756.3	821.2	927.2	1049.0	1209.3	1376.2
47.5°	605.3	617.2	625.2	631.8	646.4	676.8	719.2	797.4	913.9	1061.0	1222.6
50°	557.6	561.6	576.2	577.5	586.8	606.6	646.4	694.1	786.8	906.0	1062.3
52.5°	510.0	513.9	523.2	532.5	536.4	552.3	578.8	618.6	687.4	781.5	920.6
55°	462.3	467.6	476.8	483.5	487.4	500.7	516.6	555.0	609.3	675.5	789.4
57.5°	414.6	426.5	429.2	433.1	439.8	454.3	468.9	491.4	533.8	594.7	678.2
60°	369.6	373.5	382.8	386.8	393.4	401.3	419.9	437.1	467.6	515.3	590.8
62.5°	323.2	332.5	336.4	340.4	345.7	355.0	366.9	385.4	411.9	450.3	510.0
65°	283.5	284.8	292.7	298.0	303.3	309.9	321.9	339.1	355.0	390.7	434.5
67.5°	245.0	247.7	250.3	255.6	262.3	268.9	279.5	288.8	308.6	332.5	366.9
70°	208.0	208.0	214.6	218.6	217.2	225.2	233.1	243.7	258.3	280.8	308.6
72.5°	174.8	173.5	178.8	180.1	182.8	188.1	193.4	204.0	211.9	229.1	250.3
75°	139.1	141.7	144.4	144.4	148.3	152.3	157.6	162.9	172.2	182.8	198.7
77.5°	109.9	109.9	112.6	113.9	117.9	116.6	121.9	127.2	133.8	143.1	155.0
80°	80.8	83.4	83.4	83.4	84.8	86.1	91.4	95.4	99.3	106.0	111.3
82.5°	57.0	57.0	59.6	59.6	59.6	62.3	62.3	63.6	66.2	70.2	74.2
85°	35.8	35.8	35.8	37.1	35.8	37.1	39.7	38.4	39.7	42.4	42.4
87.5°	17.2	17.2	17.2	17.2	17.2	18.5	17.2	18.5	19.9	19.9	19.9
90°	13.7	13.5	13.2	13.1	12.8	12.2	11.7	11.1	10.5	9.6	8.6
92.5°	14.0	13.9	13.8	13.7	13.6	13.3	13.1	12.8	12.6	12.2	11.9
95°	22.8	22.9	23.0	23.1	22.8	22.2	21.7	21.1	20.5	19.7	18.9
97.5°	28.7	28.6	28.5	28.4	28.2	27.9	27.5	27.2	26.8	24.9	23.1
100°	34.7	34.5	34.2	34.1	33.6	32.7	31.8	30.8	29.9	27.9	25.9
102.5°	37.6	37.3	37.0	36.8	36.2	34.9	33.6	32.3	31.0	52.2	73.5
105°	39.0	38.5	38.0	37.8	37.2	35.9	34.6	33.3	32.0	63.9	95.7
107.5°	40.1	39.6	39.1	38.9	38.3	37.0	35.7	34.4	33.1	72.4	111.8
110°	40.6	40.1	39.6	39.4	45.2	56.9	68.6	80.2	91.9	125.6	159.4

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	41.3	40.9	40.6	40.4	65.6	115.9	166.2	216.5	266.8	268.8	270.8
115°	59.9	68.3	76.7	80.9	107.9	161.9	216.0	270.0	324.0	321.1	318.2
117.5°	200.9	231.4	262.0	277.3	285.6	302.3	319.0	335.7	352.4	350.4	348.4
120°	351.9	367.6	383.3	391.2	390.5	389.1	387.7	386.3	384.9	382.8	380.7
122.5°	419.4	419.3	419.2	419.1	418.7	418.0	417.3	416.6	415.9	413.6	411.2
125°	448.3	447.9	447.6	447.4	447.0	446.2	445.4	444.6	443.8	441.6	439.4
127.5°	475.0	474.9	474.8	474.7	474.1	473.0	471.8	470.7	469.5	467.7	466.0
130°	499.7	499.8	499.9	500.0	499.4	498.1	496.8	495.5	494.2	492.9	491.6
132.5°	523.3	523.4	523.5	523.6	523.1	522.0	521.0	519.9	518.9	517.6	516.3
135°	546.1	546.3	546.6	546.7	546.1	544.9	543.8	542.6	541.4	540.4	539.3
137.5°	567.4	567.7	568.0	568.2	567.6	566.5	565.3	564.2	563.0	561.8	560.6
140°	587.3	587.8	588.4	588.7	588.2	587.1	586.1	585.0	584.0	582.7	581.4
142.5°	606.2	606.7	607.3	607.6	607.1	606.2	605.3	604.3	603.4	601.9	600.4
145°	623.5	624.0	624.6	624.9	624.5	623.7	622.9	622.1	621.3	619.3	617.3
147.5°	639.0	639.5	640.0	640.2	639.9	639.3	638.7	638.1	637.5	635.5	633.5
150°	653.5	654.0	654.6	654.9	654.5	653.8	653.1	652.4	651.7	649.8	648.0
152.5°	665.9	666.8	667.6	668.0	667.7	667.0	666.3	665.6	664.9	663.1	661.4
155°	677.3	678.2	679.1	679.6	679.2	678.5	677.8	677.1	676.4	675.0	673.6
157.5°	687.8	688.7	689.6	690.1	689.7	688.9	688.0	687.2	686.4	685.4	684.3
160°	696.4	697.3	698.1	698.5	698.1	697.4	696.7	696.0	695.3	694.6	693.9
162.5°	704.2	705.3	706.4	706.9	706.5	705.7	704.8	704.0	703.2	702.6	702.0
165°	711.1	712.0	712.8	713.2	712.8	712.0	711.1	710.3	709.5	709.1	708.8
167.5°	716.3	717.3	718.4	718.9	718.5	717.7	716.9	716.1	715.3	714.9	714.6
170°	720.5	721.6	722.7	723.2	722.8	722.0	721.1	720.3	719.5	719.3	719.0
172.5°	723.7	724.7	725.8	726.3	725.9	725.1	724.2	723.4	722.6	722.4	722.2
175°	725.5	726.7	727.8	728.4	728.0	727.2	726.3	725.5	724.7	724.5	724.3
177.5°	726.3	727.3	728.4	728.9	728.5	727.7	726.9	726.1	725.3	725.2	725.0
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1768.3	1761.7	1757.7	1760.3	1752.4	1732.5	1732.5	1739.1	1731.2	1723.2	1711.3
5°	1817.3	1804.0	1796.1	1794.8	1776.2	1744.4	1737.8	1731.2	1714.0	1695.4	1675.6
7.5°	1865.0	1841.1	1827.9	1818.6	1792.1	1751.1	1733.8	1719.3	1691.5	1663.6	1638.5
10°	1904.7	1870.3	1854.4	1839.8	1805.4	1753.7	1725.9	1699.4	1663.6	1627.9	1596.1
12.5°	1936.5	1896.8	1876.9	1855.7	1813.3	1745.8	1711.3	1668.9	1633.2	1585.5	1553.7
15°	1989.5	1907.4	1888.8	1868.9	1825.2	1732.5	1690.1	1642.4	1593.4	1529.9	1495.4
17.5°	2031.9	1921.9	1920.6	1878.2	1821.3	1727.2	1662.3	1600.1	1547.1	1483.5	1429.2
20°	2057.0	1944.4	1923.3	1879.5	1808.0	1691.5	1623.9	1555.0	1498.1	1421.2	1366.9
22.5°	2078.2	1976.2	1920.6	1867.6	1780.2	1679.5	1580.2	1515.3	1437.1	1353.7	1302.0
25°	2086.2	1982.9	1924.6	1863.6	1760.3	1645.1	1532.5	1462.3	1374.9	1299.4	1229.2
27.5°	2087.5	1981.5	1910.0	1846.4	1732.5	1600.1	1484.8	1410.6	1314.0	1226.5	1156.3
30°	2074.3	1967.0	1902.1	1833.2	1706.0	1559.0	1426.5	1344.4	1241.1	1153.7	1080.8
32.5°	2034.5	1937.8	1884.8	1809.3	1671.6	1502.0	1370.9	1279.5	1170.9	1084.8	1014.6
35°	1968.3	1902.1	1843.8	1773.6	1626.6	1449.1	1315.3	1208.0	1098.1	1015.9	949.7
37.5°	1886.2	1850.4	1796.1	1727.2	1574.9	1401.4	1253.0	1133.8	1023.9	944.4	879.5
40°	1774.9	1784.2	1731.2	1668.9	1514.0	1336.5	1172.2	1058.3	955.0	880.8	817.2
42.5°	1654.4	1692.8	1662.3	1602.7	1446.4	1264.9	1112.6	986.8	886.1	809.3	756.3
45°	1524.6	1590.8	1572.2	1528.5	1376.2	1189.4	1027.9	906.0	817.2	743.1	696.7
47.5°	1382.8	1476.9	1476.9	1445.1	1298.1	1113.9	955.0	830.5	743.1	690.1	645.1
50°	1238.5	1344.4	1361.6	1340.4	1210.6	1027.9	866.3	753.7	678.2	626.5	593.4
52.5°	1087.5	1210.6	1242.4	1231.8	1117.9	945.7	793.4	683.5	614.6	569.6	540.4
55°	943.1	1086.1	1120.6	1124.5	1018.6	855.7	712.6	615.9	549.7	519.2	494.1
57.5°	806.7	944.4	982.8	989.4	917.9	773.5	637.1	552.3	492.7	467.6	447.7
60°	690.1	805.3	855.7	870.2	808.0	678.2	566.9	484.8	439.8	415.9	397.4
62.5°	594.7	687.4	740.4	744.4	716.6	594.7	494.1	425.2	386.8	365.6	356.3
65°	502.0	585.5	617.2	633.1	610.6	515.3	426.5	369.6	339.1	320.5	311.3
67.5°	427.8	480.8	507.3	528.5	506.0	434.5	362.9	316.6	294.1	275.5	270.2
70°	351.0	394.7	414.6	435.8	415.9	361.6	309.9	267.6	247.7	233.1	226.5
72.5°	280.8	315.2	333.8	347.0	335.1	290.1	247.7	218.6	204.0	193.4	189.4
75°	222.5	246.4	257.0	266.2	260.9	226.5	200.0	176.2	162.9	153.6	151.0
77.5°	169.5	186.8	198.7	201.3	194.7	172.2	149.7	135.1	124.5	119.2	116.6
80°	120.5	131.1	137.8	141.7	135.1	125.8	109.9	99.3	90.1	83.4	82.1
82.5°	80.8	86.1	91.4	90.1	87.4	79.5	70.2	64.9	60.9	55.6	55.6
85°	46.4	47.7	50.3	51.7	50.3	45.0	39.7	37.1	34.4	30.5	30.5
87.5°	19.9	21.2	21.2	22.5	19.9	19.9	17.2	14.6	14.6	13.2	11.9
90°	7.7	6.8	6.3	5.7	4.4	3.1	1.8	0.5	1.8	3.1	4.4
92.5°	11.5	11.2	11.0	11.2	11.7	12.2	12.6	13.1	12.6	12.2	11.7
95°	18.0	17.2	16.8	18.7	22.6	26.4	30.3	34.1	30.3	26.4	22.6
97.5°	21.2	19.3	18.4	23.2	32.7	42.3	51.8	61.4	51.8	42.3	32.7
100°	24.0	22.0	21.0	29.0	45.0	61.0	77.0	93.0	77.0	61.0	45.0
102.5°	94.7	116.0	126.6	126.7	126.9	127.2	127.4	127.6	127.4	127.2	126.9
105°	127.6	159.5	175.4	173.6	170.1	166.6	163.1	159.6	163.1	166.6	170.1
107.5°	151.1	190.4	210.1	208.6	205.7	202.8	199.8	196.9	199.8	202.8	205.7
110°	193.1	226.8	243.7	242.5	240.0	237.5	235.1	232.6	235.1	237.5	240.0

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	272.7	274.7	275.7	274.7	272.6	270.5	268.4	266.3	268.4	270.5	272.6
115°	315.3	312.4	310.9	309.9	307.9	306.0	304.0	302.0	304.0	306.0	307.9
117.5°	346.5	344.5	343.5	342.3	340.0	337.7	335.3	333.0	335.3	337.7	340.0
120°	378.6	376.5	375.5	374.6	372.9	371.1	369.4	367.6	369.4	371.1	372.9
122.5°	408.9	406.6	405.4	404.5	402.6	400.7	398.9	397.0	398.9	400.7	402.6
125°	437.1	434.9	433.8	433.0	431.5	430.0	428.5	427.0	428.5	430.0	431.5
127.5°	464.2	462.5	461.6	460.8	459.2	457.5	455.9	454.3	455.9	457.5	459.2
130°	490.3	489.0	488.4	487.5	485.6	483.7	481.9	480.0	481.9	483.7	485.6
132.5°	515.0	513.7	513.1	512.3	510.8	509.3	507.8	506.3	507.8	509.3	510.8
135°	538.3	537.2	536.7	535.8	533.9	532.0	530.2	528.3	530.2	532.0	533.9
137.5°	559.5	558.3	557.7	557.0	555.6	554.2	552.8	551.4	552.8	554.2	555.6
140°	580.1	578.8	578.2	577.7	576.8	575.9	574.9	574.0	574.9	575.9	576.8
142.5°	598.9	597.4	596.6	596.2	595.4	594.5	593.7	592.9	593.7	594.5	595.4
145°	615.3	613.3	612.3	612.4	612.5	612.6	612.8	612.9	612.8	612.6	612.5
147.5°	631.6	629.6	628.6	628.8	629.1	629.5	629.8	630.2	629.8	629.5	629.1
150°	646.1	644.2	643.3	643.7	644.5	645.4	646.2	647.0	646.2	645.4	644.5
152.5°	659.6	657.9	657.0	657.5	658.4	659.3	660.3	661.2	660.3	659.3	658.4
155°	672.2	670.8	670.1	670.6	671.7	672.7	673.8	674.8	673.8	672.7	671.7
157.5°	683.3	682.2	681.7	682.2	683.1	684.0	685.0	685.9	685.0	684.0	683.1
160°	693.2	692.5	692.2	692.5	693.2	693.9	694.6	695.3	694.6	693.9	693.2
162.5°	701.5	700.9	700.6	700.9	701.6	702.3	703.0	703.7	703.0	702.3	701.6
165°	708.4	708.1	707.9	708.3	709.0	709.7	710.4	711.1	710.4	709.7	709.0
167.5°	714.2	713.9	713.7	714.0	714.7	715.4	716.1	716.8	716.1	715.4	714.7
170°	718.8	718.5	718.4	718.8	719.5	720.2	720.9	721.6	720.9	720.2	719.5
172.5°	721.9	721.7	721.6	721.9	722.6	723.3	724.0	724.7	724.0	723.3	722.6
175°	724.0	723.8	723.7	724.1	724.9	725.8	726.6	727.4	726.6	725.8	724.9
177.5°	724.9	724.8	724.7	725.1	725.9	726.8	727.6	728.4	727.6	726.8	725.9
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1704.7	1711.3	1710.0	1696.8	1682.2	1670.3	1647.7	1650.4	1642.4	1643.8	1651.7
5°	1662.3	1662.3	1657.0	1638.5	1614.6	1601.4	1576.2	1569.6	1553.7	1552.4	1551.1
7.5°	1617.3	1610.7	1604.0	1577.5	1548.4	1527.2	1492.8	1484.8	1468.9	1458.3	1453.0
10°	1564.3	1555.0	1541.8	1511.3	1475.6	1449.1	1413.3	1402.7	1372.2	1359.0	1351.0
12.5°	1506.0	1500.7	1479.5	1454.4	1396.1	1366.9	1315.3	1325.9	1295.4	1268.9	1264.9
15°	1447.7	1427.9	1415.9	1374.9	1304.7	1291.4	1250.4	1229.2	1201.4	1180.2	1180.2
17.5°	1390.8	1360.3	1333.8	1290.1	1238.5	1201.4	1170.9	1160.3	1125.9	1104.7	1100.7
20°	1315.3	1280.8	1274.2	1212.0	1176.2	1135.1	1106.0	1079.5	1054.3	1045.1	1038.4
22.5°	1243.8	1204.0	1193.4	1140.4	1104.7	1063.6	1034.5	1015.9	997.4	990.8	978.8
25°	1166.9	1143.1	1127.2	1070.2	1030.5	992.1	972.2	959.0	941.8	940.4	932.5
27.5°	1092.8	1070.2	1054.3	1000.0	970.9	935.1	919.2	904.7	895.4	891.4	887.5
30°	1029.2	1004.0	985.5	945.7	910.0	880.8	867.6	858.3	853.0	846.4	845.1
32.5°	959.0	944.4	919.2	888.8	861.0	833.1	825.2	818.6	810.6	808.0	806.7
35°	899.4	879.5	863.6	829.2	817.2	793.4	784.1	778.8	768.2	765.6	762.9
37.5°	841.1	822.5	805.3	784.1	761.6	748.4	743.1	735.1	729.8	731.2	728.5
40°	782.8	768.2	755.0	732.5	719.2	712.6	702.0	694.1	691.4	692.7	691.4
42.5°	725.9	712.6	704.7	687.4	674.2	667.6	661.0	653.0	657.0	657.0	661.0
45°	674.2	662.3	657.0	643.7	635.8	625.2	618.6	617.2	622.5	621.2	621.2
47.5°	621.2	617.2	610.6	598.7	588.1	581.5	580.2	580.2	585.5	588.1	586.8
50°	580.2	572.2	564.3	555.0	547.0	544.4	540.4	543.1	548.4	548.4	551.0
52.5°	528.5	523.2	520.5	512.6	507.3	507.3	507.3	508.6	512.6	516.6	515.3
55°	483.5	479.5	476.8	472.9	466.2	467.6	466.2	468.9	472.9	476.8	479.5
57.5°	435.8	434.5	431.8	425.2	425.2	423.9	427.8	429.2	435.8	438.4	442.4
60°	393.4	389.4	389.4	384.1	384.1	384.1	388.1	392.1	397.4	398.7	401.3
62.5°	348.4	348.4	347.0	343.1	343.1	347.0	348.4	353.7	356.3	356.3	360.3
65°	306.0	304.6	303.3	304.6	306.0	306.0	309.9	312.6	315.2	316.6	317.9
67.5°	263.6	262.3	264.9	263.6	266.2	271.5	270.2	274.2	278.2	278.2	279.5
70°	223.8	226.5	225.2	227.8	226.5	229.1	233.1	234.4	234.4	235.8	239.7
72.5°	186.8	186.8	186.8	185.4	186.8	189.4	192.1	193.4	196.0	197.4	201.3
75°	151.0	151.0	148.3	151.0	151.0	153.6	156.3	156.3	156.3	158.9	162.9
77.5°	113.9	115.2	113.9	116.6	116.6	117.9	120.5	119.2	121.9	123.2	124.5
80°	83.4	82.1	82.1	82.1	83.4	83.4	86.1	87.4	87.4	91.4	88.7
82.5°	53.0	54.3	53.0	54.3	54.3	55.6	54.3	55.6	57.0	59.6	58.3
85°	30.5	29.1	29.1	30.5	29.1	29.1	30.5	29.1	30.5	29.1	30.5
87.5°	11.9	10.6	10.6	10.6	10.6	9.3	9.3	7.9	7.9	7.9	6.6
90°	5.7	6.3	6.8	7.7	8.6	9.6	10.5	11.1	11.7	12.2	12.8
92.5°	11.2	11.0	11.2	11.5	11.9	12.2	12.6	12.8	13.1	13.3	13.6
95°	18.7	16.8	17.2	18.0	18.9	19.7	20.5	21.1	21.7	22.2	22.8
97.5°	23.2	18.4	19.3	21.2	23.1	24.9	26.8	27.2	27.5	27.9	28.2
100°	29.0	21.0	22.0	24.0	25.9	27.9	29.9	30.8	31.8	32.7	33.6
102.5°	126.7	126.6	116.0	94.7	73.5	52.2	31.0	32.3	33.6	34.9	36.2
105°	173.6	175.4	159.5	127.6	95.7	63.9	32.0	33.3	34.6	35.9	37.2
107.5°	208.6	210.1	190.4	151.1	111.8	72.4	33.1	34.4	35.7	37.0	38.3
110°	242.5	243.7	226.8	193.1	159.4	125.6	91.9	80.2	68.6	56.9	45.2

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	274.7	275.7	274.7	272.7	270.8	268.8	266.8	216.5	166.2	115.9	65.6
115°	309.9	310.9	312.4	315.3	318.2	321.1	324.0	270.0	216.0	161.9	107.9
117.5°	342.3	343.5	344.5	346.5	348.4	350.4	352.4	335.7	319.0	302.3	285.6
120°	374.6	375.5	376.5	378.6	380.7	382.8	384.9	386.3	387.7	389.1	390.5
122.5°	404.5	405.4	406.6	408.9	411.2	413.6	415.9	416.6	417.3	418.0	418.7
125°	433.0	433.8	434.9	437.1	439.4	441.6	443.8	444.6	445.4	446.2	447.0
127.5°	460.8	461.6	462.5	464.2	466.0	467.7	469.5	470.7	471.8	473.0	474.1
130°	487.5	488.4	489.0	490.3	491.6	492.9	494.2	495.5	496.8	498.1	499.4
132.5°	512.3	513.1	513.7	515.0	516.3	517.6	518.9	519.9	521.0	522.0	523.1
135°	535.8	536.7	537.2	538.3	539.3	540.4	541.4	542.6	543.8	544.9	546.1
137.5°	557.0	557.7	558.3	559.5	560.6	561.8	563.0	564.2	565.3	566.5	567.6
140°	577.7	578.2	578.8	580.1	581.4	582.7	584.0	585.0	586.1	587.1	588.2
142.5°	596.2	596.6	597.4	598.9	600.4	601.9	603.4	604.3	605.3	606.2	607.1
145°	612.4	612.3	613.3	615.3	617.3	619.3	621.3	622.1	622.9	623.7	624.5
147.5°	628.8	628.6	629.6	631.6	633.5	635.5	637.5	638.1	638.7	639.3	639.9
150°	643.7	643.3	644.2	646.1	648.0	649.8	651.7	652.4	653.1	653.8	654.5
152.5°	657.5	657.0	657.9	659.6	661.4	663.1	664.9	665.6	666.3	667.0	667.7
155°	670.6	670.1	670.8	672.2	673.6	675.0	676.4	677.1	677.8	678.5	679.2
157.5°	682.2	681.7	682.2	683.3	684.3	685.4	686.4	687.2	688.0	688.9	689.7
160°	692.5	692.2	692.5	693.2	693.9	694.6	695.3	696.0	696.7	697.4	698.1
162.5°	700.9	700.6	700.9	701.5	702.0	702.6	703.2	704.0	704.8	705.7	706.5
165°	708.3	707.9	708.1	708.4	708.8	709.1	709.5	710.3	711.1	712.0	712.8
167.5°	714.0	713.7	713.9	714.2	714.6	714.9	715.3	716.1	716.9	717.7	718.5
170°	718.8	718.4	718.5	718.8	719.0	719.3	719.5	720.3	721.1	722.0	722.8
172.5°	721.9	721.6	721.7	721.9	722.2	722.4	722.6	723.4	724.2	725.1	725.9
175°	724.1	723.7	723.8	724.0	724.3	724.5	724.7	725.5	726.3	727.2	728.0
177.5°	725.1	724.7	724.8	724.9	725.0	725.2	725.3	726.1	726.9	727.7	728.5
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1642.4	1646.4	1637.1	1634.5	1637.1	1627.9	1630.5	1633.2	1633.2	1637.1	1639.8
5°	1547.1	1541.8	1532.5	1529.9	1527.2	1531.2	1528.5	1532.5	1533.8	1543.1	1544.4
7.5°	1453.0	1445.1	1437.1	1429.2	1426.5	1419.9	1426.5	1426.5	1435.8	1433.2	1439.8
10°	1341.8	1340.4	1329.9	1325.9	1320.6	1310.0	1324.6	1320.6	1327.2	1339.1	1341.8
12.5°	1259.6	1245.1	1251.7	1233.2	1239.8	1229.2	1230.5	1230.5	1241.1	1242.4	1239.8
15°	1181.5	1169.6	1152.4	1144.4	1140.4	1135.1	1152.4	1153.7	1145.7	1164.3	1157.7
17.5°	1102.0	1102.0	1086.1	1082.2	1071.6	1076.9	1074.2	1075.5	1072.9	1086.1	1092.8
20°	1033.2	1026.5	1021.2	1022.6	1009.3	1006.7	1004.0	1006.7	1015.9	1025.2	1027.9
22.5°	977.5	973.5	960.3	963.0	952.4	956.3	953.7	960.3	961.6	961.6	970.9
25°	924.5	919.2	920.6	915.3	911.3	911.3	907.3	911.3	916.6	919.2	920.6
27.5°	884.8	880.8	874.2	870.2	872.9	866.3	871.6	875.5	875.5	872.9	875.5
30°	837.1	839.8	839.8	826.5	831.8	829.2	833.1	835.8	835.8	837.1	834.5
32.5°	805.3	797.4	796.1	794.7	794.7	789.4	789.4	793.4	794.7	796.1	800.0
35°	762.9	762.9	756.3	760.3	755.0	756.3	755.0	756.3	759.0	755.0	759.0
37.5°	724.5	725.9	723.2	725.9	727.2	724.5	721.9	727.2	724.5	724.5	721.9
40°	691.4	690.1	691.4	691.4	691.4	692.7	690.1	690.1	690.1	687.4	684.8
42.5°	663.6	655.7	658.3	659.6	655.7	655.7	657.0	655.7	659.6	651.7	651.7
45°	623.9	621.2	622.5	622.5	625.2	621.2	623.9	625.2	621.2	619.9	617.2
47.5°	588.1	590.8	588.1	590.8	590.8	593.4	588.1	589.4	590.8	585.5	581.5
50°	552.3	552.3	556.3	555.0	556.3	553.7	553.7	552.3	553.7	551.0	547.0
52.5°	519.2	515.3	521.9	520.5	519.2	517.9	516.6	517.9	515.3	512.6	512.6
55°	478.2	478.2	482.1	483.5	483.5	480.8	478.2	479.5	478.2	476.8	475.5
57.5°	445.0	439.8	442.4	443.7	443.7	439.8	442.4	439.8	439.8	441.1	437.1
60°	402.7	402.7	400.0	404.0	404.0	401.3	401.3	402.7	400.0	398.7	397.4
62.5°	357.6	359.0	362.9	364.3	365.6	362.9	360.3	361.6	361.6	357.6	359.0
65°	319.2	321.9	327.2	325.8	323.2	324.5	321.9	323.2	319.2	320.5	316.6
67.5°	282.1	280.8	282.1	282.1	284.8	283.5	280.8	280.8	279.5	283.5	279.5
70°	242.4	242.4	242.4	242.4	243.7	245.0	242.4	239.7	241.1	238.4	237.1
72.5°	201.3	202.7	201.3	204.0	200.0	202.7	202.7	201.3	200.0	200.0	200.0
75°	162.9	165.6	161.6	162.9	161.6	164.2	162.9	162.9	160.3	158.9	160.3
77.5°	124.5	125.8	123.2	124.5	123.2	124.5	124.5	123.2	123.2	123.2	123.2
80°	88.7	90.1	88.7	87.4	86.1	88.7	86.1	87.4	88.7	87.4	90.1
82.5°	57.0	57.0	55.6	57.0	54.3	54.3	55.6	55.6	54.3	57.0	54.3
85°	27.8	27.8	30.5	27.8	26.5	26.5	26.5	27.8	26.5	29.1	27.8
87.5°	6.6	5.3	6.6	6.6	5.3	5.3	6.6	5.3	6.6	7.9	5.3
90°	13.1	13.2	13.5	13.7	14.0	14.2	14.0	13.7	13.5	13.2	13.1
92.5°	13.7	13.8	13.9	14.0	14.1	14.2	14.1	14.0	13.9	13.8	13.7
95°	23.1	23.0	22.9	22.8	22.7	22.6	22.7	22.8	22.9	23.0	23.1
97.5°	28.4	28.5	28.6	28.7	28.8	28.9	28.8	28.7	28.6	28.5	28.4
100°	34.1	34.2	34.5	34.7	35.0	35.2	35.0	34.7	34.5	34.2	34.1
102.5°	36.8	37.0	37.3	37.6	38.0	38.3	38.0	37.6	37.3	37.0	36.8
105°	37.8	38.0	38.5	39.0	39.4	39.9	39.4	39.0	38.5	38.0	37.8
107.5°	38.9	39.1	39.6	40.1	40.5	41.0	40.5	40.1	39.6	39.1	38.9
110°	39.4	39.6	40.1	40.6	41.0	41.5	41.0	40.6	40.1	39.6	39.4

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	40.4	40.6	40.9	41.3	41.6	42.0	41.6	41.3	40.9	40.6	40.4
115°	80.9	76.7	68.3	59.9	51.5	43.1	51.5	59.9	68.3	76.7	80.9
117.5°	277.3	262.0	231.4	200.9	170.3	139.7	170.3	200.9	231.4	262.0	277.3
120°	391.2	383.3	367.6	351.9	336.1	320.4	336.1	351.9	367.6	383.3	391.2
122.5°	419.1	419.2	419.3	419.4	419.5	419.6	419.5	419.4	419.3	419.2	419.1
125°	447.4	447.6	447.9	448.3	448.6	449.0	448.6	448.3	447.9	447.6	447.4
127.5°	474.7	474.8	474.9	475.0	475.2	475.3	475.2	475.0	474.9	474.8	474.7
130°	500.0	499.9	499.8	499.7	499.5	499.4	499.5	499.7	499.8	499.9	500.0
132.5°	523.6	523.5	523.4	523.3	523.2	523.1	523.2	523.3	523.4	523.5	523.6
135°	546.7	546.6	546.3	546.1	545.8	545.6	545.8	546.1	546.3	546.6	546.7
137.5°	568.2	568.0	567.7	567.4	567.0	566.7	567.0	567.4	567.7	568.0	568.2
140°	588.7	588.4	587.8	587.3	586.7	586.1	586.7	587.3	587.8	588.4	588.7
142.5°	607.6	607.3	606.7	606.2	605.6	605.0	605.6	606.2	606.7	607.3	607.6
145°	624.9	624.6	624.0	623.5	622.9	622.3	622.9	623.5	624.0	624.6	624.9
147.5°	640.2	640.0	639.5	639.0	638.6	638.1	638.6	639.0	639.5	640.0	640.2
150°	654.9	654.6	654.0	653.5	652.9	652.3	652.9	653.5	654.0	654.6	654.9
152.5°	668.0	667.6	666.8	665.9	665.1	664.3	665.1	665.9	666.8	667.6	668.0
155°	679.6	679.1	678.2	677.3	676.3	675.4	676.3	677.3	678.2	679.1	679.6
157.5°	690.1	689.6	688.7	687.8	686.8	685.9	686.8	687.8	688.7	689.6	690.1
160°	698.5	698.1	697.3	696.4	695.6	694.8	695.6	696.4	697.3	698.1	698.5
162.5°	706.9	706.4	705.3	704.2	703.2	702.1	703.2	704.2	705.3	706.4	706.9
165°	713.2	712.8	712.0	711.1	710.3	709.5	710.3	711.1	712.0	712.8	713.2
167.5°	718.9	718.4	717.3	716.3	715.2	714.2	715.2	716.3	717.3	718.4	718.9
170°	723.2	722.7	721.6	720.5	719.5	718.4	719.5	720.5	721.6	722.7	723.2
172.5°	726.3	725.8	724.7	723.7	722.6	721.6	722.6	723.7	724.7	725.8	726.3
175°	728.4	727.8	726.7	725.5	724.4	723.2	724.4	725.5	726.7	727.8	728.4
177.5°	728.9	728.4	727.3	726.3	725.2	724.2	725.2	726.3	727.3	728.4	728.9
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1635.8	1646.4	1642.4	1627.9	1645.1	1645.1	1657.0	1657.0	1671.6	1676.9	1684.8
5°	1543.1	1551.1	1557.7	1551.1	1563.0	1581.5	1592.1	1601.4	1621.3	1629.2	1641.1
7.5°	1443.8	1458.3	1465.0	1465.0	1484.8	1506.0	1527.2	1540.5	1568.3	1578.9	1590.8
10°	1347.1	1364.3	1377.5	1376.2	1409.3	1422.6	1449.1	1479.5	1507.3	1523.2	1540.5
12.5°	1245.1	1254.4	1272.9	1299.4	1307.3	1331.2	1361.6	1400.1	1450.4	1465.0	1490.1
15°	1160.3	1185.5	1200.0	1212.0	1230.5	1253.0	1286.1	1323.2	1373.6	1405.4	1431.8
17.5°	1088.8	1121.9	1131.2	1128.5	1152.4	1186.8	1225.2	1253.0	1298.1	1336.5	1361.6
20°	1030.5	1043.7	1059.6	1066.3	1084.8	1121.9	1159.0	1190.8	1227.9	1258.3	1287.5
22.5°	972.2	982.8	996.1	1008.0	1022.6	1043.7	1079.5	1119.2	1155.0	1184.2	1217.3
25°	924.5	931.2	943.1	952.4	968.2	982.8	1008.0	1051.7	1094.1	1111.3	1140.4
27.5°	878.2	883.5	891.4	902.0	910.0	924.5	947.1	982.8	1026.5	1043.7	1083.5
30°	837.1	841.1	849.0	854.3	858.3	875.5	892.7	920.6	953.7	977.5	1006.7
32.5°	798.7	802.7	810.6	812.0	817.2	826.5	842.4	867.6	896.7	916.6	941.8
35°	756.3	759.0	766.9	769.6	773.5	781.5	793.4	812.0	838.4	853.0	875.5
37.5°	723.2	721.9	727.2	731.2	736.5	740.4	744.4	762.9	782.8	796.1	813.3
40°	687.4	684.8	686.1	691.4	694.1	699.4	699.4	717.9	731.2	741.7	755.0
42.5°	651.7	650.4	647.7	650.4	653.0	654.3	655.7	668.9	682.1	691.4	706.0
45°	615.9	614.6	611.9	613.3	613.3	615.9	619.9	625.2	634.5	642.4	650.4
47.5°	582.8	580.2	576.2	574.9	577.5	577.5	577.5	582.8	592.1	594.7	602.7
50°	548.4	544.4	539.1	536.4	536.4	535.1	537.8	539.1	547.0	549.7	556.3
52.5°	511.3	508.6	503.3	498.0	499.4	496.7	498.0	499.4	502.0	506.0	510.0
55°	474.2	468.9	464.9	463.6	459.6	459.6	455.6	460.9	459.6	460.9	466.2
57.5°	438.4	433.1	426.5	423.9	419.9	418.6	415.9	414.6	415.9	419.9	423.9
60°	396.0	393.4	389.4	385.4	382.8	378.8	376.2	376.2	374.8	374.8	376.2
62.5°	355.0	353.7	348.4	347.0	344.4	341.7	337.8	335.1	335.1	337.8	339.1
65°	315.2	313.9	309.9	308.6	302.0	299.3	298.0	296.7	294.1	294.1	294.1
67.5°	278.2	274.2	274.2	267.6	262.3	259.6	257.0	255.6	255.6	255.6	257.0
70°	237.1	237.1	233.1	229.1	223.8	225.2	221.2	217.2	217.2	214.6	215.9
72.5°	197.4	196.0	192.1	190.7	186.8	182.8	180.1	182.8	178.8	177.5	178.8
75°	158.9	157.6	155.0	152.3	153.6	149.7	145.7	144.4	144.4	141.7	141.7
77.5°	121.9	124.5	119.2	117.9	115.2	112.6	111.3	109.9	109.9	109.9	112.6
80°	84.8	86.1	86.1	83.4	84.8	80.8	80.8	80.8	76.8	78.1	79.5
82.5°	54.3	54.3	53.0	54.3	53.0	53.0	51.7	51.7	50.3	50.3	51.7
85°	30.5	29.1	27.8	30.5	29.1	29.1	27.8	27.8	27.8	27.8	27.8
87.5°	6.6	7.9	7.9	7.9	7.9	9.3	9.3	9.3	10.6	10.6	10.6
90°	12.8	12.2	11.7	11.1	10.5	9.6	8.6	7.7	6.8	6.3	5.7
92.5°	13.6	13.3	13.1	12.8	12.6	12.2	11.9	11.5	11.2	11.0	11.2
95°	22.8	22.2	21.7	21.1	20.5	19.7	18.9	18.0	17.2	16.8	18.7
97.5°	28.2	27.9	27.5	27.2	26.8	24.9	23.1	21.2	19.3	18.4	23.2
100°	33.6	32.7	31.8	30.8	29.9	27.9	25.9	24.0	22.0	21.0	29.0
102.5°	36.2	34.9	33.6	32.3	31.0	52.2	73.5	94.7	116.0	126.6	126.7
105°	37.2	35.9	34.6	33.3	32.0	63.9	95.7	127.6	159.5	175.4	173.6
107.5°	38.3	37.0	35.7	34.4	33.1	72.4	111.8	151.1	190.4	210.1	208.6
110°	45.2	56.9	68.6	80.2	91.9	125.6	159.4	193.1	226.8	243.7	242.5

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	65.6	115.9	166.2	216.5	266.8	268.8	270.8	272.7	274.7	275.7	274.7
115°	107.9	161.9	216.0	270.0	324.0	321.1	318.2	315.3	312.4	310.9	309.9
117.5°	285.6	302.3	319.0	335.7	352.4	350.4	348.4	346.5	344.5	343.5	342.3
120°	390.5	389.1	387.7	386.3	384.9	382.8	380.7	378.6	376.5	375.5	374.6
122.5°	418.7	418.0	417.3	416.6	415.9	413.6	411.2	408.9	406.6	405.4	404.5
125°	447.0	446.2	445.4	444.6	443.8	441.6	439.4	437.1	434.9	433.8	433.0
127.5°	474.1	473.0	471.8	470.7	469.5	467.7	466.0	464.2	462.5	461.6	460.8
130°	499.4	498.1	496.8	495.5	494.2	492.9	491.6	490.3	489.0	488.4	487.5
132.5°	523.1	522.0	521.0	519.9	518.9	517.6	516.3	515.0	513.7	513.1	512.3
135°	546.1	544.9	543.8	542.6	541.4	540.4	539.3	538.3	537.2	536.7	535.8
137.5°	567.6	566.5	565.3	564.2	563.0	561.8	560.6	559.5	558.3	557.7	557.0
140°	588.2	587.1	586.1	585.0	584.0	582.7	581.4	580.1	578.8	578.2	577.7
142.5°	607.1	606.2	605.3	604.3	603.4	601.9	600.4	598.9	597.4	596.6	596.2
145°	624.5	623.7	622.9	622.1	621.3	619.3	617.3	615.3	613.3	612.3	612.4
147.5°	639.9	639.3	638.7	638.1	637.5	635.5	633.5	631.6	629.6	628.6	628.8
150°	654.5	653.8	653.1	652.4	651.7	649.8	648.0	646.1	644.2	643.3	643.7
152.5°	667.7	667.0	666.3	665.6	664.9	663.1	661.4	659.6	657.9	657.0	657.5
155°	679.2	678.5	677.8	677.1	676.4	675.0	673.6	672.2	670.8	670.1	670.6
157.5°	689.7	688.9	688.0	687.2	686.4	685.4	684.3	683.3	682.2	681.7	682.2
160°	698.1	697.4	696.7	696.0	695.3	694.6	693.9	693.2	692.5	692.2	692.5
162.5°	706.5	705.7	704.8	704.0	703.2	702.6	702.0	701.5	700.9	700.6	700.9
165°	712.8	712.0	711.1	710.3	709.5	709.1	708.8	708.4	708.1	707.9	708.3
167.5°	718.5	717.7	716.9	716.1	715.3	714.9	714.6	714.2	713.9	713.7	714.0
170°	722.8	722.0	721.1	720.3	719.5	719.3	719.0	718.8	718.5	718.4	718.8
172.5°	725.9	725.1	724.2	723.4	722.6	722.4	722.2	721.9	721.7	721.6	721.9
175°	728.0	727.2	726.3	725.5	724.7	724.5	724.3	724.0	723.8	723.7	724.1
177.5°	728.5	727.7	726.9	726.1	725.3	725.2	725.0	724.9	724.8	724.7	725.1
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1723.2	1723.2	1723.2	1723.2
2.5°	1691.5	1691.5	1711.3	1732.5
5°	1654.4	1663.6	1695.4	1724.6
7.5°	1618.6	1634.5	1674.2	1711.3
10°	1574.9	1596.1	1645.1	1688.8
12.5°	1532.5	1552.4	1609.3	1658.3
15°	1472.9	1498.1	1559.0	1619.9
17.5°	1413.3	1438.5	1512.6	1584.2
20°	1343.1	1376.2	1459.7	1555.0
22.5°	1278.2	1319.3	1412.0	1488.8
25°	1206.7	1270.2	1356.3	1455.7
27.5°	1143.1	1206.7	1294.1	1394.8
30°	1071.6	1136.5	1226.5	1319.3
32.5°	1002.7	1062.3	1149.7	1263.6
35°	931.2	988.1	1072.9	1188.1
37.5°	866.3	921.9	1014.6	1120.6
40°	802.7	861.0	940.4	1046.4
42.5°	743.1	794.7	866.3	972.2
45°	688.8	725.9	792.1	891.4
47.5°	631.8	664.9	725.9	825.2
50°	578.8	606.6	659.6	752.3
52.5°	527.2	551.0	600.0	674.2
55°	480.8	503.3	539.1	611.9
57.5°	433.1	450.3	484.8	543.1
60°	386.8	402.7	430.5	478.2
62.5°	340.4	353.7	380.1	418.6
65°	299.3	309.9	329.8	362.9
67.5°	259.6	266.2	282.1	308.6
70°	221.2	226.5	239.7	260.9
72.5°	180.1	185.4	200.0	214.6
75°	145.7	147.0	157.6	169.5
77.5°	113.9	112.6	120.5	129.8
80°	78.1	82.1	88.7	92.7
82.5°	53.0	54.3	57.0	59.6
85°	29.1	30.5	30.5	34.4
87.5°	11.9	13.2	13.2	14.6
90°	4.4	3.1	1.8	0.5
92.5°	11.7	12.2	12.6	13.1
95°	22.6	26.4	30.3	34.1
97.5°	32.7	42.3	51.8	61.4
100°	45.0	61.0	77.0	93.0
102.5°	126.9	127.2	127.4	127.6
105°	170.1	166.6	163.1	159.6
107.5°	205.7	202.8	199.8	196.9
110°	240.0	237.5	235.1	232.6



TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	272.6	270.5	268.4	266.3
115°	307.9	306.0	304.0	302.0
117.5°	340.0	337.7	335.3	333.0
120°	372.9	371.1	369.4	367.6
122.5°	402.6	400.7	398.9	397.0
125°	431.5	430.0	428.5	427.0
127.5°	459.2	457.5	455.9	454.3
130°	485.6	483.7	481.9	480.0
132.5°	510.8	509.3	507.8	506.3
135°	533.9	532.0	530.2	528.3
137.5°	555.6	554.2	552.8	551.4
140°	576.8	575.9	574.9	574.0
142.5°	595.4	594.5	593.7	592.9
145°	612.5	612.6	612.8	612.9
147.5°	629.1	629.5	629.8	630.2
150°	644.5	645.4	646.2	647.0
152.5°	658.4	659.3	660.3	661.2
155°	671.7	672.7	673.8	674.8
157.5°	683.1	684.0	685.0	685.9
160°	693.2	693.9	694.6	695.3
162.5°	701.6	702.3	703.0	703.7
165°	709.0	709.7	710.4	711.1
167.5°	714.7	715.4	716.1	716.8
170°	719.5	720.2	720.9	721.6
172.5°	722.6	723.3	724.0	724.7
175°	724.9	725.8	726.6	727.4
177.5°	725.9	726.8	727.6	728.4
180°	725.8	725.8	725.8	725.8

TEST NUMBER: P999122

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.56	19.52	19.39	20.37	21.42	16.05	17.01	16.88	17.86	18.92
	3H	19.38	20.23	20.22	21.09	22.18	17.40	18.26	18.25	19.12	20.20
	4H	19.55	20.36	20.41	21.22	22.32	17.87	18.68	18.73	19.54	20.64
	6H	19.60	20.34	20.47	21.22	22.33	18.18	18.93	19.06	19.80	20.91
	8H	19.58	20.29	20.46	21.18	22.29	18.27	18.98	19.15	19.87	20.98
	12H	19.55	20.22	20.44	21.11	22.24	18.31	18.99	19.20	19.87	21.01
4H	2H	18.61	19.42	19.48	20.29	21.38	16.51	17.32	17.38	18.18	19.28
	3H	19.60	20.27	20.48	21.17	22.28	17.98	18.65	18.86	19.55	20.66
	4H	19.88	20.49	20.77	21.39	22.52	18.52	19.13	19.41	20.02	21.16
	6H	20.02	20.54	20.92	21.46	22.60	18.90	19.43	19.81	20.35	21.49
	8H	20.02	20.51	20.92	21.42	22.57	19.01	19.51	19.92	20.42	21.57
	12H	19.98	20.43	20.91	21.36	22.52	19.07	19.52	20.00	20.45	21.61
8H	4H	19.90	20.39	20.80	21.30	22.45	18.67	19.16	19.57	20.07	21.22
	6H	20.08	20.48	21.01	21.44	22.59	19.10	19.51	20.04	20.47	21.62
	8H	20.11	20.47	21.05	21.42	22.59	19.25	19.61	20.20	20.56	21.73
	12H	20.10	20.41	21.04	21.35	22.57	19.35	19.67	20.30	20.61	21.83
12H	4H	19.86	20.30	20.78	21.23	22.39	18.64	19.09	19.57	20.02	21.18
	6H	20.06	20.42	21.00	21.36	22.53	19.10	19.46	20.05	20.41	21.58
	8H	20.09	20.41	21.04	21.35	22.57	19.27	19.58	20.21	20.52	21.74