

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999123

Luminaire Tested: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999123
REPORT IS A COMBINATION OF REPORTS P984872 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5705.0 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67		
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	62	57		
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49		
3	86	77	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46	42		
4	79	68	60	54	74	65	58	52	58	53	48	52	48	44	46	43	40	37		
5	73	61	53	47	68	58	51	46	52	47	42	47	42	39	42	38	35	33		
6	67	55	47	41	63	53	45	40	48	42	37	43	38	34	38	35	31	29		
7	62	50	42	37	59	48	41	36	43	37	33	39	34	31	35	31	28	26		
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	23		
9	54	42	35	30	51	40	33	29	37	31	27	33	29	25	30	26	23	21		
10	51	39	32	27	48	37	31	26	34	28	24	31	26	23	28	24	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27277	27277	27277	27277
5°	27344	29085	27448	23140
10°	27026	31750	27195	19078
15°	26370	33490	26736	16069
20°	25958	31444	25958	13968
25°	25132	27013	25246	12490
30°	23771	21235	24223	11314
35°	22564	14684	22942	10351
40°	21178	11087	21419	9583
45°	19468	9111	19787	8756
50°	17990	7996	18024	8016
55°	16305	6814	16411	7211
60°	14511	5691	14711	6293
65°	12901	4629	13139	5374
70°	11299	3632	11589	4334
75°	9482	2638	9857	3143
80°	7401	1671	7928	1865
85°	4859	842	5241	623

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 28197 cd/sqm

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.1	2.9
10°-20°	477.7	8.4
20°-30°	693.3	12.2
30°-40°	730.9	12.8
40°-50°	646.8	11.3
50°-60°	516.4	9.1
60°-70°	350.8	6.1
70°-80°	179.5	3.1
80°-90°	44.3	0.8
90°-100°	42.1	0.7
100°-110°	133.7	2.3
110°-120°	228.8	4.0
120°-130°	300.9	5.3
130°-140°	337.8	5.9
140°-150°	331.2	5.8
150°-160°	277.9	4.9
160°-170°	184.3	3.2
170°-180°	64.4	1.1
0°-30°	1335.2	23.4
0°-40°	2066.1	36.2
0°-60°	3229.3	56.6
0°-90°	3803.9	66.7
90°-120°	404.6	7.1
90°-150°	1374.5	24.1
90°-180°	1901.0	33.3
0°-180°	5705.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1925	1731	1531	1725	163
15°	1620	2366	1642	1135	1620	458
25°	1456	1971	1462	911	1456	665
35°	1188	1073	1208	756	1188	743
45°	891	646	906	621	891	692
55°	612	454	616	481	612	546
65°	363	280	370	324	363	361
75°	170	138	176	164	170	182
85°	34	36	37	26	34	40
90°	1	20	1	20	1	4
95°	30	36	30	36	30	33
105°	123	127	123	127	123	130
115°	230	230	230	230	230	227
125°	334	335	334	335	334	298
135°	432	437	432	437	432	334
145°	524	530	524	530	524	328
155°	600	604	600	604	600	276
165°	652	653	652	653	652	184
175°	679	676	679	676	679	64
180°	680	680	680	680	680	

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1732.5	1736.5	1743.1	1744.4	1757.7	1768.3	1780.2	1780.2	1784.2	1782.8	1772.3
5°	1724.6	1736.5	1753.7	1768.3	1792.1	1802.7	1818.6	1830.5	1841.1	1849.1	1847.8
7.5°	1711.3	1732.5	1757.7	1785.5	1817.3	1835.8	1858.3	1879.5	1894.1	1907.4	1916.6
10°	1688.8	1724.6	1759.0	1796.1	1837.2	1862.3	1888.8	1916.6	1939.1	1964.3	1988.2
12.5°	1658.3	1710.0	1752.4	1801.4	1851.7	1879.5	1921.9	1943.1	1986.8	2050.4	2067.6
15°	1619.9	1690.1	1729.9	1792.1	1858.3	1880.9	1939.1	1973.6	2063.7	2103.4	2151.1
17.5°	1584.2	1662.3	1715.3	1786.8	1851.7	1895.4	1952.4	2022.6	2098.1	2155.0	2208.0
20°	1555.0	1630.5	1694.1	1773.6	1855.7	1911.3	1970.9	2055.7	2137.8	2196.1	2237.2
22.5°	1488.8	1585.5	1659.7	1748.4	1847.8	1924.6	1981.5	2074.3	2163.0	2198.8	2234.5
25°	1455.7	1539.1	1625.2	1725.9	1842.5	1933.8	1982.9	2086.2	2164.3	2177.6	2185.5
27.5°	1394.8	1488.8	1589.5	1704.7	1841.1	1918.0	1980.2	2074.3	2136.5	2127.2	2103.4
30°	1319.3	1434.5	1545.8	1670.3	1822.6	1906.0	1964.3	2050.4	2082.2	2034.5	1992.1
32.5°	1263.6	1372.2	1495.4	1639.8	1801.4	1880.9	1937.8	2005.4	2012.0	1925.9	1854.4
35°	1188.1	1308.7	1447.7	1600.1	1765.6	1837.2	1890.1	1931.2	1899.4	1778.9	1694.1
37.5°	1120.6	1239.8	1388.1	1543.1	1716.6	1786.8	1829.2	1835.8	1757.7	1651.7	1527.2
40°	1046.4	1169.6	1324.6	1487.5	1662.3	1723.2	1749.7	1729.9	1617.3	1494.1	1349.7
42.5°	972.2	1094.1	1261.0	1427.9	1593.4	1645.1	1655.7	1601.4	1463.6	1319.3	1152.4
45°	891.4	1018.6	1185.5	1353.7	1514.0	1543.1	1544.4	1466.3	1303.4	1152.4	997.4
47.5°	825.2	943.1	1108.7	1276.9	1412.0	1431.8	1423.9	1333.8	1156.3	986.8	851.7
50°	752.3	864.9	1029.2	1194.7	1310.0	1315.3	1295.4	1166.9	993.4	838.4	731.2
52.5°	674.2	788.1	939.1	1098.1	1201.4	1193.4	1155.0	1017.3	854.3	725.9	643.7
55°	611.9	712.6	854.3	1009.3	1082.2	1059.6	1017.3	876.9	748.4	639.8	568.2
57.5°	543.1	631.8	770.9	906.0	948.4	927.2	884.8	753.7	634.5	552.3	504.7
60°	478.2	559.0	680.8	793.4	826.5	804.0	755.0	637.1	551.0	482.1	446.4
62.5°	418.6	488.8	590.8	694.1	707.3	684.8	642.4	547.0	472.9	418.6	392.1
65°	362.9	429.2	511.3	589.4	601.3	577.5	533.8	464.9	402.7	368.2	343.1
67.5°	308.6	361.6	434.5	491.4	498.0	475.5	439.8	384.1	345.7	308.6	290.1
70°	260.9	300.7	357.6	404.0	406.6	385.4	366.9	316.6	287.4	260.9	246.4
72.5°	214.6	242.4	286.1	320.5	321.9	308.6	291.4	259.6	234.4	215.9	201.3
75°	169.5	193.4	219.9	250.3	249.0	238.4	225.2	205.3	184.1	172.2	165.6
77.5°	129.8	144.4	165.6	185.4	185.4	180.1	172.2	157.6	144.4	132.5	125.8
80°	92.7	102.0	119.2	125.8	128.5	127.2	120.5	109.9	104.6	95.4	92.7
82.5°	59.6	66.2	74.2	80.8	84.8	82.1	80.8	75.5	67.6	64.9	62.3
85°	34.4	37.1	41.1	45.0	46.4	45.0	47.7	43.7	39.7	39.7	38.4
87.5°	14.6	15.9	18.5	18.5	19.9	19.9	18.5	19.9	19.9	18.5	17.2
90°	0.6	2.1	3.7	5.2	6.7	7.5	8.9	11.7	14.5	17.3	20.1
92.5°	12.6	13.6	14.6	15.7	16.7	17.2	17.3	17.4	17.5	17.7	17.8
95°	29.8	31.1	32.4	33.7	35.0	35.6	35.7	36.0	36.2	36.5	36.7
97.5°	49.9	51.1	52.2	53.4	54.5	55.1	55.4	55.9	56.4	56.9	57.4
100°	72.9	73.9	74.9	76.0	77.0	77.5	77.7	78.1	78.4	78.8	79.2
102.5°	97.0	97.8	98.5	99.3	100.0	100.4	100.7	101.2	101.7	102.2	102.7
105°	123.4	123.8	124.2	124.5	124.9	125.1	125.2	125.5	125.7	126.0	126.2
107.5°	149.8	150.3	150.8	151.3	151.8	152.1	152.1	152.1	152.1	152.1	152.1
110°	175.0	175.8	176.6	177.3	178.1	178.5	178.5	178.5	178.5	178.5	178.5

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	202.6	203.4	204.1	204.9	205.6	206.0	205.9	205.8	205.7	205.5	205.4
115°	229.5	230.3	231.1	231.8	232.6	233.0	232.9	232.6	232.3	232.1	231.8
117.5°	256.5	257.5	258.5	259.6	260.6	261.1	260.8	260.1	259.5	258.8	258.2
120°	283.5	284.5	285.5	286.6	287.6	288.1	287.6	286.6	285.5	284.5	283.5
122.5°	308.1	309.4	310.7	312.0	313.3	313.9	313.6	312.9	312.3	311.6	311.0
125°	334.0	335.1	336.3	337.4	338.5	339.1	338.9	338.5	338.2	337.8	337.4
127.5°	359.2	360.6	362.0	363.4	364.8	365.5	365.2	364.7	364.2	363.7	363.2
130°	382.7	384.4	386.0	387.7	389.4	390.2	390.1	389.8	389.5	389.3	389.0
132.5°	409.1	410.4	411.7	413.0	414.3	414.9	415.0	415.1	415.2	415.3	415.4
135°	432.1	433.5	434.9	436.3	437.7	438.4	438.5	438.8	439.0	439.3	439.5
137.5°	457.3	458.5	459.6	460.8	461.9	462.5	462.6	462.9	463.1	463.4	463.6
140°	479.7	480.9	482.0	483.2	484.3	484.9	485.2	485.8	486.5	487.1	487.7
142.5°	502.7	503.8	505.0	506.1	507.2	507.8	508.0	508.4	508.7	509.1	509.5
145°	524.5	525.4	526.3	527.2	528.1	528.5	528.9	529.6	530.4	531.1	531.9
147.5°	544.0	545.1	546.3	547.4	548.5	549.1	549.4	549.9	550.4	550.9	551.4
150°	564.1	564.9	565.6	566.4	567.1	567.5	567.8	568.3	568.8	569.3	569.8
152.5°	581.8	582.6	583.4	584.1	584.9	585.3	585.6	586.3	586.9	587.6	588.2
155°	599.6	600.0	600.4	600.8	601.2	601.4	601.6	602.0	602.3	602.7	603.1
157.5°	615.1	615.4	615.6	615.9	616.2	616.3	616.4	616.7	616.9	617.2	617.4
160°	628.9	629.1	629.4	629.6	629.9	630.0	630.1	630.2	630.3	630.5	630.6
162.5°	641.5	641.5	641.5	641.5	641.5	641.5	641.6	641.7	641.8	642.0	642.1
165°	652.4	652.3	652.2	652.1	652.0	651.9	651.9	651.9	651.9	651.9	651.9
167.5°	662.2	661.8	661.4	661.1	660.7	660.5	660.5	660.5	660.5	660.5	660.5
170°	669.6	669.2	668.8	668.5	668.1	667.9	667.8	667.7	667.6	667.4	667.3
172.5°	674.8	674.4	674.0	673.7	673.3	673.1	673.0	672.9	672.8	672.6	672.5
175°	678.8	678.4	678.0	677.7	677.3	677.1	677.0	676.7	676.5	676.2	676.0
177.5°	681.1	680.7	680.3	680.0	679.6	679.4	679.3	679.0	678.7	678.5	678.2
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1790.8	1792.1	1794.8	1808.0	1814.6	1816.0	1810.7	1822.6	1826.6	1822.6	1819.9
5°	1875.6	1883.5	1899.4	1916.6	1915.3	1916.6	1924.6	1932.5	1935.2	1924.6	1928.5
7.5°	1949.7	1965.6	1982.9	2009.3	2009.3	2022.6	2027.9	2034.5	2050.4	2042.5	2039.8
10°	2034.5	2055.7	2087.5	2129.9	2131.2	2144.5	2157.7	2178.9	2185.5	2180.2	2182.9
12.5°	2140.5	2181.5	2184.2	2230.5	2251.7	2254.4	2275.6	2271.6	2284.9	2284.9	2307.4
15°	2186.8	2250.4	2286.2	2331.2	2344.5	2328.6	2345.8	2364.3	2365.7	2365.7	2364.3
17.5°	2270.3	2295.5	2331.2	2355.1	2360.4	2360.4	2361.7	2369.6	2364.3	2353.7	2361.7
20°	2287.5	2298.1	2311.3	2308.7	2311.3	2298.1	2284.9	2271.6	2272.9	2266.3	2286.2
22.5°	2255.7	2253.1	2222.6	2202.7	2202.7	2176.2	2151.1	2139.2	2127.2	2131.2	2137.8
25°	2176.2	2135.2	2098.1	2069.0	2062.3	2019.9	1985.5	1974.9	1955.0	1970.9	1973.6
27.5°	2049.1	2002.7	1943.1	1918.0	1883.5	1866.3	1842.5	1810.7	1769.6	1793.4	1789.5
30°	1912.7	1843.8	1794.8	1733.8	1679.5	1675.6	1630.5	1577.5	1556.3	1556.3	1568.3
32.5°	1760.3	1668.9	1597.4	1511.3	1458.3	1435.8	1381.5	1328.5	1340.4	1300.7	1315.3
35°	1582.8	1462.3	1372.2	1288.8	1249.1	1222.6	1152.4	1123.2	1091.4	1072.9	1107.3
37.5°	1413.3	1274.2	1159.0	1067.6	1053.0	1005.3	957.7	939.1	920.6	928.5	927.2
40°	1206.7	1083.5	980.2	908.6	883.5	861.0	829.2	806.7	794.7	801.4	802.7
42.5°	1019.9	916.6	839.8	789.4	768.2	752.3	736.5	717.9	713.9	713.9	719.2
45°	875.5	790.8	739.1	698.0	686.1	674.2	662.3	654.3	651.7	646.4	650.4
47.5°	760.3	692.7	661.0	630.5	617.2	614.6	604.0	600.0	594.7	593.4	594.7
50°	663.6	621.2	592.1	574.9	565.6	561.6	556.3	548.4	545.7	552.3	549.7
52.5°	596.0	556.3	540.4	523.2	517.9	512.6	504.7	506.0	504.7	502.0	502.0
55°	528.5	503.3	487.4	474.2	472.9	467.6	460.9	458.3	457.0	454.3	458.3
57.5°	474.2	454.3	439.8	427.8	422.5	422.5	415.9	410.6	410.6	409.3	410.6
60°	419.9	400.0	390.7	378.8	374.8	373.5	369.6	366.9	362.9	362.9	362.9
62.5°	369.6	353.7	343.1	332.5	333.8	327.2	321.9	319.2	319.2	320.5	320.5
65°	321.9	311.3	298.0	288.8	286.1	284.8	282.1	280.8	276.8	279.5	279.5
67.5°	278.2	263.6	255.6	251.7	247.7	246.4	243.7	241.1	239.7	238.4	241.1
70°	234.4	222.5	215.9	213.3	209.3	208.0	206.6	202.7	204.0	205.3	206.6
72.5°	194.7	184.1	182.8	174.8	174.8	174.8	169.5	172.2	170.9	168.2	170.9
75°	153.6	148.3	145.7	141.7	143.1	141.7	140.4	136.4	136.4	137.8	139.1
77.5°	121.9	116.6	115.2	111.3	108.6	111.3	108.6	107.3	107.3	108.6	108.6
80°	90.1	87.4	83.4	83.4	83.4	82.1	82.1	82.1	80.8	79.5	80.8
82.5°	59.6	59.6	58.3	57.0	58.3	55.6	57.0	57.0	57.0	57.0	57.0
85°	38.4	37.1	37.1	35.8	35.8	35.8	37.1	34.4	34.4	35.8	35.8
87.5°	17.2	17.2	17.2	18.5	17.2	17.2	17.2	18.5	17.2	17.2	17.2
90°	19.8	19.6	19.3	19.0	18.9	19.0	19.1	19.2	19.4	19.5	19.4
92.5°	17.9	18.1	18.2	18.3	18.4	18.4	18.4	18.4	18.4	18.4	18.4
95°	36.7	36.7	36.7	36.7	36.7	36.6	36.3	36.1	35.8	35.6	35.8
97.5°	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4
100°	79.2	79.2	79.2	79.2	79.2	79.1	79.0	78.9	78.7	78.6	78.7
102.5°	102.8	103.0	103.1	103.2	103.3	103.2	103.1	103.0	102.8	102.7	102.8
105°	126.5	126.7	127.0	127.3	127.4	127.4	127.4	127.4	127.4	127.4	127.4
107.5°	152.2	152.3	152.4	152.5	152.6	152.3	151.7	151.0	150.4	149.8	150.4
110°	178.5	178.5	178.5	178.5	178.5	178.3	177.9	177.5	177.1	176.7	177.1

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	205.0	204.6	204.3	203.9	203.7	203.6	203.3	203.1	202.8	202.6	202.8
115°	231.7	231.5	231.4	231.3	231.2	231.0	230.6	230.3	229.9	229.5	229.9
117.5°	257.8	257.4	257.1	256.7	256.5	256.3	255.9	255.6	255.2	254.8	255.2
120°	283.5	283.5	283.5	283.5	283.5	283.3	282.9	282.5	282.1	281.7	282.1
122.5°	310.6	310.2	309.9	309.5	309.3	309.2	308.9	308.6	308.4	308.1	308.4
125°	337.0	336.6	336.3	335.9	335.7	335.6	335.5	335.4	335.2	335.1	335.2
127.5°	362.7	362.2	361.7	361.2	360.9	360.7	360.3	360.0	359.6	359.2	359.6
130°	388.8	388.5	388.3	388.0	387.9	387.6	387.1	386.6	386.1	385.6	386.1
132.5°	414.8	414.2	413.5	412.9	412.6	412.4	412.0	411.7	411.3	410.9	411.3
135°	439.4	439.3	439.2	439.1	439.0	438.8	438.4	438.0	437.6	437.2	437.6
137.5°	463.5	463.4	463.3	463.2	463.1	462.8	462.3	461.8	461.3	460.8	461.3
140°	487.7	487.7	487.7	487.7	487.7	487.4	486.9	486.4	485.9	485.4	485.9
142.5°	509.6	509.8	509.9	510.0	510.1	509.8	509.3	508.8	508.3	507.8	508.3
145°	532.0	532.2	532.3	532.4	532.5	532.2	531.7	531.2	530.7	530.2	530.7
147.5°	551.7	551.9	552.2	552.5	552.6	552.3	551.8	551.3	550.8	550.3	550.8
150°	570.2	570.6	570.9	571.3	571.5	571.3	570.9	570.6	570.2	569.8	570.2
152.5°	588.7	589.2	589.7	590.2	590.5	590.2	589.7	589.2	588.7	588.2	588.7
155°	603.7	604.3	605.0	605.6	605.9	605.7	605.3	605.0	604.6	604.2	604.6
157.5°	618.3	619.2	620.1	621.0	621.4	621.1	620.5	619.8	619.2	618.6	619.2
160°	631.4	632.2	632.9	633.7	634.1	633.8	633.3	632.8	632.3	631.8	632.3
162.5°	643.0	643.9	644.8	645.7	646.1	645.8	645.1	644.5	643.8	643.2	643.8
165°	652.8	653.7	654.6	655.5	655.9	655.6	654.9	654.3	653.6	653.0	653.6
167.5°	661.4	662.3	663.2	664.1	664.5	664.2	663.5	662.9	662.2	661.6	662.2
170°	668.2	669.1	670.0	670.9	671.4	671.0	670.2	669.5	668.7	667.9	668.7
172.5°	673.4	674.3	675.2	676.1	676.5	676.1	675.4	674.6	673.9	673.1	673.9
175°	676.9	677.8	678.7	679.6	680.0	679.6	678.8	678.1	677.3	676.5	677.3
177.5°	679.0	679.8	680.5	681.3	681.7	681.3	680.5	679.8	679.0	678.2	679.0
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1826.6	1817.3	1809.3	1810.7	1817.3	1812.0	1798.7	1781.5	1774.9	1767.0	1774.9
5°	1936.5	1928.5	1912.7	1914.0	1910.0	1904.7	1883.5	1857.0	1857.0	1835.8	1833.2
7.5°	2045.1	2033.2	2022.6	2019.9	2005.4	1994.8	1976.2	1939.1	1924.6	1899.4	1884.8
10°	2167.0	2157.7	2145.8	2131.2	2123.3	2104.7	2074.3	2019.9	1993.5	1959.0	1933.8
12.5°	2290.2	2288.8	2262.3	2233.2	2231.9	2202.7	2181.5	2108.7	2072.9	2026.6	1967.0
15°	2368.3	2361.7	2347.1	2332.5	2336.5	2304.7	2257.0	2170.9	2147.1	2091.5	2027.9
17.5°	2367.0	2367.0	2363.0	2360.4	2356.4	2347.1	2320.6	2263.7	2225.2	2155.0	2095.4
20°	2291.5	2308.7	2312.7	2311.3	2324.6	2331.2	2329.9	2294.1	2263.7	2201.4	2140.5
22.5°	2140.5	2180.2	2197.4	2208.0	2235.8	2250.4	2284.9	2271.6	2263.7	2217.3	2165.6
25°	2000.1	2013.3	2065.0	2067.6	2106.0	2141.8	2176.2	2198.8	2227.9	2210.7	2167.0
27.5°	1818.6	1849.1	1886.2	1914.0	1921.9	1994.8	2051.7	2094.1	2160.3	2165.6	2151.1
30°	1613.3	1627.9	1688.8	1725.9	1768.3	1821.3	1903.4	1976.2	2035.8	2090.1	2108.7
32.5°	1363.0	1422.6	1458.3	1503.4	1540.5	1634.5	1735.2	1829.2	1898.1	1989.5	2029.2
35°	1133.8	1180.2	1241.1	1259.6	1327.2	1406.7	1537.8	1658.3	1763.0	1855.7	1936.5
37.5°	944.4	981.5	1046.4	1075.5	1115.3	1217.3	1327.2	1476.9	1602.7	1716.6	1817.3
40°	814.6	842.4	891.4	900.7	933.8	1026.5	1115.3	1255.7	1422.6	1576.2	1686.2
42.5°	725.9	739.1	772.2	784.1	805.3	867.6	947.1	1079.5	1234.5	1393.4	1548.4
45°	662.3	671.5	691.4	702.0	728.5	756.3	821.2	927.2	1049.0	1209.3	1376.2
47.5°	605.3	617.2	625.2	631.8	646.4	676.8	719.2	797.4	913.9	1061.0	1222.6
50°	557.6	561.6	576.2	577.5	586.8	606.6	646.4	694.1	786.8	906.0	1062.3
52.5°	510.0	513.9	523.2	532.5	536.4	552.3	578.8	618.6	687.4	781.5	920.6
55°	462.3	467.6	476.8	483.5	487.4	500.7	516.6	555.0	609.3	675.5	789.4
57.5°	414.6	426.5	429.2	433.1	439.8	454.3	468.9	491.4	533.8	594.7	678.2
60°	369.6	373.5	382.8	386.8	393.4	401.3	419.9	437.1	467.6	515.3	590.8
62.5°	323.2	332.5	336.4	340.4	345.7	355.0	366.9	385.4	411.9	450.3	510.0
65°	283.5	284.8	292.7	298.0	303.3	309.9	321.9	339.1	355.0	390.7	434.5
67.5°	245.0	247.7	250.3	255.6	262.3	268.9	279.5	288.8	308.6	332.5	366.9
70°	208.0	208.0	214.6	218.6	217.2	225.2	233.1	243.7	258.3	280.8	308.6
72.5°	174.8	173.5	178.8	180.1	182.8	188.1	193.4	204.0	211.9	229.1	250.3
75°	139.1	141.7	144.4	144.4	148.3	152.3	157.6	162.9	172.2	182.8	198.7
77.5°	109.9	109.9	112.6	113.9	117.9	116.6	121.9	127.2	133.8	143.1	155.0
80°	80.8	83.4	83.4	83.4	84.8	86.1	91.4	95.4	99.3	106.0	111.3
82.5°	57.0	57.0	59.6	59.6	59.6	62.3	62.3	63.6	66.2	70.2	74.2
85°	35.8	35.8	35.8	37.1	35.8	37.1	39.7	38.4	39.7	42.4	42.4
87.5°	17.2	17.2	17.2	17.2	17.2	18.5	17.2	18.5	19.9	19.9	19.9
90°	19.2	19.1	19.0	18.9	19.0	19.3	19.6	19.8	20.1	17.3	14.5
92.5°	18.4	18.4	18.4	18.4	18.3	18.2	18.1	17.9	17.8	17.7	17.5
95°	36.1	36.3	36.6	36.7	36.7	36.7	36.7	36.7	36.7	36.5	36.2
97.5°	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	56.9	56.4
100°	78.9	79.0	79.1	79.2	79.2	79.2	79.2	79.2	79.2	78.8	78.4
102.5°	103.0	103.1	103.2	103.3	103.2	103.1	103.0	102.8	102.7	102.2	101.7
105°	127.4	127.4	127.4	127.4	127.3	127.0	126.7	126.5	126.2	126.0	125.7
107.5°	151.0	151.7	152.3	152.6	152.5	152.4	152.3	152.2	152.1	152.1	152.1
110°	177.5	177.9	178.3	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	203.1	203.3	203.6	203.7	203.9	204.3	204.6	205.0	205.4	205.5	205.7
115°	230.3	230.6	231.0	231.2	231.3	231.4	231.5	231.7	231.8	232.1	232.3
117.5°	255.6	255.9	256.3	256.5	256.7	257.1	257.4	257.8	258.2	258.8	259.5
120°	282.5	282.9	283.3	283.5	283.5	283.5	283.5	283.5	283.5	284.5	285.5
122.5°	308.6	308.9	309.2	309.3	309.5	309.9	310.2	310.6	311.0	311.6	312.3
125°	335.4	335.5	335.6	335.7	335.9	336.3	336.6	337.0	337.4	337.8	338.2
127.5°	360.0	360.3	360.7	360.9	361.2	361.7	362.2	362.7	363.2	363.7	364.2
130°	386.6	387.1	387.6	387.9	388.0	388.3	388.5	388.8	389.0	389.3	389.5
132.5°	411.7	412.0	412.4	412.6	412.9	413.5	414.2	414.8	415.4	415.3	415.2
135°	438.0	438.4	438.8	439.0	439.1	439.2	439.3	439.4	439.5	439.3	439.0
137.5°	461.8	462.3	462.8	463.1	463.2	463.3	463.4	463.5	463.6	463.4	463.1
140°	486.4	486.9	487.4	487.7	487.7	487.7	487.7	487.7	487.7	487.1	486.5
142.5°	508.8	509.3	509.8	510.1	510.0	509.9	509.8	509.6	509.5	509.1	508.7
145°	531.2	531.7	532.2	532.5	532.4	532.3	532.2	532.0	531.9	531.1	530.4
147.5°	551.3	551.8	552.3	552.6	552.5	552.2	551.9	551.7	551.4	550.9	550.4
150°	570.6	570.9	571.3	571.5	571.3	570.9	570.6	570.2	569.8	569.3	568.8
152.5°	589.2	589.7	590.2	590.5	590.2	589.7	589.2	588.7	588.2	587.6	586.9
155°	605.0	605.3	605.7	605.9	605.6	605.0	604.3	603.7	603.1	602.7	602.3
157.5°	619.8	620.5	621.1	621.4	621.0	620.1	619.2	618.3	617.4	617.2	616.9
160°	632.8	633.3	633.8	634.1	633.7	632.9	632.2	631.4	630.6	630.5	630.3
162.5°	644.5	645.1	645.8	646.1	645.7	644.8	643.9	643.0	642.1	642.0	641.8
165°	654.3	654.9	655.6	655.9	655.5	654.6	653.7	652.8	651.9	651.9	651.9
167.5°	662.9	663.5	664.2	664.5	664.1	663.2	662.3	661.4	660.5	660.5	660.5
170°	669.5	670.2	671.0	671.4	670.9	670.0	669.1	668.2	667.3	667.4	667.6
172.5°	674.6	675.4	676.1	676.5	676.1	675.2	674.3	673.4	672.5	672.6	672.8
175°	678.1	678.8	679.6	680.0	679.6	678.7	677.8	676.9	676.0	676.2	676.5
177.5°	679.8	680.5	681.3	681.7	681.3	680.5	679.8	679.0	678.2	678.5	678.7
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1768.3	1761.7	1757.7	1760.3	1752.4	1732.5	1732.5	1739.1	1731.2	1723.2	1711.3
5°	1817.3	1804.0	1796.1	1794.8	1776.2	1744.4	1737.8	1731.2	1714.0	1695.4	1675.6
7.5°	1865.0	1841.1	1827.9	1818.6	1792.1	1751.1	1733.8	1719.3	1691.5	1663.6	1638.5
10°	1904.7	1870.3	1854.4	1839.8	1805.4	1753.7	1725.9	1699.4	1663.6	1627.9	1596.1
12.5°	1936.5	1896.8	1876.9	1855.7	1813.3	1745.8	1711.3	1668.9	1633.2	1585.5	1553.7
15°	1989.5	1907.4	1888.8	1868.9	1825.2	1732.5	1690.1	1642.4	1593.4	1529.9	1495.4
17.5°	2031.9	1921.9	1920.6	1878.2	1821.3	1727.2	1662.3	1600.1	1547.1	1483.5	1429.2
20°	2057.0	1944.4	1923.3	1879.5	1808.0	1691.5	1623.9	1555.0	1498.1	1421.2	1366.9
22.5°	2078.2	1976.2	1920.6	1867.6	1780.2	1679.5	1580.2	1515.3	1437.1	1353.7	1302.0
25°	2086.2	1982.9	1924.6	1863.6	1760.3	1645.1	1532.5	1462.3	1374.9	1299.4	1229.2
27.5°	2087.5	1981.5	1910.0	1846.4	1732.5	1600.1	1484.8	1410.6	1314.0	1226.5	1156.3
30°	2074.3	1967.0	1902.1	1833.2	1706.0	1559.0	1426.5	1344.4	1241.1	1153.7	1080.8
32.5°	2034.5	1937.8	1884.8	1809.3	1671.6	1502.0	1370.9	1279.5	1170.9	1084.8	1014.6
35°	1968.3	1902.1	1843.8	1773.6	1626.6	1449.1	1315.3	1208.0	1098.1	1015.9	949.7
37.5°	1886.2	1850.4	1796.1	1727.2	1574.9	1401.4	1253.0	1133.8	1023.9	944.4	879.5
40°	1774.9	1784.2	1731.2	1668.9	1514.0	1336.5	1172.2	1058.3	955.0	880.8	817.2
42.5°	1654.4	1692.8	1662.3	1602.7	1446.4	1264.9	1112.6	986.8	886.1	809.3	756.3
45°	1524.6	1590.8	1572.2	1528.5	1376.2	1189.4	1027.9	906.0	817.2	743.1	696.7
47.5°	1382.8	1476.9	1476.9	1445.1	1298.1	1113.9	955.0	830.5	743.1	690.1	645.1
50°	1238.5	1344.4	1361.6	1340.4	1210.6	1027.9	866.3	753.7	678.2	626.5	593.4
52.5°	1087.5	1210.6	1242.4	1231.8	1117.9	945.7	793.4	683.5	614.6	569.6	540.4
55°	943.1	1086.1	1120.6	1124.5	1018.6	855.7	712.6	615.9	549.7	519.2	494.1
57.5°	806.7	944.4	982.8	989.4	917.9	773.5	637.1	552.3	492.7	467.6	447.7
60°	690.1	805.3	855.7	870.2	808.0	678.2	566.9	484.8	439.8	415.9	397.4
62.5°	594.7	687.4	740.4	744.4	716.6	594.7	494.1	425.2	386.8	365.6	356.3
65°	502.0	585.5	617.2	633.1	610.6	515.3	426.5	369.6	339.1	320.5	311.3
67.5°	427.8	480.8	507.3	528.5	506.0	434.5	362.9	316.6	294.1	275.5	270.2
70°	351.0	394.7	414.6	435.8	415.9	361.6	309.9	267.6	247.7	233.1	226.5
72.5°	280.8	315.2	333.8	347.0	335.1	290.1	247.7	218.6	204.0	193.4	189.4
75°	222.5	246.4	257.0	266.2	260.9	226.5	200.0	176.2	162.9	153.6	151.0
77.5°	169.5	186.8	198.7	201.3	194.7	172.2	149.7	135.1	124.5	119.2	116.6
80°	120.5	131.1	137.8	141.7	135.1	125.8	109.9	99.3	90.1	83.4	82.1
82.5°	80.8	86.1	91.4	90.1	87.4	79.5	70.2	64.9	60.9	55.6	55.6
85°	46.4	47.7	50.3	51.7	50.3	45.0	39.7	37.1	34.4	30.5	30.5
87.5°	19.9	21.2	21.2	22.5	19.9	19.9	17.2	14.6	14.6	13.2	11.9
90°	11.7	8.9	7.5	6.7	5.2	3.7	2.1	0.6	2.1	3.7	5.2
92.5°	17.4	17.3	17.2	16.7	15.7	14.6	13.6	12.6	13.6	14.6	15.7
95°	36.0	35.7	35.6	35.0	33.7	32.4	31.1	29.8	31.1	32.4	33.7
97.5°	55.9	55.4	55.1	54.5	53.4	52.2	51.1	49.9	51.1	52.2	53.4
100°	78.1	77.7	77.5	77.0	76.0	74.9	73.9	72.9	73.9	74.9	76.0
102.5°	101.2	100.7	100.4	100.0	99.3	98.5	97.8	97.0	97.8	98.5	99.3
105°	125.5	125.2	125.1	124.9	124.5	124.2	123.8	123.4	123.8	124.2	124.5
107.5°	152.1	152.1	152.1	151.8	151.3	150.8	150.3	149.8	150.3	150.8	151.3
110°	178.5	178.5	178.5	178.1	177.3	176.6	175.8	175.0	175.8	176.6	177.3

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	205.8	205.9	206.0	205.6	204.9	204.1	203.4	202.6	203.4	204.1	204.9
115°	232.6	232.9	233.0	232.6	231.8	231.1	230.3	229.5	230.3	231.1	231.8
117.5°	260.1	260.8	261.1	260.6	259.6	258.5	257.5	256.5	257.5	258.5	259.6
120°	286.6	287.6	288.1	287.6	286.6	285.5	284.5	283.5	284.5	285.5	286.6
122.5°	312.9	313.6	313.9	313.3	312.0	310.7	309.4	308.1	309.4	310.7	312.0
125°	338.5	338.9	339.1	338.5	337.4	336.3	335.1	334.0	335.1	336.3	337.4
127.5°	364.7	365.2	365.5	364.8	363.4	362.0	360.6	359.2	360.6	362.0	363.4
130°	389.8	390.1	390.2	389.4	387.7	386.0	384.4	382.7	384.4	386.0	387.7
132.5°	415.1	415.0	414.9	414.3	413.0	411.7	410.4	409.1	410.4	411.7	413.0
135°	438.8	438.5	438.4	437.7	436.3	434.9	433.5	432.1	433.5	434.9	436.3
137.5°	462.9	462.6	462.5	461.9	460.8	459.6	458.5	457.3	458.5	459.6	460.8
140°	485.8	485.2	484.9	484.3	483.2	482.0	480.9	479.7	480.9	482.0	483.2
142.5°	508.4	508.0	507.8	507.2	506.1	505.0	503.8	502.7	503.8	505.0	506.1
145°	529.6	528.9	528.5	528.1	527.2	526.3	525.4	524.5	525.4	526.3	527.2
147.5°	549.9	549.4	549.1	548.5	547.4	546.3	545.1	544.0	545.1	546.3	547.4
150°	568.3	567.8	567.5	567.1	566.4	565.6	564.9	564.1	564.9	565.6	566.4
152.5°	586.3	585.6	585.3	584.9	584.1	583.4	582.6	581.8	582.6	583.4	584.1
155°	602.0	601.6	601.4	601.2	600.8	600.4	600.0	599.6	600.0	600.4	600.8
157.5°	616.7	616.4	616.3	616.2	615.9	615.6	615.4	615.1	615.4	615.6	615.9
160°	630.2	630.1	630.0	629.9	629.6	629.4	629.1	628.9	629.1	629.4	629.6
162.5°	641.7	641.6	641.5	641.5	641.5	641.5	641.5	641.5	641.5	641.5	641.5
165°	651.9	651.9	651.9	652.0	652.1	652.2	652.3	652.4	652.3	652.2	652.1
167.5°	660.5	660.5	660.5	660.7	661.1	661.4	661.8	662.2	661.8	661.4	661.1
170°	667.7	667.8	667.9	668.1	668.5	668.8	669.2	669.6	669.2	668.8	668.5
172.5°	672.9	673.0	673.1	673.3	673.7	674.0	674.4	674.8	674.4	674.0	673.7
175°	676.7	677.0	677.1	677.3	677.7	678.0	678.4	678.8	678.4	678.0	677.7
177.5°	679.0	679.3	679.4	679.6	680.0	680.3	680.7	681.1	680.7	680.3	680.0
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1704.7	1711.3	1710.0	1696.8	1682.2	1670.3	1647.7	1650.4	1642.4	1643.8	1651.7
5°	1662.3	1662.3	1657.0	1638.5	1614.6	1601.4	1576.2	1569.6	1553.7	1552.4	1551.1
7.5°	1617.3	1610.7	1604.0	1577.5	1548.4	1527.2	1492.8	1484.8	1468.9	1458.3	1453.0
10°	1564.3	1555.0	1541.8	1511.3	1475.6	1449.1	1413.3	1402.7	1372.2	1359.0	1351.0
12.5°	1506.0	1500.7	1479.5	1454.4	1396.1	1366.9	1315.3	1325.9	1295.4	1268.9	1264.9
15°	1447.7	1427.9	1415.9	1374.9	1304.7	1291.4	1250.4	1229.2	1201.4	1180.2	1180.2
17.5°	1390.8	1360.3	1333.8	1290.1	1238.5	1201.4	1170.9	1160.3	1125.9	1104.7	1100.7
20°	1315.3	1280.8	1274.2	1212.0	1176.2	1135.1	1106.0	1079.5	1054.3	1045.1	1038.4
22.5°	1243.8	1204.0	1193.4	1140.4	1104.7	1063.6	1034.5	1015.9	997.4	990.8	978.8
25°	1166.9	1143.1	1127.2	1070.2	1030.5	992.1	972.2	959.0	941.8	940.4	932.5
27.5°	1092.8	1070.2	1054.3	1000.0	970.9	935.1	919.2	904.7	895.4	891.4	887.5
30°	1029.2	1004.0	985.5	945.7	910.0	880.8	867.6	858.3	853.0	846.4	845.1
32.5°	959.0	944.4	919.2	888.8	861.0	833.1	825.2	818.6	810.6	808.0	806.7
35°	899.4	879.5	863.6	829.2	817.2	793.4	784.1	778.8	768.2	765.6	762.9
37.5°	841.1	822.5	805.3	784.1	761.6	748.4	743.1	735.1	729.8	731.2	728.5
40°	782.8	768.2	755.0	732.5	719.2	712.6	702.0	694.1	691.4	692.7	691.4
42.5°	725.9	712.6	704.7	687.4	674.2	667.6	661.0	653.0	657.0	657.0	661.0
45°	674.2	662.3	657.0	643.7	635.8	625.2	618.6	617.2	622.5	621.2	621.2
47.5°	621.2	617.2	610.6	598.7	588.1	581.5	580.2	580.2	585.5	588.1	586.8
50°	580.2	572.2	564.3	555.0	547.0	544.4	540.4	543.1	548.4	548.4	551.0
52.5°	528.5	523.2	520.5	512.6	507.3	507.3	507.3	508.6	512.6	516.6	515.3
55°	483.5	479.5	476.8	472.9	466.2	467.6	466.2	468.9	472.9	476.8	479.5
57.5°	435.8	434.5	431.8	425.2	425.2	423.9	427.8	429.2	435.8	438.4	442.4
60°	393.4	389.4	389.4	384.1	384.1	384.1	388.1	392.1	397.4	398.7	401.3
62.5°	348.4	348.4	347.0	343.1	343.1	347.0	348.4	353.7	356.3	356.3	360.3
65°	306.0	304.6	303.3	304.6	306.0	306.0	309.9	312.6	315.2	316.6	317.9
67.5°	263.6	262.3	264.9	263.6	266.2	271.5	270.2	274.2	278.2	278.2	279.5
70°	223.8	226.5	225.2	227.8	226.5	229.1	233.1	234.4	234.4	235.8	239.7
72.5°	186.8	186.8	186.8	185.4	186.8	189.4	192.1	193.4	196.0	197.4	201.3
75°	151.0	151.0	148.3	151.0	151.0	153.6	156.3	156.3	156.3	158.9	162.9
77.5°	113.9	115.2	113.9	116.6	116.6	117.9	120.5	119.2	121.9	123.2	124.5
80°	83.4	82.1	82.1	82.1	83.4	83.4	86.1	87.4	87.4	91.4	88.7
82.5°	53.0	54.3	53.0	54.3	54.3	55.6	54.3	55.6	57.0	59.6	58.3
85°	30.5	29.1	29.1	30.5	29.1	29.1	30.5	29.1	30.5	29.1	30.5
87.5°	11.9	10.6	10.6	10.6	10.6	9.3	9.3	7.9	7.9	7.9	6.6
90°	6.7	7.5	8.9	11.7	14.5	17.3	20.1	19.8	19.6	19.3	19.0
92.5°	16.7	17.2	17.3	17.4	17.5	17.7	17.8	17.9	18.1	18.2	18.3
95°	35.0	35.6	35.7	36.0	36.2	36.5	36.7	36.7	36.7	36.7	36.7
97.5°	54.5	55.1	55.4	55.9	56.4	56.9	57.4	57.4	57.4	57.4	57.4
100°	77.0	77.5	77.7	78.1	78.4	78.8	79.2	79.2	79.2	79.2	79.2
102.5°	100.0	100.4	100.7	101.2	101.7	102.2	102.7	102.8	103.0	103.1	103.2
105°	124.9	125.1	125.2	125.5	125.7	126.0	126.2	126.5	126.7	127.0	127.3
107.5°	151.8	152.1	152.1	152.1	152.1	152.1	152.1	152.2	152.3	152.4	152.5
110°	178.1	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	205.6	206.0	205.9	205.8	205.7	205.5	205.4	205.0	204.6	204.3	203.9
115°	232.6	233.0	232.9	232.6	232.3	232.1	231.8	231.7	231.5	231.4	231.3
117.5°	260.6	261.1	260.8	260.1	259.5	258.8	258.2	257.8	257.4	257.1	256.7
120°	287.6	288.1	287.6	286.6	285.5	284.5	283.5	283.5	283.5	283.5	283.5
122.5°	313.3	313.9	313.6	312.9	312.3	311.6	311.0	310.6	310.2	309.9	309.5
125°	338.5	339.1	338.9	338.5	338.2	337.8	337.4	337.0	336.6	336.3	335.9
127.5°	364.8	365.5	365.2	364.7	364.2	363.7	363.2	362.7	362.2	361.7	361.2
130°	389.4	390.2	390.1	389.8	389.5	389.3	389.0	388.8	388.5	388.3	388.0
132.5°	414.3	414.9	415.0	415.1	415.2	415.3	415.4	414.8	414.2	413.5	412.9
135°	437.7	438.4	438.5	438.8	439.0	439.3	439.5	439.4	439.3	439.2	439.1
137.5°	461.9	462.5	462.6	462.9	463.1	463.4	463.6	463.5	463.4	463.3	463.2
140°	484.3	484.9	485.2	485.8	486.5	487.1	487.7	487.7	487.7	487.7	487.7
142.5°	507.2	507.8	508.0	508.4	508.7	509.1	509.5	509.6	509.8	509.9	510.0
145°	528.1	528.5	528.9	529.6	530.4	531.1	531.9	532.0	532.2	532.3	532.4
147.5°	548.5	549.1	549.4	549.9	550.4	550.9	551.4	551.7	551.9	552.2	552.5
150°	567.1	567.5	567.8	568.3	568.8	569.3	569.8	570.2	570.6	570.9	571.3
152.5°	584.9	585.3	585.6	586.3	586.9	587.6	588.2	588.7	589.2	589.7	590.2
155°	601.2	601.4	601.6	602.0	602.3	602.7	603.1	603.7	604.3	605.0	605.6
157.5°	616.2	616.3	616.4	616.7	616.9	617.2	617.4	618.3	619.2	620.1	621.0
160°	629.9	630.0	630.1	630.2	630.3	630.5	630.6	631.4	632.2	632.9	633.7
162.5°	641.5	641.5	641.6	641.7	641.8	642.0	642.1	643.0	643.9	644.8	645.7
165°	652.0	651.9	651.9	651.9	651.9	651.9	651.9	652.8	653.7	654.6	655.5
167.5°	660.7	660.5	660.5	660.5	660.5	660.5	660.5	661.4	662.3	663.2	664.1
170°	668.1	667.9	667.8	667.7	667.6	667.4	667.3	668.2	669.1	670.0	670.9
172.5°	673.3	673.1	673.0	672.9	672.8	672.6	672.5	673.4	674.3	675.2	676.1
175°	677.3	677.1	677.0	676.7	676.5	676.2	676.0	676.9	677.8	678.7	679.6
177.5°	679.6	679.4	679.3	679.0	678.7	678.5	678.2	679.0	679.8	680.5	681.3
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1642.4	1646.4	1637.1	1634.5	1637.1	1627.9	1630.5	1633.2	1633.2	1637.1	1639.8
5°	1547.1	1541.8	1532.5	1529.9	1527.2	1531.2	1528.5	1532.5	1533.8	1543.1	1544.4
7.5°	1453.0	1445.1	1437.1	1429.2	1426.5	1419.9	1426.5	1426.5	1435.8	1433.2	1439.8
10°	1341.8	1340.4	1329.9	1325.9	1320.6	1310.0	1324.6	1320.6	1327.2	1339.1	1341.8
12.5°	1259.6	1245.1	1251.7	1233.2	1239.8	1229.2	1230.5	1230.5	1241.1	1242.4	1239.8
15°	1181.5	1169.6	1152.4	1144.4	1140.4	1135.1	1152.4	1153.7	1145.7	1164.3	1157.7
17.5°	1102.0	1102.0	1086.1	1082.2	1071.6	1076.9	1074.2	1075.5	1072.9	1086.1	1092.8
20°	1033.2	1026.5	1021.2	1022.6	1009.3	1006.7	1004.0	1006.7	1015.9	1025.2	1027.9
22.5°	977.5	973.5	960.3	963.0	952.4	956.3	953.7	960.3	961.6	961.6	970.9
25°	924.5	919.2	920.6	915.3	911.3	911.3	907.3	911.3	916.6	919.2	920.6
27.5°	884.8	880.8	874.2	870.2	872.9	866.3	871.6	875.5	875.5	872.9	875.5
30°	837.1	839.8	839.8	826.5	831.8	829.2	833.1	835.8	835.8	837.1	834.5
32.5°	805.3	797.4	796.1	794.7	794.7	789.4	789.4	793.4	794.7	796.1	800.0
35°	762.9	762.9	756.3	760.3	755.0	756.3	755.0	756.3	759.0	755.0	759.0
37.5°	724.5	725.9	723.2	725.9	727.2	724.5	721.9	727.2	724.5	724.5	721.9
40°	691.4	690.1	691.4	691.4	691.4	692.7	690.1	690.1	690.1	687.4	684.8
42.5°	663.6	655.7	658.3	659.6	655.7	655.7	657.0	655.7	659.6	651.7	651.7
45°	623.9	621.2	622.5	622.5	625.2	621.2	623.9	625.2	621.2	619.9	617.2
47.5°	588.1	590.8	588.1	590.8	590.8	593.4	588.1	589.4	590.8	585.5	581.5
50°	552.3	552.3	556.3	555.0	556.3	553.7	553.7	552.3	553.7	551.0	547.0
52.5°	519.2	515.3	521.9	520.5	519.2	517.9	516.6	517.9	515.3	512.6	512.6
55°	478.2	478.2	482.1	483.5	483.5	480.8	478.2	479.5	478.2	476.8	475.5
57.5°	445.0	439.8	442.4	443.7	443.7	439.8	442.4	439.8	439.8	441.1	437.1
60°	402.7	402.7	400.0	404.0	404.0	401.3	401.3	402.7	400.0	398.7	397.4
62.5°	357.6	359.0	362.9	364.3	365.6	362.9	360.3	361.6	361.6	357.6	359.0
65°	319.2	321.9	327.2	325.8	323.2	324.5	321.9	323.2	319.2	320.5	316.6
67.5°	282.1	280.8	282.1	282.1	284.8	283.5	280.8	280.8	279.5	283.5	279.5
70°	242.4	242.4	242.4	242.4	243.7	245.0	242.4	239.7	241.1	238.4	237.1
72.5°	201.3	202.7	201.3	204.0	200.0	202.7	202.7	201.3	200.0	200.0	200.0
75°	162.9	165.6	161.6	162.9	161.6	164.2	162.9	162.9	160.3	158.9	160.3
77.5°	124.5	125.8	123.2	124.5	123.2	124.5	124.5	123.2	123.2	123.2	123.2
80°	88.7	90.1	88.7	87.4	86.1	88.7	86.1	87.4	88.7	87.4	90.1
82.5°	57.0	57.0	55.6	57.0	54.3	54.3	55.6	55.6	54.3	57.0	54.3
85°	27.8	27.8	30.5	27.8	26.5	26.5	26.5	27.8	26.5	29.1	27.8
87.5°	6.6	5.3	6.6	6.6	5.3	5.3	6.6	5.3	6.6	7.9	5.3
90°	18.9	19.0	19.1	19.2	19.4	19.5	19.4	19.2	19.1	19.0	18.9
92.5°	18.4	18.4	18.4	18.4	18.4	18.4	18.4	18.4	18.4	18.4	18.4
95°	36.7	36.6	36.3	36.1	35.8	35.6	35.8	36.1	36.3	36.6	36.7
97.5°	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4
100°	79.2	79.1	79.0	78.9	78.7	78.6	78.7	78.9	79.0	79.1	79.2
102.5°	103.3	103.2	103.1	103.0	102.8	102.7	102.8	103.0	103.1	103.2	103.3
105°	127.4	127.4	127.4	127.4	127.4	127.4	127.4	127.4	127.4	127.4	127.4
107.5°	152.6	152.3	151.7	151.0	150.4	149.8	150.4	151.0	151.7	152.3	152.6
110°	178.5	178.3	177.9	177.5	177.1	176.7	177.1	177.5	177.9	178.3	178.5

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	203.7	203.6	203.3	203.1	202.8	202.6	202.8	203.1	203.3	203.6	203.7
115°	231.2	231.0	230.6	230.3	229.9	229.5	229.9	230.3	230.6	231.0	231.2
117.5°	256.5	256.3	255.9	255.6	255.2	254.8	255.2	255.6	255.9	256.3	256.5
120°	283.5	283.3	282.9	282.5	282.1	281.7	282.1	282.5	282.9	283.3	283.5
122.5°	309.3	309.2	308.9	308.6	308.4	308.1	308.4	308.6	308.9	309.2	309.3
125°	335.7	335.6	335.5	335.4	335.2	335.1	335.2	335.4	335.5	335.6	335.7
127.5°	360.9	360.7	360.3	360.0	359.6	359.2	359.6	360.0	360.3	360.7	360.9
130°	387.9	387.6	387.1	386.6	386.1	385.6	386.1	386.6	387.1	387.6	387.9
132.5°	412.6	412.4	412.0	411.7	411.3	410.9	411.3	411.7	412.0	412.4	412.6
135°	439.0	438.8	438.4	438.0	437.6	437.2	437.6	438.0	438.4	438.8	439.0
137.5°	463.1	462.8	462.3	461.8	461.3	460.8	461.3	461.8	462.3	462.8	463.1
140°	487.7	487.4	486.9	486.4	485.9	485.4	485.9	486.4	486.9	487.4	487.7
142.5°	510.1	509.8	509.3	508.8	508.3	507.8	508.3	508.8	509.3	509.8	510.1
145°	532.5	532.2	531.7	531.2	530.7	530.2	530.7	531.2	531.7	532.2	532.5
147.5°	552.6	552.3	551.8	551.3	550.8	550.3	550.8	551.3	551.8	552.3	552.6
150°	571.5	571.3	570.9	570.6	570.2	569.8	570.2	570.6	570.9	571.3	571.5
152.5°	590.5	590.2	589.7	589.2	588.7	588.2	588.7	589.2	589.7	590.2	590.5
155°	605.9	605.7	605.3	605.0	604.6	604.2	604.6	605.0	605.3	605.7	605.9
157.5°	621.4	621.1	620.5	619.8	619.2	618.6	619.2	619.8	620.5	621.1	621.4
160°	634.1	633.8	633.3	632.8	632.3	631.8	632.3	632.8	633.3	633.8	634.1
162.5°	646.1	645.8	645.1	644.5	643.8	643.2	643.8	644.5	645.1	645.8	646.1
165°	655.9	655.6	654.9	654.3	653.6	653.0	653.6	654.3	654.9	655.6	655.9
167.5°	664.5	664.2	663.5	662.9	662.2	661.6	662.2	662.9	663.5	664.2	664.5
170°	671.4	671.0	670.2	669.5	668.7	667.9	668.7	669.5	670.2	671.0	671.4
172.5°	676.5	676.1	675.4	674.6	673.9	673.1	673.9	674.6	675.4	676.1	676.5
175°	680.0	679.6	678.8	678.1	677.3	676.5	677.3	678.1	678.8	679.6	680.0
177.5°	681.7	681.3	680.5	679.8	679.0	678.2	679.0	679.8	680.5	681.3	681.7
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1635.8	1646.4	1642.4	1627.9	1645.1	1645.1	1657.0	1657.0	1671.6	1676.9	1684.8
5°	1543.1	1551.1	1557.7	1551.1	1563.0	1581.5	1592.1	1601.4	1621.3	1629.2	1641.1
7.5°	1443.8	1458.3	1465.0	1465.0	1484.8	1506.0	1527.2	1540.5	1568.3	1578.9	1590.8
10°	1347.1	1364.3	1377.5	1376.2	1409.3	1422.6	1449.1	1479.5	1507.3	1523.2	1540.5
12.5°	1245.1	1254.4	1272.9	1299.4	1307.3	1331.2	1361.6	1400.1	1450.4	1465.0	1490.1
15°	1160.3	1185.5	1200.0	1212.0	1230.5	1253.0	1286.1	1323.2	1373.6	1405.4	1431.8
17.5°	1088.8	1121.9	1131.2	1128.5	1152.4	1186.8	1225.2	1253.0	1298.1	1336.5	1361.6
20°	1030.5	1043.7	1059.6	1066.3	1084.8	1121.9	1159.0	1190.8	1227.9	1258.3	1287.5
22.5°	972.2	982.8	996.1	1008.0	1022.6	1043.7	1079.5	1119.2	1155.0	1184.2	1217.3
25°	924.5	931.2	943.1	952.4	968.2	982.8	1008.0	1051.7	1094.1	1111.3	1140.4
27.5°	878.2	883.5	891.4	902.0	910.0	924.5	947.1	982.8	1026.5	1043.7	1083.5
30°	837.1	841.1	849.0	854.3	858.3	875.5	892.7	920.6	953.7	977.5	1006.7
32.5°	798.7	802.7	810.6	812.0	817.2	826.5	842.4	867.6	896.7	916.6	941.8
35°	756.3	759.0	766.9	769.6	773.5	781.5	793.4	812.0	838.4	853.0	875.5
37.5°	723.2	721.9	727.2	731.2	736.5	740.4	744.4	762.9	782.8	796.1	813.3
40°	687.4	684.8	686.1	691.4	694.1	699.4	699.4	717.9	731.2	741.7	755.0
42.5°	651.7	650.4	647.7	650.4	653.0	654.3	655.7	668.9	682.1	691.4	706.0
45°	615.9	614.6	611.9	613.3	613.3	615.9	619.9	625.2	634.5	642.4	650.4
47.5°	582.8	580.2	576.2	574.9	577.5	577.5	577.5	582.8	592.1	594.7	602.7
50°	548.4	544.4	539.1	536.4	536.4	535.1	537.8	539.1	547.0	549.7	556.3
52.5°	511.3	508.6	503.3	498.0	499.4	496.7	498.0	499.4	502.0	506.0	510.0
55°	474.2	468.9	464.9	463.6	459.6	459.6	455.6	460.9	459.6	460.9	466.2
57.5°	438.4	433.1	426.5	423.9	419.9	418.6	415.9	414.6	415.9	419.9	423.9
60°	396.0	393.4	389.4	385.4	382.8	378.8	376.2	376.2	374.8	374.8	376.2
62.5°	355.0	353.7	348.4	347.0	344.4	341.7	337.8	335.1	335.1	337.8	339.1
65°	315.2	313.9	309.9	308.6	302.0	299.3	298.0	296.7	294.1	294.1	294.1
67.5°	278.2	274.2	274.2	267.6	262.3	259.6	257.0	255.6	255.6	255.6	257.0
70°	237.1	237.1	233.1	229.1	223.8	225.2	221.2	217.2	217.2	214.6	215.9
72.5°	197.4	196.0	192.1	190.7	186.8	182.8	180.1	182.8	178.8	177.5	178.8
75°	158.9	157.6	155.0	152.3	153.6	149.7	145.7	144.4	144.4	141.7	141.7
77.5°	121.9	124.5	119.2	117.9	115.2	112.6	111.3	109.9	109.9	109.9	112.6
80°	84.8	86.1	86.1	83.4	84.8	80.8	80.8	80.8	76.8	78.1	79.5
82.5°	54.3	54.3	53.0	54.3	53.0	53.0	51.7	51.7	50.3	50.3	51.7
85°	30.5	29.1	27.8	30.5	29.1	29.1	27.8	27.8	27.8	27.8	27.8
87.5°	6.6	7.9	7.9	7.9	7.9	9.3	9.3	9.3	10.6	10.6	10.6
90°	19.0	19.3	19.6	19.8	20.1	17.3	14.5	11.7	8.9	7.5	6.7
92.5°	18.3	18.2	18.1	17.9	17.8	17.7	17.5	17.4	17.3	17.2	16.7
95°	36.7	36.7	36.7	36.7	36.7	36.5	36.2	36.0	35.7	35.6	35.0
97.5°	57.4	57.4	57.4	57.4	57.4	56.9	56.4	55.9	55.4	55.1	54.5
100°	79.2	79.2	79.2	79.2	79.2	78.8	78.4	78.1	77.7	77.5	77.0
102.5°	103.2	103.1	103.0	102.8	102.7	102.2	101.7	101.2	100.7	100.4	100.0
105°	127.3	127.0	126.7	126.5	126.2	126.0	125.7	125.5	125.2	125.1	124.9
107.5°	152.5	152.4	152.3	152.2	152.1	152.1	152.1	152.1	152.1	152.1	151.8
110°	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.1

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	203.9	204.3	204.6	205.0	205.4	205.5	205.7	205.8	205.9	206.0	205.6
115°	231.3	231.4	231.5	231.7	231.8	232.1	232.3	232.6	232.9	233.0	232.6
117.5°	256.7	257.1	257.4	257.8	258.2	258.8	259.5	260.1	260.8	261.1	260.6
120°	283.5	283.5	283.5	283.5	283.5	284.5	285.5	286.6	287.6	288.1	287.6
122.5°	309.5	309.9	310.2	310.6	311.0	311.6	312.3	312.9	313.6	313.9	313.3
125°	335.9	336.3	336.6	337.0	337.4	337.8	338.2	338.5	338.9	339.1	338.5
127.5°	361.2	361.7	362.2	362.7	363.2	363.7	364.2	364.7	365.2	365.5	364.8
130°	388.0	388.3	388.5	388.8	389.0	389.3	389.5	389.8	390.1	390.2	389.4
132.5°	412.9	413.5	414.2	414.8	415.4	415.3	415.2	415.1	415.0	414.9	414.3
135°	439.1	439.2	439.3	439.4	439.5	439.3	439.0	438.8	438.5	438.4	437.7
137.5°	463.2	463.3	463.4	463.5	463.6	463.4	463.1	462.9	462.6	462.5	461.9
140°	487.7	487.7	487.7	487.7	487.7	487.1	486.5	485.8	485.2	484.9	484.3
142.5°	510.0	509.9	509.8	509.6	509.5	509.1	508.7	508.4	508.0	507.8	507.2
145°	532.4	532.3	532.2	532.0	531.9	531.1	530.4	529.6	528.9	528.5	528.1
147.5°	552.5	552.2	551.9	551.7	551.4	550.9	550.4	549.9	549.4	549.1	548.5
150°	571.3	570.9	570.6	570.2	569.8	569.3	568.8	568.3	567.8	567.5	567.1
152.5°	590.2	589.7	589.2	588.7	588.2	587.6	586.9	586.3	585.6	585.3	584.9
155°	605.6	605.0	604.3	603.7	603.1	602.7	602.3	602.0	601.6	601.4	601.2
157.5°	621.0	620.1	619.2	618.3	617.4	617.2	616.9	616.7	616.4	616.3	616.2
160°	633.7	632.9	632.2	631.4	630.6	630.5	630.3	630.2	630.1	630.0	629.9
162.5°	645.7	644.8	643.9	643.0	642.1	642.0	641.8	641.7	641.6	641.5	641.5
165°	655.5	654.6	653.7	652.8	651.9	651.9	651.9	651.9	651.9	651.9	652.0
167.5°	664.1	663.2	662.3	661.4	660.5	660.5	660.5	660.5	660.5	660.5	660.7
170°	670.9	670.0	669.1	668.2	667.3	667.4	667.6	667.7	667.8	667.9	668.1
172.5°	676.1	675.2	674.3	673.4	672.5	672.6	672.8	672.9	673.0	673.1	673.3
175°	679.6	678.7	677.8	676.9	676.0	676.2	676.5	676.7	677.0	677.1	677.3
177.5°	681.3	680.5	679.8	679.0	678.2	678.5	678.7	679.0	679.3	679.4	679.6
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1723.2	1723.2	1723.2	1723.2
2.5°	1691.5	1691.5	1711.3	1732.5
5°	1654.4	1663.6	1695.4	1724.6
7.5°	1618.6	1634.5	1674.2	1711.3
10°	1574.9	1596.1	1645.1	1688.8
12.5°	1532.5	1552.4	1609.3	1658.3
15°	1472.9	1498.1	1559.0	1619.9
17.5°	1413.3	1438.5	1512.6	1584.2
20°	1343.1	1376.2	1459.7	1555.0
22.5°	1278.2	1319.3	1412.0	1488.8
25°	1206.7	1270.2	1356.3	1455.7
27.5°	1143.1	1206.7	1294.1	1394.8
30°	1071.6	1136.5	1226.5	1319.3
32.5°	1002.7	1062.3	1149.7	1263.6
35°	931.2	988.1	1072.9	1188.1
37.5°	866.3	921.9	1014.6	1120.6
40°	802.7	861.0	940.4	1046.4
42.5°	743.1	794.7	866.3	972.2
45°	688.8	725.9	792.1	891.4
47.5°	631.8	664.9	725.9	825.2
50°	578.8	606.6	659.6	752.3
52.5°	527.2	551.0	600.0	674.2
55°	480.8	503.3	539.1	611.9
57.5°	433.1	450.3	484.8	543.1
60°	386.8	402.7	430.5	478.2
62.5°	340.4	353.7	380.1	418.6
65°	299.3	309.9	329.8	362.9
67.5°	259.6	266.2	282.1	308.6
70°	221.2	226.5	239.7	260.9
72.5°	180.1	185.4	200.0	214.6
75°	145.7	147.0	157.6	169.5
77.5°	113.9	112.6	120.5	129.8
80°	78.1	82.1	88.7	92.7
82.5°	53.0	54.3	57.0	59.6
85°	29.1	30.5	30.5	34.4
87.5°	11.9	13.2	13.2	14.6
90°	5.2	3.7	2.1	0.6
92.5°	15.7	14.6	13.6	12.6
95°	33.7	32.4	31.1	29.8
97.5°	53.4	52.2	51.1	49.9
100°	76.0	74.9	73.9	72.9
102.5°	99.3	98.5	97.8	97.0
105°	124.5	124.2	123.8	123.4
107.5°	151.3	150.8	150.3	149.8
110°	177.3	176.6	175.8	175.0



TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	204.9	204.1	203.4	202.6
115°	231.8	231.1	230.3	229.5
117.5°	259.6	258.5	257.5	256.5
120°	286.6	285.5	284.5	283.5
122.5°	312.0	310.7	309.4	308.1
125°	337.4	336.3	335.1	334.0
127.5°	363.4	362.0	360.6	359.2
130°	387.7	386.0	384.4	382.7
132.5°	413.0	411.7	410.4	409.1
135°	436.3	434.9	433.5	432.1
137.5°	460.8	459.6	458.5	457.3
140°	483.2	482.0	480.9	479.7
142.5°	506.1	505.0	503.8	502.7
145°	527.2	526.3	525.4	524.5
147.5°	547.4	546.3	545.1	544.0
150°	566.4	565.6	564.9	564.1
152.5°	584.1	583.4	582.6	581.8
155°	600.8	600.4	600.0	599.6
157.5°	615.9	615.6	615.4	615.1
160°	629.6	629.4	629.1	628.9
162.5°	641.5	641.5	641.5	641.5
165°	652.1	652.2	652.3	652.4
167.5°	661.1	661.4	661.8	662.2
170°	668.5	668.8	669.2	669.6
172.5°	673.7	674.0	674.4	674.8
175°	677.7	678.0	678.4	678.8
177.5°	680.0	680.3	680.7	681.1
180°	680.0	680.0	680.0	680.0

TEST NUMBER: P999123

CATALOG NUMBER: SA2XXDIP-B865D530UB35-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.76	19.75	19.57	20.57	21.59	16.25	17.24	17.06	18.06	19.08
	3H	19.58	20.46	20.40	21.30	22.34	17.61	18.49	18.43	19.32	20.37
	4H	19.76	20.59	20.59	21.43	22.48	18.08	18.91	18.91	19.75	20.80
	6H	19.81	20.57	20.66	21.42	22.49	18.39	19.16	19.24	20.01	21.07
	8H	19.79	20.52	20.65	21.39	22.45	18.48	19.21	19.34	20.07	21.14
	12H	19.76	20.45	20.62	21.31	22.41	18.52	19.22	19.39	20.08	21.17
4H	2H	18.82	19.65	19.66	20.49	21.55	16.72	17.55	17.56	18.39	19.44
	3H	19.81	20.50	20.66	21.38	22.44	18.19	18.88	19.04	19.75	20.82
	4H	20.09	20.72	20.96	21.59	22.69	18.73	19.36	19.59	20.23	21.32
	6H	20.23	20.77	21.11	21.67	22.77	19.11	19.65	19.99	20.55	21.65
	8H	20.23	20.73	21.11	21.63	22.74	19.23	19.73	20.11	20.62	21.74
	12H	20.20	20.65	21.10	21.56	22.68	19.29	19.74	20.19	20.65	21.77
8H	4H	20.11	20.61	20.99	21.51	22.62	18.88	19.38	19.76	20.27	21.39
	6H	20.29	20.71	21.20	21.64	22.76	19.32	19.73	20.23	20.67	21.78
	8H	20.32	20.69	21.24	21.62	22.75	19.47	19.84	20.39	20.76	21.89
	12H	20.31	20.64	21.24	21.56	22.74	19.57	19.89	20.49	20.81	21.99
12H	4H	20.07	20.53	20.98	21.44	22.55	18.86	19.31	19.76	20.22	21.34
	6H	20.27	20.64	21.19	21.57	22.70	19.32	19.69	20.24	20.61	21.74
	8H	20.31	20.64	21.23	21.55	22.73	19.48	19.81	20.40	20.72	21.91