

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997953

Luminaire Tested: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P997953
REPORT IS A COMBINATION OF REPORTS P983690 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6061.0 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	103	99	95	92	97	94	90	87	84	81	79	75	73	71	67	66	64
2	94	87	81	76	89	83	77	73	74	70	67	67	64	61	60	57	55
3	87	77	70	64	82	73	67	62	66	61	57	60	56	52	54	50	48
4	80	69	61	55	75	66	59	53	59	54	49	54	49	45	48	45	42
5	73	62	54	48	69	59	52	46	54	48	43	49	44	40	44	40	37
6	68	56	48	42	64	53	46	41	49	43	38	44	39	35	40	36	33
7	63	51	43	37	60	49	41	36	44	38	34	41	35	32	37	33	29
8	59	46	39	33	56	44	37	32	41	35	30	37	32	29	34	30	27
9	55	43	35	30	52	41	34	29	38	32	28	34	29	26	32	27	24
10	51	39	32	27	49	38	31	27	35	29	25	32	27	24	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30413	30413	30413	30413
5°	30486	32427	30603	25799
10°	30132	35400	30321	21271
15°	29401	37339	29809	17916
20°	28943	35058	28943	15573
25°	28020	30119	28148	13925
30°	26503	23676	27007	12614
35°	25158	16372	25578	11542
40°	23613	12361	23882	10686
45°	21707	10158	22061	9762
50°	20059	8915	20095	8937
55°	18181	7596	18298	8040
60°	16177	6345	16401	7017
65°	14383	5161	14646	5992
70°	12598	4049	12919	4833
75°	10573	2940	10987	3505
80°	8255	1863	8846	2079
85°	5424	938	5848	694

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 31439 cd/sqm

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	3.0
10°-20°	532.6	8.8
20°-30°	773.0	12.8
30°-40°	814.9	13.4
40°-50°	721.1	11.9
50°-60°	575.8	9.5
60°-70°	391.1	6.5
70°-80°	200.1	3.3
80°-90°	49.1	0.8
90°-100°	40.3	0.7
100°-110°	128.0	2.1
110°-120°	219.1	3.6
120°-130°	288.1	4.8
130°-140°	323.4	5.3
140°-150°	317.1	5.2
150°-160°	266.0	4.4
160°-170°	176.4	2.9
170°-180°	61.7	1.0
0°-30°	1488.7	24.6
0°-40°	2303.6	38.0
0°-60°	3600.5	59.4
0°-90°	4240.9	70.0
90°-120°	387.4	6.4
90°-150°	1316.0	21.7
90°-180°	1820.0	30.0
0°-180°	6061.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1921	1921	1921	1921	1921	
5°	1923	2146	1930	1707	1923	182
15°	1806	2638	1831	1266	1806	510
25°	1623	2198	1630	1016	1623	742
35°	1325	1196	1347	843	1325	829
45°	994	721	1010	693	994	771
55°	682	506	687	536	682	609
65°	405	312	412	362	405	402
75°	189	154	196	183	189	203
85°	38	40	41	30	38	45
90°	0	19	0	19	0	4
95°	29	34	29	34	29	32
105°	118	122	118	122	118	125
115°	220	220	220	220	220	217
125°	320	321	320	321	320	286
135°	414	419	414	419	414	320
145°	502	508	502	508	502	314
155°	574	578	574	578	574	264
165°	625	625	625	625	625	176
175°	650	648	650	648	650	62
180°	651	651	651	651	651	

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1931.6	1936.1	1943.5	1944.9	1959.7	1971.5	1984.8	1984.8	1989.2	1987.8	1976.0
5°	1922.8	1936.1	1955.3	1971.5	1998.1	2009.9	2027.6	2040.9	2052.7	2061.6	2060.1
7.5°	1908.0	1931.6	1959.7	1990.7	2026.2	2046.8	2071.9	2095.6	2111.8	2126.6	2136.9
10°	1882.9	1922.8	1961.2	2002.5	2048.3	2076.4	2105.9	2136.9	2162.0	2190.1	2216.7
12.5°	1848.9	1906.5	1953.8	2008.4	2064.6	2095.6	2142.8	2166.5	2215.2	2286.1	2305.3
15°	1806.1	1884.4	1928.7	1998.1	2071.9	2097.1	2162.0	2200.4	2300.8	2345.2	2398.3
17.5°	1766.2	1853.4	1912.5	1992.2	2064.6	2113.3	2176.8	2255.1	2339.2	2402.7	2461.8
20°	1733.8	1817.9	1888.8	1977.4	2069.0	2131.0	2197.5	2292.0	2383.5	2448.5	2494.3
22.5°	1659.9	1767.7	1850.4	1949.4	2060.1	2145.8	2209.3	2312.7	2411.6	2451.5	2491.4
25°	1623.0	1716.0	1812.0	1924.3	2054.2	2156.1	2210.8	2326.0	2413.1	2427.9	2436.7
27.5°	1555.1	1659.9	1772.2	1900.6	2052.7	2138.4	2207.8	2312.7	2382.1	2371.7	2345.2
30°	1470.9	1599.4	1723.4	1862.2	2032.1	2125.1	2190.1	2286.1	2321.5	2268.4	2221.1
32.5°	1408.9	1530.0	1667.3	1828.3	2008.4	2097.1	2160.6	2235.9	2243.3	2147.3	2067.5
35°	1324.7	1459.1	1614.1	1784.0	1968.6	2048.3	2107.4	2153.2	2117.7	1983.3	1888.8
37.5°	1249.4	1382.3	1547.7	1720.5	1913.9	1992.2	2039.5	2046.8	1959.7	1841.6	1702.7
40°	1166.7	1304.0	1476.8	1658.4	1853.4	1921.3	1950.8	1928.7	1803.2	1665.8	1504.9
42.5°	1084.0	1219.8	1405.9	1592.0	1776.6	1834.2	1846.0	1785.4	1631.9	1470.9	1284.8
45°	993.9	1135.7	1321.7	1509.3	1688.0	1720.5	1721.9	1634.8	1453.2	1284.8	1112.0
47.5°	920.0	1051.5	1236.1	1423.6	1574.3	1596.4	1587.6	1487.1	1289.2	1100.2	949.6
50°	838.8	964.3	1147.5	1332.1	1460.6	1466.5	1444.3	1301.1	1107.6	934.8	815.2
52.5°	751.7	878.7	1047.0	1224.3	1339.5	1330.6	1287.8	1134.2	952.5	809.3	717.7
55°	682.3	794.5	952.5	1125.3	1206.5	1181.4	1134.2	977.6	834.4	713.3	633.5
57.5°	605.5	704.4	859.5	1010.1	1057.4	1033.8	986.5	840.3	707.4	615.8	562.7
60°	533.1	623.2	759.1	884.6	921.5	896.4	841.8	710.3	614.3	537.6	497.7
62.5°	466.7	544.9	658.7	773.8	788.6	763.5	716.2	609.9	527.2	466.7	437.1
65°	404.6	478.5	570.0	657.2	670.5	643.9	595.1	518.4	448.9	410.5	382.5
67.5°	344.1	403.2	484.4	547.9	555.3	530.2	490.3	428.3	385.4	344.1	323.4
70°	290.9	335.2	398.7	450.4	453.4	429.7	409.1	353.0	320.5	290.9	274.7
72.5°	239.2	270.3	319.0	357.4	358.9	344.1	324.9	289.5	261.4	240.7	224.5
75°	189.0	215.6	245.1	279.1	277.6	265.8	251.1	228.9	205.3	192.0	184.6
77.5°	144.7	161.0	184.6	206.8	206.8	200.8	192.0	175.7	161.0	147.7	140.3
80°	103.4	113.7	132.9	140.3	143.2	141.8	134.4	122.6	116.7	106.3	103.4
82.5°	66.5	73.8	82.7	90.1	94.5	91.6	90.1	84.2	75.3	72.4	69.4
85°	38.4	41.4	45.8	50.2	51.7	50.2	53.2	48.7	44.3	44.3	42.8
87.5°	16.2	17.7	20.7	20.7	22.2	22.2	20.7	22.2	22.2	20.7	19.2
90°	0.5	2.0	3.4	4.9	6.4	7.1	8.4	11.1	13.8	16.5	19.2
92.5°	12.1	13.1	14.1	15.0	16.0	16.5	16.6	16.7	16.8	16.9	17.0
95°	28.6	29.8	31.0	32.3	33.5	34.1	34.2	34.5	34.7	35.0	35.2
97.5°	47.8	48.9	50.0	51.1	52.2	52.7	52.9	53.4	53.9	54.4	54.9
100°	69.8	70.8	71.8	72.7	73.7	74.2	74.4	74.7	75.1	75.4	75.8
102.5°	92.8	93.5	94.3	95.0	95.7	96.1	96.3	96.8	97.3	97.8	98.3
105°	118.1	118.5	118.9	119.2	119.6	119.8	119.9	120.2	120.4	120.7	120.9
107.5°	143.4	143.9	144.4	144.9	145.4	145.6	145.6	145.6	145.6	145.6	145.6
110°	167.6	168.3	169.1	169.8	170.5	170.9	170.9	170.9	170.9	170.9	170.9



TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	193.9	194.6	195.4	196.1	196.8	197.2	197.1	197.0	196.9	196.8	196.7
115°	219.8	220.5	221.3	222.0	222.7	223.1	223.0	222.7	222.5	222.2	222.0
117.5°	245.6	246.6	247.6	248.5	249.5	250.0	249.7	249.1	248.4	247.8	247.2
120°	271.4	272.4	273.4	274.3	275.3	275.8	275.3	274.3	273.4	272.4	271.4
122.5°	295.0	296.2	297.4	298.7	299.9	300.5	300.2	299.6	299.0	298.4	297.8
125°	319.7	320.8	321.9	323.0	324.1	324.7	324.5	324.1	323.8	323.4	323.0
127.5°	343.9	345.3	346.6	348.0	349.3	350.0	349.8	349.3	348.8	348.3	347.8
130°	366.4	368.0	369.6	371.2	372.8	373.6	373.5	373.2	373.0	372.7	372.5
132.5°	391.7	392.9	394.1	395.4	396.6	397.2	397.3	397.4	397.5	397.7	397.8
135°	413.7	415.0	416.4	417.7	419.0	419.7	419.8	420.1	420.3	420.6	420.8
137.5°	437.9	439.0	440.1	441.2	442.3	442.8	442.9	443.2	443.4	443.7	443.9
140°	459.3	460.4	461.5	462.6	463.7	464.2	464.5	465.1	465.8	466.4	467.0
142.5°	481.3	482.4	483.5	484.6	485.7	486.2	486.4	486.8	487.1	487.5	487.9
145°	502.1	503.0	503.8	504.7	505.6	506.0	506.4	507.1	507.8	508.6	509.3
147.5°	520.8	521.9	523.0	524.1	525.2	525.8	526.0	526.5	527.0	527.5	528.0
150°	540.1	540.8	541.5	542.2	542.9	543.3	543.5	544.0	544.5	545.0	545.5
152.5°	557.1	557.8	558.6	559.3	560.0	560.4	560.7	561.3	561.9	562.5	563.1
155°	574.1	574.5	574.9	575.2	575.6	575.8	576.0	576.3	576.7	577.0	577.4
157.5°	588.9	589.1	589.4	589.6	589.9	590.0	590.1	590.4	590.6	590.9	591.1
160°	602.1	602.3	602.6	602.8	603.1	603.2	603.3	603.4	603.5	603.7	603.8
162.5°	614.2	614.2	614.2	614.2	614.2	614.2	614.3	614.4	614.5	614.7	614.8
165°	624.7	624.6	624.4	624.3	624.2	624.1	624.1	624.1	624.1	624.1	624.1
167.5°	634.0	633.6	633.2	632.9	632.5	632.3	632.3	632.3	632.3	632.3	632.3
170°	641.1	640.7	640.4	640.0	639.7	639.5	639.4	639.3	639.2	639.0	638.9
172.5°	646.1	645.7	645.3	645.0	644.6	644.4	644.3	644.2	644.1	644.0	643.9
175°	649.9	649.5	649.2	648.8	648.5	648.3	648.2	647.9	647.7	647.4	647.2
177.5°	652.1	651.7	651.4	651.0	650.7	650.5	650.4	650.1	649.9	649.6	649.4
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1996.6	1998.1	2001.1	2015.8	2023.2	2024.7	2018.8	2032.1	2036.5	2032.1	2029.1
5°	2091.1	2100.0	2117.7	2136.9	2135.4	2136.9	2145.8	2154.6	2157.6	2145.8	2150.2
7.5°	2173.8	2191.6	2210.8	2240.3	2240.3	2255.1	2261.0	2268.4	2286.1	2277.2	2274.3
10°	2268.4	2292.0	2327.4	2374.7	2376.2	2390.9	2405.7	2429.3	2436.7	2430.8	2433.8
12.5°	2386.5	2432.3	2435.2	2486.9	2510.6	2513.5	2537.1	2532.7	2547.5	2547.5	2572.6
15°	2438.2	2509.1	2549.0	2599.2	2613.9	2596.2	2615.4	2636.1	2637.6	2637.6	2636.1
17.5°	2531.2	2559.3	2599.2	2625.7	2631.7	2631.7	2633.1	2642.0	2636.1	2624.3	2633.1
20°	2550.4	2562.2	2577.0	2574.1	2577.0	2562.2	2547.5	2532.7	2534.2	2526.8	2549.0
22.5°	2515.0	2512.0	2478.1	2455.9	2455.9	2426.4	2398.3	2385.0	2371.7	2376.2	2383.5
25°	2426.4	2380.6	2339.2	2306.8	2299.4	2252.1	2213.7	2201.9	2179.8	2197.5	2200.4
27.5°	2284.6	2232.9	2166.5	2138.4	2100.0	2080.8	2054.2	2018.8	1973.0	1999.6	1995.2
30°	2132.5	2055.7	2001.1	1933.1	1872.6	1868.1	1817.9	1758.9	1735.2	1735.2	1748.5
32.5°	1962.7	1860.8	1781.0	1685.0	1626.0	1600.8	1540.3	1481.2	1494.5	1450.2	1466.5
35°	1764.8	1630.4	1530.0	1436.9	1392.6	1363.1	1284.8	1252.3	1216.9	1196.2	1234.6
37.5°	1575.7	1420.7	1292.2	1190.3	1174.1	1120.9	1067.7	1047.0	1026.4	1035.2	1033.8
40°	1345.4	1208.0	1092.8	1013.1	985.0	959.9	924.5	899.4	886.1	893.5	894.9
42.5°	1137.1	1021.9	936.3	880.2	856.5	838.8	821.1	800.4	796.0	796.0	801.9
45°	976.2	881.6	824.1	778.3	765.0	751.7	738.4	729.5	726.6	720.7	725.1
47.5°	847.7	772.4	736.9	703.0	688.2	685.2	673.4	669.0	663.1	661.6	663.1
50°	739.9	692.6	660.1	640.9	630.6	626.2	620.3	611.4	608.4	615.8	612.9
52.5°	664.6	620.3	602.5	583.3	577.4	571.5	562.7	564.1	562.7	559.7	559.7
55°	589.2	561.2	543.5	528.7	527.2	521.3	513.9	511.0	509.5	506.5	511.0
57.5°	528.7	506.5	490.3	477.0	471.1	471.1	463.7	457.8	457.8	456.3	457.8
60°	468.1	446.0	435.7	422.4	417.9	416.5	412.0	409.1	404.6	404.6	404.6
62.5°	412.0	394.3	382.5	370.7	372.2	364.8	358.9	355.9	355.9	357.4	357.4
65°	358.9	347.0	332.3	321.9	319.0	317.5	314.6	313.1	308.7	311.6	311.6
67.5°	310.1	293.9	285.0	280.6	276.2	274.7	271.7	268.8	267.3	265.8	268.8
70°	261.4	248.1	240.7	237.8	233.3	231.9	230.4	225.9	227.4	228.9	230.4
72.5°	217.1	205.3	203.8	194.9	194.9	194.9	189.0	192.0	190.5	187.6	190.5
75°	171.3	165.4	162.4	158.0	159.5	158.0	156.5	152.1	152.1	153.6	155.1
77.5°	135.9	130.0	128.5	124.1	121.1	124.1	121.1	119.6	119.6	121.1	121.1
80°	100.4	97.5	93.0	93.0	93.0	91.6	91.6	91.6	90.1	88.6	90.1
82.5°	66.5	66.5	65.0	63.5	65.0	62.0	63.5	63.5	63.5	63.5	63.5
85°	42.8	41.4	41.4	39.9	39.9	39.9	41.4	38.4	38.4	39.9	39.9
87.5°	19.2	19.2	19.2	20.7	19.2	19.2	19.2	20.7	19.2	19.2	19.2
90°	19.0	18.7	18.5	18.2	18.1	18.2	18.3	18.4	18.6	18.7	18.6
92.5°	17.1	17.3	17.4	17.5	17.6	17.6	17.6	17.6	17.6	17.6	17.6
95°	35.2	35.2	35.2	35.2	35.2	35.1	34.8	34.6	34.3	34.1	34.3
97.5°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9
100°	75.8	75.8	75.8	75.8	75.8	75.7	75.6	75.5	75.4	75.3	75.4
102.5°	98.4	98.6	98.7	98.8	98.9	98.8	98.7	98.6	98.4	98.3	98.4
105°	121.1	121.4	121.6	121.9	122.0	122.0	122.0	122.0	122.0	122.0	122.0
107.5°	145.7	145.8	145.9	146.0	146.1	145.8	145.2	144.6	144.0	143.4	144.0
110°	170.9	170.9	170.9	170.9	170.9	170.7	170.3	170.0	169.6	169.2	169.6

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	196.3	195.9	195.6	195.2	195.0	194.9	194.6	194.4	194.1	193.9	194.1
115°	221.9	221.7	221.6	221.5	221.4	221.2	220.9	220.5	220.2	219.8	220.2
117.5°	246.8	246.5	246.1	245.8	245.6	245.4	245.0	244.7	244.3	243.9	244.3
120°	271.4	271.4	271.4	271.4	271.4	271.2	270.9	270.5	270.2	269.8	270.2
122.5°	297.4	297.0	296.7	296.3	296.1	296.0	295.7	295.5	295.2	295.0	295.2
125°	322.6	322.3	321.9	321.6	321.4	321.3	321.2	321.1	320.9	320.8	320.9
127.5°	347.3	346.8	346.3	345.8	345.6	345.4	345.0	344.7	344.3	343.9	344.3
130°	372.3	372.0	371.8	371.5	371.4	371.2	370.7	370.2	369.7	369.2	369.7
132.5°	397.2	396.6	395.9	395.3	395.0	394.8	394.5	394.1	393.8	393.4	393.8
135°	420.7	420.6	420.5	420.4	420.3	420.1	419.7	419.4	419.0	418.6	419.0
137.5°	443.8	443.7	443.6	443.5	443.4	443.2	442.7	442.2	441.7	441.2	441.7
140°	467.0	467.0	467.0	467.0	467.0	466.8	466.3	465.8	465.3	464.8	465.3
142.5°	488.0	488.1	488.2	488.3	488.4	488.2	487.7	487.2	486.7	486.2	486.7
145°	509.4	509.5	509.6	509.7	509.8	509.6	509.1	508.6	508.1	507.6	508.1
147.5°	528.2	528.5	528.7	529.0	529.1	528.9	528.4	527.9	527.4	526.9	527.4
150°	545.9	546.3	546.6	547.0	547.2	547.0	546.6	546.3	545.9	545.5	545.9
152.5°	563.6	564.1	564.6	565.1	565.3	565.1	564.6	564.1	563.6	563.1	563.6
155°	578.0	578.6	579.3	579.9	580.2	580.0	579.6	579.3	578.9	578.5	578.9
157.5°	592.0	592.8	593.7	594.6	595.0	594.7	594.1	593.4	592.8	592.2	592.8
160°	604.5	605.3	606.0	606.7	607.1	606.9	606.4	605.9	605.4	604.9	605.4
162.5°	615.6	616.5	617.3	618.2	618.6	618.3	617.7	617.1	616.5	615.9	616.5
165°	625.0	625.8	626.7	627.6	628.0	627.7	627.1	626.4	625.8	625.2	625.8
167.5°	633.2	634.0	634.9	635.8	636.2	635.9	635.3	634.6	634.0	633.4	634.0
170°	639.8	640.6	641.5	642.4	642.8	642.4	641.7	641.0	640.2	639.5	640.2
172.5°	644.7	645.6	646.4	647.3	647.7	647.3	646.6	645.9	645.1	644.4	645.1
175°	648.0	648.9	649.7	650.6	651.0	650.6	649.9	649.2	648.4	647.7	648.4
177.5°	650.1	650.9	651.6	652.3	652.7	652.3	651.6	650.9	650.1	649.4	650.1
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	2036.5	2026.2	2017.3	2018.8	2026.2	2020.3	2005.5	1986.3	1978.9	1970.0	1978.9
5°	2159.1	2150.2	2132.5	2134.0	2129.5	2123.6	2100.0	2070.5	2070.5	2046.8	2043.9
7.5°	2280.2	2266.9	2255.1	2252.1	2235.9	2224.1	2203.4	2162.0	2145.8	2117.7	2101.5
10°	2416.0	2405.7	2392.4	2376.2	2367.3	2346.6	2312.7	2252.1	2222.6	2184.2	2156.1
12.5°	2553.4	2551.9	2522.4	2489.9	2488.4	2455.9	2432.3	2351.1	2311.2	2259.5	2193.0
15°	2640.5	2633.1	2616.9	2600.6	2605.1	2569.6	2516.5	2420.5	2393.9	2331.9	2261.0
17.5°	2639.0	2639.0	2634.6	2631.7	2627.2	2616.9	2587.3	2523.8	2481.0	2402.7	2336.3
20°	2554.9	2574.1	2578.5	2577.0	2591.8	2599.2	2597.7	2557.8	2523.8	2454.4	2386.5
22.5°	2386.5	2430.8	2450.0	2461.8	2492.8	2509.1	2547.5	2532.7	2523.8	2472.2	2414.6
25°	2230.0	2244.7	2302.3	2305.3	2348.1	2388.0	2426.4	2451.5	2484.0	2464.8	2416.0
27.5°	2027.6	2061.6	2103.0	2134.0	2142.8	2224.1	2287.6	2334.8	2408.7	2414.6	2398.3
30°	1798.7	1815.0	1882.9	1924.3	1971.5	2030.6	2122.2	2203.4	2269.8	2330.4	2351.1
32.5°	1519.6	1586.1	1626.0	1676.2	1717.5	1822.4	1934.6	2039.5	2116.2	2218.1	2262.5
35°	1264.1	1315.8	1383.8	1404.4	1479.8	1568.4	1714.6	1848.9	1965.6	2069.0	2159.1
37.5°	1053.0	1094.3	1166.7	1199.2	1243.5	1357.2	1479.8	1646.6	1786.9	1913.9	2026.2
40°	908.2	939.2	993.9	1004.2	1041.1	1144.5	1243.5	1400.0	1586.1	1757.4	1880.0
42.5°	809.3	824.1	861.0	874.3	897.9	967.3	1055.9	1203.6	1376.4	1553.6	1726.4
45°	738.4	748.7	770.9	782.7	812.2	843.3	915.6	1033.8	1169.6	1348.3	1534.4
47.5°	674.9	688.2	697.0	704.4	720.7	754.6	801.9	889.0	1019.0	1182.9	1363.1
50°	621.7	626.2	642.4	643.9	654.2	676.4	720.7	773.8	877.2	1010.1	1184.4
52.5°	568.6	573.0	583.3	593.7	598.1	615.8	645.4	689.7	766.5	871.3	1026.4
55°	515.4	521.3	531.6	539.0	543.5	558.2	576.0	618.8	679.3	753.2	880.2
57.5°	462.2	475.5	478.5	482.9	490.3	506.5	522.8	547.9	595.1	663.1	756.1
60°	412.0	416.5	426.8	431.2	438.6	447.5	468.1	487.3	521.3	574.5	658.7
62.5°	360.3	370.7	375.1	379.5	385.4	395.8	409.1	429.7	459.3	502.1	568.6
65°	316.0	317.5	326.4	332.3	338.2	345.6	358.9	378.1	395.8	435.7	484.4
67.5°	273.2	276.2	279.1	285.0	292.4	299.8	311.6	321.9	344.1	370.7	409.1
70°	231.9	231.9	239.2	243.7	242.2	251.1	259.9	271.7	288.0	313.1	344.1
72.5°	194.9	193.5	199.4	200.8	203.8	209.7	215.6	227.4	236.3	255.5	279.1
75°	155.1	158.0	161.0	161.0	165.4	169.8	175.7	181.6	192.0	203.8	221.5
77.5°	122.6	122.6	125.5	127.0	131.4	130.0	135.9	141.8	149.2	159.5	172.8
80°	90.1	93.0	93.0	93.0	94.5	96.0	101.9	106.3	110.8	118.1	124.1
82.5°	63.5	63.5	66.5	66.5	66.5	69.4	69.4	70.9	73.8	78.3	82.7
85°	39.9	39.9	39.9	41.4	39.9	41.4	44.3	42.8	44.3	47.3	47.3
87.5°	19.2	19.2	19.2	19.2	19.2	20.7	19.2	20.7	22.2	22.2	22.2
90°	18.4	18.3	18.2	18.1	18.2	18.5	18.7	19.0	19.2	16.5	13.8
92.5°	17.6	17.6	17.6	17.6	17.5	17.4	17.3	17.1	17.0	16.9	16.8
95°	34.6	34.8	35.1	35.2	35.2	35.2	35.2	35.2	35.2	35.0	34.7
97.5°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.4	53.9
100°	75.5	75.6	75.7	75.8	75.8	75.8	75.8	75.8	75.8	75.4	75.1
102.5°	98.6	98.7	98.8	98.9	98.8	98.7	98.6	98.4	98.3	97.8	97.3
105°	122.0	122.0	122.0	122.0	121.9	121.6	121.4	121.1	120.9	120.7	120.4
107.5°	144.6	145.2	145.8	146.1	146.0	145.9	145.8	145.7	145.6	145.6	145.6
110°	170.0	170.3	170.7	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	194.4	194.6	194.9	195.0	195.2	195.6	195.9	196.3	196.7	196.8	196.9
115°	220.5	220.9	221.2	221.4	221.5	221.6	221.7	221.9	222.0	222.2	222.5
117.5°	244.7	245.0	245.4	245.6	245.8	246.1	246.5	246.8	247.2	247.8	248.4
120°	270.5	270.9	271.2	271.4	271.4	271.4	271.4	271.4	271.4	272.4	273.4
122.5°	295.5	295.7	296.0	296.1	296.3	296.7	297.0	297.4	297.8	298.4	299.0
125°	321.1	321.2	321.3	321.4	321.6	321.9	322.3	322.6	323.0	323.4	323.8
127.5°	344.7	345.0	345.4	345.6	345.8	346.3	346.8	347.3	347.8	348.3	348.8
130°	370.2	370.7	371.2	371.4	371.5	371.8	372.0	372.3	372.5	372.7	373.0
132.5°	394.1	394.5	394.8	395.0	395.3	395.9	396.6	397.2	397.8	397.7	397.5
135°	419.4	419.7	420.1	420.3	420.4	420.5	420.6	420.7	420.8	420.6	420.3
137.5°	442.2	442.7	443.2	443.4	443.5	443.6	443.7	443.8	443.9	443.7	443.4
140°	465.8	466.3	466.8	467.0	467.0	467.0	467.0	467.0	467.0	466.4	465.8
142.5°	487.2	487.7	488.2	488.4	488.3	488.2	488.1	488.0	487.9	487.5	487.1
145°	508.6	509.1	509.6	509.8	509.7	509.6	509.5	509.4	509.3	508.6	507.8
147.5°	527.9	528.4	528.9	529.1	529.0	528.7	528.5	528.2	528.0	527.5	527.0
150°	546.3	546.6	547.0	547.2	547.0	546.6	546.3	545.9	545.5	545.0	544.5
152.5°	564.1	564.6	565.1	565.3	565.1	564.6	564.1	563.6	563.1	562.5	561.9
155°	579.3	579.6	580.0	580.2	579.9	579.3	578.6	578.0	577.4	577.0	576.7
157.5°	593.4	594.1	594.7	595.0	594.6	593.7	592.8	592.0	591.1	590.9	590.6
160°	605.9	606.4	606.9	607.1	606.7	606.0	605.3	604.5	603.8	603.7	603.5
162.5°	617.1	617.7	618.3	618.6	618.2	617.3	616.5	615.6	614.8	614.7	614.5
165°	626.4	627.1	627.7	628.0	627.6	626.7	625.8	625.0	624.1	624.1	624.1
167.5°	634.6	635.3	635.9	636.2	635.8	634.9	634.0	633.2	632.3	632.3	632.3
170°	641.0	641.7	642.4	642.8	642.4	641.5	640.6	639.8	638.9	639.0	639.2
172.5°	645.9	646.6	647.3	647.7	647.3	646.4	645.6	644.7	643.9	644.0	644.1
175°	649.2	649.9	650.6	651.0	650.6	649.7	648.9	648.0	647.2	647.4	647.7
177.5°	650.9	651.6	652.3	652.7	652.3	651.6	650.9	650.1	649.4	649.6	649.9
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1971.5	1964.1	1959.7	1962.7	1953.8	1931.6	1931.6	1939.0	1930.2	1921.3	1908.0
5°	2026.2	2011.4	2002.5	2001.1	1980.4	1944.9	1937.6	1930.2	1911.0	1890.3	1868.1
7.5°	2079.3	2052.7	2038.0	2027.6	1998.1	1952.3	1933.1	1916.9	1885.9	1854.9	1826.8
10°	2123.6	2085.2	2067.5	2051.3	2012.9	1955.3	1924.3	1894.7	1854.9	1815.0	1779.5
12.5°	2159.1	2114.8	2092.6	2069.0	2021.7	1946.4	1908.0	1860.8	1820.9	1767.7	1732.3
15°	2218.1	2126.6	2105.9	2083.8	2035.0	1931.6	1884.4	1831.2	1776.6	1705.7	1667.3
17.5°	2265.4	2142.8	2141.4	2094.1	2030.6	1925.7	1853.4	1784.0	1724.9	1654.0	1593.5
20°	2293.5	2167.9	2144.3	2095.6	2015.8	1885.9	1810.6	1733.8	1670.3	1584.6	1524.1
22.5°	2317.1	2203.4	2141.4	2082.3	1984.8	1872.6	1761.8	1689.5	1602.3	1509.3	1451.7
25°	2326.0	2210.8	2145.8	2077.9	1962.7	1834.2	1708.7	1630.4	1532.9	1448.7	1370.5
27.5°	2327.4	2209.3	2129.5	2058.7	1931.6	1784.0	1655.5	1572.8	1465.0	1367.5	1289.2
30°	2312.7	2193.0	2120.7	2043.9	1902.1	1738.2	1590.5	1498.9	1383.8	1286.3	1205.1
32.5°	2268.4	2160.6	2101.5	2017.3	1863.7	1674.7	1528.5	1426.6	1305.5	1209.5	1131.2
35°	2194.5	2120.7	2055.7	1977.4	1813.5	1615.6	1466.5	1346.8	1224.3	1132.7	1058.9
37.5°	2103.0	2063.1	2002.5	1925.7	1755.9	1562.5	1397.0	1264.1	1141.6	1053.0	980.6
40°	1978.9	1989.2	1930.2	1860.8	1688.0	1490.1	1307.0	1180.0	1064.8	982.1	911.2
42.5°	1844.5	1887.3	1853.4	1786.9	1612.7	1410.3	1240.5	1100.2	988.0	902.3	843.3
45°	1699.8	1773.6	1753.0	1704.2	1534.4	1326.2	1146.0	1010.1	911.2	828.5	776.8
47.5°	1541.8	1646.6	1646.6	1611.2	1447.3	1242.0	1064.8	926.0	828.5	769.4	719.2
50°	1380.8	1498.9	1518.1	1494.5	1349.8	1146.0	965.8	840.3	756.1	698.5	661.6
52.5°	1212.4	1349.8	1385.2	1373.4	1246.4	1054.4	884.6	762.0	685.2	635.0	602.5
55°	1051.5	1211.0	1249.4	1253.8	1135.7	954.0	794.5	686.7	612.9	578.9	550.8
57.5°	899.4	1053.0	1095.8	1103.2	1023.4	862.4	710.3	615.8	549.4	521.3	499.2
60°	769.4	897.9	954.0	970.3	900.8	756.1	632.1	540.5	490.3	463.7	443.0
62.5°	663.1	766.5	825.5	830.0	798.9	663.1	550.8	474.1	431.2	407.6	397.3
65°	559.7	652.7	688.2	705.9	680.8	574.5	475.5	412.0	378.1	357.4	347.0
67.5°	477.0	536.1	565.6	589.2	564.1	484.4	404.6	353.0	327.8	307.2	301.3
70°	391.4	440.1	462.2	485.9	463.7	403.2	345.6	298.3	276.2	259.9	252.5
72.5°	313.1	351.5	372.2	386.9	373.6	323.4	276.2	243.7	227.4	215.6	211.2
75°	248.1	274.7	286.5	296.8	290.9	252.5	223.0	196.4	181.6	171.3	168.4
77.5°	189.0	208.2	221.5	224.5	217.1	192.0	166.9	150.6	138.8	132.9	130.0
80°	134.4	146.2	153.6	158.0	150.6	140.3	122.6	110.8	100.4	93.0	91.6
82.5°	90.1	96.0	101.9	100.4	97.5	88.6	78.3	72.4	67.9	62.0	62.0
85°	51.7	53.2	56.1	57.6	56.1	50.2	44.3	41.4	38.4	34.0	34.0
87.5°	22.2	23.6	23.6	25.1	22.2	22.2	19.2	16.2	16.2	14.8	13.3
90°	11.1	8.4	7.1	6.4	4.9	3.4	2.0	0.5	2.0	3.4	4.9
92.5°	16.7	16.6	16.5	16.0	15.0	14.1	13.1	12.1	13.1	14.1	15.0
95°	34.5	34.2	34.1	33.5	32.3	31.0	29.8	28.6	29.8	31.0	32.3
97.5°	53.4	52.9	52.7	52.2	51.1	50.0	48.9	47.8	48.9	50.0	51.1
100°	74.7	74.4	74.2	73.7	72.7	71.8	70.8	69.8	70.8	71.8	72.7
102.5°	96.8	96.3	96.1	95.7	95.0	94.3	93.5	92.8	93.5	94.3	95.0
105°	120.2	119.9	119.8	119.6	119.2	118.9	118.5	118.1	118.5	118.9	119.2
107.5°	145.6	145.6	145.6	145.4	144.9	144.4	143.9	143.4	143.9	144.4	144.9
110°	170.9	170.9	170.9	170.5	169.8	169.1	168.3	167.6	168.3	169.1	169.8

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	197.0	197.1	197.2	196.8	196.1	195.4	194.6	193.9	194.6	195.4	196.1
115°	222.7	223.0	223.1	222.7	222.0	221.3	220.5	219.8	220.5	221.3	222.0
117.5°	249.1	249.7	250.0	249.5	248.5	247.6	246.6	245.6	246.6	247.6	248.5
120°	274.3	275.3	275.8	275.3	274.3	273.4	272.4	271.4	272.4	273.4	274.3
122.5°	299.6	300.2	300.5	299.9	298.7	297.4	296.2	295.0	296.2	297.4	298.7
125°	324.1	324.5	324.7	324.1	323.0	321.9	320.8	319.7	320.8	321.9	323.0
127.5°	349.3	349.8	350.0	349.3	348.0	346.6	345.3	343.9	345.3	346.6	348.0
130°	373.2	373.5	373.6	372.8	371.2	369.6	368.0	366.4	368.0	369.6	371.2
132.5°	397.4	397.3	397.2	396.6	395.4	394.1	392.9	391.7	392.9	394.1	395.4
135°	420.1	419.8	419.7	419.0	417.7	416.4	415.0	413.7	415.0	416.4	417.7
137.5°	443.2	442.9	442.8	442.3	441.2	440.1	439.0	437.9	439.0	440.1	441.2
140°	465.1	464.5	464.2	463.7	462.6	461.5	460.4	459.3	460.4	461.5	462.6
142.5°	486.8	486.4	486.2	485.7	484.6	483.5	482.4	481.3	482.4	483.5	484.6
145°	507.1	506.4	506.0	505.6	504.7	503.8	503.0	502.1	503.0	503.8	504.7
147.5°	526.5	526.0	525.8	525.2	524.1	523.0	521.9	520.8	521.9	523.0	524.1
150°	544.0	543.5	543.3	542.9	542.2	541.5	540.8	540.1	540.8	541.5	542.2
152.5°	561.3	560.7	560.4	560.0	559.3	558.6	557.8	557.1	557.8	558.6	559.3
155°	576.3	576.0	575.8	575.6	575.2	574.9	574.5	574.1	574.5	574.9	575.2
157.5°	590.4	590.1	590.0	589.9	589.6	589.4	589.1	588.9	589.1	589.4	589.6
160°	603.4	603.3	603.2	603.1	602.8	602.6	602.3	602.1	602.3	602.6	602.8
162.5°	614.4	614.3	614.2	614.2	614.2	614.2	614.2	614.2	614.2	614.2	614.2
165°	624.1	624.1	624.1	624.2	624.3	624.4	624.6	624.7	624.6	624.4	624.3
167.5°	632.3	632.3	632.3	632.5	632.9	633.2	633.6	634.0	633.6	633.2	632.9
170°	639.3	639.4	639.5	639.7	640.0	640.4	640.7	641.1	640.7	640.4	640.0
172.5°	644.2	644.3	644.4	644.6	645.0	645.3	645.7	646.1	645.7	645.3	645.0
175°	647.9	648.2	648.3	648.5	648.8	649.2	649.5	649.9	649.5	649.2	648.8
177.5°	650.1	650.4	650.5	650.7	651.0	651.4	651.7	652.1	651.7	651.4	651.0
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1900.6	1908.0	1906.5	1891.8	1875.5	1862.2	1837.1	1840.1	1831.2	1832.7	1841.6
5°	1853.4	1853.4	1847.5	1826.8	1800.2	1785.4	1757.4	1750.0	1732.3	1730.8	1729.3
7.5°	1803.2	1795.8	1788.4	1758.9	1726.4	1702.7	1664.3	1655.5	1637.8	1626.0	1620.0
10°	1744.1	1733.8	1719.0	1685.0	1645.2	1615.6	1575.7	1563.9	1530.0	1515.2	1506.3
12.5°	1679.1	1673.2	1649.6	1621.5	1556.5	1524.1	1466.5	1478.3	1444.3	1414.8	1410.3
15°	1614.1	1592.0	1578.7	1532.9	1454.6	1439.9	1394.1	1370.5	1339.5	1315.8	1315.8
17.5°	1550.6	1516.7	1487.1	1438.4	1380.8	1339.5	1305.5	1293.7	1255.3	1231.6	1227.2
20°	1466.5	1428.1	1420.7	1351.3	1311.4	1265.6	1233.1	1203.6	1175.5	1165.2	1157.8
22.5°	1386.7	1342.4	1330.6	1271.5	1231.6	1185.9	1153.4	1132.7	1112.0	1104.6	1091.4
25°	1301.1	1274.5	1256.8	1193.3	1148.9	1106.1	1084.0	1069.2	1050.0	1048.5	1039.7
27.5°	1218.4	1193.3	1175.5	1115.0	1082.5	1042.6	1024.9	1008.7	998.3	993.9	989.5
30°	1147.5	1119.4	1098.7	1054.4	1014.6	982.1	967.3	957.0	951.1	943.7	942.2
32.5°	1069.2	1053.0	1024.9	990.9	959.9	928.9	920.0	912.7	903.8	900.8	899.4
35°	1002.7	980.6	962.9	924.5	911.2	884.6	874.3	868.4	856.5	853.6	850.6
37.5°	937.8	917.1	897.9	874.3	849.2	834.4	828.5	819.6	813.7	815.2	812.2
40°	872.8	856.5	841.8	816.7	801.9	794.5	782.7	773.8	770.9	772.4	770.9
42.5°	809.3	794.5	785.7	766.5	751.7	744.3	736.9	728.1	732.5	732.5	736.9
45°	751.7	738.4	732.5	717.7	708.9	697.0	689.7	688.2	694.1	692.6	692.6
47.5°	692.6	688.2	680.8	667.5	655.7	648.3	646.8	646.8	652.7	655.7	654.2
50°	646.8	638.0	629.1	618.8	609.9	607.0	602.5	605.5	611.4	611.4	614.3
52.5°	589.2	583.3	580.4	571.5	565.6	565.6	565.6	567.1	571.5	576.0	574.5
55°	539.0	534.6	531.6	527.2	519.8	521.3	519.8	522.8	527.2	531.6	534.6
57.5°	485.9	484.4	481.4	474.1	474.1	472.6	477.0	478.5	485.9	488.8	493.3
60°	438.6	434.2	434.2	428.3	428.3	428.3	432.7	437.1	443.0	444.5	447.5
62.5°	388.4	388.4	386.9	382.5	382.5	386.9	388.4	394.3	397.3	397.3	401.7
65°	341.1	339.7	338.2	339.7	341.1	341.1	345.6	348.5	351.5	353.0	354.4
67.5°	293.9	292.4	295.4	293.9	296.8	302.7	301.3	305.7	310.1	310.1	311.6
70°	249.6	252.5	251.1	254.0	252.5	255.5	259.9	261.4	261.4	262.9	267.3
72.5°	208.2	208.2	208.2	206.8	208.2	211.2	214.1	215.6	218.6	220.0	224.5
75°	168.4	168.4	165.4	168.4	168.4	171.3	174.3	174.3	174.3	177.2	181.6
77.5°	127.0	128.5	127.0	130.0	130.0	131.4	134.4	132.9	135.9	137.3	138.8
80°	93.0	91.6	91.6	91.6	93.0	93.0	96.0	97.5	97.5	101.9	98.9
82.5°	59.1	60.5	59.1	60.5	60.5	62.0	60.5	62.0	63.5	66.5	65.0
85°	34.0	32.5	32.5	34.0	32.5	32.5	34.0	32.5	34.0	32.5	34.0
87.5°	13.3	11.8	11.8	11.8	11.8	10.3	10.3	8.9	8.9	8.9	7.4
90°	6.4	7.1	8.4	11.1	13.8	16.5	19.2	19.0	18.7	18.5	18.2
92.5°	16.0	16.5	16.6	16.7	16.8	16.9	17.0	17.1	17.3	17.4	17.5
95°	33.5	34.1	34.2	34.5	34.7	35.0	35.2	35.2	35.2	35.2	35.2
97.5°	52.2	52.7	52.9	53.4	53.9	54.4	54.9	54.9	54.9	54.9	54.9
100°	73.7	74.2	74.4	74.7	75.1	75.4	75.8	75.8	75.8	75.8	75.8
102.5°	95.7	96.1	96.3	96.8	97.3	97.8	98.3	98.4	98.6	98.7	98.8
105°	119.6	119.8	119.9	120.2	120.4	120.7	120.9	121.1	121.4	121.6	121.9
107.5°	145.4	145.6	145.6	145.6	145.6	145.6	145.6	145.7	145.8	145.9	146.0
110°	170.5	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	196.8	197.2	197.1	197.0	196.9	196.8	196.7	196.3	195.9	195.6	195.2
115°	222.7	223.1	223.0	222.7	222.5	222.2	222.0	221.9	221.7	221.6	221.5
117.5°	249.5	250.0	249.7	249.1	248.4	247.8	247.2	246.8	246.5	246.1	245.8
120°	275.3	275.8	275.3	274.3	273.4	272.4	271.4	271.4	271.4	271.4	271.4
122.5°	299.9	300.5	300.2	299.6	299.0	298.4	297.8	297.4	297.0	296.7	296.3
125°	324.1	324.7	324.5	324.1	323.8	323.4	323.0	322.6	322.3	321.9	321.6
127.5°	349.3	350.0	349.8	349.3	348.8	348.3	347.8	347.3	346.8	346.3	345.8
130°	372.8	373.6	373.5	373.2	373.0	372.7	372.5	372.3	372.0	371.8	371.5
132.5°	396.6	397.2	397.3	397.4	397.5	397.7	397.8	397.2	396.6	395.9	395.3
135°	419.0	419.7	419.8	420.1	420.3	420.6	420.8	420.7	420.6	420.5	420.4
137.5°	442.3	442.8	442.9	443.2	443.4	443.7	443.9	443.8	443.7	443.6	443.5
140°	463.7	464.2	464.5	465.1	465.8	466.4	467.0	467.0	467.0	467.0	467.0
142.5°	485.7	486.2	486.4	486.8	487.1	487.5	487.9	488.0	488.1	488.2	488.3
145°	505.6	506.0	506.4	507.1	507.8	508.6	509.3	509.4	509.5	509.6	509.7
147.5°	525.2	525.8	526.0	526.5	527.0	527.5	528.0	528.2	528.5	528.7	529.0
150°	542.9	543.3	543.5	544.0	544.5	545.0	545.5	545.9	546.3	546.6	547.0
152.5°	560.0	560.4	560.7	561.3	561.9	562.5	563.1	563.6	564.1	564.6	565.1
155°	575.6	575.8	576.0	576.3	576.7	577.0	577.4	578.0	578.6	579.3	579.9
157.5°	589.9	590.0	590.1	590.4	590.6	590.9	591.1	592.0	592.8	593.7	594.6
160°	603.1	603.2	603.3	603.4	603.5	603.7	603.8	604.5	605.3	606.0	606.7
162.5°	614.2	614.2	614.3	614.4	614.5	614.7	614.8	615.6	616.5	617.3	618.2
165°	624.2	624.1	624.1	624.1	624.1	624.1	624.1	625.0	625.8	626.7	627.6
167.5°	632.5	632.3	632.3	632.3	632.3	632.3	632.3	633.2	634.0	634.9	635.8
170°	639.7	639.5	639.4	639.3	639.2	639.0	638.9	639.8	640.6	641.5	642.4
172.5°	644.6	644.4	644.3	644.2	644.1	644.0	643.9	644.7	645.6	646.4	647.3
175°	648.5	648.3	648.2	647.9	647.7	647.4	647.2	648.0	648.9	649.7	650.6
177.5°	650.7	650.5	650.4	650.1	649.9	649.6	649.4	650.1	650.9	651.6	652.3
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1831.2	1835.7	1825.3	1822.4	1825.3	1815.0	1817.9	1820.9	1820.9	1825.3	1828.3
5°	1724.9	1719.0	1708.7	1705.7	1702.7	1707.2	1704.2	1708.7	1710.1	1720.5	1721.9
7.5°	1620.0	1611.2	1602.3	1593.5	1590.5	1583.1	1590.5	1590.5	1600.8	1597.9	1605.3
10°	1496.0	1494.5	1482.7	1478.3	1472.4	1460.6	1476.8	1472.4	1479.8	1493.0	1496.0
12.5°	1404.4	1388.2	1395.6	1374.9	1382.3	1370.5	1371.9	1371.9	1383.8	1385.2	1382.3
15°	1317.3	1304.0	1284.8	1276.0	1271.5	1265.6	1284.8	1286.3	1277.4	1298.1	1290.7
17.5°	1228.7	1228.7	1211.0	1206.5	1194.7	1200.6	1197.7	1199.2	1196.2	1211.0	1218.4
20°	1151.9	1144.5	1138.6	1140.1	1125.3	1122.4	1119.4	1122.4	1132.7	1143.0	1146.0
22.5°	1089.9	1085.4	1070.7	1073.6	1061.8	1066.2	1063.3	1070.7	1072.2	1072.2	1082.5
25°	1030.8	1024.9	1026.4	1020.5	1016.0	1016.0	1011.6	1016.0	1021.9	1024.9	1026.4
27.5°	986.5	982.1	974.7	970.3	973.2	965.8	971.7	976.2	976.2	973.2	976.2
30°	933.3	936.3	936.3	921.5	927.4	924.5	928.9	931.9	931.9	933.3	930.4
32.5°	897.9	889.0	887.6	886.1	886.1	880.2	880.2	884.6	886.1	887.6	892.0
35°	850.6	850.6	843.3	847.7	841.8	843.3	841.8	843.3	846.2	841.8	846.2
37.5°	807.8	809.3	806.3	809.3	810.8	807.8	804.9	810.8	807.8	807.8	804.9
40°	770.9	769.4	770.9	770.9	770.9	772.4	769.4	769.4	769.4	766.5	763.5
42.5°	739.9	731.0	734.0	735.4	731.0	731.0	732.5	731.0	735.4	726.6	726.6
45°	695.6	692.6	694.1	694.1	697.0	692.6	695.6	697.0	692.6	691.1	688.2
47.5°	655.7	658.7	655.7	658.7	658.7	661.6	655.7	657.2	658.7	652.7	648.3
50°	615.8	615.8	620.3	618.8	620.3	617.3	617.3	615.8	617.3	614.3	609.9
52.5°	578.9	574.5	581.9	580.4	578.9	577.4	576.0	577.4	574.5	571.5	571.5
55°	533.1	533.1	537.6	539.0	539.0	536.1	533.1	534.6	533.1	531.6	530.2
57.5°	496.2	490.3	493.3	494.7	494.7	490.3	493.3	490.3	490.3	491.8	487.3
60°	448.9	448.9	446.0	450.4	450.4	447.5	447.5	448.9	446.0	444.5	443.0
62.5°	398.7	400.2	404.6	406.1	407.6	404.6	401.7	403.2	403.2	398.7	400.2
65°	355.9	358.9	364.8	363.3	360.3	361.8	358.9	360.3	355.9	357.4	353.0
67.5°	314.6	313.1	314.6	314.6	317.5	316.0	313.1	313.1	311.6	316.0	311.6
70°	270.3	270.3	270.3	270.3	271.7	273.2	270.3	267.3	268.8	265.8	264.3
72.5°	224.5	225.9	224.5	227.4	223.0	225.9	225.9	224.5	223.0	223.0	223.0
75°	181.6	184.6	180.2	181.6	180.2	183.1	181.6	181.6	178.7	177.2	178.7
77.5°	138.8	140.3	137.3	138.8	137.3	138.8	138.8	137.3	137.3	137.3	137.3
80°	98.9	100.4	98.9	97.5	96.0	98.9	96.0	97.5	98.9	97.5	100.4
82.5°	63.5	63.5	62.0	63.5	60.5	60.5	62.0	62.0	60.5	63.5	60.5
85°	31.0	31.0	34.0	31.0	29.5	29.5	29.5	31.0	29.5	32.5	31.0
87.5°	7.4	5.9	7.4	7.4	5.9	5.9	7.4	5.9	7.4	8.9	5.9
90°	18.1	18.2	18.3	18.4	18.6	18.7	18.6	18.4	18.3	18.2	18.1
92.5°	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6
95°	35.2	35.1	34.8	34.6	34.3	34.1	34.3	34.6	34.8	35.1	35.2
97.5°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9
100°	75.8	75.7	75.6	75.5	75.4	75.3	75.4	75.5	75.6	75.7	75.8
102.5°	98.9	98.8	98.7	98.6	98.4	98.3	98.4	98.6	98.7	98.8	98.9
105°	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0
107.5°	146.1	145.8	145.2	144.6	144.0	143.4	144.0	144.6	145.2	145.8	146.1
110°	170.9	170.7	170.3	170.0	169.6	169.2	169.6	170.0	170.3	170.7	170.9

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	195.0	194.9	194.6	194.4	194.1	193.9	194.1	194.4	194.6	194.9	195.0
115°	221.4	221.2	220.9	220.5	220.2	219.8	220.2	220.5	220.9	221.2	221.4
117.5°	245.6	245.4	245.0	244.7	244.3	243.9	244.3	244.7	245.0	245.4	245.6
120°	271.4	271.2	270.9	270.5	270.2	269.8	270.2	270.5	270.9	271.2	271.4
122.5°	296.1	296.0	295.7	295.5	295.2	295.0	295.2	295.5	295.7	296.0	296.1
125°	321.4	321.3	321.2	321.1	320.9	320.8	320.9	321.1	321.2	321.3	321.4
127.5°	345.6	345.4	345.0	344.7	344.3	343.9	344.3	344.7	345.0	345.4	345.6
130°	371.4	371.2	370.7	370.2	369.7	369.2	369.7	370.2	370.7	371.2	371.4
132.5°	395.0	394.8	394.5	394.1	393.8	393.4	393.8	394.1	394.5	394.8	395.0
135°	420.3	420.1	419.7	419.4	419.0	418.6	419.0	419.4	419.7	420.1	420.3
137.5°	443.4	443.2	442.7	442.2	441.7	441.2	441.7	442.2	442.7	443.2	443.4
140°	467.0	466.8	466.3	465.8	465.3	464.8	465.3	465.8	466.3	466.8	467.0
142.5°	488.4	488.2	487.7	487.2	486.7	486.2	486.7	487.2	487.7	488.2	488.4
145°	509.8	509.6	509.1	508.6	508.1	507.6	508.1	508.6	509.1	509.6	509.8
147.5°	529.1	528.9	528.4	527.9	527.4	526.9	527.4	527.9	528.4	528.9	529.1
150°	547.2	547.0	546.6	546.3	545.9	545.5	545.9	546.3	546.6	547.0	547.2
152.5°	565.3	565.1	564.6	564.1	563.6	563.1	563.6	564.1	564.6	565.1	565.3
155°	580.2	580.0	579.6	579.3	578.9	578.5	578.9	579.3	579.6	580.0	580.2
157.5°	595.0	594.7	594.1	593.4	592.8	592.2	592.8	593.4	594.1	594.7	595.0
160°	607.1	606.9	606.4	605.9	605.4	604.9	605.4	605.9	606.4	606.9	607.1
162.5°	618.6	618.3	617.7	617.1	616.5	615.9	616.5	617.1	617.7	618.3	618.6
165°	628.0	627.7	627.1	626.4	625.8	625.2	625.8	626.4	627.1	627.7	628.0
167.5°	636.2	635.9	635.3	634.6	634.0	633.4	634.0	634.6	635.3	635.9	636.2
170°	642.8	642.4	641.7	641.0	640.2	639.5	640.2	641.0	641.7	642.4	642.8
172.5°	647.7	647.3	646.6	645.9	645.1	644.4	645.1	645.9	646.6	647.3	647.7
175°	651.0	650.6	649.9	649.2	648.4	647.7	648.4	649.2	649.9	650.6	651.0
177.5°	652.7	652.3	651.6	650.9	650.1	649.4	650.1	650.9	651.6	652.3	652.7
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1823.8	1835.7	1831.2	1815.0	1834.2	1834.2	1847.5	1847.5	1863.7	1869.6	1878.5
5°	1720.5	1729.3	1736.7	1729.3	1742.6	1763.3	1775.1	1785.4	1807.6	1816.5	1829.8
7.5°	1609.7	1626.0	1633.3	1633.3	1655.5	1679.1	1702.7	1717.5	1748.5	1760.3	1773.6
10°	1501.9	1521.1	1535.9	1534.4	1571.3	1586.1	1615.6	1649.6	1680.6	1698.3	1717.5
12.5°	1388.2	1398.5	1419.2	1448.7	1457.6	1484.2	1518.1	1561.0	1617.1	1633.3	1661.4
15°	1293.7	1321.7	1338.0	1351.3	1371.9	1397.0	1434.0	1475.3	1531.4	1566.9	1596.4
17.5°	1213.9	1250.8	1261.2	1258.2	1284.8	1323.2	1366.0	1397.0	1447.3	1490.1	1518.1
20°	1148.9	1163.7	1181.4	1188.8	1209.5	1250.8	1292.2	1327.6	1369.0	1403.0	1435.4
22.5°	1084.0	1095.8	1110.6	1123.8	1140.1	1163.7	1203.6	1247.9	1287.8	1320.3	1357.2
25°	1030.8	1038.2	1051.5	1061.8	1079.5	1095.8	1123.8	1172.6	1219.8	1239.0	1271.5
27.5°	979.1	985.0	993.9	1005.7	1014.6	1030.8	1055.9	1095.8	1144.5	1163.7	1208.0
30°	933.3	937.8	946.6	952.5	957.0	976.2	995.4	1026.4	1063.3	1089.9	1122.4
32.5°	890.5	894.9	903.8	905.3	911.2	921.5	939.2	967.3	999.8	1021.9	1050.0
35°	843.3	846.2	855.1	858.0	862.4	871.3	884.6	905.3	934.8	951.1	976.2
37.5°	806.3	804.9	810.8	815.2	821.1	825.5	830.0	850.6	872.8	887.6	906.8
40°	766.5	763.5	765.0	770.9	773.8	779.7	779.7	800.4	815.2	827.0	841.8
42.5°	726.6	725.1	722.2	725.1	728.1	729.5	731.0	745.8	760.6	770.9	787.1
45°	686.7	685.2	682.3	683.8	683.8	686.7	691.1	697.0	707.4	716.2	725.1
47.5°	649.8	646.8	642.4	640.9	643.9	643.9	643.9	649.8	660.1	663.1	671.9
50°	611.4	607.0	601.1	598.1	598.1	596.6	599.6	601.1	609.9	612.9	620.3
52.5°	570.0	567.1	561.2	555.3	556.8	553.8	555.3	556.8	559.7	564.1	568.6
55°	528.7	522.8	518.4	516.9	512.4	512.4	508.0	513.9	512.4	513.9	519.8
57.5°	488.8	482.9	475.5	472.6	468.1	466.7	463.7	462.2	463.7	468.1	472.6
60°	441.6	438.6	434.2	429.7	426.8	422.4	419.4	419.4	417.9	417.9	419.4
62.5°	395.8	394.3	388.4	386.9	384.0	381.0	376.6	373.6	373.6	376.6	378.1
65°	351.5	350.0	345.6	344.1	336.7	333.8	332.3	330.8	327.8	327.8	327.8
67.5°	310.1	305.7	305.7	298.3	292.4	289.5	286.5	285.0	285.0	285.0	286.5
70°	264.3	264.3	259.9	255.5	249.6	251.1	246.6	242.2	242.2	239.2	240.7
72.5°	220.0	218.6	214.1	212.7	208.2	203.8	200.8	203.8	199.4	197.9	199.4
75°	177.2	175.7	172.8	169.8	171.3	166.9	162.4	161.0	161.0	158.0	158.0
77.5°	135.9	138.8	132.9	131.4	128.5	125.5	124.1	122.6	122.6	122.6	125.5
80°	94.5	96.0	96.0	93.0	94.5	90.1	90.1	90.1	85.7	87.1	88.6
82.5°	60.5	60.5	59.1	60.5	59.1	59.1	57.6	57.6	56.1	56.1	57.6
85°	34.0	32.5	31.0	34.0	32.5	32.5	31.0	31.0	31.0	31.0	31.0
87.5°	7.4	8.9	8.9	8.9	8.9	10.3	10.3	10.3	11.8	11.8	11.8
90°	18.2	18.5	18.7	19.0	19.2	16.5	13.8	11.1	8.4	7.1	6.4
92.5°	17.5	17.4	17.3	17.1	17.0	16.9	16.8	16.7	16.6	16.5	16.0
95°	35.2	35.2	35.2	35.2	35.2	35.0	34.7	34.5	34.2	34.1	33.5
97.5°	54.9	54.9	54.9	54.9	54.9	54.4	53.9	53.4	52.9	52.7	52.2
100°	75.8	75.8	75.8	75.8	75.8	75.4	75.1	74.7	74.4	74.2	73.7
102.5°	98.8	98.7	98.6	98.4	98.3	97.8	97.3	96.8	96.3	96.1	95.7
105°	121.9	121.6	121.4	121.1	120.9	120.7	120.4	120.2	119.9	119.8	119.6
107.5°	146.0	145.9	145.8	145.7	145.6	145.6	145.6	145.6	145.6	145.6	145.4
110°	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.5

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	195.2	195.6	195.9	196.3	196.7	196.8	196.9	197.0	197.1	197.2	196.8
115°	221.5	221.6	221.7	221.9	222.0	222.2	222.5	222.7	223.0	223.1	222.7
117.5°	245.8	246.1	246.5	246.8	247.2	247.8	248.4	249.1	249.7	250.0	249.5
120°	271.4	271.4	271.4	271.4	271.4	272.4	273.4	274.3	275.3	275.8	275.3
122.5°	296.3	296.7	297.0	297.4	297.8	298.4	299.0	299.6	300.2	300.5	299.9
125°	321.6	321.9	322.3	322.6	323.0	323.4	323.8	324.1	324.5	324.7	324.1
127.5°	345.8	346.3	346.8	347.3	347.8	348.3	348.8	349.3	349.8	350.0	349.3
130°	371.5	371.8	372.0	372.3	372.5	372.7	373.0	373.2	373.5	373.6	372.8
132.5°	395.3	395.9	396.6	397.2	397.8	397.7	397.5	397.4	397.3	397.2	396.6
135°	420.4	420.5	420.6	420.7	420.8	420.6	420.3	420.1	419.8	419.7	419.0
137.5°	443.5	443.6	443.7	443.8	443.9	443.7	443.4	443.2	442.9	442.8	442.3
140°	467.0	467.0	467.0	467.0	467.0	466.4	465.8	465.1	464.5	464.2	463.7
142.5°	488.3	488.2	488.1	488.0	487.9	487.5	487.1	486.8	486.4	486.2	485.7
145°	509.7	509.6	509.5	509.4	509.3	508.6	507.8	507.1	506.4	506.0	505.6
147.5°	529.0	528.7	528.5	528.2	528.0	527.5	527.0	526.5	526.0	525.8	525.2
150°	547.0	546.6	546.3	545.9	545.5	545.0	544.5	544.0	543.5	543.3	542.9
152.5°	565.1	564.6	564.1	563.6	563.1	562.5	561.9	561.3	560.7	560.4	560.0
155°	579.9	579.3	578.6	578.0	577.4	577.0	576.7	576.3	576.0	575.8	575.6
157.5°	594.6	593.7	592.8	592.0	591.1	590.9	590.6	590.4	590.1	590.0	589.9
160°	606.7	606.0	605.3	604.5	603.8	603.7	603.5	603.4	603.3	603.2	603.1
162.5°	618.2	617.3	616.5	615.6	614.8	614.7	614.5	614.4	614.3	614.2	614.2
165°	627.6	626.7	625.8	625.0	624.1	624.1	624.1	624.1	624.1	624.1	624.2
167.5°	635.8	634.9	634.0	633.2	632.3	632.3	632.3	632.3	632.3	632.3	632.5
170°	642.4	641.5	640.6	639.8	638.9	639.0	639.2	639.3	639.4	639.5	639.7
172.5°	647.3	646.4	645.6	644.7	643.9	644.0	644.1	644.2	644.3	644.4	644.6
175°	650.6	649.7	648.9	648.0	647.2	647.4	647.7	647.9	648.2	648.3	648.5
177.5°	652.3	651.6	650.9	650.1	649.4	649.6	649.9	650.1	650.4	650.5	650.7
180°	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0	651.0

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1921.3	1921.3	1921.3	1921.3
2.5°	1885.9	1885.9	1908.0	1931.6
5°	1844.5	1854.9	1890.3	1922.8
7.5°	1804.6	1822.4	1866.7	1908.0
10°	1755.9	1779.5	1834.2	1882.9
12.5°	1708.7	1730.8	1794.3	1848.9
15°	1642.2	1670.3	1738.2	1806.1
17.5°	1575.7	1603.8	1686.5	1766.2
20°	1497.5	1534.4	1627.4	1733.8
22.5°	1425.1	1470.9	1574.3	1659.9
25°	1345.4	1416.2	1512.2	1623.0
27.5°	1274.5	1345.4	1442.8	1555.1
30°	1194.7	1267.1	1367.5	1470.9
32.5°	1117.9	1184.4	1281.9	1408.9
35°	1038.2	1101.7	1196.2	1324.7
37.5°	965.8	1027.9	1131.2	1249.4
40°	894.9	959.9	1048.5	1166.7
42.5°	828.5	886.1	965.8	1084.0
45°	767.9	809.3	883.1	993.9
47.5°	704.4	741.4	809.3	920.0
50°	645.4	676.4	735.4	838.8
52.5°	587.8	614.3	669.0	751.7
55°	536.1	561.2	601.1	682.3
57.5°	482.9	502.1	540.5	605.5
60°	431.2	448.9	480.0	533.1
62.5°	379.5	394.3	423.8	466.7
65°	333.8	345.6	367.7	404.6
67.5°	289.5	296.8	314.6	344.1
70°	246.6	252.5	267.3	290.9
72.5°	200.8	206.8	223.0	239.2
75°	162.4	163.9	175.7	189.0
77.5°	127.0	125.5	134.4	144.7
80°	87.1	91.6	98.9	103.4
82.5°	59.1	60.5	63.5	66.5
85°	32.5	34.0	34.0	38.4
87.5°	13.3	14.8	14.8	16.2
90°	4.9	3.4	2.0	0.5
92.5°	15.0	14.1	13.1	12.1
95°	32.3	31.0	29.8	28.6
97.5°	51.1	50.0	48.9	47.8
100°	72.7	71.8	70.8	69.8
102.5°	95.0	94.3	93.5	92.8
105°	119.2	118.9	118.5	118.1
107.5°	144.9	144.4	143.9	143.4
110°	169.8	169.1	168.3	167.6



TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	196.1	195.4	194.6	193.9
115°	222.0	221.3	220.5	219.8
117.5°	248.5	247.6	246.6	245.6
120°	274.3	273.4	272.4	271.4
122.5°	298.7	297.4	296.2	295.0
125°	323.0	321.9	320.8	319.7
127.5°	348.0	346.6	345.3	343.9
130°	371.2	369.6	368.0	366.4
132.5°	395.4	394.1	392.9	391.7
135°	417.7	416.4	415.0	413.7
137.5°	441.2	440.1	439.0	437.9
140°	462.6	461.5	460.4	459.3
142.5°	484.6	483.5	482.4	481.3
145°	504.7	503.8	503.0	502.1
147.5°	524.1	523.0	521.9	520.8
150°	542.2	541.5	540.8	540.1
152.5°	559.3	558.6	557.8	557.1
155°	575.2	574.9	574.5	574.1
157.5°	589.6	589.4	589.1	588.9
160°	602.8	602.6	602.3	602.1
162.5°	614.2	614.2	614.2	614.2
165°	624.3	624.4	624.6	624.7
167.5°	632.9	633.2	633.6	634.0
170°	640.0	640.4	640.7	641.1
172.5°	645.0	645.3	645.7	646.1
175°	648.8	649.2	649.5	649.9
177.5°	651.0	651.4	651.7	652.1
180°	651.0	651.0	651.0	651.0

TEST NUMBER: P997953

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.40	20.42	20.17	21.21	22.17	16.89	17.91	17.66	18.70	19.66
	3H	20.22	21.14	21.01	21.94	22.92	18.25	19.16	19.04	19.96	20.95
	4H	20.40	21.26	21.20	22.07	23.07	18.72	19.58	19.52	20.39	21.39
	6H	20.45	21.25	21.27	22.06	23.07	19.03	19.83	19.85	20.64	21.66
	8H	20.44	21.19	21.26	22.03	23.04	19.12	19.88	19.95	20.71	21.73
	12H	20.40	21.12	21.23	21.95	22.99	19.17	19.89	20.00	20.72	21.76
4H	2H	19.46	20.32	20.27	21.13	22.13	17.36	18.22	18.17	19.03	20.03
	3H	20.46	21.17	21.27	22.01	23.03	18.83	19.55	19.65	20.39	21.41
	4H	20.74	21.39	21.57	22.23	23.27	19.37	20.02	20.21	20.86	21.91
	6H	20.88	21.44	21.73	22.30	23.35	19.76	20.32	20.61	21.19	22.24
	8H	20.88	21.40	21.73	22.26	23.32	19.88	20.40	20.73	21.26	22.32
	12H	20.85	21.32	21.72	22.20	23.27	19.94	20.41	20.81	21.29	22.35
8H	4H	20.76	21.28	21.61	22.14	23.20	19.53	20.05	20.38	20.91	21.97
	6H	20.94	21.38	21.82	22.28	23.34	19.97	20.40	20.85	21.30	22.36
	8H	20.97	21.36	21.86	22.25	23.33	20.12	20.50	21.01	21.40	22.48
	12H	20.97	21.30	21.86	22.19	23.32	20.22	20.56	21.11	21.44	22.58
12H	4H	20.72	21.19	21.59	22.07	23.14	19.51	19.98	20.38	20.86	21.92
	6H	20.92	21.31	21.81	22.20	23.28	19.97	20.35	20.86	21.25	22.33
	8H	20.96	21.30	21.85	22.19	23.32	20.13	20.47	21.03	21.36	22.49