

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999140

Luminaire Tested: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999140
REPORT IS A COMBINATION OF REPORTS P984889 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5678.0 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64		
1	102	97	94	90	95	92	88	85	81	79	76	71	69	68	62	61	60	55		
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	55	53	51	47		
3	85	76	69	63	80	72	65	60	64	59	55	56	53	49	50	47	44	41		
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39	36		
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34	31		
6	67	55	47	41	63	52	45	40	47	41	36	42	37	33	37	33	30	28		
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27	25		
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	32	28	25	22		
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	22	20		
10	51	38	31	26	48	37	30	26	33	28	24	30	26	22	27	23	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26115	26115	26115	26115
5°	26178	27845	26278	22153
10°	25874	30397	26037	18265
15°	25247	32063	25598	15385
20°	24853	30104	24853	13372
25°	24061	25863	24170	11959
30°	22757	20330	23191	10831
35°	21603	14059	21964	9910
40°	20276	10614	20506	9175
45°	18638	8722	18944	8382
50°	17225	7655	17256	7674
55°	15612	6524	15713	6904
60°	13892	5449	14083	6025
65°	12353	4432	12577	5146
70°	10818	3478	11095	4150
75°	9079	2525	9437	3009
80°	7090	1600	7593	1787
85°	4661	804	5015	597

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 26997 cd/sqm

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.1	2.8
10°-20°	457.4	8.1
20°-30°	663.8	11.7
30°-40°	699.8	12.3
40°-50°	619.2	10.9
50°-60°	494.4	8.7
60°-70°	335.8	5.9
70°-80°	171.8	3.0
80°-90°	41.8	0.7
90°-100°	22.9	0.4
100°-110°	85.4	1.5
110°-120°	226.5	4.0
120°-130°	375.7	6.6
130°-140°	399.0	7.0
140°-150°	370.9	6.5
150°-160°	298.2	5.3
160°-170°	192.1	3.4
170°-180°	66.1	1.2
0°-30°	1278.3	22.5
0°-40°	1978.1	34.8
0°-60°	3091.7	54.5
0°-90°	3641.2	64.1
90°-120°	334.8	5.9
90°-150°	1480.4	26.1
90°-180°	2037.0	35.9
0°-180°	5678.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1650	1650	1650	1650	1650	
5°	1651	1843	1657	1466	1651	157
15°	1551	2265	1572	1087	1551	438
25°	1394	1887	1400	872	1394	637
35°	1138	1027	1156	724	1138	712
45°	853	619	867	595	853	662
55°	586	435	590	460	586	523
65°	348	268	354	311	348	345
75°	162	132	169	157	162	174
85°	33	34	36	25	33	38
90°	0	14	0	14	0	4
95°	33	22	33	22	33	39
105°	153	38	153	38	153	163
115°	289	41	289	41	289	285
125°	409	430	409	430	409	365
135°	506	522	506	522	506	391
145°	587	596	587	596	587	367
155°	646	646	646	646	646	298
165°	681	679	681	679	681	192
175°	696	692	696	692	696	66
180°	695	695	695	695	695	

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1658.7	1662.5	1668.8	1670.1	1682.8	1692.9	1704.3	1704.3	1708.2	1706.9	1696.7
5°	1651.1	1662.5	1679.0	1692.9	1715.8	1725.9	1741.1	1752.5	1762.7	1770.3	1769.0
7.5°	1638.4	1658.7	1682.8	1709.4	1739.9	1757.6	1779.2	1799.5	1813.4	1826.1	1835.0
10°	1616.8	1651.1	1684.1	1719.6	1758.9	1783.0	1808.3	1835.0	1856.5	1880.6	1903.4
12.5°	1587.7	1637.1	1677.7	1724.6	1772.8	1799.5	1840.0	1860.3	1902.2	1963.0	1979.5
15°	1550.9	1618.1	1656.2	1715.8	1779.2	1800.7	1856.5	1889.5	1975.7	2013.8	2059.4
17.5°	1516.7	1591.5	1642.2	1710.7	1772.8	1814.7	1869.2	1936.4	2008.7	2063.2	2113.9
20°	1488.8	1561.0	1621.9	1698.0	1776.6	1829.9	1887.0	1968.1	2046.7	2102.5	2141.8
22.5°	1425.4	1517.9	1588.9	1673.9	1769.0	1842.6	1897.1	1985.9	2070.8	2105.1	2139.3
25°	1393.7	1473.5	1556.0	1652.4	1763.9	1851.4	1898.4	1997.3	2072.1	2084.8	2092.4
27.5°	1335.3	1425.4	1521.7	1632.1	1762.7	1836.2	1895.8	1985.9	2045.5	2036.6	2013.8
30°	1263.0	1373.4	1479.9	1599.1	1744.9	1824.8	1880.6	1963.0	1993.5	1947.8	1907.2
32.5°	1209.8	1313.8	1431.7	1569.9	1724.6	1800.7	1855.3	1919.9	1926.3	1843.8	1775.4
35°	1137.5	1252.9	1386.0	1531.9	1690.4	1758.9	1809.6	1848.9	1818.5	1703.1	1621.9
37.5°	1072.8	1187.0	1329.0	1477.4	1643.5	1710.7	1751.3	1757.6	1682.8	1581.3	1462.1
40°	1001.8	1119.7	1268.1	1424.1	1591.5	1649.8	1675.2	1656.2	1548.4	1430.4	1292.2
42.5°	930.8	1047.5	1207.2	1367.0	1525.5	1575.0	1585.1	1533.2	1401.3	1263.0	1103.3
45°	853.4	975.2	1135.0	1296.0	1449.5	1477.4	1478.6	1403.8	1247.8	1103.3	954.9
47.5°	790.0	902.9	1061.4	1222.5	1351.8	1370.8	1363.2	1277.0	1107.1	944.7	815.4
50°	720.3	828.1	985.3	1143.8	1254.2	1259.2	1240.2	1117.2	951.1	802.7	700.0
52.5°	645.5	754.5	899.1	1051.3	1150.2	1142.6	1105.8	973.9	817.9	694.9	616.3
55°	585.9	682.2	817.9	966.3	1036.0	1014.5	973.9	839.5	716.5	612.5	544.0
57.5°	519.9	604.9	738.0	867.4	908.0	887.7	847.1	721.6	607.4	528.8	483.2
60°	457.8	535.1	651.8	759.6	791.3	769.7	722.8	610.0	527.5	461.6	427.4
62.5°	400.7	467.9	565.6	664.5	677.2	655.6	615.0	523.7	452.7	400.7	375.4
65°	347.5	410.9	489.5	564.3	575.7	552.9	511.1	445.1	385.5	352.5	328.4
67.5°	295.5	346.2	415.9	470.5	476.8	455.3	421.0	367.8	331.0	295.5	277.7
70°	249.8	287.9	342.4	386.8	389.3	369.0	351.3	303.1	275.2	249.8	235.9
72.5°	205.4	232.1	273.9	306.9	308.2	295.5	279.0	248.6	224.5	206.7	192.8
75°	162.3	185.1	210.5	239.7	238.4	228.3	215.6	196.6	176.3	164.9	158.5
77.5°	124.3	138.2	158.5	177.5	177.5	172.5	164.9	150.9	138.2	126.8	120.5
80°	88.8	97.6	114.1	120.5	123.0	121.7	115.4	105.3	100.2	91.3	88.8
82.5°	57.1	63.4	71.0	77.4	81.2	78.6	77.4	72.3	64.7	62.1	59.6
85°	33.0	35.5	39.3	43.1	44.4	43.1	45.7	41.8	38.0	38.0	36.8
87.5°	13.9	15.2	17.8	17.8	19.0	19.0	17.8	19.0	19.0	17.8	16.5
90°	0.5	1.7	2.9	4.2	5.4	6.0	6.5	7.4	8.3	9.2	10.1
92.5°	12.6	12.2	11.7	11.3	10.8	10.6	10.8	11.1	11.4	11.8	12.1
95°	32.7	29.0	25.3	21.6	17.9	16.1	16.5	17.3	18.0	18.8	19.6
97.5°	58.8	49.6	40.5	31.3	22.2	17.6	18.5	20.3	22.0	23.8	25.6
100°	89.0	73.7	58.4	43.1	27.8	20.1	21.1	23.0	24.9	26.8	28.7
102.5°	122.2	122.0	121.8	121.5	121.3	121.2	111.0	90.7	70.4	50.0	29.7
105°	152.8	156.2	159.5	162.9	166.2	167.9	152.7	122.2	91.7	61.2	30.7
107.5°	188.5	191.3	194.1	196.9	199.7	201.1	182.3	144.6	107.0	69.3	31.7
110°	222.7	225.1	227.4	229.8	232.1	233.3	217.2	184.9	152.6	120.3	88.0

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	254.9	256.9	258.9	260.9	262.9	263.9	263.0	261.1	259.2	257.3	255.4
115°	289.1	291.0	292.9	294.8	296.7	297.6	299.0	301.8	304.6	307.4	310.2
117.5°	318.7	320.9	323.2	325.4	327.7	328.8	329.7	331.6	333.5	335.4	337.3
120°	351.9	353.6	355.2	356.9	358.6	359.4	360.4	362.4	364.5	366.5	368.5
122.5°	380.1	381.9	383.7	385.4	387.2	388.1	389.2	391.5	393.7	396.0	398.2
125°	408.7	410.1	411.6	413.0	414.5	415.2	416.3	418.4	420.5	422.7	424.8
127.5°	434.9	436.5	438.0	439.6	441.1	441.9	442.7	444.4	446.1	447.7	449.4
130°	459.5	461.3	463.1	464.8	466.6	467.5	468.1	469.4	470.6	471.9	473.1
132.5°	484.6	486.1	487.5	489.0	490.5	491.2	491.8	493.0	494.3	495.5	496.7
135°	505.7	507.5	509.3	511.1	512.9	513.8	514.3	515.3	516.3	517.3	518.3
137.5°	527.9	529.2	530.6	531.9	533.2	533.9	534.5	535.6	536.7	537.8	538.9
140°	549.5	550.4	551.3	552.2	553.1	553.5	554.1	555.3	556.6	557.8	559.0
142.5°	567.6	568.4	569.2	569.9	570.7	571.1	571.8	573.3	574.7	576.2	577.6
145°	586.7	586.6	586.5	586.4	586.3	586.2	587.1	589.0	590.9	592.8	594.7
147.5°	603.3	603.0	602.6	602.3	602.0	601.8	602.7	604.6	606.5	608.4	610.3
150°	619.3	618.5	617.7	617.0	616.2	615.8	616.7	618.5	620.3	622.1	623.9
152.5°	632.9	632.0	631.1	630.2	629.3	628.9	629.7	631.4	633.1	634.7	636.4
155°	646.0	645.0	644.0	643.0	642.0	641.5	642.2	643.5	644.8	646.2	647.5
157.5°	656.5	655.6	654.7	653.8	652.9	652.5	653.0	654.0	655.1	656.1	657.1
160°	665.6	664.9	664.3	663.6	662.9	662.6	662.9	663.6	664.3	664.9	665.6
162.5°	673.6	672.9	672.3	671.6	670.9	670.6	670.9	671.4	672.0	672.5	673.1
165°	680.7	680.0	679.4	678.7	678.0	677.7	677.9	678.2	678.5	678.9	679.2
167.5°	686.2	685.5	684.9	684.2	683.5	683.2	683.4	683.7	684.0	684.4	684.7
170°	690.7	690.0	689.4	688.7	688.0	687.7	687.8	688.0	688.3	688.5	688.7
172.5°	693.7	693.0	692.4	691.7	691.0	690.7	690.8	691.0	691.3	691.5	691.7
175°	696.3	695.5	694.7	693.9	693.1	692.7	692.8	693.0	693.3	693.5	693.7
177.5°	697.3	696.5	695.7	694.9	694.1	693.7	693.8	693.9	694.0	694.2	694.3
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1714.5	1715.8	1718.3	1731.0	1737.3	1738.6	1733.5	1744.9	1748.7	1744.9	1742.4
5°	1795.7	1803.3	1818.5	1835.0	1833.7	1835.0	1842.6	1850.2	1852.7	1842.6	1846.4
7.5°	1866.7	1881.9	1898.4	1923.7	1923.7	1936.4	1941.5	1947.8	1963.0	1955.4	1952.9
10°	1947.8	1968.1	1998.5	2039.1	2040.4	2053.1	2065.8	2086.0	2092.4	2087.3	2089.9
12.5°	2049.3	2088.6	2091.1	2135.5	2155.8	2158.3	2178.6	2174.8	2187.5	2187.5	2209.1
15°	2093.7	2154.5	2188.8	2231.9	2244.6	2229.3	2245.8	2263.6	2264.9	2264.9	2263.6
17.5°	2173.5	2197.6	2231.9	2254.7	2259.8	2259.8	2261.0	2268.7	2263.6	2253.4	2261.0
20°	2190.0	2200.2	2212.9	2210.3	2212.9	2200.2	2187.5	2174.8	2176.1	2169.7	2188.8
22.5°	2159.6	2157.1	2127.9	2108.9	2108.9	2083.5	2059.4	2048.0	2036.6	2040.4	2046.7
25°	2083.5	2044.2	2008.7	1980.8	1974.5	1933.9	1900.9	1890.8	1871.7	1887.0	1889.5
27.5°	1961.8	1917.4	1860.3	1836.2	1803.3	1786.8	1763.9	1733.5	1694.2	1717.0	1713.2
30°	1831.2	1765.2	1718.3	1660.0	1608.0	1604.2	1561.0	1510.3	1490.0	1490.0	1501.4
32.5°	1685.3	1597.8	1529.3	1446.9	1396.2	1374.6	1322.6	1271.9	1283.3	1245.3	1259.2
35°	1515.4	1400.0	1313.8	1233.9	1195.8	1170.5	1103.3	1075.4	1044.9	1027.2	1060.1
37.5°	1353.1	1219.9	1109.6	1022.1	1008.2	962.5	916.8	899.1	881.3	888.9	887.7
40°	1155.3	1037.3	938.4	869.9	845.8	824.3	793.8	772.3	760.9	767.2	768.5
42.5°	976.4	877.5	804.0	755.8	735.5	720.3	705.1	687.3	683.5	683.5	688.6
45°	838.2	757.1	707.6	668.3	656.9	645.5	634.1	626.4	623.9	618.8	622.6
47.5°	727.9	663.2	632.8	603.6	590.9	588.4	578.3	574.5	569.4	568.1	569.4
50°	635.3	594.7	566.8	550.4	541.5	537.7	532.6	525.0	522.5	528.8	526.3
52.5°	570.7	532.6	517.4	500.9	495.8	490.8	483.2	484.4	483.2	480.6	480.6
55°	506.0	481.9	466.7	454.0	452.7	447.6	441.3	438.8	437.5	435.0	438.8
57.5°	454.0	435.0	421.0	409.6	404.5	404.5	398.2	393.1	393.1	391.8	393.1
60°	402.0	383.0	374.1	362.7	358.9	357.6	353.8	351.3	347.5	347.5	347.5
62.5°	353.8	338.6	328.4	318.3	319.6	313.2	308.2	305.6	305.6	306.9	306.9
65°	308.2	298.0	285.3	276.4	273.9	272.6	270.1	268.8	265.0	267.6	267.6
67.5°	266.3	252.4	244.7	240.9	237.1	235.9	233.3	230.8	229.5	228.3	230.8
70°	224.5	213.0	206.7	204.2	200.4	199.1	197.8	194.0	195.3	196.6	197.8
72.5°	186.4	176.3	175.0	167.4	167.4	167.4	162.3	164.9	163.6	161.1	163.6
75°	147.1	142.0	139.5	135.7	137.0	135.7	134.4	130.6	130.6	131.9	133.2
77.5°	116.7	111.6	110.3	106.5	104.0	106.5	104.0	102.7	102.7	104.0	104.0
80°	86.2	83.7	79.9	79.9	79.9	78.6	78.6	78.6	77.4	76.1	77.4
82.5°	57.1	57.1	55.8	54.5	55.8	53.3	54.5	54.5	54.5	54.5	54.5
85°	36.8	35.5	35.5	34.2	34.2	34.2	35.5	33.0	33.0	34.2	34.2
87.5°	16.5	16.5	16.5	17.8	16.5	16.5	16.5	17.8	16.5	16.5	16.5
90°	10.7	11.2	11.8	12.3	12.6	12.7	12.9	13.2	13.4	13.6	13.4
92.5°	12.3	12.5	12.8	13.0	13.1	13.2	13.3	13.4	13.5	13.6	13.5
95°	20.2	20.7	21.3	21.8	22.1	22.0	21.9	21.8	21.7	21.6	21.7
97.5°	25.9	26.3	26.6	26.9	27.1	27.2	27.3	27.4	27.5	27.6	27.5
100°	29.6	30.5	31.4	32.3	32.7	32.8	33.0	33.3	33.5	33.7	33.5
102.5°	30.9	32.1	33.4	34.6	35.2	35.4	35.7	36.0	36.4	36.7	36.4
105°	31.9	33.1	34.4	35.6	36.2	36.4	36.9	37.3	37.8	38.2	37.8
107.5°	32.9	34.1	35.4	36.6	37.2	37.4	37.9	38.3	38.8	39.2	38.8
110°	76.8	65.6	54.5	43.3	37.7	37.9	38.4	38.8	39.3	39.7	39.3

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	207.2	159.1	110.9	62.8	38.7	38.9	39.2	39.5	39.9	40.2	39.9
115°	258.5	206.7	155.0	103.3	77.4	73.4	65.3	57.3	49.2	41.2	49.2
117.5°	321.3	305.3	289.4	273.4	265.4	250.8	221.5	192.2	163.0	133.7	163.0
120°	369.8	371.2	372.5	373.8	374.5	367.0	351.9	336.8	321.8	306.7	321.8
122.5°	398.9	399.5	400.2	400.9	401.2	401.3	401.4	401.5	401.6	401.7	401.6
125°	425.6	426.4	427.1	427.9	428.3	428.5	428.8	429.1	429.5	429.8	429.5
127.5°	450.5	451.7	452.8	453.9	454.5	454.6	454.7	454.8	454.9	455.0	454.9
130°	474.3	475.5	476.8	478.0	478.6	478.5	478.4	478.3	478.2	478.1	478.2
132.5°	497.7	498.7	499.7	500.7	501.2	501.1	501.0	500.9	500.8	500.7	500.8
135°	519.4	520.5	521.6	522.7	523.3	523.2	523.0	522.7	522.5	522.3	522.5
137.5°	540.0	541.1	542.2	543.3	543.9	543.7	543.4	543.1	542.7	542.4	542.7
140°	560.0	561.0	562.0	563.0	563.5	563.2	562.7	562.1	561.6	561.0	561.6
142.5°	578.5	579.4	580.3	581.2	581.6	581.3	580.8	580.2	579.7	579.1	579.7
145°	595.5	596.3	597.0	597.8	598.2	597.9	597.4	596.8	596.3	595.7	596.3
147.5°	610.9	611.4	612.0	612.5	612.8	612.6	612.1	611.7	611.2	610.8	611.2
150°	624.6	625.2	625.9	626.6	626.9	626.6	626.1	625.5	625.0	624.4	625.0
152.5°	637.1	637.8	638.5	639.2	639.5	639.1	638.3	637.5	636.7	635.9	636.7
155°	648.2	648.8	649.5	650.2	650.5	650.1	649.2	648.3	647.4	646.5	647.4
157.5°	657.9	658.7	659.4	660.2	660.6	660.1	659.2	658.3	657.4	656.5	657.4
160°	666.3	666.9	667.6	668.3	668.6	668.2	667.4	666.7	665.9	665.1	665.9
162.5°	673.9	674.7	675.5	676.3	676.7	676.2	675.2	674.1	673.1	672.1	673.1
165°	680.0	680.8	681.5	682.3	682.7	682.3	681.5	680.8	680.0	679.2	680.0
167.5°	685.5	686.3	687.0	687.8	688.2	687.7	686.7	685.7	684.7	683.7	684.7
170°	689.5	690.3	691.0	691.8	692.2	691.7	690.7	689.7	688.7	687.7	688.7
172.5°	692.5	693.3	694.1	694.9	695.3	694.8	693.8	692.7	691.7	690.7	691.7
175°	694.5	695.3	696.1	696.9	697.3	696.7	695.6	694.5	693.3	692.2	693.3
177.5°	695.1	695.9	696.6	697.4	697.8	697.3	696.3	695.2	694.2	693.2	694.2
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1748.7	1739.9	1732.2	1733.5	1739.9	1734.8	1722.1	1705.6	1699.3	1691.7	1699.3
5°	1854.0	1846.4	1831.2	1832.4	1828.6	1823.5	1803.3	1777.9	1777.9	1757.6	1755.1
7.5°	1958.0	1946.6	1936.4	1933.9	1919.9	1909.8	1892.0	1856.5	1842.6	1818.5	1804.5
10°	2074.6	2065.8	2054.3	2040.4	2032.8	2015.0	1985.9	1933.9	1908.5	1875.5	1851.4
12.5°	2192.6	2191.3	2165.9	2138.0	2136.8	2108.9	2088.6	2018.8	1984.6	1940.2	1883.2
15°	2267.4	2261.0	2247.1	2233.2	2237.0	2206.5	2160.9	2078.4	2055.6	2002.4	1941.5
17.5°	2266.1	2266.1	2262.3	2259.8	2256.0	2247.1	2221.7	2167.2	2130.4	2063.2	2006.2
20°	2193.8	2210.3	2214.1	2212.9	2225.5	2231.9	2230.6	2196.4	2167.2	2107.6	2049.3
22.5°	2049.3	2087.3	2103.8	2113.9	2140.6	2154.5	2187.5	2174.8	2167.2	2122.8	2073.4
25°	1914.9	1927.5	1977.0	1979.5	2016.3	2050.5	2083.5	2105.1	2133.0	2116.5	2074.6
27.5°	1741.1	1770.3	1805.8	1832.4	1840.0	1909.8	1964.3	2004.9	2068.3	2073.4	2059.4
30°	1544.6	1558.5	1616.8	1652.4	1692.9	1743.7	1822.3	1892.0	1949.1	2001.1	2018.8
32.5°	1304.9	1362.0	1396.2	1439.3	1474.8	1564.9	1661.2	1751.3	1817.2	1904.7	1942.8
35°	1085.5	1129.9	1188.2	1206.0	1270.7	1346.7	1472.3	1587.7	1687.9	1776.6	1854.0
37.5°	904.2	939.7	1001.8	1029.7	1067.8	1165.4	1270.7	1413.9	1534.4	1643.5	1739.9
40°	779.9	806.5	853.4	862.3	894.0	982.8	1067.8	1202.2	1362.0	1509.1	1614.3
42.5°	694.9	707.6	739.3	750.7	771.0	830.6	906.7	1033.5	1181.9	1334.1	1482.4
45°	634.1	642.9	662.0	672.1	697.5	724.1	786.2	887.7	1004.3	1157.8	1317.6
47.5°	579.5	590.9	598.6	604.9	618.8	648.0	688.6	763.4	875.0	1015.8	1170.5
50°	533.9	537.7	551.6	552.9	561.8	580.8	618.8	664.5	753.3	867.4	1017.0
52.5°	488.2	492.0	500.9	509.8	513.6	528.8	554.2	592.2	658.2	748.2	881.3
55°	442.6	447.6	456.5	462.9	466.7	479.3	494.6	531.3	583.3	646.7	755.8
57.5°	396.9	408.3	410.9	414.7	421.0	435.0	448.9	470.5	511.1	569.4	649.3
60°	353.8	357.6	366.5	370.3	376.6	384.2	402.0	418.5	447.6	493.3	565.6
62.5°	309.4	318.3	322.1	325.9	331.0	339.9	351.3	369.0	394.4	431.2	488.2
65°	271.4	272.6	280.3	285.3	290.4	296.7	308.2	324.6	339.9	374.1	415.9
67.5°	234.6	237.1	239.7	244.7	251.1	257.4	267.6	276.4	295.5	318.3	351.3
70°	199.1	199.1	205.4	209.2	208.0	215.6	223.2	233.3	247.3	268.8	295.5
72.5°	167.4	166.1	171.2	172.5	175.0	180.1	185.1	195.3	202.9	219.4	239.7
75°	133.2	135.7	138.2	138.2	142.0	145.8	150.9	156.0	164.9	175.0	190.2
77.5°	105.3	105.3	107.8	109.1	112.9	111.6	116.7	121.7	128.1	137.0	148.4
80°	77.4	79.9	79.9	79.9	81.2	82.4	87.5	91.3	95.1	101.4	106.5
82.5°	54.5	54.5	57.1	57.1	57.1	59.6	59.6	60.9	63.4	67.2	71.0
85°	34.2	34.2	34.2	35.5	34.2	35.5	38.0	36.8	38.0	40.6	40.6
87.5°	16.5	16.5	16.5	16.5	16.5	17.8	16.5	17.8	19.0	19.0	19.0
90°	13.2	12.9	12.7	12.6	12.3	11.8	11.2	10.7	10.1	9.2	8.3
92.5°	13.4	13.3	13.2	13.1	13.0	12.8	12.5	12.3	12.1	11.8	11.4
95°	21.8	21.9	22.0	22.1	21.8	21.3	20.7	20.2	19.6	18.8	18.0
97.5°	27.4	27.3	27.2	27.1	26.9	26.6	26.3	25.9	25.6	23.8	22.0
100°	33.3	33.0	32.8	32.7	32.3	31.4	30.5	29.6	28.7	26.8	24.9
102.5°	36.0	35.7	35.4	35.2	34.6	33.4	32.1	30.9	29.7	50.0	70.4
105°	37.3	36.9	36.4	36.2	35.6	34.4	33.1	31.9	30.7	61.2	91.7
107.5°	38.3	37.9	37.4	37.2	36.6	35.4	34.1	32.9	31.7	69.3	107.0
110°	38.8	38.4	37.9	37.7	43.3	54.5	65.6	76.8	88.0	120.3	152.6

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	39.5	39.2	38.9	38.7	62.8	110.9	159.1	207.2	255.4	257.3	259.2
115°	57.3	65.3	73.4	77.4	103.3	155.0	206.7	258.5	310.2	307.4	304.6
117.5°	192.2	221.5	250.8	265.4	273.4	289.4	305.3	321.3	337.3	335.4	333.5
120°	336.8	351.9	367.0	374.5	373.8	372.5	371.2	369.8	368.5	366.5	364.5
122.5°	401.5	401.4	401.3	401.2	400.9	400.2	399.5	398.9	398.2	396.0	393.7
125°	429.1	428.8	428.5	428.3	427.9	427.1	426.4	425.6	424.8	422.7	420.5
127.5°	454.8	454.7	454.6	454.5	453.9	452.8	451.7	450.5	449.4	447.7	446.1
130°	478.3	478.4	478.5	478.6	478.0	476.8	475.5	474.3	473.1	471.9	470.6
132.5°	500.9	501.0	501.1	501.2	500.7	499.7	498.7	497.7	496.7	495.5	494.3
135°	522.7	523.0	523.2	523.3	522.7	521.6	520.5	519.4	518.3	517.3	516.3
137.5°	543.1	543.4	543.7	543.9	543.3	542.2	541.1	540.0	538.9	537.8	536.7
140°	562.1	562.7	563.2	563.5	563.0	562.0	561.0	560.0	559.0	557.8	556.6
142.5°	580.2	580.8	581.3	581.6	581.2	580.3	579.4	578.5	577.6	576.2	574.7
145°	596.8	597.4	597.9	598.2	597.8	597.0	596.3	595.5	594.7	592.8	590.9
147.5°	611.7	612.1	612.6	612.8	612.5	612.0	611.4	610.9	610.3	608.4	606.5
150°	625.5	626.1	626.6	626.9	626.6	625.9	625.2	624.6	623.9	622.1	620.3
152.5°	637.5	638.3	639.1	639.5	639.2	638.5	637.8	637.1	636.4	634.7	633.1
155°	648.3	649.2	650.1	650.5	650.2	649.5	648.8	648.2	647.5	646.2	644.8
157.5°	658.3	659.2	660.1	660.6	660.2	659.4	658.7	657.9	657.1	656.1	655.1
160°	666.7	667.4	668.2	668.6	668.3	667.6	666.9	666.3	665.6	664.9	664.3
162.5°	674.1	675.2	676.2	676.7	676.3	675.5	674.7	673.9	673.1	672.5	672.0
165°	680.8	681.5	682.3	682.7	682.3	681.5	680.8	680.0	679.2	678.9	678.5
167.5°	685.7	686.7	687.7	688.2	687.8	687.0	686.3	685.5	684.7	684.4	684.0
170°	689.7	690.7	691.7	692.2	691.8	691.0	690.3	689.5	688.7	688.5	688.3
172.5°	692.7	693.8	694.8	695.3	694.9	694.1	693.3	692.5	691.7	691.5	691.3
175°	694.5	695.6	696.7	697.3	696.9	696.1	695.3	694.5	693.7	693.5	693.3
177.5°	695.2	696.3	697.3	697.8	697.4	696.6	695.9	695.1	694.3	694.2	694.0
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1692.9	1686.6	1682.8	1685.3	1677.7	1658.7	1658.7	1665.0	1657.4	1649.8	1638.4
5°	1739.9	1727.2	1719.6	1718.3	1700.5	1670.1	1663.8	1657.4	1640.9	1623.2	1604.2
7.5°	1785.5	1762.7	1750.0	1741.1	1715.8	1676.4	1660.0	1646.0	1619.4	1592.8	1568.7
10°	1823.5	1790.6	1775.4	1761.4	1728.4	1679.0	1652.4	1627.0	1592.8	1558.5	1528.1
12.5°	1854.0	1815.9	1796.9	1776.6	1736.0	1671.4	1638.4	1597.8	1563.6	1517.9	1487.5
15°	1904.7	1826.1	1808.3	1789.3	1747.5	1658.7	1618.1	1572.5	1525.5	1464.7	1431.7
17.5°	1945.3	1840.0	1838.8	1798.2	1743.7	1653.6	1591.5	1531.9	1481.2	1420.3	1368.3
20°	1969.4	1861.6	1841.3	1799.5	1731.0	1619.4	1554.7	1488.8	1434.2	1360.7	1308.7
22.5°	1989.7	1892.0	1838.8	1788.0	1704.3	1608.0	1512.9	1450.7	1375.9	1296.0	1246.6
25°	1997.3	1898.4	1842.6	1784.2	1685.3	1575.0	1467.2	1400.0	1316.3	1244.0	1176.8
27.5°	1998.5	1897.1	1828.6	1767.8	1658.7	1531.9	1421.6	1350.5	1258.0	1174.3	1107.1
30°	1985.9	1883.2	1821.0	1755.1	1633.3	1492.6	1365.8	1287.1	1188.2	1104.5	1034.8
32.5°	1947.8	1855.3	1804.5	1732.2	1600.4	1438.0	1312.5	1225.0	1121.0	1038.6	971.4
35°	1884.4	1821.0	1765.2	1698.0	1557.2	1387.3	1259.2	1156.5	1051.3	972.6	909.2
37.5°	1805.8	1771.6	1719.6	1653.6	1507.8	1341.7	1199.6	1085.5	980.3	904.2	842.0
40°	1699.3	1708.2	1657.4	1597.8	1449.5	1279.5	1122.3	1013.2	914.3	843.3	782.4
42.5°	1583.9	1620.7	1591.5	1534.4	1384.8	1211.0	1065.2	944.7	848.4	774.8	724.1
45°	1459.6	1523.0	1505.3	1463.4	1317.6	1138.8	984.1	867.4	782.4	711.4	667.0
47.5°	1323.9	1413.9	1413.9	1383.5	1242.8	1066.5	914.3	795.1	711.4	660.7	617.6
50°	1185.7	1287.1	1303.6	1283.3	1159.1	984.1	829.3	721.6	649.3	599.8	568.1
52.5°	1041.1	1159.1	1189.5	1179.3	1070.3	905.4	759.6	654.3	588.4	545.3	517.4
55°	902.9	1039.9	1072.8	1076.6	975.2	819.2	682.2	589.7	526.3	497.1	473.0
57.5°	772.3	904.2	940.9	947.3	878.8	740.6	610.0	528.8	471.7	447.6	428.6
60°	660.7	771.0	819.2	833.2	773.6	649.3	542.8	464.1	421.0	398.2	380.4
62.5°	569.4	658.2	708.9	712.7	686.1	569.4	473.0	407.1	370.3	350.0	341.1
65°	480.6	560.5	590.9	606.2	584.6	493.3	408.3	353.8	324.6	306.9	298.0
67.5°	409.6	460.3	485.7	506.0	484.4	415.9	347.5	303.1	281.5	263.8	258.7
70°	336.1	377.9	396.9	417.2	398.2	346.2	296.7	256.2	237.1	223.2	216.8
72.5°	268.8	301.8	319.6	332.2	320.8	277.7	237.1	209.2	195.3	185.1	181.3
75°	213.0	235.9	246.0	254.9	249.8	216.8	191.5	168.7	156.0	147.1	144.6
77.5°	162.3	178.8	190.2	192.8	186.4	164.9	143.3	129.3	119.2	114.1	111.6
80°	115.4	125.5	131.9	135.7	129.3	120.5	105.3	95.1	86.2	79.9	78.6
82.5°	77.4	82.4	87.5	86.2	83.7	76.1	67.2	62.1	58.3	53.3	53.3
85°	44.4	45.7	48.2	49.5	48.2	43.1	38.0	35.5	33.0	29.2	29.2
87.5°	19.0	20.3	20.3	21.6	19.0	19.0	16.5	13.9	13.9	12.7	11.4
90°	7.4	6.5	6.0	5.4	4.2	2.9	1.7	0.5	1.7	2.9	4.2
92.5°	11.1	10.8	10.6	10.8	11.3	11.7	12.2	12.6	12.2	11.7	11.3
95°	17.3	16.5	16.1	17.9	21.6	25.3	29.0	32.7	29.0	25.3	21.6
97.5°	20.3	18.5	17.6	22.2	31.3	40.5	49.6	58.8	49.6	40.5	31.3
100°	23.0	21.1	20.1	27.8	43.1	58.4	73.7	89.0	73.7	58.4	43.1
102.5°	90.7	111.0	121.2	121.3	121.5	121.8	122.0	122.2	122.0	121.8	121.5
105°	122.2	152.7	167.9	166.2	162.9	159.5	156.2	152.8	156.2	159.5	162.9
107.5°	144.6	182.3	201.1	199.7	196.9	194.1	191.3	188.5	191.3	194.1	196.9
110°	184.9	217.2	233.3	232.1	229.8	227.4	225.1	222.7	225.1	227.4	229.8

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	261.1	263.0	263.9	262.9	260.9	258.9	256.9	254.9	256.9	258.9	260.9
115°	301.8	299.0	297.6	296.7	294.8	292.9	291.0	289.1	291.0	292.9	294.8
117.5°	331.6	329.7	328.8	327.7	325.4	323.2	320.9	318.7	320.9	323.2	325.4
120°	362.4	360.4	359.4	358.6	356.9	355.2	353.6	351.9	353.6	355.2	356.9
122.5°	391.5	389.2	388.1	387.2	385.4	383.7	381.9	380.1	381.9	383.7	385.4
125°	418.4	416.3	415.2	414.5	413.0	411.6	410.1	408.7	410.1	411.6	413.0
127.5°	444.4	442.7	441.9	441.1	439.6	438.0	436.5	434.9	436.5	438.0	439.6
130°	469.4	468.1	467.5	466.6	464.8	463.1	461.3	459.5	461.3	463.1	464.8
132.5°	493.0	491.8	491.2	490.5	489.0	487.5	486.1	484.6	486.1	487.5	489.0
135°	515.3	514.3	513.8	512.9	511.1	509.3	507.5	505.7	507.5	509.3	511.1
137.5°	535.6	534.5	533.9	533.2	531.9	530.6	529.2	527.9	529.2	530.6	531.9
140°	555.3	554.1	553.5	553.1	552.2	551.3	550.4	549.5	550.4	551.3	552.2
142.5°	573.3	571.8	571.1	570.7	569.9	569.2	568.4	567.6	568.4	569.2	569.9
145°	589.0	587.1	586.2	586.3	586.4	586.5	586.6	586.7	586.6	586.5	586.4
147.5°	604.6	602.7	601.8	602.0	602.3	602.6	603.0	603.3	603.0	602.6	602.3
150°	618.5	616.7	615.8	616.2	617.0	617.7	618.5	619.3	618.5	617.7	617.0
152.5°	631.4	629.7	628.9	629.3	630.2	631.1	632.0	632.9	632.0	631.1	630.2
155°	643.5	642.2	641.5	642.0	643.0	644.0	645.0	646.0	645.0	644.0	643.0
157.5°	654.0	653.0	652.5	652.9	653.8	654.7	655.6	656.5	655.6	654.7	653.8
160°	663.6	662.9	662.6	662.9	663.6	664.3	664.9	665.6	664.9	664.3	663.6
162.5°	671.4	670.9	670.6	670.9	671.6	672.3	672.9	673.6	672.9	672.3	671.6
165°	678.2	677.9	677.7	678.0	678.7	679.4	680.0	680.7	680.0	679.4	678.7
167.5°	683.7	683.4	683.2	683.5	684.2	684.9	685.5	686.2	685.5	684.9	684.2
170°	688.0	687.8	687.7	688.0	688.7	689.4	690.0	690.7	690.0	689.4	688.7
172.5°	691.0	690.8	690.7	691.0	691.7	692.4	693.0	693.7	693.0	692.4	691.7
175°	693.0	692.8	692.7	693.1	693.9	694.7	695.5	696.3	695.5	694.7	693.9
177.5°	693.9	693.8	693.7	694.1	694.9	695.7	696.5	697.3	696.5	695.7	694.9
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1632.1	1638.4	1637.1	1624.5	1610.5	1599.1	1577.5	1580.1	1572.5	1573.7	1581.3
5°	1591.5	1591.5	1586.4	1568.7	1545.8	1533.2	1509.1	1502.7	1487.5	1486.2	1485.0
7.5°	1548.4	1542.0	1535.7	1510.3	1482.4	1462.1	1429.2	1421.6	1406.3	1396.2	1391.1
10°	1497.6	1488.8	1476.1	1446.9	1412.7	1387.3	1353.1	1342.9	1313.8	1301.1	1293.5
12.5°	1441.8	1436.8	1416.5	1392.4	1336.6	1308.7	1259.2	1269.4	1240.2	1214.9	1211.0
15°	1386.0	1367.0	1355.6	1316.3	1249.1	1236.4	1197.1	1176.8	1150.2	1129.9	1129.9
17.5°	1331.5	1302.4	1277.0	1235.1	1185.7	1150.2	1121.0	1110.9	1077.9	1057.6	1053.8
20°	1259.2	1226.3	1219.9	1160.3	1126.1	1086.8	1058.9	1033.5	1009.4	1000.5	994.2
22.5°	1190.8	1152.7	1142.6	1091.8	1057.6	1018.3	990.4	972.6	954.9	948.5	937.1
25°	1117.2	1094.4	1079.2	1024.6	986.6	949.8	930.8	918.1	901.6	900.4	892.8
27.5°	1046.2	1024.6	1009.4	957.4	929.5	895.3	880.1	866.1	857.2	853.4	849.6
30°	985.3	961.2	943.5	905.4	871.2	843.3	830.6	821.7	816.7	810.3	809.1
32.5°	918.1	904.2	880.1	850.9	824.3	797.6	790.0	783.7	776.1	773.6	772.3
35°	861.1	842.0	826.8	793.8	782.4	759.6	750.7	745.7	735.5	733.0	730.4
37.5°	805.3	787.5	771.0	750.7	729.2	716.5	711.4	703.8	698.7	700.0	697.5
40°	749.5	735.5	722.8	701.3	688.6	682.2	672.1	664.5	662.0	663.2	662.0
42.5°	694.9	682.2	674.6	658.2	645.5	639.1	632.8	625.2	629.0	629.0	632.8
45°	645.5	634.1	629.0	616.3	608.7	598.6	592.2	590.9	596.0	594.7	594.7
47.5°	594.7	590.9	584.6	573.2	563.0	556.7	555.4	555.4	560.5	563.0	561.8
50°	555.4	547.8	540.2	531.3	523.7	521.2	517.4	519.9	525.0	525.0	527.5
52.5°	506.0	500.9	498.4	490.8	485.7	485.7	485.7	487.0	490.8	494.6	493.3
55°	462.9	459.1	456.5	452.7	446.4	447.6	446.4	448.9	452.7	456.5	459.1
57.5°	417.2	415.9	413.4	407.1	407.1	405.8	409.6	410.9	417.2	419.7	423.6
60°	376.6	372.8	372.8	367.8	367.8	367.8	371.6	375.4	380.4	381.7	384.2
62.5°	333.5	333.5	332.2	328.4	328.4	332.2	333.5	338.6	341.1	341.1	344.9
65°	292.9	291.7	290.4	291.7	292.9	292.9	296.7	299.3	301.8	303.1	304.3
67.5°	252.4	251.1	253.6	252.4	254.9	260.0	258.7	262.5	266.3	266.3	267.6
70°	214.3	216.8	215.6	218.1	216.8	219.4	223.2	224.5	224.5	225.7	229.5
72.5°	178.8	178.8	178.8	177.5	178.8	181.3	183.9	185.1	187.7	188.9	192.8
75°	144.6	144.6	142.0	144.6	144.6	147.1	149.6	149.6	149.6	152.2	156.0
77.5°	109.1	110.3	109.1	111.6	111.6	112.9	115.4	114.1	116.7	117.9	119.2
80°	79.9	78.6	78.6	78.6	79.9	79.9	82.4	83.7	83.7	87.5	85.0
82.5°	50.7	52.0	50.7	52.0	52.0	53.3	52.0	53.3	54.5	57.1	55.8
85°	29.2	27.9	27.9	29.2	27.9	27.9	29.2	27.9	29.2	27.9	29.2
87.5°	11.4	10.1	10.1	10.1	10.1	8.9	8.9	7.6	7.6	7.6	6.3
90°	5.4	6.0	6.5	7.4	8.3	9.2	10.1	10.7	11.2	11.8	12.3
92.5°	10.8	10.6	10.8	11.1	11.4	11.8	12.1	12.3	12.5	12.8	13.0
95°	17.9	16.1	16.5	17.3	18.0	18.8	19.6	20.2	20.7	21.3	21.8
97.5°	22.2	17.6	18.5	20.3	22.0	23.8	25.6	25.9	26.3	26.6	26.9
100°	27.8	20.1	21.1	23.0	24.9	26.8	28.7	29.6	30.5	31.4	32.3
102.5°	121.3	121.2	111.0	90.7	70.4	50.0	29.7	30.9	32.1	33.4	34.6
105°	166.2	167.9	152.7	122.2	91.7	61.2	30.7	31.9	33.1	34.4	35.6
107.5°	199.7	201.1	182.3	144.6	107.0	69.3	31.7	32.9	34.1	35.4	36.6
110°	232.1	233.3	217.2	184.9	152.6	120.3	88.0	76.8	65.6	54.5	43.3

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	262.9	263.9	263.0	261.1	259.2	257.3	255.4	207.2	159.1	110.9	62.8
115°	296.7	297.6	299.0	301.8	304.6	307.4	310.2	258.5	206.7	155.0	103.3
117.5°	327.7	328.8	329.7	331.6	333.5	335.4	337.3	321.3	305.3	289.4	273.4
120°	358.6	359.4	360.4	362.4	364.5	366.5	368.5	369.8	371.2	372.5	373.8
122.5°	387.2	388.1	389.2	391.5	393.7	396.0	398.2	398.9	399.5	400.2	400.9
125°	414.5	415.2	416.3	418.4	420.5	422.7	424.8	425.6	426.4	427.1	427.9
127.5°	441.1	441.9	442.7	444.4	446.1	447.7	449.4	450.5	451.7	452.8	453.9
130°	466.6	467.5	468.1	469.4	470.6	471.9	473.1	474.3	475.5	476.8	478.0
132.5°	490.5	491.2	491.8	493.0	494.3	495.5	496.7	497.7	498.7	499.7	500.7
135°	512.9	513.8	514.3	515.3	516.3	517.3	518.3	519.4	520.5	521.6	522.7
137.5°	533.2	533.9	534.5	535.6	536.7	537.8	538.9	540.0	541.1	542.2	543.3
140°	553.1	553.5	554.1	555.3	556.6	557.8	559.0	560.0	561.0	562.0	563.0
142.5°	570.7	571.1	571.8	573.3	574.7	576.2	577.6	578.5	579.4	580.3	581.2
145°	586.3	586.2	587.1	589.0	590.9	592.8	594.7	595.5	596.3	597.0	597.8
147.5°	602.0	601.8	602.7	604.6	606.5	608.4	610.3	610.9	611.4	612.0	612.5
150°	616.2	615.8	616.7	618.5	620.3	622.1	623.9	624.6	625.2	625.9	626.6
152.5°	629.3	628.9	629.7	631.4	633.1	634.7	636.4	637.1	637.8	638.5	639.2
155°	642.0	641.5	642.2	643.5	644.8	646.2	647.5	648.2	648.8	649.5	650.2
157.5°	652.9	652.5	653.0	654.0	655.1	656.1	657.1	657.9	658.7	659.4	660.2
160°	662.9	662.6	662.9	663.6	664.3	664.9	665.6	666.3	666.9	667.6	668.3
162.5°	670.9	670.6	670.9	671.4	672.0	672.5	673.1	673.9	674.7	675.5	676.3
165°	678.0	677.7	677.9	678.2	678.5	678.9	679.2	680.0	680.8	681.5	682.3
167.5°	683.5	683.2	683.4	683.7	684.0	684.4	684.7	685.5	686.3	687.0	687.8
170°	688.0	687.7	687.8	688.0	688.3	688.5	688.7	689.5	690.3	691.0	691.8
172.5°	691.0	690.7	690.8	691.0	691.3	691.5	691.7	692.5	693.3	694.1	694.9
175°	693.1	692.7	692.8	693.0	693.3	693.5	693.7	694.5	695.3	696.1	696.9
177.5°	694.1	693.7	693.8	693.9	694.0	694.2	694.3	695.1	695.9	696.6	697.4
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1572.5	1576.3	1567.4	1564.9	1567.4	1558.5	1561.0	1563.6	1563.6	1567.4	1569.9
5°	1481.2	1476.1	1467.2	1464.7	1462.1	1465.9	1463.4	1467.2	1468.5	1477.4	1478.6
7.5°	1391.1	1383.5	1375.9	1368.3	1365.8	1359.4	1365.8	1365.8	1374.6	1372.1	1378.4
10°	1284.6	1283.3	1273.2	1269.4	1264.3	1254.2	1268.1	1264.3	1270.7	1282.1	1284.6
12.5°	1206.0	1192.0	1198.4	1180.6	1187.0	1176.8	1178.1	1178.1	1188.2	1189.5	1187.0
15°	1131.2	1119.7	1103.3	1095.7	1091.8	1086.8	1103.3	1104.5	1096.9	1114.7	1108.3
17.5°	1055.1	1055.1	1039.9	1036.0	1025.9	1031.0	1028.4	1029.7	1027.2	1039.9	1046.2
20°	989.1	982.8	977.7	979.0	966.3	963.8	961.2	963.8	972.6	981.5	984.1
22.5°	935.9	932.1	919.4	921.9	911.8	915.6	913.0	919.4	920.7	920.7	929.5
25°	885.1	880.1	881.3	876.3	872.5	872.5	868.7	872.5	877.5	880.1	881.3
27.5°	847.1	843.3	837.0	833.2	835.7	829.3	834.4	838.2	838.2	835.7	838.2
30°	801.4	804.0	804.0	791.3	796.4	793.8	797.6	800.2	800.2	801.4	798.9
32.5°	771.0	763.4	762.1	760.9	760.9	755.8	755.8	759.6	760.9	762.1	765.9
35°	730.4	730.4	724.1	727.9	722.8	724.1	722.8	724.1	726.6	722.8	726.6
37.5°	693.7	694.9	692.4	694.9	696.2	693.7	691.1	696.2	693.7	693.7	691.1
40°	662.0	660.7	662.0	662.0	662.0	663.2	660.7	660.7	660.7	658.2	655.6
42.5°	635.3	627.7	630.3	631.5	627.7	627.7	629.0	627.7	631.5	623.9	623.9
45°	597.3	594.7	596.0	596.0	598.6	594.7	597.3	598.6	594.7	593.5	590.9
47.5°	563.0	565.6	563.0	565.6	565.6	568.1	563.0	564.3	565.6	560.5	556.7
50°	528.8	528.8	532.6	531.3	532.6	530.1	530.1	528.8	530.1	527.5	523.7
52.5°	497.1	493.3	499.6	498.4	497.1	495.8	494.6	495.8	493.3	490.8	490.8
55°	457.8	457.8	461.6	462.9	462.9	460.3	457.8	459.1	457.8	456.5	455.3
57.5°	426.1	421.0	423.6	424.8	424.8	421.0	423.6	421.0	421.0	422.3	418.5
60°	385.5	385.5	383.0	386.8	386.8	384.2	384.2	385.5	383.0	381.7	380.4
62.5°	342.4	343.7	347.5	348.7	350.0	347.5	344.9	346.2	346.2	342.4	343.7
65°	305.6	308.2	313.2	312.0	309.4	310.7	308.2	309.4	305.6	306.9	303.1
67.5°	270.1	268.8	270.1	270.1	272.6	271.4	268.8	268.8	267.6	271.4	267.6
70°	232.1	232.1	232.1	232.1	233.3	234.6	232.1	229.5	230.8	228.3	227.0
72.5°	192.8	194.0	192.8	195.3	191.5	194.0	194.0	192.8	191.5	191.5	191.5
75°	156.0	158.5	154.7	156.0	154.7	157.2	156.0	156.0	153.4	152.2	153.4
77.5°	119.2	120.5	117.9	119.2	117.9	119.2	119.2	117.9	117.9	117.9	117.9
80°	85.0	86.2	85.0	83.7	82.4	85.0	82.4	83.7	85.0	83.7	86.2
82.5°	54.5	54.5	53.3	54.5	52.0	52.0	53.3	53.3	52.0	54.5	52.0
85°	26.6	26.6	29.2	26.6	25.4	25.4	25.4	26.6	25.4	27.9	26.6
87.5°	6.3	5.1	6.3	6.3	5.1	5.1	6.3	5.1	6.3	7.6	5.1
90°	12.6	12.7	12.9	13.2	13.4	13.6	13.4	13.2	12.9	12.7	12.6
92.5°	13.1	13.2	13.3	13.4	13.5	13.6	13.5	13.4	13.3	13.2	13.1
95°	22.1	22.0	21.9	21.8	21.7	21.6	21.7	21.8	21.9	22.0	22.1
97.5°	27.1	27.2	27.3	27.4	27.5	27.6	27.5	27.4	27.3	27.2	27.1
100°	32.7	32.8	33.0	33.3	33.5	33.7	33.5	33.3	33.0	32.8	32.7
102.5°	35.2	35.4	35.7	36.0	36.4	36.7	36.4	36.0	35.7	35.4	35.2
105°	36.2	36.4	36.9	37.3	37.8	38.2	37.8	37.3	36.9	36.4	36.2
107.5°	37.2	37.4	37.9	38.3	38.8	39.2	38.8	38.3	37.9	37.4	37.2
110°	37.7	37.9	38.4	38.8	39.3	39.7	39.3	38.8	38.4	37.9	37.7

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	38.7	38.9	39.2	39.5	39.9	40.2	39.9	39.5	39.2	38.9	38.7
115°	77.4	73.4	65.3	57.3	49.2	41.2	49.2	57.3	65.3	73.4	77.4
117.5°	265.4	250.8	221.5	192.2	163.0	133.7	163.0	192.2	221.5	250.8	265.4
120°	374.5	367.0	351.9	336.8	321.8	306.7	321.8	336.8	351.9	367.0	374.5
122.5°	401.2	401.3	401.4	401.5	401.6	401.7	401.6	401.5	401.4	401.3	401.2
125°	428.3	428.5	428.8	429.1	429.5	429.8	429.5	429.1	428.8	428.5	428.3
127.5°	454.5	454.6	454.7	454.8	454.9	455.0	454.9	454.8	454.7	454.6	454.5
130°	478.6	478.5	478.4	478.3	478.2	478.1	478.2	478.3	478.4	478.5	478.6
132.5°	501.2	501.1	501.0	500.9	500.8	500.7	500.8	500.9	501.0	501.1	501.2
135°	523.3	523.2	523.0	522.7	522.5	522.3	522.5	522.7	523.0	523.2	523.3
137.5°	543.9	543.7	543.4	543.1	542.7	542.4	542.7	543.1	543.4	543.7	543.9
140°	563.5	563.2	562.7	562.1	561.6	561.0	561.6	562.1	562.7	563.2	563.5
142.5°	581.6	581.3	580.8	580.2	579.7	579.1	579.7	580.2	580.8	581.3	581.6
145°	598.2	597.9	597.4	596.8	596.3	595.7	596.3	596.8	597.4	597.9	598.2
147.5°	612.8	612.6	612.1	611.7	611.2	610.8	611.2	611.7	612.1	612.6	612.8
150°	626.9	626.6	626.1	625.5	625.0	624.4	625.0	625.5	626.1	626.6	626.9
152.5°	639.5	639.1	638.3	637.5	636.7	635.9	636.7	637.5	638.3	639.1	639.5
155°	650.5	650.1	649.2	648.3	647.4	646.5	647.4	648.3	649.2	650.1	650.5
157.5°	660.6	660.1	659.2	658.3	657.4	656.5	657.4	658.3	659.2	660.1	660.6
160°	668.6	668.2	667.4	666.7	665.9	665.1	665.9	666.7	667.4	668.2	668.6
162.5°	676.7	676.2	675.2	674.1	673.1	672.1	673.1	674.1	675.2	676.2	676.7
165°	682.7	682.3	681.5	680.8	680.0	679.2	680.0	680.8	681.5	682.3	682.7
167.5°	688.2	687.7	686.7	685.7	684.7	683.7	684.7	685.7	686.7	687.7	688.2
170°	692.2	691.7	690.7	689.7	688.7	687.7	688.7	689.7	690.7	691.7	692.2
172.5°	695.3	694.8	693.8	692.7	691.7	690.7	691.7	692.7	693.8	694.8	695.3
175°	697.3	696.7	695.6	694.5	693.3	692.2	693.3	694.5	695.6	696.7	697.3
177.5°	697.8	697.3	696.3	695.2	694.2	693.2	694.2	695.2	696.3	697.3	697.8
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1566.1	1576.3	1572.5	1558.5	1575.0	1575.0	1586.4	1586.4	1600.4	1605.4	1613.0
5°	1477.4	1485.0	1491.3	1485.0	1496.4	1514.1	1524.3	1533.2	1552.2	1559.8	1571.2
7.5°	1382.2	1396.2	1402.5	1402.5	1421.6	1441.8	1462.1	1474.8	1501.4	1511.6	1523.0
10°	1289.7	1306.2	1318.8	1317.6	1349.3	1362.0	1387.3	1416.5	1443.1	1458.3	1474.8
12.5°	1192.0	1200.9	1218.7	1244.0	1251.6	1274.5	1303.6	1340.4	1388.6	1402.5	1426.6
15°	1110.9	1135.0	1148.9	1160.3	1178.1	1199.6	1231.3	1266.8	1315.0	1345.5	1370.8
17.5°	1042.4	1074.1	1083.0	1080.4	1103.3	1136.2	1173.0	1199.6	1242.8	1279.5	1303.6
20°	986.6	999.3	1014.5	1020.8	1038.6	1074.1	1109.6	1140.0	1175.5	1204.7	1232.6
22.5°	930.8	940.9	953.6	965.0	979.0	999.3	1033.5	1071.6	1105.8	1133.7	1165.4
25°	885.1	891.5	902.9	911.8	927.0	940.9	965.0	1006.9	1047.5	1063.9	1091.8
27.5°	840.8	845.8	853.4	863.6	871.2	885.1	906.7	940.9	982.8	999.3	1037.3
30°	801.4	805.3	812.9	817.9	821.7	838.2	854.7	881.3	913.0	935.9	963.8
32.5°	764.7	768.5	776.1	777.4	782.4	791.3	806.5	830.6	858.5	877.5	901.6
35°	724.1	726.6	734.2	736.8	740.6	748.2	759.6	777.4	802.7	816.7	838.2
37.5°	692.4	691.1	696.2	700.0	705.1	708.9	712.7	730.4	749.5	762.1	778.6
40°	658.2	655.6	656.9	662.0	664.5	669.6	669.6	687.3	700.0	710.1	722.8
42.5°	623.9	622.6	620.1	622.6	625.2	626.4	627.7	640.4	653.1	662.0	675.9
45°	589.7	588.4	585.9	587.1	587.1	589.7	593.5	598.6	607.4	615.0	622.6
47.5°	558.0	555.4	551.6	550.4	552.9	552.9	552.9	558.0	566.8	569.4	577.0
50°	525.0	521.2	516.1	513.6	513.6	512.3	514.9	516.1	523.7	526.3	532.6
52.5°	489.5	487.0	481.9	476.8	478.1	475.5	476.8	478.1	480.6	484.4	488.2
55°	454.0	448.9	445.1	443.8	440.0	440.0	436.2	441.3	440.0	441.3	446.4
57.5°	419.7	414.7	408.3	405.8	402.0	400.7	398.2	396.9	398.2	402.0	405.8
60°	379.2	376.6	372.8	369.0	366.5	362.7	360.1	360.1	358.9	358.9	360.1
62.5°	339.9	338.6	333.5	332.2	329.7	327.2	323.4	320.8	320.8	323.4	324.6
65°	301.8	300.5	296.7	295.5	289.1	286.6	285.3	284.1	281.5	281.5	281.5
67.5°	266.3	262.5	262.5	256.2	251.1	248.6	246.0	244.7	244.7	244.7	246.0
70°	227.0	227.0	223.2	219.4	214.3	215.6	211.8	208.0	208.0	205.4	206.7
72.5°	188.9	187.7	183.9	182.6	178.8	175.0	172.5	175.0	171.2	169.9	171.2
75°	152.2	150.9	148.4	145.8	147.1	143.3	139.5	138.2	138.2	135.7	135.7
77.5°	116.7	119.2	114.1	112.9	110.3	107.8	106.5	105.3	105.3	105.3	107.8
80°	81.2	82.4	82.4	79.9	81.2	77.4	77.4	77.4	73.6	74.8	76.1
82.5°	52.0	52.0	50.7	52.0	50.7	50.7	49.5	49.5	48.2	48.2	49.5
85°	29.2	27.9	26.6	29.2	27.9	27.9	26.6	26.6	26.6	26.6	26.6
87.5°	6.3	7.6	7.6	7.6	7.6	8.9	8.9	8.9	10.1	10.1	10.1
90°	12.3	11.8	11.2	10.7	10.1	9.2	8.3	7.4	6.5	6.0	5.4
92.5°	13.0	12.8	12.5	12.3	12.1	11.8	11.4	11.1	10.8	10.6	10.8
95°	21.8	21.3	20.7	20.2	19.6	18.8	18.0	17.3	16.5	16.1	17.9
97.5°	26.9	26.6	26.3	25.9	25.6	23.8	22.0	20.3	18.5	17.6	22.2
100°	32.3	31.4	30.5	29.6	28.7	26.8	24.9	23.0	21.1	20.1	27.8
102.5°	34.6	33.4	32.1	30.9	29.7	50.0	70.4	90.7	111.0	121.2	121.3
105°	35.6	34.4	33.1	31.9	30.7	61.2	91.7	122.2	152.7	167.9	166.2
107.5°	36.6	35.4	34.1	32.9	31.7	69.3	107.0	144.6	182.3	201.1	199.7
110°	43.3	54.5	65.6	76.8	88.0	120.3	152.6	184.9	217.2	233.3	232.1

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	62.8	110.9	159.1	207.2	255.4	257.3	259.2	261.1	263.0	263.9	262.9
115°	103.3	155.0	206.7	258.5	310.2	307.4	304.6	301.8	299.0	297.6	296.7
117.5°	273.4	289.4	305.3	321.3	337.3	335.4	333.5	331.6	329.7	328.8	327.7
120°	373.8	372.5	371.2	369.8	368.5	366.5	364.5	362.4	360.4	359.4	358.6
122.5°	400.9	400.2	399.5	398.9	398.2	396.0	393.7	391.5	389.2	388.1	387.2
125°	427.9	427.1	426.4	425.6	424.8	422.7	420.5	418.4	416.3	415.2	414.5
127.5°	453.9	452.8	451.7	450.5	449.4	447.7	446.1	444.4	442.7	441.9	441.1
130°	478.0	476.8	475.5	474.3	473.1	471.9	470.6	469.4	468.1	467.5	466.6
132.5°	500.7	499.7	498.7	497.7	496.7	495.5	494.3	493.0	491.8	491.2	490.5
135°	522.7	521.6	520.5	519.4	518.3	517.3	516.3	515.3	514.3	513.8	512.9
137.5°	543.3	542.2	541.1	540.0	538.9	537.8	536.7	535.6	534.5	533.9	533.2
140°	563.0	562.0	561.0	560.0	559.0	557.8	556.6	555.3	554.1	553.5	553.1
142.5°	581.2	580.3	579.4	578.5	577.6	576.2	574.7	573.3	571.8	571.1	570.7
145°	597.8	597.0	596.3	595.5	594.7	592.8	590.9	589.0	587.1	586.2	586.3
147.5°	612.5	612.0	611.4	610.9	610.3	608.4	606.5	604.6	602.7	601.8	602.0
150°	626.6	625.9	625.2	624.6	623.9	622.1	620.3	618.5	616.7	615.8	616.2
152.5°	639.2	638.5	637.8	637.1	636.4	634.7	633.1	631.4	629.7	628.9	629.3
155°	650.2	649.5	648.8	648.2	647.5	646.2	644.8	643.5	642.2	641.5	642.0
157.5°	660.2	659.4	658.7	657.9	657.1	656.1	655.1	654.0	653.0	652.5	652.9
160°	668.3	667.6	666.9	666.3	665.6	664.9	664.3	663.6	662.9	662.6	662.9
162.5°	676.3	675.5	674.7	673.9	673.1	672.5	672.0	671.4	670.9	670.6	670.9
165°	682.3	681.5	680.8	680.0	679.2	678.9	678.5	678.2	677.9	677.7	678.0
167.5°	687.8	687.0	686.3	685.5	684.7	684.4	684.0	683.7	683.4	683.2	683.5
170°	691.8	691.0	690.3	689.5	688.7	688.5	688.3	688.0	687.8	687.7	688.0
172.5°	694.9	694.1	693.3	692.5	691.7	691.5	691.3	691.0	690.8	690.7	691.0
175°	696.9	696.1	695.3	694.5	693.7	693.5	693.3	693.0	692.8	692.7	693.1
177.5°	697.4	696.6	695.9	695.1	694.3	694.2	694.0	693.9	693.8	693.7	694.1
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1649.8	1649.8	1649.8	1649.8
2.5°	1619.4	1619.4	1638.4	1658.7
5°	1583.9	1592.8	1623.2	1651.1
7.5°	1549.6	1564.9	1602.9	1638.4
10°	1507.8	1528.1	1575.0	1616.8
12.5°	1467.2	1486.2	1540.8	1587.7
15°	1410.1	1434.2	1492.6	1550.9
17.5°	1353.1	1377.2	1448.2	1516.7
20°	1285.9	1317.6	1397.5	1488.8
22.5°	1223.7	1263.0	1351.8	1425.4
25°	1155.3	1216.1	1298.5	1393.7
27.5°	1094.4	1155.3	1238.9	1335.3
30°	1025.9	1088.0	1174.3	1263.0
32.5°	960.0	1017.0	1100.7	1209.8
35°	891.5	946.0	1027.2	1137.5
37.5°	829.3	882.6	971.4	1072.8
40°	768.5	824.3	900.4	1001.8
42.5°	711.4	760.9	829.3	930.8
45°	659.4	694.9	758.3	853.4
47.5°	604.9	636.6	694.9	790.0
50°	554.2	580.8	631.5	720.3
52.5°	504.7	527.5	574.5	645.5
55°	460.3	481.9	516.1	585.9
57.5°	414.7	431.2	464.1	519.9
60°	370.3	385.5	412.1	457.8
62.5°	325.9	338.6	363.9	400.7
65°	286.6	296.7	315.8	347.5
67.5°	248.6	254.9	270.1	295.5
70°	211.8	216.8	229.5	249.8
72.5°	172.5	177.5	191.5	205.4
75°	139.5	140.8	150.9	162.3
77.5°	109.1	107.8	115.4	124.3
80°	74.8	78.6	85.0	88.8
82.5°	50.7	52.0	54.5	57.1
85°	27.9	29.2	29.2	33.0
87.5°	11.4	12.7	12.7	13.9
90°	4.2	2.9	1.7	0.5
92.5°	11.3	11.7	12.2	12.6
95°	21.6	25.3	29.0	32.7
97.5°	31.3	40.5	49.6	58.8
100°	43.1	58.4	73.7	89.0
102.5°	121.5	121.8	122.0	122.2
105°	162.9	159.5	156.2	152.8
107.5°	196.9	194.1	191.3	188.5
110°	229.8	227.4	225.1	222.7



TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	260.9	258.9	256.9	254.9
115°	294.8	292.9	291.0	289.1
117.5°	325.4	323.2	320.9	318.7
120°	356.9	355.2	353.6	351.9
122.5°	385.4	383.7	381.9	380.1
125°	413.0	411.6	410.1	408.7
127.5°	439.6	438.0	436.5	434.9
130°	464.8	463.1	461.3	459.5
132.5°	489.0	487.5	486.1	484.6
135°	511.1	509.3	507.5	505.7
137.5°	531.9	530.6	529.2	527.9
140°	552.2	551.3	550.4	549.5
142.5°	569.9	569.2	568.4	567.6
145°	586.4	586.5	586.6	586.7
147.5°	602.3	602.6	603.0	603.3
150°	617.0	617.7	618.5	619.3
152.5°	630.2	631.1	632.0	632.9
155°	643.0	644.0	645.0	646.0
157.5°	653.8	654.7	655.6	656.5
160°	663.6	664.3	664.9	665.6
162.5°	671.6	672.3	672.9	673.6
165°	678.7	679.4	680.0	680.7
167.5°	684.2	684.9	685.5	686.2
170°	688.7	689.4	690.0	690.7
172.5°	691.7	692.4	693.0	693.7
175°	693.9	694.7	695.5	696.3
177.5°	694.9	695.7	696.5	697.3
180°	694.8	694.8	694.8	694.8

TEST NUMBER: P999140

CATALOG NUMBER: SA2XXDIP-B865D530UB50-4F0-XX-W2A-A

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.41	19.36	19.24	20.21	21.27	15.90	16.86	16.73	17.71	18.76
	3H	19.23	20.08	20.07	20.94	22.03	17.25	18.11	18.10	18.97	20.05
	4H	19.40	20.21	20.26	21.07	22.17	17.72	18.53	18.58	19.39	20.49
	6H	19.45	20.19	20.32	21.07	22.18	18.03	18.78	18.91	19.65	20.76
	8H	19.43	20.14	20.31	21.03	22.14	18.12	18.83	19.00	19.72	20.82
	12H	19.40	20.07	20.28	20.96	22.09	18.16	18.84	19.05	19.72	20.85
4H	2H	18.46	19.27	19.33	20.13	21.23	16.36	17.17	17.22	18.03	19.13
	3H	19.45	20.12	20.33	21.02	22.13	17.83	18.50	18.71	19.40	20.51
	4H	19.73	20.34	20.62	21.24	22.37	18.37	18.98	19.26	19.87	21.01
	6H	19.86	20.39	20.77	21.31	22.45	18.75	19.28	19.65	20.20	21.34
	8H	19.87	20.36	20.77	21.27	22.42	18.86	19.35	19.77	20.27	21.42
	12H	19.83	20.28	20.76	21.21	22.37	18.92	19.37	19.85	20.30	21.46
8H	4H	19.75	20.24	20.65	21.15	22.30	18.51	19.01	19.42	19.92	21.07
	6H	19.93	20.33	20.86	21.29	22.44	18.95	19.36	19.89	20.31	21.47
	8H	19.96	20.32	20.90	21.26	22.43	19.10	19.46	20.05	20.41	21.58
	12H	19.95	20.26	20.89	21.20	22.42	19.20	19.52	20.15	20.46	21.68
12H	4H	19.71	20.15	20.63	21.08	22.24	18.49	18.94	19.42	19.87	21.03
	6H	19.91	20.27	20.85	21.21	22.38	18.95	19.31	19.90	20.26	21.43
	8H	19.94	20.26	20.89	21.20	22.42	19.12	19.43	20.06	20.37	21.59