

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997995

Luminaire Tested: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P997995
REPORT IS A COMBINATION OF REPORTS P983732 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6971.0 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	97	94	90	95	91	88	85	81	78	76	71	69	67	62	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	55	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	68	57	50	45	51	46	41	46	41	37	40	37	34
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	37	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22
10	50	38	31	26	47	37	30	26	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31769	31769	31769	31769
5°	31845	33874	31967	26949
10°	31476	36978	31673	22219
15°	30711	39004	31139	18715
20°	30233	36622	30233	16267
25°	29270	31461	29403	14546
30°	27685	24732	28213	13176
35°	26279	17101	26719	12055
40°	24665	12912	24947	11162
45°	22674	10611	23046	10198
50°	20953	9313	20991	9335
55°	18991	7935	19113	8399
60°	16899	6629	17133	7330
65°	15027	5391	15300	6259
70°	13161	4230	13494	5049
75°	11048	3070	11479	3662
80°	8622	1947	9237	2174
85°	5664	981	6102	727

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 32840 cd/sqm

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.2	2.7
10°-20°	556.4	8.0
20°-30°	807.5	11.6
30°-40°	851.2	12.2
40°-50°	753.3	10.8
50°-60°	601.5	8.6
60°-70°	408.5	5.9
70°-80°	209.0	3.0
80°-90°	52.0	0.7
90°-100°	56.2	0.8
100°-110°	178.7	2.6
110°-120°	305.8	4.4
120°-130°	402.1	5.8
130°-140°	451.4	6.5
140°-150°	442.6	6.3
150°-160°	371.3	5.3
160°-170°	246.2	3.5
170°-180°	86.1	1.2
0°-30°	1555.0	22.3
0°-40°	2406.3	34.5
0°-60°	3761.0	54.0
0°-90°	4430.6	63.6
90°-120°	540.7	7.8
90°-150°	1836.8	26.3
90°-180°	2540.0	36.4
0°-180°	6971.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2007	2007	2007	2007	2007	
5°	2008	2242	2016	1783	2008	190
15°	1887	2755	1913	1322	1887	533
25°	1695	2295	1703	1061	1695	775
35°	1384	1250	1407	881	1384	866
45°	1038	753	1055	724	1038	805
55°	713	529	717	560	713	636
65°	423	326	430	378	423	420
75°	198	160	205	191	198	212
85°	40	42	43	31	40	47
90°	1	26	1	26	1	5
95°	40	48	40	48	40	45
105°	165	170	165	170	165	174
115°	307	307	307	307	307	303
125°	446	448	446	448	446	399
135°	577	584	577	584	577	446
145°	701	708	701	708	701	438
155°	801	807	801	807	801	369
165°	872	873	872	873	872	246
175°	907	904	907	904	907	86
180°	909	909	909	909	909	

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2017.8	2022.4	2030.1	2031.7	2047.1	2059.4	2073.3	2073.3	2077.9	2076.4	2064.1
5°	2008.5	2022.4	2042.5	2059.4	2087.2	2099.5	2118.0	2131.9	2144.3	2153.5	2152.0
7.5°	1993.1	2017.8	2047.1	2079.5	2116.5	2138.1	2164.3	2189.0	2206.0	2221.4	2232.2
10°	1966.9	2008.5	2048.6	2091.8	2139.6	2169.0	2199.8	2232.2	2258.4	2287.7	2315.5
12.5°	1931.4	1991.5	2040.9	2098.0	2156.6	2189.0	2238.4	2263.1	2314.0	2388.0	2408.1
15°	1886.6	1968.4	2014.7	2087.2	2164.3	2190.6	2258.4	2298.5	2403.4	2449.7	2505.2
17.5°	1845.0	1936.0	1997.7	2081.0	2156.6	2207.5	2273.9	2355.6	2443.5	2509.9	2571.6
20°	1811.1	1899.0	1973.0	2065.6	2161.2	2226.0	2295.4	2394.2	2489.8	2557.7	2605.5
22.5°	1733.9	1846.5	1932.9	2036.3	2152.0	2241.5	2307.8	2415.8	2519.1	2560.8	2602.4
25°	1695.4	1792.5	1892.8	2010.1	2145.8	2252.3	2309.3	2429.7	2520.7	2536.1	2545.4
27.5°	1624.4	1733.9	1851.2	1985.4	2144.3	2233.7	2306.2	2415.8	2488.3	2477.5	2449.7
30°	1536.5	1670.7	1800.3	1945.3	2122.7	2219.9	2287.7	2388.0	2425.0	2369.5	2320.1
32.5°	1471.7	1598.2	1741.6	1909.8	2098.0	2190.6	2256.9	2335.6	2343.3	2243.0	2159.7
35°	1383.7	1524.1	1686.1	1863.5	2056.3	2139.6	2201.3	2249.2	2212.1	2071.8	1973.0
37.5°	1305.1	1443.9	1616.7	1797.2	1999.3	2081.0	2130.4	2138.1	2047.1	1923.7	1778.7
40°	1218.7	1362.2	1542.6	1732.4	1936.0	2007.0	2037.8	2014.7	1883.6	1740.1	1572.0
42.5°	1132.3	1274.2	1468.6	1663.0	1855.8	1916.0	1928.3	1865.1	1704.6	1536.5	1342.1
45°	1038.2	1186.3	1380.7	1576.6	1763.2	1797.2	1798.7	1707.7	1518.0	1342.1	1161.6
47.5°	961.1	1098.4	1291.2	1487.1	1644.5	1667.6	1658.3	1553.4	1346.7	1149.3	991.9
50°	876.2	1007.3	1198.6	1391.5	1525.7	1531.8	1508.7	1359.1	1157.0	976.5	851.5
52.5°	785.2	917.9	1093.7	1278.8	1399.2	1389.9	1345.2	1184.7	995.0	845.4	749.7
55°	712.7	829.9	995.0	1175.5	1260.3	1234.1	1184.7	1021.2	871.6	745.1	661.8
57.5°	632.5	735.8	897.8	1055.2	1104.5	1079.8	1030.5	877.8	738.9	643.3	587.7
60°	556.9	651.0	792.9	924.0	962.6	936.4	879.3	742.0	641.7	561.5	519.9
62.5°	487.5	569.2	688.0	808.3	823.8	797.5	748.2	637.1	550.7	487.5	456.6
65°	422.7	499.8	595.5	686.5	700.4	672.6	621.7	541.5	469.0	428.9	399.5
67.5°	359.4	421.1	506.0	572.3	580.0	553.8	512.2	447.4	402.6	359.4	337.8
70°	303.9	350.2	416.5	470.5	473.6	448.9	427.3	368.7	334.8	303.9	286.9
72.5°	249.9	282.3	333.2	373.3	374.9	359.4	339.4	302.4	273.0	251.5	234.5
75°	197.5	225.2	256.1	291.6	290.0	277.7	262.2	239.1	214.4	200.5	192.8
77.5°	151.2	168.1	192.8	216.0	216.0	209.8	200.5	183.6	168.1	154.3	146.6
80°	108.0	118.8	138.8	146.6	149.6	148.1	140.4	128.0	121.9	111.1	108.0
82.5°	69.4	77.1	86.4	94.1	98.7	95.6	94.1	87.9	78.7	75.6	72.5
85°	40.1	43.2	47.8	52.4	54.0	52.4	55.5	50.9	46.3	46.3	44.7
87.5°	17.0	18.5	21.6	21.6	23.1	23.1	21.6	23.1	23.1	21.6	20.1
90°	0.8	2.8	4.9	6.9	9.0	10.0	11.9	15.6	19.3	23.1	26.8
92.5°	16.9	18.3	19.6	21.0	22.3	23.0	23.1	23.3	23.4	23.6	23.8
95°	39.9	41.6	43.3	45.0	46.7	47.5	47.7	48.0	48.4	48.7	49.1
97.5°	66.7	68.2	69.8	71.3	72.8	73.6	73.9	74.6	75.3	76.0	76.7
100°	97.4	98.8	100.1	101.5	102.8	103.5	103.8	104.3	104.8	105.3	105.8
102.5°	129.6	130.6	131.6	132.7	133.7	134.2	134.5	135.2	135.9	136.6	137.3
105°	164.9	165.4	165.9	166.4	166.9	167.2	167.4	167.7	168.0	168.4	168.7
107.5°	200.1	200.8	201.5	202.2	202.9	203.2	203.2	203.2	203.2	203.2	203.2
110°	233.9	234.9	235.9	237.0	238.0	238.5	238.5	238.5	238.5	238.5	238.5

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	270.7	271.7	272.7	273.8	274.8	275.3	275.2	275.0	274.9	274.7	274.5
115°	306.7	307.7	308.7	309.8	310.8	311.3	311.1	310.8	310.5	310.1	309.8
117.5°	342.8	344.2	345.5	346.9	348.2	348.9	348.5	347.6	346.8	345.9	345.1
120°	378.8	380.2	381.5	382.9	384.2	384.9	384.2	382.9	381.5	380.2	378.8
122.5°	411.8	413.5	415.2	416.9	418.6	419.4	419.0	418.1	417.3	416.4	415.6
125°	446.3	447.8	449.4	450.9	452.4	453.2	452.9	452.4	451.9	451.4	450.9
127.5°	480.0	481.9	483.7	485.6	487.5	488.4	488.1	487.4	486.7	486.1	485.4
130°	511.5	513.7	515.9	518.1	520.3	521.4	521.2	520.9	520.6	520.2	519.9
132.5°	546.7	548.4	550.1	551.8	553.5	554.4	554.5	554.7	554.8	555.0	555.2
135°	577.4	579.3	581.1	583.0	584.9	585.8	586.0	586.3	586.7	587.0	587.4
137.5°	611.1	612.6	614.2	615.7	617.2	618.0	618.2	618.5	618.9	619.2	619.6
140°	641.0	642.5	644.1	645.6	647.1	647.9	648.3	649.2	650.1	650.9	651.8
142.5°	671.7	673.2	674.8	676.3	677.8	678.6	678.9	679.4	679.9	680.4	680.9
145°	700.8	702.0	703.2	704.4	705.6	706.2	706.7	707.7	708.8	709.8	710.8
147.5°	726.9	728.4	730.0	731.5	733.0	733.8	734.1	734.8	735.5	736.2	736.9
150°	753.8	754.8	755.8	756.9	757.9	758.4	758.7	759.4	760.1	760.7	761.4
152.5°	777.5	778.5	779.5	780.6	781.6	782.1	782.5	783.4	784.3	785.1	786.0
155°	801.3	801.8	802.3	802.8	803.3	803.6	803.9	804.4	804.9	805.4	805.9
157.5°	822.0	822.3	822.7	823.0	823.3	823.5	823.7	824.0	824.4	824.7	825.1
160°	840.4	840.7	841.1	841.4	841.7	841.9	842.0	842.2	842.3	842.5	842.7
162.5°	857.3	857.3	857.3	857.3	857.3	857.3	857.4	857.5	857.7	857.8	858.0
165°	871.8	871.6	871.5	871.3	871.2	871.1	871.1	871.1	871.1	871.1	871.1
167.5°	884.9	884.4	883.9	883.4	882.9	882.6	882.6	882.6	882.6	882.6	882.6
170°	894.8	894.3	893.8	893.3	892.8	892.5	892.4	892.3	892.1	892.0	891.8
172.5°	901.7	901.2	900.7	900.2	899.7	899.4	899.3	899.2	899.0	898.9	898.7
175°	907.1	906.6	906.1	905.6	905.1	904.8	904.6	904.3	904.0	903.6	903.3
177.5°	910.2	909.7	909.2	908.7	908.2	907.9	907.7	907.4	907.0	906.7	906.3
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2085.7	2087.2	2090.3	2105.7	2113.4	2115.0	2108.8	2122.7	2127.3	2122.7	2119.6
5°	2184.4	2193.6	2212.1	2232.2	2230.7	2232.2	2241.5	2250.7	2253.8	2241.5	2246.1
7.5°	2270.8	2289.3	2309.3	2340.2	2340.2	2355.6	2361.8	2369.5	2388.0	2378.8	2375.7
10°	2369.5	2394.2	2431.2	2480.6	2482.1	2497.5	2513.0	2537.6	2545.4	2539.2	2542.3
12.5°	2492.9	2540.7	2543.8	2597.8	2622.5	2625.6	2650.3	2645.6	2661.1	2661.1	2687.3
15°	2546.9	2620.9	2662.6	2715.0	2730.5	2712.0	2732.0	2753.6	2755.2	2755.2	2753.6
17.5°	2644.1	2673.4	2715.0	2742.8	2749.0	2749.0	2750.5	2759.8	2753.6	2741.3	2750.5
20°	2664.1	2676.5	2691.9	2688.8	2691.9	2676.5	2661.1	2645.6	2647.2	2639.5	2662.6
22.5°	2627.1	2624.0	2588.6	2565.4	2565.4	2534.6	2505.2	2491.4	2477.5	2482.1	2489.8
25°	2534.6	2486.7	2443.5	2409.6	2401.9	2352.5	2312.4	2300.1	2276.9	2295.4	2298.5
27.5°	2386.5	2332.5	2263.1	2233.7	2193.6	2173.6	2145.8	2108.8	2061.0	2088.7	2084.1
30°	2227.6	2147.4	2090.3	2019.3	1956.1	1951.4	1899.0	1837.3	1812.6	1812.6	1826.5
32.5°	2050.2	1943.7	1860.4	1760.2	1698.4	1672.2	1609.0	1547.3	1561.2	1514.9	1531.8
35°	1843.5	1703.1	1598.2	1501.0	1454.7	1423.9	1342.1	1308.2	1271.1	1249.5	1289.6
37.5°	1646.0	1484.0	1349.8	1243.4	1226.4	1170.9	1115.3	1093.7	1072.1	1081.4	1079.8
40°	1405.3	1261.9	1141.6	1058.3	1028.9	1002.7	965.7	939.5	925.6	933.3	934.8
42.5°	1187.8	1067.5	978.0	919.4	894.7	876.2	857.7	836.1	831.5	831.5	837.7
45°	1019.7	921.0	860.8	813.0	799.1	785.2	771.3	762.1	759.0	752.8	757.4
47.5°	885.5	806.8	769.8	734.3	718.9	715.8	703.4	698.8	692.6	691.1	692.6
50°	772.9	723.5	689.6	669.5	658.7	654.1	647.9	638.7	635.6	643.3	640.2
52.5°	694.2	647.9	629.4	609.3	603.2	597.0	587.7	589.3	587.7	584.7	584.7
55°	615.5	586.2	567.7	552.3	550.7	544.6	536.8	533.8	532.2	529.1	533.8
57.5°	552.3	529.1	512.2	498.3	492.1	492.1	484.4	478.2	478.2	476.7	478.2
60°	489.0	465.9	455.1	441.2	436.6	435.0	430.4	427.3	422.7	422.7	422.7
62.5°	430.4	411.9	399.5	387.2	388.7	381.0	374.9	371.8	371.8	373.3	373.3
65°	374.9	362.5	347.1	336.3	333.2	331.7	328.6	327.0	322.4	325.5	325.5
67.5°	324.0	307.0	297.7	293.1	288.5	286.9	283.8	280.8	279.2	277.7	280.8
70°	273.0	259.2	251.5	248.4	243.7	242.2	240.7	236.0	237.6	239.1	240.7
72.5°	226.8	214.4	212.9	203.6	203.6	203.6	197.5	200.5	199.0	195.9	199.0
75°	178.9	172.8	169.7	165.1	166.6	165.1	163.5	158.9	158.9	160.4	162.0
77.5°	141.9	135.8	134.2	129.6	126.5	129.6	126.5	125.0	125.0	126.5	126.5
80°	104.9	101.8	97.2	97.2	97.2	95.6	95.6	95.6	94.1	92.6	94.1
82.5°	69.4	69.4	67.9	66.3	67.9	64.8	66.3	66.3	66.3	66.3	66.3
85°	44.7	43.2	43.2	41.7	41.7	41.7	43.2	40.1	40.1	41.7	41.7
87.5°	20.1	20.1	20.1	21.6	20.1	20.1	20.1	21.6	20.1	20.1	20.1
90°	26.5	26.1	25.8	25.5	25.3	25.4	25.6	25.7	25.9	26.1	25.9
92.5°	24.0	24.1	24.3	24.4	24.5	24.5	24.5	24.5	24.5	24.5	24.5
95°	49.1	49.1	49.1	49.1	49.1	48.9	48.6	48.2	47.9	47.5	47.9
97.5°	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7
100°	105.8	105.8	105.8	105.8	105.8	105.7	105.6	105.4	105.3	105.1	105.3
102.5°	137.5	137.6	137.8	137.9	138.0	137.9	137.8	137.6	137.5	137.3	137.5
105°	169.0	169.4	169.7	170.0	170.2	170.2	170.2	170.2	170.2	170.2	170.2
107.5°	203.4	203.6	203.7	203.9	204.0	203.6	202.7	201.8	201.0	200.1	201.0
110°	238.5	238.5	238.5	238.5	238.5	238.2	237.7	237.2	236.7	236.2	236.7

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	274.0	273.5	273.0	272.5	272.2	272.0	271.7	271.4	271.0	270.7	271.0
115°	309.6	309.4	309.3	309.1	309.0	308.7	308.2	307.7	307.2	306.7	307.2
117.5°	344.6	344.1	343.6	343.1	342.8	342.5	342.0	341.5	341.0	340.5	341.0
120°	378.8	378.8	378.8	378.8	378.8	378.5	378.0	377.5	377.0	376.5	377.0
122.5°	415.1	414.6	414.1	413.6	413.3	413.1	412.8	412.5	412.1	411.8	412.1
125°	450.4	449.9	449.4	448.9	448.6	448.5	448.3	448.2	448.0	447.8	448.0
127.5°	484.7	484.0	483.3	482.6	482.3	482.0	481.5	481.0	480.5	480.0	480.5
130°	519.6	519.2	518.9	518.6	518.4	518.1	517.4	516.7	516.0	515.3	516.0
132.5°	554.3	553.5	552.6	551.7	551.3	551.0	550.5	550.0	549.5	549.0	549.5
135°	587.2	587.0	586.9	586.7	586.6	586.3	585.8	585.3	584.8	584.3	584.8
137.5°	619.4	619.2	619.1	618.9	618.8	618.5	617.8	617.1	616.4	615.7	616.4
140°	651.8	651.8	651.8	651.8	651.8	651.5	650.8	650.1	649.4	648.7	649.4
142.5°	681.1	681.3	681.4	681.6	681.7	681.4	680.7	680.0	679.3	678.6	679.3
145°	711.0	711.2	711.3	711.5	711.6	711.3	710.6	709.9	709.2	708.5	709.2
147.5°	737.2	737.6	737.9	738.2	738.4	738.1	737.4	736.7	736.1	735.4	736.1
150°	761.9	762.4	762.9	763.4	763.7	763.4	762.9	762.4	761.9	761.4	761.9
152.5°	786.7	787.3	788.0	788.7	789.0	788.7	788.0	787.3	786.7	786.0	786.7
155°	806.7	807.6	808.4	809.3	809.7	809.4	808.9	808.4	807.9	807.4	807.9
157.5°	826.3	827.5	828.6	829.8	830.4	830.0	829.1	828.3	827.4	826.6	827.4
160°	843.7	844.7	845.8	846.8	847.3	847.0	846.3	845.6	844.9	844.2	844.9
162.5°	859.2	860.4	861.6	862.8	863.4	863.0	862.1	861.3	860.4	859.6	860.4
165°	872.3	873.5	874.6	875.8	876.4	876.0	875.1	874.3	873.4	872.6	873.4
167.5°	883.8	885.0	886.1	887.3	887.9	887.5	886.6	885.8	884.9	884.1	884.9
170°	893.0	894.2	895.3	896.5	897.1	896.6	895.6	894.5	893.5	892.5	893.5
172.5°	899.9	901.1	902.2	903.4	904.0	903.5	902.5	901.4	900.4	899.4	900.4
175°	904.5	905.7	906.9	908.1	908.7	908.2	907.1	906.1	905.0	904.0	905.0
177.5°	907.3	908.4	909.4	910.5	911.0	910.5	909.4	908.4	907.3	906.3	907.3
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2127.3	2116.5	2107.2	2108.8	2116.5	2110.3	2094.9	2074.9	2067.1	2057.9	2067.1
5°	2255.3	2246.1	2227.6	2229.1	2224.5	2218.3	2193.6	2162.8	2162.8	2138.1	2135.0
7.5°	2381.8	2368.0	2355.6	2352.5	2335.6	2323.2	2301.6	2258.4	2241.5	2212.1	2195.2
10°	2523.8	2513.0	2499.1	2482.1	2472.9	2451.3	2415.8	2352.5	2321.7	2281.6	2252.3
12.5°	2667.2	2665.7	2634.8	2600.9	2599.3	2565.4	2540.7	2455.9	2414.2	2360.2	2290.8
15°	2758.2	2750.5	2733.6	2716.6	2721.2	2684.2	2628.7	2528.4	2500.6	2435.8	2361.8
17.5°	2756.7	2756.7	2752.1	2749.0	2744.4	2733.6	2702.7	2636.4	2591.6	2509.9	2440.5
20°	2668.8	2688.8	2693.5	2691.9	2707.3	2715.0	2713.5	2671.9	2636.4	2563.9	2492.9
22.5°	2492.9	2539.2	2559.2	2571.6	2604.0	2620.9	2661.1	2645.6	2636.4	2582.4	2522.2
25°	2329.4	2344.8	2405.0	2408.1	2452.8	2494.5	2534.6	2560.8	2594.7	2574.7	2523.8
27.5°	2118.0	2153.5	2196.7	2229.1	2238.4	2323.2	2389.6	2438.9	2516.0	2522.2	2505.2
30°	1878.9	1895.9	1966.9	2010.1	2059.4	2121.1	2216.8	2301.6	2371.0	2434.3	2455.9
32.5°	1587.4	1656.8	1698.4	1750.9	1794.1	1903.6	2020.9	2130.4	2210.6	2317.0	2363.3
35°	1320.5	1374.5	1445.5	1467.1	1545.7	1638.3	1791.0	1931.4	2053.3	2161.2	2255.3
37.5°	1099.9	1143.1	1218.7	1252.6	1298.9	1417.7	1545.7	1720.0	1866.6	1999.3	2116.5
40°	948.7	981.1	1038.2	1049.0	1087.6	1195.5	1298.9	1462.4	1656.8	1835.7	1963.8
42.5°	845.4	860.8	899.4	913.2	937.9	1010.4	1103.0	1257.3	1437.7	1622.9	1803.3
45°	771.3	782.1	805.3	817.6	848.5	880.8	956.4	1079.8	1221.8	1408.4	1602.8
47.5°	705.0	718.9	728.1	735.8	752.8	788.3	837.7	928.7	1064.4	1235.7	1423.9
50°	649.5	654.1	671.0	672.6	683.4	706.5	752.8	808.3	916.3	1055.2	1237.2
52.5°	593.9	598.5	609.3	620.1	624.8	643.3	674.1	720.4	800.6	910.2	1072.1
55°	538.4	544.6	555.4	563.1	567.7	583.1	601.6	646.4	709.6	786.7	919.4
57.5°	482.8	496.7	499.8	504.4	512.2	529.1	546.1	572.3	621.7	692.6	789.8
60°	430.4	435.0	445.8	450.5	458.2	467.4	489.0	509.1	544.6	600.1	688.0
62.5°	376.4	387.2	391.8	396.5	402.6	413.4	427.3	448.9	479.8	524.5	593.9
65°	330.1	331.7	340.9	347.1	353.3	361.0	374.9	394.9	413.4	455.1	506.0
67.5°	285.4	288.5	291.6	297.7	305.4	313.2	325.5	336.3	359.4	387.2	427.3
70°	242.2	242.2	249.9	254.5	253.0	262.2	271.5	283.8	300.8	327.0	359.4
72.5°	203.6	202.1	208.3	209.8	212.9	219.1	225.2	237.6	246.8	266.9	291.6
75°	162.0	165.1	168.1	168.1	172.8	177.4	183.6	189.7	200.5	212.9	231.4
77.5°	128.0	128.0	131.1	132.7	137.3	135.8	141.9	148.1	155.8	166.6	180.5
80°	94.1	97.2	97.2	97.2	98.7	100.3	106.4	111.1	115.7	123.4	129.6
82.5°	66.3	66.3	69.4	69.4	69.4	72.5	72.5	74.0	77.1	81.8	86.4
85°	41.7	41.7	41.7	43.2	41.7	43.2	46.3	44.7	46.3	49.4	49.4
87.5°	20.1	20.1	20.1	20.1	20.1	21.6	20.1	21.6	23.1	23.1	23.1
90°	25.7	25.6	25.4	25.3	25.5	25.8	26.1	26.5	26.8	23.1	19.3
92.5°	24.5	24.5	24.5	24.5	24.4	24.3	24.1	24.0	23.8	23.6	23.4
95°	48.2	48.6	48.9	49.1	49.1	49.1	49.1	49.1	49.1	48.7	48.4
97.5°	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.0	75.3
100°	105.4	105.6	105.7	105.8	105.8	105.8	105.8	105.8	105.8	105.3	104.8
102.5°	137.6	137.8	137.9	138.0	137.9	137.8	137.6	137.5	137.3	136.6	135.9
105°	170.2	170.2	170.2	170.2	170.0	169.7	169.4	169.0	168.7	168.4	168.0
107.5°	201.8	202.7	203.6	204.0	203.9	203.7	203.6	203.4	203.2	203.2	203.2
110°	237.2	237.7	238.2	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	271.4	271.7	272.0	272.2	272.5	273.0	273.5	274.0	274.5	274.7	274.9
115°	307.7	308.2	308.7	309.0	309.1	309.3	309.4	309.6	309.8	310.1	310.5
117.5°	341.5	342.0	342.5	342.8	343.1	343.6	344.1	344.6	345.1	345.9	346.8
120°	377.5	378.0	378.5	378.8	378.8	378.8	378.8	378.8	378.8	380.2	381.5
122.5°	412.5	412.8	413.1	413.3	413.6	414.1	414.6	415.1	415.6	416.4	417.3
125°	448.2	448.3	448.5	448.6	448.9	449.4	449.9	450.4	450.9	451.4	451.9
127.5°	481.0	481.5	482.0	482.3	482.6	483.3	484.0	484.7	485.4	486.1	486.7
130°	516.7	517.4	518.1	518.4	518.6	518.9	519.2	519.6	519.9	520.2	520.6
132.5°	550.0	550.5	551.0	551.3	551.7	552.6	553.5	554.3	555.2	555.0	554.8
135°	585.3	585.8	586.3	586.6	586.7	586.9	587.0	587.2	587.4	587.0	586.7
137.5°	617.1	617.8	618.5	618.8	618.9	619.1	619.2	619.4	619.6	619.2	618.9
140°	650.1	650.8	651.5	651.8	651.8	651.8	651.8	651.8	651.8	650.9	650.1
142.5°	680.0	680.7	681.4	681.7	681.6	681.4	681.3	681.1	680.9	680.4	679.9
145°	709.9	710.6	711.3	711.6	711.5	711.3	711.2	711.0	710.8	709.8	708.8
147.5°	736.7	737.4	738.1	738.4	738.2	737.9	737.6	737.2	736.9	736.2	735.5
150°	762.4	762.9	763.4	763.7	763.4	762.9	762.4	761.9	761.4	760.7	760.1
152.5°	787.3	788.0	788.7	789.0	788.7	788.0	787.3	786.7	786.0	785.1	784.3
155°	808.4	808.9	809.4	809.7	809.3	808.4	807.6	806.7	805.9	805.4	804.9
157.5°	828.3	829.1	830.0	830.4	829.8	828.6	827.5	826.3	825.1	824.7	824.4
160°	845.6	846.3	847.0	847.3	846.8	845.8	844.7	843.7	842.7	842.5	842.3
162.5°	861.3	862.1	863.0	863.4	862.8	861.6	860.4	859.2	858.0	857.8	857.7
165°	874.3	875.1	876.0	876.4	875.8	874.6	873.5	872.3	871.1	871.1	871.1
167.5°	885.8	886.6	887.5	887.9	887.3	886.1	885.0	883.8	882.6	882.6	882.6
170°	894.5	895.6	896.6	897.1	896.5	895.3	894.2	893.0	891.8	892.0	892.1
172.5°	901.4	902.5	903.5	904.0	903.4	902.2	901.1	899.9	898.7	898.9	899.0
175°	906.1	907.1	908.2	908.7	908.1	906.9	905.7	904.5	903.3	903.6	904.0
177.5°	908.4	909.4	910.5	911.0	910.5	909.4	908.4	907.3	906.3	906.7	907.0
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2059.4	2051.7	2047.1	2050.2	2040.9	2017.8	2017.8	2025.5	2016.2	2007.0	1993.1
5°	2116.5	2101.1	2091.8	2090.3	2068.7	2031.7	2023.9	2016.2	1996.2	1974.6	1951.4
7.5°	2172.0	2144.3	2128.8	2118.0	2087.2	2039.4	2019.3	2002.3	1970.0	1937.6	1908.2
10°	2218.3	2178.2	2159.7	2142.7	2102.6	2042.5	2010.1	1979.2	1937.6	1895.9	1858.9
12.5°	2255.3	2209.1	2185.9	2161.2	2111.9	2033.2	1993.1	1943.7	1902.1	1846.5	1809.5
15°	2317.0	2221.4	2199.8	2176.7	2125.8	2017.8	1968.4	1912.9	1855.8	1781.8	1741.6
17.5°	2366.4	2238.4	2236.8	2187.5	2121.1	2011.6	1936.0	1863.5	1801.8	1727.8	1664.5
20°	2395.7	2264.6	2239.9	2189.0	2105.7	1970.0	1891.3	1811.1	1744.7	1655.3	1592.0
22.5°	2420.4	2301.6	2236.8	2175.1	2073.3	1956.1	1840.4	1764.8	1673.8	1576.6	1516.4
25°	2429.7	2309.3	2241.5	2170.5	2050.2	1916.0	1784.8	1703.1	1601.3	1513.3	1431.6
27.5°	2431.2	2307.8	2224.5	2150.4	2017.8	1863.5	1729.3	1642.9	1530.3	1428.5	1346.7
30°	2415.8	2290.8	2215.2	2135.0	1986.9	1815.7	1661.4	1565.8	1445.5	1343.6	1258.8
32.5°	2369.5	2256.9	2195.2	2107.2	1946.8	1749.4	1596.6	1490.2	1363.7	1263.4	1181.7
35°	2292.4	2215.2	2147.4	2065.6	1894.4	1687.6	1531.8	1406.9	1278.8	1183.2	1106.1
37.5°	2196.7	2155.1	2091.8	2011.6	1834.2	1632.1	1459.3	1320.5	1192.5	1099.9	1024.3
40°	2067.1	2077.9	2016.2	1943.7	1763.2	1556.5	1365.2	1232.6	1112.2	1025.9	951.8
42.5°	1926.8	1971.5	1936.0	1866.6	1684.6	1473.2	1295.8	1149.3	1032.0	942.6	880.8
45°	1775.6	1852.7	1831.1	1780.2	1602.8	1385.3	1197.1	1055.2	951.8	865.4	811.4
47.5°	1610.5	1720.0	1720.0	1683.0	1511.8	1297.4	1112.2	967.2	865.4	803.7	751.3
50°	1442.4	1565.8	1585.8	1561.2	1410.0	1197.1	1008.9	877.8	789.8	729.7	691.1
52.5°	1266.5	1410.0	1447.0	1434.7	1302.0	1101.4	924.0	796.0	715.8	663.3	629.4
55°	1098.4	1265.0	1305.1	1309.7	1186.3	996.5	829.9	717.3	640.2	604.7	575.4
57.5°	939.5	1099.9	1144.6	1152.4	1069.1	900.9	742.0	643.3	573.9	544.6	521.4
60°	803.7	937.9	996.5	1013.5	941.0	789.8	660.3	564.6	512.2	484.4	462.8
62.5°	692.6	800.6	862.3	867.0	834.6	692.6	575.4	495.2	450.5	425.8	415.0
65°	584.7	681.8	718.9	737.4	711.2	600.1	496.7	430.4	394.9	373.3	362.5
67.5°	498.3	560.0	590.8	615.5	589.3	506.0	422.7	368.7	342.5	320.9	314.7
70°	408.8	459.7	482.8	507.5	484.4	421.1	361.0	311.6	288.5	271.5	263.8
72.5°	327.0	367.1	388.7	404.2	390.3	337.8	288.5	254.5	237.6	225.2	220.6
75°	259.2	286.9	299.3	310.1	303.9	263.8	232.9	205.2	189.7	178.9	175.9
77.5°	197.5	217.5	231.4	234.5	226.8	200.5	174.3	157.3	145.0	138.8	135.8
80°	140.4	152.7	160.4	165.1	157.3	146.6	128.0	115.7	104.9	97.2	95.6
82.5°	94.1	100.3	106.4	104.9	101.8	92.6	81.8	75.6	71.0	64.8	64.8
85°	54.0	55.5	58.6	60.2	58.6	52.4	46.3	43.2	40.1	35.5	35.5
87.5°	23.1	24.7	24.7	26.2	23.1	23.1	20.1	17.0	17.0	15.4	13.9
90°	15.6	11.9	10.0	9.0	6.9	4.9	2.8	0.8	2.8	4.9	6.9
92.5°	23.3	23.1	23.0	22.3	21.0	19.6	18.3	16.9	18.3	19.6	21.0
95°	48.0	47.7	47.5	46.7	45.0	43.3	41.6	39.9	41.6	43.3	45.0
97.5°	74.6	73.9	73.6	72.8	71.3	69.8	68.2	66.7	68.2	69.8	71.3
100°	104.3	103.8	103.5	102.8	101.5	100.1	98.8	97.4	98.8	100.1	101.5
102.5°	135.2	134.5	134.2	133.7	132.7	131.6	130.6	129.6	130.6	131.6	132.7
105°	167.7	167.4	167.2	166.9	166.4	165.9	165.4	164.9	165.4	165.9	166.4
107.5°	203.2	203.2	203.2	202.9	202.2	201.5	200.8	200.1	200.8	201.5	202.2
110°	238.5	238.5	238.5	238.0	237.0	235.9	234.9	233.9	234.9	235.9	237.0

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	275.0	275.2	275.3	274.8	273.8	272.7	271.7	270.7	271.7	272.7	273.8
115°	310.8	311.1	311.3	310.8	309.8	308.7	307.7	306.7	307.7	308.7	309.8
117.5°	347.6	348.5	348.9	348.2	346.9	345.5	344.2	342.8	344.2	345.5	346.9
120°	382.9	384.2	384.9	384.2	382.9	381.5	380.2	378.8	380.2	381.5	382.9
122.5°	418.1	419.0	419.4	418.6	416.9	415.2	413.5	411.8	413.5	415.2	416.9
125°	452.4	452.9	453.2	452.4	450.9	449.4	447.8	446.3	447.8	449.4	450.9
127.5°	487.4	488.1	488.4	487.5	485.6	483.7	481.9	480.0	481.9	483.7	485.6
130°	520.9	521.2	521.4	520.3	518.1	515.9	513.7	511.5	513.7	515.9	518.1
132.5°	554.7	554.5	554.4	553.5	551.8	550.1	548.4	546.7	548.4	550.1	551.8
135°	586.3	586.0	585.8	584.9	583.0	581.1	579.3	577.4	579.3	581.1	583.0
137.5°	618.5	618.2	618.0	617.2	615.7	614.2	612.6	611.1	612.6	614.2	615.7
140°	649.2	648.3	647.9	647.1	645.6	644.1	642.5	641.0	642.5	644.1	645.6
142.5°	679.4	678.9	678.6	677.8	676.3	674.8	673.2	671.7	673.2	674.8	676.3
145°	707.7	706.7	706.2	705.6	704.4	703.2	702.0	700.8	702.0	703.2	704.4
147.5°	734.8	734.1	733.8	733.0	731.5	730.0	728.4	726.9	728.4	730.0	731.5
150°	759.4	758.7	758.4	757.9	756.9	755.8	754.8	753.8	754.8	755.8	756.9
152.5°	783.4	782.5	782.1	781.6	780.6	779.5	778.5	777.5	778.5	779.5	780.6
155°	804.4	803.9	803.6	803.3	802.8	802.3	801.8	801.3	801.8	802.3	802.8
157.5°	824.0	823.7	823.5	823.3	823.0	822.7	822.3	822.0	822.3	822.7	823.0
160°	842.2	842.0	841.9	841.7	841.4	841.1	840.7	840.4	840.7	841.1	841.4
162.5°	857.5	857.4	857.3	857.3	857.3	857.3	857.3	857.3	857.3	857.3	857.3
165°	871.1	871.1	871.1	871.2	871.3	871.5	871.6	871.8	871.6	871.5	871.3
167.5°	882.6	882.6	882.6	882.9	883.4	883.9	884.4	884.9	884.4	883.9	883.4
170°	892.3	892.4	892.5	892.8	893.3	893.8	894.3	894.8	894.3	893.8	893.3
172.5°	899.2	899.3	899.4	899.7	900.2	900.7	901.2	901.7	901.2	900.7	900.2
175°	904.3	904.6	904.8	905.1	905.6	906.1	906.6	907.1	906.6	906.1	905.6
177.5°	907.4	907.7	907.9	908.2	908.7	909.2	909.7	910.2	909.7	909.2	908.7
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1985.4	1993.1	1991.5	1976.1	1959.2	1945.3	1919.0	1922.1	1912.9	1914.4	1923.7
5°	1936.0	1936.0	1929.8	1908.2	1880.5	1865.1	1835.7	1828.0	1809.5	1808.0	1806.4
7.5°	1883.6	1875.9	1868.1	1837.3	1803.3	1778.7	1738.6	1729.3	1710.8	1698.4	1692.3
10°	1821.9	1811.1	1795.6	1760.2	1718.5	1687.6	1646.0	1633.7	1598.2	1582.7	1573.5
12.5°	1754.0	1747.8	1723.1	1693.8	1625.9	1592.0	1531.8	1544.2	1508.7	1477.9	1473.2
15°	1686.1	1663.0	1649.1	1601.3	1519.5	1504.1	1456.3	1431.6	1399.2	1374.5	1374.5
17.5°	1619.8	1584.3	1553.4	1502.5	1442.4	1399.2	1363.7	1351.4	1311.2	1286.6	1281.9
20°	1531.8	1491.7	1484.0	1411.5	1369.9	1322.0	1288.1	1257.3	1227.9	1217.1	1209.4
22.5°	1448.5	1402.3	1389.9	1328.2	1286.6	1238.7	1204.8	1183.2	1161.6	1153.9	1140.0
25°	1359.1	1331.3	1312.8	1246.5	1200.2	1155.4	1132.3	1116.9	1096.8	1095.3	1086.0
27.5°	1272.7	1246.5	1227.9	1164.7	1130.8	1089.1	1070.6	1053.6	1042.8	1038.2	1033.6
30°	1198.6	1169.3	1147.7	1101.4	1059.8	1025.9	1010.4	999.6	993.5	985.7	984.2
32.5°	1116.9	1099.9	1070.6	1035.1	1002.7	970.3	961.1	953.4	944.1	941.0	939.5
35°	1047.5	1024.3	1005.8	965.7	951.8	924.0	913.2	907.1	894.7	891.6	888.6
37.5°	979.6	958.0	937.9	913.2	887.0	871.6	865.4	856.2	850.0	851.5	848.5
40°	911.7	894.7	879.3	853.1	837.7	829.9	817.6	808.3	805.3	806.8	805.3
42.5°	845.4	829.9	820.7	800.6	785.2	777.5	769.8	760.5	765.1	765.1	769.8
45°	785.2	771.3	765.1	749.7	740.5	728.1	720.4	718.9	725.0	723.5	723.5
47.5°	723.5	718.9	711.2	697.3	684.9	677.2	675.7	675.7	681.8	684.9	683.4
50°	675.7	666.4	657.2	646.4	637.1	634.0	629.4	632.5	638.7	638.7	641.7
52.5°	615.5	609.3	606.3	597.0	590.8	590.8	590.8	592.4	597.0	601.6	600.1
55°	563.1	558.4	555.4	550.7	543.0	544.6	543.0	546.1	550.7	555.4	558.4
57.5°	507.5	506.0	502.9	495.2	495.2	493.6	498.3	499.8	507.5	510.6	515.2
60°	458.2	453.5	453.5	447.4	447.4	447.4	452.0	456.6	462.8	464.3	467.4
62.5°	405.7	405.7	404.2	399.5	399.5	404.2	405.7	411.9	415.0	415.0	419.6
65°	356.4	354.8	353.3	354.8	356.4	356.4	361.0	364.1	367.1	368.7	370.2
67.5°	307.0	305.4	308.5	307.0	310.1	316.2	314.7	319.3	324.0	324.0	325.5
70°	260.7	263.8	262.2	265.3	263.8	266.9	271.5	273.0	273.0	274.6	279.2
72.5°	217.5	217.5	217.5	216.0	217.5	220.6	223.7	225.2	228.3	229.9	234.5
75°	175.9	175.9	172.8	175.9	175.9	178.9	182.0	182.0	182.0	185.1	189.7
77.5°	132.7	134.2	132.7	135.8	135.8	137.3	140.4	138.8	141.9	143.5	145.0
80°	97.2	95.6	95.6	95.6	97.2	97.2	100.3	101.8	101.8	106.4	103.4
82.5°	61.7	63.2	61.7	63.2	63.2	64.8	63.2	64.8	66.3	69.4	67.9
85°	35.5	33.9	33.9	35.5	33.9	33.9	35.5	33.9	35.5	33.9	35.5
87.5°	13.9	12.3	12.3	12.3	12.3	10.8	10.8	9.3	9.3	9.3	7.7
90°	9.0	10.0	11.9	15.6	19.3	23.1	26.8	26.5	26.1	25.8	25.5
92.5°	22.3	23.0	23.1	23.3	23.4	23.6	23.8	24.0	24.1	24.3	24.4
95°	46.7	47.5	47.7	48.0	48.4	48.7	49.1	49.1	49.1	49.1	49.1
97.5°	72.8	73.6	73.9	74.6	75.3	76.0	76.7	76.7	76.7	76.7	76.7
100°	102.8	103.5	103.8	104.3	104.8	105.3	105.8	105.8	105.8	105.8	105.8
102.5°	133.7	134.2	134.5	135.2	135.9	136.6	137.3	137.5	137.6	137.8	137.9
105°	166.9	167.2	167.4	167.7	168.0	168.4	168.7	169.0	169.4	169.7	170.0
107.5°	202.9	203.2	203.2	203.2	203.2	203.2	203.2	203.4	203.6	203.7	203.9
110°	238.0	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	274.8	275.3	275.2	275.0	274.9	274.7	274.5	274.0	273.5	273.0	272.5
115°	310.8	311.3	311.1	310.8	310.5	310.1	309.8	309.6	309.4	309.3	309.1
117.5°	348.2	348.9	348.5	347.6	346.8	345.9	345.1	344.6	344.1	343.6	343.1
120°	384.2	384.9	384.2	382.9	381.5	380.2	378.8	378.8	378.8	378.8	378.8
122.5°	418.6	419.4	419.0	418.1	417.3	416.4	415.6	415.1	414.6	414.1	413.6
125°	452.4	453.2	452.9	452.4	451.9	451.4	450.9	450.4	449.9	449.4	448.9
127.5°	487.5	488.4	488.1	487.4	486.7	486.1	485.4	484.7	484.0	483.3	482.6
130°	520.3	521.4	521.2	520.9	520.6	520.2	519.9	519.6	519.2	518.9	518.6
132.5°	553.5	554.4	554.5	554.7	554.8	555.0	555.2	554.3	553.5	552.6	551.7
135°	584.9	585.8	586.0	586.3	586.7	587.0	587.4	587.2	587.0	586.9	586.7
137.5°	617.2	618.0	618.2	618.5	618.9	619.2	619.6	619.4	619.2	619.1	618.9
140°	647.1	647.9	648.3	649.2	650.1	650.9	651.8	651.8	651.8	651.8	651.8
142.5°	677.8	678.6	678.9	679.4	679.9	680.4	680.9	681.1	681.3	681.4	681.6
145°	705.6	706.2	706.7	707.7	708.8	709.8	710.8	711.0	711.2	711.3	711.5
147.5°	733.0	733.8	734.1	734.8	735.5	736.2	736.9	737.2	737.6	737.9	738.2
150°	757.9	758.4	758.7	759.4	760.1	760.7	761.4	761.9	762.4	762.9	763.4
152.5°	781.6	782.1	782.5	783.4	784.3	785.1	786.0	786.7	787.3	788.0	788.7
155°	803.3	803.6	803.9	804.4	804.9	805.4	805.9	806.7	807.6	808.4	809.3
157.5°	823.3	823.5	823.7	824.0	824.4	824.7	825.1	826.3	827.5	828.6	829.8
160°	841.7	841.9	842.0	842.2	842.3	842.5	842.7	843.7	844.7	845.8	846.8
162.5°	857.3	857.3	857.4	857.5	857.7	857.8	858.0	859.2	860.4	861.6	862.8
165°	871.2	871.1	871.1	871.1	871.1	871.1	871.1	872.3	873.5	874.6	875.8
167.5°	882.9	882.6	882.6	882.6	882.6	882.6	882.6	883.8	885.0	886.1	887.3
170°	892.8	892.5	892.4	892.3	892.1	892.0	891.8	893.0	894.2	895.3	896.5
172.5°	899.7	899.4	899.3	899.2	899.0	898.9	898.7	899.9	901.1	902.2	903.4
175°	905.1	904.8	904.6	904.3	904.0	903.6	903.3	904.5	905.7	906.9	908.1
177.5°	908.2	907.9	907.7	907.4	907.0	906.7	906.3	907.3	908.4	909.4	910.5
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1912.9	1917.5	1906.7	1903.6	1906.7	1895.9	1899.0	1902.1	1902.1	1906.7	1909.8
5°	1801.8	1795.6	1784.8	1781.8	1778.7	1783.3	1780.2	1784.8	1786.4	1797.2	1798.7
7.5°	1692.3	1683.0	1673.8	1664.5	1661.4	1653.7	1661.4	1661.4	1672.2	1669.1	1676.9
10°	1562.7	1561.2	1548.8	1544.2	1538.0	1525.7	1542.6	1538.0	1545.7	1559.6	1562.7
12.5°	1467.1	1450.1	1457.8	1436.2	1443.9	1431.6	1433.1	1433.1	1445.5	1447.0	1443.9
15°	1376.0	1362.2	1342.1	1332.8	1328.2	1322.0	1342.1	1343.6	1334.4	1356.0	1348.3
17.5°	1283.5	1283.5	1265.0	1260.3	1248.0	1254.2	1251.1	1252.6	1249.5	1265.0	1272.7
20°	1203.3	1195.5	1189.4	1190.9	1175.5	1172.4	1169.3	1172.4	1183.2	1194.0	1197.1
22.5°	1138.5	1133.8	1118.4	1121.5	1109.2	1113.8	1110.7	1118.4	1120.0	1120.0	1130.8
25°	1076.8	1070.6	1072.1	1066.0	1061.3	1061.3	1056.7	1061.3	1067.5	1070.6	1072.1
27.5°	1030.5	1025.9	1018.1	1013.5	1016.6	1008.9	1015.1	1019.7	1019.7	1016.6	1019.7
30°	974.9	978.0	978.0	962.6	968.8	965.7	970.3	973.4	973.4	974.9	971.9
32.5°	937.9	928.7	927.1	925.6	925.6	919.4	919.4	924.0	925.6	927.1	931.8
35°	888.6	888.6	880.8	885.5	879.3	880.8	879.3	880.8	883.9	879.3	883.9
37.5°	843.8	845.4	842.3	845.4	846.9	843.8	840.7	846.9	843.8	843.8	840.7
40°	805.3	803.7	805.3	805.3	805.3	806.8	803.7	803.7	803.7	800.6	797.5
42.5°	772.9	763.6	766.7	768.2	763.6	763.6	765.1	763.6	768.2	759.0	759.0
45°	726.6	723.5	725.0	725.0	728.1	723.5	726.6	728.1	723.5	722.0	718.9
47.5°	684.9	688.0	684.9	688.0	688.0	691.1	684.9	686.5	688.0	681.8	677.2
50°	643.3	643.3	647.9	646.4	647.9	644.8	644.8	643.3	644.8	641.7	637.1
52.5°	604.7	600.1	607.8	606.3	604.7	603.2	601.6	603.2	600.1	597.0	597.0
55°	556.9	556.9	561.5	563.1	563.1	560.0	556.9	558.4	556.9	555.4	553.8
57.5°	518.3	512.2	515.2	516.8	516.8	512.2	515.2	512.2	512.2	513.7	509.1
60°	469.0	469.0	465.9	470.5	470.5	467.4	467.4	469.0	465.9	464.3	462.8
62.5°	416.5	418.1	422.7	424.2	425.8	422.7	419.6	421.1	421.1	416.5	418.1
65°	371.8	374.9	381.0	379.5	376.4	377.9	374.9	376.4	371.8	373.3	368.7
67.5°	328.6	327.0	328.6	328.6	331.7	330.1	327.0	327.0	325.5	330.1	325.5
70°	282.3	282.3	282.3	282.3	283.8	285.4	282.3	279.2	280.8	277.7	276.1
72.5°	234.5	236.0	234.5	237.6	232.9	236.0	236.0	234.5	232.9	232.9	232.9
75°	189.7	192.8	188.2	189.7	188.2	191.3	189.7	189.7	186.7	185.1	186.7
77.5°	145.0	146.6	143.5	145.0	143.5	145.0	145.0	143.5	143.5	143.5	143.5
80°	103.4	104.9	103.4	101.8	100.3	103.4	100.3	101.8	103.4	101.8	104.9
82.5°	66.3	66.3	64.8	66.3	63.2	63.2	64.8	64.8	63.2	66.3	63.2
85°	32.4	32.4	35.5	32.4	30.9	30.9	30.9	32.4	30.9	33.9	32.4
87.5°	7.7	6.2	7.7	7.7	6.2	6.2	7.7	6.2	7.7	9.3	6.2
90°	25.3	25.4	25.6	25.7	25.9	26.1	25.9	25.7	25.6	25.4	25.3
92.5°	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5
95°	49.1	48.9	48.6	48.2	47.9	47.5	47.9	48.2	48.6	48.9	49.1
97.5°	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7
100°	105.8	105.7	105.6	105.4	105.3	105.1	105.3	105.4	105.6	105.7	105.8
102.5°	138.0	137.9	137.8	137.6	137.5	137.3	137.5	137.6	137.8	137.9	138.0
105°	170.2	170.2	170.2	170.2	170.2	170.2	170.2	170.2	170.2	170.2	170.2
107.5°	204.0	203.6	202.7	201.8	201.0	200.1	201.0	201.8	202.7	203.6	204.0
110°	238.5	238.2	237.7	237.2	236.7	236.2	236.7	237.2	237.7	238.2	238.5

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	272.2	272.0	271.7	271.4	271.0	270.7	271.0	271.4	271.7	272.0	272.2
115°	309.0	308.7	308.2	307.7	307.2	306.7	307.2	307.7	308.2	308.7	309.0
117.5°	342.8	342.5	342.0	341.5	341.0	340.5	341.0	341.5	342.0	342.5	342.8
120°	378.8	378.5	378.0	377.5	377.0	376.5	377.0	377.5	378.0	378.5	378.8
122.5°	413.3	413.1	412.8	412.5	412.1	411.8	412.1	412.5	412.8	413.1	413.3
125°	448.6	448.5	448.3	448.2	448.0	447.8	448.0	448.2	448.3	448.5	448.6
127.5°	482.3	482.0	481.5	481.0	480.5	480.0	480.5	481.0	481.5	482.0	482.3
130°	518.4	518.1	517.4	516.7	516.0	515.3	516.0	516.7	517.4	518.1	518.4
132.5°	551.3	551.0	550.5	550.0	549.5	549.0	549.5	550.0	550.5	551.0	551.3
135°	586.6	586.3	585.8	585.3	584.8	584.3	584.8	585.3	585.8	586.3	586.6
137.5°	618.8	618.5	617.8	617.1	616.4	615.7	616.4	617.1	617.8	618.5	618.8
140°	651.8	651.5	650.8	650.1	649.4	648.7	649.4	650.1	650.8	651.5	651.8
142.5°	681.7	681.4	680.7	680.0	679.3	678.6	679.3	680.0	680.7	681.4	681.7
145°	711.6	711.3	710.6	709.9	709.2	708.5	709.2	709.9	710.6	711.3	711.6
147.5°	738.4	738.1	737.4	736.7	736.1	735.4	736.1	736.7	737.4	738.1	738.4
150°	763.7	763.4	762.9	762.4	761.9	761.4	761.9	762.4	762.9	763.4	763.7
152.5°	789.0	788.7	788.0	787.3	786.7	786.0	786.7	787.3	788.0	788.7	789.0
155°	809.7	809.4	808.9	808.4	807.9	807.4	807.9	808.4	808.9	809.4	809.7
157.5°	830.4	830.0	829.1	828.3	827.4	826.6	827.4	828.3	829.1	830.0	830.4
160°	847.3	847.0	846.3	845.6	844.9	844.2	844.9	845.6	846.3	847.0	847.3
162.5°	863.4	863.0	862.1	861.3	860.4	859.6	860.4	861.3	862.1	863.0	863.4
165°	876.4	876.0	875.1	874.3	873.4	872.6	873.4	874.3	875.1	876.0	876.4
167.5°	887.9	887.5	886.6	885.8	884.9	884.1	884.9	885.8	886.6	887.5	887.9
170°	897.1	896.6	895.6	894.5	893.5	892.5	893.5	894.5	895.6	896.6	897.1
172.5°	904.0	903.5	902.5	901.4	900.4	899.4	900.4	901.4	902.5	903.5	904.0
175°	908.7	908.2	907.1	906.1	905.0	904.0	905.0	906.1	907.1	908.2	908.7
177.5°	911.0	910.5	909.4	908.4	907.3	906.3	907.3	908.4	909.4	910.5	911.0
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1905.2	1917.5	1912.9	1895.9	1916.0	1916.0	1929.8	1929.8	1946.8	1953.0	1962.2
5°	1797.2	1806.4	1814.1	1806.4	1820.3	1841.9	1854.3	1865.1	1888.2	1897.4	1911.3
7.5°	1681.5	1698.4	1706.2	1706.2	1729.3	1754.0	1778.7	1794.1	1826.5	1838.8	1852.7
10°	1568.9	1588.9	1604.3	1602.8	1641.4	1656.8	1687.6	1723.1	1755.5	1774.0	1794.1
12.5°	1450.1	1460.9	1482.5	1513.3	1522.6	1550.4	1585.8	1630.6	1689.2	1706.2	1735.5
15°	1351.4	1380.7	1397.6	1411.5	1433.1	1459.3	1497.9	1541.1	1599.7	1636.7	1667.6
17.5°	1268.1	1306.6	1317.4	1314.3	1342.1	1382.2	1426.9	1459.3	1511.8	1556.5	1585.8
20°	1200.2	1215.6	1234.1	1241.8	1263.4	1306.6	1349.8	1386.8	1430.0	1465.5	1499.4
22.5°	1132.3	1144.6	1160.1	1173.9	1190.9	1215.6	1257.3	1303.5	1345.2	1379.1	1417.7
25°	1076.8	1084.5	1098.4	1109.2	1127.7	1144.6	1173.9	1224.9	1274.2	1294.3	1328.2
27.5°	1022.8	1028.9	1038.2	1050.5	1059.8	1076.8	1103.0	1144.6	1195.5	1215.6	1261.9
30°	974.9	979.6	988.8	995.0	999.6	1019.7	1039.7	1072.1	1110.7	1138.5	1172.4
32.5°	930.2	934.8	944.1	945.6	951.8	962.6	981.1	1010.4	1044.4	1067.5	1096.8
35°	880.8	883.9	893.2	896.3	900.9	910.2	924.0	945.6	976.5	993.5	1019.7
37.5°	842.3	840.7	846.9	851.5	857.7	862.3	867.0	888.6	911.7	927.1	947.2
40°	800.6	797.5	799.1	805.3	808.3	814.5	814.5	836.1	851.5	863.9	879.3
42.5°	759.0	757.4	754.4	757.4	760.5	762.1	763.6	779.0	794.5	805.3	822.2
45°	717.3	715.8	712.7	714.2	714.2	717.3	722.0	728.1	738.9	748.2	757.4
47.5°	678.8	675.7	671.0	669.5	672.6	672.6	672.6	678.8	689.6	692.6	701.9
50°	638.7	634.0	627.9	624.8	624.8	623.2	626.3	627.9	637.1	640.2	647.9
52.5°	595.5	592.4	586.2	580.0	581.6	578.5	580.0	581.6	584.7	589.3	593.9
55°	552.3	546.1	541.5	539.9	535.3	535.3	530.7	536.8	535.3	536.8	543.0
57.5°	510.6	504.4	496.7	493.6	489.0	487.5	484.4	482.8	484.4	489.0	493.6
60°	461.2	458.2	453.5	448.9	445.8	441.2	438.1	438.1	436.6	436.6	438.1
62.5°	413.4	411.9	405.7	404.2	401.1	398.0	393.4	390.3	390.3	393.4	394.9
65°	367.1	365.6	361.0	359.4	351.7	348.6	347.1	345.6	342.5	342.5	342.5
67.5°	324.0	319.3	319.3	311.6	305.4	302.4	299.3	297.7	297.7	297.7	299.3
70°	276.1	276.1	271.5	266.9	260.7	262.2	257.6	253.0	253.0	249.9	251.5
72.5°	229.9	228.3	223.7	222.1	217.5	212.9	209.8	212.9	208.3	206.7	208.3
75°	185.1	183.6	180.5	177.4	178.9	174.3	169.7	168.1	168.1	165.1	165.1
77.5°	141.9	145.0	138.8	137.3	134.2	131.1	129.6	128.0	128.0	128.0	131.1
80°	98.7	100.3	100.3	97.2	98.7	94.1	94.1	94.1	89.5	91.0	92.6
82.5°	63.2	63.2	61.7	63.2	61.7	61.7	60.2	60.2	58.6	58.6	60.2
85°	35.5	33.9	32.4	35.5	33.9	33.9	32.4	32.4	32.4	32.4	32.4
87.5°	7.7	9.3	9.3	9.3	9.3	10.8	10.8	10.8	12.3	12.3	12.3
90°	25.5	25.8	26.1	26.5	26.8	23.1	19.3	15.6	11.9	10.0	9.0
92.5°	24.4	24.3	24.1	24.0	23.8	23.6	23.4	23.3	23.1	23.0	22.3
95°	49.1	49.1	49.1	49.1	49.1	48.7	48.4	48.0	47.7	47.5	46.7
97.5°	76.7	76.7	76.7	76.7	76.7	76.0	75.3	74.6	73.9	73.6	72.8
100°	105.8	105.8	105.8	105.8	105.8	105.3	104.8	104.3	103.8	103.5	102.8
102.5°	137.9	137.8	137.6	137.5	137.3	136.6	135.9	135.2	134.5	134.2	133.7
105°	170.0	169.7	169.4	169.0	168.7	168.4	168.0	167.7	167.4	167.2	166.9
107.5°	203.9	203.7	203.6	203.4	203.2	203.2	203.2	203.2	203.2	203.2	202.9
110°	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.0

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	272.5	273.0	273.5	274.0	274.5	274.7	274.9	275.0	275.2	275.3	274.8
115°	309.1	309.3	309.4	309.6	309.8	310.1	310.5	310.8	311.1	311.3	310.8
117.5°	343.1	343.6	344.1	344.6	345.1	345.9	346.8	347.6	348.5	348.9	348.2
120°	378.8	378.8	378.8	378.8	378.8	380.2	381.5	382.9	384.2	384.9	384.2
122.5°	413.6	414.1	414.6	415.1	415.6	416.4	417.3	418.1	419.0	419.4	418.6
125°	448.9	449.4	449.9	450.4	450.9	451.4	451.9	452.4	452.9	453.2	452.4
127.5°	482.6	483.3	484.0	484.7	485.4	486.1	486.7	487.4	488.1	488.4	487.5
130°	518.6	518.9	519.2	519.6	519.9	520.2	520.6	520.9	521.2	521.4	520.3
132.5°	551.7	552.6	553.5	554.3	555.2	555.0	554.8	554.7	554.5	554.4	553.5
135°	586.7	586.9	587.0	587.2	587.4	587.0	586.7	586.3	586.0	585.8	584.9
137.5°	618.9	619.1	619.2	619.4	619.6	619.2	618.9	618.5	618.2	618.0	617.2
140°	651.8	651.8	651.8	651.8	651.8	650.9	650.1	649.2	648.3	647.9	647.1
142.5°	681.6	681.4	681.3	681.1	680.9	680.4	679.9	679.4	678.9	678.6	677.8
145°	711.5	711.3	711.2	711.0	710.8	709.8	708.8	707.7	706.7	706.2	705.6
147.5°	738.2	737.9	737.6	737.2	736.9	736.2	735.5	734.8	734.1	733.8	733.0
150°	763.4	762.9	762.4	761.9	761.4	760.7	760.1	759.4	758.7	758.4	757.9
152.5°	788.7	788.0	787.3	786.7	786.0	785.1	784.3	783.4	782.5	782.1	781.6
155°	809.3	808.4	807.6	806.7	805.9	805.4	804.9	804.4	803.9	803.6	803.3
157.5°	829.8	828.6	827.5	826.3	825.1	824.7	824.4	824.0	823.7	823.5	823.3
160°	846.8	845.8	844.7	843.7	842.7	842.5	842.3	842.2	842.0	841.9	841.7
162.5°	862.8	861.6	860.4	859.2	858.0	857.8	857.7	857.5	857.4	857.3	857.3
165°	875.8	874.6	873.5	872.3	871.1	871.1	871.1	871.1	871.1	871.1	871.2
167.5°	887.3	886.1	885.0	883.8	882.6	882.6	882.6	882.6	882.6	882.6	882.9
170°	896.5	895.3	894.2	893.0	891.8	892.0	892.1	892.3	892.4	892.5	892.8
172.5°	903.4	902.2	901.1	899.9	898.7	898.9	899.0	899.2	899.3	899.4	899.7
175°	908.1	906.9	905.7	904.5	903.3	903.6	904.0	904.3	904.6	904.8	905.1
177.5°	910.5	909.4	908.4	907.3	906.3	906.7	907.0	907.4	907.7	907.9	908.2
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2007.0	2007.0	2007.0	2007.0
2.5°	1970.0	1970.0	1993.1	2017.8
5°	1926.8	1937.6	1974.6	2008.5
7.5°	1885.1	1903.6	1949.9	1993.1
10°	1834.2	1858.9	1916.0	1966.9
12.5°	1784.8	1808.0	1874.3	1931.4
15°	1715.4	1744.7	1815.7	1886.6
17.5°	1646.0	1675.3	1761.7	1845.0
20°	1564.2	1602.8	1700.0	1811.1
22.5°	1488.6	1536.5	1644.5	1733.9
25°	1405.3	1479.4	1579.7	1695.4
27.5°	1331.3	1405.3	1507.2	1624.4
30°	1248.0	1323.6	1428.5	1536.5
32.5°	1167.8	1237.2	1339.0	1471.7
35°	1084.5	1150.8	1249.5	1383.7
37.5°	1008.9	1073.7	1181.7	1305.1
40°	934.8	1002.7	1095.3	1218.7
42.5°	865.4	925.6	1008.9	1132.3
45°	802.2	845.4	922.5	1038.2
47.5°	735.8	774.4	845.4	961.1
50°	674.1	706.5	768.2	876.2
52.5°	614.0	641.7	698.8	785.2
55°	560.0	586.2	627.9	712.7
57.5°	504.4	524.5	564.6	632.5
60°	450.5	469.0	501.4	556.9
62.5°	396.5	411.9	442.7	487.5
65°	348.6	361.0	384.1	422.7
67.5°	302.4	310.1	328.6	359.4
70°	257.6	263.8	279.2	303.9
72.5°	209.8	216.0	232.9	249.9
75°	169.7	171.2	183.6	197.5
77.5°	132.7	131.1	140.4	151.2
80°	91.0	95.6	103.4	108.0
82.5°	61.7	63.2	66.3	69.4
85°	33.9	35.5	35.5	40.1
87.5°	13.9	15.4	15.4	17.0
90°	6.9	4.9	2.8	0.8
92.5°	21.0	19.6	18.3	16.9
95°	45.0	43.3	41.6	39.9
97.5°	71.3	69.8	68.2	66.7
100°	101.5	100.1	98.8	97.4
102.5°	132.7	131.6	130.6	129.6
105°	166.4	165.9	165.4	164.9
107.5°	202.2	201.5	200.8	200.1
110°	237.0	235.9	234.9	233.9

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	273.8	272.7	271.7	270.7
115°	309.8	308.7	307.7	306.7
117.5°	346.9	345.5	344.2	342.8
120°	382.9	381.5	380.2	378.8
122.5°	416.9	415.2	413.5	411.8
125°	450.9	449.4	447.8	446.3
127.5°	485.6	483.7	481.9	480.0
130°	518.1	515.9	513.7	511.5
132.5°	551.8	550.1	548.4	546.7
135°	583.0	581.1	579.3	577.4
137.5°	615.7	614.2	612.6	611.1
140°	645.6	644.1	642.5	641.0
142.5°	676.3	674.8	673.2	671.7
145°	704.4	703.2	702.0	700.8
147.5°	731.5	730.0	728.4	726.9
150°	756.9	755.8	754.8	753.8
152.5°	780.6	779.5	778.5	777.5
155°	802.8	802.3	801.8	801.3
157.5°	823.0	822.7	822.3	822.0
160°	841.4	841.1	840.7	840.4
162.5°	857.3	857.3	857.3	857.3
165°	871.3	871.5	871.6	871.8
167.5°	883.4	883.9	884.4	884.9
170°	893.3	893.8	894.3	894.8
172.5°	900.2	900.7	901.2	901.7
175°	905.6	906.1	906.6	907.1
177.5°	908.7	909.2	909.7	910.2
180°	908.7	908.7	908.7	908.7

TEST NUMBER: P997995

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.04	19.99	19.88	20.85	21.91	16.53	17.48	17.37	18.34	19.41
	3H	19.86	20.71	20.71	21.58	22.67	17.88	18.74	18.74	19.60	20.70
	4H	20.03	20.83	20.90	21.71	22.81	18.35	19.15	19.22	20.03	21.13
	6H	20.08	20.82	20.96	21.70	22.82	18.66	19.40	19.54	20.28	21.40
	8H	20.06	20.77	20.95	21.66	22.78	18.75	19.45	19.64	20.35	21.47
	12H	20.03	20.70	20.92	21.59	22.73	18.79	19.46	19.69	20.35	21.50
4H	2H	19.09	19.90	19.97	20.77	21.87	16.99	17.79	17.86	18.67	19.77
	3H	20.08	20.75	20.96	21.65	22.77	18.46	19.13	19.34	20.03	21.15
	4H	20.36	20.97	21.26	21.87	23.02	19.00	19.60	19.89	20.51	21.65
	6H	20.50	21.02	21.41	21.94	23.09	19.38	19.90	20.29	20.83	21.98
	8H	20.50	20.99	21.41	21.90	23.07	19.49	19.98	20.41	20.90	22.06
	12H	20.46	20.90	21.40	21.84	23.01	19.55	19.99	20.49	20.93	22.10
8H	4H	20.38	20.87	21.29	21.78	22.95	19.15	19.63	20.06	20.55	21.71
	6H	20.56	20.96	21.50	21.92	23.08	19.58	19.99	20.52	20.95	22.11
	8H	20.59	20.95	21.54	21.90	23.08	19.73	20.09	20.68	21.04	22.22
	12H	20.58	20.89	21.53	21.84	23.07	19.83	20.15	20.78	21.09	22.32
12H	4H	20.34	20.78	21.27	21.72	22.88	19.12	19.56	20.06	20.50	21.67
	6H	20.54	20.90	21.49	21.85	23.03	19.58	19.94	20.53	20.89	22.07
	8H	20.57	20.89	21.53	21.83	23.06	19.75	20.06	20.70	21.00	22.23