

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998007

Luminaire Tested: SA2XXDIP-B1005D725UB40-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998007
REPORT IS A COMBINATION OF REPORTS P983744 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D725UB40-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6538.1 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998007

CATALOG NUMBER: SA2XXDIP-B1005D725UB40-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P998007

CATALOG NUMBER: SA2XXDIP-B1005D725UB40-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	97	92	88	83	90	85	81	78	73	70	67	61	59	57	51	49	48
2	88	80	73	67	81	74	68	63	63	58	54	53	50	46	44	41	39
3	80	69	61	55	73	64	57	52	55	49	45	46	42	39	38	35	32
4	73	61	53	46	67	57	49	43	49	43	38	41	36	33	34	30	28
5	67	54	46	39	61	50	43	37	43	37	32	37	32	28	30	27	24
6	61	48	40	34	56	45	37	32	39	33	28	33	28	24	27	24	21
7	57	44	35	29	52	41	33	28	35	29	25	30	25	21	25	21	18
8	52	40	31	26	48	37	30	25	32	26	22	27	22	19	23	19	16
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	15
10	46	33	26	21	42	31	24	20	27	21	17	23	19	15	20	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16681	16681	16681
5°	16757	15969	15880
10°	16645	15416	15191
15°	16409	14845	14486
20°	16112	14243	13816
25°	15821	13668	13209
30°	15411	13083	12607
35°	14996	12520	12166
40°	14558	12033	11726
45°	14144	11591	11345
50°	13695	11183	10966
55°	13227	10751	10583
60°	12651	10300	10179
65°	12055	9782	9714
70°	11377	9225	9213
75°	10511	8668	8741
80°	9141	8090	8252
85°	7769	7544	7828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14144 cd/sqm

TEST NUMBER: P998007

CATALOG NUMBER: SA2XXDIP-B1005D725UB40-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	1.5
10°-20°	286.5	4.4
20°-30°	434.1	6.6
30°-40°	528.7	8.1
40°-50°	568.8	8.7
50°-60°	552.4	8.4
60°-70°	482.4	7.4
70°-80°	371.3	5.7
80°-90°	251.2	3.8
90°-100°	227.2	3.5
100°-110°	302.2	4.6
110°-120°	385.4	5.9
120°-130°	444.1	6.8
130°-140°	466.1	7.1
140°-150°	441.4	6.8
150°-160°	367.5	5.6
160°-170°	243.7	3.7
170°-180°	85.2	1.3
0°-30°	820.6	12.6
0°-40°	1349.2	20.6
0°-60°	2470.4	37.8
0°-90°	3575.3	54.7
90°-120°	914.7	14.0
90°-150°	2266.3	34.7
90°-180°	2963.0	45.3
0°-180°	6538.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1054	1054	1054	1054	1054	
5°	1057	1052	1043	1052	1051	100
15°	1008	1011	1011	1025	1023	284
25°	916	927	941	959	964	421
35°	790	816	845	878	889	494
45°	648	689	742	790	805	500
55°	496	551	631	686	706	444
65°	339	414	504	567	586	337
75°	188	273	371	437	457	199
85°	55	150	247	312	333	58
90°	16	114	228	288	307	13
95°	52	131	224	282	299	54
105°	171	217	298	353	370	181
115°	310	331	398	443	458	306
125°	445	452	498	537	550	398
135°	573	581	598	630	639	443
145°	694	699	704	714	718	434
155°	793	795	798	802	799	365
165°	863	862	862	868	864	243
175°	898	896	894	899	895	85
180°	899	899	899	899	899	

TEST NUMBER: P998007

CATALOG NUMBER: SA2XXDIP-B1005D725UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1053.8	1053.8	1053.8	1053.8	1053.8
2.5°	1061.5	1056.9	1046.2	1053.8	1050.8
5°	1056.9	1052.3	1043.1	1052.3	1050.8
7.5°	1049.2	1046.2	1038.5	1049.2	1047.7
10°	1040.1	1037.0	1032.4	1044.7	1043.1
12.5°	1024.8	1026.3	1023.3	1035.5	1034.0
15°	1008.0	1011.1	1011.1	1024.8	1023.3
17.5°	986.6	992.7	997.3	1011.1	1011.1
20°	965.2	972.9	979.0	995.8	995.8
22.5°	942.3	951.5	960.7	977.5	980.5
25°	916.4	927.1	940.8	959.1	963.7
27.5°	885.8	902.6	917.9	940.8	943.9
30°	855.3	875.1	895.0	919.4	924.0
32.5°	821.7	844.6	869.0	898.0	907.2
35°	789.6	815.6	844.6	878.2	888.9
37.5°	754.5	783.5	820.1	856.8	867.5
40°	719.3	752.9	794.2	833.9	847.6
42.5°	685.7	719.3	768.2	812.5	826.3
45°	647.6	688.8	742.3	789.6	804.9
47.5°	610.9	655.2	716.3	765.2	782.0
50°	572.7	620.1	688.8	740.7	757.5
52.5°	536.1	586.5	659.8	713.2	731.6
55°	496.4	551.3	630.8	685.7	705.6
57.5°	458.2	519.3	598.7	658.3	678.1
60°	416.9	482.6	569.7	627.7	649.1
62.5°	380.3	449.0	536.1	598.7	618.5
65°	339.1	413.9	504.0	566.6	586.5
67.5°	302.4	380.3	471.9	534.5	555.9
70°	262.7	342.1	436.8	502.5	520.8
72.5°	226.0	308.5	404.7	468.9	491.8
75°	187.9	273.4	371.1	436.8	456.7
77.5°	151.2	239.8	339.1	404.7	426.1
80°	114.5	207.7	307.0	371.1	392.5
82.5°	84.0	175.6	276.4	340.6	360.4
85°	55.0	149.7	247.4	311.6	332.9
87.5°	33.6	125.2	223.0	285.6	305.5
90°	16.1	113.8	228.2	287.7	306.8
92.5°	30.4	117.5	211.4	271.7	290.0
95°	51.7	131.1	224.2	282.3	299.1
97.5°	76.7	149.3	240.8	297.4	315.7
100°	107.1	169.7	257.4	313.9	330.0
102.5°	137.5	192.4	277.9	333.6	349.7
105°	170.8	217.4	298.3	353.3	370.1
107.5°	205.7	245.4	321.8	374.5	387.5
110°	237.6	272.7	347.5	396.4	411.0



TEST NUMBER: P998007

CATALOG NUMBER: SA2XXDIP-B1005D725UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	274.0	303.0	372.5	419.1	434.4
115°	309.7	331.0	398.2	443.4	457.9
117.5°	343.9	362.1	422.4	466.1	479.0
120°	379.5	391.7	446.7	489.4	503.9
122.5°	412.2	421.2	474.0	513.0	525.2
125°	444.8	451.6	498.2	537.2	550.1
127.5°	478.2	485.0	523.2	558.3	569.8
130°	509.3	517.6	548.2	583.4	592.5
132.5°	544.2	550.2	573.9	605.3	615.2
135°	573.0	581.3	598.2	629.5	639.4
137.5°	606.4	613.2	622.4	650.7	658.3
140°	636.0	641.3	648.2	672.6	678.8
142.5°	666.3	671.7	674.0	693.0	697.7
145°	693.7	699.0	703.6	713.5	718.1
147.5°	719.5	726.3	729.4	732.4	733.9
150°	746.1	750.6	753.6	755.9	753.6
152.5°	769.6	774.1	777.9	781.0	777.9
155°	793.1	795.4	797.7	801.5	799.2
157.5°	813.6	815.1	816.6	821.9	818.2
160°	831.8	833.3	834.1	838.6	835.6
162.5°	848.5	848.5	849.3	854.6	850.8
165°	862.9	862.2	862.2	867.5	863.7
167.5°	875.8	873.6	873.6	878.9	875.1
170°	885.7	883.4	882.7	888.0	883.4
172.5°	892.5	890.3	889.5	894.8	890.3
175°	897.8	895.6	894.0	899.4	894.8
177.5°	900.9	898.6	897.1	901.6	897.1
180°	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P998007

CATALOG NUMBER: SA2XXDIP-B1005D725UB40-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.40	16.36	16.30	17.29	18.49	18.48	19.44	19.38	20.37	21.57
	3H	16.87	17.74	17.78	18.68	19.90	21.07	21.94	21.99	22.88	24.10
	4H	17.35	18.17	18.28	19.12	20.35	22.33	23.16	23.26	24.10	25.33
	6H	17.64	18.40	18.58	19.35	20.60	23.63	24.40	24.57	25.35	26.59
	8H	17.70	18.43	18.64	19.40	20.64	24.29	25.02	25.24	25.99	27.24
	12H	17.72	18.42	18.67	19.38	20.65	25.02	25.72	25.97	26.68	27.95
4H	2H	16.46	17.29	17.40	18.23	19.46	18.82	19.64	19.75	20.59	21.82
	3H	18.18	18.88	19.12	19.85	21.10	21.61	22.32	22.56	23.29	24.54
	4H	18.80	19.45	19.76	20.42	21.69	23.03	23.68	23.99	24.65	25.92
	6H	19.22	19.79	20.19	20.78	22.05	24.51	25.07	25.47	26.07	27.33
	8H	19.33	19.86	20.30	20.85	22.13	25.27	25.80	26.24	26.78	28.07
	12H	19.38	19.86	20.37	20.87	22.16	26.10	26.58	27.09	27.59	28.88
8H	4H	19.60	20.13	20.57	21.12	22.40	23.19	23.72	24.15	24.70	25.99
	6H	20.24	20.68	21.23	21.71	22.99	24.82	25.27	25.81	26.29	27.57
	8H	20.46	20.86	21.46	21.87	23.17	25.71	26.11	26.71	27.12	28.42
	12H	20.60	20.95	21.61	21.96	23.30	26.71	27.06	27.72	28.07	29.41
12H	4H	19.80	20.29	20.79	21.29	22.58	23.17	23.65	24.15	24.65	25.94
	6H	20.57	20.97	21.57	21.99	23.28	24.85	25.24	25.85	26.26	27.56
	8H	20.88	21.23	21.89	22.24	23.59	25.78	26.13	26.79	27.14	28.48