

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999174

Luminaire Tested: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999174
REPORT IS A COMBINATION OF REPORTS P984923 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6318.0 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	101	96	93	89	94	90	87	84	79	76	74	68	67	65	59	57	56
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48
3	84	75	68	62	79	71	64	59	62	57	53	54	50	47	47	44	42
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37
5	71	60	52	46	67	57	49	44	50	44	40	44	40	36	38	35	32
6	66	54	46	40	62	51	44	39	45	40	35	40	35	32	35	31	29
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	29	26
8	57	45	37	32	53	42	35	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27163	27163	27163	27163
5°	27228	28962	27333	23041
10°	26912	31616	27080	18997
15°	26259	33348	26624	16002
20°	25850	31312	25850	13908
25°	25027	26900	25140	12438
30°	23670	21146	24123	11266
35°	22469	14623	22845	10307
40°	21089	11040	21330	9543
45°	19387	9073	19704	8719
50°	17916	7962	17947	7981
55°	16238	6785	16342	7181
60°	14450	5667	14647	6268
65°	12848	4609	13082	5351
70°	11251	3616	11537	4317
75°	9443	2626	9812	3131
80°	7369	1663	7896	1858
85°	4845	837	5212	621

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 28078 cd/sqm

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.4	2.6
10°-20°	475.7	7.5
20°-30°	690.4	10.9
30°-40°	727.8	11.5
40°-50°	644.1	10.2
50°-60°	514.3	8.1
60°-70°	349.3	5.5
70°-80°	178.7	2.8
80°-90°	44.8	0.7
90°-100°	56.0	0.9
100°-110°	177.9	2.8
110°-120°	304.4	4.8
120°-130°	400.4	6.3
130°-140°	449.4	7.1
140°-150°	440.7	7.0
150°-160°	369.7	5.9
160°-170°	245.2	3.9
170°-180°	85.7	1.4
0°-30°	1329.6	21.0
0°-40°	2057.4	32.6
0°-60°	3215.7	50.9
0°-90°	3788.6	60.0
90°-120°	538.3	8.5
90°-150°	1828.9	28.9
90°-180°	2529.0	40.0
0°-180°	6318.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1716	1716	1716	1716	1716	
5°	1717	1916	1724	1525	1717	163
15°	1613	2356	1636	1130	1613	456
25°	1450	1963	1456	908	1450	663
35°	1183	1068	1203	753	1183	740
45°	888	644	902	619	888	689
55°	609	452	613	479	609	544
65°	361	278	368	323	361	359
75°	169	137	175	164	169	181
85°	34	36	37	26	34	40
90°	1	26	1	26	1	5
95°	40	47	40	47	40	44
105°	164	170	164	170	164	173
115°	305	305	305	305	305	302
125°	444	446	444	446	444	397
135°	575	582	575	582	575	444
145°	698	706	698	706	698	436
155°	798	804	798	804	798	367
165°	868	869	868	869	868	245
175°	903	900	903	900	903	86
180°	905	905	905	905	905	

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1725.2	1729.2	1735.8	1737.1	1750.3	1760.8	1772.7	1772.7	1776.7	1775.3	1764.8
5°	1717.3	1729.2	1746.3	1760.8	1784.6	1795.1	1811.0	1822.8	1833.4	1841.3	1840.0
7.5°	1704.1	1725.2	1750.3	1778.0	1809.6	1828.1	1850.5	1871.6	1886.1	1899.3	1908.6
10°	1681.7	1717.3	1751.6	1788.5	1829.4	1854.5	1880.9	1908.6	1931.0	1956.0	1979.8
12.5°	1651.4	1702.8	1745.0	1793.8	1843.9	1871.6	1913.8	1934.9	1978.5	2041.8	2058.9
15°	1613.1	1683.0	1722.6	1784.6	1850.5	1873.0	1931.0	1965.3	2055.0	2094.5	2142.0
17.5°	1577.5	1655.3	1708.1	1779.3	1843.9	1887.5	1944.2	2014.1	2089.3	2146.0	2198.7
20°	1548.5	1623.7	1687.0	1766.1	1847.9	1903.3	1962.6	2047.1	2128.8	2186.9	2227.8
22.5°	1482.5	1578.8	1652.7	1741.1	1840.0	1916.5	1973.2	2065.5	2153.9	2189.5	2225.1
25°	1449.6	1532.7	1618.4	1718.6	1834.7	1925.7	1974.5	2077.4	2155.2	2168.4	2176.3
27.5°	1388.9	1482.5	1582.8	1697.5	1833.4	1909.9	1971.9	2065.5	2127.5	2118.3	2094.5
30°	1313.7	1428.5	1539.2	1663.2	1814.9	1898.0	1956.0	2041.8	2073.4	2026.0	1983.7
32.5°	1258.3	1366.5	1489.1	1632.9	1793.8	1873.0	1929.7	1996.9	2003.5	1917.8	1846.6
35°	1183.1	1303.2	1441.6	1593.3	1758.2	1829.4	1882.2	1923.1	1891.4	1771.4	1687.0
37.5°	1115.9	1234.6	1382.3	1536.6	1709.4	1779.3	1821.5	1828.1	1750.3	1644.8	1520.8
40°	1042.0	1164.7	1319.0	1481.2	1655.3	1716.0	1742.4	1722.6	1610.5	1487.8	1344.0
42.5°	968.1	1089.5	1255.7	1421.9	1586.7	1638.2	1648.7	1594.6	1457.5	1313.7	1147.5
45°	887.7	1014.3	1180.5	1348.0	1507.6	1536.6	1537.9	1460.1	1297.9	1147.5	993.2
47.5°	821.7	939.1	1104.0	1271.5	1406.0	1425.8	1417.9	1328.2	1151.5	982.6	848.1
50°	749.2	861.3	1024.8	1189.7	1304.5	1309.7	1290.0	1162.0	989.2	834.9	728.1
52.5°	671.4	784.8	935.2	1093.4	1196.3	1188.4	1150.1	1013.0	850.7	722.8	641.0
55°	609.4	709.6	850.7	1005.1	1077.6	1055.2	1013.0	873.2	745.2	637.1	565.8
57.5°	540.8	629.2	767.6	902.2	944.4	923.3	881.1	750.5	631.8	550.0	502.5
60°	476.2	556.6	678.0	790.1	823.0	800.6	751.8	634.4	548.7	480.1	444.5
62.5°	416.8	486.7	588.3	691.1	704.3	681.9	639.7	544.7	470.9	416.8	390.4
65°	361.4	427.3	509.1	586.9	598.8	575.1	531.5	463.0	401.0	366.7	341.6
67.5°	307.3	360.1	432.6	489.3	495.9	473.5	437.9	382.5	344.3	307.3	288.9
70°	259.8	299.4	356.1	402.3	404.9	383.8	365.4	315.2	286.2	259.8	245.3
72.5°	213.7	241.4	284.9	319.2	320.5	307.3	290.2	258.5	233.5	215.0	200.5
75°	168.8	192.6	219.0	249.3	248.0	237.4	224.2	204.4	183.3	171.5	164.9
77.5°	129.3	143.8	164.9	184.7	184.7	179.4	171.5	157.0	143.8	131.9	125.3
80°	92.3	101.6	118.7	125.3	127.9	126.6	120.0	109.5	104.2	95.0	92.3
82.5°	59.4	65.9	73.9	80.5	84.4	81.8	80.5	75.2	67.3	64.6	62.0
85°	34.3	36.9	40.9	44.8	46.2	44.8	47.5	43.5	39.6	39.6	38.3
87.5°	14.5	15.8	18.5	18.5	19.8	19.8	18.5	19.8	19.8	18.5	17.1
90°	0.8	2.8	4.8	6.9	8.9	9.9	11.8	15.5	19.2	23.0	26.7
92.5°	16.8	18.2	19.5	20.9	22.2	22.9	23.0	23.2	23.3	23.5	23.7
95°	39.7	41.4	43.1	44.8	46.5	47.3	47.5	47.8	48.2	48.5	48.9
97.5°	66.4	67.9	69.5	71.0	72.5	73.3	73.6	74.3	75.0	75.6	76.3
100°	97.0	98.4	99.7	101.1	102.4	103.1	103.4	103.9	104.4	104.9	105.4
102.5°	129.0	130.0	131.0	132.1	133.1	133.6	133.9	134.6	135.3	136.0	136.7
105°	164.1	164.6	165.1	165.6	166.1	166.4	166.6	166.9	167.3	167.6	168.0
107.5°	199.3	200.0	200.6	201.3	202.0	202.3	202.3	202.3	202.3	202.3	202.3
110°	232.9	233.9	234.9	235.9	236.9	237.4	237.4	237.4	237.4	237.4	237.4

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	269.5	270.5	271.5	272.6	273.6	274.1	274.0	273.8	273.7	273.5	273.3
115°	305.4	306.4	307.4	308.5	309.5	310.0	309.8	309.5	309.1	308.8	308.4
117.5°	341.3	342.7	344.0	345.4	346.7	347.4	347.0	346.1	345.3	344.4	343.6
120°	377.2	378.6	379.9	381.3	382.6	383.3	382.6	381.3	379.9	378.6	377.2
122.5°	410.0	411.7	413.4	415.1	416.8	417.6	417.2	416.3	415.5	414.6	413.8
125°	444.3	445.8	447.4	448.9	450.4	451.2	450.9	450.4	449.9	449.4	448.9
127.5°	477.9	479.8	481.6	483.5	485.4	486.3	486.0	485.3	484.6	484.0	483.3
130°	509.2	511.4	513.6	515.9	518.1	519.2	519.0	518.7	518.3	518.0	517.6
132.5°	544.4	546.1	547.8	549.5	551.2	552.0	552.1	552.3	552.4	552.6	552.8
135°	574.9	576.8	578.6	580.5	582.4	583.3	583.5	583.8	584.1	584.5	584.8
137.5°	608.5	610.0	611.6	613.1	614.6	615.4	615.6	615.9	616.2	616.6	616.9
140°	638.3	639.8	641.3	642.8	644.3	645.1	645.5	646.4	647.3	648.1	649.0
142.5°	668.8	670.3	671.9	673.4	674.9	675.7	676.0	676.5	677.0	677.5	678.0
145°	697.8	699.0	700.2	701.4	702.6	703.2	703.7	704.7	705.7	706.7	707.7
147.5°	723.8	725.3	726.8	728.3	729.8	730.6	730.9	731.6	732.3	733.0	733.7
150°	750.5	751.5	752.5	753.6	754.6	755.1	755.4	756.1	756.8	757.4	758.1
152.5°	774.2	775.2	776.2	777.2	778.2	778.7	779.1	780.0	780.9	781.7	782.6
155°	797.8	798.3	798.8	799.3	799.8	800.1	800.4	800.9	801.4	801.9	802.4
157.5°	818.4	818.8	819.1	819.5	819.8	820.0	820.2	820.5	820.8	821.2	821.5
160°	836.8	837.1	837.5	837.8	838.1	838.3	838.4	838.6	838.7	838.9	839.1
162.5°	853.6	853.6	853.6	853.6	853.6	853.6	853.7	853.8	854.0	854.1	854.3
165°	868.1	867.9	867.7	867.6	867.4	867.3	867.3	867.3	867.3	867.3	867.3
167.5°	881.1	880.6	880.1	879.6	879.1	878.8	878.8	878.8	878.8	878.8	878.8
170°	891.0	890.5	890.0	889.5	889.0	888.7	888.6	888.4	888.3	888.1	887.9
172.5°	897.8	897.3	896.8	896.3	895.8	895.6	895.5	895.3	895.2	895.0	894.8
175°	903.2	902.7	902.2	901.7	901.2	900.9	900.7	900.4	900.1	899.7	899.4
177.5°	906.2	905.7	905.2	904.7	904.2	904.0	903.8	903.5	903.1	902.8	902.4
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1783.3	1784.6	1787.2	1800.4	1807.0	1808.3	1803.0	1814.9	1818.9	1814.9	1812.3
5°	1867.7	1875.6	1891.4	1908.6	1907.2	1908.6	1916.5	1924.4	1927.0	1916.5	1920.4
7.5°	1941.5	1957.4	1974.5	2000.9	2000.9	2014.1	2019.4	2026.0	2041.8	2033.9	2031.2
10°	2026.0	2047.1	2078.7	2120.9	2122.2	2135.4	2148.6	2169.7	2176.3	2171.0	2173.7
12.5°	2131.5	2172.4	2175.0	2221.2	2242.3	2244.9	2266.0	2262.0	2275.2	2275.2	2297.7
15°	2177.6	2240.9	2276.6	2321.4	2334.6	2318.8	2335.9	2354.4	2355.7	2355.7	2354.4
17.5°	2260.7	2285.8	2321.4	2345.1	2350.4	2350.4	2351.7	2359.7	2354.4	2343.8	2351.7
20°	2277.9	2288.4	2301.6	2299.0	2301.6	2288.4	2275.2	2262.0	2263.4	2256.8	2276.6
22.5°	2246.2	2243.6	2213.2	2193.5	2193.5	2167.1	2142.0	2130.2	2118.3	2122.2	2128.8
25°	2167.1	2126.2	2089.3	2060.2	2053.7	2011.4	1977.1	1966.6	1946.8	1962.6	1965.3
27.5°	2040.5	1994.3	1934.9	1909.9	1875.6	1858.4	1834.7	1803.0	1762.2	1785.9	1781.9
30°	1904.6	1836.0	1787.2	1726.5	1672.5	1668.5	1623.7	1570.9	1549.8	1549.8	1561.7
32.5°	1752.9	1661.9	1590.7	1505.0	1452.2	1429.8	1375.7	1322.9	1334.8	1295.2	1309.7
35°	1576.2	1456.2	1366.5	1283.4	1243.8	1217.4	1147.5	1118.5	1086.8	1068.4	1102.7
37.5°	1407.4	1268.9	1154.1	1063.1	1048.6	1001.1	953.6	935.2	916.7	924.6	923.3
40°	1201.6	1078.9	976.0	904.8	879.8	857.3	825.7	803.3	791.4	798.0	799.3
42.5°	1015.6	912.7	836.2	786.1	765.0	749.2	733.4	714.9	710.9	710.9	716.2
45°	871.8	787.4	736.0	695.1	683.2	671.4	659.5	651.6	648.9	643.7	647.6
47.5°	757.1	689.8	658.2	627.8	614.6	612.0	601.5	597.5	592.2	590.9	592.2
50°	660.8	618.6	589.6	572.4	563.2	559.2	554.0	546.1	543.4	550.0	547.4
52.5°	593.5	554.0	538.1	521.0	515.7	510.4	502.5	503.8	502.5	499.9	499.9
55°	526.3	501.2	485.4	472.2	470.9	465.6	459.0	456.4	455.0	452.4	456.4
57.5°	472.2	452.4	437.9	426.0	420.8	420.8	414.2	408.9	408.9	407.6	408.9
60°	418.1	398.3	389.1	377.2	373.3	372.0	368.0	365.4	361.4	361.4	361.4
62.5°	368.0	352.2	341.6	331.1	332.4	325.8	320.5	317.9	317.9	319.2	319.2
65°	320.5	310.0	296.8	287.5	284.9	283.6	280.9	279.6	275.7	278.3	278.3
67.5°	277.0	262.5	254.6	250.6	246.6	245.3	242.7	240.1	238.7	237.4	240.1
70°	233.5	221.6	215.0	212.4	208.4	207.1	205.8	201.8	203.1	204.4	205.8
72.5°	193.9	183.3	182.0	174.1	174.1	174.1	168.8	171.5	170.1	167.5	170.1
75°	153.0	147.7	145.1	141.1	142.4	141.1	139.8	135.9	135.9	137.2	138.5
77.5°	121.3	116.1	114.8	110.8	108.2	110.8	108.2	106.8	106.8	108.2	108.2
80°	89.7	87.1	83.1	83.1	83.1	81.8	81.8	81.8	80.5	79.1	80.5
82.5°	59.4	59.4	58.0	56.7	58.0	55.4	56.7	56.7	56.7	56.7	56.7
85°	38.3	36.9	36.9	35.6	35.6	35.6	36.9	34.3	34.3	35.6	35.6
87.5°	17.1	17.1	17.1	18.5	17.1	17.1	17.1	18.5	17.1	17.1	17.1
90°	26.4	26.0	25.7	25.4	25.2	25.3	25.5	25.6	25.8	26.0	25.8
92.5°	23.9	24.0	24.2	24.3	24.4	24.4	24.4	24.4	24.4	24.4	24.4
95°	48.9	48.9	48.9	48.9	48.9	48.7	48.4	48.0	47.7	47.3	47.7
97.5°	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3
100°	105.4	105.4	105.4	105.4	105.4	105.3	105.1	105.0	104.8	104.6	104.8
102.5°	136.9	137.0	137.2	137.3	137.4	137.3	137.2	137.0	136.9	136.7	136.9
105°	168.3	168.7	169.0	169.3	169.5	169.5	169.5	169.5	169.5	169.5	169.5
107.5°	202.5	202.7	202.8	203.0	203.1	202.7	201.8	201.0	200.1	199.3	200.1
110°	237.4	237.4	237.4	237.4	237.4	237.2	236.7	236.2	235.7	235.2	235.7

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	272.8	272.3	271.8	271.3	271.0	270.8	270.5	270.2	269.8	269.5	269.8
115°	308.2	308.1	307.9	307.8	307.7	307.4	306.9	306.4	305.9	305.4	305.9
117.5°	343.1	342.6	342.1	341.6	341.3	341.0	340.5	340.0	339.5	339.0	339.5
120°	377.2	377.2	377.2	377.2	377.2	376.9	376.4	375.9	375.4	374.9	375.4
122.5°	413.3	412.8	412.3	411.8	411.5	411.3	411.0	410.7	410.3	410.0	410.3
125°	448.4	447.9	447.4	446.9	446.6	446.5	446.4	446.2	446.1	445.9	446.1
127.5°	482.6	481.9	481.2	480.5	480.2	479.9	479.4	478.9	478.4	477.9	478.4
130°	517.3	516.9	516.6	516.3	516.1	515.8	515.1	514.4	513.8	513.1	513.8
132.5°	551.9	551.1	550.2	549.3	548.9	548.6	548.1	547.6	547.1	546.6	547.1
135°	584.6	584.5	584.3	584.2	584.1	583.8	583.3	582.8	582.3	581.8	582.3
137.5°	616.7	616.5	616.4	616.2	616.1	615.8	615.1	614.4	613.8	613.1	613.8
140°	649.0	649.0	649.0	649.0	649.0	648.7	648.0	647.3	646.6	645.9	646.6
142.5°	678.2	678.3	678.5	678.6	678.7	678.4	677.7	677.0	676.4	675.7	676.4
145°	707.9	708.1	708.2	708.4	708.5	708.2	707.5	706.8	706.2	705.5	706.2
147.5°	734.0	734.4	734.7	735.0	735.2	734.9	734.2	733.5	732.9	732.2	732.9
150°	758.6	759.1	759.6	760.1	760.4	760.1	759.6	759.1	758.6	758.1	758.6
152.5°	783.3	783.9	784.6	785.3	785.6	785.3	784.6	783.9	783.3	782.6	783.3
155°	803.2	804.1	804.9	805.8	806.2	805.9	805.4	804.9	804.4	803.9	804.4
157.5°	822.7	823.9	825.0	826.2	826.8	826.4	825.5	824.7	823.8	823.0	823.8
160°	840.1	841.1	842.1	843.1	843.6	843.3	842.6	841.9	841.3	840.6	841.3
162.5°	855.5	856.7	857.9	859.1	859.7	859.3	858.4	857.6	856.7	855.9	856.7
165°	868.5	869.7	870.9	872.1	872.7	872.3	871.4	870.5	869.7	868.8	869.7
167.5°	880.0	881.2	882.3	883.5	884.1	883.7	882.8	882.0	881.1	880.3	881.1
170°	889.1	890.3	891.5	892.7	893.3	892.8	891.8	890.7	889.7	888.7	889.7
172.5°	896.0	897.2	898.3	899.5	900.1	899.6	898.6	897.6	896.6	895.6	896.6
175°	900.6	901.8	902.9	904.1	904.7	904.2	903.2	902.1	901.1	900.1	901.1
177.5°	903.4	904.4	905.5	906.5	907.0	906.5	905.5	904.4	903.4	902.4	903.4
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1818.9	1809.6	1801.7	1803.0	1809.6	1804.4	1791.2	1774.0	1767.4	1759.5	1767.4
5°	1928.3	1920.4	1904.6	1905.9	1902.0	1896.7	1875.6	1849.2	1849.2	1828.1	1825.5
7.5°	2036.5	2024.6	2014.1	2011.4	1996.9	1986.4	1967.9	1931.0	1916.5	1891.4	1876.9
10°	2157.8	2148.6	2136.7	2122.2	2114.3	2095.9	2065.5	2011.4	1985.1	1950.8	1925.7
12.5°	2280.5	2279.2	2252.8	2223.8	2222.5	2193.5	2172.4	2099.8	2064.2	2018.0	1958.7
15°	2358.3	2351.7	2337.2	2322.7	2326.7	2295.0	2247.5	2161.8	2138.1	2082.7	2019.4
17.5°	2357.0	2357.0	2353.1	2350.4	2346.5	2337.2	2310.9	2254.1	2215.9	2146.0	2086.6
20°	2281.8	2299.0	2302.9	2301.6	2314.8	2321.4	2320.1	2284.5	2254.1	2192.1	2131.5
22.5°	2131.5	2171.0	2188.2	2198.7	2226.4	2240.9	2275.2	2262.0	2254.1	2208.0	2156.5
25°	1991.7	2004.8	2056.3	2058.9	2097.2	2132.8	2167.1	2189.5	2218.5	2201.4	2157.8
27.5°	1811.0	1841.3	1878.2	1905.9	1913.8	1986.4	2043.1	2085.3	2151.3	2156.5	2142.0
30°	1606.5	1621.0	1681.7	1718.6	1760.8	1813.6	1895.4	1967.9	2027.3	2081.3	2099.8
32.5°	1357.2	1416.6	1452.2	1497.0	1534.0	1627.6	1727.9	1821.5	1890.1	1981.1	2020.7
35°	1129.0	1175.2	1235.9	1254.3	1321.6	1400.8	1531.3	1651.4	1755.6	1847.9	1928.3
37.5°	940.4	977.4	1042.0	1071.0	1110.6	1212.1	1321.6	1470.7	1596.0	1709.4	1809.6
40°	811.2	838.9	887.7	896.9	929.9	1022.2	1110.6	1250.4	1416.6	1569.6	1679.1
42.5°	722.8	736.0	769.0	780.8	801.9	863.9	943.1	1075.0	1229.3	1387.6	1541.9
45°	659.5	668.7	688.5	699.1	725.4	753.1	817.8	923.3	1044.6	1204.2	1370.4
47.5°	602.8	614.6	622.6	629.2	643.7	674.0	716.2	794.0	910.1	1056.5	1217.4
50°	555.3	559.2	573.8	575.1	584.3	604.1	643.7	691.1	783.5	902.2	1057.8
52.5°	507.8	511.8	521.0	530.2	534.2	550.0	576.4	616.0	684.6	778.2	916.7
55°	460.3	465.6	474.8	481.4	485.4	498.6	514.4	552.7	606.7	672.7	786.1
57.5°	412.8	424.7	427.3	431.3	437.9	452.4	466.9	489.3	531.5	592.2	675.3
60°	368.0	372.0	381.2	385.1	391.7	399.7	418.1	435.3	465.6	513.1	588.3
62.5°	321.8	331.1	335.0	339.0	344.3	353.5	365.4	383.8	410.2	448.5	507.8
65°	282.3	283.6	291.5	296.8	302.0	308.6	320.5	337.7	353.5	389.1	432.6
67.5°	244.0	246.6	249.3	254.6	261.2	267.8	278.3	287.5	307.3	331.1	365.4
70°	207.1	207.1	213.7	217.6	216.3	224.2	232.1	242.7	257.2	279.6	307.3
72.5°	174.1	172.8	178.1	179.4	182.0	187.3	192.6	203.1	211.0	228.2	249.3
75°	138.5	141.1	143.8	143.8	147.7	151.7	157.0	162.2	171.5	182.0	197.8
77.5°	109.5	109.5	112.1	113.4	117.4	116.1	121.3	126.6	133.2	142.4	154.3
80°	80.5	83.1	83.1	83.1	84.4	85.7	91.0	95.0	98.9	105.5	110.8
82.5°	56.7	56.7	59.4	59.4	59.4	62.0	62.0	63.3	65.9	69.9	73.9
85°	35.6	35.6	35.6	36.9	35.6	36.9	39.6	38.3	39.6	42.2	42.2
87.5°	17.1	17.1	17.1	17.1	17.1	18.5	17.1	18.5	19.8	19.8	19.8
90°	25.6	25.5	25.3	25.2	25.4	25.7	26.0	26.4	26.7	23.0	19.2
92.5°	24.4	24.4	24.4	24.4	24.3	24.2	24.0	23.9	23.7	23.5	23.3
95°	48.0	48.4	48.7	48.9	48.9	48.9	48.9	48.9	48.9	48.5	48.2
97.5°	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	75.6	75.0
100°	105.0	105.1	105.3	105.4	105.4	105.4	105.4	105.4	105.4	104.9	104.4
102.5°	137.0	137.2	137.3	137.4	137.3	137.2	137.0	136.9	136.7	136.0	135.3
105°	169.5	169.5	169.5	169.5	169.3	169.0	168.7	168.3	168.0	167.6	167.3
107.5°	201.0	201.8	202.7	203.1	203.0	202.8	202.7	202.5	202.3	202.3	202.3
110°	236.2	236.7	237.2	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	270.2	270.5	270.8	271.0	271.3	271.8	272.3	272.8	273.3	273.5	273.7
115°	306.4	306.9	307.4	307.7	307.8	307.9	308.1	308.2	308.4	308.8	309.1
117.5°	340.0	340.5	341.0	341.3	341.6	342.1	342.6	343.1	343.6	344.4	345.3
120°	375.9	376.4	376.9	377.2	377.2	377.2	377.2	377.2	377.2	378.6	379.9
122.5°	410.7	411.0	411.3	411.5	411.8	412.3	412.8	413.3	413.8	414.6	415.5
125°	446.2	446.4	446.5	446.6	446.9	447.4	447.9	448.4	448.9	449.4	449.9
127.5°	478.9	479.4	479.9	480.2	480.5	481.2	481.9	482.6	483.3	484.0	484.6
130°	514.4	515.1	515.8	516.1	516.3	516.6	516.9	517.3	517.6	518.0	518.3
132.5°	547.6	548.1	548.6	548.9	549.3	550.2	551.1	551.9	552.8	552.6	552.4
135°	582.8	583.3	583.8	584.1	584.2	584.3	584.5	584.6	584.8	584.5	584.1
137.5°	614.4	615.1	615.8	616.1	616.2	616.4	616.5	616.7	616.9	616.6	616.2
140°	647.3	648.0	648.7	649.0	649.0	649.0	649.0	649.0	649.0	648.1	647.3
142.5°	677.0	677.7	678.4	678.7	678.6	678.5	678.3	678.2	678.0	677.5	677.0
145°	706.8	707.5	708.2	708.5	708.4	708.2	708.1	707.9	707.7	706.7	705.7
147.5°	733.5	734.2	734.9	735.2	735.0	734.7	734.4	734.0	733.7	733.0	732.3
150°	759.1	759.6	760.1	760.4	760.1	759.6	759.1	758.6	758.1	757.4	756.8
152.5°	783.9	784.6	785.3	785.6	785.3	784.6	783.9	783.3	782.6	781.7	780.9
155°	804.9	805.4	805.9	806.2	805.8	804.9	804.1	803.2	802.4	801.9	801.4
157.5°	824.7	825.5	826.4	826.8	826.2	825.0	823.9	822.7	821.5	821.2	820.8
160°	841.9	842.6	843.3	843.6	843.1	842.1	841.1	840.1	839.1	838.9	838.7
162.5°	857.6	858.4	859.3	859.7	859.1	857.9	856.7	855.5	854.3	854.1	854.0
165°	870.5	871.4	872.3	872.7	872.1	870.9	869.7	868.5	867.3	867.3	867.3
167.5°	882.0	882.8	883.7	884.1	883.5	882.3	881.2	880.0	878.8	878.8	878.8
170°	890.7	891.8	892.8	893.3	892.7	891.5	890.3	889.1	887.9	888.1	888.3
172.5°	897.6	898.6	899.6	900.1	899.5	898.3	897.2	896.0	894.8	895.0	895.2
175°	902.1	903.2	904.2	904.7	904.1	902.9	901.8	900.6	899.4	899.7	900.1
177.5°	904.4	905.5	906.5	907.0	906.5	905.5	904.4	903.4	902.4	902.8	903.1
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1760.8	1754.2	1750.3	1752.9	1745.0	1725.2	1725.2	1731.8	1723.9	1716.0	1704.1
5°	1809.6	1796.4	1788.5	1787.2	1768.8	1737.1	1730.5	1723.9	1706.8	1688.3	1668.5
7.5°	1857.1	1833.4	1820.2	1811.0	1784.6	1743.7	1726.5	1712.0	1684.3	1656.6	1631.6
10°	1896.7	1862.4	1846.6	1832.1	1797.8	1746.3	1718.6	1692.2	1656.6	1621.0	1589.4
12.5°	1928.3	1888.8	1869.0	1847.9	1805.7	1738.4	1704.1	1661.9	1626.3	1578.8	1547.2
15°	1981.1	1899.3	1880.9	1861.1	1817.6	1725.2	1683.0	1635.5	1586.7	1523.4	1489.1
17.5°	2023.3	1913.8	1912.5	1870.3	1813.6	1719.9	1655.3	1593.3	1540.6	1477.3	1423.2
20°	2048.4	1936.3	1915.2	1871.6	1800.4	1684.3	1617.1	1548.5	1491.8	1415.3	1361.2
22.5°	2069.5	1967.9	1912.5	1859.8	1772.7	1672.5	1573.5	1508.9	1431.1	1348.0	1296.6
25°	2077.4	1974.5	1916.5	1855.8	1752.9	1638.2	1526.1	1456.2	1369.1	1293.9	1224.0
27.5°	2078.7	1973.2	1902.0	1838.7	1725.2	1593.3	1478.6	1404.7	1308.4	1221.4	1151.5
30°	2065.5	1958.7	1894.1	1825.5	1698.8	1552.4	1420.5	1338.8	1235.9	1148.8	1076.3
32.5°	2026.0	1929.7	1876.9	1801.7	1664.6	1495.7	1365.1	1274.1	1166.0	1080.2	1010.3
35°	1960.0	1894.1	1836.0	1766.1	1619.7	1443.0	1309.7	1202.9	1093.4	1011.7	945.7
37.5°	1878.2	1842.6	1788.5	1719.9	1568.3	1395.5	1247.8	1129.0	1019.6	940.4	875.8
40°	1767.4	1776.7	1723.9	1661.9	1507.6	1330.8	1167.3	1053.9	951.0	877.1	813.8
42.5°	1647.4	1685.7	1655.3	1596.0	1440.3	1259.6	1107.9	982.6	882.4	805.9	753.1
45°	1518.1	1584.1	1565.6	1522.1	1370.4	1184.4	1023.5	902.2	813.8	739.9	693.8
47.5°	1377.0	1470.7	1470.7	1439.0	1292.6	1109.3	951.0	827.0	739.9	687.2	642.3
50°	1233.2	1338.8	1355.9	1334.8	1205.5	1023.5	862.6	750.5	675.3	623.9	590.9
52.5°	1082.9	1205.5	1237.2	1226.7	1113.2	941.8	790.1	680.6	612.0	567.2	538.1
55°	939.1	1081.6	1115.9	1119.8	1014.3	852.1	709.6	613.3	547.4	517.0	492.0
57.5°	803.3	940.4	978.7	985.3	914.1	770.3	634.4	550.0	490.7	465.6	445.8
60°	687.2	801.9	852.1	866.6	804.6	675.3	564.5	482.7	437.9	414.2	395.7
62.5°	592.2	684.6	737.3	741.3	713.6	592.2	492.0	423.4	385.1	364.0	354.8
65°	499.9	583.0	614.6	630.5	608.0	513.1	424.7	368.0	337.7	319.2	310.0
67.5°	426.0	478.8	505.2	526.3	503.8	432.6	361.4	315.2	292.8	274.3	269.1
70°	349.5	393.1	412.8	433.9	414.2	360.1	308.6	266.4	246.6	232.1	225.5
72.5°	279.6	313.9	332.4	345.6	333.7	288.9	246.6	217.6	203.1	192.6	188.6
75°	221.6	245.3	255.9	265.1	259.8	225.5	199.2	175.4	162.2	153.0	150.4
77.5°	168.8	186.0	197.8	200.5	193.9	171.5	149.0	134.5	124.0	118.7	116.1
80°	120.0	130.6	137.2	141.1	134.5	125.3	109.5	98.9	89.7	83.1	81.8
82.5°	80.5	85.7	91.0	89.7	87.1	79.1	69.9	64.6	60.7	55.4	55.4
85°	46.2	47.5	50.1	51.4	50.1	44.8	39.6	36.9	34.3	30.3	30.3
87.5°	19.8	21.1	21.1	22.4	19.8	19.8	17.1	14.5	14.5	13.2	11.9
90°	15.5	11.8	9.9	8.9	6.9	4.8	2.8	0.8	2.8	4.8	6.9
92.5°	23.2	23.0	22.9	22.2	20.9	19.5	18.2	16.8	18.2	19.5	20.9
95°	47.8	47.5	47.3	46.5	44.8	43.1	41.4	39.7	41.4	43.1	44.8
97.5°	74.3	73.6	73.3	72.5	71.0	69.5	67.9	66.4	67.9	69.5	71.0
100°	103.9	103.4	103.1	102.4	101.1	99.7	98.4	97.0	98.4	99.7	101.1
102.5°	134.6	133.9	133.6	133.1	132.1	131.0	130.0	129.0	130.0	131.0	132.1
105°	166.9	166.6	166.4	166.1	165.6	165.1	164.6	164.1	164.6	165.1	165.6
107.5°	202.3	202.3	202.3	202.0	201.3	200.6	200.0	199.3	200.0	200.6	201.3
110°	237.4	237.4	237.4	236.9	235.9	234.9	233.9	232.9	233.9	234.9	235.9

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	273.8	274.0	274.1	273.6	272.6	271.5	270.5	269.5	270.5	271.5	272.6
115°	309.5	309.8	310.0	309.5	308.5	307.4	306.4	305.4	306.4	307.4	308.5
117.5°	346.1	347.0	347.4	346.7	345.4	344.0	342.7	341.3	342.7	344.0	345.4
120°	381.3	382.6	383.3	382.6	381.3	379.9	378.6	377.2	378.6	379.9	381.3
122.5°	416.3	417.2	417.6	416.8	415.1	413.4	411.7	410.0	411.7	413.4	415.1
125°	450.4	450.9	451.2	450.4	448.9	447.4	445.8	444.3	445.8	447.4	448.9
127.5°	485.3	486.0	486.3	485.4	483.5	481.6	479.8	477.9	479.8	481.6	483.5
130°	518.7	519.0	519.2	518.1	515.9	513.6	511.4	509.2	511.4	513.6	515.9
132.5°	552.3	552.1	552.0	551.2	549.5	547.8	546.1	544.4	546.1	547.8	549.5
135°	583.8	583.5	583.3	582.4	580.5	578.6	576.8	574.9	576.8	578.6	580.5
137.5°	615.9	615.6	615.4	614.6	613.1	611.6	610.0	608.5	610.0	611.6	613.1
140°	646.4	645.5	645.1	644.3	642.8	641.3	639.8	638.3	639.8	641.3	642.8
142.5°	676.5	676.0	675.7	674.9	673.4	671.9	670.3	668.8	670.3	671.9	673.4
145°	704.7	703.7	703.2	702.6	701.4	700.2	699.0	697.8	699.0	700.2	701.4
147.5°	731.6	730.9	730.6	729.8	728.3	726.8	725.3	723.8	725.3	726.8	728.3
150°	756.1	755.4	755.1	754.6	753.6	752.5	751.5	750.5	751.5	752.5	753.6
152.5°	780.0	779.1	778.7	778.2	777.2	776.2	775.2	774.2	775.2	776.2	777.2
155°	800.9	800.4	800.1	799.8	799.3	798.8	798.3	797.8	798.3	798.8	799.3
157.5°	820.5	820.2	820.0	819.8	819.5	819.1	818.8	818.4	818.8	819.1	819.5
160°	838.6	838.4	838.3	838.1	837.8	837.5	837.1	836.8	837.1	837.5	837.8
162.5°	853.8	853.7	853.6	853.6	853.6	853.6	853.6	853.6	853.6	853.6	853.6
165°	867.3	867.3	867.3	867.4	867.6	867.7	867.9	868.1	867.9	867.7	867.6
167.5°	878.8	878.8	878.8	879.1	879.6	880.1	880.6	881.1	880.6	880.1	879.6
170°	888.4	888.6	888.7	889.0	889.5	890.0	890.5	891.0	890.5	890.0	889.5
172.5°	895.3	895.5	895.6	895.8	896.3	896.8	897.3	897.8	897.3	896.8	896.3
175°	900.4	900.7	900.9	901.2	901.7	902.2	902.7	903.2	902.7	902.2	901.7
177.5°	903.5	903.8	904.0	904.2	904.7	905.2	905.7	906.2	905.7	905.2	904.7
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1697.5	1704.1	1702.8	1689.6	1675.1	1663.2	1640.8	1643.4	1635.5	1636.9	1644.8
5°	1655.3	1655.3	1650.0	1631.6	1607.8	1594.6	1569.6	1563.0	1547.2	1545.8	1544.5
7.5°	1610.5	1603.9	1597.3	1570.9	1541.9	1520.8	1486.5	1478.6	1462.7	1452.2	1446.9
10°	1557.7	1548.5	1535.3	1505.0	1469.3	1443.0	1407.4	1396.8	1366.5	1353.3	1345.4
12.5°	1499.7	1494.4	1473.3	1448.2	1390.2	1361.2	1309.7	1320.3	1290.0	1263.6	1259.6
15°	1441.6	1421.9	1410.0	1369.1	1299.2	1286.0	1245.1	1224.0	1196.3	1175.2	1175.2
17.5°	1384.9	1354.6	1328.2	1284.7	1233.2	1196.3	1166.0	1155.4	1121.1	1100.0	1096.1
20°	1309.7	1275.5	1268.9	1206.9	1171.3	1130.4	1101.3	1075.0	1049.9	1040.7	1034.1
22.5°	1238.5	1199.0	1188.4	1135.6	1100.0	1059.1	1030.1	1011.7	993.2	986.6	974.7
25°	1162.0	1138.3	1122.5	1065.7	1026.2	987.9	968.1	954.9	937.8	936.5	928.6
27.5°	1088.2	1065.7	1049.9	995.8	966.8	931.2	915.4	900.9	891.6	887.7	883.7
30°	1024.8	999.8	981.3	941.8	906.1	877.1	863.9	854.7	849.4	842.8	841.5
32.5°	954.9	940.4	915.4	885.0	857.3	829.6	821.7	815.1	807.2	804.6	803.3
35°	895.6	875.8	860.0	825.7	813.8	790.1	780.8	775.6	765.0	762.4	759.7
37.5°	837.6	819.1	801.9	780.8	758.4	745.2	739.9	732.0	726.8	728.1	725.4
40°	779.5	765.0	751.8	729.4	716.2	709.6	699.1	691.1	688.5	689.8	688.5
42.5°	722.8	709.6	701.7	684.6	671.4	664.8	658.2	650.3	654.2	654.2	658.2
45°	671.4	659.5	654.2	641.0	633.1	622.6	616.0	614.6	619.9	618.6	618.6
47.5°	618.6	614.6	608.0	596.2	585.6	579.0	577.7	577.7	583.0	585.6	584.3
50°	577.7	569.8	561.9	552.7	544.7	542.1	538.1	540.8	546.1	546.1	548.7
52.5°	526.3	521.0	518.4	510.4	505.2	505.2	505.2	506.5	510.4	514.4	513.1
55°	481.4	477.5	474.8	470.9	464.3	465.6	464.3	466.9	470.9	474.8	477.5
57.5°	433.9	432.6	430.0	423.4	423.4	422.1	426.0	427.3	433.9	436.6	440.5
60°	391.7	387.8	387.8	382.5	382.5	382.5	386.5	390.4	395.7	397.0	399.7
62.5°	346.9	346.9	345.6	341.6	341.6	345.6	346.9	352.2	354.8	354.8	358.8
65°	304.7	303.4	302.0	303.4	304.7	304.7	308.6	311.3	313.9	315.2	316.6
67.5°	262.5	261.2	263.8	262.5	265.1	270.4	269.1	273.0	277.0	277.0	278.3
70°	222.9	225.5	224.2	226.9	225.5	228.2	232.1	233.5	233.5	234.8	238.7
72.5°	186.0	186.0	186.0	184.7	186.0	188.6	191.3	192.6	195.2	196.5	200.5
75°	150.4	150.4	147.7	150.4	150.4	153.0	155.6	155.6	155.6	158.3	162.2
77.5°	113.4	114.8	113.4	116.1	116.1	117.4	120.0	118.7	121.3	122.7	124.0
80°	83.1	81.8	81.8	81.8	83.1	83.1	85.7	87.1	87.1	91.0	88.4
82.5°	52.8	54.1	52.8	54.1	54.1	55.4	54.1	55.4	56.7	59.4	58.0
85°	30.3	29.0	29.0	30.3	29.0	29.0	30.3	29.0	30.3	29.0	30.3
87.5°	11.9	10.6	10.6	10.6	10.6	9.2	9.2	7.9	7.9	7.9	6.6
90°	8.9	9.9	11.8	15.5	19.2	23.0	26.7	26.4	26.0	25.7	25.4
92.5°	22.2	22.9	23.0	23.2	23.3	23.5	23.7	23.9	24.0	24.2	24.3
95°	46.5	47.3	47.5	47.8	48.2	48.5	48.9	48.9	48.9	48.9	48.9
97.5°	72.5	73.3	73.6	74.3	75.0	75.6	76.3	76.3	76.3	76.3	76.3
100°	102.4	103.1	103.4	103.9	104.4	104.9	105.4	105.4	105.4	105.4	105.4
102.5°	133.1	133.6	133.9	134.6	135.3	136.0	136.7	136.9	137.0	137.2	137.3
105°	166.1	166.4	166.6	166.9	167.3	167.6	168.0	168.3	168.7	169.0	169.3
107.5°	202.0	202.3	202.3	202.3	202.3	202.3	202.3	202.5	202.7	202.8	203.0
110°	236.9	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	273.6	274.1	274.0	273.8	273.7	273.5	273.3	272.8	272.3	271.8	271.3
115°	309.5	310.0	309.8	309.5	309.1	308.8	308.4	308.2	308.1	307.9	307.8
117.5°	346.7	347.4	347.0	346.1	345.3	344.4	343.6	343.1	342.6	342.1	341.6
120°	382.6	383.3	382.6	381.3	379.9	378.6	377.2	377.2	377.2	377.2	377.2
122.5°	416.8	417.6	417.2	416.3	415.5	414.6	413.8	413.3	412.8	412.3	411.8
125°	450.4	451.2	450.9	450.4	449.9	449.4	448.9	448.4	447.9	447.4	446.9
127.5°	485.4	486.3	486.0	485.3	484.6	484.0	483.3	482.6	481.9	481.2	480.5
130°	518.1	519.2	519.0	518.7	518.3	518.0	517.6	517.3	516.9	516.6	516.3
132.5°	551.2	552.0	552.1	552.3	552.4	552.6	552.8	551.9	551.1	550.2	549.3
135°	582.4	583.3	583.5	583.8	584.1	584.5	584.8	584.6	584.5	584.3	584.2
137.5°	614.6	615.4	615.6	615.9	616.2	616.6	616.9	616.7	616.5	616.4	616.2
140°	644.3	645.1	645.5	646.4	647.3	648.1	649.0	649.0	649.0	649.0	649.0
142.5°	674.9	675.7	676.0	676.5	677.0	677.5	678.0	678.2	678.3	678.5	678.6
145°	702.6	703.2	703.7	704.7	705.7	706.7	707.7	707.9	708.1	708.2	708.4
147.5°	729.8	730.6	730.9	731.6	732.3	733.0	733.7	734.0	734.4	734.7	735.0
150°	754.6	755.1	755.4	756.1	756.8	757.4	758.1	758.6	759.1	759.6	760.1
152.5°	778.2	778.7	779.1	780.0	780.9	781.7	782.6	783.3	783.9	784.6	785.3
155°	799.8	800.1	800.4	800.9	801.4	801.9	802.4	803.2	804.1	804.9	805.8
157.5°	819.8	820.0	820.2	820.5	820.8	821.2	821.5	822.7	823.9	825.0	826.2
160°	838.1	838.3	838.4	838.6	838.7	838.9	839.1	840.1	841.1	842.1	843.1
162.5°	853.6	853.6	853.7	853.8	854.0	854.1	854.3	855.5	856.7	857.9	859.1
165°	867.4	867.3	867.3	867.3	867.3	867.3	867.3	868.5	869.7	870.9	872.1
167.5°	879.1	878.8	878.8	878.8	878.8	878.8	878.8	880.0	881.2	882.3	883.5
170°	889.0	888.7	888.6	888.4	888.3	888.1	887.9	889.1	890.3	891.5	892.7
172.5°	895.8	895.6	895.5	895.3	895.2	895.0	894.8	896.0	897.2	898.3	899.5
175°	901.2	900.9	900.7	900.4	900.1	899.7	899.4	900.6	901.8	902.9	904.1
177.5°	904.2	904.0	903.8	903.5	903.1	902.8	902.4	903.4	904.4	905.5	906.5
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1635.5	1639.5	1630.3	1627.6	1630.3	1621.0	1623.7	1626.3	1626.3	1630.3	1632.9
5°	1540.6	1535.3	1526.1	1523.4	1520.8	1524.7	1522.1	1526.1	1527.4	1536.6	1537.9
7.5°	1446.9	1439.0	1431.1	1423.2	1420.5	1413.9	1420.5	1420.5	1429.8	1427.1	1433.7
10°	1336.1	1334.8	1324.3	1320.3	1315.0	1304.5	1319.0	1315.0	1321.6	1333.5	1336.1
12.5°	1254.3	1239.8	1246.4	1228.0	1234.6	1224.0	1225.3	1225.3	1235.9	1237.2	1234.6
15°	1176.5	1164.7	1147.5	1139.6	1135.6	1130.4	1147.5	1148.8	1140.9	1159.4	1152.8
17.5°	1097.4	1097.4	1081.6	1077.6	1067.1	1072.3	1069.7	1071.0	1068.4	1081.6	1088.2
20°	1028.8	1022.2	1016.9	1018.3	1005.1	1002.4	999.8	1002.4	1011.7	1020.9	1023.5
22.5°	973.4	969.4	956.3	958.9	948.3	952.3	949.7	956.3	957.6	957.6	966.8
25°	920.6	915.4	916.7	911.4	907.5	907.5	903.5	907.5	912.7	915.4	916.7
27.5°	881.1	877.1	870.5	866.6	869.2	862.6	867.9	871.8	871.8	869.2	871.8
30°	833.6	836.2	836.2	823.0	828.3	825.7	829.6	832.3	832.3	833.6	831.0
32.5°	801.9	794.0	792.7	791.4	791.4	786.1	786.1	790.1	791.4	792.7	796.7
35°	759.7	759.7	753.1	757.1	751.8	753.1	751.8	753.1	755.8	751.8	755.8
37.5°	721.5	722.8	720.2	722.8	724.1	721.5	718.8	724.1	721.5	721.5	718.8
40°	688.5	687.2	688.5	688.5	688.5	689.8	687.2	687.2	687.2	684.6	681.9
42.5°	660.8	652.9	655.5	656.9	652.9	652.9	654.2	652.9	656.9	648.9	648.9
45°	621.2	618.6	619.9	619.9	622.6	618.6	621.2	622.6	618.6	617.3	614.6
47.5°	585.6	588.3	585.6	588.3	588.3	590.9	585.6	586.9	588.3	583.0	579.0
50°	550.0	550.0	554.0	552.7	554.0	551.3	551.3	550.0	551.3	548.7	544.7
52.5°	517.0	513.1	519.7	518.4	517.0	515.7	514.4	515.7	513.1	510.4	510.4
55°	476.2	476.2	480.1	481.4	481.4	478.8	476.2	477.5	476.2	474.8	473.5
57.5°	443.2	437.9	440.5	441.9	441.9	437.9	440.5	437.9	437.9	439.2	435.3
60°	401.0	401.0	398.3	402.3	402.3	399.7	399.7	401.0	398.3	397.0	395.7
62.5°	356.1	357.4	361.4	362.7	364.0	361.4	358.8	360.1	360.1	356.1	357.4
65°	317.9	320.5	325.8	324.5	321.8	323.1	320.5	321.8	317.9	319.2	315.2
67.5°	280.9	279.6	280.9	280.9	283.6	282.3	279.6	279.6	278.3	282.3	278.3
70°	241.4	241.4	241.4	241.4	242.7	244.0	241.4	238.7	240.1	237.4	236.1
72.5°	200.5	201.8	200.5	203.1	199.2	201.8	201.8	200.5	199.2	199.2	199.2
75°	162.2	164.9	160.9	162.2	160.9	163.6	162.2	162.2	159.6	158.3	159.6
77.5°	124.0	125.3	122.7	124.0	122.7	124.0	124.0	122.7	122.7	122.7	122.7
80°	88.4	89.7	88.4	87.1	85.7	88.4	85.7	87.1	88.4	87.1	89.7
82.5°	56.7	56.7	55.4	56.7	54.1	54.1	55.4	55.4	54.1	56.7	54.1
85°	27.7	27.7	30.3	27.7	26.4	26.4	26.4	27.7	26.4	29.0	27.7
87.5°	6.6	5.3	6.6	6.6	5.3	5.3	6.6	5.3	6.6	7.9	5.3
90°	25.2	25.3	25.5	25.6	25.8	26.0	25.8	25.6	25.5	25.3	25.2
92.5°	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4
95°	48.9	48.7	48.4	48.0	47.7	47.3	47.7	48.0	48.4	48.7	48.9
97.5°	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3
100°	105.4	105.3	105.1	105.0	104.8	104.6	104.8	105.0	105.1	105.3	105.4
102.5°	137.4	137.3	137.2	137.0	136.9	136.7	136.9	137.0	137.2	137.3	137.4
105°	169.5	169.5	169.5	169.5	169.5	169.5	169.5	169.5	169.5	169.5	169.5
107.5°	203.1	202.7	201.8	201.0	200.1	199.3	200.1	201.0	201.8	202.7	203.1
110°	237.4	237.2	236.7	236.2	235.7	235.2	235.7	236.2	236.7	237.2	237.4

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	271.0	270.8	270.5	270.2	269.8	269.5	269.8	270.2	270.5	270.8	271.0
115°	307.7	307.4	306.9	306.4	305.9	305.4	305.9	306.4	306.9	307.4	307.7
117.5°	341.3	341.0	340.5	340.0	339.5	339.0	339.5	340.0	340.5	341.0	341.3
120°	377.2	376.9	376.4	375.9	375.4	374.9	375.4	375.9	376.4	376.9	377.2
122.5°	411.5	411.3	411.0	410.7	410.3	410.0	410.3	410.7	411.0	411.3	411.5
125°	446.6	446.5	446.4	446.2	446.1	445.9	446.1	446.2	446.4	446.5	446.6
127.5°	480.2	479.9	479.4	478.9	478.4	477.9	478.4	478.9	479.4	479.9	480.2
130°	516.1	515.8	515.1	514.4	513.8	513.1	513.8	514.4	515.1	515.8	516.1
132.5°	548.9	548.6	548.1	547.6	547.1	546.6	547.1	547.6	548.1	548.6	548.9
135°	584.1	583.8	583.3	582.8	582.3	581.8	582.3	582.8	583.3	583.8	584.1
137.5°	616.1	615.8	615.1	614.4	613.8	613.1	613.8	614.4	615.1	615.8	616.1
140°	649.0	648.7	648.0	647.3	646.6	645.9	646.6	647.3	648.0	648.7	649.0
142.5°	678.7	678.4	677.7	677.0	676.4	675.7	676.4	677.0	677.7	678.4	678.7
145°	708.5	708.2	707.5	706.8	706.2	705.5	706.2	706.8	707.5	708.2	708.5
147.5°	735.2	734.9	734.2	733.5	732.9	732.2	732.9	733.5	734.2	734.9	735.2
150°	760.4	760.1	759.6	759.1	758.6	758.1	758.6	759.1	759.6	760.1	760.4
152.5°	785.6	785.3	784.6	783.9	783.3	782.6	783.3	783.9	784.6	785.3	785.6
155°	806.2	805.9	805.4	804.9	804.4	803.9	804.4	804.9	805.4	805.9	806.2
157.5°	826.8	826.4	825.5	824.7	823.8	823.0	823.8	824.7	825.5	826.4	826.8
160°	843.6	843.3	842.6	841.9	841.3	840.6	841.3	841.9	842.6	843.3	843.6
162.5°	859.7	859.3	858.4	857.6	856.7	855.9	856.7	857.6	858.4	859.3	859.7
165°	872.7	872.3	871.4	870.5	869.7	868.8	869.7	870.5	871.4	872.3	872.7
167.5°	884.1	883.7	882.8	882.0	881.1	880.3	881.1	882.0	882.8	883.7	884.1
170°	893.3	892.8	891.8	890.7	889.7	888.7	889.7	890.7	891.8	892.8	893.3
172.5°	900.1	899.6	898.6	897.6	896.6	895.6	896.6	897.6	898.6	899.6	900.1
175°	904.7	904.2	903.2	902.1	901.1	900.1	901.1	902.1	903.2	904.2	904.7
177.5°	907.0	906.5	905.5	904.4	903.4	902.4	903.4	904.4	905.5	906.5	907.0
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1628.9	1639.5	1635.5	1621.0	1638.2	1638.2	1650.0	1650.0	1664.6	1669.8	1677.7
5°	1536.6	1544.5	1551.1	1544.5	1556.4	1574.9	1585.4	1594.6	1614.4	1622.3	1634.2
7.5°	1437.7	1452.2	1458.8	1458.8	1478.6	1499.7	1520.8	1534.0	1561.7	1572.2	1584.1
10°	1341.4	1358.5	1371.7	1370.4	1403.4	1416.6	1443.0	1473.3	1501.0	1516.8	1534.0
12.5°	1239.8	1249.1	1267.5	1293.9	1301.8	1325.6	1355.9	1394.2	1444.3	1458.8	1483.9
15°	1155.4	1180.5	1195.0	1206.9	1225.3	1247.8	1280.7	1317.7	1367.8	1399.4	1425.8
17.5°	1084.2	1117.2	1126.4	1123.8	1147.5	1181.8	1220.1	1247.8	1292.6	1330.8	1355.9
20°	1026.2	1039.4	1055.2	1061.8	1080.2	1117.2	1154.1	1185.8	1222.7	1253.0	1282.0
22.5°	968.1	978.7	991.9	1003.7	1018.3	1039.4	1075.0	1114.5	1150.1	1179.2	1212.1
25°	920.6	927.2	939.1	948.3	964.2	978.7	1003.7	1047.3	1089.5	1106.6	1135.6
27.5°	874.5	879.8	887.7	898.2	906.1	920.6	943.1	978.7	1022.2	1039.4	1078.9
30°	833.6	837.6	845.5	850.7	854.7	871.8	889.0	916.7	949.7	973.4	1002.4
32.5°	795.3	799.3	807.2	808.5	813.8	823.0	838.9	863.9	892.9	912.7	937.8
35°	753.1	755.8	763.7	766.3	770.3	778.2	790.1	808.5	834.9	849.4	871.8
37.5°	720.2	718.8	724.1	728.1	733.4	737.3	741.3	759.7	779.5	792.7	809.9
40°	684.6	681.9	683.2	688.5	691.1	696.4	696.4	714.9	728.1	738.6	751.8
42.5°	648.9	647.6	645.0	647.6	650.3	651.6	652.9	666.1	679.3	688.5	703.0
45°	613.3	612.0	609.4	610.7	610.7	613.3	617.3	622.6	631.8	639.7	647.6
47.5°	580.4	577.7	573.8	572.4	575.1	575.1	575.1	580.4	589.6	592.2	600.1
50°	546.1	542.1	536.8	534.2	534.2	532.9	535.5	536.8	544.7	547.4	554.0
52.5°	509.1	506.5	501.2	495.9	497.3	494.6	495.9	497.3	499.9	503.8	507.8
55°	472.2	466.9	463.0	461.6	457.7	457.7	453.7	459.0	457.7	459.0	464.3
57.5°	436.6	431.3	424.7	422.1	418.1	416.8	414.2	412.8	414.2	418.1	422.1
60°	394.4	391.7	387.8	383.8	381.2	377.2	374.6	374.6	373.3	373.3	374.6
62.5°	353.5	352.2	346.9	345.6	342.9	340.3	336.3	333.7	333.7	336.3	337.7
65°	313.9	312.6	308.6	307.3	300.7	298.1	296.8	295.5	292.8	292.8	292.8
67.5°	277.0	273.0	273.0	266.4	261.2	258.5	255.9	254.6	254.6	254.6	255.9
70°	236.1	236.1	232.1	228.2	222.9	224.2	220.3	216.3	216.3	213.7	215.0
72.5°	196.5	195.2	191.3	189.9	186.0	182.0	179.4	182.0	178.1	176.7	178.1
75°	158.3	157.0	154.3	151.7	153.0	149.0	145.1	143.8	143.8	141.1	141.1
77.5°	121.3	124.0	118.7	117.4	114.8	112.1	110.8	109.5	109.5	109.5	112.1
80°	84.4	85.7	85.7	83.1	84.4	80.5	80.5	80.5	76.5	77.8	79.1
82.5°	54.1	54.1	52.8	54.1	52.8	52.8	51.4	51.4	50.1	50.1	51.4
85°	30.3	29.0	27.7	30.3	29.0	29.0	27.7	27.7	27.7	27.7	27.7
87.5°	6.6	7.9	7.9	7.9	7.9	9.2	9.2	9.2	10.6	10.6	10.6
90°	25.4	25.7	26.0	26.4	26.7	23.0	19.2	15.5	11.8	9.9	8.9
92.5°	24.3	24.2	24.0	23.9	23.7	23.5	23.3	23.2	23.0	22.9	22.2
95°	48.9	48.9	48.9	48.9	48.9	48.5	48.2	47.8	47.5	47.3	46.5
97.5°	76.3	76.3	76.3	76.3	76.3	75.6	75.0	74.3	73.6	73.3	72.5
100°	105.4	105.4	105.4	105.4	105.4	104.9	104.4	103.9	103.4	103.1	102.4
102.5°	137.3	137.2	137.0	136.9	136.7	136.0	135.3	134.6	133.9	133.6	133.1
105°	169.3	169.0	168.7	168.3	168.0	167.6	167.3	166.9	166.6	166.4	166.1
107.5°	203.0	202.8	202.7	202.5	202.3	202.3	202.3	202.3	202.3	202.3	202.0
110°	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	237.4	236.9

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	271.3	271.8	272.3	272.8	273.3	273.5	273.7	273.8	274.0	274.1	273.6
115°	307.8	307.9	308.1	308.2	308.4	308.8	309.1	309.5	309.8	310.0	309.5
117.5°	341.6	342.1	342.6	343.1	343.6	344.4	345.3	346.1	347.0	347.4	346.7
120°	377.2	377.2	377.2	377.2	377.2	378.6	379.9	381.3	382.6	383.3	382.6
122.5°	411.8	412.3	412.8	413.3	413.8	414.6	415.5	416.3	417.2	417.6	416.8
125°	446.9	447.4	447.9	448.4	448.9	449.4	449.9	450.4	450.9	451.2	450.4
127.5°	480.5	481.2	481.9	482.6	483.3	484.0	484.6	485.3	486.0	486.3	485.4
130°	516.3	516.6	516.9	517.3	517.6	518.0	518.3	518.7	519.0	519.2	518.1
132.5°	549.3	550.2	551.1	551.9	552.8	552.6	552.4	552.3	552.1	552.0	551.2
135°	584.2	584.3	584.5	584.6	584.8	584.5	584.1	583.8	583.5	583.3	582.4
137.5°	616.2	616.4	616.5	616.7	616.9	616.6	616.2	615.9	615.6	615.4	614.6
140°	649.0	649.0	649.0	649.0	649.0	648.1	647.3	646.4	645.5	645.1	644.3
142.5°	678.6	678.5	678.3	678.2	678.0	677.5	677.0	676.5	676.0	675.7	674.9
145°	708.4	708.2	708.1	707.9	707.7	706.7	705.7	704.7	703.7	703.2	702.6
147.5°	735.0	734.7	734.4	734.0	733.7	733.0	732.3	731.6	730.9	730.6	729.8
150°	760.1	759.6	759.1	758.6	758.1	757.4	756.8	756.1	755.4	755.1	754.6
152.5°	785.3	784.6	783.9	783.3	782.6	781.7	780.9	780.0	779.1	778.7	778.2
155°	805.8	804.9	804.1	803.2	802.4	801.9	801.4	800.9	800.4	800.1	799.8
157.5°	826.2	825.0	823.9	822.7	821.5	821.2	820.8	820.5	820.2	820.0	819.8
160°	843.1	842.1	841.1	840.1	839.1	838.9	838.7	838.6	838.4	838.3	838.1
162.5°	859.1	857.9	856.7	855.5	854.3	854.1	854.0	853.8	853.7	853.6	853.6
165°	872.1	870.9	869.7	868.5	867.3	867.3	867.3	867.3	867.3	867.3	867.4
167.5°	883.5	882.3	881.2	880.0	878.8	878.8	878.8	878.8	878.8	878.8	879.1
170°	892.7	891.5	890.3	889.1	887.9	888.1	888.3	888.4	888.6	888.7	889.0
172.5°	899.5	898.3	897.2	896.0	894.8	895.0	895.2	895.3	895.5	895.6	895.8
175°	904.1	902.9	901.8	900.6	899.4	899.7	900.1	900.4	900.7	900.9	901.2
177.5°	906.5	905.5	904.4	903.4	902.4	902.8	903.1	903.5	903.8	904.0	904.2
180°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1716.0	1716.0	1716.0	1716.0
2.5°	1684.3	1684.3	1704.1	1725.2
5°	1647.4	1656.6	1688.3	1717.3
7.5°	1611.8	1627.6	1667.2	1704.1
10°	1568.3	1589.4	1638.2	1681.7
12.5°	1526.1	1545.8	1602.6	1651.4
15°	1466.7	1491.8	1552.4	1613.1
17.5°	1407.4	1432.4	1506.3	1577.5
20°	1337.4	1370.4	1453.5	1548.5
22.5°	1272.8	1313.7	1406.0	1482.5
25°	1201.6	1264.9	1350.6	1449.6
27.5°	1138.3	1201.6	1288.6	1388.9
30°	1067.1	1131.7	1221.4	1313.7
32.5°	998.5	1057.8	1144.9	1258.3
35°	927.2	984.0	1068.4	1183.1
37.5°	862.6	918.0	1010.3	1115.9
40°	799.3	857.3	936.5	1042.0
42.5°	739.9	791.4	862.6	968.1
45°	685.9	722.8	788.7	887.7
47.5°	629.2	662.1	722.8	821.7
50°	576.4	604.1	656.9	749.2
52.5°	525.0	548.7	597.5	671.4
55°	478.8	501.2	536.8	609.4
57.5°	431.3	448.5	482.7	540.8
60°	385.1	401.0	428.7	476.2
62.5°	339.0	352.2	378.5	416.8
65°	298.1	308.6	328.4	361.4
67.5°	258.5	265.1	280.9	307.3
70°	220.3	225.5	238.7	259.8
72.5°	179.4	184.7	199.2	213.7
75°	145.1	146.4	157.0	168.8
77.5°	113.4	112.1	120.0	129.3
80°	77.8	81.8	88.4	92.3
82.5°	52.8	54.1	56.7	59.4
85°	29.0	30.3	30.3	34.3
87.5°	11.9	13.2	13.2	14.5
90°	6.9	4.8	2.8	0.8
92.5°	20.9	19.5	18.2	16.8
95°	44.8	43.1	41.4	39.7
97.5°	71.0	69.5	67.9	66.4
100°	101.1	99.7	98.4	97.0
102.5°	132.1	131.0	130.0	129.0
105°	165.6	165.1	164.6	164.1
107.5°	201.3	200.6	200.0	199.3
110°	235.9	234.9	233.9	232.9

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	272.6	271.5	270.5	269.5
115°	308.5	307.4	306.4	305.4
117.5°	345.4	344.0	342.7	341.3
120°	381.3	379.9	378.6	377.2
122.5°	415.1	413.4	411.7	410.0
125°	448.9	447.4	445.8	444.3
127.5°	483.5	481.6	479.8	477.9
130°	515.9	513.6	511.4	509.2
132.5°	549.5	547.8	546.1	544.4
135°	580.5	578.6	576.8	574.9
137.5°	613.1	611.6	610.0	608.5
140°	642.8	641.3	639.8	638.3
142.5°	673.4	671.9	670.3	668.8
145°	701.4	700.2	699.0	697.8
147.5°	728.3	726.8	725.3	723.8
150°	753.6	752.5	751.5	750.5
152.5°	777.2	776.2	775.2	774.2
155°	799.3	798.8	798.3	797.8
157.5°	819.5	819.1	818.8	818.4
160°	837.8	837.5	837.1	836.8
162.5°	853.6	853.6	853.6	853.6
165°	867.6	867.7	867.9	868.1
167.5°	879.6	880.1	880.6	881.1
170°	889.5	890.0	890.5	891.0
172.5°	896.3	896.8	897.3	897.8
175°	901.7	902.2	902.7	903.2
177.5°	904.7	905.2	905.7	906.2
180°	904.7	904.7	904.7	904.7

TEST NUMBER: P999174

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.20	19.11	19.07	20.00	21.13	15.69	16.61	16.57	17.50	18.62
	3H	19.01	19.83	19.90	20.73	21.88	17.04	17.86	17.93	18.76	19.91
	4H	19.18	19.96	20.09	20.86	22.02	17.51	18.28	18.41	19.18	20.35
	6H	19.23	19.95	20.15	20.86	22.03	17.82	18.53	18.73	19.44	20.61
	8H	19.21	19.89	20.14	20.82	21.99	17.90	18.58	18.82	19.51	20.68
	12H	19.18	19.82	20.10	20.75	21.94	17.94	18.59	18.87	19.51	20.71
4H	2H	18.25	19.02	19.15	19.93	21.09	16.14	16.92	17.05	17.82	18.98
	3H	19.23	19.87	20.15	20.81	21.99	17.61	18.25	18.53	19.19	20.36
	4H	19.51	20.10	20.44	21.03	22.23	18.15	18.73	19.07	19.66	20.87
	6H	19.64	20.15	20.59	21.10	22.31	18.53	19.03	19.47	19.99	21.19
	8H	19.64	20.11	20.59	21.06	22.28	18.64	19.11	19.59	20.06	21.28
	12H	19.61	20.03	20.57	21.00	22.22	18.70	19.12	19.66	20.09	21.31
8H	4H	19.52	19.99	20.47	20.94	22.16	18.29	18.76	19.24	19.71	20.93
	6H	19.70	20.09	20.67	21.08	22.30	18.73	19.12	19.70	20.11	21.32
	8H	19.73	20.08	20.71	21.06	22.29	18.88	19.22	19.86	20.20	21.44
	12H	19.72	20.02	20.70	21.00	22.28	18.98	19.28	19.96	20.25	21.53
12H	4H	19.48	19.91	20.45	20.87	22.09	18.27	18.69	19.23	19.66	20.88
	6H	19.68	20.03	20.66	21.01	22.24	18.73	19.07	19.71	20.05	21.29
	8H	19.72	20.02	20.70	20.99	22.27	18.89	19.19	19.87	20.17	21.45