

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999177

Luminaire Tested: SA2XXDIP-B865D725UB30-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999177
REPORT IS A COMBINATION OF REPORTS P984926 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D725UB30-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6005.0 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999177

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P999177

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	97	92	87	83	89	85	81	77	71	69	66	59	57	55	48	47	45
2	87	79	72	67	80	73	67	62	62	57	53	51	48	45	42	39	37
3	79	69	61	55	73	64	57	51	54	49	44	45	41	37	36	33	31
4	72	61	52	46	66	56	49	43	48	42	37	40	35	32	32	29	26
5	66	54	45	39	61	50	42	37	42	36	32	35	31	27	29	25	23
6	61	48	40	34	56	45	37	32	38	32	28	32	27	24	26	22	20
7	56	43	35	29	52	40	33	28	34	28	24	29	24	21	24	20	17
8	52	39	31	26	48	37	29	24	31	25	21	26	22	18	22	18	15
9	48	36	28	23	45	33	26	22	29	23	19	24	20	16	20	16	14
10	45	33	25	20	42	31	24	19	26	21	17	22	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14408	14408	14408
5°	14473	13793	13716
10°	14375	13315	13121
15°	14172	12822	12511
20°	13917	12303	11934
25°	13665	11806	11409
30°	13310	11300	10889
35°	12952	10814	10507
40°	12575	10392	10129
45°	12215	10011	9799
50°	11830	9659	9472
55°	11423	9285	9140
60°	10927	8895	8791
65°	10409	8448	8389
70°	9826	7969	7957
75°	9079	7486	7549
80°	7896	6986	7127
85°	6710	6516	6763

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12215 cd/sqm

TEST NUMBER: P999177

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.3	1.4
10°-20°	247.5	4.1
20°-30°	375.0	6.2
30°-40°	456.6	7.6
40°-50°	491.3	8.2
50°-60°	477.1	7.9
60°-70°	416.7	6.9
70°-80°	320.7	5.3
80°-90°	217.4	3.6
90°-100°	204.1	3.4
100°-110°	286.1	4.8
110°-120°	375.9	6.3
120°-130°	440.2	7.3
130°-140°	466.1	7.8
140°-150°	443.5	7.4
150°-160°	369.7	6.2
160°-170°	245.2	4.1
170°-180°	85.7	1.4
0°-30°	708.7	11.8
0°-40°	1165.3	19.4
0°-60°	2133.7	35.5
0°-90°	3088.4	51.4
90°-120°	866.2	14.4
90°-150°	2216.0	36.9
90°-180°	2917.0	48.6
0°-180°	6005.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	910	910	910	910	910	
5°	913	909	901	909	908	87
15°	871	873	873	885	884	245
25°	792	801	813	828	832	364
35°	682	704	730	758	768	426
45°	559	595	641	682	695	432
55°	429	476	545	592	609	383
65°	293	358	435	489	506	291
75°	162	236	320	377	394	172
85°	48	129	214	269	288	50
90°	14	100	201	252	269	12
95°	50	120	201	251	265	53
105°	171	211	281	329	344	181
115°	311	330	388	426	439	307
125°	447	454	494	527	538	400
135°	576	585	599	626	635	446
145°	698	703	708	716	720	436
155°	798	800	802	806	804	367
165°	868	867	867	873	869	245
175°	903	901	899	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P999177

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	910.2	910.2	910.2	910.2	910.2
2.5°	916.8	912.8	903.6	910.2	907.6
5°	912.8	908.9	901.0	908.9	907.6
7.5°	906.2	903.6	897.0	906.2	904.9
10°	898.3	895.7	891.7	902.3	901.0
12.5°	885.1	886.5	883.8	894.4	893.1
15°	870.6	873.3	873.3	885.1	883.8
17.5°	852.2	857.4	861.4	873.3	873.3
20°	833.7	840.3	845.6	860.1	860.1
22.5°	813.9	821.8	829.7	844.2	846.9
25°	791.5	800.7	812.6	828.4	832.4
27.5°	765.1	779.6	792.8	812.6	815.2
30°	738.7	755.9	773.0	794.1	798.1
32.5°	709.7	729.5	750.6	775.6	783.6
35°	682.0	704.4	729.5	758.5	767.7
37.5°	651.6	676.7	708.4	740.0	749.3
40°	621.3	650.3	685.9	720.2	732.1
42.5°	592.3	621.3	663.5	701.8	713.6
45°	559.3	594.9	641.1	682.0	695.2
47.5°	527.7	565.9	618.7	660.9	675.4
50°	494.7	535.6	594.9	639.8	654.3
52.5°	463.0	506.5	569.9	616.0	631.9
55°	428.7	476.2	544.8	592.3	609.4
57.5°	395.7	448.5	517.1	568.5	585.7
60°	360.1	416.8	492.0	542.2	560.6
62.5°	328.5	387.8	463.0	517.1	534.2
65°	292.8	357.5	435.3	489.4	506.5
67.5°	261.2	328.5	407.6	461.7	480.2
70°	226.9	295.5	377.3	434.0	449.8
72.5°	195.2	266.5	349.6	405.0	424.8
75°	162.3	236.1	320.5	377.3	394.4
77.5°	130.6	207.1	292.8	349.6	368.0
80°	98.9	179.4	265.1	320.5	339.0
82.5°	72.6	151.7	238.8	294.2	311.3
85°	47.5	129.3	213.7	269.1	287.6
87.5°	29.0	108.2	192.6	246.7	263.8
90°	14.0	99.6	200.8	252.1	268.7
92.5°	28.7	104.7	186.0	238.1	253.9
95°	50.3	119.9	200.6	250.7	265.0
97.5°	75.6	139.3	218.8	267.6	283.4
100°	106.2	161.1	237.3	286.1	299.8
102.5°	136.9	185.0	259.4	307.6	321.4
105°	170.7	211.3	281.4	329.1	343.6
107.5°	205.9	240.6	306.5	352.2	362.9
110°	238.2	269.1	333.7	375.9	388.2



TEST NUMBER: P999177

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	274.8	300.5	360.4	400.3	413.3
115°	310.7	329.8	387.5	426.4	438.6
117.5°	345.3	361.9	413.5	450.8	461.7
120°	381.2	392.5	439.2	476.1	488.3
122.5°	414.0	422.9	467.9	501.2	511.6
125°	446.9	453.8	493.8	527.1	538.2
127.5°	480.5	487.6	520.2	550.1	559.7
130°	511.8	520.5	546.6	576.8	584.3
132.5°	547.0	553.3	573.9	600.3	608.6
135°	576.2	584.6	599.3	626.3	634.6
137.5°	609.8	616.7	624.8	649.1	655.3
140°	639.6	645.1	651.6	672.7	677.6
142.5°	670.1	675.7	678.0	694.5	698.1
145°	697.8	703.2	707.7	716.4	720.0
147.5°	723.8	730.6	733.7	736.5	737.5
150°	750.5	755.1	758.1	760.4	758.1
152.5°	774.2	778.7	782.6	785.6	782.6
155°	797.8	800.1	802.4	806.2	803.9
157.5°	818.4	820.0	821.5	826.8	823.0
160°	836.8	838.3	839.1	843.6	840.6
162.5°	853.6	853.6	854.3	859.7	855.9
165°	868.1	867.3	867.3	872.7	868.8
167.5°	881.1	878.8	878.8	884.1	880.3
170°	891.0	888.7	887.9	893.3	888.7
172.5°	897.8	895.6	894.8	900.1	895.6
175°	903.2	900.9	899.4	904.7	900.1
177.5°	906.2	904.0	902.4	907.0	902.4
180°	904.7	904.7	904.7	904.7	904.7

TEST NUMBER: P999177

CATALOG NUMBER: SA2XXDIP-B865D725UB30-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.61	15.53	15.54	16.49	17.74	17.68	18.61	18.61	19.57	20.81
	3H	16.07	16.91	17.01	17.88	19.14	20.27	21.11	21.22	22.08	23.35
	4H	16.55	17.35	17.51	18.32	19.59	21.53	22.33	22.49	23.30	24.58
	6H	16.84	17.57	17.80	18.55	19.84	22.83	23.57	23.80	24.54	25.84
	8H	16.90	17.60	17.87	18.60	19.88	23.49	24.20	24.47	25.19	26.48
	12H	16.92	17.59	17.90	18.58	19.89	24.22	24.89	25.20	25.88	27.19
4H	2H	15.66	16.46	16.63	17.43	18.71	18.02	18.81	18.98	19.79	21.06
	3H	17.38	18.05	18.35	19.05	20.34	20.81	21.49	21.79	22.49	23.78
	4H	18.00	18.62	18.98	19.62	20.93	22.23	22.86	23.21	23.85	25.16
	6H	18.42	18.96	19.41	19.98	21.29	23.70	24.25	24.70	25.26	26.57
	8H	18.53	19.04	19.52	20.05	21.38	24.46	24.97	25.46	25.98	27.31
	12H	18.58	19.04	19.59	20.07	21.40	25.30	25.76	26.31	26.79	28.12
8H	4H	18.79	19.30	19.79	20.32	21.64	22.38	22.89	23.38	23.90	25.23
	6H	19.43	19.86	20.45	20.91	22.24	24.01	24.44	25.03	25.49	26.82
	8H	19.65	20.03	20.68	21.07	22.41	24.90	25.29	25.93	26.32	27.67
	12H	19.79	20.13	20.82	21.16	22.55	25.90	26.24	26.93	27.27	28.66
12H	4H	19.00	19.46	20.01	20.49	21.82	22.36	22.82	23.37	23.85	25.18
	6H	19.77	20.15	20.79	21.18	22.53	24.04	24.42	25.07	25.46	26.80
	8H	20.07	20.41	21.10	21.44	22.83	24.97	25.31	26.00	26.34	27.73