

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998016

Luminaire Tested: SA2XXDIP-B1005D725UB50-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998016
REPORT IS A COMBINATION OF REPORTS P983753 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D725UB50-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6322.0 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998016

CATALOG NUMBER: SA2XXDIP-B1005D725UB50-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P998016

CATALOG NUMBER: SA2XXDIP-B1005D725UB50-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86		73	73	73		60
1	97	92	88	83	90	85	81	78	73	70	67		61	59	57		51
2	88	80	73	67	81	74	68	63	63	58	54		53	50	46		44
3	80	69	61	55	73	64	57	52	55	49	45		46	42	39		38
4	73	61	53	46	67	57	49	43	49	43	38		41	36	33		34
5	67	54	46	39	61	50	43	37	43	37	32		37	32	28		30
6	61	48	40	34	56	45	37	32	39	33	28		33	28	24		27
7	57	44	35	29	52	41	33	28	35	29	25		30	25	21		25
8	52	40	31	26	48	37	30	25	32	26	22		27	22	19		23
9	49	36	28	23	45	34	27	22	29	23	19		25	20	17		21
10	46	33	26	21	42	31	24	20	27	21	17		23	19	15		20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16130	16130	16130
5°	16202	15441	15354
10°	16094	14906	14688
15°	15867	14353	14006
20°	15580	13772	13358
25°	15298	13216	12771
30°	14901	12651	12190
35°	14500	12105	11764
40°	14078	11634	11339
45°	13674	11207	10970
50°	13243	10813	10604
55°	12787	10395	10233
60°	12235	9958	9842
65°	11653	9457	9392
70°	11000	8921	8909
75°	10159	8383	8452
80°	8846	7821	7978
85°	7515	7294	7570

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13674 cd/sqm

TEST NUMBER: P998016

CATALOG NUMBER: SA2XXDIP-B1005D725UB50-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	1.5
10°-20°	277.0	4.4
20°-30°	419.8	6.6
30°-40°	511.2	8.1
40°-50°	550.0	8.7
50°-60°	534.1	8.4
60°-70°	466.4	7.4
70°-80°	359.0	5.7
80°-90°	242.9	3.8
90°-100°	219.7	3.5
100°-110°	292.2	4.6
110°-120°	372.7	5.9
120°-130°	429.4	6.8
130°-140°	450.7	7.1
140°-150°	426.8	6.8
150°-160°	355.4	5.6
160°-170°	235.7	3.7
170°-180°	82.4	1.3
0°-30°	793.4	12.6
0°-40°	1304.6	20.6
0°-60°	2388.7	37.8
0°-90°	3457.0	54.7
90°-120°	884.5	14.0
90°-150°	2191.5	34.7
90°-180°	2865.0	45.3
0°-180°	6322.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1019	1019	1019	1019	1019	
5°	1022	1018	1009	1018	1016	97
15°	975	978	978	991	989	275
25°	886	896	910	927	932	407
35°	764	789	817	849	860	477
45°	626	666	718	764	778	483
55°	480	533	610	663	682	429
65°	328	400	487	548	567	326
75°	182	264	359	422	442	192
85°	53	145	239	301	322	56
90°	16	110	221	278	297	13
95°	50	127	217	273	289	52
105°	165	210	288	342	358	175
115°	300	320	385	429	443	296
125°	430	437	482	519	532	385
135°	554	562	578	609	618	429
145°	671	676	680	690	694	419
155°	767	769	771	775	773	353
165°	834	834	834	839	835	235
175°	868	866	865	870	865	82
180°	870	870	870	870	870	

TEST NUMBER: P998016

CATALOG NUMBER: SA2XXDIP-B1005D725UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1019.0	1019.0	1019.0	1019.0	1019.0
2.5°	1026.3	1021.9	1011.6	1019.0	1016.0
5°	1021.9	1017.5	1008.6	1017.5	1016.0
7.5°	1014.5	1011.6	1004.2	1014.5	1013.1
10°	1005.7	1002.7	998.3	1010.1	1008.6
12.5°	990.9	992.4	989.4	1001.2	999.8
15°	974.7	977.6	977.6	990.9	989.4
17.5°	954.0	959.9	964.3	977.6	977.6
20°	933.3	940.7	946.6	962.8	962.8
22.5°	911.2	920.0	928.9	945.1	948.1
25°	886.1	896.4	909.7	927.4	931.8
27.5°	856.5	872.8	887.5	909.7	912.6
30°	827.0	846.2	865.4	889.0	893.4
32.5°	794.5	816.6	840.3	868.3	877.2
35°	763.5	788.6	816.6	849.1	859.5
37.5°	729.5	757.6	793.0	828.5	838.8
40°	695.6	728.0	767.9	806.3	819.6
42.5°	663.1	695.6	742.8	785.6	798.9
45°	626.1	666.0	717.7	763.5	778.3
47.5°	590.7	633.5	692.6	739.9	756.1
50°	553.8	599.6	666.0	716.2	732.5
52.5°	518.3	567.1	638.0	689.6	707.4
55°	479.9	533.1	609.9	663.1	682.3
57.5°	443.0	502.1	578.9	636.5	655.7
60°	403.2	466.7	550.8	606.9	627.6
62.5°	367.7	434.2	518.3	578.9	598.1
65°	327.8	400.2	487.3	547.9	567.1
67.5°	292.4	367.7	456.3	516.9	537.5
70°	254.0	330.8	422.4	485.9	503.6
72.5°	218.6	298.3	391.3	453.4	475.5
75°	181.6	264.3	358.9	422.4	441.6
77.5°	146.2	231.9	327.8	391.3	412.0
80°	110.8	200.8	296.8	358.9	379.5
82.5°	81.2	169.8	267.3	329.3	348.5
85°	53.2	144.7	239.2	301.3	321.9
87.5°	32.5	121.1	215.6	276.2	295.4
90°	15.5	109.9	220.6	278.2	296.7
92.5°	29.4	113.6	204.4	262.7	280.5
95°	50.0	126.7	216.8	272.9	289.2
97.5°	74.2	144.3	232.9	287.5	305.3
100°	103.5	164.1	249.0	303.6	319.1
102.5°	132.9	186.0	268.7	322.6	338.1
105°	165.2	210.2	288.5	341.6	357.8
107.5°	199.0	237.3	311.2	362.1	374.7
110°	229.7	263.7	336.1	383.4	397.3



TEST NUMBER: P998016

CATALOG NUMBER: SA2XXDIP-B1005D725UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	265.0	293.0	360.2	405.2	420.1
115°	299.5	320.2	385.1	428.7	442.8
117.5°	332.5	350.1	408.6	450.7	463.2
120°	367.0	378.7	432.0	473.4	487.4
122.5°	398.5	407.4	458.3	496.0	507.8
125°	430.1	436.8	481.7	519.4	532.0
127.5°	462.4	469.0	505.9	539.9	551.0
130°	492.5	500.6	530.1	564.0	572.9
132.5°	526.3	532.1	555.0	585.3	594.9
135°	554.1	562.2	578.4	608.8	618.4
137.5°	586.4	593.0	601.9	629.2	636.6
140°	615.1	620.2	626.8	650.4	656.3
142.5°	644.4	649.5	651.7	670.2	674.6
145°	670.8	675.9	680.4	690.0	694.3
147.5°	695.8	702.4	705.3	708.3	709.7
150°	721.4	725.9	728.8	731.0	728.8
152.5°	744.2	748.6	752.3	755.2	752.3
155°	767.0	769.2	771.4	775.0	772.8
157.5°	786.8	788.2	789.7	794.8	791.2
160°	804.4	805.9	806.6	811.0	808.1
162.5°	820.5	820.5	821.3	826.4	822.7
165°	834.5	833.7	833.7	838.9	835.2
167.5°	847.0	844.7	844.7	849.9	846.2
170°	856.5	854.3	853.6	858.7	854.3
172.5°	863.1	860.9	860.2	865.3	860.9
175°	868.2	866.0	864.6	869.7	865.3
177.5°	871.2	869.0	867.5	871.9	867.5
180°	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P998016

CATALOG NUMBER: SA2XXDIP-B1005D725UB50-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.28	16.24	16.19	17.18	18.37	18.36	19.32	19.26	20.25	21.45
	3H	16.75	17.62	17.66	18.56	19.78	20.95	21.82	21.87	22.77	23.99
	4H	17.23	18.06	18.16	19.00	20.23	22.21	23.04	23.14	23.98	25.21
	6H	17.52	18.29	18.46	19.24	20.48	23.51	24.28	24.45	25.23	26.47
	8H	17.58	18.31	18.53	19.28	20.52	24.17	24.91	25.12	25.88	27.12
	12H	17.60	18.30	18.55	19.26	20.53	24.90	25.60	25.86	26.57	27.83
4H	2H	16.34	17.17	17.28	18.12	19.35	18.70	19.53	19.63	20.47	21.70
	3H	18.06	18.76	19.00	19.74	20.98	21.50	22.20	22.44	23.17	24.42
	4H	18.68	19.33	19.64	20.30	21.57	22.92	23.56	23.87	24.53	25.80
	6H	19.10	19.67	20.07	20.66	21.93	24.39	24.96	25.36	25.95	27.21
	8H	19.22	19.75	20.18	20.73	22.02	25.15	25.68	26.12	26.67	27.95
	12H	19.26	19.75	20.25	20.75	22.04	25.98	26.47	26.97	27.47	28.76
8H	4H	19.48	20.01	20.45	21.00	22.28	23.07	23.60	24.04	24.59	25.87
	6H	20.12	20.57	21.11	21.59	22.87	24.70	25.15	25.70	26.18	27.46
	8H	20.34	20.74	21.34	21.75	23.05	25.59	25.99	26.60	27.01	28.30
	12H	20.48	20.83	21.49	21.84	23.19	26.59	26.95	27.60	27.96	29.30
12H	4H	19.69	20.17	20.67	21.17	22.46	23.05	23.53	24.04	24.53	25.82
	6H	20.45	20.85	21.46	21.87	23.17	24.73	25.13	25.73	26.14	27.44
	8H	20.76	21.12	21.77	22.13	23.47	25.66	26.02	26.67	27.03	28.37