

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998023

Luminaire Tested: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998023
REPORT IS A COMBINATION OF REPORTS P983760 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7922.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	92	88	92	89	86	83	76	74	72	65	63	62	55	54	52
2	91	84	78	73	84	78	73	69	68	64	60	58	55	53	49	47	45
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39
4	77	66	58	52	71	62	55	50	54	49	44	46	42	39	39	36	34
5	71	59	51	45	65	55	48	43	48	43	39	42	38	34	36	33	30
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	27	24
8	56	44	36	31	52	42	35	30	37	31	27	32	28	24	28	24	22
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31359	31359	31359	31359
5°	31436	33437	31556	26602
10°	31070	36502	31265	21932
15°	30317	38501	30739	18474
20°	29843	36150	29843	16057
25°	28892	31057	29025	14360
30°	27328	24414	27849	13007
35°	25941	16882	26375	11901
40°	24348	12746	24625	11018
45°	22382	10474	22749	10067
50°	20683	9193	20721	9215
55°	18746	7833	18868	8291
60°	16680	6542	16911	7235
65°	14831	5321	15105	6179
70°	12992	4175	13321	4983
75°	10903	3032	11328	3614
80°	8511	1922	9117	2144
85°	5594	966	6018	717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 32417 cd/sqm

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.7	2.4
10°-20°	549.2	6.9
20°-30°	797.1	10.1
30°-40°	840.3	10.6
40°-50°	743.6	9.4
50°-60°	593.7	7.5
60°-70°	403.3	5.1
70°-80°	206.3	2.6
80°-90°	52.0	0.7
90°-100°	198.6	2.5
100°-110°	699.4	8.8
110°-120°	734.5	9.3
120°-130°	604.3	7.6
130°-140°	485.4	6.1
140°-150°	366.7	4.6
150°-160°	257.8	3.3
160°-170°	151.7	1.9
170°-180°	49.4	0.6
0°-30°	1535.0	19.4
0°-40°	2375.3	30.0
0°-60°	3712.6	46.9
0°-90°	4374.3	55.2
90°-120°	1632.5	20.6
90°-150°	3088.8	39.0
90°-180°	3548.0	44.8
0°-180°	7922.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1981	1981	1981	1981	1981	
5°	1983	2213	1990	1760	1983	188
15°	1862	2720	1888	1305	1862	526
25°	1674	2266	1681	1048	1674	765
35°	1366	1234	1389	870	1366	855
45°	1025	743	1042	714	1025	795
55°	704	522	708	553	704	628
65°	417	321	425	373	417	415
75°	195	158	202	189	195	209
85°	40	41	43	30	40	46
90°	1	32	1	32	1	5
95°	34	112	34	112	34	35
105°	120	1104	120	1104	120	127
115°	211	1453	211	1453	211	209
125°	294	1179	294	1179	294	261
135°	345	977	345	977	345	266
145°	394	780	394	780	394	247
155°	448	655	448	655	448	206
165°	488	575	488	575	488	138
175°	508	518	508	518	508	48
180°	509	509	509	509	509	

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	1991.8	1996.4	2004.0	2005.5	2020.7	2032.9	2046.6	2046.6	2051.2	2049.7	2037.5
5°	1982.7	1996.4	2016.2	2032.9	2060.3	2072.5	2090.8	2104.5	2116.7	2125.8	2124.3
7.5°	1967.4	1991.8	2020.7	2052.7	2089.3	2110.6	2136.5	2160.8	2177.6	2192.8	2203.5
10°	1941.5	1982.7	2022.3	2064.9	2112.1	2141.0	2171.5	2203.5	2229.4	2258.3	2285.7
12.5°	1906.5	1965.9	2014.6	2071.0	2128.9	2160.8	2209.6	2233.9	2284.2	2357.3	2377.1
15°	1862.4	1943.1	1988.8	2060.3	2136.5	2162.4	2229.4	2268.9	2372.5	2418.2	2473.0
17.5°	1821.2	1911.1	1972.0	2054.2	2128.9	2179.1	2244.6	2325.3	2412.1	2477.6	2538.5
20°	1787.7	1874.5	1947.6	2039.0	2133.4	2197.4	2265.9	2363.4	2457.8	2524.8	2572.0
22.5°	1711.6	1822.8	1908.0	2010.1	2124.3	2212.6	2278.1	2384.7	2486.7	2527.8	2568.9
25°	1673.5	1769.5	1868.5	1984.2	2118.2	2223.3	2279.6	2398.4	2488.2	2503.5	2512.6
27.5°	1603.5	1711.6	1827.3	1959.8	2116.7	2205.0	2276.6	2384.7	2456.2	2445.6	2418.2
30°	1516.7	1649.2	1777.1	1920.2	2095.3	2191.3	2258.3	2357.3	2393.8	2339.0	2290.3
32.5°	1452.7	1577.6	1719.2	1885.2	2071.0	2162.4	2227.8	2305.5	2313.1	2214.1	2131.9
35°	1365.9	1504.5	1664.4	1839.5	2029.9	2112.1	2173.0	2220.2	2183.7	2045.1	1947.6
37.5°	1288.3	1425.3	1595.9	1774.0	1973.5	2054.2	2103.0	2110.6	2020.7	1898.9	1755.8
40°	1203.0	1344.6	1522.8	1710.1	1911.1	1981.1	2011.6	1988.8	1859.3	1717.7	1551.7
42.5°	1117.7	1257.8	1449.7	1641.6	1831.9	1891.3	1903.5	1841.0	1682.7	1516.7	1324.8
45°	1024.8	1171.0	1362.9	1556.3	1740.5	1774.0	1775.6	1685.7	1498.4	1324.8	1146.7
47.5°	948.7	1084.2	1274.6	1468.0	1623.3	1646.1	1637.0	1533.4	1329.4	1134.5	979.1
50°	864.9	994.4	1183.2	1373.6	1506.0	1512.1	1489.3	1341.6	1142.1	963.9	840.6
52.5°	775.1	906.1	1079.7	1262.4	1381.2	1372.0	1327.9	1169.5	982.2	834.5	740.1
55°	703.5	819.3	982.2	1160.4	1244.1	1218.2	1169.5	1008.1	860.4	735.5	653.3
57.5°	624.3	726.4	886.3	1041.6	1090.3	1065.9	1017.2	866.5	729.4	635.0	580.2
60°	549.7	642.6	782.7	912.1	950.2	924.3	868.0	732.5	633.5	554.3	513.2
62.5°	481.2	561.9	679.2	797.9	813.2	787.3	738.5	628.9	543.6	481.2	450.7
65°	417.2	493.4	587.8	677.6	691.3	663.9	613.7	534.5	462.9	423.3	394.4
67.5°	354.8	415.7	499.5	565.0	572.6	546.7	505.6	441.6	397.4	354.8	333.5
70°	300.0	345.7	411.2	464.4	467.5	443.1	421.8	363.9	330.4	300.0	283.2
72.5°	246.7	278.7	328.9	368.5	370.0	354.8	335.0	298.5	269.5	248.2	231.5
75°	194.9	222.3	252.8	287.8	286.3	274.1	258.9	236.0	211.7	198.0	190.3
77.5°	149.2	166.0	190.3	213.2	213.2	207.1	198.0	181.2	166.0	152.3	144.7
80°	106.6	117.3	137.1	144.7	147.7	146.2	138.6	126.4	120.3	109.6	106.6
82.5°	68.5	76.1	85.3	92.9	97.5	94.4	92.9	86.8	77.7	74.6	71.6
85°	39.6	42.6	47.2	51.8	53.3	51.8	54.8	50.3	45.7	45.7	44.2
87.5°	16.8	18.3	21.3	21.3	22.8	22.8	21.3	22.8	22.8	21.3	19.8
90°	1.0	3.9	7.8	9.8	11.8	13.2	14.7	19.6	26.5	32.3	33.3
92.5°	14.7	20.6	28.4	33.3	41.1	46.5	51.9	78.4	115.6	148.9	150.9
95°	34.3	38.2	48.0	56.8	72.5	84.2	96.0	141.1	226.3	340.0	384.0
97.5°	50.9	56.8	67.6	80.3	98.0	111.2	124.4	182.2	300.8	484.0	626.0
100°	75.4	78.4	87.2	102.9	122.5	136.2	149.9	201.8	321.3	532.9	774.0
102.5°	98.0	99.9	108.7	124.4	145.0	158.7	172.4	219.4	322.3	514.3	778.8
105°	119.5	123.4	130.3	145.0	166.5	180.2	194.0	240.0	327.2	488.9	725.9
107.5°	143.0	146.0	152.8	166.5	188.1	201.8	215.5	260.6	338.0	475.1	677.0
110°	166.5	170.5	176.3	189.1	209.7	223.9	238.1	281.2	351.7	471.2	643.7

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	188.1	192.0	198.9	210.6	230.2	244.9	259.6	300.8	366.4	472.2	622.1
115°	210.6	215.5	221.4	233.2	252.8	266.0	279.2	321.3	381.1	476.1	607.4
117.5°	234.1	238.1	243.9	254.7	273.3	287.0	300.8	340.0	396.8	482.0	599.6
120°	255.7	259.6	265.5	274.3	293.9	307.6	321.3	359.5	412.4	487.9	592.7
122.5°	276.3	279.2	285.1	294.9	314.5	328.7	342.9	378.2	426.2	494.7	588.8
125°	293.9	296.8	302.7	314.5	334.1	347.8	361.5	396.8	440.9	501.6	583.9
127.5°	308.6	312.5	320.4	333.1	351.7	365.9	380.1	414.4	454.6	508.5	581.0
130°	321.3	325.3	335.1	348.8	368.4	382.1	395.8	430.1	467.3	516.3	579.0
132.5°	333.1	338.0	348.8	363.5	384.0	397.8	411.5	443.8	480.0	524.1	578.0
135°	344.8	348.8	360.5	375.2	397.8	411.5	425.2	456.5	490.8	530.0	577.0
137.5°	355.6	360.5	372.3	388.0	410.5	423.2	436.0	467.3	499.6	535.9	577.0
140°	368.4	372.3	384.0	399.7	421.3	434.0	446.7	476.1	506.5	539.8	576.1
142.5°	381.1	384.0	394.8	410.5	431.1	442.8	454.6	483.0	512.4	542.7	576.1
145°	393.8	397.8	407.5	422.2	441.8	452.6	463.4	489.8	517.3	544.7	574.1
147.5°	407.5	410.5	420.3	434.0	450.7	460.4	470.2	495.7	520.2	545.7	571.2
150°	421.3	424.2	432.0	444.8	459.5	468.3	477.1	499.6	522.2	544.7	568.2
152.5°	435.0	436.0	443.8	454.6	468.3	476.2	484.0	503.6	523.2	542.7	563.3
155°	447.7	448.7	454.6	465.4	476.1	483.4	490.8	507.5	524.1	540.8	557.4
157.5°	458.5	459.5	464.4	474.2	483.0	489.4	495.7	510.4	524.1	536.9	551.6
160°	469.3	470.2	474.2	482.0	489.8	495.2	500.6	512.4	524.1	533.9	545.7
162.5°	480.0	479.1	483.0	488.9	495.7	499.6	503.6	513.4	523.2	531.0	540.8
165°	487.9	486.9	488.9	494.7	499.6	502.6	505.5	514.3	521.2	527.1	533.9
167.5°	494.7	493.8	495.7	499.6	503.6	505.6	507.5	514.3	520.2	523.2	528.1
170°	501.6	499.6	500.6	503.6	505.5	507.0	508.5	513.4	518.3	520.2	523.2
172.5°	505.5	504.5	503.6	506.5	507.5	508.4	509.4	512.4	515.3	516.3	517.3
175°	508.5	507.5	506.5	508.5	508.5	509.0	509.4	511.4	513.4	512.4	513.4
177.5°	510.4	508.5	507.5	509.4	509.4	509.4	509.4	510.4	512.4	510.4	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	2058.8	2060.3	2063.4	2078.6	2086.2	2087.7	2081.6	2095.3	2099.9	2095.3	2092.3
5°	2156.3	2165.4	2183.7	2203.5	2201.9	2203.5	2212.6	2221.7	2224.8	2212.6	2217.2
7.5°	2241.5	2259.8	2279.6	2310.1	2310.1	2325.3	2331.4	2339.0	2357.3	2348.1	2345.1
10°	2339.0	2363.4	2399.9	2448.6	2450.2	2465.4	2480.6	2505.0	2512.6	2506.5	2509.5
12.5°	2460.8	2508.0	2511.1	2564.4	2588.7	2591.8	2616.1	2611.6	2626.8	2626.8	2652.7
15°	2514.1	2587.2	2628.3	2680.1	2695.3	2677.1	2696.8	2718.2	2719.7	2719.7	2718.2
17.5°	2610.1	2639.0	2680.1	2707.5	2713.6	2713.6	2715.1	2724.3	2718.2	2706.0	2715.1
20°	2629.8	2642.0	2657.3	2654.2	2657.3	2642.0	2626.8	2611.6	2613.1	2605.5	2628.3
22.5°	2593.3	2590.3	2555.2	2532.4	2532.4	2501.9	2473.0	2459.3	2445.6	2450.2	2457.8
25°	2501.9	2454.7	2412.1	2378.6	2371.0	2322.2	2282.7	2270.5	2247.6	2265.9	2268.9
27.5°	2355.7	2302.4	2233.9	2205.0	2165.4	2145.6	2118.2	2081.6	2034.4	2061.8	2057.3
30°	2198.9	2119.7	2063.4	1993.3	1930.9	1926.3	1874.5	1813.6	1789.3	1789.3	1803.0
32.5°	2023.8	1918.7	1836.5	1737.5	1676.6	1650.7	1588.3	1527.4	1541.1	1495.4	1512.1
35°	1819.7	1681.2	1577.6	1481.7	1436.0	1405.5	1324.8	1291.3	1254.8	1233.5	1273.0
37.5°	1624.8	1464.9	1332.4	1227.4	1210.6	1155.8	1101.0	1079.7	1058.3	1067.5	1065.9
40°	1387.3	1245.6	1126.9	1044.6	1015.7	989.8	953.3	927.4	913.7	921.3	922.8
42.5°	1172.5	1053.8	965.4	907.6	883.2	864.9	846.7	825.3	820.8	820.8	826.9
45°	1006.6	909.1	849.7	802.5	788.8	775.1	761.4	752.3	749.2	743.1	747.7
47.5°	874.1	796.4	759.9	724.8	709.6	706.6	694.4	689.8	683.7	682.2	683.7
50°	762.9	714.2	680.7	660.9	650.2	645.7	639.6	630.4	627.4	635.0	632.0
52.5°	685.3	639.6	621.3	601.5	595.4	589.3	580.2	581.7	580.2	577.1	577.1
55°	607.6	578.7	560.4	545.2	543.6	537.5	529.9	526.9	525.4	522.3	526.9
57.5°	545.2	522.3	505.6	491.9	485.8	485.8	478.2	472.1	472.1	470.5	472.1
60°	482.7	459.9	449.2	435.5	430.9	429.4	424.9	421.8	417.2	417.2	417.2
62.5°	424.9	406.6	394.4	382.2	383.7	376.1	370.0	367.0	367.0	368.5	368.5
65°	370.0	357.9	342.6	332.0	328.9	327.4	324.4	322.8	318.3	321.3	321.3
67.5°	319.8	303.0	293.9	289.3	284.8	283.2	280.2	277.1	275.6	274.1	277.1
70°	269.5	255.8	248.2	245.2	240.6	239.1	237.6	233.0	234.5	236.0	237.6
72.5°	223.8	211.7	210.1	201.0	201.0	201.0	194.9	198.0	196.4	193.4	196.4
75°	176.6	170.6	167.5	162.9	164.5	162.9	161.4	156.8	156.8	158.4	159.9
77.5°	140.1	134.0	132.5	127.9	124.9	127.9	124.9	123.3	123.3	124.9	124.9
80°	103.5	100.5	95.9	95.9	95.9	94.4	94.4	94.4	92.9	91.4	92.9
82.5°	68.5	68.5	67.0	65.5	67.0	64.0	65.5	65.5	65.5	65.5	65.5
85°	44.2	42.6	42.6	41.1	41.1	41.1	42.6	39.6	39.6	41.1	41.1
87.5°	19.8	19.8	19.8	21.3	19.8	19.8	19.8	21.3	19.8	19.8	19.8
90°	32.3	31.3	29.4	31.3	31.8	32.3	32.3	32.3	32.3	32.3	32.3
92.5°	126.4	98.9	84.3	73.5	69.6	65.6	64.7	60.7	61.7	59.8	61.7
95°	336.0	256.7	196.9	155.8	145.0	134.2	121.5	113.6	110.7	111.7	110.7
97.5°	630.9	525.1	419.3	320.4	291.0	261.6	223.4	203.8	193.0	187.1	193.0
100°	915.0	894.5	773.0	638.8	579.5	520.2	438.9	396.8	368.4	350.7	368.4
102.5°	1020.8	1136.4	1132.5	1043.4	979.7	916.0	825.9	746.5	709.3	683.8	709.3
105°	986.5	1190.3	1301.0	1313.8	1297.6	1281.4	1220.7	1159.9	1117.8	1104.1	1117.8
107.5°	914.0	1132.5	1297.1	1393.1	1412.7	1432.3	1431.3	1422.5	1409.8	1387.2	1409.8
110°	846.4	1053.2	1228.5	1353.9	1394.1	1434.3	1476.4	1495.0	1503.8	1502.8	1503.8

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	799.4	980.7	1147.2	1283.4	1330.9	1378.4	1441.1	1475.4	1494.0	1500.9	1494.0
115°	762.2	923.8	1074.7	1203.1	1253.6	1304.0	1373.5	1418.6	1444.1	1452.9	1444.1
117.5°	736.7	876.8	1012.0	1131.5	1179.5	1227.5	1299.1	1347.1	1373.5	1380.4	1373.5
120°	717.1	843.5	965.0	1068.8	1113.4	1158.0	1226.6	1272.6	1301.0	1310.8	1301.0
122.5°	700.5	817.1	925.8	1022.8	1062.0	1101.2	1160.9	1206.0	1230.5	1238.3	1230.5
125°	684.8	791.6	892.5	978.7	1015.4	1052.2	1109.0	1146.2	1170.7	1178.6	1170.7
127.5°	670.1	766.1	859.2	941.5	975.8	1010.1	1060.0	1095.3	1116.8	1122.7	1116.8
130°	655.4	741.6	825.9	903.3	935.6	967.9	1015.9	1049.2	1068.8	1076.7	1068.8
132.5°	643.7	718.1	794.5	864.1	894.0	923.8	970.9	1004.2	1021.8	1028.7	1021.8
135°	632.9	696.6	761.2	825.9	853.3	880.7	922.9	955.2	972.8	976.7	972.8
137.5°	625.0	678.9	734.8	787.7	812.2	836.7	876.8	905.2	920.9	926.8	920.9
140°	618.2	662.3	709.3	754.4	776.0	797.5	828.8	854.3	869.0	874.9	869.0
142.5°	611.3	648.6	686.8	724.0	741.2	758.3	787.7	810.2	822.9	822.9	822.9
145°	605.4	635.8	668.1	698.5	712.7	726.9	750.4	767.1	776.9	779.8	776.9
147.5°	599.6	626.0	652.5	677.0	687.8	698.5	719.1	732.8	739.7	741.6	739.7
150°	591.7	615.2	636.8	657.4	666.2	675.0	689.7	701.5	707.3	708.3	707.3
152.5°	584.9	604.5	624.1	640.7	648.0	655.4	666.2	676.0	679.9	679.9	679.9
155°	576.1	594.7	610.3	625.0	630.4	635.8	646.6	653.4	657.4	655.4	657.4
157.5°	568.2	582.9	596.6	609.4	613.8	618.2	626.0	631.9	633.9	633.9	633.9
160°	559.4	572.1	582.9	593.7	597.1	600.5	607.4	612.3	613.3	613.3	613.3
162.5°	551.6	561.4	570.2	579.0	581.4	583.9	590.7	593.7	594.7	593.7	594.7
165°	542.7	550.6	557.4	564.3	566.2	568.2	572.1	576.1	576.1	575.1	576.1
167.5°	533.9	539.8	545.7	550.6	552.6	554.5	556.5	558.4	558.4	557.4	558.4
170°	527.1	532.0	534.9	538.8	539.8	540.8	541.8	544.7	543.7	541.8	543.7
172.5°	520.2	523.2	525.1	528.1	528.6	529.0	530.0	531.0	530.0	529.0	530.0
175°	514.3	517.3	518.3	519.2	519.7	520.2	520.2	521.2	520.2	518.3	520.2
177.5°	510.4	512.4	512.4	513.4	513.4	513.4	513.4	513.4	512.4	510.4	512.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	2099.9	2089.3	2080.1	2081.6	2089.3	2083.2	2067.9	2048.1	2040.5	2031.4	2040.5
5°	2226.3	2217.2	2198.9	2200.4	2195.9	2189.8	2165.4	2134.9	2134.9	2110.6	2107.5
7.5°	2351.2	2337.5	2325.3	2322.2	2305.5	2293.3	2272.0	2229.4	2212.6	2183.7	2166.9
10°	2491.3	2480.6	2466.9	2450.2	2441.0	2419.7	2384.7	2322.2	2291.8	2252.2	2223.3
12.5°	2632.9	2631.4	2600.9	2567.4	2565.9	2532.4	2508.0	2424.3	2383.2	2329.9	2261.3
15°	2722.7	2715.1	2698.4	2681.6	2686.2	2649.6	2594.8	2495.8	2468.4	2404.5	2331.4
17.5°	2721.2	2721.2	2716.6	2713.6	2709.0	2698.4	2667.9	2602.4	2558.3	2477.6	2409.0
20°	2634.4	2654.2	2658.8	2657.3	2672.5	2680.1	2678.6	2637.5	2602.4	2530.9	2460.8
22.5°	2460.8	2506.5	2526.3	2538.5	2570.5	2587.2	2626.8	2611.6	2602.4	2549.1	2489.8
25°	2299.4	2314.6	2374.0	2377.1	2421.2	2462.3	2501.9	2527.8	2561.3	2541.5	2491.3
27.5°	2090.8	2125.8	2168.4	2200.4	2209.6	2293.3	2358.8	2407.5	2483.7	2489.8	2473.0
30°	1854.7	1871.5	1941.5	1984.2	2032.9	2093.8	2188.2	2272.0	2340.5	2403.0	2424.3
32.5°	1566.9	1635.5	1676.6	1728.4	1771.0	1879.1	1994.8	2103.0	2182.1	2287.2	2332.9
35°	1303.5	1356.8	1426.8	1448.2	1525.8	1617.2	1768.0	1906.5	2026.8	2133.4	2226.3
37.5°	1085.7	1128.4	1203.0	1236.5	1282.2	1399.4	1525.8	1697.9	1842.6	1973.5	2089.3
40°	936.5	968.5	1024.8	1035.5	1073.6	1180.2	1282.2	1443.6	1635.5	1812.1	1938.5
42.5°	834.5	849.7	887.8	901.5	925.9	997.4	1088.8	1241.1	1419.2	1602.0	1780.1
45°	761.4	772.1	794.9	807.1	837.5	869.5	944.1	1065.9	1206.0	1390.3	1582.2
47.5°	695.9	709.6	718.8	726.4	743.1	778.1	826.9	916.7	1050.7	1219.7	1405.5
50°	641.1	645.7	662.4	663.9	674.6	697.4	743.1	797.9	904.5	1041.6	1221.3
52.5°	586.3	590.8	601.5	612.2	616.7	635.0	665.5	711.1	790.3	898.4	1058.3
55°	531.5	537.5	548.2	555.8	560.4	575.6	593.9	638.0	700.5	776.6	907.6
57.5°	476.6	490.3	493.4	498.0	505.6	522.3	539.1	565.0	613.7	683.7	779.7
60°	424.9	429.4	440.1	444.7	452.3	461.4	482.7	502.5	537.5	592.4	679.2
62.5°	371.6	382.2	386.8	391.4	397.4	408.1	421.8	443.1	473.6	517.7	586.3
65°	325.9	327.4	336.5	342.6	348.7	356.3	370.0	389.8	408.1	449.2	499.5
67.5°	281.7	284.8	287.8	293.9	301.5	309.1	321.3	332.0	354.8	382.2	421.8
70°	239.1	239.1	246.7	251.3	249.7	258.9	268.0	280.2	296.9	322.8	354.8
72.5°	201.0	199.5	205.6	207.1	210.1	216.2	222.3	234.5	243.6	263.4	287.8
75°	159.9	162.9	166.0	166.0	170.6	175.1	181.2	187.3	198.0	210.1	228.4
77.5°	126.4	126.4	129.4	131.0	135.5	134.0	140.1	146.2	153.8	164.5	178.2
80°	92.9	95.9	95.9	95.9	97.5	99.0	105.1	109.6	114.2	121.8	127.9
82.5°	65.5	65.5	68.5	68.5	68.5	71.6	71.6	73.1	76.1	80.7	85.3
85°	41.1	41.1	41.1	42.6	41.1	42.6	45.7	44.2	45.7	48.7	48.7
87.5°	19.8	19.8	19.8	19.8	19.8	21.3	19.8	21.3	22.8	22.8	22.8
90°	32.3	32.3	32.3	31.8	31.3	29.4	31.3	32.3	33.3	32.3	26.5
92.5°	60.7	64.7	65.6	69.6	73.5	84.3	98.9	126.4	150.9	148.9	115.6
95°	113.6	121.5	134.2	145.0	155.8	196.9	256.7	336.0	384.0	340.0	226.3
97.5°	203.8	223.4	261.6	291.0	320.4	419.3	525.1	630.9	626.0	484.0	300.8
100°	396.8	438.9	520.2	579.5	638.8	773.0	894.5	915.0	774.0	532.9	321.3
102.5°	746.5	825.9	916.0	979.7	1043.4	1132.5	1136.4	1020.8	778.8	514.3	322.3
105°	1159.9	1220.7	1281.4	1297.6	1313.8	1301.0	1190.3	986.5	725.9	488.9	327.2
107.5°	1422.5	1431.3	1432.3	1412.7	1393.1	1297.1	1132.5	914.0	677.0	475.1	338.0
110°	1495.0	1476.4	1434.3	1394.1	1353.9	1228.5	1053.2	846.4	643.7	471.2	351.7

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1475.4	1441.1	1378.4	1330.9	1283.4	1147.2	980.7	799.4	622.1	472.2	366.4
115°	1418.6	1373.5	1304.0	1253.6	1203.1	1074.7	923.8	762.2	607.4	476.1	381.1
117.5°	1347.1	1299.1	1227.5	1179.5	1131.5	1012.0	876.8	736.7	599.6	482.0	396.8
120°	1272.6	1226.6	1158.0	1113.4	1068.8	965.0	843.5	717.1	592.7	487.9	412.4
122.5°	1206.0	1160.9	1101.2	1062.0	1022.8	925.8	817.1	700.5	588.8	494.7	426.2
125°	1146.2	1109.0	1052.2	1015.4	978.7	892.5	791.6	684.8	583.9	501.6	440.9
127.5°	1095.3	1060.0	1010.1	975.8	941.5	859.2	766.1	670.1	581.0	508.5	454.6
130°	1049.2	1015.9	967.9	935.6	903.3	825.9	741.6	655.4	579.0	516.3	467.3
132.5°	1004.2	970.9	923.8	894.0	864.1	794.5	718.1	643.7	578.0	524.1	480.0
135°	955.2	922.9	880.7	853.3	825.9	761.2	696.6	632.9	577.0	530.0	490.8
137.5°	905.2	876.8	836.7	812.2	787.7	734.8	678.9	625.0	577.0	535.9	499.6
140°	854.3	828.8	797.5	776.0	754.4	709.3	662.3	618.2	576.1	539.8	506.5
142.5°	810.2	787.7	758.3	741.2	724.0	686.8	648.6	611.3	576.1	542.7	512.4
145°	767.1	750.4	726.9	712.7	698.5	668.1	635.8	605.4	574.1	544.7	517.3
147.5°	732.8	719.1	698.5	687.8	677.0	652.5	626.0	599.6	571.2	545.7	520.2
150°	701.5	689.7	675.0	666.2	657.4	636.8	615.2	591.7	568.2	544.7	522.2
152.5°	676.0	666.2	655.4	648.0	640.7	624.1	604.5	584.9	563.3	542.7	523.2
155°	653.4	646.6	635.8	630.4	625.0	610.3	594.7	576.1	557.4	540.8	524.1
157.5°	631.9	626.0	618.2	613.8	609.4	596.6	582.9	568.2	551.6	536.9	524.1
160°	612.3	607.4	600.5	597.1	593.7	582.9	572.1	559.4	545.7	533.9	524.1
162.5°	593.7	590.7	583.9	581.4	579.0	570.2	561.4	551.6	540.8	531.0	523.2
165°	576.1	572.1	568.2	566.2	564.3	557.4	550.6	542.7	533.9	527.1	521.2
167.5°	558.4	556.5	554.5	552.6	550.6	545.7	539.8	533.9	528.1	523.2	520.2
170°	544.7	541.8	540.8	539.8	538.8	534.9	532.0	527.1	523.2	520.2	518.3
172.5°	531.0	530.0	529.0	528.6	528.1	525.1	523.2	520.2	517.3	516.3	515.3
175°	521.2	520.2	520.2	519.7	519.2	518.3	517.3	514.3	513.4	512.4	513.4
177.5°	513.4	513.4	513.4	513.4	513.4	512.4	512.4	510.4	509.4	510.4	512.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	2032.9	2025.3	2020.7	2023.8	2014.6	1991.8	1991.8	1999.4	1990.3	1981.1	1967.4
5°	2089.3	2074.0	2064.9	2063.4	2042.1	2005.5	1997.9	1990.3	1970.5	1949.2	1926.3
7.5°	2144.1	2116.7	2101.4	2090.8	2060.3	2013.1	1993.3	1976.6	1944.6	1912.6	1883.7
10°	2189.8	2150.2	2131.9	2115.1	2075.6	2016.2	1984.2	1953.7	1912.6	1871.5	1835.0
12.5°	2226.3	2180.6	2157.8	2133.4	2084.7	2007.0	1967.4	1918.7	1877.6	1822.8	1786.2
15°	2287.2	2192.8	2171.5	2148.6	2098.4	1991.8	1943.1	1888.3	1831.9	1758.8	1719.2
17.5°	2335.9	2209.6	2208.0	2159.3	2093.8	1985.7	1911.1	1839.5	1778.6	1705.5	1643.1
20°	2364.9	2235.4	2211.1	2160.8	2078.6	1944.6	1866.9	1787.7	1722.3	1633.9	1571.5
22.5°	2389.2	2272.0	2208.0	2147.1	2046.6	1930.9	1816.7	1742.1	1652.2	1556.3	1496.9
25°	2398.4	2279.6	2212.6	2142.6	2023.8	1891.3	1761.9	1681.2	1580.6	1493.9	1413.1
27.5°	2399.9	2278.1	2195.9	2122.8	1991.8	1839.5	1707.0	1621.8	1510.6	1410.1	1329.4
30°	2384.7	2261.3	2186.7	2107.5	1961.3	1792.3	1640.0	1545.6	1426.8	1326.3	1242.6
32.5°	2339.0	2227.8	2166.9	2080.1	1921.8	1726.8	1576.1	1471.0	1346.1	1247.2	1166.5
35°	2262.9	2186.7	2119.7	2039.0	1870.0	1665.9	1512.1	1388.8	1262.4	1168.0	1091.8
37.5°	2168.4	2127.3	2064.9	1985.7	1810.6	1611.1	1440.6	1303.5	1177.1	1085.7	1011.1
40°	2040.5	2051.2	1990.3	1918.7	1740.5	1536.5	1347.7	1216.7	1097.9	1012.7	939.6
42.5°	1902.0	1946.1	1911.1	1842.6	1662.9	1454.3	1279.1	1134.5	1018.7	930.4	869.5
45°	1752.7	1828.9	1807.5	1757.3	1582.2	1367.5	1181.7	1041.6	939.6	854.3	801.0
47.5°	1589.8	1697.9	1697.9	1661.4	1492.3	1280.7	1097.9	954.8	854.3	793.4	741.6
50°	1423.8	1545.6	1565.4	1541.1	1391.8	1181.7	995.9	866.5	779.7	720.3	682.2
52.5°	1250.2	1391.8	1428.4	1416.2	1285.2	1087.3	912.1	785.8	706.6	654.8	621.3
55°	1084.2	1248.7	1288.3	1292.8	1171.0	983.7	819.3	708.1	632.0	596.9	568.0
57.5°	927.4	1085.7	1129.9	1137.5	1055.3	889.3	732.5	635.0	566.5	537.5	514.7
60°	793.4	925.9	983.7	1000.5	928.9	779.7	651.8	557.3	505.6	478.2	456.8
62.5°	683.7	790.3	851.2	855.8	823.8	683.7	568.0	488.8	444.7	420.3	409.6
65°	577.1	673.1	709.6	727.9	702.0	592.4	490.3	424.9	389.8	368.5	357.9
67.5°	491.9	552.8	583.2	607.6	581.7	499.5	417.2	363.9	338.1	316.7	310.6
70°	403.5	453.8	476.6	501.0	478.2	415.7	356.3	307.6	284.8	268.0	260.4
72.5°	322.8	362.4	383.7	399.0	385.3	333.5	284.8	251.3	234.5	222.3	217.8
75°	255.8	283.2	295.4	306.1	300.0	260.4	229.9	202.5	187.3	176.6	173.6
77.5°	194.9	214.7	228.4	231.5	223.8	198.0	172.1	155.3	143.1	137.1	134.0
80°	138.6	150.8	158.4	162.9	155.3	144.7	126.4	114.2	103.5	95.9	94.4
82.5°	92.9	99.0	105.1	103.5	100.5	91.4	80.7	74.6	70.0	64.0	64.0
85°	53.3	54.8	57.9	59.4	57.9	51.8	45.7	42.6	39.6	35.0	35.0
87.5°	22.8	24.4	24.4	25.9	22.8	22.8	19.8	16.8	16.8	15.2	13.7
90°	19.6	14.7	13.2	11.8	9.8	7.8	3.9	1.0	3.9	7.8	9.8
92.5°	78.4	51.9	46.5	41.1	33.3	28.4	20.6	14.7	20.6	28.4	33.3
95°	141.1	96.0	84.2	72.5	56.8	48.0	38.2	34.3	38.2	48.0	56.8
97.5°	182.2	124.4	111.2	98.0	80.3	67.6	56.8	50.9	56.8	67.6	80.3
100°	201.8	149.9	136.2	122.5	102.9	87.2	78.4	75.4	78.4	87.2	102.9
102.5°	219.4	172.4	158.7	145.0	124.4	108.7	99.9	98.0	99.9	108.7	124.4
105°	240.0	194.0	180.2	166.5	145.0	130.3	123.4	119.5	123.4	130.3	145.0
107.5°	260.6	215.5	201.8	188.1	166.5	152.8	146.0	143.0	146.0	152.8	166.5
110°	281.2	238.1	223.9	209.7	189.1	176.3	170.5	166.5	170.5	176.3	189.1

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	300.8	259.6	244.9	230.2	210.6	198.9	192.0	188.1	192.0	198.9	210.6
115°	321.3	279.2	266.0	252.8	233.2	221.4	215.5	210.6	215.5	221.4	233.2
117.5°	340.0	300.8	287.0	273.3	254.7	243.9	238.1	234.1	238.1	243.9	254.7
120°	359.5	321.3	307.6	293.9	274.3	265.5	259.6	255.7	259.6	265.5	274.3
122.5°	378.2	342.9	328.7	314.5	294.9	285.1	279.2	276.3	279.2	285.1	294.9
125°	396.8	361.5	347.8	334.1	314.5	302.7	296.8	293.9	296.8	302.7	314.5
127.5°	414.4	380.1	365.9	351.7	333.1	320.4	312.5	308.6	312.5	320.4	333.1
130°	430.1	395.8	382.1	368.4	348.8	335.1	325.3	321.3	325.3	335.1	348.8
132.5°	443.8	411.5	397.8	384.0	363.5	348.8	338.0	333.1	338.0	348.8	363.5
135°	456.5	425.2	411.5	397.8	375.2	360.5	348.8	344.8	348.8	360.5	375.2
137.5°	467.3	436.0	423.2	410.5	388.0	372.3	360.5	355.6	360.5	372.3	388.0
140°	476.1	446.7	434.0	421.3	399.7	384.0	372.3	368.4	372.3	384.0	399.7
142.5°	483.0	454.6	442.8	431.1	410.5	394.8	384.0	381.1	384.0	394.8	410.5
145°	489.8	463.4	452.6	441.8	422.2	407.5	397.8	393.8	397.8	407.5	422.2
147.5°	495.7	470.2	460.4	450.7	434.0	420.3	410.5	407.5	410.5	420.3	434.0
150°	499.6	477.1	468.3	459.5	444.8	432.0	424.2	421.3	424.2	432.0	444.8
152.5°	503.6	484.0	476.2	468.3	454.6	443.8	436.0	435.0	436.0	443.8	454.6
155°	507.5	490.8	483.4	476.1	465.4	454.6	448.7	447.7	448.7	454.6	465.4
157.5°	510.4	495.7	489.4	483.0	474.2	464.4	459.5	458.5	459.5	464.4	474.2
160°	512.4	500.6	495.2	489.8	482.0	474.2	470.2	469.3	470.2	474.2	482.0
162.5°	513.4	503.6	499.6	495.7	488.9	483.0	479.1	480.0	479.1	483.0	488.9
165°	514.3	505.5	502.6	499.6	494.7	488.9	486.9	487.9	486.9	488.9	494.7
167.5°	514.3	507.5	505.6	503.6	499.6	495.7	493.8	494.7	493.8	495.7	499.6
170°	513.4	508.5	507.0	505.5	503.6	500.6	499.6	501.6	499.6	500.6	503.6
172.5°	512.4	509.4	508.4	507.5	506.5	503.6	504.5	505.5	504.5	503.6	506.5
175°	511.4	509.4	509.0	508.5	508.5	506.5	507.5	508.5	507.5	506.5	508.5
177.5°	510.4	509.4	509.4	509.4	509.4	507.5	508.5	510.4	508.5	507.5	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	1959.8	1967.4	1965.9	1950.7	1933.9	1920.2	1894.3	1897.4	1888.3	1889.8	1898.9
5°	1911.1	1911.1	1905.0	1883.7	1856.3	1841.0	1812.1	1804.5	1786.2	1784.7	1783.2
7.5°	1859.3	1851.7	1844.1	1813.6	1780.1	1755.8	1716.2	1707.0	1688.8	1676.6	1670.5
10°	1798.4	1787.7	1772.5	1737.5	1696.4	1665.9	1624.8	1612.6	1577.6	1562.4	1553.2
12.5°	1731.4	1725.3	1700.9	1672.0	1605.0	1571.5	1512.1	1524.3	1489.3	1458.8	1454.3
15°	1664.4	1641.6	1627.9	1580.6	1499.9	1484.7	1437.5	1413.1	1381.2	1356.8	1356.8
17.5°	1598.9	1563.9	1533.4	1483.2	1423.8	1381.2	1346.1	1334.0	1294.4	1270.0	1265.4
20°	1512.1	1472.5	1464.9	1393.3	1352.2	1305.0	1271.5	1241.1	1212.1	1201.5	1193.9
22.5°	1429.9	1384.2	1372.0	1311.1	1270.0	1222.8	1189.3	1168.0	1146.7	1139.0	1125.3
25°	1341.6	1314.2	1295.9	1230.4	1184.7	1140.6	1117.7	1102.5	1082.7	1081.2	1072.0
27.5°	1256.3	1230.4	1212.1	1149.7	1116.2	1075.1	1056.8	1040.1	1029.4	1024.8	1020.3
30°	1183.2	1154.3	1133.0	1087.3	1046.2	1012.7	997.4	986.8	980.7	973.1	971.5
32.5°	1102.5	1085.7	1056.8	1021.8	989.8	957.8	948.7	941.1	931.9	928.9	927.4
35°	1034.0	1011.1	992.9	953.3	939.6	912.1	901.5	895.4	883.2	880.2	877.1
37.5°	967.0	945.6	925.9	901.5	875.6	860.4	854.3	845.1	839.1	840.6	837.5
40°	900.0	883.2	868.0	842.1	826.9	819.3	807.1	797.9	794.9	796.4	794.9
42.5°	834.5	819.3	810.1	790.3	775.1	767.5	759.9	750.7	755.3	755.3	759.9
45°	775.1	761.4	755.3	740.1	730.9	718.8	711.1	709.6	715.7	714.2	714.2
47.5°	714.2	709.6	702.0	688.3	676.1	668.5	667.0	667.0	673.1	676.1	674.6
50°	667.0	657.8	648.7	638.0	628.9	625.9	621.3	624.3	630.4	630.4	633.5
52.5°	607.6	601.5	598.5	589.3	583.2	583.2	583.2	584.7	589.3	593.9	592.4
55°	555.8	551.2	548.2	543.6	536.0	537.5	536.0	539.1	543.6	548.2	551.2
57.5°	501.0	499.5	496.4	488.8	488.8	487.3	491.9	493.4	501.0	504.0	508.6
60°	452.3	447.7	447.7	441.6	441.6	441.6	446.2	450.7	456.8	458.4	461.4
62.5°	400.5	400.5	399.0	394.4	394.4	399.0	400.5	406.6	409.6	409.6	414.2
65°	351.8	350.2	348.7	350.2	351.8	351.8	356.3	359.4	362.4	363.9	365.5
67.5°	303.0	301.5	304.6	303.0	306.1	312.2	310.6	315.2	319.8	319.8	321.3
70°	257.4	260.4	258.9	261.9	260.4	263.4	268.0	269.5	269.5	271.1	275.6
72.5°	214.7	214.7	214.7	213.2	214.7	217.8	220.8	222.3	225.4	226.9	231.5
75°	173.6	173.6	170.6	173.6	173.6	176.6	179.7	179.7	179.7	182.7	187.3
77.5°	131.0	132.5	131.0	134.0	134.0	135.5	138.6	137.1	140.1	141.6	143.1
80°	95.9	94.4	94.4	94.4	95.9	95.9	99.0	100.5	100.5	105.1	102.0
82.5°	60.9	62.4	60.9	62.4	62.4	64.0	62.4	64.0	65.5	68.5	67.0
85°	35.0	33.5	33.5	35.0	33.5	33.5	35.0	33.5	35.0	33.5	35.0
87.5°	13.7	12.2	12.2	12.2	12.2	10.7	10.7	9.1	9.1	9.1	7.6
90°	11.8	13.2	14.7	19.6	26.5	32.3	33.3	32.3	31.3	29.4	31.3
92.5°	41.1	46.5	51.9	78.4	115.6	148.9	150.9	126.4	98.9	84.3	73.5
95°	72.5	84.2	96.0	141.1	226.3	340.0	384.0	336.0	256.7	196.9	155.8
97.5°	98.0	111.2	124.4	182.2	300.8	484.0	626.0	630.9	525.1	419.3	320.4
100°	122.5	136.2	149.9	201.8	321.3	532.9	774.0	915.0	894.5	773.0	638.8
102.5°	145.0	158.7	172.4	219.4	322.3	514.3	778.8	1020.8	1136.4	1132.5	1043.4
105°	166.5	180.2	194.0	240.0	327.2	488.9	725.9	986.5	1190.3	1301.0	1313.8
107.5°	188.1	201.8	215.5	260.6	338.0	475.1	677.0	914.0	1132.5	1297.1	1393.1
110°	209.7	223.9	238.1	281.2	351.7	471.2	643.7	846.4	1053.2	1228.5	1353.9

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	230.2	244.9	259.6	300.8	366.4	472.2	622.1	799.4	980.7	1147.2	1283.4
115°	252.8	266.0	279.2	321.3	381.1	476.1	607.4	762.2	923.8	1074.7	1203.1
117.5°	273.3	287.0	300.8	340.0	396.8	482.0	599.6	736.7	876.8	1012.0	1131.5
120°	293.9	307.6	321.3	359.5	412.4	487.9	592.7	717.1	843.5	965.0	1068.8
122.5°	314.5	328.7	342.9	378.2	426.2	494.7	588.8	700.5	817.1	925.8	1022.8
125°	334.1	347.8	361.5	396.8	440.9	501.6	583.9	684.8	791.6	892.5	978.7
127.5°	351.7	365.9	380.1	414.4	454.6	508.5	581.0	670.1	766.1	859.2	941.5
130°	368.4	382.1	395.8	430.1	467.3	516.3	579.0	655.4	741.6	825.9	903.3
132.5°	384.0	397.8	411.5	443.8	480.0	524.1	578.0	643.7	718.1	794.5	864.1
135°	397.8	411.5	425.2	456.5	490.8	530.0	577.0	632.9	696.6	761.2	825.9
137.5°	410.5	423.2	436.0	467.3	499.6	535.9	577.0	625.0	678.9	734.8	787.7
140°	421.3	434.0	446.7	476.1	506.5	539.8	576.1	618.2	662.3	709.3	754.4
142.5°	431.1	442.8	454.6	483.0	512.4	542.7	576.1	611.3	648.6	686.8	724.0
145°	441.8	452.6	463.4	489.8	517.3	544.7	574.1	605.4	635.8	668.1	698.5
147.5°	450.7	460.4	470.2	495.7	520.2	545.7	571.2	599.6	626.0	652.5	677.0
150°	459.5	468.3	477.1	499.6	522.2	544.7	568.2	591.7	615.2	636.8	657.4
152.5°	468.3	476.2	484.0	503.6	523.2	542.7	563.3	584.9	604.5	624.1	640.7
155°	476.1	483.4	490.8	507.5	524.1	540.8	557.4	576.1	594.7	610.3	625.0
157.5°	483.0	489.4	495.7	510.4	524.1	536.9	551.6	568.2	582.9	596.6	609.4
160°	489.8	495.2	500.6	512.4	524.1	533.9	545.7	559.4	572.1	582.9	593.7
162.5°	495.7	499.6	503.6	513.4	523.2	531.0	540.8	551.6	561.4	570.2	579.0
165°	499.6	502.6	505.5	514.3	521.2	527.1	533.9	542.7	550.6	557.4	564.3
167.5°	503.6	505.6	507.5	514.3	520.2	523.2	528.1	533.9	539.8	545.7	550.6
170°	505.5	507.0	508.5	513.4	518.3	520.2	523.2	527.1	532.0	534.9	538.8
172.5°	507.5	508.4	509.4	512.4	515.3	516.3	517.3	520.2	523.2	525.1	528.1
175°	508.5	509.0	509.4	511.4	513.4	512.4	513.4	514.3	517.3	518.3	519.2
177.5°	509.4	509.4	509.4	510.4	512.4	510.4	509.4	510.4	512.4	512.4	513.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	1888.3	1892.8	1882.2	1879.1	1882.2	1871.5	1874.5	1877.6	1877.6	1882.2	1885.2
5°	1778.6	1772.5	1761.9	1758.8	1755.8	1760.3	1757.3	1761.9	1763.4	1774.0	1775.6
7.5°	1670.5	1661.4	1652.2	1643.1	1640.0	1632.4	1640.0	1640.0	1650.7	1647.7	1655.3
10°	1542.6	1541.1	1528.9	1524.3	1518.2	1506.0	1522.8	1518.2	1525.8	1539.5	1542.6
12.5°	1448.2	1431.4	1439.0	1417.7	1425.3	1413.1	1414.7	1414.7	1426.8	1428.4	1425.3
15°	1358.3	1344.6	1324.8	1315.7	1311.1	1305.0	1324.8	1326.3	1317.2	1338.5	1330.9
17.5°	1267.0	1267.0	1248.7	1244.1	1231.9	1238.0	1235.0	1236.5	1233.5	1248.7	1256.3
20°	1187.8	1180.2	1174.1	1175.6	1160.4	1157.3	1154.3	1157.3	1168.0	1178.6	1181.7
22.5°	1123.8	1119.2	1104.0	1107.1	1094.9	1099.4	1096.4	1104.0	1105.5	1105.5	1116.2
25°	1062.9	1056.8	1058.3	1052.2	1047.7	1047.7	1043.1	1047.7	1053.8	1056.8	1058.3
27.5°	1017.2	1012.7	1005.0	1000.5	1003.5	995.9	1002.0	1006.6	1006.6	1003.5	1006.6
30°	962.4	965.4	965.4	950.2	956.3	953.3	957.8	960.9	960.9	962.4	959.4
32.5°	925.9	916.7	915.2	913.7	913.7	907.6	907.6	912.1	913.7	915.2	919.8
35°	877.1	877.1	869.5	874.1	868.0	869.5	868.0	869.5	872.6	868.0	872.6
37.5°	833.0	834.5	831.4	834.5	836.0	833.0	829.9	836.0	833.0	833.0	829.9
40°	794.9	793.4	794.9	794.9	794.9	796.4	793.4	793.4	793.4	790.3	787.3
42.5°	762.9	753.8	756.8	758.3	753.8	753.8	755.3	753.8	758.3	749.2	749.2
45°	717.2	714.2	715.7	715.7	718.8	714.2	717.2	718.8	714.2	712.7	709.6
47.5°	676.1	679.2	676.1	679.2	679.2	682.2	676.1	677.6	679.2	673.1	668.5
50°	635.0	635.0	639.6	638.0	639.6	636.5	636.5	635.0	636.5	633.5	628.9
52.5°	596.9	592.4	600.0	598.5	596.9	595.4	593.9	595.4	592.4	589.3	589.3
55°	549.7	549.7	554.3	555.8	555.8	552.8	549.7	551.2	549.7	548.2	546.7
57.5°	511.7	505.6	508.6	510.1	510.1	505.6	508.6	505.6	505.6	507.1	502.5
60°	462.9	462.9	459.9	464.4	464.4	461.4	461.4	462.9	459.9	458.4	456.8
62.5°	411.2	412.7	417.2	418.8	420.3	417.2	414.2	415.7	415.7	411.2	412.7
65°	367.0	370.0	376.1	374.6	371.6	373.1	370.0	371.6	367.0	368.5	363.9
67.5°	324.4	322.8	324.4	324.4	327.4	325.9	322.8	322.8	321.3	325.9	321.3
70°	278.7	278.7	278.7	278.7	280.2	281.7	278.7	275.6	277.1	274.1	272.6
72.5°	231.5	233.0	231.5	234.5	229.9	233.0	233.0	231.5	229.9	229.9	229.9
75°	187.3	190.3	185.8	187.3	185.8	188.8	187.3	187.3	184.3	182.7	184.3
77.5°	143.1	144.7	141.6	143.1	141.6	143.1	143.1	141.6	141.6	141.6	141.6
80°	102.0	103.5	102.0	100.5	99.0	102.0	99.0	100.5	102.0	100.5	103.5
82.5°	65.5	65.5	64.0	65.5	62.4	62.4	64.0	64.0	62.4	65.5	62.4
85°	32.0	32.0	35.0	32.0	30.5	30.5	30.5	32.0	30.5	33.5	32.0
87.5°	7.6	6.1	7.6	7.6	6.1	6.1	7.6	6.1	7.6	9.1	6.1
90°	31.8	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	31.8
92.5°	69.6	65.6	64.7	60.7	61.7	59.8	61.7	60.7	64.7	65.6	69.6
95°	145.0	134.2	121.5	113.6	110.7	111.7	110.7	113.6	121.5	134.2	145.0
97.5°	291.0	261.6	223.4	203.8	193.0	187.1	193.0	203.8	223.4	261.6	291.0
100°	579.5	520.2	438.9	396.8	368.4	350.7	368.4	396.8	438.9	520.2	579.5
102.5°	979.7	916.0	825.9	746.5	709.3	683.8	709.3	746.5	825.9	916.0	979.7
105°	1297.6	1281.4	1220.7	1159.9	1117.8	1104.1	1117.8	1159.9	1220.7	1281.4	1297.6
107.5°	1412.7	1432.3	1431.3	1422.5	1409.8	1387.2	1409.8	1422.5	1431.3	1432.3	1412.7
110°	1394.1	1434.3	1476.4	1495.0	1503.8	1502.8	1503.8	1495.0	1476.4	1434.3	1394.1

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1330.9	1378.4	1441.1	1475.4	1494.0	1500.9	1494.0	1475.4	1441.1	1378.4	1330.9
115°	1253.6	1304.0	1373.5	1418.6	1444.1	1452.9	1444.1	1418.6	1373.5	1304.0	1253.6
117.5°	1179.5	1227.5	1299.1	1347.1	1373.5	1380.4	1373.5	1347.1	1299.1	1227.5	1179.5
120°	1113.4	1158.0	1226.6	1272.6	1301.0	1310.8	1301.0	1272.6	1226.6	1158.0	1113.4
122.5°	1062.0	1101.2	1160.9	1206.0	1230.5	1238.3	1230.5	1206.0	1160.9	1101.2	1062.0
125°	1015.4	1052.2	1109.0	1146.2	1170.7	1178.6	1170.7	1146.2	1109.0	1052.2	1015.4
127.5°	975.8	1010.1	1060.0	1095.3	1116.8	1122.7	1116.8	1095.3	1060.0	1010.1	975.8
130°	935.6	967.9	1015.9	1049.2	1068.8	1076.7	1068.8	1049.2	1015.9	967.9	935.6
132.5°	894.0	923.8	970.9	1004.2	1021.8	1028.7	1021.8	1004.2	970.9	923.8	894.0
135°	853.3	880.7	922.9	955.2	972.8	976.7	972.8	955.2	922.9	880.7	853.3
137.5°	812.2	836.7	876.8	905.2	920.9	926.8	920.9	905.2	876.8	836.7	812.2
140°	776.0	797.5	828.8	854.3	869.0	874.9	869.0	854.3	828.8	797.5	776.0
142.5°	741.2	758.3	787.7	810.2	822.9	822.9	822.9	810.2	787.7	758.3	741.2
145°	712.7	726.9	750.4	767.1	776.9	779.8	776.9	767.1	750.4	726.9	712.7
147.5°	687.8	698.5	719.1	732.8	739.7	741.6	739.7	732.8	719.1	698.5	687.8
150°	666.2	675.0	689.7	701.5	707.3	708.3	707.3	701.5	689.7	675.0	666.2
152.5°	648.0	655.4	666.2	676.0	679.9	679.9	679.9	676.0	666.2	655.4	648.0
155°	630.4	635.8	646.6	653.4	657.4	655.4	657.4	653.4	646.6	635.8	630.4
157.5°	613.8	618.2	626.0	631.9	633.9	633.9	633.9	631.9	626.0	618.2	613.8
160°	597.1	600.5	607.4	612.3	613.3	613.3	613.3	612.3	607.4	600.5	597.1
162.5°	581.4	583.9	590.7	593.7	594.7	593.7	594.7	593.7	590.7	583.9	581.4
165°	566.2	568.2	572.1	576.1	576.1	575.1	576.1	576.1	572.1	568.2	566.2
167.5°	552.6	554.5	556.5	558.4	558.4	557.4	558.4	558.4	556.5	554.5	552.6
170°	539.8	540.8	541.8	544.7	543.7	541.8	543.7	544.7	541.8	540.8	539.8
172.5°	528.6	529.0	530.0	531.0	530.0	529.0	530.0	531.0	530.0	529.0	528.6
175°	519.7	520.2	520.2	521.2	520.2	518.3	520.2	521.2	520.2	520.2	519.7
177.5°	513.4	513.4	513.4	513.4	512.4	510.4	512.4	513.4	513.4	513.4	513.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1	1981.1
2.5°	1880.6	1892.8	1888.3	1871.5	1891.3	1891.3	1905.0	1905.0	1921.8	1927.8	1937.0
5°	1774.0	1783.2	1790.8	1783.2	1796.9	1818.2	1830.4	1841.0	1863.9	1873.0	1886.7
7.5°	1659.8	1676.6	1684.2	1684.2	1707.0	1731.4	1755.8	1771.0	1803.0	1815.2	1828.9
10°	1548.7	1568.5	1583.7	1582.2	1620.2	1635.5	1665.9	1700.9	1732.9	1751.2	1771.0
12.5°	1431.4	1442.1	1463.4	1493.9	1503.0	1530.4	1565.4	1609.6	1667.4	1684.2	1713.1
15°	1334.0	1362.9	1379.6	1393.3	1414.7	1440.6	1478.6	1521.3	1579.1	1615.7	1646.1
17.5°	1251.7	1289.8	1300.5	1297.4	1324.8	1364.4	1408.6	1440.6	1492.3	1536.5	1565.4
20°	1184.7	1200.0	1218.2	1225.8	1247.2	1289.8	1332.4	1369.0	1411.6	1446.6	1480.1
22.5°	1117.7	1129.9	1145.1	1158.8	1175.6	1200.0	1241.1	1286.8	1327.9	1361.4	1399.4
25°	1062.9	1070.5	1084.2	1094.9	1113.2	1129.9	1158.8	1209.1	1257.8	1277.6	1311.1
27.5°	1009.6	1015.7	1024.8	1037.0	1046.2	1062.9	1088.8	1129.9	1180.2	1200.0	1245.6
30°	962.4	967.0	976.1	982.2	986.8	1006.6	1026.4	1058.3	1096.4	1123.8	1157.3
32.5°	918.2	922.8	931.9	933.5	939.6	950.2	968.5	997.4	1030.9	1053.8	1082.7
35°	869.5	872.6	881.7	884.7	889.3	898.4	912.1	933.5	963.9	980.7	1006.6
37.5°	831.4	829.9	836.0	840.6	846.7	851.2	855.8	877.1	900.0	915.2	935.0
40°	790.3	787.3	788.8	794.9	797.9	804.0	804.0	825.3	840.6	852.8	868.0
42.5°	749.2	747.7	744.6	747.7	750.7	752.3	753.8	769.0	784.2	794.9	811.6
45°	708.1	706.6	703.5	705.0	705.0	708.1	712.7	718.8	729.4	738.5	747.7
47.5°	670.0	667.0	662.4	660.9	663.9	663.9	663.9	670.0	680.7	683.7	692.9
50°	630.4	625.9	619.8	616.7	616.7	615.2	618.2	619.8	628.9	632.0	639.6
52.5°	587.8	584.7	578.7	572.6	574.1	571.0	572.6	574.1	577.1	581.7	586.3
55°	545.2	539.1	534.5	533.0	528.4	528.4	523.8	529.9	528.4	529.9	536.0
57.5°	504.0	498.0	490.3	487.3	482.7	481.2	478.2	476.6	478.2	482.7	487.3
60°	455.3	452.3	447.7	443.1	440.1	435.5	432.5	432.5	430.9	430.9	432.5
62.5°	408.1	406.6	400.5	399.0	395.9	392.9	388.3	385.3	385.3	388.3	389.8
65°	362.4	360.9	356.3	354.8	347.2	344.1	342.6	341.1	338.1	338.1	338.1
67.5°	319.8	315.2	315.2	307.6	301.5	298.5	295.4	293.9	293.9	293.9	295.4
70°	272.6	272.6	268.0	263.4	257.4	258.9	254.3	249.7	249.7	246.7	248.2
72.5°	226.9	225.4	220.8	219.3	214.7	210.1	207.1	210.1	205.6	204.1	205.6
75°	182.7	181.2	178.2	175.1	176.6	172.1	167.5	166.0	166.0	162.9	162.9
77.5°	140.1	143.1	137.1	135.5	132.5	129.4	127.9	126.4	126.4	126.4	129.4
80°	97.5	99.0	99.0	95.9	97.5	92.9	92.9	92.9	88.3	89.8	91.4
82.5°	62.4	62.4	60.9	62.4	60.9	60.9	59.4	59.4	57.9	57.9	59.4
85°	35.0	33.5	32.0	35.0	33.5	33.5	32.0	32.0	32.0	32.0	32.0
87.5°	7.6	9.1	9.1	9.1	9.1	10.7	10.7	10.7	12.2	12.2	12.2
90°	31.3	29.4	31.3	32.3	33.3	32.3	26.5	19.6	14.7	13.2	11.8
92.5°	73.5	84.3	98.9	126.4	150.9	148.9	115.6	78.4	51.9	46.5	41.1
95°	155.8	196.9	256.7	336.0	384.0	340.0	226.3	141.1	96.0	84.2	72.5
97.5°	320.4	419.3	525.1	630.9	626.0	484.0	300.8	182.2	124.4	111.2	98.0
100°	638.8	773.0	894.5	915.0	774.0	532.9	321.3	201.8	149.9	136.2	122.5
102.5°	1043.4	1132.5	1136.4	1020.8	778.8	514.3	322.3	219.4	172.4	158.7	145.0
105°	1313.8	1301.0	1190.3	986.5	725.9	488.9	327.2	240.0	194.0	180.2	166.5
107.5°	1393.1	1297.1	1132.5	914.0	677.0	475.1	338.0	260.6	215.5	201.8	188.1
110°	1353.9	1228.5	1053.2	846.4	643.7	471.2	351.7	281.2	238.1	223.9	209.7

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1283.4	1147.2	980.7	799.4	622.1	472.2	366.4	300.8	259.6	244.9	230.2
115°	1203.1	1074.7	923.8	762.2	607.4	476.1	381.1	321.3	279.2	266.0	252.8
117.5°	1131.5	1012.0	876.8	736.7	599.6	482.0	396.8	340.0	300.8	287.0	273.3
120°	1068.8	965.0	843.5	717.1	592.7	487.9	412.4	359.5	321.3	307.6	293.9
122.5°	1022.8	925.8	817.1	700.5	588.8	494.7	426.2	378.2	342.9	328.7	314.5
125°	978.7	892.5	791.6	684.8	583.9	501.6	440.9	396.8	361.5	347.8	334.1
127.5°	941.5	859.2	766.1	670.1	581.0	508.5	454.6	414.4	380.1	365.9	351.7
130°	903.3	825.9	741.6	655.4	579.0	516.3	467.3	430.1	395.8	382.1	368.4
132.5°	864.1	794.5	718.1	643.7	578.0	524.1	480.0	443.8	411.5	397.8	384.0
135°	825.9	761.2	696.6	632.9	577.0	530.0	490.8	456.5	425.2	411.5	397.8
137.5°	787.7	734.8	678.9	625.0	577.0	535.9	499.6	467.3	436.0	423.2	410.5
140°	754.4	709.3	662.3	618.2	576.1	539.8	506.5	476.1	446.7	434.0	421.3
142.5°	724.0	686.8	648.6	611.3	576.1	542.7	512.4	483.0	454.6	442.8	431.1
145°	698.5	668.1	635.8	605.4	574.1	544.7	517.3	489.8	463.4	452.6	441.8
147.5°	677.0	652.5	626.0	599.6	571.2	545.7	520.2	495.7	470.2	460.4	450.7
150°	657.4	636.8	615.2	591.7	568.2	544.7	522.2	499.6	477.1	468.3	459.5
152.5°	640.7	624.1	604.5	584.9	563.3	542.7	523.2	503.6	484.0	476.2	468.3
155°	625.0	610.3	594.7	576.1	557.4	540.8	524.1	507.5	490.8	483.4	476.1
157.5°	609.4	596.6	582.9	568.2	551.6	536.9	524.1	510.4	495.7	489.4	483.0
160°	593.7	582.9	572.1	559.4	545.7	533.9	524.1	512.4	500.6	495.2	489.8
162.5°	579.0	570.2	561.4	551.6	540.8	531.0	523.2	513.4	503.6	499.6	495.7
165°	564.3	557.4	550.6	542.7	533.9	527.1	521.2	514.3	505.5	502.6	499.6
167.5°	550.6	545.7	539.8	533.9	528.1	523.2	520.2	514.3	507.5	505.6	503.6
170°	538.8	534.9	532.0	527.1	523.2	520.2	518.3	513.4	508.5	507.0	505.5
172.5°	528.1	525.1	523.2	520.2	517.3	516.3	515.3	512.4	509.4	508.4	507.5
175°	519.2	518.3	517.3	514.3	513.4	512.4	513.4	511.4	509.4	509.0	508.5
177.5°	513.4	512.4	512.4	510.4	509.4	510.4	512.4	510.4	509.4	509.4	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1981.1	1981.1	1981.1	1981.1
2.5°	1944.6	1944.6	1967.4	1991.8
5°	1902.0	1912.6	1949.2	1982.7
7.5°	1860.8	1879.1	1924.8	1967.4
10°	1810.6	1835.0	1891.3	1941.5
12.5°	1761.9	1784.7	1850.2	1906.5
15°	1693.3	1722.3	1792.3	1862.4
17.5°	1624.8	1653.7	1739.0	1821.2
20°	1544.1	1582.2	1678.1	1787.7
22.5°	1469.5	1516.7	1623.3	1711.6
25°	1387.3	1460.3	1559.3	1673.5
27.5°	1314.2	1387.3	1487.8	1603.5
30°	1231.9	1306.5	1410.1	1516.7
32.5°	1152.7	1221.3	1321.8	1452.7
35°	1070.5	1136.0	1233.5	1365.9
37.5°	995.9	1059.9	1166.5	1288.3
40°	922.8	989.8	1081.2	1203.0
42.5°	854.3	913.7	995.9	1117.7
45°	791.8	834.5	910.6	1024.8
47.5°	726.4	764.4	834.5	948.7
50°	665.5	697.4	758.3	864.9
52.5°	606.1	633.5	689.8	775.1
55°	552.8	578.7	619.8	703.5
57.5°	498.0	517.7	557.3	624.3
60°	444.7	462.9	494.9	549.7
62.5°	391.4	406.6	437.0	481.2
65°	344.1	356.3	379.2	417.2
67.5°	298.5	306.1	324.4	354.8
70°	254.3	260.4	275.6	300.0
72.5°	207.1	213.2	229.9	246.7
75°	167.5	169.0	181.2	194.9
77.5°	131.0	129.4	138.6	149.2
80°	89.8	94.4	102.0	106.6
82.5°	60.9	62.4	65.5	68.5
85°	33.5	35.0	35.0	39.6
87.5°	13.7	15.2	15.2	16.8
90°	9.8	7.8	3.9	1.0
92.5°	33.3	28.4	20.6	14.7
95°	56.8	48.0	38.2	34.3
97.5°	80.3	67.6	56.8	50.9
100°	102.9	87.2	78.4	75.4
102.5°	124.4	108.7	99.9	98.0
105°	145.0	130.3	123.4	119.5
107.5°	166.5	152.8	146.0	143.0
110°	189.1	176.3	170.5	166.5



TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	210.6	198.9	192.0	188.1
115°	233.2	221.4	215.5	210.6
117.5°	254.7	243.9	238.1	234.1
120°	274.3	265.5	259.6	255.7
122.5°	294.9	285.1	279.2	276.3
125°	314.5	302.7	296.8	293.9
127.5°	333.1	320.4	312.5	308.6
130°	348.8	335.1	325.3	321.3
132.5°	363.5	348.8	338.0	333.1
135°	375.2	360.5	348.8	344.8
137.5°	388.0	372.3	360.5	355.6
140°	399.7	384.0	372.3	368.4
142.5°	410.5	394.8	384.0	381.1
145°	422.2	407.5	397.8	393.8
147.5°	434.0	420.3	410.5	407.5
150°	444.8	432.0	424.2	421.3
152.5°	454.6	443.8	436.0	435.0
155°	465.4	454.6	448.7	447.7
157.5°	474.2	464.4	459.5	458.5
160°	482.0	474.2	470.2	469.3
162.5°	488.9	483.0	479.1	480.0
165°	494.7	488.9	486.9	487.9
167.5°	499.6	495.7	493.8	494.7
170°	503.6	500.6	499.6	501.6
172.5°	506.5	503.6	504.5	505.5
175°	508.5	506.5	507.5	508.5
177.5°	509.4	507.5	508.5	510.4
180°	509.4	509.4	509.4	509.4

TEST NUMBER: P998023

CATALOG NUMBER: SA2XXDIP-B1005D925UB27-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.29	19.16	19.21	20.09	21.29	15.78	16.65	16.70	17.59	18.78
	3H	19.10	19.88	20.03	20.82	22.04	17.13	17.91	18.06	18.85	20.07
	4H	19.27	20.01	20.22	20.95	22.18	17.59	18.33	18.54	19.27	20.50
	6H	19.32	20.00	20.27	20.95	22.19	17.90	18.58	18.85	19.53	20.77
	8H	19.30	19.94	20.26	20.91	22.15	17.98	18.63	18.95	19.60	20.84
	12H	19.26	19.87	20.23	20.83	22.10	18.02	18.64	18.99	19.60	20.87
4H	2H	18.33	19.07	19.28	20.01	21.25	16.23	16.97	17.18	17.91	19.14
	3H	19.31	19.93	20.27	20.90	22.15	17.69	18.30	18.65	19.28	20.53
	4H	19.59	20.15	20.56	21.12	22.39	18.23	18.79	19.20	19.76	21.03
	6H	19.72	20.20	20.70	21.20	22.46	18.61	19.09	19.59	20.08	21.35
	8H	19.72	20.17	20.70	21.16	22.44	18.72	19.17	19.70	20.15	21.44
	12H	19.68	20.09	20.69	21.09	22.38	18.77	19.18	19.78	20.18	21.47
8H	4H	19.60	20.05	20.58	21.04	22.32	18.37	18.82	19.35	19.81	21.09
	6H	19.78	20.15	20.79	21.18	22.46	18.80	19.17	19.81	20.20	21.48
	8H	19.81	20.14	20.83	21.15	22.45	18.95	19.28	19.97	20.30	21.60
	12H	19.79	20.08	20.81	21.09	22.44	19.05	19.33	20.07	20.34	21.69
12H	4H	19.56	19.96	20.56	20.97	22.25	18.34	18.75	19.35	19.75	21.04
	6H	19.76	20.08	20.77	21.10	22.40	18.80	19.13	19.82	20.15	21.45
	8H	19.79	20.08	20.81	21.09	22.43	18.96	19.25	19.98	20.26	21.60