

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999192

Luminaire Tested: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999192
REPORT IS A COMBINATION OF REPORTS P984941 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6282.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	101	96	93	89	94	90	87	84	79	76	74	68	67	65	59	57	56
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48
3	84	75	68	62	79	71	64	59	62	57	53	54	50	47	47	44	42
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37
5	71	60	52	46	67	57	49	44	50	44	40	44	40	36	38	35	32
6	66	54	46	40	62	51	44	39	45	40	35	40	35	32	35	31	29
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	29	26
8	57	45	37	32	53	42	35	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27013	27013	27013	27013
5°	27077	28801	27180	22914
10°	26763	31441	26931	18891
15°	26114	33163	26477	15913
20°	25706	31139	25706	13832
25°	24887	26752	25001	12368
30°	23539	21029	23987	11203
35°	22345	14541	22718	10251
40°	20972	10979	21211	9491
45°	19278	9022	19595	8671
50°	17816	7919	17847	7938
55°	16148	6748	16251	7141
60°	14368	5636	14568	6232
65°	12776	4584	13011	5323
70°	11191	3597	11476	4294
75°	9392	2611	9762	3112
80°	7329	1655	7856	1848
85°	4817	832	5184	616

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 27922 cd/sqm

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.6
10°-20°	473.1	7.5
20°-30°	686.6	10.9
30°-40°	723.8	11.5
40°-50°	640.5	10.2
50°-60°	511.4	8.1
60°-70°	347.4	5.5
70°-80°	177.7	2.8
80°-90°	44.6	0.7
90°-100°	55.6	0.9
100°-110°	176.9	2.8
110°-120°	302.6	4.8
120°-130°	398.0	6.3
130°-140°	446.8	7.1
140°-150°	438.1	7.0
150°-160°	367.5	5.8
160°-170°	243.7	3.9
170°-180°	85.2	1.4
0°-30°	1322.2	21.0
0°-40°	2046.0	32.6
0°-60°	3197.9	50.9
0°-90°	3767.6	60.0
90°-120°	535.2	8.5
90°-150°	1818.0	28.9
90°-180°	2514.0	40.0
0°-180°	6282.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1706	1706	1706	1706	1706	
5°	1708	1906	1714	1516	1708	162
15°	1604	2343	1626	1124	1604	453
25°	1442	1952	1448	902	1442	659
35°	1177	1062	1196	749	1177	736
45°	883	640	897	615	883	685
55°	606	450	610	476	606	541
65°	359	277	366	321	359	357
75°	168	136	174	163	168	180
85°	34	35	37	26	34	40
90°	1	26	1	26	1	4
95°	40	47	40	47	40	44
105°	163	168	163	168	163	172
115°	304	304	304	304	304	300
125°	442	443	442	443	442	395
135°	572	578	572	578	572	442
145°	694	701	694	701	694	433
155°	793	799	793	799	793	365
165°	863	864	863	864	863	243
175°	898	895	898	895	898	85
180°	899	899	899	899	899	

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1715.7	1719.6	1726.1	1727.5	1740.6	1751.1	1762.9	1762.9	1766.8	1765.5	1755.0
5°	1707.8	1719.6	1736.6	1751.1	1774.7	1785.2	1800.9	1812.7	1823.2	1831.1	1829.8
7.5°	1694.7	1715.7	1740.6	1768.1	1799.6	1818.0	1840.3	1861.2	1875.7	1888.8	1898.0
10°	1672.4	1707.8	1741.9	1778.6	1819.3	1844.2	1870.4	1898.0	1920.3	1945.2	1968.8
12.5°	1642.2	1693.4	1735.3	1783.9	1833.7	1861.2	1903.2	1924.2	1967.5	2030.5	2047.5
15°	1604.2	1673.7	1713.0	1774.7	1840.3	1862.6	1920.3	1954.4	2043.6	2082.9	2130.1
17.5°	1568.7	1646.1	1698.6	1769.4	1833.7	1877.0	1933.4	2002.9	2077.7	2134.1	2186.5
20°	1539.9	1614.7	1677.6	1756.3	1837.6	1892.7	1951.8	2035.7	2117.0	2174.7	2215.4
22.5°	1474.3	1570.1	1643.5	1731.4	1829.8	1905.8	1962.2	2054.1	2141.9	2177.4	2212.8
25°	1441.5	1524.2	1609.4	1709.1	1824.5	1915.0	1963.6	2065.9	2143.3	2156.4	2164.2
27.5°	1381.2	1474.3	1574.0	1688.1	1823.2	1899.3	1960.9	2054.1	2115.7	2106.5	2082.9
30°	1306.4	1420.5	1530.7	1654.0	1804.8	1887.5	1945.2	2030.5	2061.9	2014.7	1972.7
32.5°	1251.3	1358.9	1480.9	1623.8	1783.9	1862.6	1919.0	1985.9	1992.4	1907.2	1836.3
35°	1176.6	1295.9	1433.6	1584.5	1748.4	1819.3	1871.7	1912.4	1880.9	1761.6	1677.6
37.5°	1109.7	1227.7	1374.6	1528.1	1699.9	1769.4	1811.4	1818.0	1740.6	1635.6	1512.3
40°	1036.2	1158.2	1311.7	1473.0	1646.1	1706.5	1732.7	1713.0	1601.5	1479.6	1336.6
42.5°	962.8	1083.4	1248.7	1414.0	1577.9	1629.1	1639.6	1585.8	1449.4	1306.4	1141.1
45°	882.7	1008.7	1173.9	1340.5	1499.2	1528.1	1529.4	1452.0	1290.7	1141.1	987.7
47.5°	817.2	933.9	1097.9	1264.4	1398.2	1417.9	1410.0	1320.8	1145.1	977.2	843.4
50°	745.0	856.5	1019.2	1183.1	1297.2	1302.5	1282.8	1155.6	983.7	830.3	724.0
52.5°	667.6	780.4	930.0	1087.4	1189.7	1181.8	1143.8	1007.4	846.0	718.8	637.5
55°	606.0	705.7	846.0	999.5	1071.6	1049.3	1007.4	868.3	741.1	633.5	562.7
57.5°	537.8	625.7	763.4	897.2	939.2	918.2	876.2	746.3	628.3	547.0	499.7
60°	473.5	553.5	674.2	785.7	818.5	796.2	747.6	630.9	545.7	477.4	442.0
62.5°	414.5	484.0	585.0	687.3	700.4	678.1	636.2	541.7	468.3	414.5	388.3
65°	359.4	425.0	506.3	583.7	595.5	571.9	528.6	460.4	398.7	364.6	339.7
67.5°	305.6	358.1	430.2	486.6	493.2	470.9	435.5	380.4	342.3	305.6	287.3
70°	258.4	297.7	354.1	400.1	402.7	381.7	363.3	313.5	284.6	258.4	244.0
72.5°	212.5	240.0	283.3	317.4	318.7	305.6	288.6	257.1	232.2	213.8	199.4
75°	167.9	191.5	217.7	247.9	246.6	236.1	223.0	203.3	182.3	170.5	164.0
77.5°	128.5	143.0	164.0	183.6	183.6	178.4	170.5	156.1	143.0	131.2	124.6
80°	91.8	101.0	118.0	124.6	127.2	125.9	119.4	108.9	103.6	94.4	91.8
82.5°	59.0	65.6	73.5	80.0	83.9	81.3	80.0	74.8	66.9	64.3	61.6
85°	34.1	36.7	40.7	44.6	45.9	44.6	47.2	43.3	39.3	39.3	38.0
87.5°	14.4	15.7	18.4	18.4	19.7	19.7	18.4	19.7	19.7	18.4	17.1
90°	0.8	2.8	4.8	6.9	8.9	9.9	11.8	15.5	19.2	22.9	26.6
92.5°	16.7	18.1	19.4	20.8	22.1	22.8	22.9	23.0	23.2	23.3	23.5
95°	39.5	41.2	42.9	44.6	46.3	47.1	47.3	47.6	47.9	48.3	48.6
97.5°	66.0	67.5	69.1	70.6	72.1	72.9	73.2	73.9	74.6	75.2	75.9
100°	96.4	97.8	99.1	100.5	101.8	102.5	102.7	103.2	103.7	104.2	104.7
102.5°	128.3	129.3	130.3	131.3	132.3	132.8	133.1	133.8	134.5	135.2	135.9
105°	163.2	163.7	164.2	164.7	165.2	165.5	165.7	166.0	166.3	166.7	167.0
107.5°	198.1	198.8	199.4	200.1	200.8	201.1	201.1	201.1	201.1	201.1	201.1
110°	231.5	232.5	233.5	234.5	235.5	236.0	236.0	236.0	236.0	236.0	236.0

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	267.9	268.9	269.9	271.0	272.0	272.5	272.4	272.2	272.1	271.9	271.7
115°	303.6	304.6	305.6	306.6	307.6	308.1	307.9	307.6	307.3	306.9	306.6
117.5°	339.3	340.6	342.0	343.3	344.6	345.3	344.9	344.0	343.2	342.3	341.5
120°	374.9	376.3	377.6	379.0	380.3	381.0	380.3	379.0	377.6	376.3	374.9
122.5°	407.6	409.3	410.9	412.6	414.3	415.1	414.7	413.9	413.0	412.2	411.4
125°	441.7	443.2	444.7	446.2	447.7	448.5	448.3	447.8	447.3	446.8	446.3
127.5°	475.1	477.0	478.8	480.7	482.6	483.5	483.2	482.5	481.8	481.1	480.4
130°	506.2	508.4	510.6	512.8	515.0	516.1	515.9	515.6	515.3	514.9	514.6
132.5°	541.1	542.8	544.5	546.2	547.9	548.7	548.8	549.0	549.1	549.3	549.5
135°	571.5	573.3	575.2	577.0	578.9	579.8	580.0	580.3	580.7	581.0	581.4
137.5°	604.9	606.4	607.9	609.4	610.9	611.7	611.9	612.2	612.5	612.9	613.2
140°	634.5	636.0	637.5	639.0	640.5	641.3	641.7	642.6	643.4	644.3	645.1
142.5°	664.8	666.3	667.9	669.4	670.9	671.7	672.0	672.5	673.0	673.5	674.0
145°	693.7	694.9	696.1	697.2	698.4	699.0	699.5	700.5	701.6	702.6	703.6
147.5°	719.5	721.0	722.5	724.0	725.5	726.3	726.6	727.3	728.0	728.7	729.4
150°	746.1	747.1	748.1	749.1	750.1	750.6	750.9	751.6	752.3	752.9	753.6
152.5°	769.6	770.6	771.6	772.6	773.6	774.1	774.5	775.4	776.2	777.1	777.9
155°	793.1	793.6	794.1	794.6	795.1	795.4	795.7	796.2	796.7	797.2	797.7
157.5°	813.6	813.9	814.3	814.6	814.9	815.1	815.3	815.6	815.9	816.3	816.6
160°	831.8	832.1	832.5	832.8	833.1	833.3	833.4	833.6	833.7	833.9	834.1
162.5°	848.5	848.5	848.5	848.5	848.5	848.5	848.6	848.8	848.9	849.1	849.3
165°	862.9	862.7	862.6	862.4	862.3	862.2	862.2	862.2	862.2	862.2	862.2
167.5°	875.8	875.3	874.8	874.3	873.8	873.6	873.6	873.6	873.6	873.6	873.6
170°	885.7	885.2	884.7	884.2	883.7	883.4	883.3	883.2	883.0	882.9	882.7
172.5°	892.5	892.0	891.5	891.0	890.5	890.3	890.2	890.0	889.9	889.7	889.5
175°	897.8	897.3	896.8	896.3	895.8	895.6	895.4	895.1	894.7	894.4	894.0
177.5°	900.9	900.4	899.9	899.4	898.9	898.6	898.4	898.1	897.8	897.4	897.1
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1773.4	1774.7	1777.3	1790.4	1797.0	1798.3	1793.0	1804.8	1808.8	1804.8	1802.2
5°	1857.3	1865.2	1880.9	1898.0	1896.7	1898.0	1905.8	1913.7	1916.3	1905.8	1909.8
7.5°	1930.8	1946.5	1963.6	1989.8	1989.8	2002.9	2008.2	2014.7	2030.5	2022.6	2020.0
10°	2014.7	2035.7	2067.2	2109.2	2110.5	2123.6	2136.7	2157.7	2164.2	2159.0	2161.6
12.5°	2119.6	2160.3	2162.9	2208.8	2229.8	2232.5	2253.4	2249.5	2262.6	2262.6	2284.9
15°	2165.6	2228.5	2263.9	2308.5	2321.6	2305.9	2323.0	2341.3	2342.6	2342.6	2341.3
17.5°	2248.2	2273.1	2308.5	2332.1	2337.4	2337.4	2338.7	2346.6	2341.3	2330.8	2338.7
20°	2265.2	2275.7	2288.9	2286.2	2288.9	2275.7	2262.6	2249.5	2250.8	2244.3	2263.9
22.5°	2233.8	2231.1	2201.0	2181.3	2181.3	2155.1	2130.1	2118.3	2106.5	2110.5	2117.0
25°	2155.1	2114.4	2077.7	2048.8	2042.3	2000.3	1966.2	1955.7	1936.0	1951.8	1954.4
27.5°	2029.1	1983.2	1924.2	1899.3	1865.2	1848.1	1824.5	1793.0	1752.4	1776.0	1772.1
30°	1894.0	1825.8	1777.3	1717.0	1663.2	1659.3	1614.7	1562.2	1541.2	1541.2	1553.0
32.5°	1743.2	1652.7	1581.9	1496.6	1444.1	1421.8	1368.1	1315.6	1327.4	1288.1	1302.5
35°	1567.4	1448.1	1358.9	1276.2	1236.9	1210.7	1141.1	1112.3	1080.8	1062.4	1096.6
37.5°	1399.5	1261.8	1147.7	1057.2	1042.8	995.6	948.3	930.0	911.6	919.5	918.2
40°	1194.9	1072.9	970.6	899.8	874.9	852.6	821.1	798.8	787.0	793.6	794.9
42.5°	1010.0	907.7	831.6	781.8	760.8	745.0	729.3	710.9	707.0	707.0	712.2
45°	867.0	783.1	731.9	691.2	679.4	667.6	655.8	648.0	645.3	640.1	644.0
47.5°	752.9	686.0	654.5	624.4	611.2	608.6	598.1	594.2	588.9	587.6	588.9
50°	657.1	615.2	586.3	569.3	560.1	556.1	550.9	543.0	540.4	547.0	544.3
52.5°	590.2	550.9	535.2	518.1	512.9	507.6	499.7	501.1	499.7	497.1	497.1
55°	523.4	498.4	482.7	469.6	468.3	463.0	456.5	453.8	452.5	449.9	453.8
57.5°	469.6	449.9	435.5	423.7	418.4	418.4	411.9	406.6	406.6	405.3	406.6
60°	415.8	396.1	386.9	375.1	371.2	369.9	366.0	363.3	359.4	359.4	359.4
62.5°	366.0	350.2	339.7	329.2	330.5	324.0	318.7	316.1	316.1	317.4	317.4
65°	318.7	308.2	295.1	285.9	283.3	282.0	279.4	278.1	274.1	276.8	276.8
67.5°	275.4	261.0	253.2	249.2	245.3	244.0	241.3	238.7	237.4	236.1	238.7
70°	232.2	220.4	213.8	211.2	207.2	205.9	204.6	200.7	202.0	203.3	204.6
72.5°	192.8	182.3	181.0	173.1	173.1	173.1	167.9	170.5	169.2	166.6	169.2
75°	152.2	146.9	144.3	140.3	141.7	140.3	139.0	135.1	135.1	136.4	137.7
77.5°	120.7	115.4	114.1	110.2	107.6	110.2	107.6	106.2	106.2	107.6	107.6
80°	89.2	86.6	82.6	82.6	82.6	81.3	81.3	81.3	80.0	78.7	80.0
82.5°	59.0	59.0	57.7	56.4	57.7	55.1	56.4	56.4	56.4	56.4	56.4
85°	38.0	36.7	36.7	35.4	35.4	35.4	36.7	34.1	34.1	35.4	35.4
87.5°	17.1	17.1	17.1	18.4	17.1	17.1	17.1	18.4	17.1	17.1	17.1
90°	26.2	25.9	25.5	25.2	25.0	25.1	25.3	25.4	25.6	25.8	25.6
92.5°	23.7	23.9	24.0	24.2	24.3	24.3	24.3	24.3	24.3	24.3	24.3
95°	48.6	48.6	48.6	48.6	48.6	48.4	48.1	47.8	47.4	47.1	47.4
97.5°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9
100°	104.7	104.7	104.7	104.7	104.7	104.6	104.5	104.3	104.2	104.0	104.2
102.5°	136.1	136.2	136.4	136.5	136.6	136.5	136.4	136.2	136.1	135.9	136.1
105°	167.3	167.7	168.0	168.3	168.5	168.5	168.5	168.5	168.5	168.5	168.5
107.5°	201.3	201.5	201.6	201.8	201.9	201.5	200.6	199.8	198.9	198.1	198.9
110°	236.0	236.0	236.0	236.0	236.0	235.8	235.3	234.8	234.3	233.8	234.3

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	271.2	270.7	270.2	269.7	269.4	269.2	268.9	268.6	268.2	267.9	268.2
115°	306.4	306.3	306.1	306.0	305.9	305.6	305.1	304.6	304.1	303.6	304.1
117.5°	341.0	340.5	340.0	339.5	339.3	339.0	338.5	338.0	337.5	337.0	337.5
120°	374.9	374.9	374.9	374.9	374.9	374.6	374.1	373.6	373.1	372.6	373.1
122.5°	410.9	410.4	409.9	409.4	409.1	408.9	408.6	408.3	407.9	407.6	407.9
125°	445.8	445.3	444.8	444.3	444.0	443.9	443.7	443.6	443.4	443.2	443.4
127.5°	479.7	479.1	478.4	477.7	477.4	477.1	476.6	476.1	475.6	475.1	475.6
130°	514.3	513.9	513.6	513.3	513.1	512.8	512.1	511.4	510.7	510.0	510.7
132.5°	548.7	547.8	547.0	546.1	545.7	545.4	544.9	544.4	543.9	543.4	543.9
135°	581.2	581.0	580.9	580.7	580.6	580.3	579.8	579.3	578.8	578.3	578.8
137.5°	613.0	612.9	612.7	612.6	612.5	612.2	611.5	610.8	610.1	609.4	610.1
140°	645.1	645.1	645.1	645.1	645.1	644.8	644.1	643.4	642.8	642.1	642.8
142.5°	674.2	674.3	674.5	674.6	674.7	674.4	673.7	673.0	672.4	671.7	672.4
145°	703.8	703.9	704.1	704.2	704.3	704.0	703.3	702.6	702.0	701.3	702.0
147.5°	729.7	730.1	730.4	730.7	730.9	730.6	729.9	729.2	728.5	727.8	728.5
150°	754.1	754.6	755.1	755.6	755.9	755.6	755.1	754.6	754.1	753.6	754.1
152.5°	778.6	779.3	780.0	780.7	781.0	780.7	780.0	779.3	778.6	777.9	778.6
155°	798.5	799.4	800.2	801.1	801.5	801.2	800.7	800.2	799.7	799.2	799.7
157.5°	817.8	819.0	820.1	821.3	821.9	821.5	820.7	819.8	819.0	818.2	819.0
160°	835.1	836.1	837.1	838.1	838.6	838.3	837.6	836.9	836.3	835.6	836.3
162.5°	850.5	851.7	852.8	854.0	854.6	854.2	853.3	852.5	851.6	850.8	851.6
165°	863.4	864.6	865.7	866.9	867.5	867.1	866.2	865.4	864.5	863.7	864.5
167.5°	874.8	876.0	877.1	878.3	878.9	878.5	877.6	876.8	875.9	875.1	875.9
170°	883.9	885.1	886.2	887.4	888.0	887.5	886.5	885.4	884.4	883.4	884.4
172.5°	890.7	891.9	893.0	894.2	894.8	894.3	893.3	892.3	891.3	890.3	891.3
175°	895.2	896.4	897.6	898.8	899.4	898.9	897.9	896.8	895.8	894.8	895.8
177.5°	898.1	899.1	900.1	901.1	901.6	901.1	900.1	899.1	898.1	897.1	898.1
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1808.8	1799.6	1791.7	1793.0	1799.6	1794.4	1781.2	1764.2	1757.6	1749.8	1757.6
5°	1917.7	1909.8	1894.0	1895.4	1891.4	1886.2	1865.2	1839.0	1839.0	1818.0	1815.3
7.5°	2025.2	2013.4	2002.9	2000.3	1985.9	1975.4	1957.0	1920.3	1905.8	1880.9	1866.5
10°	2145.9	2136.7	2124.9	2110.5	2102.6	2084.2	2054.1	2000.3	1974.1	1939.9	1915.0
12.5°	2267.9	2266.6	2240.3	2211.5	2210.2	2181.3	2160.3	2088.2	2052.8	2006.8	1947.8
15°	2345.3	2338.7	2324.3	2309.8	2313.8	2282.3	2235.1	2149.8	2126.2	2071.1	2008.2
17.5°	2343.9	2343.9	2340.0	2337.4	2333.4	2324.3	2298.0	2241.6	2203.6	2134.1	2075.1
20°	2269.2	2286.2	2290.2	2288.9	2302.0	2308.5	2307.2	2271.8	2241.6	2180.0	2119.6
22.5°	2119.6	2159.0	2176.0	2186.5	2214.1	2228.5	2262.6	2249.5	2241.6	2195.7	2144.6
25°	1980.6	1993.7	2044.9	2047.5	2085.5	2121.0	2155.1	2177.4	2206.2	2189.2	2145.9
27.5°	1800.9	1831.1	1867.8	1895.4	1903.2	1975.4	2031.8	2073.7	2139.3	2144.6	2130.1
30°	1597.6	1612.0	1672.4	1709.1	1751.1	1803.5	1884.9	1957.0	2016.0	2069.8	2088.2
32.5°	1349.7	1408.7	1444.1	1488.7	1525.5	1618.6	1718.3	1811.4	1879.6	1970.1	2009.5
35°	1122.8	1168.7	1229.0	1247.4	1314.3	1393.0	1522.8	1642.2	1745.8	1837.6	1917.7
37.5°	935.2	971.9	1036.2	1065.1	1104.4	1205.4	1314.3	1462.5	1587.1	1699.9	1799.6
40°	806.7	834.2	882.7	891.9	924.7	1016.5	1104.4	1243.5	1408.7	1560.9	1669.7
42.5°	718.8	731.9	764.7	776.5	797.5	859.1	937.8	1069.0	1222.5	1379.9	1533.3
45°	655.8	665.0	684.7	695.2	721.4	749.0	813.2	918.2	1038.8	1197.5	1362.8
47.5°	599.4	611.2	619.1	625.7	640.1	670.3	712.2	789.6	905.0	1050.6	1210.7
50°	552.2	556.1	570.6	571.9	581.1	600.7	640.1	687.3	779.1	897.2	1052.0
52.5°	505.0	508.9	518.1	527.3	531.2	547.0	573.2	612.5	680.8	773.9	911.6
55°	457.8	463.0	472.2	478.8	482.7	495.8	511.5	549.6	603.4	668.9	781.8
57.5°	410.6	422.4	425.0	428.9	435.5	449.9	464.3	486.6	528.6	588.9	671.6
60°	366.0	369.9	379.1	383.0	389.6	397.4	415.8	432.8	463.0	510.2	585.0
62.5°	320.0	329.2	333.2	337.1	342.3	351.5	363.3	381.7	407.9	446.0	505.0
65°	280.7	282.0	289.9	295.1	300.4	306.9	318.7	335.8	351.5	386.9	430.2
67.5°	242.7	245.3	247.9	253.2	259.7	266.3	276.8	285.9	305.6	329.2	363.3
70°	205.9	205.9	212.5	216.4	215.1	223.0	230.9	241.3	255.8	278.1	305.6
72.5°	173.1	171.8	177.1	178.4	181.0	186.3	191.5	202.0	209.9	226.9	247.9
75°	137.7	140.3	143.0	143.0	146.9	150.8	156.1	161.3	170.5	181.0	196.7
77.5°	108.9	108.9	111.5	112.8	116.7	115.4	120.7	125.9	132.5	141.7	153.5
80°	80.0	82.6	82.6	82.6	83.9	85.3	90.5	94.4	98.4	104.9	110.2
82.5°	56.4	56.4	59.0	59.0	59.0	61.6	61.6	63.0	65.6	69.5	73.5
85°	35.4	35.4	35.4	36.7	35.4	36.7	39.3	38.0	39.3	42.0	42.0
87.5°	17.1	17.1	17.1	17.1	17.1	18.4	17.1	18.4	19.7	19.7	19.7
90°	25.4	25.3	25.1	25.0	25.2	25.5	25.9	26.2	26.6	22.9	19.2
92.5°	24.3	24.3	24.3	24.3	24.2	24.0	23.9	23.7	23.5	23.3	23.2
95°	47.8	48.1	48.4	48.6	48.6	48.6	48.6	48.6	48.6	48.3	47.9
97.5°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.2	74.6
100°	104.3	104.5	104.6	104.7	104.7	104.7	104.7	104.7	104.7	104.2	103.7
102.5°	136.2	136.4	136.5	136.6	136.5	136.4	136.2	136.1	135.9	135.2	134.5
105°	168.5	168.5	168.5	168.5	168.3	168.0	167.7	167.3	167.0	166.7	166.3
107.5°	199.8	200.6	201.5	201.9	201.8	201.6	201.5	201.3	201.1	201.1	201.1
110°	234.8	235.3	235.8	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	268.6	268.9	269.2	269.4	269.7	270.2	270.7	271.2	271.7	271.9	272.1
115°	304.6	305.1	305.6	305.9	306.0	306.1	306.3	306.4	306.6	306.9	307.3
117.5°	338.0	338.5	339.0	339.3	339.5	340.0	340.5	341.0	341.5	342.3	343.2
120°	373.6	374.1	374.6	374.9	374.9	374.9	374.9	374.9	374.9	376.3	377.6
122.5°	408.3	408.6	408.9	409.1	409.4	409.9	410.4	410.9	411.4	412.2	413.0
125°	443.6	443.7	443.9	444.0	444.3	444.8	445.3	445.8	446.3	446.8	447.3
127.5°	476.1	476.6	477.1	477.4	477.7	478.4	479.1	479.7	480.4	481.1	481.8
130°	511.4	512.1	512.8	513.1	513.3	513.6	513.9	514.3	514.6	514.9	515.3
132.5°	544.4	544.9	545.4	545.7	546.1	547.0	547.8	548.7	549.5	549.3	549.1
135°	579.3	579.8	580.3	580.6	580.7	580.9	581.0	581.2	581.4	581.0	580.7
137.5°	610.8	611.5	612.2	612.5	612.6	612.7	612.9	613.0	613.2	612.9	612.5
140°	643.4	644.1	644.8	645.1	645.1	645.1	645.1	645.1	645.1	644.3	643.4
142.5°	673.0	673.7	674.4	674.7	674.6	674.5	674.3	674.2	674.0	673.5	673.0
145°	702.6	703.3	704.0	704.3	704.2	704.1	703.9	703.8	703.6	702.6	701.6
147.5°	729.2	729.9	730.6	730.9	730.7	730.4	730.1	729.7	729.4	728.7	728.0
150°	754.6	755.1	755.6	755.9	755.6	755.1	754.6	754.1	753.6	752.9	752.3
152.5°	779.3	780.0	780.7	781.0	780.7	780.0	779.3	778.6	777.9	777.1	776.2
155°	800.2	800.7	801.2	801.5	801.1	800.2	799.4	798.5	797.7	797.2	796.7
157.5°	819.8	820.7	821.5	821.9	821.3	820.1	819.0	817.8	816.6	816.3	815.9
160°	836.9	837.6	838.3	838.6	838.1	837.1	836.1	835.1	834.1	833.9	833.7
162.5°	852.5	853.3	854.2	854.6	854.0	852.8	851.7	850.5	849.3	849.1	848.9
165°	865.4	866.2	867.1	867.5	866.9	865.7	864.6	863.4	862.2	862.2	862.2
167.5°	876.8	877.6	878.5	878.9	878.3	877.1	876.0	874.8	873.6	873.6	873.6
170°	885.4	886.5	887.5	888.0	887.4	886.2	885.1	883.9	882.7	882.9	883.0
172.5°	892.3	893.3	894.3	894.8	894.2	893.0	891.9	890.7	889.5	889.7	889.9
175°	896.8	897.9	898.9	899.4	898.8	897.6	896.4	895.2	894.0	894.4	894.7
177.5°	899.1	900.1	901.1	901.6	901.1	900.1	899.1	898.1	897.1	897.4	897.8
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1751.1	1744.5	1740.6	1743.2	1735.3	1715.7	1715.7	1722.2	1714.3	1706.5	1694.7
5°	1799.6	1786.5	1778.6	1777.3	1758.9	1727.5	1720.9	1714.3	1697.3	1678.9	1659.3
7.5°	1846.8	1823.2	1810.1	1800.9	1774.7	1734.0	1717.0	1702.5	1675.0	1647.4	1622.5
10°	1886.2	1852.1	1836.3	1821.9	1787.8	1736.6	1709.1	1682.9	1647.4	1612.0	1580.6
12.5°	1917.7	1878.3	1858.6	1837.6	1795.7	1728.8	1694.7	1652.7	1617.3	1570.1	1538.6
15°	1970.1	1888.8	1870.4	1850.8	1807.5	1715.7	1673.7	1626.5	1577.9	1515.0	1480.9
17.5°	2012.1	1903.2	1901.9	1859.9	1803.5	1710.4	1646.1	1584.5	1532.0	1469.1	1415.3
20°	2037.0	1925.5	1904.5	1861.2	1790.4	1675.0	1608.1	1539.9	1483.5	1407.4	1353.6
22.5°	2058.0	1957.0	1901.9	1849.4	1762.9	1663.2	1564.8	1500.5	1423.2	1340.5	1289.4
25°	2065.9	1963.6	1905.8	1845.5	1743.2	1629.1	1517.6	1448.1	1361.5	1286.7	1217.2
27.5°	2067.2	1962.2	1891.4	1828.5	1715.7	1584.5	1470.4	1396.9	1301.2	1214.6	1145.1
30°	2054.1	1947.8	1883.5	1815.3	1689.4	1543.8	1412.7	1331.3	1229.0	1142.5	1070.3
32.5°	2014.7	1919.0	1866.5	1791.7	1655.3	1487.4	1357.6	1267.1	1159.5	1074.3	1004.7
35°	1949.1	1883.5	1825.8	1756.3	1610.7	1435.0	1302.5	1196.2	1087.4	1006.0	940.5
37.5°	1867.8	1832.4	1778.6	1710.4	1559.6	1387.7	1240.8	1122.8	1013.9	935.2	870.9
40°	1757.6	1766.8	1714.3	1652.7	1499.2	1323.5	1160.8	1048.0	945.7	872.3	809.3
42.5°	1638.3	1676.3	1646.1	1587.1	1432.3	1252.6	1101.8	977.2	877.5	801.4	749.0
45°	1509.7	1575.3	1556.9	1513.7	1362.8	1177.9	1017.9	897.2	809.3	735.8	689.9
47.5°	1369.4	1462.5	1462.5	1431.0	1285.4	1103.1	945.7	822.4	735.8	683.4	638.8
50°	1226.4	1331.3	1348.4	1327.4	1198.9	1017.9	857.8	746.3	671.6	620.4	587.6
52.5°	1076.9	1198.9	1230.3	1219.8	1107.0	936.5	785.7	676.8	608.6	564.0	535.2
55°	933.9	1075.6	1109.7	1113.6	1008.7	847.3	705.7	609.9	544.3	514.2	489.3
57.5°	798.8	935.2	973.3	979.8	909.0	766.0	630.9	547.0	487.9	463.0	443.3
60°	683.4	797.5	847.3	861.8	800.1	671.6	561.4	480.1	435.5	411.9	393.5
62.5°	588.9	680.8	733.2	737.2	709.6	588.9	489.3	421.0	383.0	362.0	352.8
65°	497.1	579.8	611.2	627.0	604.7	510.2	422.4	366.0	335.8	317.4	308.2
67.5°	423.7	476.1	502.4	523.4	501.1	430.2	359.4	313.5	291.2	272.8	267.6
70°	347.6	390.9	410.6	431.5	411.9	358.1	306.9	265.0	245.3	230.9	224.3
72.5°	278.1	312.2	330.5	343.7	331.9	287.3	245.3	216.4	202.0	191.5	187.6
75°	220.4	244.0	254.5	263.6	258.4	224.3	198.1	174.5	161.3	152.2	149.5
77.5°	167.9	184.9	196.7	199.4	192.8	170.5	148.2	133.8	123.3	118.0	115.4
80°	119.4	129.9	136.4	140.3	133.8	124.6	108.9	98.4	89.2	82.6	81.3
82.5°	80.0	85.3	90.5	89.2	86.6	78.7	69.5	64.3	60.3	55.1	55.1
85°	45.9	47.2	49.8	51.2	49.8	44.6	39.3	36.7	34.1	30.2	30.2
87.5°	19.7	21.0	21.0	22.3	19.7	19.7	17.1	14.4	14.4	13.1	11.8
90°	15.5	11.8	9.9	8.9	6.9	4.8	2.8	0.8	2.8	4.8	6.9
92.5°	23.0	22.9	22.8	22.1	20.8	19.4	18.1	16.7	18.1	19.4	20.8
95°	47.6	47.3	47.1	46.3	44.6	42.9	41.2	39.5	41.2	42.9	44.6
97.5°	73.9	73.2	72.9	72.1	70.6	69.1	67.5	66.0	67.5	69.1	70.6
100°	103.2	102.7	102.5	101.8	100.5	99.1	97.8	96.4	97.8	99.1	100.5
102.5°	133.8	133.1	132.8	132.3	131.3	130.3	129.3	128.3	129.3	130.3	131.3
105°	166.0	165.7	165.5	165.2	164.7	164.2	163.7	163.2	163.7	164.2	164.7
107.5°	201.1	201.1	201.1	200.8	200.1	199.4	198.8	198.1	198.8	199.4	200.1
110°	236.0	236.0	236.0	235.5	234.5	233.5	232.5	231.5	232.5	233.5	234.5

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	272.2	272.4	272.5	272.0	271.0	269.9	268.9	267.9	268.9	269.9	271.0
115°	307.6	307.9	308.1	307.6	306.6	305.6	304.6	303.6	304.6	305.6	306.6
117.5°	344.0	344.9	345.3	344.6	343.3	342.0	340.6	339.3	340.6	342.0	343.3
120°	379.0	380.3	381.0	380.3	379.0	377.6	376.3	374.9	376.3	377.6	379.0
122.5°	413.9	414.7	415.1	414.3	412.6	410.9	409.3	407.6	409.3	410.9	412.6
125°	447.8	448.3	448.5	447.7	446.2	444.7	443.2	441.7	443.2	444.7	446.2
127.5°	482.5	483.2	483.5	482.6	480.7	478.8	477.0	475.1	477.0	478.8	480.7
130°	515.6	515.9	516.1	515.0	512.8	510.6	508.4	506.2	508.4	510.6	512.8
132.5°	549.0	548.8	548.7	547.9	546.2	544.5	542.8	541.1	542.8	544.5	546.2
135°	580.3	580.0	579.8	578.9	577.0	575.2	573.3	571.5	573.3	575.2	577.0
137.5°	612.2	611.9	611.7	610.9	609.4	607.9	606.4	604.9	606.4	607.9	609.4
140°	642.6	641.7	641.3	640.5	639.0	637.5	636.0	634.5	636.0	637.5	639.0
142.5°	672.5	672.0	671.7	670.9	669.4	667.9	666.3	664.8	666.3	667.9	669.4
145°	700.5	699.5	699.0	698.4	697.2	696.1	694.9	693.7	694.9	696.1	697.2
147.5°	727.3	726.6	726.3	725.5	724.0	722.5	721.0	719.5	721.0	722.5	724.0
150°	751.6	750.9	750.6	750.1	749.1	748.1	747.1	746.1	747.1	748.1	749.1
152.5°	775.4	774.5	774.1	773.6	772.6	771.6	770.6	769.6	770.6	771.6	772.6
155°	796.2	795.7	795.4	795.1	794.6	794.1	793.6	793.1	793.6	794.1	794.6
157.5°	815.6	815.3	815.1	814.9	814.6	814.3	813.9	813.6	813.9	814.3	814.6
160°	833.6	833.4	833.3	833.1	832.8	832.5	832.1	831.8	832.1	832.5	832.8
162.5°	848.8	848.6	848.5	848.5	848.5	848.5	848.5	848.5	848.5	848.5	848.5
165°	862.2	862.2	862.2	862.3	862.4	862.6	862.7	862.9	862.7	862.6	862.4
167.5°	873.6	873.6	873.6	873.8	874.3	874.8	875.3	875.8	875.3	874.8	874.3
170°	883.2	883.3	883.4	883.7	884.2	884.7	885.2	885.7	885.2	884.7	884.2
172.5°	890.0	890.2	890.3	890.5	891.0	891.5	892.0	892.5	892.0	891.5	891.0
175°	895.1	895.4	895.6	895.8	896.3	896.8	897.3	897.8	897.3	896.8	896.3
177.5°	898.1	898.4	898.6	898.9	899.4	899.9	900.4	900.9	900.4	899.9	899.4
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1688.1	1694.7	1693.4	1680.2	1665.8	1654.0	1631.7	1634.3	1626.5	1627.8	1635.6
5°	1646.1	1646.1	1640.9	1622.5	1598.9	1585.8	1560.9	1554.3	1538.6	1537.3	1536.0
7.5°	1601.5	1595.0	1588.4	1562.2	1533.3	1512.3	1478.2	1470.4	1454.6	1444.1	1438.9
10°	1549.1	1539.9	1526.8	1496.6	1461.2	1435.0	1399.5	1389.1	1358.9	1345.8	1337.9
12.5°	1491.4	1486.1	1465.1	1440.2	1382.5	1353.6	1302.5	1313.0	1282.8	1256.6	1252.6
15°	1433.6	1414.0	1402.2	1361.5	1292.0	1278.9	1238.2	1217.2	1189.7	1168.7	1168.7
17.5°	1377.2	1347.1	1320.8	1277.6	1226.4	1189.7	1159.5	1149.0	1114.9	1093.9	1090.0
20°	1302.5	1268.4	1261.8	1200.2	1164.8	1124.1	1095.2	1069.0	1044.1	1034.9	1028.3
22.5°	1231.7	1192.3	1181.8	1129.3	1093.9	1053.3	1024.4	1006.0	987.7	981.1	969.3
25°	1155.6	1132.0	1116.2	1059.8	1020.5	982.4	962.8	949.6	932.6	931.3	923.4
27.5°	1082.1	1059.8	1044.1	990.3	961.4	926.0	910.3	895.9	886.7	882.7	878.8
30°	1019.2	994.2	975.9	936.5	901.1	872.3	859.1	850.0	844.7	838.2	836.8
32.5°	949.6	935.2	910.3	880.1	852.6	825.0	817.2	810.6	802.7	800.1	798.8
35°	890.6	870.9	855.2	821.1	809.3	785.7	776.5	771.3	760.8	758.1	755.5
37.5°	832.9	814.5	797.5	776.5	754.2	741.1	735.8	728.0	722.7	724.0	721.4
40°	775.2	760.8	747.6	725.3	712.2	705.7	695.2	687.3	684.7	686.0	684.7
42.5°	718.8	705.7	697.8	680.8	667.6	661.1	654.5	646.6	650.6	650.6	654.5
45°	667.6	655.8	650.6	637.5	629.6	619.1	612.5	611.2	616.5	615.2	615.2
47.5°	615.2	611.2	604.7	592.9	582.4	575.8	574.5	574.5	579.8	582.4	581.1
50°	574.5	566.6	558.8	549.6	541.7	539.1	535.2	537.8	543.0	543.0	545.7
52.5°	523.4	518.1	515.5	507.6	502.4	502.4	502.4	503.7	507.6	511.5	510.2
55°	478.8	474.8	472.2	468.3	461.7	463.0	461.7	464.3	468.3	472.2	474.8
57.5°	431.5	430.2	427.6	421.0	421.0	419.7	423.7	425.0	431.5	434.2	438.1
60°	389.6	385.6	385.6	380.4	380.4	380.4	384.3	388.3	393.5	394.8	397.4
62.5°	345.0	345.0	343.7	339.7	339.7	343.7	345.0	350.2	352.8	352.8	356.8
65°	303.0	301.7	300.4	301.7	303.0	303.0	306.9	309.6	312.2	313.5	314.8
67.5°	261.0	259.7	262.3	261.0	263.6	268.9	267.6	271.5	275.4	275.4	276.8
70°	221.7	224.3	223.0	225.6	224.3	226.9	230.9	232.2	232.2	233.5	237.4
72.5°	184.9	184.9	184.9	183.6	184.9	187.6	190.2	191.5	194.1	195.4	199.4
75°	149.5	149.5	146.9	149.5	149.5	152.2	154.8	154.8	154.8	157.4	161.3
77.5°	112.8	114.1	112.8	115.4	115.4	116.7	119.4	118.0	120.7	122.0	123.3
80°	82.6	81.3	81.3	81.3	82.6	82.6	85.3	86.6	86.6	90.5	87.9
82.5°	52.5	53.8	52.5	53.8	53.8	55.1	53.8	55.1	56.4	59.0	57.7
85°	30.2	28.9	28.9	30.2	28.9	28.9	30.2	28.9	30.2	28.9	30.2
87.5°	11.8	10.5	10.5	10.5	10.5	9.2	9.2	7.9	7.9	7.9	6.6
90°	8.9	9.9	11.8	15.5	19.2	22.9	26.6	26.2	25.9	25.5	25.2
92.5°	22.1	22.8	22.9	23.0	23.2	23.3	23.5	23.7	23.9	24.0	24.2
95°	46.3	47.1	47.3	47.6	47.9	48.3	48.6	48.6	48.6	48.6	48.6
97.5°	72.1	72.9	73.2	73.9	74.6	75.2	75.9	75.9	75.9	75.9	75.9
100°	101.8	102.5	102.7	103.2	103.7	104.2	104.7	104.7	104.7	104.7	104.7
102.5°	132.3	132.8	133.1	133.8	134.5	135.2	135.9	136.1	136.2	136.4	136.5
105°	165.2	165.5	165.7	166.0	166.3	166.7	167.0	167.3	167.7	168.0	168.3
107.5°	200.8	201.1	201.1	201.1	201.1	201.1	201.1	201.3	201.5	201.6	201.8
110°	235.5	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	272.0	272.5	272.4	272.2	272.1	271.9	271.7	271.2	270.7	270.2	269.7
115°	307.6	308.1	307.9	307.6	307.3	306.9	306.6	306.4	306.3	306.1	306.0
117.5°	344.6	345.3	344.9	344.0	343.2	342.3	341.5	341.0	340.5	340.0	339.5
120°	380.3	381.0	380.3	379.0	377.6	376.3	374.9	374.9	374.9	374.9	374.9
122.5°	414.3	415.1	414.7	413.9	413.0	412.2	411.4	410.9	410.4	409.9	409.4
125°	447.7	448.5	448.3	447.8	447.3	446.8	446.3	445.8	445.3	444.8	444.3
127.5°	482.6	483.5	483.2	482.5	481.8	481.1	480.4	479.7	479.1	478.4	477.7
130°	515.0	516.1	515.9	515.6	515.3	514.9	514.6	514.3	513.9	513.6	513.3
132.5°	547.9	548.7	548.8	549.0	549.1	549.3	549.5	548.7	547.8	547.0	546.1
135°	578.9	579.8	580.0	580.3	580.7	581.0	581.4	581.2	581.0	580.9	580.7
137.5°	610.9	611.7	611.9	612.2	612.5	612.9	613.2	613.0	612.9	612.7	612.6
140°	640.5	641.3	641.7	642.6	643.4	644.3	645.1	645.1	645.1	645.1	645.1
142.5°	670.9	671.7	672.0	672.5	673.0	673.5	674.0	674.2	674.3	674.5	674.6
145°	698.4	699.0	699.5	700.5	701.6	702.6	703.6	703.8	703.9	704.1	704.2
147.5°	725.5	726.3	726.6	727.3	728.0	728.7	729.4	729.7	730.1	730.4	730.7
150°	750.1	750.6	750.9	751.6	752.3	752.9	753.6	754.1	754.6	755.1	755.6
152.5°	773.6	774.1	774.5	775.4	776.2	777.1	777.9	778.6	779.3	780.0	780.7
155°	795.1	795.4	795.7	796.2	796.7	797.2	797.7	798.5	799.4	800.2	801.1
157.5°	814.9	815.1	815.3	815.6	815.9	816.3	816.6	817.8	819.0	820.1	821.3
160°	833.1	833.3	833.4	833.6	833.7	833.9	834.1	835.1	836.1	837.1	838.1
162.5°	848.5	848.5	848.6	848.8	848.9	849.1	849.3	850.5	851.7	852.8	854.0
165°	862.3	862.2	862.2	862.2	862.2	862.2	862.2	863.4	864.6	865.7	866.9
167.5°	873.8	873.6	873.6	873.6	873.6	873.6	873.6	874.8	876.0	877.1	878.3
170°	883.7	883.4	883.3	883.2	883.0	882.9	882.7	883.9	885.1	886.2	887.4
172.5°	890.5	890.3	890.2	890.0	889.9	889.7	889.5	890.7	891.9	893.0	894.2
175°	895.8	895.6	895.4	895.1	894.7	894.4	894.0	895.2	896.4	897.6	898.8
177.5°	898.9	898.6	898.4	898.1	897.8	897.4	897.1	898.1	899.1	900.1	901.1
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1626.5	1630.4	1621.2	1618.6	1621.2	1612.0	1614.7	1617.3	1617.3	1621.2	1623.8
5°	1532.0	1526.8	1517.6	1515.0	1512.3	1516.3	1513.7	1517.6	1518.9	1528.1	1529.4
7.5°	1438.9	1431.0	1423.2	1415.3	1412.7	1406.1	1412.7	1412.7	1421.8	1419.2	1425.8
10°	1328.7	1327.4	1316.9	1313.0	1307.7	1297.2	1311.7	1307.7	1314.3	1326.1	1328.7
12.5°	1247.4	1233.0	1239.5	1221.2	1227.7	1217.2	1218.5	1218.5	1229.0	1230.3	1227.7
15°	1170.0	1158.2	1141.1	1133.3	1129.3	1124.1	1141.1	1142.5	1134.6	1153.0	1146.4
17.5°	1091.3	1091.3	1075.6	1071.6	1061.1	1066.4	1063.8	1065.1	1062.4	1075.6	1082.1
20°	1023.1	1016.5	1011.3	1012.6	999.5	996.9	994.2	996.9	1006.0	1015.2	1017.9
22.5°	968.0	964.1	951.0	953.6	943.1	947.0	944.4	951.0	952.3	952.3	961.4
25°	915.5	910.3	911.6	906.4	902.4	902.4	898.5	902.4	907.7	910.3	911.6
27.5°	876.2	872.3	865.7	861.8	864.4	857.8	863.1	867.0	867.0	864.4	867.0
30°	829.0	831.6	831.6	818.5	823.7	821.1	825.0	827.7	827.7	829.0	826.3
32.5°	797.5	789.6	788.3	787.0	787.0	781.8	781.8	785.7	787.0	788.3	792.2
35°	755.5	755.5	749.0	752.9	747.6	749.0	747.6	749.0	751.6	747.6	751.6
37.5°	717.5	718.8	716.2	718.8	720.1	717.5	714.9	720.1	717.5	717.5	714.9
40°	684.7	683.4	684.7	684.7	684.7	686.0	683.4	683.4	683.4	680.8	678.1
42.5°	657.1	649.3	651.9	653.2	649.3	649.3	650.6	649.3	653.2	645.3	645.3
45°	617.8	615.2	616.5	616.5	619.1	615.2	617.8	619.1	615.2	613.9	611.2
47.5°	582.4	585.0	582.4	585.0	585.0	587.6	582.4	583.7	585.0	579.8	575.8
50°	547.0	547.0	550.9	549.6	550.9	548.3	548.3	547.0	548.3	545.7	541.7
52.5°	514.2	510.2	516.8	515.5	514.2	512.9	511.5	512.9	510.2	507.6	507.6
55°	473.5	473.5	477.4	478.8	478.8	476.1	473.5	474.8	473.5	472.2	470.9
57.5°	440.7	435.5	438.1	439.4	439.4	435.5	438.1	435.5	435.5	436.8	432.8
60°	398.7	398.7	396.1	400.1	400.1	397.4	397.4	398.7	396.1	394.8	393.5
62.5°	354.1	355.5	359.4	360.7	362.0	359.4	356.8	358.1	358.1	354.1	355.5
65°	316.1	318.7	324.0	322.7	320.0	321.4	318.7	320.0	316.1	317.4	313.5
67.5°	279.4	278.1	279.4	279.4	282.0	280.7	278.1	278.1	276.8	280.7	276.8
70°	240.0	240.0	240.0	240.0	241.3	242.7	240.0	237.4	238.7	236.1	234.8
72.5°	199.4	200.7	199.4	202.0	198.1	200.7	200.7	199.4	198.1	198.1	198.1
75°	161.3	164.0	160.0	161.3	160.0	162.6	161.3	161.3	158.7	157.4	158.7
77.5°	123.3	124.6	122.0	123.3	122.0	123.3	123.3	122.0	122.0	122.0	122.0
80°	87.9	89.2	87.9	86.6	85.3	87.9	85.3	86.6	87.9	86.6	89.2
82.5°	56.4	56.4	55.1	56.4	53.8	53.8	55.1	55.1	53.8	56.4	53.8
85°	27.5	27.5	30.2	27.5	26.2	26.2	26.2	27.5	26.2	28.9	27.5
87.5°	6.6	5.2	6.6	6.6	5.2	5.2	6.6	5.2	6.6	7.9	5.2
90°	25.0	25.1	25.3	25.4	25.6	25.8	25.6	25.4	25.3	25.1	25.0
92.5°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3
95°	48.6	48.4	48.1	47.8	47.4	47.1	47.4	47.8	48.1	48.4	48.6
97.5°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9
100°	104.7	104.6	104.5	104.3	104.2	104.0	104.2	104.3	104.5	104.6	104.7
102.5°	136.6	136.5	136.4	136.2	136.1	135.9	136.1	136.2	136.4	136.5	136.6
105°	168.5	168.5	168.5	168.5	168.5	168.5	168.5	168.5	168.5	168.5	168.5
107.5°	201.9	201.5	200.6	199.8	198.9	198.1	198.9	199.8	200.6	201.5	201.9
110°	236.0	235.8	235.3	234.8	234.3	233.8	234.3	234.8	235.3	235.8	236.0

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	269.4	269.2	268.9	268.6	268.2	267.9	268.2	268.6	268.9	269.2	269.4
115°	305.9	305.6	305.1	304.6	304.1	303.6	304.1	304.6	305.1	305.6	305.9
117.5°	339.3	339.0	338.5	338.0	337.5	337.0	337.5	338.0	338.5	339.0	339.3
120°	374.9	374.6	374.1	373.6	373.1	372.6	373.1	373.6	374.1	374.6	374.9
122.5°	409.1	408.9	408.6	408.3	407.9	407.6	407.9	408.3	408.6	408.9	409.1
125°	444.0	443.9	443.7	443.6	443.4	443.2	443.4	443.6	443.7	443.9	444.0
127.5°	477.4	477.1	476.6	476.1	475.6	475.1	475.6	476.1	476.6	477.1	477.4
130°	513.1	512.8	512.1	511.4	510.7	510.0	510.7	511.4	512.1	512.8	513.1
132.5°	545.7	545.4	544.9	544.4	543.9	543.4	543.9	544.4	544.9	545.4	545.7
135°	580.6	580.3	579.8	579.3	578.8	578.3	578.8	579.3	579.8	580.3	580.6
137.5°	612.5	612.2	611.5	610.8	610.1	609.4	610.1	610.8	611.5	612.2	612.5
140°	645.1	644.8	644.1	643.4	642.8	642.1	642.8	643.4	644.1	644.8	645.1
142.5°	674.7	674.4	673.7	673.0	672.4	671.7	672.4	673.0	673.7	674.4	674.7
145°	704.3	704.0	703.3	702.6	702.0	701.3	702.0	702.6	703.3	704.0	704.3
147.5°	730.9	730.6	729.9	729.2	728.5	727.8	728.5	729.2	729.9	730.6	730.9
150°	755.9	755.6	755.1	754.6	754.1	753.6	754.1	754.6	755.1	755.6	755.9
152.5°	781.0	780.7	780.0	779.3	778.6	777.9	778.6	779.3	780.0	780.7	781.0
155°	801.5	801.2	800.7	800.2	799.7	799.2	799.7	800.2	800.7	801.2	801.5
157.5°	821.9	821.5	820.7	819.8	819.0	818.2	819.0	819.8	820.7	821.5	821.9
160°	838.6	838.3	837.6	836.9	836.3	835.6	836.3	836.9	837.6	838.3	838.6
162.5°	854.6	854.2	853.3	852.5	851.6	850.8	851.6	852.5	853.3	854.2	854.6
165°	867.5	867.1	866.2	865.4	864.5	863.7	864.5	865.4	866.2	867.1	867.5
167.5°	878.9	878.5	877.6	876.8	875.9	875.1	875.9	876.8	877.6	878.5	878.9
170°	888.0	887.5	886.5	885.4	884.4	883.4	884.4	885.4	886.5	887.5	888.0
172.5°	894.8	894.3	893.3	892.3	891.3	890.3	891.3	892.3	893.3	894.3	894.8
175°	899.4	898.9	897.9	896.8	895.8	894.8	895.8	896.8	897.9	898.9	899.4
177.5°	901.6	901.1	900.1	899.1	898.1	897.1	898.1	899.1	900.1	901.1	901.6
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1619.9	1630.4	1626.5	1612.0	1629.1	1629.1	1640.9	1640.9	1655.3	1660.6	1668.4
5°	1528.1	1536.0	1542.5	1536.0	1547.8	1566.1	1576.6	1585.8	1605.5	1613.3	1625.2
7.5°	1429.7	1444.1	1450.7	1450.7	1470.4	1491.4	1512.3	1525.5	1553.0	1563.5	1575.3
10°	1334.0	1351.0	1364.1	1362.8	1395.6	1408.7	1435.0	1465.1	1492.7	1508.4	1525.5
12.5°	1233.0	1242.1	1260.5	1286.7	1294.6	1318.2	1348.4	1386.4	1436.3	1450.7	1475.6
15°	1149.0	1173.9	1188.4	1200.2	1218.5	1240.8	1273.6	1310.4	1360.2	1391.7	1417.9
17.5°	1078.2	1111.0	1120.2	1117.5	1141.1	1175.2	1213.3	1240.8	1285.4	1323.5	1348.4
20°	1020.5	1033.6	1049.3	1055.9	1074.3	1111.0	1147.7	1179.2	1215.9	1246.1	1274.9
22.5°	962.8	973.3	986.4	998.2	1012.6	1033.6	1069.0	1108.4	1143.8	1172.6	1205.4
25°	915.5	922.1	933.9	943.1	958.8	973.3	998.2	1041.5	1083.4	1100.5	1129.3
27.5°	869.6	874.9	882.7	893.2	901.1	915.5	937.8	973.3	1016.5	1033.6	1072.9
30°	829.0	832.9	840.8	846.0	850.0	867.0	884.1	911.6	944.4	968.0	996.9
32.5°	790.9	794.9	802.7	804.0	809.3	818.5	834.2	859.1	888.0	907.7	932.6
35°	749.0	751.6	759.5	762.1	766.0	773.9	785.7	804.0	830.3	844.7	867.0
37.5°	716.2	714.9	720.1	724.0	729.3	733.2	737.2	755.5	775.2	788.3	805.4
40°	680.8	678.1	679.4	684.7	687.3	692.6	692.6	710.9	724.0	734.5	747.6
42.5°	645.3	644.0	641.4	644.0	646.6	648.0	649.3	662.4	675.5	684.7	699.1
45°	609.9	608.6	606.0	607.3	607.3	609.9	613.9	619.1	628.3	636.2	644.0
47.5°	577.1	574.5	570.6	569.3	571.9	571.9	571.9	577.1	586.3	588.9	596.8
50°	543.0	539.1	533.8	531.2	531.2	529.9	532.5	533.8	541.7	544.3	550.9
52.5°	506.3	503.7	498.4	493.2	494.5	491.9	493.2	494.5	497.1	501.1	505.0
55°	469.6	464.3	460.4	459.1	455.1	455.1	451.2	456.5	455.1	456.5	461.7
57.5°	434.2	428.9	422.4	419.7	415.8	414.5	411.9	410.6	411.9	415.8	419.7
60°	392.2	389.6	385.6	381.7	379.1	375.1	372.5	372.5	371.2	371.2	372.5
62.5°	351.5	350.2	345.0	343.7	341.0	338.4	334.5	331.9	331.9	334.5	335.8
65°	312.2	310.9	306.9	305.6	299.1	296.4	295.1	293.8	291.2	291.2	291.2
67.5°	275.4	271.5	271.5	265.0	259.7	257.1	254.5	253.2	253.2	253.2	254.5
70°	234.8	234.8	230.9	226.9	221.7	223.0	219.0	215.1	215.1	212.5	213.8
72.5°	195.4	194.1	190.2	188.9	184.9	181.0	178.4	181.0	177.1	175.8	177.1
75°	157.4	156.1	153.5	150.8	152.2	148.2	144.3	143.0	143.0	140.3	140.3
77.5°	120.7	123.3	118.0	116.7	114.1	111.5	110.2	108.9	108.9	108.9	111.5
80°	83.9	85.3	85.3	82.6	83.9	80.0	80.0	80.0	76.1	77.4	78.7
82.5°	53.8	53.8	52.5	53.8	52.5	52.5	51.2	51.2	49.8	49.8	51.2
85°	30.2	28.9	27.5	30.2	28.9	28.9	27.5	27.5	27.5	27.5	27.5
87.5°	6.6	7.9	7.9	7.9	7.9	9.2	9.2	9.2	10.5	10.5	10.5
90°	25.2	25.5	25.9	26.2	26.6	22.9	19.2	15.5	11.8	9.9	8.9
92.5°	24.2	24.0	23.9	23.7	23.5	23.3	23.2	23.0	22.9	22.8	22.1
95°	48.6	48.6	48.6	48.6	48.6	48.3	47.9	47.6	47.3	47.1	46.3
97.5°	75.9	75.9	75.9	75.9	75.9	75.2	74.6	73.9	73.2	72.9	72.1
100°	104.7	104.7	104.7	104.7	104.7	104.2	103.7	103.2	102.7	102.5	101.8
102.5°	136.5	136.4	136.2	136.1	135.9	135.2	134.5	133.8	133.1	132.8	132.3
105°	168.3	168.0	167.7	167.3	167.0	166.7	166.3	166.0	165.7	165.5	165.2
107.5°	201.8	201.6	201.5	201.3	201.1	201.1	201.1	201.1	201.1	201.1	200.8
110°	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	235.5

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	269.7	270.2	270.7	271.2	271.7	271.9	272.1	272.2	272.4	272.5	272.0
115°	306.0	306.1	306.3	306.4	306.6	306.9	307.3	307.6	307.9	308.1	307.6
117.5°	339.5	340.0	340.5	341.0	341.5	342.3	343.2	344.0	344.9	345.3	344.6
120°	374.9	374.9	374.9	374.9	374.9	376.3	377.6	379.0	380.3	381.0	380.3
122.5°	409.4	409.9	410.4	410.9	411.4	412.2	413.0	413.9	414.7	415.1	414.3
125°	444.3	444.8	445.3	445.8	446.3	446.8	447.3	447.8	448.3	448.5	447.7
127.5°	477.7	478.4	479.1	479.7	480.4	481.1	481.8	482.5	483.2	483.5	482.6
130°	513.3	513.6	513.9	514.3	514.6	514.9	515.3	515.6	515.9	516.1	515.0
132.5°	546.1	547.0	547.8	548.7	549.5	549.3	549.1	549.0	548.8	548.7	547.9
135°	580.7	580.9	581.0	581.2	581.4	581.0	580.7	580.3	580.0	579.8	578.9
137.5°	612.6	612.7	612.9	613.0	613.2	612.9	612.5	612.2	611.9	611.7	610.9
140°	645.1	645.1	645.1	645.1	645.1	644.3	643.4	642.6	641.7	641.3	640.5
142.5°	674.6	674.5	674.3	674.2	674.0	673.5	673.0	672.5	672.0	671.7	670.9
145°	704.2	704.1	703.9	703.8	703.6	702.6	701.6	700.5	699.5	699.0	698.4
147.5°	730.7	730.4	730.1	729.7	729.4	728.7	728.0	727.3	726.6	726.3	725.5
150°	755.6	755.1	754.6	754.1	753.6	752.9	752.3	751.6	750.9	750.6	750.1
152.5°	780.7	780.0	779.3	778.6	777.9	777.1	776.2	775.4	774.5	774.1	773.6
155°	801.1	800.2	799.4	798.5	797.7	797.2	796.7	796.2	795.7	795.4	795.1
157.5°	821.3	820.1	819.0	817.8	816.6	816.3	815.9	815.6	815.3	815.1	814.9
160°	838.1	837.1	836.1	835.1	834.1	833.9	833.7	833.6	833.4	833.3	833.1
162.5°	854.0	852.8	851.7	850.5	849.3	849.1	848.9	848.8	848.6	848.5	848.5
165°	866.9	865.7	864.6	863.4	862.2	862.2	862.2	862.2	862.2	862.2	862.3
167.5°	878.3	877.1	876.0	874.8	873.6	873.6	873.6	873.6	873.6	873.6	873.8
170°	887.4	886.2	885.1	883.9	882.7	882.9	883.0	883.2	883.3	883.4	883.7
172.5°	894.2	893.0	891.9	890.7	889.5	889.7	889.9	890.0	890.2	890.3	890.5
175°	898.8	897.6	896.4	895.2	894.0	894.4	894.7	895.1	895.4	895.6	895.8
177.5°	901.1	900.1	899.1	898.1	897.1	897.4	897.8	898.1	898.4	898.6	898.9
180°	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4	899.4

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1706.5	1706.5	1706.5	1706.5
2.5°	1675.0	1675.0	1694.7	1715.7
5°	1638.3	1647.4	1678.9	1707.8
7.5°	1602.9	1618.6	1657.9	1694.7
10°	1559.6	1580.6	1629.1	1672.4
12.5°	1517.6	1537.3	1593.7	1642.2
15°	1458.6	1483.5	1543.8	1604.2
17.5°	1399.5	1424.5	1497.9	1568.7
20°	1330.0	1362.8	1445.5	1539.9
22.5°	1265.8	1306.4	1398.2	1474.3
25°	1194.9	1257.9	1343.1	1441.5
27.5°	1132.0	1194.9	1281.5	1381.2
30°	1061.1	1125.4	1214.6	1306.4
32.5°	992.9	1052.0	1138.5	1251.3
35°	922.1	978.5	1062.4	1176.6
37.5°	857.8	912.9	1004.7	1109.7
40°	794.9	852.6	931.3	1036.2
42.5°	735.8	787.0	857.8	962.8
45°	682.1	718.8	784.4	882.7
47.5°	625.7	658.5	718.8	817.2
50°	573.2	600.7	653.2	745.0
52.5°	522.0	545.7	594.2	667.6
55°	476.1	498.4	533.8	606.0
57.5°	428.9	446.0	480.1	537.8
60°	383.0	398.7	426.3	473.5
62.5°	337.1	350.2	376.4	414.5
65°	296.4	306.9	326.6	359.4
67.5°	257.1	263.6	279.4	305.6
70°	219.0	224.3	237.4	258.4
72.5°	178.4	183.6	198.1	212.5
75°	144.3	145.6	156.1	167.9
77.5°	112.8	111.5	119.4	128.5
80°	77.4	81.3	87.9	91.8
82.5°	52.5	53.8	56.4	59.0
85°	28.9	30.2	30.2	34.1
87.5°	11.8	13.1	13.1	14.4
90°	6.9	4.8	2.8	0.8
92.5°	20.8	19.4	18.1	16.7
95°	44.6	42.9	41.2	39.5
97.5°	70.6	69.1	67.5	66.0
100°	100.5	99.1	97.8	96.4
102.5°	131.3	130.3	129.3	128.3
105°	164.7	164.2	163.7	163.2
107.5°	200.1	199.4	198.8	198.1
110°	234.5	233.5	232.5	231.5

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	271.0	269.9	268.9	267.9
115°	306.6	305.6	304.6	303.6
117.5°	343.3	342.0	340.6	339.3
120°	379.0	377.6	376.3	374.9
122.5°	412.6	410.9	409.3	407.6
125°	446.2	444.7	443.2	441.7
127.5°	480.7	478.8	477.0	475.1
130°	512.8	510.6	508.4	506.2
132.5°	546.2	544.5	542.8	541.1
135°	577.0	575.2	573.3	571.5
137.5°	609.4	607.9	606.4	604.9
140°	639.0	637.5	636.0	634.5
142.5°	669.4	667.9	666.3	664.8
145°	697.2	696.1	694.9	693.7
147.5°	724.0	722.5	721.0	719.5
150°	749.1	748.1	747.1	746.1
152.5°	772.6	771.6	770.6	769.6
155°	794.6	794.1	793.6	793.1
157.5°	814.6	814.3	813.9	813.6
160°	832.8	832.5	832.1	831.8
162.5°	848.5	848.5	848.5	848.5
165°	862.4	862.6	862.7	862.9
167.5°	874.3	874.8	875.3	875.8
170°	884.2	884.7	885.2	885.7
172.5°	891.0	891.5	892.0	892.5
175°	896.3	896.8	897.3	897.8
177.5°	899.4	899.9	900.4	900.9
180°	899.4	899.4	899.4	899.4

TEST NUMBER: P999192

CATALOG NUMBER: SA2XXDIP-B865D725UB40-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.18	19.10	19.05	19.99	21.11	15.67	16.59	16.55	17.48	18.60
	3H	19.00	19.82	19.88	20.71	21.87	17.02	17.84	17.91	18.74	19.89
	4H	19.17	19.94	20.07	20.85	22.01	17.49	18.26	18.39	19.17	20.33
	6H	19.21	19.93	20.13	20.84	22.01	17.80	18.51	18.71	19.42	20.59
	8H	19.20	19.87	20.12	20.80	21.97	17.88	18.56	18.80	19.49	20.66
	12H	19.16	19.80	20.09	20.73	21.92	17.93	18.57	18.85	19.49	20.69
4H	2H	18.23	19.00	19.14	19.91	21.07	16.13	16.90	17.03	17.80	18.96
	3H	19.21	19.86	20.13	20.79	21.97	17.59	18.23	18.51	19.17	20.35
	4H	19.49	20.08	20.42	21.01	22.21	18.13	18.71	19.06	19.65	20.85
	6H	19.63	20.13	20.57	21.09	22.29	18.51	19.01	19.45	19.97	21.17
	8H	19.62	20.10	20.57	21.04	22.26	18.62	19.09	19.57	20.04	21.26
	12H	19.59	20.02	20.55	20.98	22.20	18.68	19.10	19.64	20.07	21.29
8H	4H	19.51	19.98	20.45	20.93	22.14	18.27	18.75	19.22	19.69	20.91
	6H	19.69	20.07	20.66	21.07	22.28	18.71	19.10	19.68	20.09	21.30
	8H	19.72	20.06	20.70	21.04	22.27	18.86	19.20	19.84	20.19	21.42
	12H	19.70	20.01	20.69	20.98	22.26	18.96	19.26	19.94	20.23	21.51
12H	4H	19.46	19.89	20.43	20.86	22.08	18.25	18.67	19.21	19.64	20.86
	6H	19.66	20.01	20.64	20.99	22.22	18.71	19.05	19.69	20.04	21.27
	8H	19.70	20.00	20.68	20.98	22.26	18.87	19.17	19.85	20.15	21.43