

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999201

Luminaire Tested: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999201
REPORT IS A COMBINATION OF REPORTS P984950 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6074.0 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60		
1	101	96	93	89	94	90	87	84	79	76	74	68	67	65	59	57	56	52		
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48	44		
3	84	75	68	62	79	71	64	59	62	57	53	54	50	47	47	44	42	38		
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37	33		
5	71	60	52	46	67	57	49	44	50	44	40	44	40	36	38	35	32	29		
6	66	54	46	40	62	51	44	39	45	40	35	40	35	32	35	31	29	26		
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	29	26	23		
8	57	45	37	32	53	42	35	31	38	32	28	34	29	26	30	26	23	21		
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21	19		
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26115	26115	26115	26115
5°	26178	27845	26278	22153
10°	25874	30397	26037	18265
15°	25247	32063	25598	15385
20°	24853	30104	24853	13372
25°	24061	25863	24170	11959
30°	22757	20330	23191	10831
35°	21603	14059	21964	9910
40°	20276	10614	20506	9175
45°	18638	8722	18944	8382
50°	17225	7655	17256	7674
55°	15612	6524	15713	6904
60°	13892	5449	14083	6025
65°	12353	4432	12577	5146
70°	10818	3478	11095	4150
75°	9079	2525	9437	3009
80°	7090	1600	7593	1787
85°	4661	804	5015	597

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 26997 cd/sqm

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.1	2.6
10°-20°	457.4	7.5
20°-30°	663.8	10.9
30°-40°	699.8	11.5
40°-50°	619.2	10.2
50°-60°	494.4	8.1
60°-70°	335.8	5.5
70°-80°	171.8	2.8
80°-90°	43.1	0.7
90°-100°	53.8	0.9
100°-110°	171.0	2.8
110°-120°	292.7	4.8
120°-130°	384.9	6.3
130°-140°	432.0	7.1
140°-150°	423.7	7.0
150°-160°	355.4	5.9
160°-170°	235.7	3.9
170°-180°	82.4	1.4
0°-30°	1278.3	21.0
0°-40°	1978.1	32.6
0°-60°	3091.7	50.9
0°-90°	3642.5	60.0
90°-120°	517.5	8.5
90°-150°	1758.1	28.9
90°-180°	2432.0	40.0
0°-180°	6074.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1650	1650	1650	1650	1650	
5°	1651	1843	1657	1466	1651	157
15°	1551	2265	1572	1087	1551	438
25°	1394	1887	1400	872	1394	637
35°	1138	1027	1156	724	1138	712
45°	853	619	867	595	853	662
55°	586	435	590	460	586	523
65°	348	268	354	311	348	345
75°	162	132	169	157	162	174
85°	33	34	36	25	33	38
90°	1	25	1	25	1	4
95°	38	46	38	46	38	43
105°	158	163	158	163	158	167
115°	294	294	294	294	294	290
125°	427	429	427	429	427	382
135°	553	559	553	559	553	427
145°	671	678	671	678	671	419
155°	767	773	767	773	767	353
165°	834	835	834	835	834	235
175°	868	865	868	865	868	82
180°	870	870	870	870	870	

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1658.7	1662.5	1668.8	1670.1	1682.8	1692.9	1704.3	1704.3	1708.2	1706.9	1696.7
5°	1651.1	1662.5	1679.0	1692.9	1715.8	1725.9	1741.1	1752.5	1762.7	1770.3	1769.0
7.5°	1638.4	1658.7	1682.8	1709.4	1739.9	1757.6	1779.2	1799.5	1813.4	1826.1	1835.0
10°	1616.8	1651.1	1684.1	1719.6	1758.9	1783.0	1808.3	1835.0	1856.5	1880.6	1903.4
12.5°	1587.7	1637.1	1677.7	1724.6	1772.8	1799.5	1840.0	1860.3	1902.2	1963.0	1979.5
15°	1550.9	1618.1	1656.2	1715.8	1779.2	1800.7	1856.5	1889.5	1975.7	2013.8	2059.4
17.5°	1516.7	1591.5	1642.2	1710.7	1772.8	1814.7	1869.2	1936.4	2008.7	2063.2	2113.9
20°	1488.8	1561.0	1621.9	1698.0	1776.6	1829.9	1887.0	1968.1	2046.7	2102.5	2141.8
22.5°	1425.4	1517.9	1588.9	1673.9	1769.0	1842.6	1897.1	1985.9	2070.8	2105.1	2139.3
25°	1393.7	1473.5	1556.0	1652.4	1763.9	1851.4	1898.4	1997.3	2072.1	2084.8	2092.4
27.5°	1335.3	1425.4	1521.7	1632.1	1762.7	1836.2	1895.8	1985.9	2045.5	2036.6	2013.8
30°	1263.0	1373.4	1479.9	1599.1	1744.9	1824.8	1880.6	1963.0	1993.5	1947.8	1907.2
32.5°	1209.8	1313.8	1431.7	1569.9	1724.6	1800.7	1855.3	1919.9	1926.3	1843.8	1775.4
35°	1137.5	1252.9	1386.0	1531.9	1690.4	1758.9	1809.6	1848.9	1818.5	1703.1	1621.9
37.5°	1072.8	1187.0	1329.0	1477.4	1643.5	1710.7	1751.3	1757.6	1682.8	1581.3	1462.1
40°	1001.8	1119.7	1268.1	1424.1	1591.5	1649.8	1675.2	1656.2	1548.4	1430.4	1292.2
42.5°	930.8	1047.5	1207.2	1367.0	1525.5	1575.0	1585.1	1533.2	1401.3	1263.0	1103.3
45°	853.4	975.2	1135.0	1296.0	1449.5	1477.4	1478.6	1403.8	1247.8	1103.3	954.9
47.5°	790.0	902.9	1061.4	1222.5	1351.8	1370.8	1363.2	1277.0	1107.1	944.7	815.4
50°	720.3	828.1	985.3	1143.8	1254.2	1259.2	1240.2	1117.2	951.1	802.7	700.0
52.5°	645.5	754.5	899.1	1051.3	1150.2	1142.6	1105.8	973.9	817.9	694.9	616.3
55°	585.9	682.2	817.9	966.3	1036.0	1014.5	973.9	839.5	716.5	612.5	544.0
57.5°	519.9	604.9	738.0	867.4	908.0	887.7	847.1	721.6	607.4	528.8	483.2
60°	457.8	535.1	651.8	759.6	791.3	769.7	722.8	610.0	527.5	461.6	427.4
62.5°	400.7	467.9	565.6	664.5	677.2	655.6	615.0	523.7	452.7	400.7	375.4
65°	347.5	410.9	489.5	564.3	575.7	552.9	511.1	445.1	385.5	352.5	328.4
67.5°	295.5	346.2	415.9	470.5	476.8	455.3	421.0	367.8	331.0	295.5	277.7
70°	249.8	287.9	342.4	386.8	389.3	369.0	351.3	303.1	275.2	249.8	235.9
72.5°	205.4	232.1	273.9	306.9	308.2	295.5	279.0	248.6	224.5	206.7	192.8
75°	162.3	185.1	210.5	239.7	238.4	228.3	215.6	196.6	176.3	164.9	158.5
77.5°	124.3	138.2	158.5	177.5	177.5	172.5	164.9	150.9	138.2	126.8	120.5
80°	88.8	97.6	114.1	120.5	123.0	121.7	115.4	105.3	100.2	91.3	88.8
82.5°	57.1	63.4	71.0	77.4	81.2	78.6	77.4	72.3	64.7	62.1	59.6
85°	33.0	35.5	39.3	43.1	44.4	43.1	45.7	41.8	38.0	38.0	36.8
87.5°	13.9	15.2	17.8	17.8	19.0	19.0	17.8	19.0	19.0	17.8	16.5
90°	0.7	2.7	4.6	6.6	8.5	9.5	11.3	14.9	18.5	22.1	25.7
92.5°	16.1	17.4	18.7	20.0	21.3	22.0	22.1	22.3	22.4	22.6	22.8
95°	38.2	39.8	41.4	43.1	44.7	45.5	45.7	46.0	46.3	46.7	47.0
97.5°	63.9	65.4	66.8	68.3	69.8	70.5	70.8	71.5	72.1	72.8	73.4
100°	93.2	94.5	95.8	97.1	98.4	99.1	99.3	99.8	100.3	100.8	101.3
102.5°	124.0	125.0	126.0	126.9	127.9	128.4	128.7	129.4	130.1	130.7	131.4
105°	157.8	158.3	158.8	159.3	159.8	160.0	160.2	160.5	160.8	161.2	161.5
107.5°	191.6	192.2	192.9	193.5	194.2	194.5	194.5	194.5	194.5	194.5	194.5
110°	223.8	224.8	225.8	226.8	227.8	228.3	228.3	228.3	228.3	228.3	228.3

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	259.1	260.1	261.1	262.0	263.0	263.5	263.4	263.2	263.1	262.9	262.7
115°	293.6	294.6	295.6	296.5	297.5	298.0	297.8	297.5	297.2	296.8	296.5
117.5°	328.1	329.4	330.7	332.0	333.3	333.9	333.5	332.7	331.9	331.1	330.3
120°	362.6	363.9	365.2	366.5	367.8	368.4	367.8	366.5	365.2	363.9	362.6
122.5°	394.1	395.7	397.4	399.0	400.7	401.5	401.1	400.3	399.4	398.6	397.8
125°	427.1	428.6	430.1	431.6	433.1	433.8	433.5	433.0	432.5	432.0	431.5
127.5°	459.4	461.2	463.0	464.8	466.6	467.5	467.2	466.5	465.9	465.2	464.6
130°	489.5	491.6	493.8	495.9	498.0	499.1	498.9	498.6	498.3	497.9	497.6
132.5°	523.3	524.9	526.5	528.2	529.8	530.6	530.7	530.9	531.0	531.2	531.4
135°	552.6	554.4	556.2	558.0	559.8	560.7	560.9	561.2	561.5	561.9	562.2
137.5°	584.9	586.4	587.8	589.3	590.8	591.5	591.7	592.0	592.3	592.7	593.0
140°	613.6	615.1	616.5	618.0	619.5	620.2	620.6	621.4	622.2	623.0	623.8
142.5°	642.9	644.4	645.8	647.3	648.8	649.5	649.7	650.2	650.7	651.2	651.7
145°	670.8	671.9	673.1	674.2	675.3	675.9	676.4	677.4	678.4	679.4	680.4
147.5°	695.8	697.3	698.7	700.2	701.7	702.4	702.7	703.4	704.0	704.7	705.3
150°	721.4	722.4	723.4	724.4	725.4	725.9	726.2	726.9	727.5	728.2	728.8
152.5°	744.2	745.2	746.2	747.1	748.1	748.6	749.0	749.8	750.7	751.5	752.3
155°	767.0	767.5	768.0	768.5	769.0	769.2	769.4	769.9	770.4	770.9	771.4
157.5°	786.8	787.1	787.4	787.7	788.0	788.2	788.4	788.7	789.0	789.4	789.7
160°	804.4	804.7	805.1	805.4	805.7	805.9	806.0	806.1	806.3	806.4	806.6
162.5°	820.5	820.5	820.5	820.5	820.5	820.5	820.6	820.8	820.9	821.1	821.3
165°	834.5	834.3	834.1	834.0	833.8	833.7	833.7	833.7	833.7	833.7	833.7
167.5°	847.0	846.5	846.0	845.5	845.0	844.7	844.7	844.7	844.7	844.7	844.7
170°	856.5	856.0	855.5	855.0	854.5	854.3	854.2	854.1	853.9	853.8	853.6
172.5°	863.1	862.6	862.1	861.6	861.1	860.9	860.8	860.7	860.5	860.4	860.2
175°	868.2	867.7	867.2	866.7	866.2	866.0	865.8	865.5	865.2	864.9	864.6
177.5°	871.2	870.7	870.2	869.7	869.2	869.0	868.8	868.5	868.2	867.8	867.5
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1714.5	1715.8	1718.3	1731.0	1737.3	1738.6	1733.5	1744.9	1748.7	1744.9	1742.4
5°	1795.7	1803.3	1818.5	1835.0	1833.7	1835.0	1842.6	1850.2	1852.7	1842.6	1846.4
7.5°	1866.7	1881.9	1898.4	1923.7	1923.7	1936.4	1941.5	1947.8	1963.0	1955.4	1952.9
10°	1947.8	1968.1	1998.5	2039.1	2040.4	2053.1	2065.8	2086.0	2092.4	2087.3	2089.9
12.5°	2049.3	2088.6	2091.1	2135.5	2155.8	2158.3	2178.6	2174.8	2187.5	2187.5	2209.1
15°	2093.7	2154.5	2188.8	2231.9	2244.6	2229.3	2245.8	2263.6	2264.9	2264.9	2263.6
17.5°	2173.5	2197.6	2231.9	2254.7	2259.8	2259.8	2261.0	2268.7	2263.6	2253.4	2261.0
20°	2190.0	2200.2	2212.9	2210.3	2212.9	2200.2	2187.5	2174.8	2176.1	2169.7	2188.8
22.5°	2159.6	2157.1	2127.9	2108.9	2108.9	2083.5	2059.4	2048.0	2036.6	2040.4	2046.7
25°	2083.5	2044.2	2008.7	1980.8	1974.5	1933.9	1900.9	1890.8	1871.7	1887.0	1889.5
27.5°	1961.8	1917.4	1860.3	1836.2	1803.3	1786.8	1763.9	1733.5	1694.2	1717.0	1713.2
30°	1831.2	1765.2	1718.3	1660.0	1608.0	1604.2	1561.0	1510.3	1490.0	1490.0	1501.4
32.5°	1685.3	1597.8	1529.3	1446.9	1396.2	1374.6	1322.6	1271.9	1283.3	1245.3	1259.2
35°	1515.4	1400.0	1313.8	1233.9	1195.8	1170.5	1103.3	1075.4	1044.9	1027.2	1060.1
37.5°	1353.1	1219.9	1109.6	1022.1	1008.2	962.5	916.8	899.1	881.3	888.9	887.7
40°	1155.3	1037.3	938.4	869.9	845.8	824.3	793.8	772.3	760.9	767.2	768.5
42.5°	976.4	877.5	804.0	755.8	735.5	720.3	705.1	687.3	683.5	683.5	688.6
45°	838.2	757.1	707.6	668.3	656.9	645.5	634.1	626.4	623.9	618.8	622.6
47.5°	727.9	663.2	632.8	603.6	590.9	588.4	578.3	574.5	569.4	568.1	569.4
50°	635.3	594.7	566.8	550.4	541.5	537.7	532.6	525.0	522.5	528.8	526.3
52.5°	570.7	532.6	517.4	500.9	495.8	490.8	483.2	484.4	483.2	480.6	480.6
55°	506.0	481.9	466.7	454.0	452.7	447.6	441.3	438.8	437.5	435.0	438.8
57.5°	454.0	435.0	421.0	409.6	404.5	404.5	398.2	393.1	393.1	391.8	393.1
60°	402.0	383.0	374.1	362.7	358.9	357.6	353.8	351.3	347.5	347.5	347.5
62.5°	353.8	338.6	328.4	318.3	319.6	313.2	308.2	305.6	305.6	306.9	306.9
65°	308.2	298.0	285.3	276.4	273.9	272.6	270.1	268.8	265.0	267.6	267.6
67.5°	266.3	252.4	244.7	240.9	237.1	235.9	233.3	230.8	229.5	228.3	230.8
70°	224.5	213.0	206.7	204.2	200.4	199.1	197.8	194.0	195.3	196.6	197.8
72.5°	186.4	176.3	175.0	167.4	167.4	167.4	162.3	164.9	163.6	161.1	163.6
75°	147.1	142.0	139.5	135.7	137.0	135.7	134.4	130.6	130.6	131.9	133.2
77.5°	116.7	111.6	110.3	106.5	104.0	106.5	104.0	102.7	102.7	104.0	104.0
80°	86.2	83.7	79.9	79.9	79.9	78.6	78.6	78.6	77.4	76.1	77.4
82.5°	57.1	57.1	55.8	54.5	55.8	53.3	54.5	54.5	54.5	54.5	54.5
85°	36.8	35.5	35.5	34.2	34.2	34.2	35.5	33.0	33.0	34.2	34.2
87.5°	16.5	16.5	16.5	17.8	16.5	16.5	16.5	17.8	16.5	16.5	16.5
90°	25.4	25.0	24.7	24.4	24.2	24.3	24.5	24.6	24.8	25.0	24.8
92.5°	23.0	23.1	23.3	23.4	23.5	23.5	23.5	23.5	23.5	23.5	23.5
95°	47.0	47.0	47.0	47.0	47.0	46.8	46.5	46.2	45.8	45.5	45.8
97.5°	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4
100°	101.3	101.3	101.3	101.3	101.3	101.2	101.0	100.9	100.7	100.5	100.7
102.5°	131.6	131.7	131.9	132.0	132.1	132.0	131.9	131.7	131.6	131.4	131.6
105°	161.8	162.1	162.4	162.7	162.9	162.9	162.9	162.9	162.9	162.9	162.9
107.5°	194.7	194.8	195.0	195.1	195.2	194.8	194.0	193.2	192.4	191.6	192.4
110°	228.3	228.3	228.3	228.3	228.3	228.0	227.5	227.0	226.5	226.0	226.5

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	262.2	261.7	261.2	260.7	260.5	260.3	260.0	259.7	259.4	259.1	259.4
115°	296.3	296.2	296.0	295.9	295.8	295.6	295.1	294.6	294.1	293.6	294.1
117.5°	329.8	329.3	328.8	328.3	328.1	327.9	327.4	326.9	326.4	325.9	326.4
120°	362.6	362.6	362.6	362.6	362.6	362.4	361.9	361.4	360.9	360.4	360.9
122.5°	397.3	396.8	396.3	395.8	395.6	395.4	395.1	394.8	394.4	394.1	394.4
125°	431.0	430.5	430.0	429.5	429.3	429.2	429.1	428.9	428.8	428.6	428.8
127.5°	463.9	463.3	462.6	461.9	461.6	461.4	460.9	460.4	459.9	459.4	459.9
130°	497.3	496.9	496.6	496.3	496.1	495.8	495.1	494.5	493.8	493.2	493.8
132.5°	530.6	529.8	528.9	528.1	527.7	527.5	527.0	526.5	526.0	525.5	526.0
135°	562.0	561.9	561.7	561.6	561.5	561.3	560.8	560.3	559.8	559.3	559.8
137.5°	592.8	592.7	592.5	592.4	592.3	592.0	591.3	590.6	590.0	589.3	590.0
140°	623.8	623.8	623.8	623.8	623.8	623.5	622.8	622.2	621.5	620.9	621.5
142.5°	651.9	652.1	652.2	652.4	652.5	652.2	651.5	650.8	650.2	649.5	650.2
145°	680.6	680.7	680.9	681.0	681.1	680.8	680.1	679.4	678.8	678.1	678.8
147.5°	705.6	706.0	706.3	706.6	706.8	706.5	705.8	705.1	704.5	703.8	704.5
150°	729.3	729.8	730.3	730.8	731.0	730.8	730.3	729.8	729.3	728.8	729.3
152.5°	752.9	753.6	754.2	754.9	755.2	754.9	754.2	753.6	752.9	752.3	752.9
155°	772.2	773.0	773.8	774.6	775.0	774.8	774.3	773.8	773.3	772.8	773.3
157.5°	790.8	792.0	793.1	794.2	794.8	794.4	793.6	792.8	792.0	791.2	792.0
160°	807.6	808.6	809.5	810.5	811.0	810.7	810.0	809.4	808.7	808.1	808.7
162.5°	822.4	823.6	824.7	825.8	826.4	826.0	825.2	824.3	823.5	822.7	823.5
165°	834.9	836.0	837.2	838.3	838.9	838.5	837.7	836.8	836.0	835.2	836.0
167.5°	845.9	847.0	848.2	849.3	849.9	849.5	848.7	847.8	847.0	846.2	847.0
170°	854.7	855.9	857.0	858.1	858.7	858.2	857.2	856.3	855.3	854.3	855.3
172.5°	861.3	862.5	863.6	864.7	865.3	864.8	863.8	862.9	861.9	860.9	861.9
175°	865.7	866.9	868.0	869.1	869.7	869.2	868.2	867.3	866.3	865.3	866.3
177.5°	868.5	869.5	870.4	871.4	871.9	871.4	870.4	869.5	868.5	867.5	868.5
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1748.7	1739.9	1732.2	1733.5	1739.9	1734.8	1722.1	1705.6	1699.3	1691.7	1699.3
5°	1854.0	1846.4	1831.2	1832.4	1828.6	1823.5	1803.3	1777.9	1777.9	1757.6	1755.1
7.5°	1958.0	1946.6	1936.4	1933.9	1919.9	1909.8	1892.0	1856.5	1842.6	1818.5	1804.5
10°	2074.6	2065.8	2054.3	2040.4	2032.8	2015.0	1985.9	1933.9	1908.5	1875.5	1851.4
12.5°	2192.6	2191.3	2165.9	2138.0	2136.8	2108.9	2088.6	2018.8	1984.6	1940.2	1883.2
15°	2267.4	2261.0	2247.1	2233.2	2237.0	2206.5	2160.9	2078.4	2055.6	2002.4	1941.5
17.5°	2266.1	2266.1	2262.3	2259.8	2256.0	2247.1	2221.7	2167.2	2130.4	2063.2	2006.2
20°	2193.8	2210.3	2214.1	2212.9	2225.5	2231.9	2230.6	2196.4	2167.2	2107.6	2049.3
22.5°	2049.3	2087.3	2103.8	2113.9	2140.6	2154.5	2187.5	2174.8	2167.2	2122.8	2073.4
25°	1914.9	1927.5	1977.0	1979.5	2016.3	2050.5	2083.5	2105.1	2133.0	2116.5	2074.6
27.5°	1741.1	1770.3	1805.8	1832.4	1840.0	1909.8	1964.3	2004.9	2068.3	2073.4	2059.4
30°	1544.6	1558.5	1616.8	1652.4	1692.9	1743.7	1822.3	1892.0	1949.1	2001.1	2018.8
32.5°	1304.9	1362.0	1396.2	1439.3	1474.8	1564.9	1661.2	1751.3	1817.2	1904.7	1942.8
35°	1085.5	1129.9	1188.2	1206.0	1270.7	1346.7	1472.3	1587.7	1687.9	1776.6	1854.0
37.5°	904.2	939.7	1001.8	1029.7	1067.8	1165.4	1270.7	1413.9	1534.4	1643.5	1739.9
40°	779.9	806.5	853.4	862.3	894.0	982.8	1067.8	1202.2	1362.0	1509.1	1614.3
42.5°	694.9	707.6	739.3	750.7	771.0	830.6	906.7	1033.5	1181.9	1334.1	1482.4
45°	634.1	642.9	662.0	672.1	697.5	724.1	786.2	887.7	1004.3	1157.8	1317.6
47.5°	579.5	590.9	598.6	604.9	618.8	648.0	688.6	763.4	875.0	1015.8	1170.5
50°	533.9	537.7	551.6	552.9	561.8	580.8	618.8	664.5	753.3	867.4	1017.0
52.5°	488.2	492.0	500.9	509.8	513.6	528.8	554.2	592.2	658.2	748.2	881.3
55°	442.6	447.6	456.5	462.9	466.7	479.3	494.6	531.3	583.3	646.7	755.8
57.5°	396.9	408.3	410.9	414.7	421.0	435.0	448.9	470.5	511.1	569.4	649.3
60°	353.8	357.6	366.5	370.3	376.6	384.2	402.0	418.5	447.6	493.3	565.6
62.5°	309.4	318.3	322.1	325.9	331.0	339.9	351.3	369.0	394.4	431.2	488.2
65°	271.4	272.6	280.3	285.3	290.4	296.7	308.2	324.6	339.9	374.1	415.9
67.5°	234.6	237.1	239.7	244.7	251.1	257.4	267.6	276.4	295.5	318.3	351.3
70°	199.1	199.1	205.4	209.2	208.0	215.6	223.2	233.3	247.3	268.8	295.5
72.5°	167.4	166.1	171.2	172.5	175.0	180.1	185.1	195.3	202.9	219.4	239.7
75°	133.2	135.7	138.2	138.2	142.0	145.8	150.9	156.0	164.9	175.0	190.2
77.5°	105.3	105.3	107.8	109.1	112.9	111.6	116.7	121.7	128.1	137.0	148.4
80°	77.4	79.9	79.9	79.9	81.2	82.4	87.5	91.3	95.1	101.4	106.5
82.5°	54.5	54.5	57.1	57.1	57.1	59.6	59.6	60.9	63.4	67.2	71.0
85°	34.2	34.2	34.2	35.5	34.2	35.5	38.0	36.8	38.0	40.6	40.6
87.5°	16.5	16.5	16.5	16.5	16.5	17.8	16.5	17.8	19.0	19.0	19.0
90°	24.6	24.5	24.3	24.2	24.4	24.7	25.0	25.4	25.7	22.1	18.5
92.5°	23.5	23.5	23.5	23.5	23.4	23.3	23.1	23.0	22.8	22.6	22.4
95°	46.2	46.5	46.8	47.0	47.0	47.0	47.0	47.0	47.0	46.7	46.3
97.5°	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	72.8	72.1
100°	100.9	101.0	101.2	101.3	101.3	101.3	101.3	101.3	101.3	100.8	100.3
102.5°	131.7	131.9	132.0	132.1	132.0	131.9	131.7	131.6	131.4	130.7	130.1
105°	162.9	162.9	162.9	162.9	162.7	162.4	162.1	161.8	161.5	161.2	160.8
107.5°	193.2	194.0	194.8	195.2	195.1	195.0	194.8	194.7	194.5	194.5	194.5
110°	227.0	227.5	228.0	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	259.7	260.0	260.3	260.5	260.7	261.2	261.7	262.2	262.7	262.9	263.1
115°	294.6	295.1	295.6	295.8	295.9	296.0	296.2	296.3	296.5	296.8	297.2
117.5°	326.9	327.4	327.9	328.1	328.3	328.8	329.3	329.8	330.3	331.1	331.9
120°	361.4	361.9	362.4	362.6	362.6	362.6	362.6	362.6	362.6	363.9	365.2
122.5°	394.8	395.1	395.4	395.6	395.8	396.3	396.8	397.3	397.8	398.6	399.4
125°	428.9	429.1	429.2	429.3	429.5	430.0	430.5	431.0	431.5	432.0	432.5
127.5°	460.4	460.9	461.4	461.6	461.9	462.6	463.3	463.9	464.6	465.2	465.9
130°	494.5	495.1	495.8	496.1	496.3	496.6	496.9	497.3	497.6	497.9	498.3
132.5°	526.5	527.0	527.5	527.7	528.1	528.9	529.8	530.6	531.4	531.2	531.0
135°	560.3	560.8	561.3	561.5	561.6	561.7	561.9	562.0	562.2	561.9	561.5
137.5°	590.6	591.3	592.0	592.3	592.4	592.5	592.7	592.8	593.0	592.7	592.3
140°	622.2	622.8	623.5	623.8	623.8	623.8	623.8	623.8	623.8	623.0	622.2
142.5°	650.8	651.5	652.2	652.5	652.4	652.2	652.1	651.9	651.7	651.2	650.7
145°	679.4	680.1	680.8	681.1	681.0	680.9	680.7	680.6	680.4	679.4	678.4
147.5°	705.1	705.8	706.5	706.8	706.6	706.3	706.0	705.6	705.3	704.7	704.0
150°	729.8	730.3	730.8	731.0	730.8	730.3	729.8	729.3	728.8	728.2	727.5
152.5°	753.6	754.2	754.9	755.2	754.9	754.2	753.6	752.9	752.3	751.5	750.7
155°	773.8	774.3	774.8	775.0	774.6	773.8	773.0	772.2	771.4	770.9	770.4
157.5°	792.8	793.6	794.4	794.8	794.2	793.1	792.0	790.8	789.7	789.4	789.0
160°	809.4	810.0	810.7	811.0	810.5	809.5	808.6	807.6	806.6	806.4	806.3
162.5°	824.3	825.2	826.0	826.4	825.8	824.7	823.6	822.4	821.3	821.1	820.9
165°	836.8	837.7	838.5	838.9	838.3	837.2	836.0	834.9	833.7	833.7	833.7
167.5°	847.8	848.7	849.5	849.9	849.3	848.2	847.0	845.9	844.7	844.7	844.7
170°	856.3	857.2	858.2	858.7	858.1	857.0	855.9	854.7	853.6	853.8	853.9
172.5°	862.9	863.8	864.8	865.3	864.7	863.6	862.5	861.3	860.2	860.4	860.5
175°	867.3	868.2	869.2	869.7	869.1	868.0	866.9	865.7	864.6	864.9	865.2
177.5°	869.5	870.4	871.4	871.9	871.4	870.4	869.5	868.5	867.5	867.8	868.2
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1692.9	1686.6	1682.8	1685.3	1677.7	1658.7	1658.7	1665.0	1657.4	1649.8	1638.4
5°	1739.9	1727.2	1719.6	1718.3	1700.5	1670.1	1663.8	1657.4	1640.9	1623.2	1604.2
7.5°	1785.5	1762.7	1750.0	1741.1	1715.8	1676.4	1660.0	1646.0	1619.4	1592.8	1568.7
10°	1823.5	1790.6	1775.4	1761.4	1728.4	1679.0	1652.4	1627.0	1592.8	1558.5	1528.1
12.5°	1854.0	1815.9	1796.9	1776.6	1736.0	1671.4	1638.4	1597.8	1563.6	1517.9	1487.5
15°	1904.7	1826.1	1808.3	1789.3	1747.5	1658.7	1618.1	1572.5	1525.5	1464.7	1431.7
17.5°	1945.3	1840.0	1838.8	1798.2	1743.7	1653.6	1591.5	1531.9	1481.2	1420.3	1368.3
20°	1969.4	1861.6	1841.3	1799.5	1731.0	1619.4	1554.7	1488.8	1434.2	1360.7	1308.7
22.5°	1989.7	1892.0	1838.8	1788.0	1704.3	1608.0	1512.9	1450.7	1375.9	1296.0	1246.6
25°	1997.3	1898.4	1842.6	1784.2	1685.3	1575.0	1467.2	1400.0	1316.3	1244.0	1176.8
27.5°	1998.5	1897.1	1828.6	1767.8	1658.7	1531.9	1421.6	1350.5	1258.0	1174.3	1107.1
30°	1985.9	1883.2	1821.0	1755.1	1633.3	1492.6	1365.8	1287.1	1188.2	1104.5	1034.8
32.5°	1947.8	1855.3	1804.5	1732.2	1600.4	1438.0	1312.5	1225.0	1121.0	1038.6	971.4
35°	1884.4	1821.0	1765.2	1698.0	1557.2	1387.3	1259.2	1156.5	1051.3	972.6	909.2
37.5°	1805.8	1771.6	1719.6	1653.6	1507.8	1341.7	1199.6	1085.5	980.3	904.2	842.0
40°	1699.3	1708.2	1657.4	1597.8	1449.5	1279.5	1122.3	1013.2	914.3	843.3	782.4
42.5°	1583.9	1620.7	1591.5	1534.4	1384.8	1211.0	1065.2	944.7	848.4	774.8	724.1
45°	1459.6	1523.0	1505.3	1463.4	1317.6	1138.8	984.1	867.4	782.4	711.4	667.0
47.5°	1323.9	1413.9	1413.9	1383.5	1242.8	1066.5	914.3	795.1	711.4	660.7	617.6
50°	1185.7	1287.1	1303.6	1283.3	1159.1	984.1	829.3	721.6	649.3	599.8	568.1
52.5°	1041.1	1159.1	1189.5	1179.3	1070.3	905.4	759.6	654.3	588.4	545.3	517.4
55°	902.9	1039.9	1072.8	1076.6	975.2	819.2	682.2	589.7	526.3	497.1	473.0
57.5°	772.3	904.2	940.9	947.3	878.8	740.6	610.0	528.8	471.7	447.6	428.6
60°	660.7	771.0	819.2	833.2	773.6	649.3	542.8	464.1	421.0	398.2	380.4
62.5°	569.4	658.2	708.9	712.7	686.1	569.4	473.0	407.1	370.3	350.0	341.1
65°	480.6	560.5	590.9	606.2	584.6	493.3	408.3	353.8	324.6	306.9	298.0
67.5°	409.6	460.3	485.7	506.0	484.4	415.9	347.5	303.1	281.5	263.8	258.7
70°	336.1	377.9	396.9	417.2	398.2	346.2	296.7	256.2	237.1	223.2	216.8
72.5°	268.8	301.8	319.6	332.2	320.8	277.7	237.1	209.2	195.3	185.1	181.3
75°	213.0	235.9	246.0	254.9	249.8	216.8	191.5	168.7	156.0	147.1	144.6
77.5°	162.3	178.8	190.2	192.8	186.4	164.9	143.3	129.3	119.2	114.1	111.6
80°	115.4	125.5	131.9	135.7	129.3	120.5	105.3	95.1	86.2	79.9	78.6
82.5°	77.4	82.4	87.5	86.2	83.7	76.1	67.2	62.1	58.3	53.3	53.3
85°	44.4	45.7	48.2	49.5	48.2	43.1	38.0	35.5	33.0	29.2	29.2
87.5°	19.0	20.3	20.3	21.6	19.0	19.0	16.5	13.9	13.9	12.7	11.4
90°	14.9	11.3	9.5	8.5	6.6	4.6	2.7	0.7	2.7	4.6	6.6
92.5°	22.3	22.1	22.0	21.3	20.0	18.7	17.4	16.1	17.4	18.7	20.0
95°	46.0	45.7	45.5	44.7	43.1	41.4	39.8	38.2	39.8	41.4	43.1
97.5°	71.5	70.8	70.5	69.8	68.3	66.8	65.4	63.9	65.4	66.8	68.3
100°	99.8	99.3	99.1	98.4	97.1	95.8	94.5	93.2	94.5	95.8	97.1
102.5°	129.4	128.7	128.4	127.9	126.9	126.0	125.0	124.0	125.0	126.0	126.9
105°	160.5	160.2	160.0	159.8	159.3	158.8	158.3	157.8	158.3	158.8	159.3
107.5°	194.5	194.5	194.5	194.2	193.5	192.9	192.2	191.6	192.2	192.9	193.5
110°	228.3	228.3	228.3	227.8	226.8	225.8	224.8	223.8	224.8	225.8	226.8

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	263.2	263.4	263.5	263.0	262.0	261.1	260.1	259.1	260.1	261.1	262.0
115°	297.5	297.8	298.0	297.5	296.5	295.6	294.6	293.6	294.6	295.6	296.5
117.5°	332.7	333.5	333.9	333.3	332.0	330.7	329.4	328.1	329.4	330.7	332.0
120°	366.5	367.8	368.4	367.8	366.5	365.2	363.9	362.6	363.9	365.2	366.5
122.5°	400.3	401.1	401.5	400.7	399.0	397.4	395.7	394.1	395.7	397.4	399.0
125°	433.0	433.5	433.8	433.1	431.6	430.1	428.6	427.1	428.6	430.1	431.6
127.5°	466.5	467.2	467.5	466.6	464.8	463.0	461.2	459.4	461.2	463.0	464.8
130°	498.6	498.9	499.1	498.0	495.9	493.8	491.6	489.5	491.6	493.8	495.9
132.5°	530.9	530.7	530.6	529.8	528.2	526.5	524.9	523.3	524.9	526.5	528.2
135°	561.2	560.9	560.7	559.8	558.0	556.2	554.4	552.6	554.4	556.2	558.0
137.5°	592.0	591.7	591.5	590.8	589.3	587.8	586.4	584.9	586.4	587.8	589.3
140°	621.4	620.6	620.2	619.5	618.0	616.5	615.1	613.6	615.1	616.5	618.0
142.5°	650.2	649.7	649.5	648.8	647.3	645.8	644.4	642.9	644.4	645.8	647.3
145°	677.4	676.4	675.9	675.3	674.2	673.1	671.9	670.8	671.9	673.1	674.2
147.5°	703.4	702.7	702.4	701.7	700.2	698.7	697.3	695.8	697.3	698.7	700.2
150°	726.9	726.2	725.9	725.4	724.4	723.4	722.4	721.4	722.4	723.4	724.4
152.5°	749.8	749.0	748.6	748.1	747.1	746.2	745.2	744.2	745.2	746.2	747.1
155°	769.9	769.4	769.2	769.0	768.5	768.0	767.5	767.0	767.5	768.0	768.5
157.5°	788.7	788.4	788.2	788.0	787.7	787.4	787.1	786.8	787.1	787.4	787.7
160°	806.1	806.0	805.9	805.7	805.4	805.1	804.7	804.4	804.7	805.1	805.4
162.5°	820.8	820.6	820.5	820.5	820.5	820.5	820.5	820.5	820.5	820.5	820.5
165°	833.7	833.7	833.7	833.8	834.0	834.1	834.3	834.5	834.3	834.1	834.0
167.5°	844.7	844.7	844.7	845.0	845.5	846.0	846.5	847.0	846.5	846.0	845.5
170°	854.1	854.2	854.3	854.5	855.0	855.5	856.0	856.5	856.0	855.5	855.0
172.5°	860.7	860.8	860.9	861.1	861.6	862.1	862.6	863.1	862.6	862.1	861.6
175°	865.5	865.8	866.0	866.2	866.7	867.2	867.7	868.2	867.7	867.2	866.7
177.5°	868.5	868.8	869.0	869.2	869.7	870.2	870.7	871.2	870.7	870.2	869.7
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1632.1	1638.4	1637.1	1624.5	1610.5	1599.1	1577.5	1580.1	1572.5	1573.7	1581.3
5°	1591.5	1591.5	1586.4	1568.7	1545.8	1533.2	1509.1	1502.7	1487.5	1486.2	1485.0
7.5°	1548.4	1542.0	1535.7	1510.3	1482.4	1462.1	1429.2	1421.6	1406.3	1396.2	1391.1
10°	1497.6	1488.8	1476.1	1446.9	1412.7	1387.3	1353.1	1342.9	1313.8	1301.1	1293.5
12.5°	1441.8	1436.8	1416.5	1392.4	1336.6	1308.7	1259.2	1269.4	1240.2	1214.9	1211.0
15°	1386.0	1367.0	1355.6	1316.3	1249.1	1236.4	1197.1	1176.8	1150.2	1129.9	1129.9
17.5°	1331.5	1302.4	1277.0	1235.1	1185.7	1150.2	1121.0	1110.9	1077.9	1057.6	1053.8
20°	1259.2	1226.3	1219.9	1160.3	1126.1	1086.8	1058.9	1033.5	1009.4	1000.5	994.2
22.5°	1190.8	1152.7	1142.6	1091.8	1057.6	1018.3	990.4	972.6	954.9	948.5	937.1
25°	1117.2	1094.4	1079.2	1024.6	986.6	949.8	930.8	918.1	901.6	900.4	892.8
27.5°	1046.2	1024.6	1009.4	957.4	929.5	895.3	880.1	866.1	857.2	853.4	849.6
30°	985.3	961.2	943.5	905.4	871.2	843.3	830.6	821.7	816.7	810.3	809.1
32.5°	918.1	904.2	880.1	850.9	824.3	797.6	790.0	783.7	776.1	773.6	772.3
35°	861.1	842.0	826.8	793.8	782.4	759.6	750.7	745.7	735.5	733.0	730.4
37.5°	805.3	787.5	771.0	750.7	729.2	716.5	711.4	703.8	698.7	700.0	697.5
40°	749.5	735.5	722.8	701.3	688.6	682.2	672.1	664.5	662.0	663.2	662.0
42.5°	694.9	682.2	674.6	658.2	645.5	639.1	632.8	625.2	629.0	629.0	632.8
45°	645.5	634.1	629.0	616.3	608.7	598.6	592.2	590.9	596.0	594.7	594.7
47.5°	594.7	590.9	584.6	573.2	563.0	556.7	555.4	555.4	560.5	563.0	561.8
50°	555.4	547.8	540.2	531.3	523.7	521.2	517.4	519.9	525.0	525.0	527.5
52.5°	506.0	500.9	498.4	490.8	485.7	485.7	485.7	487.0	490.8	494.6	493.3
55°	462.9	459.1	456.5	452.7	446.4	447.6	446.4	448.9	452.7	456.5	459.1
57.5°	417.2	415.9	413.4	407.1	407.1	405.8	409.6	410.9	417.2	419.7	423.6
60°	376.6	372.8	372.8	367.8	367.8	367.8	371.6	375.4	380.4	381.7	384.2
62.5°	333.5	333.5	332.2	328.4	328.4	332.2	333.5	338.6	341.1	341.1	344.9
65°	292.9	291.7	290.4	291.7	292.9	292.9	296.7	299.3	301.8	303.1	304.3
67.5°	252.4	251.1	253.6	252.4	254.9	260.0	258.7	262.5	266.3	266.3	267.6
70°	214.3	216.8	215.6	218.1	216.8	219.4	223.2	224.5	224.5	225.7	229.5
72.5°	178.8	178.8	178.8	177.5	178.8	181.3	183.9	185.1	187.7	188.9	192.8
75°	144.6	144.6	142.0	144.6	144.6	147.1	149.6	149.6	149.6	152.2	156.0
77.5°	109.1	110.3	109.1	111.6	111.6	112.9	115.4	114.1	116.7	117.9	119.2
80°	79.9	78.6	78.6	78.6	79.9	79.9	82.4	83.7	83.7	87.5	85.0
82.5°	50.7	52.0	50.7	52.0	52.0	53.3	52.0	53.3	54.5	57.1	55.8
85°	29.2	27.9	27.9	29.2	27.9	27.9	29.2	27.9	29.2	27.9	29.2
87.5°	11.4	10.1	10.1	10.1	10.1	8.9	8.9	7.6	7.6	7.6	6.3
90°	8.5	9.5	11.3	14.9	18.5	22.1	25.7	25.4	25.0	24.7	24.4
92.5°	21.3	22.0	22.1	22.3	22.4	22.6	22.8	23.0	23.1	23.3	23.4
95°	44.7	45.5	45.7	46.0	46.3	46.7	47.0	47.0	47.0	47.0	47.0
97.5°	69.8	70.5	70.8	71.5	72.1	72.8	73.4	73.4	73.4	73.4	73.4
100°	98.4	99.1	99.3	99.8	100.3	100.8	101.3	101.3	101.3	101.3	101.3
102.5°	127.9	128.4	128.7	129.4	130.1	130.7	131.4	131.6	131.7	131.9	132.0
105°	159.8	160.0	160.2	160.5	160.8	161.2	161.5	161.8	162.1	162.4	162.7
107.5°	194.2	194.5	194.5	194.5	194.5	194.5	194.5	194.7	194.8	195.0	195.1
110°	227.8	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	263.0	263.5	263.4	263.2	263.1	262.9	262.7	262.2	261.7	261.2	260.7
115°	297.5	298.0	297.8	297.5	297.2	296.8	296.5	296.3	296.2	296.0	295.9
117.5°	333.3	333.9	333.5	332.7	331.9	331.1	330.3	329.8	329.3	328.8	328.3
120°	367.8	368.4	367.8	366.5	365.2	363.9	362.6	362.6	362.6	362.6	362.6
122.5°	400.7	401.5	401.1	400.3	399.4	398.6	397.8	397.3	396.8	396.3	395.8
125°	433.1	433.8	433.5	433.0	432.5	432.0	431.5	431.0	430.5	430.0	429.5
127.5°	466.6	467.5	467.2	466.5	465.9	465.2	464.6	463.9	463.3	462.6	461.9
130°	498.0	499.1	498.9	498.6	498.3	497.9	497.6	497.3	496.9	496.6	496.3
132.5°	529.8	530.6	530.7	530.9	531.0	531.2	531.4	530.6	529.8	528.9	528.1
135°	559.8	560.7	560.9	561.2	561.5	561.9	562.2	562.0	561.9	561.7	561.6
137.5°	590.8	591.5	591.7	592.0	592.3	592.7	593.0	592.8	592.7	592.5	592.4
140°	619.5	620.2	620.6	621.4	622.2	623.0	623.8	623.8	623.8	623.8	623.8
142.5°	648.8	649.5	649.7	650.2	650.7	651.2	651.7	651.9	652.1	652.2	652.4
145°	675.3	675.9	676.4	677.4	678.4	679.4	680.4	680.6	680.7	680.9	681.0
147.5°	701.7	702.4	702.7	703.4	704.0	704.7	705.3	705.6	706.0	706.3	706.6
150°	725.4	725.9	726.2	726.9	727.5	728.2	728.8	729.3	729.8	730.3	730.8
152.5°	748.1	748.6	749.0	749.8	750.7	751.5	752.3	752.9	753.6	754.2	754.9
155°	769.0	769.2	769.4	769.9	770.4	770.9	771.4	772.2	773.0	773.8	774.6
157.5°	788.0	788.2	788.4	788.7	789.0	789.4	789.7	790.8	792.0	793.1	794.2
160°	805.7	805.9	806.0	806.1	806.3	806.4	806.6	807.6	808.6	809.5	810.5
162.5°	820.5	820.5	820.6	820.8	820.9	821.1	821.3	822.4	823.6	824.7	825.8
165°	833.8	833.7	833.7	833.7	833.7	833.7	833.7	834.9	836.0	837.2	838.3
167.5°	845.0	844.7	844.7	844.7	844.7	844.7	844.7	845.9	847.0	848.2	849.3
170°	854.5	854.3	854.2	854.1	853.9	853.8	853.6	854.7	855.9	857.0	858.1
172.5°	861.1	860.9	860.8	860.7	860.5	860.4	860.2	861.3	862.5	863.6	864.7
175°	866.2	866.0	865.8	865.5	865.2	864.9	864.6	865.7	866.9	868.0	869.1
177.5°	869.2	869.0	868.8	868.5	868.2	867.8	867.5	868.5	869.5	870.4	871.4
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1572.5	1576.3	1567.4	1564.9	1567.4	1558.5	1561.0	1563.6	1563.6	1567.4	1569.9
5°	1481.2	1476.1	1467.2	1464.7	1462.1	1465.9	1463.4	1467.2	1468.5	1477.4	1478.6
7.5°	1391.1	1383.5	1375.9	1368.3	1365.8	1359.4	1365.8	1365.8	1374.6	1372.1	1378.4
10°	1284.6	1283.3	1273.2	1269.4	1264.3	1254.2	1268.1	1264.3	1270.7	1282.1	1284.6
12.5°	1206.0	1192.0	1198.4	1180.6	1187.0	1176.8	1178.1	1178.1	1188.2	1189.5	1187.0
15°	1131.2	1119.7	1103.3	1095.7	1091.8	1086.8	1103.3	1104.5	1096.9	1114.7	1108.3
17.5°	1055.1	1055.1	1039.9	1036.0	1025.9	1031.0	1028.4	1029.7	1027.2	1039.9	1046.2
20°	989.1	982.8	977.7	979.0	966.3	963.8	961.2	963.8	972.6	981.5	984.1
22.5°	935.9	932.1	919.4	921.9	911.8	915.6	913.0	919.4	920.7	920.7	929.5
25°	885.1	880.1	881.3	876.3	872.5	872.5	868.7	872.5	877.5	880.1	881.3
27.5°	847.1	843.3	837.0	833.2	835.7	829.3	834.4	838.2	838.2	835.7	838.2
30°	801.4	804.0	804.0	791.3	796.4	793.8	797.6	800.2	800.2	801.4	798.9
32.5°	771.0	763.4	762.1	760.9	760.9	755.8	755.8	759.6	760.9	762.1	765.9
35°	730.4	730.4	724.1	727.9	722.8	724.1	722.8	724.1	726.6	722.8	726.6
37.5°	693.7	694.9	692.4	694.9	696.2	693.7	691.1	696.2	693.7	693.7	691.1
40°	662.0	660.7	662.0	662.0	662.0	663.2	660.7	660.7	660.7	658.2	655.6
42.5°	635.3	627.7	630.3	631.5	627.7	627.7	629.0	627.7	631.5	623.9	623.9
45°	597.3	594.7	596.0	596.0	598.6	594.7	597.3	598.6	594.7	593.5	590.9
47.5°	563.0	565.6	563.0	565.6	565.6	568.1	563.0	564.3	565.6	560.5	556.7
50°	528.8	528.8	532.6	531.3	532.6	530.1	530.1	528.8	530.1	527.5	523.7
52.5°	497.1	493.3	499.6	498.4	497.1	495.8	494.6	495.8	493.3	490.8	490.8
55°	457.8	457.8	461.6	462.9	462.9	460.3	457.8	459.1	457.8	456.5	455.3
57.5°	426.1	421.0	423.6	424.8	424.8	421.0	423.6	421.0	421.0	422.3	418.5
60°	385.5	385.5	383.0	386.8	386.8	384.2	384.2	385.5	383.0	381.7	380.4
62.5°	342.4	343.7	347.5	348.7	350.0	347.5	344.9	346.2	346.2	342.4	343.7
65°	305.6	308.2	313.2	312.0	309.4	310.7	308.2	309.4	305.6	306.9	303.1
67.5°	270.1	268.8	270.1	270.1	272.6	271.4	268.8	268.8	267.6	271.4	267.6
70°	232.1	232.1	232.1	232.1	233.3	234.6	232.1	229.5	230.8	228.3	227.0
72.5°	192.8	194.0	192.8	195.3	191.5	194.0	194.0	192.8	191.5	191.5	191.5
75°	156.0	158.5	154.7	156.0	154.7	157.2	156.0	156.0	153.4	152.2	153.4
77.5°	119.2	120.5	117.9	119.2	117.9	119.2	119.2	117.9	117.9	117.9	117.9
80°	85.0	86.2	85.0	83.7	82.4	85.0	82.4	83.7	85.0	83.7	86.2
82.5°	54.5	54.5	53.3	54.5	52.0	52.0	53.3	53.3	52.0	54.5	52.0
85°	26.6	26.6	29.2	26.6	25.4	25.4	25.4	26.6	25.4	27.9	26.6
87.5°	6.3	5.1	6.3	6.3	5.1	5.1	6.3	5.1	6.3	7.6	5.1
90°	24.2	24.3	24.5	24.6	24.8	25.0	24.8	24.6	24.5	24.3	24.2
92.5°	23.5	23.5	23.5	23.5	23.5	23.5	23.5	23.5	23.5	23.5	23.5
95°	47.0	46.8	46.5	46.2	45.8	45.5	45.8	46.2	46.5	46.8	47.0
97.5°	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4
100°	101.3	101.2	101.0	100.9	100.7	100.5	100.7	100.9	101.0	101.2	101.3
102.5°	132.1	132.0	131.9	131.7	131.6	131.4	131.6	131.7	131.9	132.0	132.1
105°	162.9	162.9	162.9	162.9	162.9	162.9	162.9	162.9	162.9	162.9	162.9
107.5°	195.2	194.8	194.0	193.2	192.4	191.6	192.4	193.2	194.0	194.8	195.2
110°	228.3	228.0	227.5	227.0	226.5	226.0	226.5	227.0	227.5	228.0	228.3

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	260.5	260.3	260.0	259.7	259.4	259.1	259.4	259.7	260.0	260.3	260.5
115°	295.8	295.6	295.1	294.6	294.1	293.6	294.1	294.6	295.1	295.6	295.8
117.5°	328.1	327.9	327.4	326.9	326.4	325.9	326.4	326.9	327.4	327.9	328.1
120°	362.6	362.4	361.9	361.4	360.9	360.4	360.9	361.4	361.9	362.4	362.6
122.5°	395.6	395.4	395.1	394.8	394.4	394.1	394.4	394.8	395.1	395.4	395.6
125°	429.3	429.2	429.1	428.9	428.8	428.6	428.8	428.9	429.1	429.2	429.3
127.5°	461.6	461.4	460.9	460.4	459.9	459.4	459.9	460.4	460.9	461.4	461.6
130°	496.1	495.8	495.1	494.5	493.8	493.2	493.8	494.5	495.1	495.8	496.1
132.5°	527.7	527.5	527.0	526.5	526.0	525.5	526.0	526.5	527.0	527.5	527.7
135°	561.5	561.3	560.8	560.3	559.8	559.3	559.8	560.3	560.8	561.3	561.5
137.5°	592.3	592.0	591.3	590.6	590.0	589.3	590.0	590.6	591.3	592.0	592.3
140°	623.8	623.5	622.8	622.2	621.5	620.9	621.5	622.2	622.8	623.5	623.8
142.5°	652.5	652.2	651.5	650.8	650.2	649.5	650.2	650.8	651.5	652.2	652.5
145°	681.1	680.8	680.1	679.4	678.8	678.1	678.8	679.4	680.1	680.8	681.1
147.5°	706.8	706.5	705.8	705.1	704.5	703.8	704.5	705.1	705.8	706.5	706.8
150°	731.0	730.8	730.3	729.8	729.3	728.8	729.3	729.8	730.3	730.8	731.0
152.5°	755.2	754.9	754.2	753.6	752.9	752.3	752.9	753.6	754.2	754.9	755.2
155°	775.0	774.8	774.3	773.8	773.3	772.8	773.3	773.8	774.3	774.8	775.0
157.5°	794.8	794.4	793.6	792.8	792.0	791.2	792.0	792.8	793.6	794.4	794.8
160°	811.0	810.7	810.0	809.4	808.7	808.1	808.7	809.4	810.0	810.7	811.0
162.5°	826.4	826.0	825.2	824.3	823.5	822.7	823.5	824.3	825.2	826.0	826.4
165°	838.9	838.5	837.7	836.8	836.0	835.2	836.0	836.8	837.7	838.5	838.9
167.5°	849.9	849.5	848.7	847.8	847.0	846.2	847.0	847.8	848.7	849.5	849.9
170°	858.7	858.2	857.2	856.3	855.3	854.3	855.3	856.3	857.2	858.2	858.7
172.5°	865.3	864.8	863.8	862.9	861.9	860.9	861.9	862.9	863.8	864.8	865.3
175°	869.7	869.2	868.2	867.3	866.3	865.3	866.3	867.3	868.2	869.2	869.7
177.5°	871.9	871.4	870.4	869.5	868.5	867.5	868.5	869.5	870.4	871.4	871.9
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
2.5°	1566.1	1576.3	1572.5	1558.5	1575.0	1575.0	1586.4	1586.4	1600.4	1605.4	1613.0
5°	1477.4	1485.0	1491.3	1485.0	1496.4	1514.1	1524.3	1533.2	1552.2	1559.8	1571.2
7.5°	1382.2	1396.2	1402.5	1402.5	1421.6	1441.8	1462.1	1474.8	1501.4	1511.6	1523.0
10°	1289.7	1306.2	1318.8	1317.6	1349.3	1362.0	1387.3	1416.5	1443.1	1458.3	1474.8
12.5°	1192.0	1200.9	1218.7	1244.0	1251.6	1274.5	1303.6	1340.4	1388.6	1402.5	1426.6
15°	1110.9	1135.0	1148.9	1160.3	1178.1	1199.6	1231.3	1266.8	1315.0	1345.5	1370.8
17.5°	1042.4	1074.1	1083.0	1080.4	1103.3	1136.2	1173.0	1199.6	1242.8	1279.5	1303.6
20°	986.6	999.3	1014.5	1020.8	1038.6	1074.1	1109.6	1140.0	1175.5	1204.7	1232.6
22.5°	930.8	940.9	953.6	965.0	979.0	999.3	1033.5	1071.6	1105.8	1133.7	1165.4
25°	885.1	891.5	902.9	911.8	927.0	940.9	965.0	1006.9	1047.5	1063.9	1091.8
27.5°	840.8	845.8	853.4	863.6	871.2	885.1	906.7	940.9	982.8	999.3	1037.3
30°	801.4	805.3	812.9	817.9	821.7	838.2	854.7	881.3	913.0	935.9	963.8
32.5°	764.7	768.5	776.1	777.4	782.4	791.3	806.5	830.6	858.5	877.5	901.6
35°	724.1	726.6	734.2	736.8	740.6	748.2	759.6	777.4	802.7	816.7	838.2
37.5°	692.4	691.1	696.2	700.0	705.1	708.9	712.7	730.4	749.5	762.1	778.6
40°	658.2	655.6	656.9	662.0	664.5	669.6	669.6	687.3	700.0	710.1	722.8
42.5°	623.9	622.6	620.1	622.6	625.2	626.4	627.7	640.4	653.1	662.0	675.9
45°	589.7	588.4	585.9	587.1	587.1	589.7	593.5	598.6	607.4	615.0	622.6
47.5°	558.0	555.4	551.6	550.4	552.9	552.9	552.9	558.0	566.8	569.4	577.0
50°	525.0	521.2	516.1	513.6	513.6	512.3	514.9	516.1	523.7	526.3	532.6
52.5°	489.5	487.0	481.9	476.8	478.1	475.5	476.8	478.1	480.6	484.4	488.2
55°	454.0	448.9	445.1	443.8	440.0	440.0	436.2	441.3	440.0	441.3	446.4
57.5°	419.7	414.7	408.3	405.8	402.0	400.7	398.2	396.9	398.2	402.0	405.8
60°	379.2	376.6	372.8	369.0	366.5	362.7	360.1	360.1	358.9	358.9	360.1
62.5°	339.9	338.6	333.5	332.2	329.7	327.2	323.4	320.8	320.8	323.4	324.6
65°	301.8	300.5	296.7	295.5	289.1	286.6	285.3	284.1	281.5	281.5	281.5
67.5°	266.3	262.5	262.5	256.2	251.1	248.6	246.0	244.7	244.7	244.7	246.0
70°	227.0	227.0	223.2	219.4	214.3	215.6	211.8	208.0	208.0	205.4	206.7
72.5°	188.9	187.7	183.9	182.6	178.8	175.0	172.5	175.0	171.2	169.9	171.2
75°	152.2	150.9	148.4	145.8	147.1	143.3	139.5	138.2	138.2	135.7	135.7
77.5°	116.7	119.2	114.1	112.9	110.3	107.8	106.5	105.3	105.3	105.3	107.8
80°	81.2	82.4	82.4	79.9	81.2	77.4	77.4	77.4	73.6	74.8	76.1
82.5°	52.0	52.0	50.7	52.0	50.7	50.7	49.5	49.5	48.2	48.2	49.5
85°	29.2	27.9	26.6	29.2	27.9	27.9	26.6	26.6	26.6	26.6	26.6
87.5°	6.3	7.6	7.6	7.6	7.6	8.9	8.9	8.9	10.1	10.1	10.1
90°	24.4	24.7	25.0	25.4	25.7	22.1	18.5	14.9	11.3	9.5	8.5
92.5°	23.4	23.3	23.1	23.0	22.8	22.6	22.4	22.3	22.1	22.0	21.3
95°	47.0	47.0	47.0	47.0	47.0	46.7	46.3	46.0	45.7	45.5	44.7
97.5°	73.4	73.4	73.4	73.4	73.4	72.8	72.1	71.5	70.8	70.5	69.8
100°	101.3	101.3	101.3	101.3	101.3	100.8	100.3	99.8	99.3	99.1	98.4
102.5°	132.0	131.9	131.7	131.6	131.4	130.7	130.1	129.4	128.7	128.4	127.9
105°	162.7	162.4	162.1	161.8	161.5	161.2	160.8	160.5	160.2	160.0	159.8
107.5°	195.1	195.0	194.8	194.7	194.5	194.5	194.5	194.5	194.5	194.5	194.2
110°	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3	227.8

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	260.7	261.2	261.7	262.2	262.7	262.9	263.1	263.2	263.4	263.5	263.0
115°	295.9	296.0	296.2	296.3	296.5	296.8	297.2	297.5	297.8	298.0	297.5
117.5°	328.3	328.8	329.3	329.8	330.3	331.1	331.9	332.7	333.5	333.9	333.3
120°	362.6	362.6	362.6	362.6	362.6	363.9	365.2	366.5	367.8	368.4	367.8
122.5°	395.8	396.3	396.8	397.3	397.8	398.6	399.4	400.3	401.1	401.5	400.7
125°	429.5	430.0	430.5	431.0	431.5	432.0	432.5	433.0	433.5	433.8	433.1
127.5°	461.9	462.6	463.3	463.9	464.6	465.2	465.9	466.5	467.2	467.5	466.6
130°	496.3	496.6	496.9	497.3	497.6	497.9	498.3	498.6	498.9	499.1	498.0
132.5°	528.1	528.9	529.8	530.6	531.4	531.2	531.0	530.9	530.7	530.6	529.8
135°	561.6	561.7	561.9	562.0	562.2	561.9	561.5	561.2	560.9	560.7	559.8
137.5°	592.4	592.5	592.7	592.8	593.0	592.7	592.3	592.0	591.7	591.5	590.8
140°	623.8	623.8	623.8	623.8	623.8	623.0	622.2	621.4	620.6	620.2	619.5
142.5°	652.4	652.2	652.1	651.9	651.7	651.2	650.7	650.2	649.7	649.5	648.8
145°	681.0	680.9	680.7	680.6	680.4	679.4	678.4	677.4	676.4	675.9	675.3
147.5°	706.6	706.3	706.0	705.6	705.3	704.7	704.0	703.4	702.7	702.4	701.7
150°	730.8	730.3	729.8	729.3	728.8	728.2	727.5	726.9	726.2	725.9	725.4
152.5°	754.9	754.2	753.6	752.9	752.3	751.5	750.7	749.8	749.0	748.6	748.1
155°	774.6	773.8	773.0	772.2	771.4	770.9	770.4	769.9	769.4	769.2	769.0
157.5°	794.2	793.1	792.0	790.8	789.7	789.4	789.0	788.7	788.4	788.2	788.0
160°	810.5	809.5	808.6	807.6	806.6	806.4	806.3	806.1	806.0	805.9	805.7
162.5°	825.8	824.7	823.6	822.4	821.3	821.1	820.9	820.8	820.6	820.5	820.5
165°	838.3	837.2	836.0	834.9	833.7	833.7	833.7	833.7	833.7	833.7	833.8
167.5°	849.3	848.2	847.0	845.9	844.7	844.7	844.7	844.7	844.7	844.7	845.0
170°	858.1	857.0	855.9	854.7	853.6	853.8	853.9	854.1	854.2	854.3	854.5
172.5°	864.7	863.6	862.5	861.3	860.2	860.4	860.5	860.7	860.8	860.9	861.1
175°	869.1	868.0	866.9	865.7	864.6	864.9	865.2	865.5	865.8	866.0	866.2
177.5°	871.4	870.4	869.5	868.5	867.5	867.8	868.2	868.5	868.8	869.0	869.2
180°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1649.8	1649.8	1649.8	1649.8
2.5°	1619.4	1619.4	1638.4	1658.7
5°	1583.9	1592.8	1623.2	1651.1
7.5°	1549.6	1564.9	1602.9	1638.4
10°	1507.8	1528.1	1575.0	1616.8
12.5°	1467.2	1486.2	1540.8	1587.7
15°	1410.1	1434.2	1492.6	1550.9
17.5°	1353.1	1377.2	1448.2	1516.7
20°	1285.9	1317.6	1397.5	1488.8
22.5°	1223.7	1263.0	1351.8	1425.4
25°	1155.3	1216.1	1298.5	1393.7
27.5°	1094.4	1155.3	1238.9	1335.3
30°	1025.9	1088.0	1174.3	1263.0
32.5°	960.0	1017.0	1100.7	1209.8
35°	891.5	946.0	1027.2	1137.5
37.5°	829.3	882.6	971.4	1072.8
40°	768.5	824.3	900.4	1001.8
42.5°	711.4	760.9	829.3	930.8
45°	659.4	694.9	758.3	853.4
47.5°	604.9	636.6	694.9	790.0
50°	554.2	580.8	631.5	720.3
52.5°	504.7	527.5	574.5	645.5
55°	460.3	481.9	516.1	585.9
57.5°	414.7	431.2	464.1	519.9
60°	370.3	385.5	412.1	457.8
62.5°	325.9	338.6	363.9	400.7
65°	286.6	296.7	315.8	347.5
67.5°	248.6	254.9	270.1	295.5
70°	211.8	216.8	229.5	249.8
72.5°	172.5	177.5	191.5	205.4
75°	139.5	140.8	150.9	162.3
77.5°	109.1	107.8	115.4	124.3
80°	74.8	78.6	85.0	88.8
82.5°	50.7	52.0	54.5	57.1
85°	27.9	29.2	29.2	33.0
87.5°	11.4	12.7	12.7	13.9
90°	6.6	4.6	2.7	0.7
92.5°	20.0	18.7	17.4	16.1
95°	43.1	41.4	39.8	38.2
97.5°	68.3	66.8	65.4	63.9
100°	97.1	95.8	94.5	93.2
102.5°	126.9	126.0	125.0	124.0
105°	159.3	158.8	158.3	157.8
107.5°	193.5	192.9	192.2	191.6
110°	226.8	225.8	224.8	223.8

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	262.0	261.1	260.1	259.1
115°	296.5	295.6	294.6	293.6
117.5°	332.0	330.7	329.4	328.1
120°	366.5	365.2	363.9	362.6
122.5°	399.0	397.4	395.7	394.1
125°	431.6	430.1	428.6	427.1
127.5°	464.8	463.0	461.2	459.4
130°	495.9	493.8	491.6	489.5
132.5°	528.2	526.5	524.9	523.3
135°	558.0	556.2	554.4	552.6
137.5°	589.3	587.8	586.4	584.9
140°	618.0	616.5	615.1	613.6
142.5°	647.3	645.8	644.4	642.9
145°	674.2	673.1	671.9	670.8
147.5°	700.2	698.7	697.3	695.8
150°	724.4	723.4	722.4	721.4
152.5°	747.1	746.2	745.2	744.2
155°	768.5	768.0	767.5	767.0
157.5°	787.7	787.4	787.1	786.8
160°	805.4	805.1	804.7	804.4
162.5°	820.5	820.5	820.5	820.5
165°	834.0	834.1	834.3	834.5
167.5°	845.5	846.0	846.5	847.0
170°	855.0	855.5	856.0	856.5
172.5°	861.6	862.1	862.6	863.1
175°	866.7	867.2	867.7	868.2
177.5°	869.7	870.2	870.7	871.2
180°	869.7	869.7	869.7	869.7

TEST NUMBER: P999201

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.06	18.98	18.94	19.87	20.99	15.55	16.47	16.43	17.36	18.49
	3H	18.88	19.70	19.76	20.60	21.75	16.90	17.72	17.79	18.62	19.77
	4H	19.05	19.82	19.95	20.73	21.89	17.37	18.14	18.27	19.05	20.21
	6H	19.10	19.81	20.01	20.72	21.89	17.68	18.39	18.59	19.30	20.48
	8H	19.08	19.76	20.00	20.68	21.86	17.76	18.44	18.69	19.37	20.54
	12H	19.04	19.69	19.97	20.61	21.81	17.81	18.45	18.73	19.38	20.57
4H	2H	18.11	18.88	19.02	19.79	20.95	16.01	16.78	16.91	17.69	18.85
	3H	19.10	19.74	20.01	20.68	21.85	17.47	18.12	18.39	19.05	20.23
	4H	19.37	19.96	20.30	20.89	22.09	18.01	18.60	18.94	19.53	20.73
	6H	19.51	20.01	20.45	20.97	22.17	18.39	18.90	19.33	19.85	21.05
	8H	19.51	19.98	20.45	20.93	22.14	18.50	18.98	19.45	19.92	21.14
	12H	19.47	19.90	20.44	20.86	22.08	18.56	18.99	19.53	19.95	21.17
8H	4H	19.39	19.86	20.33	20.81	22.02	18.16	18.63	19.10	19.58	20.79
	6H	19.57	19.96	20.54	20.95	22.16	18.59	18.98	19.56	19.97	21.19
	8H	19.60	19.94	20.58	20.92	22.15	18.74	19.09	19.72	20.07	21.30
	12H	19.59	19.89	20.57	20.86	22.14	18.84	19.14	19.82	20.11	21.39
12H	4H	19.35	19.77	20.31	20.74	21.96	18.13	18.56	19.10	19.52	20.74
	6H	19.55	19.89	20.53	20.87	22.10	18.59	18.94	19.57	19.92	21.15
	8H	19.58	19.88	20.56	20.86	22.14	18.75	19.06	19.74	20.03	21.31