

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999205

Luminaire Tested: SA2XXDIP-B865D725UB50-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999205
REPORT IS A COMBINATION OF REPORTS P984954 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D725UB50-4F0-XX-W2A-D4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6003.0 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999205

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P999205

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	96	91	87	83	88	84	80	77	71	68	65	58	56	54	47	45	44
2	87	79	72	66	80	73	67	62	61	57	53	50	47	44	40	38	36
3	79	69	61	55	72	63	56	51	53	48	44	44	40	37	35	32	30
4	72	61	52	46	66	56	48	43	47	41	37	39	35	31	31	28	25
5	66	54	45	39	60	50	42	36	42	36	31	35	30	27	28	25	22
6	61	48	40	33	55	44	37	31	38	32	27	31	27	23	25	22	19
7	56	43	35	29	51	40	33	27	34	28	24	28	24	20	23	19	17
8	52	39	31	26	48	36	29	24	31	25	21	26	21	18	21	18	15
9	48	36	28	23	44	33	26	21	28	23	19	24	19	16	19	16	13
10	45	33	25	20	41	30	24	19	26	21	17	22	18	14	18	15	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13852	13852	13852
5°	13914	13261	13185
10°	13822	12801	12614
15°	13625	12327	12029
20°	13380	11827	11473
25°	13136	11349	10969
30°	12796	10864	10469
35°	12453	10396	10102
40°	12089	9992	9738
45°	11743	9625	9421
50°	11373	9287	9106
55°	10984	8927	8787
60°	10505	8554	8452
65°	10007	8122	8066
70°	9445	7660	7651
75°	8727	7199	7258
80°	7593	6717	6851
85°	6455	6266	6502

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11743 cd/sqm

TEST NUMBER: P999205

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.0	1.4
10°-20°	237.9	4.0
20°-30°	360.5	6.0
30°-40°	439.0	7.3
40°-50°	472.3	7.9
50°-60°	458.7	7.6
60°-70°	400.6	6.7
70°-80°	308.3	5.1
80°-90°	208.9	3.5
90°-100°	297.2	5.0
100°-110°	627.2	10.4
110°-120°	618.6	10.3
120°-130°	490.5	8.2
130°-140°	379.5	6.3
140°-150°	277.2	4.6
150°-160°	193.0	3.2
160°-170°	113.6	1.9
170°-180°	37.0	0.6
0°-30°	681.4	11.4
0°-40°	1120.4	18.7
0°-60°	2051.4	34.2
0°-90°	2969.2	49.5
90°-120°	1543.1	25.7
90°-150°	2690.2	44.8
90°-180°	3034.0	50.5
0°-180°	6003.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	875	875	875	875	875	
5°	878	874	866	874	872	83
15°	837	840	840	851	850	236
25°	761	770	781	796	800	350
35°	656	677	701	729	738	410
45°	538	572	616	656	668	415
55°	412	458	524	569	586	369
65°	282	344	418	470	487	280
75°	156	227	308	363	379	165
85°	46	124	206	259	276	48
90°	13	96	192	242	258	11
95°	36	133	434	303	293	34
105°	96	178	653	1126	995	102
115°	163	218	531	1053	1217	161
125°	223	263	481	838	972	198
135°	260	310	446	680	783	201
145°	295	339	430	542	598	185
155°	336	362	418	472	491	154
165°	366	377	400	424	431	103
175°	381	381	385	390	388	36
180°	382	382	382	382	382	

TEST NUMBER: P999205

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	875.1	875.1	875.1	875.1	875.1
2.5°	881.4	877.6	868.7	875.1	872.5
5°	877.6	873.8	866.2	873.8	872.5
7.5°	871.3	868.7	862.4	871.3	870.0
10°	863.7	861.1	857.3	867.5	866.2
12.5°	851.0	852.3	849.7	859.9	858.6
15°	837.0	839.6	839.6	851.0	849.7
17.5°	819.3	824.4	828.2	839.6	839.6
20°	801.5	807.9	812.9	826.9	826.9
22.5°	782.5	790.1	797.7	811.7	814.2
25°	760.9	769.8	781.2	796.5	800.3
27.5°	735.6	749.5	762.2	781.2	783.8
30°	710.2	726.7	743.2	763.5	767.3
32.5°	682.3	701.3	721.6	745.7	753.3
35°	655.7	677.2	701.3	729.2	738.1
37.5°	626.5	650.6	681.0	711.5	720.4
40°	597.3	625.2	659.5	692.5	703.9
42.5°	569.4	597.3	637.9	674.7	686.1
45°	537.7	572.0	616.4	655.7	668.4
47.5°	507.3	544.1	594.8	635.4	649.3
50°	475.6	514.9	572.0	615.1	629.0
52.5°	445.1	487.0	547.9	592.3	607.5
55°	412.2	457.8	523.8	569.4	585.9
57.5°	380.5	431.2	497.1	546.6	563.1
60°	346.2	400.8	473.1	521.2	539.0
62.5°	315.8	372.9	445.1	497.1	513.6
65°	281.5	343.7	418.5	470.5	487.0
67.5°	251.1	315.8	391.9	443.9	461.6
70°	218.1	284.1	362.7	417.2	432.5
72.5°	187.7	256.2	336.1	389.3	408.4
75°	156.0	227.0	308.2	362.7	379.2
77.5°	125.6	199.1	281.5	336.1	353.8
80°	95.1	172.5	254.9	308.2	325.9
82.5°	69.8	145.8	229.6	282.8	299.3
85°	45.7	124.3	205.5	258.7	276.5
87.5°	27.9	104.0	185.2	237.2	253.6
90°	13.4	96.1	192.4	242.0	257.6
92.5°	22.4	113.4	269.1	257.6	265.5
95°	35.8	132.9	433.6	302.6	293.0
97.5°	47.1	146.7	606.1	402.0	339.3
100°	65.4	157.8	706.8	608.0	450.5
102.5°	81.0	168.4	701.5	897.8	690.0
105°	95.9	178.2	653.1	1125.9	994.8
107.5°	113.5	188.0	607.5	1202.0	1196.8
110°	129.9	198.2	574.9	1177.9	1273.3

TEST NUMBER: P999205

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	146.1	208.9	549.9	1121.6	1262.9
115°	162.9	218.3	531.3	1053.4	1216.8
117.5°	179.3	229.1	516.5	989.2	1152.3
120°	195.4	239.4	503.8	929.4	1091.4
122.5°	210.8	251.4	493.2	882.0	1025.7
125°	222.7	263.1	480.6	838.4	972.0
127.5°	233.8	275.5	470.8	798.4	919.9
130°	243.3	287.6	461.8	759.4	875.3
132.5°	252.1	299.4	453.4	719.4	830.4
135°	259.7	309.7	446.4	680.1	782.6
137.5°	267.8	318.4	440.0	640.4	735.1
140°	277.3	325.2	434.2	604.2	686.0
142.5°	286.9	331.8	431.7	570.6	638.3
145°	295.1	339.2	430.2	541.6	598.4
147.5°	305.4	345.0	428.0	516.6	560.8
150°	315.7	350.9	425.8	499.2	530.8
152.5°	326.0	356.8	422.1	485.6	509.5
155°	335.5	362.3	417.7	472.4	491.1
157.5°	343.6	366.7	413.3	459.9	475.0
160°	351.7	371.1	408.9	447.4	459.6
162.5°	359.7	374.4	405.2	435.7	444.9
165°	365.6	376.6	400.1	424.4	430.9
167.5°	370.7	378.8	395.7	414.0	417.7
170°	375.9	379.9	392.0	404.5	406.0
172.5°	378.8	381.0	387.6	396.0	396.4
175°	381.0	381.4	384.7	389.5	388.4
177.5°	382.5	381.8	381.8	384.7	382.5
180°	381.8	381.8	381.8	381.8	381.8

TEST NUMBER: P999205

CATALOG NUMBER: SA2XXDIP-B865D725UB50-4F0-XX-W2A-D4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.29	15.20	15.24	16.17	17.45	17.37	18.27	18.32	19.25	20.52
	3H	15.75	16.57	16.71	17.56	18.85	19.96	20.78	20.92	21.76	23.06
	4H	16.23	17.01	17.21	18.00	19.30	21.21	21.99	22.19	22.98	24.28
	6H	16.52	17.24	17.50	18.23	19.55	22.51	23.23	23.50	24.22	25.54
	8H	16.58	17.27	17.57	18.28	19.59	23.17	23.86	24.16	24.87	26.19
	12H	16.60	17.25	17.59	18.26	19.60	23.90	24.56	24.90	25.56	26.90
4H	2H	15.35	16.13	16.33	17.11	18.42	17.70	18.48	18.68	19.47	20.77
	3H	17.06	17.72	18.05	18.73	20.05	20.49	21.16	21.48	22.17	23.49
	4H	17.68	18.29	18.68	19.30	20.64	21.91	22.52	22.91	23.53	24.87
	6H	18.10	18.63	19.11	19.66	21.00	23.38	23.91	24.39	24.95	26.28
	8H	18.21	18.71	19.22	19.73	21.08	24.14	24.64	25.15	25.66	27.02
	12H	18.25	18.71	19.28	19.75	21.11	24.97	25.43	26.00	26.47	27.83
8H	4H	18.47	18.97	19.48	20.00	21.35	22.06	22.56	23.07	23.58	24.94
	6H	19.11	19.53	20.14	20.59	21.94	23.69	24.11	24.73	25.18	26.53
	8H	19.33	19.70	20.37	20.75	22.12	24.58	24.95	25.62	26.00	27.37
	12H	19.47	19.80	20.51	20.84	22.25	25.58	25.91	26.63	26.96	28.37
12H	4H	18.67	19.13	19.70	20.17	21.53	22.04	22.49	23.07	23.53	24.89
	6H	19.44	19.82	20.48	20.87	22.24	23.72	24.09	24.76	25.14	26.51
	8H	19.75	20.08	20.80	21.13	22.54	24.65	24.98	25.70	26.03	27.44