

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999210

Luminaire Tested: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999210
REPORT IS A COMBINATION OF REPORTS P984959 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7002.0 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	38	36	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26934	26934	26934	26934
5°	26998	28717	27101	22848
10°	26685	31350	26851	18836
15°	26038	33067	26399	15866
20°	25631	31047	25631	13791
25°	24814	26673	24926	12333
30°	23470	20967	23917	11171
35°	22279	14498	22651	10221
40°	20911	10946	21150	9463
45°	19224	8995	19538	8646
50°	17763	7896	17796	7915
55°	16100	6728	16204	7120
60°	14326	5619	14526	6215
65°	12737	4571	12972	5307
70°	11156	3586	11442	4279
75°	9364	2603	9728	3105
80°	7305	1650	7832	1842
85°	4803	830	5170	616

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 27842 cd/sqm

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.1	2.3
10°-20°	471.7	6.7
20°-30°	684.6	9.8
30°-40°	721.7	10.3
40°-50°	638.6	9.1
50°-60°	509.9	7.3
60°-70°	346.4	4.9
70°-80°	177.2	2.5
80°-90°	45.2	0.6
90°-100°	71.8	1.0
100°-110°	228.2	3.3
110°-120°	390.5	5.6
120°-130°	513.6	7.3
130°-140°	576.5	8.2
140°-150°	565.4	8.1
150°-160°	474.2	6.8
160°-170°	314.5	4.5
170°-180°	109.9	1.6
0°-30°	1318.3	18.8
0°-40°	2040.0	29.1
0°-60°	3188.6	45.5
0°-90°	3757.3	53.7
90°-120°	690.5	9.9
90°-150°	2346.0	33.5
90°-180°	3245.0	46.3
0°-180°	7002.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1702	1702	1702	1702	1702	
5°	1703	1900	1709	1512	1703	161
15°	1600	2336	1622	1121	1600	452
25°	1437	1946	1444	900	1437	657
35°	1173	1059	1193	747	1173	734
45°	880	638	895	613	880	683
55°	604	449	608	475	604	539
65°	358	276	365	320	358	356
75°	167	136	174	162	167	180
85°	34	35	37	26	34	40
90°	1	33	1	33	1	5
95°	51	61	51	61	51	57
105°	211	217	211	217	211	222
115°	392	392	392	392	392	388
125°	570	572	570	572	570	509
135°	738	746	738	746	738	570
145°	895	905	895	905	895	559
155°	1023	1031	1023	1031	1023	471
165°	1114	1114	1114	1114	1114	314
175°	1159	1155	1159	1155	1159	110
180°	1161	1161	1161	1161	1161	

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1710.6	1714.6	1721.1	1722.4	1735.5	1746.0	1757.7	1757.7	1761.6	1760.3	1749.9
5°	1702.8	1714.6	1731.6	1746.0	1769.5	1780.0	1795.7	1807.4	1817.9	1825.7	1824.4
7.5°	1689.7	1710.6	1735.5	1763.0	1794.3	1812.7	1834.9	1855.8	1870.2	1883.3	1892.4
10°	1667.5	1702.8	1736.8	1773.4	1814.0	1838.8	1865.0	1892.4	1914.7	1939.5	1963.1
12.5°	1637.4	1688.4	1730.3	1778.6	1828.3	1855.8	1897.7	1918.6	1961.7	2024.5	2041.5
15°	1599.5	1668.8	1708.0	1769.5	1834.9	1857.1	1914.7	1948.7	2037.6	2076.8	2123.9
17.5°	1564.2	1641.3	1693.6	1764.3	1828.3	1871.5	1927.7	1997.1	2071.6	2127.8	2180.2
20°	1535.4	1609.9	1672.7	1751.2	1832.3	1887.2	1946.1	2029.8	2110.8	2168.4	2208.9
22.5°	1470.0	1565.5	1638.7	1726.3	1824.4	1900.3	1956.5	2048.1	2135.7	2171.0	2206.3
25°	1437.3	1519.7	1604.7	1704.1	1819.2	1909.4	1957.8	2059.8	2137.0	2150.1	2157.9
27.5°	1377.1	1470.0	1569.4	1683.2	1817.9	1893.7	1955.2	2048.1	2109.5	2100.4	2076.8
30°	1302.6	1416.4	1526.2	1649.2	1799.6	1882.0	1939.5	2024.5	2055.9	2008.8	1967.0
32.5°	1247.7	1354.9	1476.5	1619.1	1778.6	1857.1	1913.4	1980.1	1986.6	1901.6	1831.0
35°	1173.1	1292.1	1429.5	1579.9	1743.3	1814.0	1866.3	1906.8	1875.4	1756.4	1672.7
37.5°	1106.4	1224.1	1370.6	1523.6	1694.9	1764.3	1806.1	1812.7	1735.5	1630.9	1507.9
40°	1033.2	1154.8	1307.8	1468.7	1641.3	1701.5	1727.6	1708.0	1596.9	1475.2	1332.7
42.5°	959.9	1080.3	1245.1	1409.8	1573.3	1624.3	1634.8	1581.2	1445.2	1302.6	1137.8
45°	880.2	1005.7	1170.5	1336.6	1494.9	1523.6	1524.9	1447.8	1286.9	1137.8	984.8
47.5°	814.8	931.2	1094.7	1260.7	1394.1	1413.8	1405.9	1317.0	1141.7	974.3	840.9
50°	742.8	854.0	1016.2	1179.7	1293.4	1298.7	1279.1	1152.2	980.9	827.9	721.9
52.5°	665.7	778.2	927.3	1084.2	1186.2	1178.4	1140.4	1004.4	843.6	716.7	635.6
55°	604.2	703.6	843.6	996.6	1068.5	1046.3	1004.4	865.8	738.9	631.7	561.1
57.5°	536.2	623.8	761.2	894.6	936.4	915.5	873.6	744.2	626.5	545.4	498.3
60°	472.1	551.9	672.2	783.4	816.1	793.9	745.5	629.1	544.1	476.1	440.7
62.5°	413.3	482.6	583.3	685.3	698.4	676.1	634.3	540.1	466.9	413.3	387.1
65°	358.3	423.7	504.8	582.0	593.8	570.2	527.1	459.0	397.6	363.6	338.7
67.5°	304.7	357.0	429.0	485.2	491.7	469.5	434.2	379.3	341.3	304.7	286.4
70°	257.6	296.9	353.1	398.9	401.5	380.6	362.3	312.6	283.8	257.6	243.3
72.5°	211.9	239.3	282.5	316.5	317.8	304.7	287.7	256.3	231.5	213.2	198.8
75°	167.4	190.9	217.1	247.2	245.9	235.4	222.3	202.7	181.8	170.0	163.5
77.5°	128.2	142.6	163.5	183.1	183.1	177.9	170.0	155.6	142.6	130.8	124.2
80°	91.5	100.7	117.7	124.2	126.9	125.6	119.0	108.5	103.3	94.2	91.5
82.5°	58.9	65.4	73.2	79.8	83.7	81.1	79.8	74.5	66.7	64.1	61.5
85°	34.0	36.6	40.5	44.5	45.8	44.5	47.1	43.2	39.2	39.2	37.9
87.5°	14.4	15.7	18.3	18.3	19.6	19.6	18.3	19.6	19.6	18.3	17.0
90°	1.0	3.6	6.2	8.8	11.4	12.7	15.1	19.9	24.7	29.5	34.3
92.5°	21.5	23.3	25.0	26.8	28.5	29.4	29.5	29.7	30.0	30.2	30.4
95°	50.9	53.1	55.3	57.4	59.6	60.7	60.9	61.4	61.8	62.3	62.7
97.5°	85.2	87.2	89.1	91.1	93.0	94.0	94.4	95.3	96.2	97.0	97.9
100°	124.4	126.1	127.9	129.6	131.3	132.2	132.5	133.2	133.9	134.5	135.2
102.5°	165.5	166.8	168.1	169.4	170.7	171.4	171.8	172.7	173.6	174.4	175.3
105°	210.6	211.2	211.9	212.5	213.2	213.5	213.7	214.2	214.6	215.1	215.5
107.5°	255.6	256.5	257.3	258.2	259.1	259.5	259.5	259.5	259.5	259.5	259.5
110°	298.7	300.0	301.3	302.6	303.9	304.6	304.6	304.6	304.6	304.6	304.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	345.7	347.0	348.3	349.6	350.9	351.6	351.5	351.3	351.0	350.8	350.6
115°	391.7	393.0	394.3	395.6	396.9	397.6	397.4	397.0	396.5	396.1	395.7
117.5°	437.8	439.5	441.3	443.0	444.7	445.6	445.1	444.0	442.9	441.8	440.7
120°	483.8	485.5	487.3	489.0	490.7	491.6	490.7	489.0	487.3	485.5	483.8
122.5°	525.9	528.1	530.3	532.4	534.6	535.7	535.2	534.1	533.0	531.9	530.8
125°	570.0	572.0	573.9	575.9	577.8	578.8	578.5	577.8	577.2	576.5	575.9
127.5°	613.1	615.5	617.9	620.3	622.7	623.9	623.5	622.6	621.7	620.8	619.9
130°	653.2	656.0	658.9	661.7	664.6	666.0	665.8	665.3	664.9	664.4	664.0
132.5°	698.3	700.5	702.7	704.8	707.0	708.1	708.2	708.4	708.7	708.9	709.1
135°	737.5	739.9	742.3	744.6	747.0	748.2	748.4	748.9	749.3	749.8	750.2
137.5°	780.6	782.6	784.5	786.5	788.4	789.4	789.6	790.0	790.5	790.9	791.3
140°	818.8	820.8	822.7	824.7	826.6	827.6	828.1	829.2	830.3	831.4	832.5
142.5°	857.9	859.9	861.8	863.8	865.7	866.7	867.0	867.7	868.4	869.0	869.7
145°	895.1	896.6	898.2	899.7	901.2	902.0	902.7	904.0	905.3	906.6	907.9
147.5°	928.4	930.4	932.4	934.3	936.3	937.3	937.7	938.6	939.5	940.3	941.2
150°	962.7	964.0	965.3	966.6	967.9	968.6	969.0	969.9	970.8	971.6	972.5
152.5°	993.1	994.4	995.7	997.0	998.3	999.0	999.5	1000.6	1001.7	1002.8	1003.9
155°	1023.4	1024.1	1024.7	1025.4	1026.1	1026.4	1026.7	1027.4	1028.0	1028.7	1029.3
157.5°	1049.9	1050.3	1050.7	1051.2	1051.6	1051.8	1052.0	1052.5	1052.9	1053.4	1053.8
160°	1073.4	1073.8	1074.3	1074.7	1075.2	1075.4	1075.5	1075.7	1075.9	1076.1	1076.3
162.5°	1094.9	1094.9	1094.9	1094.9	1094.9	1094.9	1095.0	1095.2	1095.5	1095.7	1095.9
165°	1113.5	1113.3	1113.1	1112.9	1112.7	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
167.5°	1130.2	1129.6	1128.9	1128.3	1127.6	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3
170°	1142.9	1142.3	1141.6	1141.0	1140.3	1140.0	1139.9	1139.7	1139.4	1139.2	1139.0
172.5°	1151.7	1151.1	1150.4	1149.8	1149.1	1148.8	1148.7	1148.5	1148.2	1148.0	1147.8
175°	1158.6	1158.0	1157.3	1156.7	1156.0	1155.7	1155.5	1155.0	1154.6	1154.1	1153.7
177.5°	1162.5	1161.9	1161.2	1160.6	1159.9	1159.6	1159.4	1158.9	1158.5	1158.0	1157.6
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1768.2	1769.5	1772.1	1785.2	1791.7	1793.0	1787.8	1799.6	1803.5	1799.6	1797.0
5°	1851.9	1859.7	1875.4	1892.4	1891.1	1892.4	1900.3	1908.1	1910.7	1900.3	1904.2
7.5°	1925.1	1940.8	1957.8	1984.0	1984.0	1997.1	2002.3	2008.8	2024.5	2016.7	2014.1
10°	2008.8	2029.8	2061.1	2103.0	2104.3	2117.4	2130.5	2151.4	2157.9	2152.7	2155.3
12.5°	2113.5	2154.0	2156.6	2202.4	2223.3	2225.9	2246.9	2242.9	2256.0	2256.0	2278.2
15°	2159.2	2222.0	2257.3	2301.8	2314.9	2299.2	2316.2	2334.5	2335.8	2335.8	2334.5
17.5°	2241.6	2266.5	2301.8	2325.3	2330.6	2330.6	2331.9	2339.7	2334.5	2324.0	2331.9
20°	2258.6	2269.1	2282.2	2279.5	2282.2	2269.1	2256.0	2242.9	2244.2	2237.7	2257.3
22.5°	2227.2	2224.6	2194.5	2174.9	2174.9	2148.8	2123.9	2112.1	2100.4	2104.3	2110.8
25°	2148.8	2108.2	2071.6	2042.8	2036.3	1994.4	1960.4	1950.0	1930.4	1946.1	1948.7
27.5°	2023.2	1977.4	1918.6	1893.7	1859.7	1842.7	1819.2	1787.8	1747.3	1770.8	1766.9
30°	1888.5	1820.5	1772.1	1712.0	1658.3	1654.4	1609.9	1557.6	1536.7	1536.7	1548.5
32.5°	1738.1	1647.9	1577.2	1492.2	1439.9	1417.7	1364.1	1311.8	1323.5	1284.3	1298.7
35°	1562.9	1443.8	1354.9	1272.5	1233.3	1207.1	1137.8	1109.0	1077.7	1059.3	1093.3
37.5°	1395.5	1258.1	1144.4	1054.1	1039.7	992.6	945.6	927.3	908.9	916.8	915.5
40°	1191.4	1069.8	967.8	897.2	872.3	850.1	818.7	796.5	784.7	791.2	792.5
42.5°	1007.0	905.0	829.2	779.5	758.5	742.8	727.2	708.8	704.9	704.9	710.2
45°	864.5	780.8	729.8	689.2	677.5	665.7	653.9	646.1	643.5	638.2	642.1
47.5°	750.7	684.0	652.6	622.5	609.4	606.8	596.4	592.4	587.2	585.9	587.2
50°	655.2	613.4	584.6	567.6	558.4	554.5	549.3	541.4	538.8	545.4	542.7
52.5°	588.5	549.3	533.6	516.6	511.4	506.1	498.3	499.6	498.3	495.7	495.7
55°	521.8	497.0	481.3	468.2	466.9	461.7	455.1	452.5	451.2	448.6	452.5
57.5°	468.2	448.6	434.2	422.4	417.2	417.2	410.7	405.4	405.4	404.1	405.4
60°	414.6	395.0	385.8	374.0	370.1	368.8	364.9	362.3	358.3	358.3	358.3
62.5°	364.9	349.2	338.7	328.3	329.6	323.0	317.8	315.2	315.2	316.5	316.5
65°	317.8	307.3	294.3	285.1	282.5	281.2	278.6	277.3	273.3	276.0	276.0
67.5°	274.6	260.3	252.4	248.5	244.6	243.3	240.6	238.0	236.7	235.4	238.0
70°	231.5	219.7	213.2	210.6	206.6	205.3	204.0	200.1	201.4	202.7	204.0
72.5°	192.3	181.8	180.5	172.6	172.6	172.6	167.4	170.0	168.7	166.1	168.7
75°	151.7	146.5	143.9	139.9	141.2	139.9	138.6	134.7	134.7	136.0	137.3
77.5°	120.3	115.1	113.8	109.9	107.2	109.9	107.2	105.9	105.9	107.2	107.2
80°	88.9	86.3	82.4	82.4	82.4	81.1	81.1	81.1	79.8	78.5	79.8
82.5°	58.9	58.9	57.5	56.2	57.5	54.9	56.2	56.2	56.2	56.2	56.2
85°	37.9	36.6	36.6	35.3	35.3	35.3	36.6	34.0	34.0	35.3	35.3
87.5°	17.0	17.0	17.0	18.3	17.0	17.0	17.0	18.3	17.0	17.0	17.0
90°	33.9	33.4	33.0	32.5	32.3	32.4	32.6	32.9	33.1	33.3	33.1
92.5°	30.6	30.8	31.0	31.2	31.3	31.3	31.3	31.3	31.3	31.3	31.3
95°	62.7	62.7	62.7	62.7	62.7	62.5	62.0	61.6	61.1	60.7	61.1
97.5°	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9
100°	135.2	135.2	135.2	135.2	135.2	135.1	134.9	134.6	134.4	134.2	134.4
102.5°	175.5	175.7	176.0	176.2	176.3	176.2	176.0	175.7	175.5	175.3	175.5
105°	215.9	216.3	216.8	217.2	217.4	217.4	217.4	217.4	217.4	217.4	217.4
107.5°	259.7	259.9	260.2	260.4	260.5	260.0	258.9	257.8	256.7	255.6	256.7
110°	304.6	304.6	304.6	304.6	304.6	304.3	303.6	302.9	302.3	301.6	302.3

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	350.0	349.3	348.7	348.0	347.7	347.5	347.0	346.6	346.1	345.7	346.1
115°	395.5	395.3	395.0	394.8	394.7	394.4	393.7	393.0	392.4	391.7	392.4
117.5°	440.1	439.4	438.8	438.1	437.8	437.5	436.8	436.1	435.5	434.8	435.5
120°	483.8	483.8	483.8	483.8	483.8	483.5	482.8	482.2	481.5	480.9	481.5
122.5°	530.2	529.5	528.9	528.2	527.9	527.7	527.2	526.8	526.3	525.9	526.3
125°	575.2	574.6	573.9	573.2	572.9	572.8	572.6	572.4	572.2	572.0	572.2
127.5°	619.0	618.2	617.3	616.4	616.0	615.7	615.0	614.4	613.7	613.1	613.7
130°	663.6	663.2	662.7	662.3	662.1	661.7	660.8	659.9	659.0	658.1	659.0
132.5°	708.0	706.9	705.8	704.7	704.2	703.9	703.2	702.5	701.9	701.2	701.9
135°	750.0	749.8	749.5	749.3	749.2	748.9	748.2	747.6	746.9	746.3	746.9
137.5°	791.1	790.9	790.7	790.5	790.4	790.0	789.1	788.2	787.3	786.4	787.3
140°	832.5	832.5	832.5	832.5	832.5	832.1	831.2	830.3	829.4	828.5	829.4
142.5°	869.9	870.1	870.4	870.6	870.7	870.3	869.4	868.5	867.6	866.7	867.6
145°	908.1	908.3	908.6	908.8	908.9	908.5	907.6	906.7	905.8	904.9	905.8
147.5°	941.6	942.0	942.5	942.9	943.1	942.7	941.8	940.9	940.1	939.2	940.1
150°	973.2	973.8	974.5	975.2	975.5	975.2	974.5	973.8	973.2	972.5	973.2
152.5°	1004.8	1005.6	1006.5	1007.4	1007.8	1007.4	1006.5	1005.6	1004.8	1003.9	1004.8
155°	1030.4	1031.5	1032.6	1033.7	1034.2	1033.9	1033.2	1032.6	1031.9	1031.3	1031.9
157.5°	1055.3	1056.9	1058.4	1059.9	1060.7	1060.2	1059.1	1058.0	1056.9	1055.8	1056.9
160°	1077.6	1078.9	1080.2	1081.5	1082.2	1081.8	1080.9	1080.0	1079.2	1078.3	1079.2
162.5°	1097.4	1099.0	1100.5	1102.0	1102.8	1102.3	1101.2	1100.1	1099.0	1097.9	1099.0
165°	1114.1	1115.6	1117.1	1118.6	1119.4	1118.9	1117.8	1116.7	1115.6	1114.5	1115.6
167.5°	1128.8	1130.3	1131.8	1133.3	1134.1	1133.6	1132.5	1131.4	1130.3	1129.2	1130.3
170°	1140.5	1142.1	1143.6	1145.1	1145.9	1145.2	1143.9	1142.6	1141.3	1140.0	1141.3
172.5°	1149.3	1150.9	1152.4	1153.9	1154.7	1154.0	1152.7	1151.4	1150.1	1148.8	1150.1
175°	1155.2	1156.8	1158.3	1159.8	1160.6	1159.9	1158.6	1157.3	1156.0	1154.7	1156.0
177.5°	1158.9	1160.2	1161.5	1162.8	1163.5	1162.8	1161.5	1160.2	1158.9	1157.6	1158.9
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1803.5	1794.3	1786.5	1787.8	1794.3	1789.1	1776.0	1759.0	1752.5	1744.6	1752.5
5°	1912.0	1904.2	1888.5	1889.8	1885.9	1880.7	1859.7	1833.6	1833.6	1812.7	1810.0
7.5°	2019.3	2007.5	1997.1	1994.4	1980.1	1969.6	1951.3	1914.7	1900.3	1875.4	1861.0
10°	2139.6	2130.5	2118.7	2104.3	2096.5	2078.1	2048.1	1994.4	1968.3	1934.3	1909.4
12.5°	2261.2	2259.9	2233.8	2205.0	2203.7	2174.9	2154.0	2082.1	2046.8	2001.0	1942.1
15°	2338.4	2331.9	2317.5	2303.1	2307.0	2275.6	2228.5	2143.5	2120.0	2065.1	2002.3
17.5°	2337.1	2337.1	2333.2	2330.6	2326.6	2317.5	2291.3	2235.1	2197.2	2127.8	2069.0
20°	2262.5	2279.5	2283.5	2282.2	2295.2	2301.8	2300.5	2265.2	2235.1	2173.6	2113.5
22.5°	2113.5	2152.7	2169.7	2180.2	2207.6	2222.0	2256.0	2242.9	2235.1	2189.3	2138.3
25°	1974.8	1987.9	2038.9	2041.5	2079.5	2114.8	2148.8	2171.0	2199.8	2182.8	2139.6
27.5°	1795.7	1825.7	1862.4	1889.8	1897.7	1969.6	2025.8	2067.7	2133.1	2138.3	2123.9
30°	1592.9	1607.3	1667.5	1704.1	1746.0	1798.3	1879.4	1951.3	2010.1	2063.8	2082.1
32.5°	1345.8	1404.6	1439.9	1484.4	1521.0	1613.9	1713.3	1806.1	1874.1	1964.4	2003.6
35°	1119.5	1165.3	1225.4	1243.7	1310.4	1388.9	1518.4	1637.4	1740.7	1832.3	1912.0
37.5°	932.5	969.1	1033.2	1062.0	1101.2	1201.9	1310.4	1458.2	1582.5	1694.9	1794.3
40°	804.3	831.8	880.2	889.3	922.0	1013.6	1101.2	1239.8	1404.6	1556.3	1664.9
42.5°	716.7	729.8	762.5	774.2	795.2	856.6	935.1	1065.9	1218.9	1375.8	1528.9
45°	653.9	663.1	682.7	693.2	719.3	746.8	810.9	915.5	1035.8	1194.0	1358.8
47.5°	597.7	609.4	617.3	623.8	638.2	668.3	710.2	787.3	902.4	1047.6	1207.1
50°	550.6	554.5	568.9	570.2	579.4	599.0	638.2	685.3	776.9	894.6	1048.9
52.5°	503.5	507.4	516.6	525.7	529.7	545.4	571.5	610.8	678.8	771.6	908.9
55°	456.4	461.7	470.8	477.4	481.3	494.4	510.1	548.0	601.6	667.0	779.5
57.5°	409.4	421.1	423.7	427.7	434.2	448.6	463.0	485.2	527.1	587.2	669.6
60°	364.9	368.8	378.0	381.9	388.4	396.3	414.6	431.6	461.7	508.7	583.3
62.5°	319.1	328.3	332.2	336.1	341.3	350.5	362.3	380.6	406.7	444.7	503.5
65°	279.9	281.2	289.0	294.3	299.5	306.0	317.8	334.8	350.5	385.8	429.0
67.5°	241.9	244.6	247.2	252.4	259.0	265.5	276.0	285.1	304.7	328.3	362.3
70°	205.3	205.3	211.9	215.8	214.5	222.3	230.2	240.6	255.0	277.3	304.7
72.5°	172.6	171.3	176.6	177.9	180.5	185.7	190.9	201.4	209.3	226.3	247.2
75°	137.3	139.9	142.6	142.6	146.5	150.4	155.6	160.9	170.0	180.5	196.2
77.5°	108.5	108.5	111.2	112.5	116.4	115.1	120.3	125.6	132.1	141.2	153.0
80°	79.8	82.4	82.4	82.4	83.7	85.0	90.2	94.2	98.1	104.6	109.9
82.5°	56.2	56.2	58.9	58.9	58.9	61.5	61.5	62.8	65.4	69.3	73.2
85°	35.3	35.3	35.3	36.6	35.3	36.6	39.2	37.9	39.2	41.9	41.9
87.5°	17.0	17.0	17.0	17.0	17.0	18.3	17.0	18.3	19.6	19.6	19.6
90°	32.9	32.6	32.4	32.3	32.5	33.0	33.4	33.9	34.3	29.5	24.7
92.5°	31.3	31.3	31.3	31.3	31.2	31.0	30.8	30.6	30.4	30.2	30.0
95°	61.6	62.0	62.5	62.7	62.7	62.7	62.7	62.7	62.7	62.3	61.8
97.5°	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.0	96.2
100°	134.6	134.9	135.1	135.2	135.2	135.2	135.2	135.2	135.2	134.5	133.9
102.5°	175.7	176.0	176.2	176.3	176.2	176.0	175.7	175.5	175.3	174.4	173.6
105°	217.4	217.4	217.4	217.4	217.2	216.8	216.3	215.9	215.5	215.1	214.6
107.5°	257.8	258.9	260.0	260.5	260.4	260.2	259.9	259.7	259.5	259.5	259.5
110°	302.9	303.6	304.3	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	346.6	347.0	347.5	347.7	348.0	348.7	349.3	350.0	350.6	350.8	351.0
115°	393.0	393.7	394.4	394.7	394.8	395.0	395.3	395.5	395.7	396.1	396.5
117.5°	436.1	436.8	437.5	437.8	438.1	438.8	439.4	440.1	440.7	441.8	442.9
120°	482.2	482.8	483.5	483.8	483.8	483.8	483.8	483.8	483.8	485.5	487.3
122.5°	526.8	527.2	527.7	527.9	528.2	528.9	529.5	530.2	530.8	531.9	533.0
125°	572.4	572.6	572.8	572.9	573.2	573.9	574.6	575.2	575.9	576.5	577.2
127.5°	614.4	615.0	615.7	616.0	616.4	617.3	618.2	619.0	619.9	620.8	621.7
130°	659.9	660.8	661.7	662.1	662.3	662.7	663.2	663.6	664.0	664.4	664.9
132.5°	702.5	703.2	703.9	704.2	704.7	705.8	706.9	708.0	709.1	708.9	708.7
135°	747.6	748.2	748.9	749.2	749.3	749.5	749.8	750.0	750.2	749.8	749.3
137.5°	788.2	789.1	790.0	790.4	790.5	790.7	790.9	791.1	791.3	790.9	790.5
140°	830.3	831.2	832.1	832.5	832.5	832.5	832.5	832.5	832.5	831.4	830.3
142.5°	868.5	869.4	870.3	870.7	870.6	870.4	870.1	869.9	869.7	869.0	868.4
145°	906.7	907.6	908.5	908.9	908.8	908.6	908.3	908.1	907.9	906.6	905.3
147.5°	940.9	941.8	942.7	943.1	942.9	942.5	942.0	941.6	941.2	940.3	939.5
150°	973.8	974.5	975.2	975.5	975.2	974.5	973.8	973.2	972.5	971.6	970.8
152.5°	1005.6	1006.5	1007.4	1007.8	1007.4	1006.5	1005.6	1004.8	1003.9	1002.8	1001.7
155°	1032.6	1033.2	1033.9	1034.2	1033.7	1032.6	1031.5	1030.4	1029.3	1028.7	1028.0
157.5°	1058.0	1059.1	1060.2	1060.7	1059.9	1058.4	1056.9	1055.3	1053.8	1053.4	1052.9
160°	1080.0	1080.9	1081.8	1082.2	1081.5	1080.2	1078.9	1077.6	1076.3	1076.1	1075.9
162.5°	1100.1	1101.2	1102.3	1102.8	1102.0	1100.5	1099.0	1097.4	1095.9	1095.7	1095.5
165°	1116.7	1117.8	1118.9	1119.4	1118.6	1117.1	1115.6	1114.1	1112.6	1112.6	1112.6
167.5°	1131.4	1132.5	1133.6	1134.1	1133.3	1131.8	1130.3	1128.8	1127.3	1127.3	1127.3
170°	1142.6	1143.9	1145.2	1145.9	1145.1	1143.6	1142.1	1140.5	1139.0	1139.2	1139.4
172.5°	1151.4	1152.7	1154.0	1154.7	1153.9	1152.4	1150.9	1149.3	1147.8	1148.0	1148.2
175°	1157.3	1158.6	1159.9	1160.6	1159.8	1158.3	1156.8	1155.2	1153.7	1154.1	1154.6
177.5°	1160.2	1161.5	1162.8	1163.5	1162.8	1161.5	1160.2	1158.9	1157.6	1158.0	1158.5
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1746.0	1739.4	1735.5	1738.1	1730.3	1710.6	1710.6	1717.2	1709.3	1701.5	1689.7
5°	1794.3	1781.3	1773.4	1772.1	1753.8	1722.4	1715.9	1709.3	1692.3	1674.0	1654.4
7.5°	1841.4	1817.9	1804.8	1795.7	1769.5	1729.0	1712.0	1697.6	1670.1	1642.6	1617.8
10°	1880.7	1846.7	1831.0	1816.6	1782.6	1731.6	1704.1	1677.9	1642.6	1607.3	1575.9
12.5°	1912.0	1872.8	1853.2	1832.3	1790.4	1723.7	1689.7	1647.9	1612.6	1565.5	1534.1
15°	1964.4	1883.3	1865.0	1845.3	1802.2	1710.6	1668.8	1621.7	1573.3	1510.5	1476.5
17.5°	2006.2	1897.7	1896.4	1854.5	1798.3	1705.4	1641.3	1579.9	1527.5	1464.8	1411.1
20°	2031.1	1919.9	1899.0	1855.8	1785.2	1670.1	1603.4	1535.4	1479.2	1403.3	1349.7
22.5°	2052.0	1951.3	1896.4	1844.0	1757.7	1658.3	1560.2	1496.2	1419.0	1336.6	1285.6
25°	2059.8	1957.8	1900.3	1840.1	1738.1	1624.3	1513.2	1443.8	1357.5	1283.0	1213.7
27.5°	2061.1	1956.5	1885.9	1823.1	1710.6	1579.9	1466.1	1392.8	1297.4	1211.1	1141.7
30°	2048.1	1942.1	1878.0	1810.0	1684.5	1539.3	1408.5	1327.4	1225.4	1139.1	1067.2
32.5°	2008.8	1913.4	1861.0	1786.5	1650.5	1483.1	1353.6	1263.4	1156.1	1071.1	1001.8
35°	1943.4	1878.0	1820.5	1751.2	1606.0	1430.8	1298.7	1192.7	1084.2	1003.1	937.7
37.5°	1862.4	1827.0	1773.4	1705.4	1555.0	1383.7	1237.2	1119.5	1011.0	932.5	868.4
40°	1752.5	1761.6	1709.3	1647.9	1494.9	1319.6	1157.4	1045.0	942.9	869.7	806.9
42.5°	1633.5	1671.4	1641.3	1582.5	1428.2	1249.0	1098.6	974.3	874.9	799.1	746.8
45°	1505.3	1570.7	1552.4	1509.2	1358.8	1174.4	1014.9	894.6	806.9	733.7	687.9
47.5°	1365.4	1458.2	1458.2	1426.8	1281.7	1099.9	942.9	820.0	733.7	681.4	636.9
50°	1222.8	1327.4	1344.4	1323.5	1195.4	1014.9	855.3	744.2	669.6	618.6	585.9
52.5°	1073.7	1195.4	1226.7	1216.3	1103.8	933.8	783.4	674.8	606.8	562.4	533.6
55°	931.2	1072.4	1106.4	1110.3	1005.7	844.9	703.6	608.1	542.7	512.7	487.8
57.5°	796.5	932.5	970.4	976.9	906.3	763.8	629.1	545.4	486.5	461.7	442.0
60°	681.4	795.2	844.9	859.2	797.8	669.6	559.8	478.7	434.2	410.7	392.3
62.5°	587.2	678.8	731.1	735.0	707.5	587.2	487.8	419.8	381.9	361.0	351.8
65°	495.7	578.1	609.4	625.1	602.9	508.7	421.1	364.9	334.8	316.5	307.3
67.5°	422.4	474.7	500.9	521.8	499.6	429.0	358.3	312.6	290.3	272.0	266.8
70°	346.6	389.7	409.4	430.3	410.7	357.0	306.0	264.2	244.6	230.2	223.6
72.5°	277.3	311.3	329.6	342.7	330.9	286.4	244.6	215.8	201.4	190.9	187.0
75°	219.7	243.3	253.7	262.9	257.6	223.6	197.5	173.9	160.9	151.7	149.1
77.5°	167.4	184.4	196.2	198.8	192.3	170.0	147.8	133.4	122.9	117.7	115.1
80°	119.0	129.5	136.0	139.9	133.4	124.2	108.5	98.1	88.9	82.4	81.1
82.5°	79.8	85.0	90.2	88.9	86.3	78.5	69.3	64.1	60.2	54.9	54.9
85°	45.8	47.1	49.7	51.0	49.7	44.5	39.2	36.6	34.0	30.1	30.1
87.5°	19.6	20.9	20.9	22.2	19.6	19.6	17.0	14.4	14.4	13.1	11.8
90°	19.9	15.1	12.7	11.4	8.8	6.2	3.6	1.0	3.6	6.2	8.8
92.5°	29.7	29.5	29.4	28.5	26.8	25.0	23.3	21.5	23.3	25.0	26.8
95°	61.4	60.9	60.7	59.6	57.4	55.3	53.1	50.9	53.1	55.3	57.4
97.5°	95.3	94.4	94.0	93.0	91.1	89.1	87.2	85.2	87.2	89.1	91.1
100°	133.2	132.5	132.2	131.3	129.6	127.9	126.1	124.4	126.1	127.9	129.6
102.5°	172.7	171.8	171.4	170.7	169.4	168.1	166.8	165.5	166.8	168.1	169.4
105°	214.2	213.7	213.5	213.2	212.5	211.9	211.2	210.6	211.2	211.9	212.5
107.5°	259.5	259.5	259.5	259.1	258.2	257.3	256.5	255.6	256.5	257.3	258.2
110°	304.6	304.6	304.6	303.9	302.6	301.3	300.0	298.7	300.0	301.3	302.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	351.3	351.5	351.6	350.9	349.6	348.3	347.0	345.7	347.0	348.3	349.6
115°	397.0	397.4	397.6	396.9	395.6	394.3	393.0	391.7	393.0	394.3	395.6
117.5°	444.0	445.1	445.6	444.7	443.0	441.3	439.5	437.8	439.5	441.3	443.0
120°	489.0	490.7	491.6	490.7	489.0	487.3	485.5	483.8	485.5	487.3	489.0
122.5°	534.1	535.2	535.7	534.6	532.4	530.3	528.1	525.9	528.1	530.3	532.4
125°	577.8	578.5	578.8	577.8	575.9	573.9	572.0	570.0	572.0	573.9	575.9
127.5°	622.6	623.5	623.9	622.7	620.3	617.9	615.5	613.1	615.5	617.9	620.3
130°	665.3	665.8	666.0	664.6	661.7	658.9	656.0	653.2	656.0	658.9	661.7
132.5°	708.4	708.2	708.1	707.0	704.8	702.7	700.5	698.3	700.5	702.7	704.8
135°	748.9	748.4	748.2	747.0	744.6	742.3	739.9	737.5	739.9	742.3	744.6
137.5°	790.0	789.6	789.4	788.4	786.5	784.5	782.6	780.6	782.6	784.5	786.5
140°	829.2	828.1	827.6	826.6	824.7	822.7	820.8	818.8	820.8	822.7	824.7
142.5°	867.7	867.0	866.7	865.7	863.8	861.8	859.9	857.9	859.9	861.8	863.8
145°	904.0	902.7	902.0	901.2	899.7	898.2	896.6	895.1	896.6	898.2	899.7
147.5°	938.6	937.7	937.3	936.3	934.3	932.4	930.4	928.4	930.4	932.4	934.3
150°	969.9	969.0	968.6	967.9	966.6	965.3	964.0	962.7	964.0	965.3	966.6
152.5°	1000.6	999.5	999.0	998.3	997.0	995.7	994.4	993.1	994.4	995.7	997.0
155°	1027.4	1026.7	1026.4	1026.1	1025.4	1024.7	1024.1	1023.4	1024.1	1024.7	1025.4
157.5°	1052.5	1052.0	1051.8	1051.6	1051.2	1050.7	1050.3	1049.9	1050.3	1050.7	1051.2
160°	1075.7	1075.5	1075.4	1075.2	1074.7	1074.3	1073.8	1073.4	1073.8	1074.3	1074.7
162.5°	1095.2	1095.0	1094.9	1094.9	1094.9	1094.9	1094.9	1094.9	1094.9	1094.9	1094.9
165°	1112.6	1112.6	1112.6	1112.7	1112.9	1113.1	1113.3	1113.5	1113.3	1113.1	1112.9
167.5°	1127.3	1127.3	1127.3	1127.6	1128.3	1128.9	1129.6	1130.2	1129.6	1128.9	1128.3
170°	1139.7	1139.9	1140.0	1140.3	1141.0	1141.6	1142.3	1142.9	1142.3	1141.6	1141.0
172.5°	1148.5	1148.7	1148.8	1149.1	1149.8	1150.4	1151.1	1151.7	1151.1	1150.4	1149.8
175°	1155.0	1155.5	1155.7	1156.0	1156.7	1157.3	1158.0	1158.6	1158.0	1157.3	1156.7
177.5°	1158.9	1159.4	1159.6	1159.9	1160.6	1161.2	1161.9	1162.5	1161.9	1161.2	1160.6
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1683.2	1689.7	1688.4	1675.3	1660.9	1649.2	1626.9	1629.6	1621.7	1623.0	1630.9
5°	1641.3	1641.3	1636.1	1617.8	1594.2	1581.2	1556.3	1549.8	1534.1	1532.8	1531.5
7.5°	1596.9	1590.3	1583.8	1557.6	1528.9	1507.9	1473.9	1466.1	1450.4	1439.9	1434.7
10°	1544.5	1535.4	1522.3	1492.2	1456.9	1430.8	1395.5	1385.0	1354.9	1341.8	1334.0
12.5°	1487.0	1481.8	1460.8	1436.0	1378.5	1349.7	1298.7	1309.1	1279.1	1252.9	1249.0
15°	1429.5	1409.8	1398.1	1357.5	1288.2	1275.1	1234.6	1213.7	1186.2	1165.3	1165.3
17.5°	1373.2	1343.1	1317.0	1273.8	1222.8	1186.2	1156.1	1145.7	1111.7	1090.7	1086.8
20°	1298.7	1264.7	1258.1	1196.7	1161.4	1120.8	1092.0	1065.9	1041.0	1031.9	1025.3
22.5°	1228.1	1188.8	1178.4	1126.0	1090.7	1050.2	1021.4	1003.1	984.8	978.3	966.5
25°	1152.2	1128.7	1113.0	1056.7	1017.5	979.6	959.9	946.9	929.9	928.6	920.7
27.5°	1079.0	1056.7	1041.0	987.4	958.6	923.3	907.6	893.2	884.1	880.2	876.2
30°	1016.2	991.3	973.0	933.8	898.5	869.7	856.6	847.5	842.2	835.7	834.4
32.5°	946.9	932.5	907.6	877.6	850.1	822.6	814.8	808.2	800.4	797.8	796.5
35°	888.0	868.4	852.7	818.7	806.9	783.4	774.2	769.0	758.5	755.9	753.3
37.5°	830.5	812.2	795.2	774.2	752.0	738.9	733.7	725.8	720.6	721.9	719.3
40°	772.9	758.5	745.5	723.2	710.2	703.6	693.2	685.3	682.7	684.0	682.7
42.5°	716.7	703.6	695.8	678.8	665.7	659.1	652.6	644.8	648.7	648.7	652.6
45°	665.7	653.9	648.7	635.6	627.8	617.3	610.8	609.4	614.7	613.4	613.4
47.5°	613.4	609.4	602.9	591.1	580.7	574.1	572.8	572.8	578.1	580.7	579.4
50°	572.8	565.0	557.1	548.0	540.1	537.5	533.6	536.2	541.4	541.4	544.1
52.5°	521.8	516.6	514.0	506.1	500.9	500.9	500.9	502.2	506.1	510.1	508.7
55°	477.4	473.4	470.8	466.9	460.4	461.7	460.4	463.0	466.9	470.8	473.4
57.5°	430.3	429.0	426.4	419.8	419.8	418.5	422.4	423.7	430.3	432.9	436.8
60°	388.4	384.5	384.5	379.3	379.3	379.3	383.2	387.1	392.3	393.7	396.3
62.5°	344.0	344.0	342.7	338.7	338.7	342.7	344.0	349.2	351.8	351.8	355.7
65°	302.1	300.8	299.5	300.8	302.1	302.1	306.0	308.6	311.3	312.6	313.9
67.5°	260.3	259.0	261.6	260.3	262.9	268.1	266.8	270.7	274.6	274.6	276.0
70°	221.0	223.6	222.3	224.9	223.6	226.3	230.2	231.5	231.5	232.8	236.7
72.5°	184.4	184.4	184.4	183.1	184.4	187.0	189.6	190.9	193.6	194.9	198.8
75°	149.1	149.1	146.5	149.1	149.1	151.7	154.3	154.3	154.3	156.9	160.9
77.5°	112.5	113.8	112.5	115.1	115.1	116.4	119.0	117.7	120.3	121.6	122.9
80°	82.4	81.1	81.1	81.1	82.4	82.4	85.0	86.3	86.3	90.2	87.6
82.5°	52.3	53.6	52.3	53.6	53.6	54.9	53.6	54.9	56.2	58.9	57.5
85°	30.1	28.8	28.8	30.1	28.8	28.8	30.1	28.8	30.1	28.8	30.1
87.5°	11.8	10.5	10.5	10.5	10.5	9.2	9.2	7.8	7.8	7.8	6.5
90°	11.4	12.7	15.1	19.9	24.7	29.5	34.3	33.9	33.4	33.0	32.5
92.5°	28.5	29.4	29.5	29.7	30.0	30.2	30.4	30.6	30.8	31.0	31.2
95°	59.6	60.7	60.9	61.4	61.8	62.3	62.7	62.7	62.7	62.7	62.7
97.5°	93.0	94.0	94.4	95.3	96.2	97.0	97.9	97.9	97.9	97.9	97.9
100°	131.3	132.2	132.5	133.2	133.9	134.5	135.2	135.2	135.2	135.2	135.2
102.5°	170.7	171.4	171.8	172.7	173.6	174.4	175.3	175.5	175.7	176.0	176.2
105°	213.2	213.5	213.7	214.2	214.6	215.1	215.5	215.9	216.3	216.8	217.2
107.5°	259.1	259.5	259.5	259.5	259.5	259.5	259.5	259.7	259.9	260.2	260.4
110°	303.9	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	350.9	351.6	351.5	351.3	351.0	350.8	350.6	350.0	349.3	348.7	348.0
115°	396.9	397.6	397.4	397.0	396.5	396.1	395.7	395.5	395.3	395.0	394.8
117.5°	444.7	445.6	445.1	444.0	442.9	441.8	440.7	440.1	439.4	438.8	438.1
120°	490.7	491.6	490.7	489.0	487.3	485.5	483.8	483.8	483.8	483.8	483.8
122.5°	534.6	535.7	535.2	534.1	533.0	531.9	530.8	530.2	529.5	528.9	528.2
125°	577.8	578.8	578.5	577.8	577.2	576.5	575.9	575.2	574.6	573.9	573.2
127.5°	622.7	623.9	623.5	622.6	621.7	620.8	619.9	619.0	618.2	617.3	616.4
130°	664.6	666.0	665.8	665.3	664.9	664.4	664.0	663.6	663.2	662.7	662.3
132.5°	707.0	708.1	708.2	708.4	708.7	708.9	709.1	708.0	706.9	705.8	704.7
135°	747.0	748.2	748.4	748.9	749.3	749.8	750.2	750.0	749.8	749.5	749.3
137.5°	788.4	789.4	789.6	790.0	790.5	790.9	791.3	791.1	790.9	790.7	790.5
140°	826.6	827.6	828.1	829.2	830.3	831.4	832.5	832.5	832.5	832.5	832.5
142.5°	865.7	866.7	867.0	867.7	868.4	869.0	869.7	869.9	870.1	870.4	870.6
145°	901.2	902.0	902.7	904.0	905.3	906.6	907.9	908.1	908.3	908.6	908.8
147.5°	936.3	937.3	937.7	938.6	939.5	940.3	941.2	941.6	942.0	942.5	942.9
150°	967.9	968.6	969.0	969.9	970.8	971.6	972.5	973.2	973.8	974.5	975.2
152.5°	998.3	999.0	999.5	1000.6	1001.7	1002.8	1003.9	1004.8	1005.6	1006.5	1007.4
155°	1026.1	1026.4	1026.7	1027.4	1028.0	1028.7	1029.3	1030.4	1031.5	1032.6	1033.7
157.5°	1051.6	1051.8	1052.0	1052.5	1052.9	1053.4	1053.8	1055.3	1056.9	1058.4	1059.9
160°	1075.2	1075.4	1075.5	1075.7	1075.9	1076.1	1076.3	1077.6	1078.9	1080.2	1081.5
162.5°	1094.9	1094.9	1095.0	1095.2	1095.5	1095.7	1095.9	1097.4	1099.0	1100.5	1102.0
165°	1112.7	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1114.1	1115.6	1117.1	1118.6
167.5°	1127.6	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3	1128.8	1130.3	1131.8	1133.3
170°	1140.3	1140.0	1139.9	1139.7	1139.4	1139.2	1139.0	1140.5	1142.1	1143.6	1145.1
172.5°	1149.1	1148.8	1148.7	1148.5	1148.2	1148.0	1147.8	1149.3	1150.9	1152.4	1153.9
175°	1156.0	1155.7	1155.5	1155.0	1154.6	1154.1	1153.7	1155.2	1156.8	1158.3	1159.8
177.5°	1159.9	1159.6	1159.4	1158.9	1158.5	1158.0	1157.6	1158.9	1160.2	1161.5	1162.8
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1621.7	1625.6	1616.5	1613.9	1616.5	1607.3	1609.9	1612.6	1612.6	1616.5	1619.1
5°	1527.5	1522.3	1513.2	1510.5	1507.9	1511.9	1509.2	1513.2	1514.5	1523.6	1524.9
7.5°	1434.7	1426.8	1419.0	1411.1	1408.5	1402.0	1408.5	1408.5	1417.7	1415.1	1421.6
10°	1324.8	1323.5	1313.1	1309.1	1303.9	1293.4	1307.8	1303.9	1310.4	1322.2	1324.8
12.5°	1243.7	1229.4	1235.9	1217.6	1224.1	1213.7	1215.0	1215.0	1225.4	1226.7	1224.1
15°	1166.6	1154.8	1137.8	1130.0	1126.0	1120.8	1137.8	1139.1	1131.3	1149.6	1143.0
17.5°	1088.1	1088.1	1072.4	1068.5	1058.0	1063.3	1060.7	1062.0	1059.3	1072.4	1079.0
20°	1020.1	1013.6	1008.3	1009.6	996.6	994.0	991.3	994.0	1003.1	1012.3	1014.9
22.5°	965.2	961.3	948.2	950.8	940.3	944.3	941.6	948.2	949.5	949.5	958.6
25°	912.9	907.6	908.9	903.7	899.8	899.8	895.9	899.8	905.0	907.6	908.9
27.5°	873.6	869.7	863.2	859.2	861.9	855.3	860.6	864.5	864.5	861.9	864.5
30°	826.5	829.2	829.2	816.1	821.3	818.7	822.6	825.2	825.2	826.5	823.9
32.5°	795.2	787.3	786.0	784.7	784.7	779.5	779.5	783.4	784.7	786.0	789.9
35°	753.3	753.3	746.8	750.7	745.5	746.8	745.5	746.8	749.4	745.5	749.4
37.5°	715.4	716.7	714.1	716.7	718.0	715.4	712.8	718.0	715.4	715.4	712.8
40°	682.7	681.4	682.7	682.7	682.7	684.0	681.4	681.4	681.4	678.8	676.1
42.5°	655.2	647.4	650.0	651.3	647.4	647.4	648.7	647.4	651.3	643.5	643.5
45°	616.0	613.4	614.7	614.7	617.3	613.4	616.0	617.3	613.4	612.1	609.4
47.5°	580.7	583.3	580.7	583.3	583.3	585.9	580.7	582.0	583.3	578.1	574.1
50°	545.4	545.4	549.3	548.0	549.3	546.7	546.7	545.4	546.7	544.1	540.1
52.5°	512.7	508.7	515.3	514.0	512.7	511.4	510.1	511.4	508.7	506.1	506.1
55°	472.1	472.1	476.1	477.4	477.4	474.7	472.1	473.4	472.1	470.8	469.5
57.5°	439.4	434.2	436.8	438.1	438.1	434.2	436.8	434.2	434.2	435.5	431.6
60°	397.6	397.6	395.0	398.9	398.9	396.3	396.3	397.6	395.0	393.7	392.3
62.5°	353.1	354.4	358.3	359.7	361.0	358.3	355.7	357.0	357.0	353.1	354.4
65°	315.2	317.8	323.0	321.7	319.1	320.4	317.8	319.1	315.2	316.5	312.6
67.5°	278.6	277.3	278.6	278.6	281.2	279.9	277.3	277.3	276.0	279.9	276.0
70°	239.3	239.3	239.3	239.3	240.6	241.9	239.3	236.7	238.0	235.4	234.1
72.5°	198.8	200.1	198.8	201.4	197.5	200.1	200.1	198.8	197.5	197.5	197.5
75°	160.9	163.5	159.6	160.9	159.6	162.2	160.9	160.9	158.2	156.9	158.2
77.5°	122.9	124.2	121.6	122.9	121.6	122.9	122.9	121.6	121.6	121.6	121.6
80°	87.6	88.9	87.6	86.3	85.0	87.6	85.0	86.3	87.6	86.3	88.9
82.5°	56.2	56.2	54.9	56.2	53.6	53.6	54.9	54.9	53.6	56.2	53.6
85°	27.5	27.5	30.1	27.5	26.2	26.2	26.2	27.5	26.2	28.8	27.5
87.5°	6.5	5.2	6.5	6.5	5.2	5.2	6.5	5.2	6.5	7.8	5.2
90°	32.3	32.4	32.6	32.9	33.1	33.3	33.1	32.9	32.6	32.4	32.3
92.5°	31.3	31.3	31.3	31.3	31.3	31.3	31.3	31.3	31.3	31.3	31.3
95°	62.7	62.5	62.0	61.6	61.1	60.7	61.1	61.6	62.0	62.5	62.7
97.5°	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9
100°	135.2	135.1	134.9	134.6	134.4	134.2	134.4	134.6	134.9	135.1	135.2
102.5°	176.3	176.2	176.0	175.7	175.5	175.3	175.5	175.7	176.0	176.2	176.3
105°	217.4	217.4	217.4	217.4	217.4	217.4	217.4	217.4	217.4	217.4	217.4
107.5°	260.5	260.0	258.9	257.8	256.7	255.6	256.7	257.8	258.9	260.0	260.5
110°	304.6	304.3	303.6	302.9	302.3	301.6	302.3	302.9	303.6	304.3	304.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	347.7	347.5	347.0	346.6	346.1	345.7	346.1	346.6	347.0	347.5	347.7
115°	394.7	394.4	393.7	393.0	392.4	391.7	392.4	393.0	393.7	394.4	394.7
117.5°	437.8	437.5	436.8	436.1	435.5	434.8	435.5	436.1	436.8	437.5	437.8
120°	483.8	483.5	482.8	482.2	481.5	480.9	481.5	482.2	482.8	483.5	483.8
122.5°	527.9	527.7	527.2	526.8	526.3	525.9	526.3	526.8	527.2	527.7	527.9
125°	572.9	572.8	572.6	572.4	572.2	572.0	572.2	572.4	572.6	572.8	572.9
127.5°	616.0	615.7	615.0	614.4	613.7	613.1	613.7	614.4	615.0	615.7	616.0
130°	662.1	661.7	660.8	659.9	659.0	658.1	659.0	659.9	660.8	661.7	662.1
132.5°	704.2	703.9	703.2	702.5	701.9	701.2	701.9	702.5	703.2	703.9	704.2
135°	749.2	748.9	748.2	747.6	746.9	746.3	746.9	747.6	748.2	748.9	749.2
137.5°	790.4	790.0	789.1	788.2	787.3	786.4	787.3	788.2	789.1	790.0	790.4
140°	832.5	832.1	831.2	830.3	829.4	828.5	829.4	830.3	831.2	832.1	832.5
142.5°	870.7	870.3	869.4	868.5	867.6	866.7	867.6	868.5	869.4	870.3	870.7
145°	908.9	908.5	907.6	906.7	905.8	904.9	905.8	906.7	907.6	908.5	908.9
147.5°	943.1	942.7	941.8	940.9	940.1	939.2	940.1	940.9	941.8	942.7	943.1
150°	975.5	975.2	974.5	973.8	973.2	972.5	973.2	973.8	974.5	975.2	975.5
152.5°	1007.8	1007.4	1006.5	1005.6	1004.8	1003.9	1004.8	1005.6	1006.5	1007.4	1007.8
155°	1034.2	1033.9	1033.2	1032.6	1031.9	1031.3	1031.9	1032.6	1033.2	1033.9	1034.2
157.5°	1060.7	1060.2	1059.1	1058.0	1056.9	1055.8	1056.9	1058.0	1059.1	1060.2	1060.7
160°	1082.2	1081.8	1080.9	1080.0	1079.2	1078.3	1079.2	1080.0	1080.9	1081.8	1082.2
162.5°	1102.8	1102.3	1101.2	1100.1	1099.0	1097.9	1099.0	1100.1	1101.2	1102.3	1102.8
165°	1119.4	1118.9	1117.8	1116.7	1115.6	1114.5	1115.6	1116.7	1117.8	1118.9	1119.4
167.5°	1134.1	1133.6	1132.5	1131.4	1130.3	1129.2	1130.3	1131.4	1132.5	1133.6	1134.1
170°	1145.9	1145.2	1143.9	1142.6	1141.3	1140.0	1141.3	1142.6	1143.9	1145.2	1145.9
172.5°	1154.7	1154.0	1152.7	1151.4	1150.1	1148.8	1150.1	1151.4	1152.7	1154.0	1154.7
175°	1160.6	1159.9	1158.6	1157.3	1156.0	1154.7	1156.0	1157.3	1158.6	1159.9	1160.6
177.5°	1163.5	1162.8	1161.5	1160.2	1158.9	1157.6	1158.9	1160.2	1161.5	1162.8	1163.5
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1615.2	1625.6	1621.7	1607.3	1624.3	1624.3	1636.1	1636.1	1650.5	1655.7	1663.6
5°	1523.6	1531.5	1538.0	1531.5	1543.2	1561.5	1572.0	1581.2	1600.8	1608.6	1620.4
7.5°	1425.5	1439.9	1446.5	1446.5	1466.1	1487.0	1507.9	1521.0	1548.5	1558.9	1570.7
10°	1330.1	1347.1	1360.1	1358.8	1391.5	1404.6	1430.8	1460.8	1488.3	1504.0	1521.0
12.5°	1229.4	1238.5	1256.8	1283.0	1290.8	1314.4	1344.4	1382.4	1432.1	1446.5	1471.3
15°	1145.7	1170.5	1184.9	1196.7	1215.0	1237.2	1269.9	1306.5	1356.2	1387.6	1413.8
17.5°	1075.0	1107.7	1116.9	1114.3	1137.8	1171.8	1209.7	1237.2	1281.7	1319.6	1344.4
20°	1017.5	1030.6	1046.3	1052.8	1071.1	1107.7	1144.4	1175.7	1212.4	1242.4	1271.2
22.5°	959.9	970.4	983.5	995.3	1009.6	1030.6	1065.9	1105.1	1140.4	1169.2	1201.9
25°	912.9	919.4	931.2	940.3	956.0	970.4	995.3	1038.4	1080.3	1097.3	1126.0
27.5°	867.1	872.3	880.2	890.6	898.5	912.9	935.1	970.4	1013.6	1030.6	1069.8
30°	826.5	830.5	838.3	843.6	847.5	864.5	881.5	908.9	941.6	965.2	994.0
32.5°	788.6	792.5	800.4	801.7	806.9	816.1	831.8	856.6	885.4	905.0	929.9
35°	746.8	749.4	757.2	759.8	763.8	771.6	783.4	801.7	827.9	842.2	864.5
37.5°	714.1	712.8	718.0	721.9	727.2	731.1	735.0	753.3	772.9	786.0	803.0
40°	678.8	676.1	677.5	682.7	685.3	690.5	690.5	708.8	721.9	732.4	745.5
42.5°	643.5	642.1	639.5	642.1	644.8	646.1	647.4	660.5	673.5	682.7	697.1
45°	608.1	606.8	604.2	605.5	605.5	608.1	612.1	617.3	626.5	634.3	642.1
47.5°	575.4	572.8	568.9	567.6	570.2	570.2	570.2	575.4	584.6	587.2	595.1
50°	541.4	537.5	532.3	529.7	529.7	528.4	531.0	532.3	540.1	542.7	549.3
52.5°	504.8	502.2	497.0	491.7	493.1	490.4	491.7	493.1	495.7	499.6	503.5
55°	468.2	463.0	459.0	457.7	453.8	453.8	449.9	455.1	453.8	455.1	460.4
57.5°	432.9	427.7	421.1	418.5	414.6	413.3	410.7	409.4	410.7	414.6	418.5
60°	391.0	388.4	384.5	380.6	378.0	374.0	371.4	371.4	370.1	370.1	371.4
62.5°	350.5	349.2	344.0	342.7	340.0	337.4	333.5	330.9	330.9	333.5	334.8
65°	311.3	310.0	306.0	304.7	298.2	295.6	294.3	293.0	290.3	290.3	290.3
67.5°	274.6	270.7	270.7	264.2	259.0	256.3	253.7	252.4	252.4	252.4	253.7
70°	234.1	234.1	230.2	226.3	221.0	222.3	218.4	214.5	214.5	211.9	213.2
72.5°	194.9	193.6	189.6	188.3	184.4	180.5	177.9	180.5	176.6	175.2	176.6
75°	156.9	155.6	153.0	150.4	151.7	147.8	143.9	142.6	142.6	139.9	139.9
77.5°	120.3	122.9	117.7	116.4	113.8	111.2	109.9	108.5	108.5	108.5	111.2
80°	83.7	85.0	85.0	82.4	83.7	79.8	79.8	79.8	75.9	77.2	78.5
82.5°	53.6	53.6	52.3	53.6	52.3	52.3	51.0	51.0	49.7	49.7	51.0
85°	30.1	28.8	27.5	30.1	28.8	28.8	27.5	27.5	27.5	27.5	27.5
87.5°	6.5	7.8	7.8	7.8	7.8	9.2	9.2	9.2	10.5	10.5	10.5
90°	32.5	33.0	33.4	33.9	34.3	29.5	24.7	19.9	15.1	12.7	11.4
92.5°	31.2	31.0	30.8	30.6	30.4	30.2	30.0	29.7	29.5	29.4	28.5
95°	62.7	62.7	62.7	62.7	62.7	62.3	61.8	61.4	60.9	60.7	59.6
97.5°	97.9	97.9	97.9	97.9	97.9	97.0	96.2	95.3	94.4	94.0	93.0
100°	135.2	135.2	135.2	135.2	135.2	134.5	133.9	133.2	132.5	132.2	131.3
102.5°	176.2	176.0	175.7	175.5	175.3	174.4	173.6	172.7	171.8	171.4	170.7
105°	217.2	216.8	216.3	215.9	215.5	215.1	214.6	214.2	213.7	213.5	213.2
107.5°	260.4	260.2	259.9	259.7	259.5	259.5	259.5	259.5	259.5	259.5	259.1
110°	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6	304.6	303.9

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	348.0	348.7	349.3	350.0	350.6	350.8	351.0	351.3	351.5	351.6	350.9
115°	394.8	395.0	395.3	395.5	395.7	396.1	396.5	397.0	397.4	397.6	396.9
117.5°	438.1	438.8	439.4	440.1	440.7	441.8	442.9	444.0	445.1	445.6	444.7
120°	483.8	483.8	483.8	483.8	483.8	485.5	487.3	489.0	490.7	491.6	490.7
122.5°	528.2	528.9	529.5	530.2	530.8	531.9	533.0	534.1	535.2	535.7	534.6
125°	573.2	573.9	574.6	575.2	575.9	576.5	577.2	577.8	578.5	578.8	577.8
127.5°	616.4	617.3	618.2	619.0	619.9	620.8	621.7	622.6	623.5	623.9	622.7
130°	662.3	662.7	663.2	663.6	664.0	664.4	664.9	665.3	665.8	666.0	664.6
132.5°	704.7	705.8	706.9	708.0	709.1	708.9	708.7	708.4	708.2	708.1	707.0
135°	749.3	749.5	749.8	750.0	750.2	749.8	749.3	748.9	748.4	748.2	747.0
137.5°	790.5	790.7	790.9	791.1	791.3	790.9	790.5	790.0	789.6	789.4	788.4
140°	832.5	832.5	832.5	832.5	832.5	831.4	830.3	829.2	828.1	827.6	826.6
142.5°	870.6	870.4	870.1	869.9	869.7	869.0	868.4	867.7	867.0	866.7	865.7
145°	908.8	908.6	908.3	908.1	907.9	906.6	905.3	904.0	902.7	902.0	901.2
147.5°	942.9	942.5	942.0	941.6	941.2	940.3	939.5	938.6	937.7	937.3	936.3
150°	975.2	974.5	973.8	973.2	972.5	971.6	970.8	969.9	969.0	968.6	967.9
152.5°	1007.4	1006.5	1005.6	1004.8	1003.9	1002.8	1001.7	1000.6	999.5	999.0	998.3
155°	1033.7	1032.6	1031.5	1030.4	1029.3	1028.7	1028.0	1027.4	1026.7	1026.4	1026.1
157.5°	1059.9	1058.4	1056.9	1055.3	1053.8	1053.4	1052.9	1052.5	1052.0	1051.8	1051.6
160°	1081.5	1080.2	1078.9	1077.6	1076.3	1076.1	1075.9	1075.7	1075.5	1075.4	1075.2
162.5°	1102.0	1100.5	1099.0	1097.4	1095.9	1095.7	1095.5	1095.2	1095.0	1094.9	1094.9
165°	1118.6	1117.1	1115.6	1114.1	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.7
167.5°	1133.3	1131.8	1130.3	1128.8	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3	1127.6
170°	1145.1	1143.6	1142.1	1140.5	1139.0	1139.2	1139.4	1139.7	1139.9	1140.0	1140.3
172.5°	1153.9	1152.4	1150.9	1149.3	1147.8	1148.0	1148.2	1148.5	1148.7	1148.8	1149.1
175°	1159.8	1158.3	1156.8	1155.2	1153.7	1154.1	1154.6	1155.0	1155.5	1155.7	1156.0
177.5°	1162.8	1161.5	1160.2	1158.9	1157.6	1158.0	1158.5	1158.9	1159.4	1159.6	1159.9
180°	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1701.5	1701.5	1701.5	1701.5
2.5°	1670.1	1670.1	1689.7	1710.6
5°	1633.5	1642.6	1674.0	1702.8
7.5°	1598.2	1613.9	1653.1	1689.7
10°	1555.0	1575.9	1624.3	1667.5
12.5°	1513.2	1532.8	1589.0	1637.4
15°	1454.3	1479.2	1539.3	1599.5
17.5°	1395.5	1420.3	1493.5	1564.2
20°	1326.1	1358.8	1441.2	1535.4
22.5°	1262.1	1302.6	1394.1	1470.0
25°	1191.4	1254.2	1339.2	1437.3
27.5°	1128.7	1191.4	1277.8	1377.1
30°	1058.0	1122.1	1211.1	1302.6
32.5°	990.0	1048.9	1135.2	1247.7
35°	919.4	975.6	1059.3	1173.1
37.5°	855.3	910.3	1001.8	1106.4
40°	792.5	850.1	928.6	1033.2
42.5°	733.7	784.7	855.3	959.9
45°	680.1	716.7	782.1	880.2
47.5°	623.8	656.5	716.7	814.8
50°	571.5	599.0	651.3	742.8
52.5°	520.5	544.1	592.4	665.7
55°	474.7	497.0	532.3	604.2
57.5°	427.7	444.7	478.7	536.2
60°	381.9	397.6	425.0	472.1
62.5°	336.1	349.2	375.3	413.3
65°	295.6	306.0	325.6	358.3
67.5°	256.3	262.9	278.6	304.7
70°	218.4	223.6	236.7	257.6
72.5°	177.9	183.1	197.5	211.9
75°	143.9	145.2	155.6	167.4
77.5°	112.5	111.2	119.0	128.2
80°	77.2	81.1	87.6	91.5
82.5°	52.3	53.6	56.2	58.9
85°	28.8	30.1	30.1	34.0
87.5°	11.8	13.1	13.1	14.4
90°	8.8	6.2	3.6	1.0
92.5°	26.8	25.0	23.3	21.5
95°	57.4	55.3	53.1	50.9
97.5°	91.1	89.1	87.2	85.2
100°	129.6	127.9	126.1	124.4
102.5°	169.4	168.1	166.8	165.5
105°	212.5	211.9	211.2	210.6
107.5°	258.2	257.3	256.5	255.6
110°	302.6	301.3	300.0	298.7



TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	349.6	348.3	347.0	345.7
115°	395.6	394.3	393.0	391.7
117.5°	443.0	441.3	439.5	437.8
120°	489.0	487.3	485.5	483.8
122.5°	532.4	530.3	528.1	525.9
125°	575.9	573.9	572.0	570.0
127.5°	620.3	617.9	615.5	613.1
130°	661.7	658.9	656.0	653.2
132.5°	704.8	702.7	700.5	698.3
135°	744.6	742.3	739.9	737.5
137.5°	786.5	784.5	782.6	780.6
140°	824.7	822.7	820.8	818.8
142.5°	863.8	861.8	859.9	857.9
145°	899.7	898.2	896.6	895.1
147.5°	934.3	932.4	930.4	928.4
150°	966.6	965.3	964.0	962.7
152.5°	997.0	995.7	994.4	993.1
155°	1025.4	1024.7	1024.1	1023.4
157.5°	1051.2	1050.7	1050.3	1049.9
160°	1074.7	1074.3	1073.8	1073.4
162.5°	1094.9	1094.9	1094.9	1094.9
165°	1112.9	1113.1	1113.3	1113.5
167.5°	1128.3	1128.9	1129.6	1130.2
170°	1141.0	1141.6	1142.3	1142.9
172.5°	1149.8	1150.4	1151.1	1151.7
175°	1156.7	1157.3	1158.0	1158.6
177.5°	1160.6	1161.2	1161.9	1162.5
180°	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P999210

CATALOG NUMBER: SA2XXDIP-B865D925UB27-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.62	18.48	18.55	19.42	20.65	15.11	15.97	16.05	16.92	18.14
	3H	18.43	19.20	19.38	20.15	21.40	16.46	17.23	17.40	18.18	19.43
	4H	18.60	19.33	19.56	20.29	21.54	16.92	17.65	17.88	18.61	19.86
	6H	18.65	19.31	19.62	20.28	21.54	17.23	17.90	18.20	18.86	20.13
	8H	18.63	19.26	19.60	20.24	21.51	17.31	17.95	18.29	18.93	20.19
	12H	18.59	19.19	19.57	20.17	21.45	17.35	17.96	18.33	18.93	20.22
4H	2H	17.66	18.39	18.63	19.35	20.60	15.56	16.29	16.52	17.24	18.50
	3H	18.64	19.25	19.62	20.23	21.50	17.02	17.62	17.99	18.61	19.88
	4H	18.92	19.47	19.90	20.45	21.74	17.55	18.11	18.54	19.09	20.38
	6H	19.05	19.52	20.04	20.53	21.82	17.93	18.41	18.93	19.41	20.70
	8H	19.05	19.49	20.04	20.49	21.79	18.04	18.49	19.04	19.49	20.79
	12H	19.01	19.41	20.03	20.43	21.73	18.10	18.50	19.11	19.51	20.82
8H	4H	18.93	19.37	19.92	20.37	21.67	17.70	18.14	18.69	19.14	20.44
	6H	19.11	19.47	20.13	20.51	21.81	18.13	18.50	19.15	19.54	20.84
	8H	19.14	19.46	20.17	20.49	21.81	18.28	18.60	19.31	19.63	20.95
	12H	19.12	19.40	20.15	20.43	21.79	18.37	18.66	19.41	19.68	21.04
12H	4H	18.89	19.28	19.90	20.30	21.61	17.67	18.07	18.68	19.08	20.39
	6H	19.09	19.41	20.11	20.43	21.76	18.13	18.45	19.16	19.48	20.80
	8H	19.12	19.40	20.15	20.42	21.79	18.29	18.57	19.32	19.59	20.96