

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998082

Luminaire Tested: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998082
REPORT IS A COMBINATION OF REPORTS P983819 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5075.0 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	29	29	28
2	84	77	72	67	75	69	64	60	54	50	48	39	37	36	26	25	24
3	77	68	61	56	68	61	55	51	47	44	40	35	32	30	23	22	21
4	70	60	53	47	63	54	48	43	42	38	34	31	28	26	21	19	18
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	17	16
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	16	14
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	15	13	11
9	47	36	29	24	42	32	26	22	26	21	18	19	16	14	14	12	10
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9026	9026	9026	9026
5°	9047	9623	9082	7656
10°	8942	10506	8998	6312
15°	8725	11080	8846	5317
20°	8589	10405	8589	4622
25°	8316	8938	8353	4132
30°	7865	7027	8014	3744
35°	7466	4859	7591	3424
40°	7007	3669	7088	3171
45°	6443	3015	6548	2896
50°	5952	2646	5964	2652
55°	5396	2254	5430	2386
60°	4801	1883	4867	2082
65°	4269	1532	4348	1779
70°	3737	1201	3833	1435
75°	3138	873	3261	1039
80°	2451	553	2627	618
85°	1610	277	1737	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9330 cd/sqm

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	1.1
10°-20°	158.1	3.1
20°-30°	229.4	4.5
30°-40°	241.8	4.8
40°-50°	214.0	4.2
50°-60°	170.9	3.4
60°-70°	116.1	2.3
70°-80°	59.4	1.2
80°-90°	17.9	0.4
90°-100°	84.4	1.7
100°-110°	268.2	5.3
110°-120°	458.9	9.0
120°-130°	603.6	11.9
130°-140°	677.5	13.3
140°-150°	664.4	13.1
150°-160°	557.3	11.0
160°-170°	369.6	7.3
170°-180°	129.2	2.5
0°-30°	441.8	8.7
0°-40°	683.6	13.5
0°-60°	1068.5	21.1
0°-90°	1261.9	24.9
90°-120°	811.5	16.0
90°-150°	2757.0	54.3
90°-180°	3813.0	75.1
0°-180°	5075.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	570	570	570	570	570	
5°	571	637	573	507	571	54
15°	536	783	543	376	536	151
25°	482	652	484	302	482	220
35°	393	355	400	250	393	246
45°	295	214	300	206	295	229
55°	202	150	204	159	202	181
65°	120	92	122	107	120	119
75°	56	46	58	54	56	60
85°	11	12	12	9	11	13
90°	1	39	1	39	1	4
95°	60	71	60	71	60	67
105°	248	256	248	256	248	261
115°	460	460	460	460	460	455
125°	670	672	670	672	670	599
135°	867	877	867	877	867	670
145°	1052	1064	1052	1064	1052	657
155°	1203	1212	1203	1212	1203	554
165°	1309	1310	1309	1310	1309	369
175°	1362	1357	1362	1357	1362	129
180°	1364	1364	1364	1364	1364	

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	573.3	574.6	576.8	577.2	581.6	585.1	589.0	589.0	590.3	589.9	586.4
5°	570.6	574.6	580.3	585.1	593.0	596.5	601.7	605.7	609.2	611.8	611.4
7.5°	566.2	573.3	581.6	590.8	601.3	607.4	614.9	621.9	626.7	631.1	634.2
10°	558.8	570.6	582.0	594.3	607.9	616.2	625.0	634.2	641.6	649.9	657.8
12.5°	548.7	565.8	579.8	596.0	612.7	621.9	635.9	642.9	657.4	678.4	684.1
15°	536.0	559.2	572.4	593.0	614.9	622.3	641.6	653.0	682.8	696.0	711.7
17.5°	524.2	550.0	567.6	591.2	612.7	627.2	646.0	669.2	694.2	713.1	730.6
20°	514.5	539.5	560.5	586.8	614.0	632.4	652.1	680.2	707.4	726.6	740.2
22.5°	492.6	524.6	549.1	578.5	611.4	636.8	655.6	686.3	715.7	727.5	739.4
25°	481.7	509.3	537.8	571.1	609.6	639.9	656.1	690.3	716.1	720.5	723.1
27.5°	461.5	492.6	525.9	564.0	609.2	634.6	655.2	686.3	706.9	703.9	696.0
30°	436.5	474.6	511.5	552.7	603.1	630.7	649.9	678.4	689.0	673.2	659.2
32.5°	418.1	454.0	494.8	542.6	596.0	622.3	641.2	663.5	665.7	637.2	613.6
35°	393.1	433.0	479.0	529.4	584.2	607.9	625.4	639.0	628.5	588.6	560.5
37.5°	370.8	410.2	459.3	510.6	568.0	591.2	605.2	607.4	581.6	546.5	505.3
40°	346.2	387.0	438.3	492.2	550.0	570.2	578.9	572.4	535.1	494.4	446.6
42.5°	321.7	362.0	417.2	472.5	527.2	544.3	547.8	529.9	484.3	436.5	381.3
45°	295.0	337.0	392.2	447.9	500.9	510.6	511.0	485.2	431.3	381.3	330.0
47.5°	273.0	312.0	366.8	422.5	467.2	473.8	471.1	441.3	382.6	326.5	281.8
50°	248.9	286.2	340.5	395.3	433.4	435.2	428.6	386.1	328.7	277.4	241.9
52.5°	223.1	260.8	310.7	363.3	397.5	394.9	382.2	336.6	282.7	240.2	213.0
55°	202.5	235.8	282.7	334.0	358.1	350.6	336.6	290.1	247.6	211.7	188.0
57.5°	179.7	209.1	255.1	299.8	313.8	306.8	292.8	249.4	209.9	182.8	167.0
60°	158.2	184.9	225.3	262.5	273.5	266.0	249.8	210.8	182.3	159.5	147.7
62.5°	138.5	161.7	195.5	229.7	234.0	226.6	212.6	181.0	156.5	138.5	129.7
65°	120.1	142.0	169.2	195.0	199.0	191.1	176.6	153.8	133.2	121.8	113.5
67.5°	102.1	119.6	143.8	162.6	164.8	157.3	145.5	127.1	114.4	102.1	96.0
70°	86.3	99.5	118.3	133.7	134.5	127.5	121.4	104.7	95.1	86.3	81.5
72.5°	71.0	80.2	94.7	106.1	106.5	102.1	96.4	85.9	77.6	71.4	66.6
75°	56.1	64.0	72.8	82.8	82.4	78.9	74.5	67.9	60.9	57.0	54.8
77.5°	43.0	47.8	54.8	61.4	61.4	59.6	57.0	52.2	47.8	43.8	41.6
80°	30.7	33.7	39.4	41.6	42.5	42.1	39.9	36.4	34.6	31.6	30.7
82.5°	19.7	21.9	24.5	26.7	28.0	27.2	26.7	25.0	22.4	21.5	20.6
85°	11.4	12.3	13.6	14.9	15.3	14.9	15.8	14.5	13.1	13.1	12.7
87.5°	4.8	5.3	6.1	6.1	6.6	6.6	6.1	6.6	6.6	6.1	5.7
90°	1.2	4.3	7.3	10.4	13.5	15.0	17.8	23.4	29.1	34.7	40.3
92.5°	25.3	27.3	29.4	31.4	33.5	34.5	34.6	34.9	35.2	35.4	35.7
95°	59.8	62.4	65.0	67.5	70.1	71.4	71.7	72.2	72.7	73.2	73.7
97.5°	100.1	102.4	104.7	107.0	109.3	110.5	111.0	112.0	113.1	114.1	115.1
100°	146.2	148.2	150.3	152.3	154.4	155.4	155.8	156.5	157.3	158.0	158.8
102.5°	194.5	196.0	197.6	199.1	200.6	201.4	201.9	202.9	204.0	205.0	206.0
105°	247.5	248.3	249.0	249.8	250.5	250.9	251.2	251.7	252.2	252.7	253.2
107.5°	300.4	301.4	302.4	303.5	304.5	305.0	305.0	305.0	305.0	305.0	305.0
110°	351.0	352.5	354.1	355.6	357.1	357.9	357.9	357.9	357.9	357.9	357.9

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	406.3	407.8	409.4	410.9	412.4	413.2	413.1	412.8	412.5	412.3	412.0
115°	460.4	461.9	463.5	465.0	466.5	467.3	467.0	466.5	466.0	465.5	465.0
117.5°	514.5	516.5	518.6	520.6	522.7	523.7	523.1	521.8	520.5	519.2	517.9
120°	568.6	570.6	572.7	574.7	576.8	577.8	576.8	574.7	572.7	570.6	568.6
122.5°	618.1	620.7	623.2	625.8	628.3	629.6	629.0	627.7	626.4	625.1	623.8
125°	669.8	672.1	674.4	676.7	679.0	680.2	679.8	679.1	678.3	677.6	676.8
127.5°	720.5	723.3	726.1	729.0	731.8	733.2	732.7	731.6	730.6	729.5	728.5
130°	767.7	771.0	774.3	777.6	780.9	782.6	782.3	781.8	781.3	780.8	780.3
132.5°	820.6	823.2	825.7	828.3	830.8	832.1	832.2	832.5	832.8	833.0	833.3
135°	866.7	869.5	872.3	875.1	877.9	879.3	879.6	880.1	880.6	881.1	881.6
137.5°	917.3	919.6	921.9	924.2	926.5	927.7	928.0	928.5	929.0	929.5	930.0
140°	962.2	964.5	966.8	969.1	971.4	972.5	973.1	974.4	975.7	977.0	978.3
142.5°	1008.2	1010.5	1012.8	1015.1	1017.4	1018.6	1019.0	1019.7	1020.5	1021.2	1022.0
145°	1052.0	1053.8	1055.6	1057.3	1059.1	1060.0	1060.8	1062.3	1063.8	1065.4	1066.9
147.5°	1091.1	1093.4	1095.7	1098.0	1100.3	1101.5	1102.0	1103.0	1104.1	1105.1	1106.1
150°	1131.4	1132.9	1134.5	1136.0	1137.5	1138.3	1138.8	1139.8	1140.9	1141.9	1142.9
152.5°	1167.1	1168.6	1170.2	1171.7	1173.2	1174.0	1174.6	1175.9	1177.2	1178.4	1179.7
155°	1202.7	1203.5	1204.3	1205.0	1205.8	1206.2	1206.6	1207.3	1208.1	1208.8	1209.6
157.5°	1233.8	1234.3	1234.8	1235.3	1235.8	1236.1	1236.4	1236.9	1237.4	1237.9	1238.4
160°	1261.4	1261.9	1262.4	1262.9	1263.4	1263.7	1263.8	1264.1	1264.4	1264.6	1264.9
162.5°	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.9	1287.2	1287.4	1287.7	1287.9
165°	1308.6	1308.4	1308.1	1307.9	1307.6	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
167.5°	1328.2	1327.4	1326.6	1325.9	1325.1	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7
170°	1343.2	1342.4	1341.6	1340.9	1340.1	1339.7	1339.6	1339.3	1339.0	1338.8	1338.5
172.5°	1353.5	1352.7	1352.0	1351.2	1350.5	1350.1	1350.0	1349.7	1349.4	1349.2	1348.9
175°	1361.6	1360.8	1360.0	1359.3	1358.5	1358.1	1357.8	1357.3	1356.8	1356.3	1355.8
177.5°	1366.2	1365.4	1364.6	1363.9	1363.1	1362.7	1362.4	1361.9	1361.4	1360.9	1360.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	592.5	593.0	593.9	598.2	600.4	600.9	599.1	603.1	604.4	603.1	602.2
5°	620.6	623.2	628.5	634.2	633.7	634.2	636.8	639.4	640.3	636.8	638.1
7.5°	645.1	650.4	656.1	664.8	664.8	669.2	671.0	673.2	678.4	675.8	674.9
10°	673.2	680.2	690.7	704.7	705.2	709.6	713.9	720.9	723.1	721.4	722.3
12.5°	708.2	721.8	722.7	738.0	745.1	745.9	752.9	751.6	756.0	756.0	763.5
15°	723.6	744.6	756.4	771.3	775.7	770.5	776.2	782.3	782.7	782.7	782.3
17.5°	751.2	759.5	771.3	779.2	781.0	781.0	781.4	784.1	782.3	778.8	781.4
20°	756.9	760.4	764.8	763.9	764.8	760.4	756.0	751.6	752.1	749.9	756.4
22.5°	746.4	745.5	735.4	728.8	728.8	720.1	711.7	707.8	703.9	705.2	707.4
25°	720.1	706.5	694.2	684.6	682.4	668.4	657.0	653.5	646.9	652.1	653.0
27.5°	678.0	662.7	642.9	634.6	623.2	617.5	609.6	599.1	585.5	593.4	592.1
30°	632.9	610.1	593.9	573.7	555.7	554.4	539.5	522.0	515.0	515.0	518.9
32.5°	582.5	552.2	528.5	500.1	482.5	475.1	457.1	439.6	443.5	430.4	435.2
35°	523.7	483.8	454.0	426.4	413.3	404.5	381.3	371.6	361.1	355.0	366.4
37.5°	467.6	421.6	383.5	353.2	348.4	332.6	316.9	310.7	304.6	307.2	306.8
40°	399.3	358.5	324.3	300.7	292.3	284.9	274.4	266.9	263.0	265.2	265.6
42.5°	337.5	303.3	277.9	261.2	254.2	248.9	243.7	237.5	236.2	236.2	238.0
45°	289.7	261.6	244.6	231.0	227.0	223.1	219.1	216.5	215.6	213.9	215.2
47.5°	251.6	229.2	218.7	208.6	204.2	203.4	199.8	198.5	196.8	196.3	196.8
50°	219.6	205.5	195.9	190.2	187.1	185.8	184.1	181.4	180.6	182.8	181.9
52.5°	197.2	184.1	178.8	173.1	171.4	169.6	167.0	167.4	167.0	166.1	166.1
55°	174.9	166.5	161.3	156.9	156.5	154.7	152.5	151.6	151.2	150.3	151.6
57.5°	156.9	150.3	145.5	141.6	139.8	139.8	137.6	135.9	135.9	135.4	135.9
60°	138.9	132.4	129.3	125.3	124.0	123.6	122.3	121.4	120.1	120.1	120.1
62.5°	122.3	117.0	113.5	110.0	110.4	108.3	106.5	105.6	105.6	106.1	106.1
65°	106.5	103.0	98.6	95.5	94.7	94.2	93.4	92.9	91.6	92.5	92.5
67.5°	92.0	87.2	84.6	83.3	82.0	81.5	80.6	79.8	79.3	78.9	79.8
70°	77.6	73.6	71.4	70.6	69.2	68.8	68.4	67.1	67.5	67.9	68.4
72.5°	64.4	60.9	60.5	57.9	57.9	57.9	56.1	57.0	56.5	55.7	56.5
75°	50.8	49.1	48.2	46.9	47.3	46.9	46.5	45.1	45.1	45.6	46.0
77.5°	40.3	38.6	38.1	36.8	35.9	36.8	35.9	35.5	35.5	35.9	35.9
80°	29.8	28.9	27.6	27.6	27.6	27.2	27.2	27.2	26.7	26.3	26.7
82.5°	19.7	19.7	19.3	18.8	19.3	18.4	18.8	18.8	18.8	18.8	18.8
85°	12.7	12.3	12.3	11.8	11.8	11.8	12.3	11.4	11.4	11.8	11.8
87.5°	5.7	5.7	5.7	6.1	5.7	5.7	5.7	6.1	5.7	5.7	5.7
90°	39.8	39.3	38.8	38.3	38.0	38.1	38.4	38.6	38.9	39.1	38.9
92.5°	35.9	36.2	36.4	36.7	36.8	36.8	36.8	36.8	36.8	36.8	36.8
95°	73.7	73.7	73.7	73.7	73.7	73.4	72.9	72.4	71.9	71.4	71.9
97.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1
100°	158.8	158.8	158.8	158.8	158.8	158.7	158.4	158.2	157.9	157.7	157.9
102.5°	206.3	206.5	206.8	207.1	207.2	207.1	206.8	206.5	206.3	206.0	206.3
105°	253.7	254.2	254.7	255.2	255.5	255.5	255.5	255.5	255.5	255.5	255.5
107.5°	305.3	305.5	305.8	306.1	306.2	305.6	304.3	303.0	301.7	300.4	301.7
110°	357.9	357.9	357.9	357.9	357.9	357.5	356.8	356.0	355.3	354.5	355.3

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	411.2	410.5	409.7	409.0	408.6	408.3	407.8	407.3	406.8	406.3	406.8
115°	464.7	464.5	464.2	463.9	463.8	463.4	462.7	461.9	461.2	460.4	461.2
117.5°	517.1	516.4	515.6	514.9	514.5	514.1	513.3	512.6	511.8	511.0	511.8
120°	568.6	568.6	568.6	568.6	568.6	568.2	567.4	566.7	565.9	565.1	565.9
122.5°	623.0	622.3	621.5	620.8	620.4	620.1	619.6	619.1	618.6	618.1	618.6
125°	676.0	675.2	674.5	673.7	673.3	673.2	672.9	672.7	672.4	672.2	672.4
127.5°	727.5	726.5	725.4	724.4	723.9	723.5	722.8	722.0	721.3	720.5	721.3
130°	779.8	779.3	778.8	778.3	778.0	777.5	776.5	775.4	774.4	773.4	774.4
132.5°	832.0	830.7	829.4	828.1	827.5	827.1	826.4	825.6	824.9	824.1	824.9
135°	881.4	881.1	880.9	880.6	880.5	880.1	879.3	878.6	877.8	877.0	877.8
137.5°	929.7	929.5	929.2	928.9	928.8	928.3	927.3	926.2	925.2	924.2	925.2
140°	978.3	978.3	978.3	978.3	978.3	977.8	976.8	975.7	974.7	973.7	974.7
142.5°	1022.3	1022.5	1022.8	1023.1	1023.2	1022.7	1021.7	1020.6	1019.6	1018.6	1019.6
145°	1067.2	1067.4	1067.7	1068.0	1068.1	1067.6	1066.6	1065.5	1064.5	1063.5	1064.5
147.5°	1106.6	1107.1	1107.6	1108.1	1108.4	1107.9	1106.9	1105.8	1104.8	1103.8	1104.8
150°	1143.7	1144.4	1145.2	1145.9	1146.3	1145.9	1145.2	1144.4	1143.7	1142.9	1143.7
152.5°	1180.7	1181.7	1182.8	1183.8	1184.3	1183.8	1182.8	1181.7	1180.7	1179.7	1180.7
155°	1210.9	1212.2	1213.5	1214.8	1215.4	1215.0	1214.2	1213.5	1212.7	1211.9	1212.7
157.5°	1240.2	1242.0	1243.8	1245.6	1246.5	1245.9	1244.6	1243.3	1242.0	1240.7	1242.0
160°	1266.4	1268.0	1269.5	1271.0	1271.8	1271.3	1270.3	1269.2	1268.2	1267.2	1268.2
162.5°	1289.7	1291.5	1293.3	1295.1	1296.0	1295.4	1294.1	1292.8	1291.5	1290.2	1291.5
165°	1309.3	1311.1	1312.8	1314.6	1315.5	1314.9	1313.6	1312.3	1311.1	1309.8	1311.1
167.5°	1326.5	1328.3	1330.1	1331.9	1332.8	1332.2	1330.9	1329.6	1328.3	1327.0	1328.3
170°	1340.3	1342.1	1343.9	1345.7	1346.6	1345.8	1344.3	1342.8	1341.2	1339.7	1341.2
172.5°	1350.7	1352.5	1354.3	1356.1	1357.0	1356.2	1354.7	1353.2	1351.6	1350.1	1351.6
175°	1357.6	1359.4	1361.2	1363.0	1363.9	1363.1	1361.6	1360.1	1358.5	1357.0	1358.5
177.5°	1361.9	1363.5	1365.0	1366.5	1367.3	1366.5	1365.0	1363.5	1361.9	1360.4	1361.9
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	604.4	601.3	598.7	599.1	601.3	599.5	595.2	589.5	587.3	584.6	587.3
5°	640.7	638.1	632.9	633.3	632.0	630.2	623.2	614.4	614.4	607.4	606.6
7.5°	676.7	672.7	669.2	668.4	663.5	660.0	653.9	641.6	636.8	628.5	623.7
10°	717.0	713.9	710.0	705.2	702.5	696.4	686.3	668.4	659.6	648.2	639.9
12.5°	757.8	757.3	748.6	738.9	738.5	728.8	721.8	697.7	685.9	670.5	650.8
15°	783.6	781.4	776.6	771.8	773.1	762.6	746.8	718.3	710.4	692.0	671.0
17.5°	783.2	783.2	781.9	781.0	779.7	776.6	767.8	749.0	736.3	713.1	693.3
20°	758.2	763.9	765.2	764.8	769.2	771.3	770.9	759.1	749.0	728.4	708.2
22.5°	708.2	721.4	727.1	730.6	739.8	744.6	756.0	751.6	749.0	733.7	716.6
25°	661.8	666.2	683.3	684.1	696.8	708.7	720.1	727.5	737.2	731.5	717.0
27.5°	601.7	611.8	624.1	633.3	635.9	660.0	678.9	692.9	714.8	716.6	711.7
30°	533.8	538.6	558.8	571.1	585.1	602.6	629.8	653.9	673.6	691.6	697.7
32.5°	451.0	470.7	482.5	497.4	509.7	540.8	574.1	605.2	628.0	658.3	671.4
35°	375.2	390.5	410.7	416.8	439.1	465.4	508.8	548.7	583.3	614.0	640.7
37.5°	312.5	324.8	346.2	355.9	369.0	402.8	439.1	488.7	530.3	568.0	601.3
40°	269.5	278.7	295.0	298.0	309.0	339.7	369.0	415.5	470.7	521.5	557.9
42.5°	240.2	244.6	255.5	259.5	266.5	287.1	313.4	357.2	408.5	461.1	512.3
45°	219.1	222.2	228.8	232.3	241.0	250.2	271.7	306.8	347.1	400.1	455.4
47.5°	200.3	204.2	206.9	209.1	213.9	224.0	238.0	263.8	302.4	351.1	404.5
50°	184.5	185.8	190.6	191.1	194.2	200.7	213.9	229.7	260.3	299.8	351.5
52.5°	168.7	170.0	173.1	176.2	177.5	182.8	191.5	204.7	227.5	258.6	304.6
55°	153.0	154.7	157.8	160.0	161.3	165.7	170.9	183.6	201.6	223.5	261.2
57.5°	137.2	141.1	142.0	143.3	145.5	150.3	155.1	162.6	176.6	196.8	224.4
60°	122.3	123.6	126.7	128.0	130.2	132.8	138.9	144.6	154.7	170.5	195.5
62.5°	106.9	110.0	111.3	112.6	114.4	117.5	121.4	127.5	136.3	149.0	168.7
65°	93.8	94.2	96.9	98.6	100.4	102.6	106.5	112.2	117.5	129.3	143.8
67.5°	81.1	82.0	82.8	84.6	86.8	89.0	92.5	95.5	102.1	110.0	121.4
70°	68.8	68.8	71.0	72.3	71.9	74.5	77.1	80.6	85.5	92.9	102.1
72.5°	57.9	57.4	59.2	59.6	60.5	62.2	64.0	67.5	70.1	75.8	82.8
75°	46.0	46.9	47.8	47.8	49.1	50.4	52.2	53.9	57.0	60.5	65.7
77.5°	36.4	36.4	37.3	37.7	39.0	38.6	40.3	42.1	44.3	47.3	51.3
80°	26.7	27.6	27.6	27.6	28.0	28.5	30.2	31.6	32.9	35.1	36.8
82.5°	18.8	18.8	19.7	19.7	19.7	20.6	20.6	21.0	21.9	23.2	24.5
85°	11.8	11.8	11.8	12.3	11.8	12.3	13.1	12.7	13.1	14.0	14.0
87.5°	5.7	5.7	5.7	5.7	5.7	6.1	5.7	6.1	6.6	6.6	6.6
90°	38.6	38.4	38.1	38.0	38.3	38.8	39.3	39.8	40.3	34.7	29.1
92.5°	36.8	36.8	36.8	36.8	36.7	36.4	36.2	35.9	35.7	35.4	35.2
95°	72.4	72.9	73.4	73.7	73.7	73.7	73.7	73.7	73.7	73.2	72.7
97.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	114.1	113.1
100°	158.2	158.4	158.7	158.8	158.8	158.8	158.8	158.8	158.8	158.0	157.3
102.5°	206.5	206.8	207.1	207.2	207.1	206.8	206.5	206.3	206.0	205.0	204.0
105°	255.5	255.5	255.5	255.5	255.2	254.7	254.2	253.7	253.2	252.7	252.2
107.5°	303.0	304.3	305.6	306.2	306.1	305.8	305.5	305.3	305.0	305.0	305.0
110°	356.0	356.8	357.5	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	407.3	407.8	408.3	408.6	409.0	409.7	410.5	411.2	412.0	412.3	412.5
115°	461.9	462.7	463.4	463.8	463.9	464.2	464.5	464.7	465.0	465.5	466.0
117.5°	512.6	513.3	514.1	514.5	514.9	515.6	516.4	517.1	517.9	519.2	520.5
120°	566.7	567.4	568.2	568.6	568.6	568.6	568.6	568.6	568.6	570.6	572.7
122.5°	619.1	619.6	620.1	620.4	620.8	621.5	622.3	623.0	623.8	625.1	626.4
125°	672.7	672.9	673.2	673.3	673.7	674.5	675.2	676.0	676.8	677.6	678.3
127.5°	722.0	722.8	723.5	723.9	724.4	725.4	726.5	727.5	728.5	729.5	730.6
130°	775.4	776.5	777.5	778.0	778.3	778.8	779.3	779.8	780.3	780.8	781.3
132.5°	825.6	826.4	827.1	827.5	828.1	829.4	830.7	832.0	833.3	833.0	832.8
135°	878.6	879.3	880.1	880.5	880.6	880.9	881.1	881.4	881.6	881.1	880.6
137.5°	926.2	927.3	928.3	928.8	928.9	929.2	929.5	929.7	930.0	929.5	929.0
140°	975.7	976.8	977.8	978.3	978.3	978.3	978.3	978.3	978.3	977.0	975.7
142.5°	1020.6	1021.7	1022.7	1023.2	1023.1	1022.8	1022.5	1022.3	1022.0	1021.2	1020.5
145°	1065.5	1066.6	1067.6	1068.1	1068.0	1067.7	1067.4	1067.2	1066.9	1065.4	1063.8
147.5°	1105.8	1106.9	1107.9	1108.4	1108.1	1107.6	1107.1	1106.6	1106.1	1105.1	1104.1
150°	1144.4	1145.2	1145.9	1146.3	1145.9	1145.2	1144.4	1143.7	1142.9	1141.9	1140.9
152.5°	1181.7	1182.8	1183.8	1184.3	1183.8	1182.8	1181.7	1180.7	1179.7	1178.4	1177.2
155°	1213.5	1214.2	1215.0	1215.4	1214.8	1213.5	1212.2	1210.9	1209.6	1208.8	1208.1
157.5°	1243.3	1244.6	1245.9	1246.5	1245.6	1243.8	1242.0	1240.2	1238.4	1237.9	1237.4
160°	1269.2	1270.3	1271.3	1271.8	1271.0	1269.5	1268.0	1266.4	1264.9	1264.6	1264.4
162.5°	1292.8	1294.1	1295.4	1296.0	1295.1	1293.3	1291.5	1289.7	1287.9	1287.7	1287.4
165°	1312.3	1313.6	1314.9	1315.5	1314.6	1312.8	1311.1	1309.3	1307.5	1307.5	1307.5
167.5°	1329.6	1330.9	1332.2	1332.8	1331.9	1330.1	1328.3	1326.5	1324.7	1324.7	1324.7
170°	1342.8	1344.3	1345.8	1346.6	1345.7	1343.9	1342.1	1340.3	1338.5	1338.8	1339.0
172.5°	1353.2	1354.7	1356.2	1357.0	1356.1	1354.3	1352.5	1350.7	1348.9	1349.2	1349.4
175°	1360.1	1361.6	1363.1	1363.9	1363.0	1361.2	1359.4	1357.6	1355.8	1356.3	1356.8
177.5°	1363.5	1365.0	1366.5	1367.3	1366.5	1365.0	1363.5	1361.9	1360.4	1360.9	1361.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	585.1	582.9	581.6	582.5	579.8	573.3	573.3	575.4	572.8	570.2	566.2
5°	601.3	596.9	594.3	593.9	587.7	577.2	575.0	572.8	567.1	561.0	554.4
7.5°	617.1	609.2	604.8	601.7	593.0	579.4	573.7	568.9	559.7	550.5	542.1
10°	630.2	618.8	613.6	608.8	597.4	580.3	571.1	562.3	550.5	538.6	528.1
12.5°	640.7	627.6	621.0	614.0	600.0	577.6	566.2	552.2	540.4	524.6	514.1
15°	658.3	631.1	625.0	618.4	603.9	573.3	559.2	543.4	527.2	506.2	494.8
17.5°	672.3	635.9	635.5	621.5	602.6	571.5	550.0	529.4	511.9	490.9	472.9
20°	680.6	643.4	636.4	621.9	598.2	559.7	537.3	514.5	495.7	470.3	452.3
22.5°	687.6	653.9	635.5	618.0	589.0	555.7	522.9	501.4	475.5	447.9	430.8
25°	690.3	656.1	636.8	616.6	582.5	544.3	507.1	483.8	454.9	429.9	406.7
27.5°	690.7	655.6	632.0	610.9	573.3	529.4	491.3	466.8	434.8	405.8	382.6
30°	686.3	650.8	629.4	606.6	564.5	515.8	472.0	444.8	410.7	381.7	357.6
32.5°	673.2	641.2	623.7	598.7	553.1	497.0	453.6	423.4	387.4	358.9	335.7
35°	651.3	629.4	610.1	586.8	538.2	479.5	435.2	399.7	363.3	336.2	314.2
37.5°	624.1	612.3	594.3	571.5	521.1	463.7	414.6	375.2	338.8	312.5	291.0
40°	587.3	590.3	572.8	552.2	500.9	442.2	387.9	350.2	316.0	291.4	270.4
42.5°	547.4	560.1	550.0	530.3	478.6	418.5	368.1	326.5	293.2	267.8	250.2
45°	504.4	526.4	520.2	505.8	455.4	393.6	340.1	299.8	270.4	245.9	230.5
47.5°	457.5	488.7	488.7	478.1	429.5	368.6	316.0	274.8	245.9	228.3	213.4
50°	409.8	444.8	450.5	443.5	400.6	340.1	286.6	249.4	224.4	207.3	196.3
52.5°	359.8	400.6	411.1	407.6	369.9	312.9	262.5	226.1	203.4	188.5	178.8
55°	312.0	359.4	370.8	372.1	337.0	283.1	235.8	203.8	181.9	171.8	163.5
57.5°	266.9	312.5	325.2	327.4	303.7	255.9	210.8	182.8	163.0	154.7	148.1
60°	228.3	266.5	283.1	287.9	267.3	224.4	187.6	160.4	145.5	137.6	131.5
62.5°	196.8	227.5	245.0	246.3	237.1	196.8	163.5	140.7	128.0	121.0	117.9
65°	166.1	193.7	204.2	209.5	202.0	170.5	141.1	122.3	112.2	106.1	103.0
67.5°	141.6	159.1	167.9	174.9	167.4	143.8	120.1	104.7	97.3	91.2	89.4
70°	116.1	130.6	137.2	144.2	137.6	119.6	102.6	88.5	82.0	77.1	74.9
72.5°	92.9	104.3	110.4	114.8	110.9	96.0	82.0	72.3	67.5	64.0	62.7
75°	73.6	81.5	85.0	88.1	86.3	74.9	66.2	58.3	53.9	50.8	50.0
77.5°	56.1	61.8	65.7	66.6	64.4	57.0	49.5	44.7	41.2	39.4	38.6
80°	39.9	43.4	45.6	46.9	44.7	41.6	36.4	32.9	29.8	27.6	27.2
82.5°	26.7	28.5	30.2	29.8	28.9	26.3	23.2	21.5	20.2	18.4	18.4
85°	15.3	15.8	16.7	17.1	16.7	14.9	13.1	12.3	11.4	10.1	10.1
87.5°	6.6	7.0	7.0	7.5	6.6	6.6	5.7	4.8	4.8	4.4	3.9
90°	23.4	17.8	15.0	13.5	10.4	7.3	4.3	1.2	4.3	7.3	10.4
92.5°	34.9	34.6	34.5	33.5	31.4	29.4	27.3	25.3	27.3	29.4	31.4
95°	72.2	71.7	71.4	70.1	67.5	65.0	62.4	59.8	62.4	65.0	67.5
97.5°	112.0	111.0	110.5	109.3	107.0	104.7	102.4	100.1	102.4	104.7	107.0
100°	156.5	155.8	155.4	154.4	152.3	150.3	148.2	146.2	148.2	150.3	152.3
102.5°	202.9	201.9	201.4	200.6	199.1	197.6	196.0	194.5	196.0	197.6	199.1
105°	251.7	251.2	250.9	250.5	249.8	249.0	248.3	247.5	248.3	249.0	249.8
107.5°	305.0	305.0	305.0	304.5	303.5	302.4	301.4	300.4	301.4	302.4	303.5
110°	357.9	357.9	357.9	357.1	355.6	354.1	352.5	351.0	352.5	354.1	355.6

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	412.8	413.1	413.2	412.4	410.9	409.4	407.8	406.3	407.8	409.4	410.9
115°	466.5	467.0	467.3	466.5	465.0	463.5	461.9	460.4	461.9	463.5	465.0
117.5°	521.8	523.1	523.7	522.7	520.6	518.6	516.5	514.5	516.5	518.6	520.6
120°	574.7	576.8	577.8	576.8	574.7	572.7	570.6	568.6	570.6	572.7	574.7
122.5°	627.7	629.0	629.6	628.3	625.8	623.2	620.7	618.1	620.7	623.2	625.8
125°	679.1	679.8	680.2	679.0	676.7	674.4	672.1	669.8	672.1	674.4	676.7
127.5°	731.6	732.7	733.2	731.8	729.0	726.1	723.3	720.5	723.3	726.1	729.0
130°	781.8	782.3	782.6	780.9	777.6	774.3	771.0	767.7	771.0	774.3	777.6
132.5°	832.5	832.2	832.1	830.8	828.3	825.7	823.2	820.6	823.2	825.7	828.3
135°	880.1	879.6	879.3	877.9	875.1	872.3	869.5	866.7	869.5	872.3	875.1
137.5°	928.5	928.0	927.7	926.5	924.2	921.9	919.6	917.3	919.6	921.9	924.2
140°	974.4	973.1	972.5	971.4	969.1	966.8	964.5	962.2	964.5	966.8	969.1
142.5°	1019.7	1019.0	1018.6	1017.4	1015.1	1012.8	1010.5	1008.2	1010.5	1012.8	1015.1
145°	1062.3	1060.8	1060.0	1059.1	1057.3	1055.6	1053.8	1052.0	1053.8	1055.6	1057.3
147.5°	1103.0	1102.0	1101.5	1100.3	1098.0	1095.7	1093.4	1091.1	1093.4	1095.7	1098.0
150°	1139.8	1138.8	1138.3	1137.5	1136.0	1134.5	1132.9	1131.4	1132.9	1134.5	1136.0
152.5°	1175.9	1174.6	1174.0	1173.2	1171.7	1170.2	1168.6	1167.1	1168.6	1170.2	1171.7
155°	1207.3	1206.6	1206.2	1205.8	1205.0	1204.3	1203.5	1202.7	1203.5	1204.3	1205.0
157.5°	1236.9	1236.4	1236.1	1235.8	1235.3	1234.8	1234.3	1233.8	1234.3	1234.8	1235.3
160°	1264.1	1263.8	1263.7	1263.4	1262.9	1262.4	1261.9	1261.4	1261.9	1262.4	1262.9
162.5°	1287.2	1286.9	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8
165°	1307.5	1307.5	1307.5	1307.6	1307.9	1308.1	1308.4	1308.6	1308.4	1308.1	1307.9
167.5°	1324.7	1324.7	1324.7	1325.1	1325.9	1326.6	1327.4	1328.2	1327.4	1326.6	1325.9
170°	1339.3	1339.6	1339.7	1340.1	1340.9	1341.6	1342.4	1343.2	1342.4	1341.6	1340.9
172.5°	1349.7	1350.0	1350.1	1350.5	1351.2	1352.0	1352.7	1353.5	1352.7	1352.0	1351.2
175°	1357.3	1357.8	1358.1	1358.5	1359.3	1360.0	1360.8	1361.6	1360.8	1360.0	1359.3
177.5°	1361.9	1362.4	1362.7	1363.1	1363.9	1364.6	1365.4	1366.2	1365.4	1364.6	1363.9
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	564.0	566.2	565.8	561.4	556.6	552.7	545.2	546.1	543.4	543.9	546.5
5°	550.0	550.0	548.3	542.1	534.2	529.9	521.5	519.3	514.1	513.6	513.2
7.5°	535.1	532.9	530.7	522.0	512.3	505.3	493.9	491.3	486.0	482.5	480.8
10°	517.6	514.5	510.1	500.1	488.2	479.5	467.6	464.1	454.0	449.7	447.0
12.5°	498.3	496.6	489.5	481.2	461.9	452.3	435.2	438.7	428.6	419.9	418.5
15°	479.0	472.5	468.5	454.9	431.7	427.3	413.7	406.7	397.5	390.5	390.5
17.5°	460.2	450.1	441.3	426.9	409.8	397.5	387.4	383.9	372.5	365.5	364.2
20°	435.2	423.8	421.6	401.0	389.2	375.6	366.0	357.2	348.9	345.8	343.6
22.5°	411.5	398.4	394.9	377.3	365.5	351.9	342.3	336.2	330.0	327.8	323.9
25°	386.1	378.2	373.0	354.1	341.0	328.3	321.7	317.3	311.6	311.2	308.5
27.5°	361.6	354.1	348.9	330.9	321.2	309.4	304.2	299.3	296.3	295.0	293.6
30°	340.5	332.2	326.1	312.9	301.1	291.4	287.1	284.0	282.2	280.1	279.6
32.5°	317.3	312.5	304.2	294.1	284.9	275.7	273.0	270.8	268.2	267.3	266.9
35°	297.6	291.0	285.7	274.4	270.4	262.5	259.5	257.7	254.2	253.3	252.4
37.5°	278.3	272.2	266.5	259.5	252.0	247.6	245.9	243.2	241.5	241.9	241.0
40°	259.0	254.2	249.8	242.4	238.0	235.8	232.3	229.7	228.8	229.2	228.8
42.5°	240.2	235.8	233.2	227.5	223.1	220.9	218.7	216.1	217.4	217.4	218.7
45°	223.1	219.1	217.4	213.0	210.4	206.9	204.7	204.2	206.0	205.5	205.5
47.5°	205.5	204.2	202.0	198.1	194.6	192.4	192.0	192.0	193.7	194.6	194.2
50°	192.0	189.3	186.7	183.6	181.0	180.1	178.8	179.7	181.4	181.4	182.3
52.5°	174.9	173.1	172.2	169.6	167.9	167.9	167.9	168.3	169.6	170.9	170.5
55°	160.0	158.7	157.8	156.5	154.3	154.7	154.3	155.1	156.5	157.8	158.7
57.5°	144.2	143.8	142.9	140.7	140.7	140.2	141.6	142.0	144.2	145.1	146.4
60°	130.2	128.9	128.9	127.1	127.1	127.1	128.4	129.7	131.5	131.9	132.8
62.5°	115.3	115.3	114.8	113.5	113.5	114.8	115.3	117.0	117.9	117.9	119.2
65°	101.2	100.8	100.4	100.8	101.2	101.2	102.6	103.4	104.3	104.7	105.2
67.5°	87.2	86.8	87.7	87.2	88.1	89.8	89.4	90.7	92.0	92.0	92.5
70°	74.1	74.9	74.5	75.4	74.9	75.8	77.1	77.6	77.6	78.0	79.3
72.5°	61.8	61.8	61.8	61.4	61.8	62.7	63.5	64.0	64.9	65.3	66.6
75°	50.0	50.0	49.1	50.0	50.0	50.8	51.7	51.7	51.7	52.6	53.9
77.5°	37.7	38.1	37.7	38.6	38.6	39.0	39.9	39.4	40.3	40.8	41.2
80°	27.6	27.2	27.2	27.2	27.6	27.6	28.5	28.9	28.9	30.2	29.4
82.5°	17.5	18.0	17.5	18.0	18.0	18.4	18.0	18.4	18.8	19.7	19.3
85°	10.1	9.6	9.6	10.1	9.6	9.6	10.1	9.6	10.1	9.6	10.1
87.5°	3.9	3.5	3.5	3.5	3.5	3.1	3.1	2.6	2.6	2.6	2.2
90°	13.5	15.0	17.8	23.4	29.1	34.7	40.3	39.8	39.3	38.8	38.3
92.5°	33.5	34.5	34.6	34.9	35.2	35.4	35.7	35.9	36.2	36.4	36.7
95°	70.1	71.4	71.7	72.2	72.7	73.2	73.7	73.7	73.7	73.7	73.7
97.5°	109.3	110.5	111.0	112.0	113.1	114.1	115.1	115.1	115.1	115.1	115.1
100°	154.4	155.4	155.8	156.5	157.3	158.0	158.8	158.8	158.8	158.8	158.8
102.5°	200.6	201.4	201.9	202.9	204.0	205.0	206.0	206.3	206.5	206.8	207.1
105°	250.5	250.9	251.2	251.7	252.2	252.7	253.2	253.7	254.2	254.7	255.2
107.5°	304.5	305.0	305.0	305.0	305.0	305.0	305.0	305.3	305.5	305.8	306.1
110°	357.1	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	412.4	413.2	413.1	412.8	412.5	412.3	412.0	411.2	410.5	409.7	409.0
115°	466.5	467.3	467.0	466.5	466.0	465.5	465.0	464.7	464.5	464.2	463.9
117.5°	522.7	523.7	523.1	521.8	520.5	519.2	517.9	517.1	516.4	515.6	514.9
120°	576.8	577.8	576.8	574.7	572.7	570.6	568.6	568.6	568.6	568.6	568.6
122.5°	628.3	629.6	629.0	627.7	626.4	625.1	623.8	623.0	622.3	621.5	620.8
125°	679.0	680.2	679.8	679.1	678.3	677.6	676.8	676.0	675.2	674.5	673.7
127.5°	731.8	733.2	732.7	731.6	730.6	729.5	728.5	727.5	726.5	725.4	724.4
130°	780.9	782.6	782.3	781.8	781.3	780.8	780.3	779.8	779.3	778.8	778.3
132.5°	830.8	832.1	832.2	832.5	832.8	833.0	833.3	832.0	830.7	829.4	828.1
135°	877.9	879.3	879.6	880.1	880.6	881.1	881.6	881.4	881.1	880.9	880.6
137.5°	926.5	927.7	928.0	928.5	929.0	929.5	930.0	929.7	929.5	929.2	928.9
140°	971.4	972.5	973.1	974.4	975.7	977.0	978.3	978.3	978.3	978.3	978.3
142.5°	1017.4	1018.6	1019.0	1019.7	1020.5	1021.2	1022.0	1022.3	1022.5	1022.8	1023.1
145°	1059.1	1060.0	1060.8	1062.3	1063.8	1065.4	1066.9	1067.2	1067.4	1067.7	1068.0
147.5°	1100.3	1101.5	1102.0	1103.0	1104.1	1105.1	1106.1	1106.6	1107.1	1107.6	1108.1
150°	1137.5	1138.3	1138.8	1139.8	1140.9	1141.9	1142.9	1143.7	1144.4	1145.2	1145.9
152.5°	1173.2	1174.0	1174.6	1175.9	1177.2	1178.4	1179.7	1180.7	1181.7	1182.8	1183.8
155°	1205.8	1206.2	1206.6	1207.3	1208.1	1208.8	1209.6	1210.9	1212.2	1213.5	1214.8
157.5°	1235.8	1236.1	1236.4	1236.9	1237.4	1237.9	1238.4	1240.2	1242.0	1243.8	1245.6
160°	1263.4	1263.7	1263.8	1264.1	1264.4	1264.6	1264.9	1266.4	1268.0	1269.5	1271.0
162.5°	1286.8	1286.8	1286.9	1287.2	1287.4	1287.7	1287.9	1289.7	1291.5	1293.3	1295.1
165°	1307.6	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1309.3	1311.1	1312.8	1314.6
167.5°	1325.1	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1326.5	1328.3	1330.1	1331.9
170°	1340.1	1339.7	1339.6	1339.3	1339.0	1338.8	1338.5	1340.3	1342.1	1343.9	1345.7
172.5°	1350.5	1350.1	1350.0	1349.7	1349.4	1349.2	1348.9	1350.7	1352.5	1354.3	1356.1
175°	1358.5	1358.1	1357.8	1357.3	1356.8	1356.3	1355.8	1357.6	1359.4	1361.2	1363.0
177.5°	1363.1	1362.7	1362.4	1361.9	1361.4	1360.9	1360.4	1361.9	1363.5	1365.0	1366.5
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	543.4	544.8	541.7	540.8	541.7	538.6	539.5	540.4	540.4	541.7	542.6
5°	511.9	510.1	507.1	506.2	505.3	506.6	505.8	507.1	507.5	510.6	511.0
7.5°	480.8	478.1	475.5	472.9	472.0	469.8	472.0	472.0	475.1	474.2	476.4
10°	444.0	443.5	440.0	438.7	437.0	433.4	438.3	437.0	439.1	443.1	444.0
12.5°	416.8	412.0	414.2	408.0	410.2	406.7	407.1	407.1	410.7	411.1	410.2
15°	390.9	387.0	381.3	378.7	377.3	375.6	381.3	381.7	379.1	385.2	383.0
17.5°	364.6	364.6	359.4	358.1	354.6	356.3	355.4	355.9	355.0	359.4	361.6
20°	341.8	339.7	337.9	338.3	334.0	333.1	332.2	333.1	336.2	339.2	340.1
22.5°	323.4	322.1	317.7	318.6	315.1	316.4	315.6	317.7	318.2	318.2	321.2
25°	305.9	304.2	304.6	302.8	301.5	301.5	300.2	301.5	303.3	304.2	304.6
27.5°	292.8	291.4	289.3	287.9	288.8	286.6	288.4	289.7	289.7	288.8	289.7
30°	277.0	277.9	277.9	273.5	275.2	274.4	275.7	276.5	276.5	277.0	276.1
32.5°	266.5	263.8	263.4	263.0	263.0	261.2	261.2	262.5	263.0	263.4	264.7
35°	252.4	252.4	250.2	251.6	249.8	250.2	249.8	250.2	251.1	249.8	251.1
37.5°	239.7	240.2	239.3	240.2	240.6	239.7	238.9	240.6	239.7	239.7	238.9
40°	228.8	228.3	228.8	228.8	228.8	229.2	228.3	228.3	228.3	227.5	226.6
42.5°	219.6	216.9	217.8	218.3	216.9	216.9	217.4	216.9	218.3	215.6	215.6
45°	206.4	205.5	206.0	206.0	206.9	205.5	206.4	206.9	205.5	205.1	204.2
47.5°	194.6	195.5	194.6	195.5	195.5	196.3	194.6	195.0	195.5	193.7	192.4
50°	182.8	182.8	184.1	183.6	184.1	183.2	183.2	182.8	183.2	182.3	181.0
52.5°	171.8	170.5	172.7	172.2	171.8	171.4	170.9	171.4	170.5	169.6	169.6
55°	158.2	158.2	159.5	160.0	160.0	159.1	158.2	158.7	158.2	157.8	157.3
57.5°	147.3	145.5	146.4	146.8	146.8	145.5	146.4	145.5	145.5	145.9	144.6
60°	133.2	133.2	132.4	133.7	133.7	132.8	132.8	133.2	132.4	131.9	131.5
62.5°	118.3	118.8	120.1	120.5	121.0	120.1	119.2	119.6	119.6	118.3	118.8
65°	105.6	106.5	108.3	107.8	106.9	107.4	106.5	106.9	105.6	106.1	104.7
67.5°	93.4	92.9	93.4	93.4	94.2	93.8	92.9	92.9	92.5	93.8	92.5
70°	80.2	80.2	80.2	80.2	80.6	81.1	80.2	79.3	79.8	78.9	78.4
72.5°	66.6	67.1	66.6	67.5	66.2	67.1	67.1	66.6	66.2	66.2	66.2
75°	53.9	54.8	53.5	53.9	53.5	54.3	53.9	53.9	53.0	52.6	53.0
77.5°	41.2	41.6	40.8	41.2	40.8	41.2	41.2	40.8	40.8	40.8	40.8
80°	29.4	29.8	29.4	28.9	28.5	29.4	28.5	28.9	29.4	28.9	29.8
82.5°	18.8	18.8	18.4	18.8	18.0	18.0	18.4	18.4	18.0	18.8	18.0
85°	9.2	9.2	10.1	9.2	8.8	8.8	8.8	9.2	8.8	9.6	9.2
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.6	1.8
90°	38.0	38.1	38.4	38.6	38.9	39.1	38.9	38.6	38.4	38.1	38.0
92.5°	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8
95°	73.7	73.4	72.9	72.4	71.9	71.4	71.9	72.4	72.9	73.4	73.7
97.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1
100°	158.8	158.7	158.4	158.2	157.9	157.7	157.9	158.2	158.4	158.7	158.8
102.5°	207.2	207.1	206.8	206.5	206.3	206.0	206.3	206.5	206.8	207.1	207.2
105°	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5
107.5°	306.2	305.6	304.3	303.0	301.7	300.4	301.7	303.0	304.3	305.6	306.2
110°	357.9	357.5	356.8	356.0	355.3	354.5	355.3	356.0	356.8	357.5	357.9

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	408.6	408.3	407.8	407.3	406.8	406.3	406.8	407.3	407.8	408.3	408.6
115°	463.8	463.4	462.7	461.9	461.2	460.4	461.2	461.9	462.7	463.4	463.8
117.5°	514.5	514.1	513.3	512.6	511.8	511.0	511.8	512.6	513.3	514.1	514.5
120°	568.6	568.2	567.4	566.7	565.9	565.1	565.9	566.7	567.4	568.2	568.6
122.5°	620.4	620.1	619.6	619.1	618.6	618.1	618.6	619.1	619.6	620.1	620.4
125°	673.3	673.2	672.9	672.7	672.4	672.2	672.4	672.7	672.9	673.2	673.3
127.5°	723.9	723.5	722.8	722.0	721.3	720.5	721.3	722.0	722.8	723.5	723.9
130°	778.0	777.5	776.5	775.4	774.4	773.4	774.4	775.4	776.5	777.5	778.0
132.5°	827.5	827.1	826.4	825.6	824.9	824.1	824.9	825.6	826.4	827.1	827.5
135°	880.5	880.1	879.3	878.6	877.8	877.0	877.8	878.6	879.3	880.1	880.5
137.5°	928.8	928.3	927.3	926.2	925.2	924.2	925.2	926.2	927.3	928.3	928.8
140°	978.3	977.8	976.8	975.7	974.7	973.7	974.7	975.7	976.8	977.8	978.3
142.5°	1023.2	1022.7	1021.7	1020.6	1019.6	1018.6	1019.6	1020.6	1021.7	1022.7	1023.2
145°	1068.1	1067.6	1066.6	1065.5	1064.5	1063.5	1064.5	1065.5	1066.6	1067.6	1068.1
147.5°	1108.4	1107.9	1106.9	1105.8	1104.8	1103.8	1104.8	1105.8	1106.9	1107.9	1108.4
150°	1146.3	1145.9	1145.2	1144.4	1143.7	1142.9	1143.7	1144.4	1145.2	1145.9	1146.3
152.5°	1184.3	1183.8	1182.8	1181.7	1180.7	1179.7	1180.7	1181.7	1182.8	1183.8	1184.3
155°	1215.4	1215.0	1214.2	1213.5	1212.7	1211.9	1212.7	1213.5	1214.2	1215.0	1215.4
157.5°	1246.5	1245.9	1244.6	1243.3	1242.0	1240.7	1242.0	1243.3	1244.6	1245.9	1246.5
160°	1271.8	1271.3	1270.3	1269.2	1268.2	1267.2	1268.2	1269.2	1270.3	1271.3	1271.8
162.5°	1296.0	1295.4	1294.1	1292.8	1291.5	1290.2	1291.5	1292.8	1294.1	1295.4	1296.0
165°	1315.5	1314.9	1313.6	1312.3	1311.1	1309.8	1311.1	1312.3	1313.6	1314.9	1315.5
167.5°	1332.8	1332.2	1330.9	1329.6	1328.3	1327.0	1328.3	1329.6	1330.9	1332.2	1332.8
170°	1346.6	1345.8	1344.3	1342.8	1341.2	1339.7	1341.2	1342.8	1344.3	1345.8	1346.6
172.5°	1357.0	1356.2	1354.7	1353.2	1351.6	1350.1	1351.6	1353.2	1354.7	1356.2	1357.0
175°	1363.9	1363.1	1361.6	1360.1	1358.5	1357.0	1358.5	1360.1	1361.6	1363.1	1363.9
177.5°	1367.3	1366.5	1365.0	1363.5	1361.9	1360.4	1361.9	1363.5	1365.0	1366.5	1367.3
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	541.3	544.8	543.4	538.6	544.3	544.3	548.3	548.3	553.1	554.8	557.5
5°	510.6	513.2	515.4	513.2	517.2	523.3	526.8	529.9	536.4	539.1	543.0
7.5°	477.7	482.5	484.7	484.7	491.3	498.3	505.3	509.7	518.9	522.4	526.4
10°	445.7	451.4	455.8	455.4	466.3	470.7	479.5	489.5	498.7	504.0	509.7
12.5°	412.0	415.0	421.2	429.9	432.6	440.5	450.5	463.2	479.9	484.7	493.0
15°	383.9	392.2	397.1	401.0	407.1	414.6	425.6	437.8	454.5	465.0	473.8
17.5°	360.3	371.2	374.3	373.4	381.3	392.7	405.4	414.6	429.5	442.2	450.5
20°	341.0	345.4	350.6	352.8	358.9	371.2	383.5	394.0	406.3	416.4	426.0
22.5°	321.7	325.2	329.6	333.5	338.3	345.4	357.2	370.3	382.2	391.8	402.8
25°	305.9	308.1	312.0	315.1	320.4	325.2	333.5	348.0	362.0	367.7	377.3
27.5°	290.6	292.3	295.0	298.5	301.1	305.9	313.4	325.2	339.7	345.4	358.5
30°	277.0	278.3	280.9	282.7	284.0	289.7	295.4	304.6	315.6	323.4	333.1
32.5°	264.3	265.6	268.2	268.7	270.4	273.5	278.7	287.1	296.7	303.3	311.6
35°	250.2	251.1	253.8	254.6	255.9	258.6	262.5	268.7	277.4	282.2	289.7
37.5°	239.3	238.9	240.6	241.9	243.7	245.0	246.3	252.4	259.0	263.4	269.1
40°	227.5	226.6	227.0	228.8	229.7	231.4	231.4	237.5	241.9	245.4	249.8
42.5°	215.6	215.2	214.3	215.2	216.1	216.5	216.9	221.3	225.7	228.8	233.6
45°	203.8	203.4	202.5	202.9	202.9	203.8	205.1	206.9	209.9	212.6	215.2
47.5°	192.8	192.0	190.6	190.2	191.1	191.1	191.1	192.8	195.9	196.8	199.4
50°	181.4	180.1	178.4	177.5	177.5	177.1	177.9	178.4	181.0	181.9	184.1
52.5°	169.2	168.3	166.5	164.8	165.2	164.3	164.8	165.2	166.1	167.4	168.7
55°	156.9	155.1	153.8	153.4	152.1	152.1	150.8	152.5	152.1	152.5	154.3
57.5°	145.1	143.3	141.1	140.2	138.9	138.5	137.6	137.2	137.6	138.9	140.2
60°	131.0	130.2	128.9	127.5	126.7	125.3	124.5	124.5	124.0	124.0	124.5
62.5°	117.5	117.0	115.3	114.8	113.9	113.1	111.8	110.9	110.9	111.8	112.2
65°	104.3	103.9	102.6	102.1	99.9	99.0	98.6	98.2	97.3	97.3	97.3
67.5°	92.0	90.7	90.7	88.5	86.8	85.9	85.0	84.6	84.6	84.6	85.0
70°	78.4	78.4	77.1	75.8	74.1	74.5	73.2	71.9	71.9	71.0	71.4
72.5°	65.3	64.9	63.5	63.1	61.8	60.5	59.6	60.5	59.2	58.7	59.2
75°	52.6	52.2	51.3	50.4	50.8	49.5	48.2	47.8	47.8	46.9	46.9
77.5°	40.3	41.2	39.4	39.0	38.1	37.3	36.8	36.4	36.4	36.4	37.3
80°	28.0	28.5	28.5	27.6	28.0	26.7	26.7	26.7	25.4	25.9	26.3
82.5°	18.0	18.0	17.5	18.0	17.5	17.5	17.1	17.1	16.7	16.7	17.1
85°	10.1	9.6	9.2	10.1	9.6	9.6	9.2	9.2	9.2	9.2	9.2
87.5°	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5
90°	38.3	38.8	39.3	39.8	40.3	34.7	29.1	23.4	17.8	15.0	13.5
92.5°	36.7	36.4	36.2	35.9	35.7	35.4	35.2	34.9	34.6	34.5	33.5
95°	73.7	73.7	73.7	73.7	73.7	73.2	72.7	72.2	71.7	71.4	70.1
97.5°	115.1	115.1	115.1	115.1	115.1	114.1	113.1	112.0	111.0	110.5	109.3
100°	158.8	158.8	158.8	158.8	158.8	158.0	157.3	156.5	155.8	155.4	154.4
102.5°	207.1	206.8	206.5	206.3	206.0	205.0	204.0	202.9	201.9	201.4	200.6
105°	255.2	254.7	254.2	253.7	253.2	252.7	252.2	251.7	251.2	250.9	250.5
107.5°	306.1	305.8	305.5	305.3	305.0	305.0	305.0	305.0	305.0	305.0	304.5
110°	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.1

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	409.0	409.7	410.5	411.2	412.0	412.3	412.5	412.8	413.1	413.2	412.4
115°	463.9	464.2	464.5	464.7	465.0	465.5	466.0	466.5	467.0	467.3	466.5
117.5°	514.9	515.6	516.4	517.1	517.9	519.2	520.5	521.8	523.1	523.7	522.7
120°	568.6	568.6	568.6	568.6	568.6	570.6	572.7	574.7	576.8	577.8	576.8
122.5°	620.8	621.5	622.3	623.0	623.8	625.1	626.4	627.7	629.0	629.6	628.3
125°	673.7	674.5	675.2	676.0	676.8	677.6	678.3	679.1	679.8	680.2	679.0
127.5°	724.4	725.4	726.5	727.5	728.5	729.5	730.6	731.6	732.7	733.2	731.8
130°	778.3	778.8	779.3	779.8	780.3	780.8	781.3	781.8	782.3	782.6	780.9
132.5°	828.1	829.4	830.7	832.0	833.3	833.0	832.8	832.5	832.2	832.1	830.8
135°	880.6	880.9	881.1	881.4	881.6	881.1	880.6	880.1	879.6	879.3	877.9
137.5°	928.9	929.2	929.5	929.7	930.0	929.5	929.0	928.5	928.0	927.7	926.5
140°	978.3	978.3	978.3	978.3	978.3	977.0	975.7	974.4	973.1	972.5	971.4
142.5°	1023.1	1022.8	1022.5	1022.3	1022.0	1021.2	1020.5	1019.7	1019.0	1018.6	1017.4
145°	1068.0	1067.7	1067.4	1067.2	1066.9	1065.4	1063.8	1062.3	1060.8	1060.0	1059.1
147.5°	1108.1	1107.6	1107.1	1106.6	1106.1	1105.1	1104.1	1103.0	1102.0	1101.5	1100.3
150°	1145.9	1145.2	1144.4	1143.7	1142.9	1141.9	1140.9	1139.8	1138.8	1138.3	1137.5
152.5°	1183.8	1182.8	1181.7	1180.7	1179.7	1178.4	1177.2	1175.9	1174.6	1174.0	1173.2
155°	1214.8	1213.5	1212.2	1210.9	1209.6	1208.8	1208.1	1207.3	1206.6	1206.2	1205.8
157.5°	1245.6	1243.8	1242.0	1240.2	1238.4	1237.9	1237.4	1236.9	1236.4	1236.1	1235.8
160°	1271.0	1269.5	1268.0	1266.4	1264.9	1264.6	1264.4	1264.1	1263.8	1263.7	1263.4
162.5°	1295.1	1293.3	1291.5	1289.7	1287.9	1287.7	1287.4	1287.2	1286.9	1286.8	1286.8
165°	1314.6	1312.8	1311.1	1309.3	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.6
167.5°	1331.9	1330.1	1328.3	1326.5	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1325.1
170°	1345.7	1343.9	1342.1	1340.3	1338.5	1338.8	1339.0	1339.3	1339.6	1339.7	1340.1
172.5°	1356.1	1354.3	1352.5	1350.7	1348.9	1349.2	1349.4	1349.7	1350.0	1350.1	1350.5
175°	1363.0	1361.2	1359.4	1357.6	1355.8	1356.3	1356.8	1357.3	1357.8	1358.1	1358.5
177.5°	1366.5	1365.0	1363.5	1361.9	1360.4	1360.9	1361.4	1361.9	1362.4	1362.7	1363.1
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	570.2	570.2	570.2	570.2
2.5°	559.7	559.7	566.2	573.3
5°	547.4	550.5	561.0	570.6
7.5°	535.6	540.8	554.0	566.2
10°	521.1	528.1	544.3	558.8
12.5°	507.1	513.6	532.5	548.7
15°	487.4	495.7	515.8	536.0
17.5°	467.6	476.0	500.5	524.2
20°	444.4	455.4	483.0	514.5
22.5°	422.9	436.5	467.2	492.6
25°	399.3	420.3	448.8	481.7
27.5°	378.2	399.3	428.2	461.5
30°	354.6	376.0	405.8	436.5
32.5°	331.8	351.5	380.4	418.1
35°	308.1	326.9	355.0	393.1
37.5°	286.6	305.0	335.7	370.8
40°	265.6	284.9	311.2	346.2
42.5°	245.9	263.0	286.6	321.7
45°	227.9	240.2	262.1	295.0
47.5°	209.1	220.0	240.2	273.0
50°	191.5	200.7	218.3	248.9
52.5°	174.4	182.3	198.5	223.1
55°	159.1	166.5	178.4	202.5
57.5°	143.3	149.0	160.4	179.7
60°	128.0	133.2	142.4	158.2
62.5°	112.6	117.0	125.8	138.5
65°	99.0	102.6	109.1	120.1
67.5°	85.9	88.1	93.4	102.1
70°	73.2	74.9	79.3	86.3
72.5°	59.6	61.4	66.2	71.0
75°	48.2	48.6	52.2	56.1
77.5°	37.7	37.3	39.9	43.0
80°	25.9	27.2	29.4	30.7
82.5°	17.5	18.0	18.8	19.7
85°	9.6	10.1	10.1	11.4
87.5°	3.9	4.4	4.4	4.8
90°	10.4	7.3	4.3	1.2
92.5°	31.4	29.4	27.3	25.3
95°	67.5	65.0	62.4	59.8
97.5°	107.0	104.7	102.4	100.1
100°	152.3	150.3	148.2	146.2
102.5°	199.1	197.6	196.0	194.5
105°	249.8	249.0	248.3	247.5
107.5°	303.5	302.4	301.4	300.4
110°	355.6	354.1	352.5	351.0



TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	410.9	409.4	407.8	406.3
115°	465.0	463.5	461.9	460.4
117.5°	520.6	518.6	516.5	514.5
120°	574.7	572.7	570.6	568.6
122.5°	625.8	623.2	620.7	618.1
125°	676.7	674.4	672.1	669.8
127.5°	729.0	726.1	723.3	720.5
130°	777.6	774.3	771.0	767.7
132.5°	828.3	825.7	823.2	820.6
135°	875.1	872.3	869.5	866.7
137.5°	924.2	921.9	919.6	917.3
140°	969.1	966.8	964.5	962.2
142.5°	1015.1	1012.8	1010.5	1008.2
145°	1057.3	1055.6	1053.8	1052.0
147.5°	1098.0	1095.7	1093.4	1091.1
150°	1136.0	1134.5	1132.9	1131.4
152.5°	1171.7	1170.2	1168.6	1167.1
155°	1205.0	1204.3	1203.5	1202.7
157.5°	1235.3	1234.8	1234.3	1233.8
160°	1262.9	1262.4	1261.9	1261.4
162.5°	1286.8	1286.8	1286.8	1286.8
165°	1307.9	1308.1	1308.4	1308.6
167.5°	1325.9	1326.6	1327.4	1328.2
170°	1340.9	1341.6	1342.4	1343.2
172.5°	1351.2	1352.0	1352.7	1353.5
175°	1359.3	1360.0	1360.8	1361.6
177.5°	1363.9	1364.6	1365.4	1366.2
180°	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P998082

CATALOG NUMBER: SA2XXDIP-B290D1080UB27-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.49	11.15	11.64	12.28	13.88	7.98	8.64	9.13	9.78	11.37
	3H	11.29	11.87	12.44	13.02	14.63	9.31	9.90	10.47	11.05	12.65
	4H	11.44	12.00	12.61	13.15	14.76	9.76	10.32	10.93	11.47	13.08
	6H	11.48	11.99	12.65	13.14	14.76	10.06	10.58	11.24	11.72	13.34
	8H	11.45	11.94	12.63	13.10	14.72	10.14	10.63	11.31	11.79	13.40
	12H	11.41	11.87	12.59	13.03	14.66	10.17	10.64	11.35	11.79	13.43
4H	2H	10.50	11.07	11.68	12.21	13.82	8.40	8.96	9.58	10.11	11.72
	3H	11.47	11.93	12.65	13.10	14.73	9.85	10.31	11.02	11.48	13.11
	4H	11.74	12.17	12.92	13.32	14.97	10.37	10.80	11.55	11.96	13.60
	6H	11.86	12.22	13.04	13.40	15.04	10.74	11.11	11.93	12.29	13.92
	8H	11.85	12.19	13.03	13.36	15.01	10.85	11.19	12.03	12.36	14.01
	12H	11.80	12.12	13.00	13.30	14.95	10.89	11.20	12.09	12.39	14.04
8H	4H	11.73	12.07	12.91	13.24	14.89	10.50	10.84	11.68	12.01	13.66
	6H	11.90	12.18	13.10	13.40	15.04	10.93	11.21	12.13	12.42	14.07
	8H	11.93	12.18	13.14	13.37	15.03	11.08	11.32	12.28	12.51	14.18
	12H	11.91	12.12	13.12	13.31	15.01	11.16	11.37	12.37	12.56	14.26
12H	4H	11.68	11.99	12.88	13.17	14.82	10.46	10.77	11.66	11.96	13.61
	6H	11.88	12.13	13.09	13.32	14.98	10.93	11.17	12.13	12.36	14.03
	8H	11.90	12.12	13.11	13.31	15.00	11.07	11.29	12.28	12.48	14.18