

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999256

Luminaire Tested: SA2XXDIP-B865D925UB40-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999256
REPORT IS A COMBINATION OF REPORTS P985005 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D925UB40-4F0-XX-W2A-D4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7018.0 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999256

CATALOG NUMBER: SA2XXDIP-B865D925UB40-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P999256

CATALOG NUMBER: SA2XXDIP-B865D925UB40-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	95	90	86	82	87	82	79	75	68	65	63	55	53	51	42	41	40
2	86	78	71	66	78	71	66	61	59	55	51	47	44	42	37	34	33
3	78	68	60	54	71	62	56	50	51	46	42	41	38	35	32	29	27
4	71	60	52	45	65	55	48	42	45	40	36	37	32	29	28	25	23
5	65	53	45	39	59	49	41	36	40	35	30	33	28	25	25	22	20
6	60	48	39	33	54	44	36	31	36	31	26	29	25	22	23	20	17
7	55	43	35	29	50	39	32	27	33	27	23	27	22	19	21	18	15
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	14
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	18	14	12
10	44	32	25	20	41	30	23	19	25	20	16	21	16	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14326	14326	14326
5°	14390	13714	13636
10°	14294	13239	13046
15°	14091	12747	12439
20°	13837	12231	11864
25°	13585	11737	11343
30°	13234	11236	10827
35°	12878	10751	10447
40°	12502	10333	10070
45°	12145	9953	9742
50°	11761	9603	9417
55°	11357	9232	9087
60°	10863	8845	8741
65°	10352	8400	8341
70°	9770	7922	7911
75°	9023	7444	7505
80°	7856	6946	7087
85°	6667	6480	6723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12145 cd/sqm

TEST NUMBER: P999256

CATALOG NUMBER: SA2XXDIP-B865D925UB40-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	1.2
10°-20°	246.0	3.5
20°-30°	372.8	5.3
30°-40°	454.0	6.5
40°-50°	488.4	7.0
50°-60°	474.4	6.8
60°-70°	414.3	5.9
70°-80°	318.8	4.5
80°-90°	216.8	3.1
90°-100°	354.4	5.1
100°-110°	807.7	11.5
110°-120°	807.0	11.5
120°-130°	644.7	9.2
130°-140°	502.9	7.2
140°-150°	370.2	5.3
150°-160°	258.3	3.7
160°-170°	152.1	2.2
170°-180°	49.5	0.7
0°-30°	704.6	10.0
0°-40°	1158.6	16.5
0°-60°	2121.4	30.2
0°-90°	3071.3	43.8
90°-120°	1969.1	28.1
90°-150°	3486.9	49.7
90°-180°	3947.0	56.2
0°-180°	7018.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	905	905	905	905	905	
5°	908	904	896	904	902	86
15°	866	868	868	880	879	244
25°	787	796	808	824	828	362
35°	678	700	725	754	763	424
45°	556	592	637	678	691	429
55°	426	474	542	589	606	381
65°	291	355	433	487	504	289
75°	161	235	319	375	392	171
85°	47	128	212	268	286	50
90°	14	102	206	258	274	11
95°	45	157	536	346	328	44
105°	126	225	841	1460	1280	135
115°	216	286	688	1375	1590	214
125°	297	351	630	1098	1274	265
135°	347	414	593	898	1032	269
145°	395	454	576	723	796	248
155°	449	485	559	632	657	207
165°	489	504	535	568	577	138
175°	510	510	515	521	520	48
180°	511	511	511	511	511	

TEST NUMBER: P999256

CATALOG NUMBER: SA2XXDIP-B865D925UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	905.0	905.0	905.0	905.0	905.0
2.5°	911.5	907.6	898.4	905.0	902.3
5°	907.6	903.6	895.8	903.6	902.3
7.5°	901.0	898.4	891.8	901.0	899.7
10°	893.2	890.5	886.6	897.1	895.8
12.5°	880.0	881.3	878.7	889.2	887.9
15°	865.6	868.2	868.2	880.0	878.7
17.5°	847.2	852.5	856.4	868.2	868.2
20°	828.9	835.4	840.7	855.1	855.1
22.5°	809.2	817.1	825.0	839.4	842.0
25°	786.9	796.1	807.9	823.6	827.6
27.5°	760.7	775.1	788.2	807.9	810.5
30°	734.5	751.5	768.6	789.5	793.5
32.5°	705.6	725.3	746.3	771.2	779.1
35°	678.1	700.4	725.3	754.1	763.3
37.5°	647.9	672.8	704.3	735.8	745.0
40°	617.7	646.6	682.0	716.1	727.9
42.5°	588.9	617.7	659.7	697.7	709.5
45°	556.1	591.5	637.4	678.1	691.2
47.5°	524.6	562.6	615.1	657.1	671.5
50°	491.8	532.5	591.5	636.1	650.5
52.5°	460.3	503.6	566.6	612.5	628.2
55°	426.2	473.5	541.7	588.9	605.9
57.5°	393.5	445.9	514.1	565.3	582.3
60°	358.0	414.4	489.2	539.0	557.4
62.5°	326.6	385.6	460.3	514.1	531.2
65°	291.2	355.4	432.8	486.6	503.6
67.5°	259.7	326.6	405.3	459.0	477.4
70°	225.6	293.8	375.1	431.5	447.2
72.5°	194.1	264.9	347.6	402.6	422.3
75°	161.3	234.8	318.7	375.1	392.1
77.5°	129.8	205.9	291.2	347.6	365.9
80°	98.4	178.4	263.6	318.7	337.1
82.5°	72.1	150.8	237.4	292.5	309.5
85°	47.2	128.5	212.5	267.6	285.9
87.5°	28.9	107.5	191.5	245.3	262.3
90°	14.1	102.4	206.5	257.5	273.7
92.5°	26.5	128.0	312.6	282.2	288.1
95°	44.9	156.6	535.9	346.1	328.4
97.5°	60.3	177.1	769.4	482.0	393.5
100°	84.8	194.2	907.3	760.9	545.8
102.5°	106.1	210.2	903.0	1151.6	869.3
105°	126.5	225.4	840.8	1460.0	1280.3
107.5°	150.0	240.4	782.5	1564.9	1553.7
110°	172.2	256.0	741.2	1535.7	1659.2

TEST NUMBER: P999256

CATALOG NUMBER: SA2XXDIP-B865D925UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	193.8	271.8	710.5	1463.2	1648.1
115°	216.4	286.4	687.8	1375.0	1589.5
117.5°	238.7	302.2	670.8	1291.8	1506.3
120°	260.3	317.6	656.0	1214.9	1427.3
122.5°	280.9	334.8	644.2	1154.2	1342.8
125°	297.3	351.4	630.1	1098.3	1273.7
127.5°	312.1	368.2	619.3	1048.0	1207.2
130°	324.8	384.4	609.5	998.6	1150.5
132.5°	336.6	400.2	600.6	947.6	1093.2
135°	347.1	414.0	593.1	897.7	1032.0
137.5°	357.9	425.7	586.6	847.2	971.4
140°	370.7	435.2	580.3	801.7	908.8
142.5°	383.5	444.1	577.7	758.9	847.6
145°	394.9	453.9	575.7	722.6	796.4
147.5°	408.7	461.8	572.8	691.0	748.9
150°	422.5	469.6	569.8	668.0	710.3
152.5°	436.2	477.4	564.9	649.9	681.8
155°	449.0	484.8	559.0	632.2	657.3
157.5°	459.8	490.7	553.1	615.5	635.6
160°	470.6	496.6	547.2	598.8	615.0
162.5°	481.4	501.0	542.3	583.0	595.4
165°	489.3	504.0	535.4	567.8	576.7
167.5°	496.1	507.0	529.5	554.1	559.0
170°	503.0	508.4	524.6	541.3	543.3
172.5°	506.9	509.9	518.7	530.0	530.5
175°	509.9	510.4	514.8	521.2	519.7
177.5°	511.9	510.9	510.9	514.8	511.9
180°	510.9	510.9	510.9	510.9	510.9



TEST NUMBER: P999256

CATALOG NUMBER: SA2XXDIP-B865D925UB40-4F0-XX-W2A-D4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.86	14.71	14.86	15.73	17.08	16.94	17.79	17.93	18.80	20.16
	3H	15.32	16.09	16.33	17.11	18.49	19.52	20.29	20.53	21.32	22.69
	4H	15.80	16.53	16.82	17.55	18.94	20.78	21.51	21.80	22.54	23.92
	6H	16.08	16.76	17.11	17.79	19.18	22.07	22.75	23.10	23.78	25.18
	8H	16.14	16.78	17.17	17.83	19.22	22.73	23.38	23.77	24.43	25.82
	12H	16.15	16.77	17.20	17.81	19.23	23.46	24.07	24.50	25.12	26.53
4H	2H	14.91	15.64	15.94	16.67	18.05	17.26	18.00	18.29	19.02	20.40
	3H	16.62	17.24	17.65	18.29	19.69	20.05	20.67	21.09	21.73	23.12
	4H	17.24	17.81	18.28	18.86	20.27	21.47	22.04	22.51	23.09	24.50
	6H	17.65	18.15	18.70	19.22	20.63	22.94	23.43	23.99	24.51	25.91
	8H	17.76	18.23	18.81	19.29	20.72	23.70	24.16	24.75	25.22	26.65
	12H	17.80	18.23	18.88	19.30	20.74	24.52	24.95	25.59	26.02	27.46
8H	4H	18.03	18.49	19.08	19.56	20.98	21.61	22.08	22.67	23.14	24.57
	6H	18.66	19.05	19.74	20.15	21.58	23.24	23.63	24.32	24.74	26.16
	8H	18.88	19.23	19.96	20.31	21.76	24.13	24.48	25.21	25.57	27.01
	12H	19.02	19.32	20.10	20.40	21.89	25.13	25.43	26.21	26.52	28.00
12H	4H	18.23	18.65	19.30	19.73	21.16	21.59	22.01	22.66	23.09	24.52
	6H	18.99	19.34	20.08	20.43	21.87	23.27	23.61	24.35	24.70	26.14
	8H	19.30	19.60	20.38	20.69	22.17	24.20	24.50	25.28	25.59	27.07