

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998131

Luminaire Tested: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998131
REPORT IS A COMBINATION OF REPORTS P983871 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5267.0 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	90	90	90	90	68	68	68	49	49	49	32	32	32	32	32	23
1	92	88	84	81	82	78	75	73	60	58	56	43	42	41	28	28	27	27	27	20
2	84	77	71	66	74	69	64	60	53	50	47	38	36	35	25	24	23	23	23	17
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	22	21	20	20	20	15
4	70	60	53	47	62	54	47	43	42	37	34	30	28	25	20	19	17	17	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15	15	15	11
6	59	48	40	35	52	43	36	32	33	29	25	25	22	19	17	15	13	13	13	10
7	55	43	36	30	48	39	32	28	30	26	22	22	19	17	15	13	12	12	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	17	15	14	12	11	11	11	8
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	10	10	7
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8760	8760	8760	8760
5°	8781	9341	8815	7431
10°	8680	10197	8734	6127
15°	8468	10755	8587	5160
20°	8337	10098	8337	4486
25°	8071	8676	8107	4012
30°	7634	6819	7780	3633
35°	7247	4716	7367	3324
40°	6800	3561	6879	3078
45°	6253	2926	6355	2812
50°	5778	2568	5787	2574
55°	5236	2188	5271	2316
60°	4661	1828	4725	2021
65°	4145	1487	4220	1726
70°	3629	1166	3720	1392
75°	3043	846	3166	1009
80°	2379	536	2547	599
85°	1568	270	1681	200

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9055 cd/sqm

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.7	1.0
10°-20°	153.4	2.9
20°-30°	222.7	4.2
30°-40°	234.7	4.5
40°-50°	207.7	3.9
50°-60°	165.9	3.1
60°-70°	112.7	2.1
70°-80°	57.6	1.1
80°-90°	17.3	0.3
90°-100°	226.3	4.3
100°-110°	796.9	15.1
110°-120°	836.9	15.9
120°-130°	688.5	13.1
130°-140°	553.1	10.5
140°-150°	417.8	7.9
150°-160°	293.7	5.6
160°-170°	172.9	3.3
170°-180°	56.2	1.1
0°-30°	428.8	8.1
0°-40°	663.5	12.6
0°-60°	1037.1	19.7
0°-90°	1224.7	23.3
90°-120°	1860.0	35.3
90°-150°	3519.4	66.8
90°-180°	4042.0	76.7
0°-180°	5267.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	553	553	553	553	553	
5°	554	618	556	492	554	53
15°	520	760	528	364	520	147
25°	468	633	470	293	468	214
35°	382	345	388	243	382	239
45°	286	208	291	200	286	222
55°	196	146	198	154	196	175
65°	117	90	119	104	117	116
75°	54	44	57	53	54	58
85°	11	12	12	8	11	13
90°	1	37	1	37	1	3
95°	39	127	39	127	39	40
105°	136	1258	136	1258	136	145
115°	240	1655	240	1655	240	238
125°	335	1343	335	1343	335	298
135°	393	1113	393	1113	393	304
145°	449	888	449	888	449	282
155°	510	747	510	747	510	235
165°	556	655	556	655	556	157
175°	579	590	579	590	579	55
180°	580	580	580	580	580	

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	556.4	557.7	559.8	560.2	564.5	567.9	571.7	571.7	573.0	572.6	569.2
5°	553.8	557.7	563.2	567.9	575.5	578.9	584.0	587.9	591.3	593.8	593.4
7.5°	549.6	556.4	564.5	573.4	583.6	589.6	596.8	603.6	608.3	612.5	615.5
10°	542.4	553.8	564.9	576.8	590.0	598.1	606.6	615.5	622.8	630.8	638.5
12.5°	532.6	549.2	562.8	578.5	594.7	603.6	617.2	624.0	638.1	658.5	664.0
15°	520.2	542.8	555.5	575.5	596.8	604.0	622.8	633.8	662.7	675.5	690.8
17.5°	508.7	533.8	550.9	573.8	594.7	608.7	627.0	649.5	673.8	692.1	709.1
20°	499.4	523.6	544.1	569.6	596.0	613.8	633.0	660.2	686.6	705.3	718.5
22.5°	478.1	509.2	533.0	561.5	593.4	618.1	636.4	666.1	694.6	706.1	717.6
25°	467.5	494.3	521.9	554.3	591.7	621.0	636.8	670.0	695.1	699.3	701.9
27.5°	447.9	478.1	510.5	547.5	591.3	615.9	635.9	666.1	686.1	683.2	675.5
30°	423.7	460.7	496.4	536.4	585.3	612.1	630.8	658.5	668.7	653.4	639.8
32.5°	405.8	440.7	480.2	526.6	578.5	604.0	622.3	644.0	646.1	618.5	595.5
35°	381.6	420.3	464.9	513.9	567.0	590.0	607.0	620.2	610.0	571.3	544.1
37.5°	359.9	398.2	445.8	495.6	551.3	573.8	587.4	589.6	564.5	530.4	490.5
40°	336.0	375.6	425.4	477.7	533.8	553.4	561.9	555.5	519.4	479.8	433.5
42.5°	312.2	351.4	405.0	458.6	511.7	528.3	531.7	514.3	470.0	423.7	370.1
45°	286.3	327.1	380.7	434.7	486.2	495.6	496.0	470.9	418.6	370.1	320.3
47.5°	265.0	302.9	356.0	410.1	453.5	459.8	457.3	428.4	371.4	316.9	273.5
50°	241.6	277.8	330.5	383.7	420.7	422.4	416.0	374.8	319.0	269.3	234.8
52.5°	216.5	253.1	301.6	352.6	385.8	383.3	370.9	326.7	274.4	233.1	206.7
55°	196.5	228.9	274.4	324.1	347.5	340.3	326.7	281.6	240.3	205.5	182.5
57.5°	174.4	202.9	247.6	291.0	304.6	297.8	284.2	242.0	203.8	177.4	162.1
60°	153.6	179.5	218.6	254.8	265.4	258.2	242.5	204.6	177.0	154.8	143.4
62.5°	134.4	157.0	189.7	222.9	227.2	219.9	206.3	175.7	151.9	134.4	125.9
65°	116.6	137.8	164.2	189.3	193.1	185.5	171.4	149.3	129.3	118.3	110.2
67.5°	99.1	116.1	139.5	157.8	159.9	152.7	141.2	123.4	111.0	99.1	93.2
70°	83.8	96.6	114.9	129.7	130.6	123.8	117.8	101.7	92.3	83.8	79.1
72.5°	68.9	77.8	91.9	102.9	103.4	99.1	93.6	83.4	75.3	69.3	64.7
75°	54.4	62.1	70.6	80.4	80.0	76.6	72.3	65.9	59.1	55.3	53.2
77.5°	41.7	46.4	53.2	59.6	59.6	57.9	55.3	50.6	46.4	42.5	40.4
80°	29.8	32.8	38.3	40.4	41.3	40.8	38.7	35.3	33.6	30.6	29.8
82.5°	19.1	21.3	23.8	25.9	27.2	26.4	25.9	24.2	21.7	20.8	20.0
85°	11.1	11.9	13.2	14.5	14.9	14.5	15.3	14.0	12.8	12.8	12.3
87.5°	4.7	5.1	6.0	6.0	6.4	6.4	6.0	6.4	6.4	6.0	5.5
90°	1.1	4.5	8.9	11.2	13.4	15.0	16.7	22.3	30.1	36.8	38.0
92.5°	16.7	23.4	32.4	38.0	46.9	53.0	59.2	89.3	131.7	169.7	171.9
95°	39.1	43.5	54.7	64.7	82.6	96.0	109.4	160.7	257.9	387.3	437.6
97.5°	58.0	64.7	77.0	91.5	111.6	126.7	141.8	207.6	342.7	551.4	713.3
100°	86.0	89.3	99.3	117.2	139.5	155.2	170.8	229.9	366.1	607.2	881.8
102.5°	111.6	113.9	123.9	141.8	165.2	180.8	196.5	250.0	367.2	586.0	887.4
105°	136.2	140.6	148.5	165.2	189.8	205.4	221.0	273.5	372.8	557.0	827.1
107.5°	163.0	166.3	174.1	189.8	214.3	230.0	245.6	296.9	385.1	541.4	771.3
110°	189.8	194.2	200.9	215.4	238.9	255.0	271.2	320.4	400.7	536.9	733.4



TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	214.3	218.8	226.6	240.0	262.3	279.0	295.8	342.7	417.5	538.0	708.8
115°	240.0	245.6	252.3	265.7	288.0	303.0	318.1	366.1	434.2	542.5	692.1
117.5°	266.8	271.2	277.9	290.2	311.4	327.0	342.7	387.3	452.1	549.2	683.1
120°	291.3	295.8	302.5	312.6	334.9	350.5	366.1	409.7	469.9	555.9	675.3
122.5°	314.8	318.1	324.8	336.0	358.3	374.5	390.7	430.9	485.6	563.7	670.9
125°	334.9	338.2	344.9	358.3	380.6	396.2	411.9	452.1	502.3	571.5	665.3
127.5°	351.6	356.1	365.0	379.5	400.7	416.9	433.1	472.2	517.9	579.3	661.9
130°	366.1	370.6	381.8	397.4	419.7	435.4	451.0	490.0	532.5	588.3	659.7
132.5°	379.5	385.1	397.4	414.1	437.6	453.2	468.8	505.7	547.0	597.2	658.6
135°	392.9	397.4	410.8	427.5	453.2	468.8	484.5	520.2	559.2	603.9	657.5
137.5°	405.2	410.8	424.2	442.0	467.7	482.2	496.7	532.5	569.3	610.6	657.5
140°	419.7	424.2	437.6	455.4	480.0	494.5	509.0	542.5	577.1	615.1	656.4
142.5°	434.2	437.6	449.8	467.7	491.2	504.6	517.9	550.3	583.8	618.4	656.4
145°	448.7	453.2	464.4	481.1	503.4	515.7	528.0	558.1	589.4	620.6	654.1
147.5°	464.4	467.7	478.9	494.5	513.5	524.6	535.8	564.8	592.7	621.8	650.8
150°	480.0	483.3	492.3	506.8	523.5	533.6	543.6	569.3	595.0	620.6	647.4
152.5°	495.6	496.7	505.7	517.9	533.6	542.5	551.4	573.8	596.1	618.4	641.8
155°	510.1	511.2	517.9	530.2	542.5	550.8	559.2	578.2	597.2	616.2	635.1
157.5°	522.4	523.5	529.1	540.3	550.3	557.6	564.8	581.6	597.2	611.7	628.4
160°	534.7	535.8	540.3	549.2	558.1	564.2	570.4	583.8	597.2	608.4	621.8
162.5°	547.0	545.8	550.3	557.0	564.8	569.3	573.8	584.9	596.1	605.0	616.2
165°	555.9	554.8	557.0	563.7	569.3	572.6	576.0	586.0	593.8	600.5	608.4
167.5°	563.7	562.6	564.8	569.3	573.8	576.0	578.2	586.0	592.7	596.1	601.7
170°	571.5	569.3	570.4	573.8	576.0	577.6	579.3	584.9	590.5	592.7	596.1
172.5°	576.0	574.9	573.8	577.1	578.2	579.4	580.5	583.8	587.1	588.3	589.4
175°	579.3	578.2	577.1	579.3	579.3	579.9	580.5	582.7	584.9	583.8	584.9
177.5°	581.6	579.3	578.2	580.5	580.5	580.5	580.5	581.6	583.8	581.6	580.5
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	575.1	575.5	576.4	580.6	582.8	583.2	581.5	585.3	586.6	585.3	584.5
5°	602.3	604.9	610.0	615.5	615.1	615.5	618.1	620.6	621.5	618.1	619.3
7.5°	626.2	631.3	636.8	645.3	645.3	649.5	651.3	653.4	658.5	655.9	655.1
10°	653.4	660.2	670.4	684.0	684.4	688.7	692.9	699.7	701.9	700.2	701.0
12.5°	687.4	700.6	701.4	716.3	723.1	724.0	730.8	729.5	733.8	733.8	741.0
15°	702.3	722.7	734.2	748.7	752.9	747.8	753.3	759.3	759.7	759.7	759.3
17.5°	729.1	737.2	748.7	756.3	758.0	758.0	758.4	761.0	759.3	755.9	758.4
20°	734.6	738.0	742.3	741.4	742.3	738.0	733.8	729.5	729.9	727.8	734.2
22.5°	724.4	723.6	713.8	707.4	707.4	698.9	690.8	687.0	683.2	684.4	686.6
25°	698.9	685.7	673.8	664.4	662.3	648.7	637.6	634.2	627.9	633.0	633.8
27.5°	658.1	643.2	624.0	615.9	604.9	599.4	591.7	581.5	568.3	576.0	574.7
30°	614.2	592.1	576.4	556.8	539.4	538.1	523.6	506.6	499.8	499.8	503.6
32.5°	565.3	536.0	513.0	485.4	468.3	461.1	443.7	426.7	430.5	417.7	422.4
35°	508.3	469.6	440.7	413.9	401.1	392.6	370.1	360.7	350.5	344.6	355.6
37.5°	453.9	409.2	372.2	342.9	338.2	322.9	307.5	301.6	295.6	298.2	297.8
40°	387.5	348.0	314.8	291.8	283.7	276.5	266.3	259.1	255.2	257.4	257.8
42.5°	327.5	294.4	269.7	253.5	246.7	241.6	236.5	230.6	229.3	229.3	231.0
45°	281.2	253.9	237.4	224.2	220.3	216.5	212.7	210.1	209.3	207.6	208.9
47.5°	244.2	222.5	212.3	202.5	198.2	197.4	194.0	192.7	191.0	190.6	191.0
50°	213.1	199.5	190.1	184.6	181.6	180.4	178.7	176.1	175.3	177.4	176.5
52.5°	191.4	178.7	173.6	168.0	166.3	164.6	162.1	162.5	162.1	161.2	161.2
55°	169.7	161.6	156.5	152.3	151.9	150.2	148.0	147.2	146.8	145.9	147.2
57.5°	152.3	145.9	141.2	137.4	135.7	135.7	133.6	131.9	131.9	131.4	131.9
60°	134.8	128.5	125.5	121.7	120.4	120.0	118.7	117.8	116.6	116.6	116.6
62.5°	118.7	113.6	110.2	106.8	107.2	105.1	103.4	102.5	102.5	102.9	102.9
65°	103.4	100.0	95.7	92.7	91.9	91.5	90.6	90.2	88.9	89.8	89.8
67.5°	89.3	84.6	82.1	80.8	79.5	79.1	78.3	77.4	77.0	76.6	77.4
70°	75.3	71.5	69.3	68.5	67.2	66.8	66.4	65.1	65.5	65.9	66.4
72.5°	62.5	59.1	58.7	56.1	56.1	56.1	54.4	55.3	54.9	54.0	54.9
75°	49.3	47.6	46.8	45.5	45.9	45.5	45.1	43.8	43.8	44.2	44.7
77.5°	39.1	37.4	37.0	35.7	34.9	35.7	34.9	34.5	34.5	34.9	34.9
80°	28.9	28.1	26.8	26.8	26.8	26.4	26.4	26.4	25.9	25.5	25.9
82.5°	19.1	19.1	18.7	18.3	18.7	17.9	18.3	18.3	18.3	18.3	18.3
85°	12.3	11.9	11.9	11.5	11.5	11.5	11.9	11.1	11.1	11.5	11.5
87.5°	5.5	5.5	5.5	6.0	5.5	5.5	5.5	6.0	5.5	5.5	5.5
90°	36.8	35.7	33.5	35.7	36.2	36.8	36.8	36.8	36.8	36.8	36.8
92.5°	144.0	112.7	96.0	83.7	79.2	74.8	73.7	69.2	70.3	68.1	70.3
95°	382.9	292.5	224.4	177.5	165.2	152.9	138.4	129.5	126.1	127.3	126.1
97.5°	718.9	598.3	477.8	365.0	331.5	298.0	254.5	232.2	219.9	213.2	219.9
100°	1042.6	1019.1	880.7	727.8	660.2	592.7	500.1	452.1	419.7	399.6	419.7
102.5°	1163.1	1294.9	1290.4	1188.8	1116.2	1043.7	941.0	850.6	808.2	779.1	808.2
105°	1124.1	1356.2	1482.4	1496.9	1478.5	1460.1	1390.8	1321.6	1273.6	1258.0	1273.6
107.5°	1041.5	1290.4	1477.9	1587.3	1609.6	1632.0	1630.8	1620.8	1606.3	1580.6	1606.3
110°	964.4	1200.0	1399.8	1542.7	1588.4	1634.2	1682.2	1703.4	1713.4	1712.3	1713.4

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	910.9	1117.4	1307.1	1462.3	1516.4	1570.6	1642.0	1681.1	1702.3	1710.1	1702.3
115°	868.4	1052.6	1224.5	1370.8	1428.2	1485.7	1565.0	1616.3	1645.4	1655.4	1645.4
117.5°	839.4	999.0	1153.1	1289.3	1344.0	1398.7	1480.1	1534.8	1565.0	1572.8	1565.0
120°	817.1	961.1	1099.5	1217.8	1268.6	1319.4	1397.5	1450.0	1482.4	1493.5	1482.4
122.5°	798.1	931.0	1054.9	1165.4	1210.1	1254.7	1322.8	1374.1	1402.0	1410.9	1402.0
125°	780.3	901.9	1016.9	1115.1	1157.0	1198.9	1263.6	1306.0	1333.9	1342.8	1333.9
127.5°	763.5	872.9	979.0	1072.7	1111.8	1150.9	1207.8	1248.0	1272.5	1279.2	1272.5
130°	746.8	845.0	941.0	1029.2	1066.1	1102.9	1157.6	1195.5	1217.8	1226.8	1217.8
132.5°	733.4	818.2	905.3	984.5	1018.6	1052.6	1106.2	1144.2	1164.2	1172.1	1164.2
135°	721.1	793.7	867.3	941.0	972.2	1003.5	1051.5	1088.3	1108.4	1112.9	1108.4
137.5°	712.2	773.6	837.2	897.5	925.4	953.3	999.0	1031.4	1049.3	1056.0	1049.3
140°	704.4	754.6	808.2	859.5	884.0	908.6	944.3	973.4	990.1	996.8	990.1
142.5°	696.5	739.0	782.5	824.9	844.4	864.0	897.5	923.1	937.7	937.7	937.7
145°	689.8	724.4	761.3	795.9	812.1	828.3	855.0	874.0	885.2	888.5	885.2
147.5°	683.1	713.3	743.4	771.3	783.6	795.9	819.3	835.0	842.8	845.0	842.8
150°	674.2	701.0	725.6	749.0	759.0	769.1	785.8	799.2	805.9	807.0	805.9
152.5°	666.4	688.7	711.1	730.0	738.4	746.8	759.1	770.2	774.7	774.7	774.7
155°	656.4	677.6	695.4	712.2	718.3	724.4	736.7	744.5	749.0	746.8	749.0
157.5°	647.4	664.2	679.8	694.3	699.3	704.4	713.3	720.0	722.2	722.2	722.2
160°	637.4	651.9	664.2	676.4	680.3	684.3	692.1	697.7	698.8	698.8	698.8
162.5°	628.4	639.6	649.7	659.7	662.5	665.3	673.1	676.4	677.6	676.4	677.6
165°	618.4	627.3	635.1	643.0	645.2	647.4	651.9	656.4	656.4	655.2	656.4
167.5°	608.4	615.1	621.8	627.3	629.6	631.8	634.0	636.3	636.3	635.1	636.3
170°	600.5	606.1	609.5	613.9	615.0	616.2	617.3	620.6	619.5	617.3	619.5
172.5°	592.7	596.1	598.3	601.7	602.2	602.8	603.9	605.0	603.9	602.8	603.9
175°	586.0	589.4	590.5	591.6	592.2	592.7	592.7	593.8	592.7	590.5	592.7
177.5°	581.6	583.8	583.8	584.9	584.9	584.9	584.9	584.9	583.8	581.6	583.8
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	586.6	583.6	581.1	581.5	583.6	581.9	577.7	572.1	570.0	567.5	570.0
5°	621.9	619.3	614.2	614.7	613.4	611.7	604.9	596.4	596.4	589.6	588.7
7.5°	656.8	653.0	649.5	648.7	644.0	640.6	634.7	622.8	618.1	610.0	605.3
10°	695.9	692.9	689.1	684.4	681.9	675.9	666.1	648.7	640.2	629.1	621.0
12.5°	735.5	735.0	726.5	717.2	716.8	707.4	700.6	677.2	665.7	650.8	631.7
15°	760.6	758.4	753.8	749.1	750.4	740.2	724.8	697.2	689.5	671.7	651.3
17.5°	760.1	760.1	758.9	758.0	756.7	753.8	745.3	727.0	714.6	692.1	672.9
20°	735.9	741.4	742.7	742.3	746.5	748.7	748.2	736.8	727.0	707.0	687.4
22.5°	687.4	700.2	705.7	709.1	718.0	722.7	733.8	729.5	727.0	712.1	695.5
25°	642.3	646.6	663.2	664.0	676.3	687.8	698.9	706.1	715.5	710.0	695.9
27.5°	584.0	593.8	605.7	614.7	617.2	640.6	658.9	672.5	693.8	695.5	690.8
30°	518.1	522.8	542.4	554.3	567.9	584.9	611.3	634.7	653.8	671.2	677.2
32.5°	437.7	456.9	468.3	482.8	494.7	524.9	557.2	587.4	609.6	638.9	651.7
35°	364.1	379.0	398.6	404.5	426.2	451.7	493.9	532.6	566.2	596.0	621.9
37.5°	303.3	315.2	336.0	345.4	358.2	390.9	426.2	474.3	514.7	551.3	583.6
40°	261.6	270.5	286.3	289.3	299.9	329.7	358.2	403.3	456.9	506.2	541.5
42.5°	233.1	237.4	248.0	251.8	258.6	278.6	304.1	346.7	396.5	447.5	497.3
45°	212.7	215.7	222.0	225.4	234.0	242.9	263.7	297.8	336.9	388.4	442.0
47.5°	194.4	198.2	200.8	202.9	207.6	217.4	231.0	256.1	293.5	340.7	392.6
50°	179.1	180.4	185.0	185.5	188.4	194.8	207.6	222.9	252.7	291.0	341.2
52.5°	163.8	165.0	168.0	171.0	172.3	177.4	185.9	198.7	220.8	251.0	295.6
55°	148.5	150.2	153.1	155.3	156.5	160.8	165.9	178.2	195.7	216.9	253.5
57.5°	133.1	137.0	137.8	139.1	141.2	145.9	150.6	157.8	171.4	191.0	217.8
60°	118.7	120.0	122.9	124.2	126.3	128.9	134.8	140.4	150.2	165.5	189.7
62.5°	103.8	106.8	108.0	109.3	111.0	114.0	117.8	123.8	132.3	144.6	163.8
65°	91.0	91.5	94.0	95.7	97.4	99.5	103.4	108.9	114.0	125.5	139.5
67.5°	78.7	79.5	80.4	82.1	84.2	86.4	89.8	92.7	99.1	106.8	117.8
70°	66.8	66.8	68.9	70.2	69.8	72.3	74.9	78.3	82.9	90.2	99.1
72.5°	56.1	55.7	57.4	57.9	58.7	60.4	62.1	65.5	68.1	73.6	80.4
75°	44.7	45.5	46.4	46.4	47.6	48.9	50.6	52.3	55.3	58.7	63.8
77.5°	35.3	35.3	36.2	36.6	37.9	37.4	39.1	40.8	43.0	45.9	49.8
80°	25.9	26.8	26.8	26.8	27.2	27.6	29.4	30.6	31.9	34.0	35.7
82.5°	18.3	18.3	19.1	19.1	19.1	20.0	20.0	20.4	21.3	22.5	23.8
85°	11.5	11.5	11.5	11.9	11.5	11.9	12.8	12.3	12.8	13.6	13.6
87.5°	5.5	5.5	5.5	5.5	5.5	6.0	5.5	6.0	6.4	6.4	6.4
90°	36.8	36.8	36.8	36.2	35.7	33.5	35.7	36.8	38.0	36.8	30.1
92.5°	69.2	73.7	74.8	79.2	83.7	96.0	112.7	144.0	171.9	169.7	131.7
95°	129.5	138.4	152.9	165.2	177.5	224.4	292.5	382.9	437.6	387.3	257.9
97.5°	232.2	254.5	298.0	331.5	365.0	477.8	598.3	718.9	713.3	551.4	342.7
100°	452.1	500.1	592.7	660.2	727.8	880.7	1019.1	1042.6	881.8	607.2	366.1
102.5°	850.6	941.0	1043.7	1116.2	1188.8	1290.4	1294.9	1163.1	887.4	586.0	367.2
105°	1321.6	1390.8	1460.1	1478.5	1496.9	1482.4	1356.2	1124.1	827.1	557.0	372.8
107.5°	1620.8	1630.8	1632.0	1609.6	1587.3	1477.9	1290.4	1041.5	771.3	541.4	385.1
110°	1703.4	1682.2	1634.2	1588.4	1542.7	1399.8	1200.0	964.4	733.4	536.9	400.7

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1681.1	1642.0	1570.6	1516.4	1462.3	1307.1	1117.4	910.9	708.8	538.0	417.5
115°	1616.3	1565.0	1485.7	1428.2	1370.8	1224.5	1052.6	868.4	692.1	542.5	434.2
117.5°	1534.8	1480.1	1398.7	1344.0	1289.3	1153.1	999.0	839.4	683.1	549.2	452.1
120°	1450.0	1397.5	1319.4	1268.6	1217.8	1099.5	961.1	817.1	675.3	555.9	469.9
122.5°	1374.1	1322.8	1254.7	1210.1	1165.4	1054.9	931.0	798.1	670.9	563.7	485.6
125°	1306.0	1263.6	1198.9	1157.0	1115.1	1016.9	901.9	780.3	665.3	571.5	502.3
127.5°	1248.0	1207.8	1150.9	1111.8	1072.7	979.0	872.9	763.5	661.9	579.3	517.9
130°	1195.5	1157.6	1102.9	1066.1	1029.2	941.0	845.0	746.8	659.7	588.3	532.5
132.5°	1144.2	1106.2	1052.6	1018.6	984.5	905.3	818.2	733.4	658.6	597.2	547.0
135°	1088.3	1051.5	1003.5	972.2	941.0	867.3	793.7	721.1	657.5	603.9	559.2
137.5°	1031.4	999.0	953.3	925.4	897.5	837.2	773.6	712.2	657.5	610.6	569.3
140°	973.4	944.3	908.6	884.0	859.5	808.2	754.6	704.4	656.4	615.1	577.1
142.5°	923.1	897.5	864.0	844.4	824.9	782.5	739.0	696.5	656.4	618.4	583.8
145°	874.0	855.0	828.3	812.1	795.9	761.3	724.4	689.8	654.1	620.6	589.4
147.5°	835.0	819.3	795.9	783.6	771.3	743.4	713.3	683.1	650.8	621.8	592.7
150°	799.2	785.8	769.1	759.0	749.0	725.6	701.0	674.2	647.4	620.6	595.0
152.5°	770.2	759.1	746.8	738.4	730.0	711.1	688.7	666.4	641.8	618.4	596.1
155°	744.5	736.7	724.4	718.3	712.2	695.4	677.6	656.4	635.1	616.2	597.2
157.5°	720.0	713.3	704.4	699.3	694.3	679.8	664.2	647.4	628.4	611.7	597.2
160°	697.7	692.1	684.3	680.3	676.4	664.2	651.9	637.4	621.8	608.4	597.2
162.5°	676.4	673.1	665.3	662.5	659.7	649.7	639.6	628.4	616.2	605.0	596.1
165°	656.4	651.9	647.4	645.2	643.0	635.1	627.3	618.4	608.4	600.5	593.8
167.5°	636.3	634.0	631.8	629.6	627.3	621.8	615.1	608.4	601.7	596.1	592.7
170°	620.6	617.3	616.2	615.0	613.9	609.5	606.1	600.5	596.1	592.7	590.5
172.5°	605.0	603.9	602.8	602.2	601.7	598.3	596.1	592.7	589.4	588.3	587.1
175°	593.8	592.7	592.7	592.2	591.6	590.5	589.4	586.0	584.9	583.8	584.9
177.5°	584.9	584.9	584.9	584.9	584.9	583.8	583.8	581.6	580.5	581.6	583.8
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	567.9	565.7	564.5	565.3	562.8	556.4	556.4	558.5	556.0	553.4	549.6
5°	583.6	579.4	576.8	576.4	570.4	560.2	558.1	556.0	550.4	544.5	538.1
7.5°	598.9	591.3	587.0	584.0	575.5	562.3	556.8	552.1	543.2	534.3	526.2
10°	611.7	600.6	595.5	590.8	579.8	563.2	554.3	545.8	534.3	522.8	512.6
12.5°	621.9	609.1	602.8	596.0	582.3	560.6	549.6	536.0	524.5	509.2	499.0
15°	638.9	612.5	606.6	600.2	586.2	556.4	542.8	527.5	511.7	491.3	480.2
17.5°	652.5	617.2	616.8	603.2	584.9	554.7	533.8	513.9	496.8	476.4	459.0
20°	660.6	624.5	617.6	603.6	580.6	543.2	521.5	499.4	481.1	456.4	439.0
22.5°	667.4	634.7	616.8	599.8	571.7	539.4	507.5	486.6	461.5	434.7	418.1
25°	670.0	636.8	618.1	598.5	565.3	528.3	492.2	469.6	441.5	417.3	394.7
27.5°	670.4	636.4	613.4	593.0	556.4	513.9	476.8	453.0	422.0	393.9	371.4
30°	666.1	631.7	610.8	588.7	547.9	500.7	458.1	431.8	398.6	370.5	347.1
32.5°	653.4	622.3	605.3	581.1	536.8	482.4	440.3	410.9	376.0	348.4	325.8
35°	632.1	610.8	592.1	569.6	522.4	465.4	422.4	387.9	352.6	326.3	305.0
37.5°	605.7	594.3	576.8	554.7	505.8	450.0	402.4	364.1	328.8	303.3	282.4
40°	570.0	573.0	556.0	536.0	486.2	429.2	376.5	339.9	306.7	282.9	262.5
42.5°	531.3	543.6	533.8	514.7	464.5	406.2	357.3	316.9	284.6	259.9	242.9
45°	489.6	510.9	504.9	490.9	442.0	382.0	330.1	291.0	262.5	238.6	223.7
47.5°	444.1	474.3	474.3	464.1	416.9	357.7	306.7	266.7	238.6	221.6	207.2
50°	397.7	431.8	437.3	430.5	388.8	330.1	278.2	242.0	217.8	201.2	190.6
52.5°	349.2	388.8	399.0	395.6	359.0	303.7	254.8	219.5	197.4	182.9	173.6
55°	302.9	348.8	359.9	361.1	327.1	274.8	228.9	197.8	176.5	166.7	158.7
57.5°	259.1	303.3	315.6	317.8	294.8	248.4	204.6	177.4	158.2	150.2	143.8
60°	221.6	258.6	274.8	279.5	259.5	217.8	182.1	155.7	141.2	133.6	127.6
62.5°	191.0	220.8	237.8	239.1	230.1	191.0	158.7	136.5	124.2	117.4	114.4
65°	161.2	188.0	198.2	203.3	196.1	165.5	137.0	118.7	108.9	102.9	100.0
67.5°	137.4	154.4	162.9	169.7	162.5	139.5	116.6	101.7	94.4	88.5	86.8
70°	112.7	126.8	133.1	139.9	133.6	116.1	99.5	85.9	79.5	74.9	72.7
72.5°	90.2	101.2	107.2	111.4	107.6	93.2	79.5	70.2	65.5	62.1	60.8
75°	71.5	79.1	82.5	85.5	83.8	72.7	64.2	56.6	52.3	49.3	48.5
77.5°	54.4	60.0	63.8	64.7	62.5	55.3	48.1	43.4	40.0	38.3	37.4
80°	38.7	42.1	44.2	45.5	43.4	40.4	35.3	31.9	28.9	26.8	26.4
82.5°	25.9	27.6	29.4	28.9	28.1	25.5	22.5	20.8	19.6	17.9	17.9
85°	14.9	15.3	16.2	16.6	16.2	14.5	12.8	11.9	11.1	9.8	9.8
87.5°	6.4	6.8	6.8	7.2	6.4	6.4	5.5	4.7	4.7	4.3	3.8
90°	22.3	16.7	15.0	13.4	11.2	8.9	4.5	1.1	4.5	8.9	11.2
92.5°	89.3	59.2	53.0	46.9	38.0	32.4	23.4	16.7	23.4	32.4	38.0
95°	160.7	109.4	96.0	82.6	64.7	54.7	43.5	39.1	43.5	54.7	64.7
97.5°	207.6	141.8	126.7	111.6	91.5	77.0	64.7	58.0	64.7	77.0	91.5
100°	229.9	170.8	155.2	139.5	117.2	99.3	89.3	86.0	89.3	99.3	117.2
102.5°	250.0	196.5	180.8	165.2	141.8	123.9	113.9	111.6	113.9	123.9	141.8
105°	273.5	221.0	205.4	189.8	165.2	148.5	140.6	136.2	140.6	148.5	165.2
107.5°	296.9	245.6	230.0	214.3	189.8	174.1	166.3	163.0	166.3	174.1	189.8
110°	320.4	271.2	255.0	238.9	215.4	200.9	194.2	189.8	194.2	200.9	215.4

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	342.7	295.8	279.0	262.3	240.0	226.6	218.8	214.3	218.8	226.6	240.0
115°	366.1	318.1	303.0	288.0	265.7	252.3	245.6	240.0	245.6	252.3	265.7
117.5°	387.3	342.7	327.0	311.4	290.2	277.9	271.2	266.8	271.2	277.9	290.2
120°	409.7	366.1	350.5	334.9	312.6	302.5	295.8	291.3	295.8	302.5	312.6
122.5°	430.9	390.7	374.5	358.3	336.0	324.8	318.1	314.8	318.1	324.8	336.0
125°	452.1	411.9	396.2	380.6	358.3	344.9	338.2	334.9	338.2	344.9	358.3
127.5°	472.2	433.1	416.9	400.7	379.5	365.0	356.1	351.6	356.1	365.0	379.5
130°	490.0	451.0	435.4	419.7	397.4	381.8	370.6	366.1	370.6	381.8	397.4
132.5°	505.7	468.8	453.2	437.6	414.1	397.4	385.1	379.5	385.1	397.4	414.1
135°	520.2	484.5	468.8	453.2	427.5	410.8	397.4	392.9	397.4	410.8	427.5
137.5°	532.5	496.7	482.2	467.7	442.0	424.2	410.8	405.2	410.8	424.2	442.0
140°	542.5	509.0	494.5	480.0	455.4	437.6	424.2	419.7	424.2	437.6	455.4
142.5°	550.3	517.9	504.6	491.2	467.7	449.8	437.6	434.2	437.6	449.8	467.7
145°	558.1	528.0	515.7	503.4	481.1	464.4	453.2	448.7	453.2	464.4	481.1
147.5°	564.8	535.8	524.6	513.5	494.5	478.9	467.7	464.4	467.7	478.9	494.5
150°	569.3	543.6	533.6	523.5	506.8	492.3	483.3	480.0	483.3	492.3	506.8
152.5°	573.8	551.4	542.5	533.6	517.9	505.7	496.7	495.6	496.7	505.7	517.9
155°	578.2	559.2	550.8	542.5	530.2	517.9	511.2	510.1	511.2	517.9	530.2
157.5°	581.6	564.8	557.6	550.3	540.3	529.1	523.5	522.4	523.5	529.1	540.3
160°	583.8	570.4	564.2	558.1	549.2	540.3	535.8	534.7	535.8	540.3	549.2
162.5°	584.9	573.8	569.3	564.8	557.0	550.3	545.8	547.0	545.8	550.3	557.0
165°	586.0	576.0	572.6	569.3	563.7	557.0	554.8	555.9	554.8	557.0	563.7
167.5°	586.0	578.2	576.0	573.8	569.3	564.8	562.6	563.7	562.6	564.8	569.3
170°	584.9	579.3	577.6	576.0	573.8	570.4	569.3	571.5	569.3	570.4	573.8
172.5°	583.8	580.5	579.4	578.2	577.1	573.8	574.9	576.0	574.9	573.8	577.1
175°	582.7	580.5	579.9	579.3	579.3	577.1	578.2	579.3	578.2	577.1	579.3
177.5°	581.6	580.5	580.5	580.5	580.5	578.2	579.3	581.6	579.3	578.2	580.5
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	547.5	549.6	549.2	544.9	540.2	536.4	529.2	530.0	527.5	527.9	530.4
5°	533.8	533.8	532.1	526.2	518.5	514.3	506.2	504.1	499.0	498.5	498.1
7.5°	519.4	517.3	515.1	506.6	497.3	490.5	479.4	476.8	471.7	468.3	466.6
10°	502.4	499.4	495.1	485.4	473.9	465.4	453.9	450.5	440.7	436.4	433.9
12.5°	483.7	482.0	475.1	467.1	448.3	439.0	422.4	425.8	416.0	407.5	406.2
15°	464.9	458.6	454.7	441.5	419.0	414.7	401.6	394.7	385.8	379.0	379.0
17.5°	446.6	436.9	428.4	414.3	397.7	385.8	376.0	372.6	361.6	354.8	353.5
20°	422.4	411.3	409.2	389.2	377.7	364.5	355.2	346.7	338.6	335.6	333.5
22.5°	399.4	386.7	383.3	366.2	354.8	341.6	332.2	326.3	320.3	318.2	314.4
25°	374.8	367.1	362.0	343.7	330.9	318.6	312.2	308.0	302.4	302.0	299.5
27.5°	350.9	343.7	338.6	321.2	311.8	300.3	295.2	290.5	287.6	286.3	285.0
30°	330.5	322.4	316.5	303.7	292.2	282.9	278.6	275.6	273.9	271.8	271.4
32.5°	308.0	303.3	295.2	285.4	276.5	267.6	265.0	262.9	260.3	259.5	259.1
35°	288.8	282.4	277.3	266.3	262.5	254.8	251.8	250.1	246.7	245.9	245.0
37.5°	270.1	264.2	258.6	251.8	244.6	240.3	238.6	236.1	234.4	234.8	234.0
40°	251.4	246.7	242.5	235.2	231.0	228.9	225.4	222.9	222.0	222.5	222.0
42.5°	233.1	228.9	226.3	220.8	216.5	214.4	212.3	209.7	211.0	211.0	212.3
45°	216.5	212.7	211.0	206.7	204.2	200.8	198.7	198.2	199.9	199.5	199.5
47.5°	199.5	198.2	196.1	192.3	188.9	186.7	186.3	186.3	188.0	188.9	188.4
50°	186.3	183.8	181.2	178.2	175.7	174.8	173.6	174.4	176.1	176.1	177.0
52.5°	169.7	168.0	167.2	164.6	162.9	162.9	162.9	163.3	164.6	165.9	165.5
55°	155.3	154.0	153.1	151.9	149.7	150.2	149.7	150.6	151.9	153.1	154.0
57.5°	139.9	139.5	138.7	136.5	136.5	136.1	137.4	137.8	139.9	140.8	142.1
60°	126.3	125.1	125.1	123.4	123.4	123.4	124.6	125.9	127.6	128.0	128.9
62.5°	111.9	111.9	111.4	110.2	110.2	111.4	111.9	113.6	114.4	114.4	115.7
65°	98.3	97.8	97.4	97.8	98.3	98.3	99.5	100.4	101.2	101.7	102.1
67.5°	84.6	84.2	85.1	84.6	85.5	87.2	86.8	88.1	89.3	89.3	89.8
70°	71.9	72.7	72.3	73.2	72.7	73.6	74.9	75.3	75.3	75.7	77.0
72.5°	60.0	60.0	60.0	59.6	60.0	60.8	61.7	62.1	63.0	63.4	64.7
75°	48.5	48.5	47.6	48.5	48.5	49.3	50.2	50.2	50.2	51.0	52.3
77.5°	36.6	37.0	36.6	37.4	37.4	37.9	38.7	38.3	39.1	39.6	40.0
80°	26.8	26.4	26.4	26.4	26.8	26.8	27.6	28.1	28.1	29.4	28.5
82.5°	17.0	17.4	17.0	17.4	17.4	17.9	17.4	17.9	18.3	19.1	18.7
85°	9.8	9.4	9.4	9.8	9.4	9.4	9.8	9.4	9.8	9.4	9.8
87.5°	3.8	3.4	3.4	3.4	3.4	3.0	3.0	2.6	2.6	2.6	2.1
90°	13.4	15.0	16.7	22.3	30.1	36.8	38.0	36.8	35.7	33.5	35.7
92.5°	46.9	53.0	59.2	89.3	131.7	169.7	171.9	144.0	112.7	96.0	83.7
95°	82.6	96.0	109.4	160.7	257.9	387.3	437.6	382.9	292.5	224.4	177.5
97.5°	111.6	126.7	141.8	207.6	342.7	551.4	713.3	718.9	598.3	477.8	365.0
100°	139.5	155.2	170.8	229.9	366.1	607.2	881.8	1042.6	1019.1	880.7	727.8
102.5°	165.2	180.8	196.5	250.0	367.2	586.0	887.4	1163.1	1294.9	1290.4	1188.8
105°	189.8	205.4	221.0	273.5	372.8	557.0	827.1	1124.1	1356.2	1482.4	1496.9
107.5°	214.3	230.0	245.6	296.9	385.1	541.4	771.3	1041.5	1290.4	1477.9	1587.3
110°	238.9	255.0	271.2	320.4	400.7	536.9	733.4	964.4	1200.0	1399.8	1542.7

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	262.3	279.0	295.8	342.7	417.5	538.0	708.8	910.9	1117.4	1307.1	1462.3
115°	288.0	303.0	318.1	366.1	434.2	542.5	692.1	868.4	1052.6	1224.5	1370.8
117.5°	311.4	327.0	342.7	387.3	452.1	549.2	683.1	839.4	999.0	1153.1	1289.3
120°	334.9	350.5	366.1	409.7	469.9	555.9	675.3	817.1	961.1	1099.5	1217.8
122.5°	358.3	374.5	390.7	430.9	485.6	563.7	670.9	798.1	931.0	1054.9	1165.4
125°	380.6	396.2	411.9	452.1	502.3	571.5	665.3	780.3	901.9	1016.9	1115.1
127.5°	400.7	416.9	433.1	472.2	517.9	579.3	661.9	763.5	872.9	979.0	1072.7
130°	419.7	435.4	451.0	490.0	532.5	588.3	659.7	746.8	845.0	941.0	1029.2
132.5°	437.6	453.2	468.8	505.7	547.0	597.2	658.6	733.4	818.2	905.3	984.5
135°	453.2	468.8	484.5	520.2	559.2	603.9	657.5	721.1	793.7	867.3	941.0
137.5°	467.7	482.2	496.7	532.5	569.3	610.6	657.5	712.2	773.6	837.2	897.5
140°	480.0	494.5	509.0	542.5	577.1	615.1	656.4	704.4	754.6	808.2	859.5
142.5°	491.2	504.6	517.9	550.3	583.8	618.4	656.4	696.5	739.0	782.5	824.9
145°	503.4	515.7	528.0	558.1	589.4	620.6	654.1	689.8	724.4	761.3	795.9
147.5°	513.5	524.6	535.8	564.8	592.7	621.8	650.8	683.1	713.3	743.4	771.3
150°	523.5	533.6	543.6	569.3	595.0	620.6	647.4	674.2	701.0	725.6	749.0
152.5°	533.6	542.5	551.4	573.8	596.1	618.4	641.8	666.4	688.7	711.1	730.0
155°	542.5	550.8	559.2	578.2	597.2	616.2	635.1	656.4	677.6	695.4	712.2
157.5°	550.3	557.6	564.8	581.6	597.2	611.7	628.4	647.4	664.2	679.8	694.3
160°	558.1	564.2	570.4	583.8	597.2	608.4	621.8	637.4	651.9	664.2	676.4
162.5°	564.8	569.3	573.8	584.9	596.1	605.0	616.2	628.4	639.6	649.7	659.7
165°	569.3	572.6	576.0	586.0	593.8	600.5	608.4	618.4	627.3	635.1	643.0
167.5°	573.8	576.0	578.2	586.0	592.7	596.1	601.7	608.4	615.1	621.8	627.3
170°	576.0	577.6	579.3	584.9	590.5	592.7	596.1	600.5	606.1	609.5	613.9
172.5°	578.2	579.4	580.5	583.8	587.1	588.3	589.4	592.7	596.1	598.3	601.7
175°	579.3	579.9	580.5	582.7	584.9	583.8	584.9	586.0	589.4	590.5	591.6
177.5°	580.5	580.5	580.5	581.6	583.8	581.6	580.5	581.6	583.8	583.8	584.9
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	527.5	528.7	525.8	524.9	525.8	522.8	523.6	524.5	524.5	525.8	526.6
5°	496.8	495.1	492.2	491.3	490.5	491.7	490.9	492.2	492.6	495.6	496.0
7.5°	466.6	464.1	461.5	459.0	458.1	456.0	458.1	458.1	461.1	460.3	462.4
10°	430.9	430.5	427.1	425.8	424.1	420.7	425.4	424.1	426.2	430.1	430.9
12.5°	404.5	399.9	402.0	396.0	398.2	394.7	395.2	395.2	398.6	399.0	398.2
15°	379.4	375.6	370.1	367.5	366.2	364.5	370.1	370.5	368.0	373.9	371.8
17.5°	353.9	353.9	348.8	347.5	344.1	345.8	345.0	345.4	344.6	348.8	350.9
20°	331.8	329.7	328.0	328.4	324.1	323.3	322.4	323.3	326.3	329.2	330.1
22.5°	313.9	312.7	308.4	309.2	305.8	307.1	306.3	308.4	308.8	308.8	311.8
25°	296.9	295.2	295.6	293.9	292.7	292.7	291.4	292.7	294.4	295.2	295.6
27.5°	284.2	282.9	280.7	279.5	280.3	278.2	279.9	281.2	281.2	280.3	281.2
30°	268.8	269.7	269.7	265.4	267.1	266.3	267.6	268.4	268.4	268.8	268.0
32.5°	258.6	256.1	255.7	255.2	255.2	253.5	253.5	254.8	255.2	255.7	256.9
35°	245.0	245.0	242.9	244.2	242.5	242.9	242.5	242.9	243.7	242.5	243.7
37.5°	232.7	233.1	232.3	233.1	233.5	232.7	231.8	233.5	232.7	232.7	231.8
40°	222.0	221.6	222.0	222.0	222.0	222.5	221.6	221.6	221.6	220.8	219.9
42.5°	213.1	210.6	211.4	211.8	210.6	210.6	211.0	210.6	211.8	209.3	209.3
45°	200.4	199.5	199.9	199.9	200.8	199.5	200.4	200.8	199.5	199.1	198.2
47.5°	188.9	189.7	188.9	189.7	189.7	190.6	188.9	189.3	189.7	188.0	186.7
50°	177.4	177.4	178.7	178.2	178.7	177.8	177.8	177.4	177.8	177.0	175.7
52.5°	166.7	165.5	167.6	167.2	166.7	166.3	165.9	166.3	165.5	164.6	164.6
55°	153.6	153.6	154.8	155.3	155.3	154.4	153.6	154.0	153.6	153.1	152.7
57.5°	142.9	141.2	142.1	142.5	142.5	141.2	142.1	141.2	141.2	141.7	140.4
60°	129.3	129.3	128.5	129.7	129.7	128.9	128.9	129.3	128.5	128.0	127.6
62.5°	114.9	115.3	116.6	117.0	117.4	116.6	115.7	116.1	116.1	114.9	115.3
65°	102.5	103.4	105.1	104.6	103.8	104.2	103.4	103.8	102.5	102.9	101.7
67.5°	90.6	90.2	90.6	90.6	91.5	91.0	90.2	90.2	89.8	91.0	89.8
70°	77.8	77.8	77.8	77.8	78.3	78.7	77.8	77.0	77.4	76.6	76.1
72.5°	64.7	65.1	64.7	65.5	64.2	65.1	65.1	64.7	64.2	64.2	64.2
75°	52.3	53.2	51.9	52.3	51.9	52.7	52.3	52.3	51.5	51.0	51.5
77.5°	40.0	40.4	39.6	40.0	39.6	40.0	40.0	39.6	39.6	39.6	39.6
80°	28.5	28.9	28.5	28.1	27.6	28.5	27.6	28.1	28.5	28.1	28.9
82.5°	18.3	18.3	17.9	18.3	17.4	17.4	17.9	17.9	17.4	18.3	17.4
85°	8.9	8.9	9.8	8.9	8.5	8.5	8.5	8.9	8.5	9.4	8.9
87.5°	2.1	1.7	2.1	2.1	1.7	1.7	2.1	1.7	2.1	2.6	1.7
90°	36.2	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.2
92.5°	79.2	74.8	73.7	69.2	70.3	68.1	70.3	69.2	73.7	74.8	79.2
95°	165.2	152.9	138.4	129.5	126.1	127.3	126.1	129.5	138.4	152.9	165.2
97.5°	331.5	298.0	254.5	232.2	219.9	213.2	219.9	232.2	254.5	298.0	331.5
100°	660.2	592.7	500.1	452.1	419.7	399.6	419.7	452.1	500.1	592.7	660.2
102.5°	1116.2	1043.7	941.0	850.6	808.2	779.1	808.2	850.6	941.0	1043.7	1116.2
105°	1478.5	1460.1	1390.8	1321.6	1273.6	1258.0	1273.6	1321.6	1390.8	1460.1	1478.5
107.5°	1609.6	1632.0	1630.8	1620.8	1606.3	1580.6	1606.3	1620.8	1630.8	1632.0	1609.6
110°	1588.4	1634.2	1682.2	1703.4	1713.4	1712.3	1713.4	1703.4	1682.2	1634.2	1588.4

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1516.4	1570.6	1642.0	1681.1	1702.3	1710.1	1702.3	1681.1	1642.0	1570.6	1516.4
115°	1428.2	1485.7	1565.0	1616.3	1645.4	1655.4	1645.4	1616.3	1565.0	1485.7	1428.2
117.5°	1344.0	1398.7	1480.1	1534.8	1565.0	1572.8	1565.0	1534.8	1480.1	1398.7	1344.0
120°	1268.6	1319.4	1397.5	1450.0	1482.4	1493.5	1482.4	1450.0	1397.5	1319.4	1268.6
122.5°	1210.1	1254.7	1322.8	1374.1	1402.0	1410.9	1402.0	1374.1	1322.8	1254.7	1210.1
125°	1157.0	1198.9	1263.6	1306.0	1333.9	1342.8	1333.9	1306.0	1263.6	1198.9	1157.0
127.5°	1111.8	1150.9	1207.8	1248.0	1272.5	1279.2	1272.5	1248.0	1207.8	1150.9	1111.8
130°	1066.1	1102.9	1157.6	1195.5	1217.8	1226.8	1217.8	1195.5	1157.6	1102.9	1066.1
132.5°	1018.6	1052.6	1106.2	1144.2	1164.2	1172.1	1164.2	1144.2	1106.2	1052.6	1018.6
135°	972.2	1003.5	1051.5	1088.3	1108.4	1112.9	1108.4	1088.3	1051.5	1003.5	972.2
137.5°	925.4	953.3	999.0	1031.4	1049.3	1056.0	1049.3	1031.4	999.0	953.3	925.4
140°	884.0	908.6	944.3	973.4	990.1	996.8	990.1	973.4	944.3	908.6	884.0
142.5°	844.4	864.0	897.5	923.1	937.7	937.7	937.7	923.1	897.5	864.0	844.4
145°	812.1	828.3	855.0	874.0	885.2	888.5	885.2	874.0	855.0	828.3	812.1
147.5°	783.6	795.9	819.3	835.0	842.8	845.0	842.8	835.0	819.3	795.9	783.6
150°	759.0	769.1	785.8	799.2	805.9	807.0	805.9	799.2	785.8	769.1	759.0
152.5°	738.4	746.8	759.1	770.2	774.7	774.7	774.7	770.2	759.1	746.8	738.4
155°	718.3	724.4	736.7	744.5	749.0	746.8	749.0	744.5	736.7	724.4	718.3
157.5°	699.3	704.4	713.3	720.0	722.2	722.2	722.2	720.0	713.3	704.4	699.3
160°	680.3	684.3	692.1	697.7	698.8	698.8	698.8	697.7	692.1	684.3	680.3
162.5°	662.5	665.3	673.1	676.4	677.6	676.4	677.6	676.4	673.1	665.3	662.5
165°	645.2	647.4	651.9	656.4	656.4	655.2	656.4	656.4	651.9	647.4	645.2
167.5°	629.6	631.8	634.0	636.3	636.3	635.1	636.3	636.3	634.0	631.8	629.6
170°	615.0	616.2	617.3	620.6	619.5	617.3	619.5	620.6	617.3	616.2	615.0
172.5°	602.2	602.8	603.9	605.0	603.9	602.8	603.9	605.0	603.9	602.8	602.2
175°	592.2	592.7	592.7	593.8	592.7	590.5	592.7	593.8	592.7	592.7	592.2
177.5°	584.9	584.9	584.9	584.9	583.8	581.6	583.8	584.9	584.9	584.9	584.9
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	525.3	528.7	527.5	522.8	528.3	528.3	532.1	532.1	536.8	538.5	541.1
5°	495.6	498.1	500.2	498.1	501.9	507.9	511.3	514.3	520.7	523.2	527.0
7.5°	463.7	468.3	470.5	470.5	476.8	483.7	490.5	494.7	503.6	507.0	510.9
10°	432.6	438.1	442.4	442.0	452.6	456.9	465.4	475.1	484.1	489.2	494.7
12.5°	399.9	402.8	408.8	417.3	419.8	427.5	437.3	449.6	465.8	470.5	478.5
15°	372.6	380.7	385.4	389.2	395.2	402.4	413.0	425.0	441.1	451.3	459.8
17.5°	349.7	360.3	363.3	362.4	370.1	381.1	393.5	402.4	416.9	429.2	437.3
20°	330.9	335.2	340.3	342.4	348.4	360.3	372.2	382.4	394.3	404.1	413.5
22.5°	312.2	315.6	319.9	323.7	328.4	335.2	346.7	359.4	370.9	380.3	390.9
25°	296.9	299.0	302.9	305.8	310.9	315.6	323.7	337.7	351.4	356.9	366.2
27.5°	282.0	283.7	286.3	289.7	292.2	296.9	304.1	315.6	329.7	335.2	348.0
30°	268.8	270.1	272.7	274.4	275.6	281.2	286.7	295.6	306.3	313.9	323.3
32.5°	256.5	257.8	260.3	260.8	262.5	265.4	270.5	278.6	288.0	294.4	302.4
35°	242.9	243.7	246.3	247.1	248.4	251.0	254.8	260.8	269.3	273.9	281.2
37.5°	232.3	231.8	233.5	234.8	236.5	237.8	239.1	245.0	251.4	255.7	261.2
40°	220.8	219.9	220.3	222.0	222.9	224.6	224.6	230.6	234.8	238.2	242.5
42.5°	209.3	208.9	208.0	208.9	209.7	210.1	210.6	214.8	219.1	222.0	226.7
45°	197.8	197.4	196.5	196.9	196.9	197.8	199.1	200.8	203.8	206.3	208.9
47.5°	187.2	186.3	185.0	184.6	185.5	185.5	185.5	187.2	190.1	191.0	193.5
50°	176.1	174.8	173.1	172.3	172.3	171.9	172.7	173.1	175.7	176.5	178.7
52.5°	164.2	163.3	161.6	159.9	160.4	159.5	159.9	160.4	161.2	162.5	163.8
55°	152.3	150.6	149.3	148.9	147.6	147.6	146.3	148.0	147.6	148.0	149.7
57.5°	140.8	139.1	137.0	136.1	134.8	134.4	133.6	133.1	133.6	134.8	136.1
60°	127.2	126.3	125.1	123.8	122.9	121.7	120.8	120.8	120.4	120.4	120.8
62.5°	114.0	113.6	111.9	111.4	110.6	109.7	108.5	107.6	107.6	108.5	108.9
65°	101.2	100.8	99.5	99.1	97.0	96.1	95.7	95.3	94.4	94.4	94.4
67.5°	89.3	88.1	88.1	85.9	84.2	83.4	82.5	82.1	82.1	82.1	82.5
70°	76.1	76.1	74.9	73.6	71.9	72.3	71.0	69.8	69.8	68.9	69.3
72.5°	63.4	63.0	61.7	61.3	60.0	58.7	57.9	58.7	57.4	57.0	57.4
75°	51.0	50.6	49.8	48.9	49.3	48.1	46.8	46.4	46.4	45.5	45.5
77.5°	39.1	40.0	38.3	37.9	37.0	36.2	35.7	35.3	35.3	35.3	36.2
80°	27.2	27.6	27.6	26.8	27.2	25.9	25.9	25.9	24.7	25.1	25.5
82.5°	17.4	17.4	17.0	17.4	17.0	17.0	16.6	16.6	16.2	16.2	16.6
85°	9.8	9.4	8.9	9.8	9.4	9.4	8.9	8.9	8.9	8.9	8.9
87.5°	2.1	2.6	2.6	2.6	2.6	3.0	3.0	3.0	3.4	3.4	3.4
90°	35.7	33.5	35.7	36.8	38.0	36.8	30.1	22.3	16.7	15.0	13.4
92.5°	83.7	96.0	112.7	144.0	171.9	169.7	131.7	89.3	59.2	53.0	46.9
95°	177.5	224.4	292.5	382.9	437.6	387.3	257.9	160.7	109.4	96.0	82.6
97.5°	365.0	477.8	598.3	718.9	713.3	551.4	342.7	207.6	141.8	126.7	111.6
100°	727.8	880.7	1019.1	1042.6	881.8	607.2	366.1	229.9	170.8	155.2	139.5
102.5°	1188.8	1290.4	1294.9	1163.1	887.4	586.0	367.2	250.0	196.5	180.8	165.2
105°	1496.9	1482.4	1356.2	1124.1	827.1	557.0	372.8	273.5	221.0	205.4	189.8
107.5°	1587.3	1477.9	1290.4	1041.5	771.3	541.4	385.1	296.9	245.6	230.0	214.3
110°	1542.7	1399.8	1200.0	964.4	733.4	536.9	400.7	320.4	271.2	255.0	238.9

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1462.3	1307.1	1117.4	910.9	708.8	538.0	417.5	342.7	295.8	279.0	262.3
115°	1370.8	1224.5	1052.6	868.4	692.1	542.5	434.2	366.1	318.1	303.0	288.0
117.5°	1289.3	1153.1	999.0	839.4	683.1	549.2	452.1	387.3	342.7	327.0	311.4
120°	1217.8	1099.5	961.1	817.1	675.3	555.9	469.9	409.7	366.1	350.5	334.9
122.5°	1165.4	1054.9	931.0	798.1	670.9	563.7	485.6	430.9	390.7	374.5	358.3
125°	1115.1	1016.9	901.9	780.3	665.3	571.5	502.3	452.1	411.9	396.2	380.6
127.5°	1072.7	979.0	872.9	763.5	661.9	579.3	517.9	472.2	433.1	416.9	400.7
130°	1029.2	941.0	845.0	746.8	659.7	588.3	532.5	490.0	451.0	435.4	419.7
132.5°	984.5	905.3	818.2	733.4	658.6	597.2	547.0	505.7	468.8	453.2	437.6
135°	941.0	867.3	793.7	721.1	657.5	603.9	559.2	520.2	484.5	468.8	453.2
137.5°	897.5	837.2	773.6	712.2	657.5	610.6	569.3	532.5	496.7	482.2	467.7
140°	859.5	808.2	754.6	704.4	656.4	615.1	577.1	542.5	509.0	494.5	480.0
142.5°	824.9	782.5	739.0	696.5	656.4	618.4	583.8	550.3	517.9	504.6	491.2
145°	795.9	761.3	724.4	689.8	654.1	620.6	589.4	558.1	528.0	515.7	503.4
147.5°	771.3	743.4	713.3	683.1	650.8	621.8	592.7	564.8	535.8	524.6	513.5
150°	749.0	725.6	701.0	674.2	647.4	620.6	595.0	569.3	543.6	533.6	523.5
152.5°	730.0	711.1	688.7	666.4	641.8	618.4	596.1	573.8	551.4	542.5	533.6
155°	712.2	695.4	677.6	656.4	635.1	616.2	597.2	578.2	559.2	550.8	542.5
157.5°	694.3	679.8	664.2	647.4	628.4	611.7	597.2	581.6	564.8	557.6	550.3
160°	676.4	664.2	651.9	637.4	621.8	608.4	597.2	583.8	570.4	564.2	558.1
162.5°	659.7	649.7	639.6	628.4	616.2	605.0	596.1	584.9	573.8	569.3	564.8
165°	643.0	635.1	627.3	618.4	608.4	600.5	593.8	586.0	576.0	572.6	569.3
167.5°	627.3	621.8	615.1	608.4	601.7	596.1	592.7	586.0	578.2	576.0	573.8
170°	613.9	609.5	606.1	600.5	596.1	592.7	590.5	584.9	579.3	577.6	576.0
172.5°	601.7	598.3	596.1	592.7	589.4	588.3	587.1	583.8	580.5	579.4	578.2
175°	591.6	590.5	589.4	586.0	584.9	583.8	584.9	582.7	580.5	579.9	579.3
177.5°	584.9	583.8	583.8	581.6	580.5	581.6	583.8	581.6	580.5	580.5	580.5
180°	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5	580.5

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	553.4	553.4	553.4	553.4
2.5°	543.2	543.2	549.6	556.4
5°	531.3	534.3	544.5	553.8
7.5°	519.8	524.9	537.7	549.6
10°	505.8	512.6	528.3	542.4
12.5°	492.2	498.5	516.8	532.6
15°	473.0	481.1	500.7	520.2
17.5°	453.9	462.0	485.8	508.7
20°	431.3	442.0	468.8	499.4
22.5°	410.5	423.7	453.5	478.1
25°	387.5	407.9	435.6	467.5
27.5°	367.1	387.5	415.6	447.9
30°	344.1	365.0	393.9	423.7
32.5°	322.0	341.2	369.2	405.8
35°	299.0	317.3	344.6	381.6
37.5°	278.2	296.1	325.8	359.9
40°	257.8	276.5	302.0	336.0
42.5°	238.6	255.2	278.2	312.2
45°	221.2	233.1	254.4	286.3
47.5°	202.9	213.5	233.1	265.0
50°	185.9	194.8	211.8	241.6
52.5°	169.3	177.0	192.7	216.5
55°	154.4	161.6	173.1	196.5
57.5°	139.1	144.6	155.7	174.4
60°	124.2	129.3	138.2	153.6
62.5°	109.3	113.6	122.1	134.4
65°	96.1	99.5	105.9	116.6
67.5°	83.4	85.5	90.6	99.1
70°	71.0	72.7	77.0	83.8
72.5°	57.9	59.6	64.2	68.9
75°	46.8	47.2	50.6	54.4
77.5°	36.6	36.2	38.7	41.7
80°	25.1	26.4	28.5	29.8
82.5°	17.0	17.4	18.3	19.1
85°	9.4	9.8	9.8	11.1
87.5°	3.8	4.3	4.3	4.7
90°	11.2	8.9	4.5	1.1
92.5°	38.0	32.4	23.4	16.7
95°	64.7	54.7	43.5	39.1
97.5°	91.5	77.0	64.7	58.0
100°	117.2	99.3	89.3	86.0
102.5°	141.8	123.9	113.9	111.6
105°	165.2	148.5	140.6	136.2
107.5°	189.8	174.1	166.3	163.0
110°	215.4	200.9	194.2	189.8



TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	240.0	226.6	218.8	214.3
115°	265.7	252.3	245.6	240.0
117.5°	290.2	277.9	271.2	266.8
120°	312.6	302.5	295.8	291.3
122.5°	336.0	324.8	318.1	314.8
125°	358.3	344.9	338.2	334.9
127.5°	379.5	365.0	356.1	351.6
130°	397.4	381.8	370.6	366.1
132.5°	414.1	397.4	385.1	379.5
135°	427.5	410.8	397.4	392.9
137.5°	442.0	424.2	410.8	405.2
140°	455.4	437.6	424.2	419.7
142.5°	467.7	449.8	437.6	434.2
145°	481.1	464.4	453.2	448.7
147.5°	494.5	478.9	467.7	464.4
150°	506.8	492.3	483.3	480.0
152.5°	517.9	505.7	496.7	495.6
155°	530.2	517.9	511.2	510.1
157.5°	540.3	529.1	523.5	522.4
160°	549.2	540.3	535.8	534.7
162.5°	557.0	550.3	545.8	547.0
165°	563.7	557.0	554.8	555.9
167.5°	569.3	564.8	562.6	563.7
170°	573.8	570.4	569.3	571.5
172.5°	577.1	573.8	574.9	576.0
175°	579.3	577.1	578.2	579.3
177.5°	580.5	578.2	579.3	581.6
180°	580.5	580.5	580.5	580.5

TEST NUMBER: P998131

CATALOG NUMBER: SA2XXDIP-B290D1080UB50-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.12	10.77	11.28	11.91	13.52	7.61	8.26	8.77	9.41	11.02
	3H	10.92	11.50	12.08	12.65	14.27	8.94	9.52	10.11	10.68	12.30
	4H	11.07	11.63	12.25	12.78	14.41	9.39	9.95	10.57	11.10	12.73
	6H	11.11	11.62	12.29	12.77	14.41	9.69	10.20	10.87	11.35	12.99
	8H	11.08	11.56	12.27	12.73	14.37	9.77	10.25	10.95	11.42	13.05
	12H	11.04	11.50	12.23	12.66	14.31	9.80	10.26	10.99	11.42	13.08
4H	2H	10.13	10.69	11.32	11.84	13.47	8.03	8.58	9.22	9.74	11.37
	3H	11.10	11.56	12.29	12.73	14.38	9.47	9.93	10.66	11.11	12.75
	4H	11.36	11.79	12.55	12.95	14.61	10.00	10.42	11.19	11.59	13.25
	6H	11.48	11.85	12.68	13.03	14.68	10.37	10.73	11.56	11.92	13.57
	8H	11.48	11.82	12.67	13.00	14.66	10.47	10.81	11.67	11.99	13.66
	12H	11.43	11.74	12.64	12.93	14.60	10.52	10.83	11.73	12.02	13.69
8H	4H	11.36	11.70	12.55	12.88	14.54	10.13	10.47	11.32	11.64	13.31
	6H	11.53	11.81	12.74	13.03	14.69	10.55	10.83	11.77	12.05	13.72
	8H	11.56	11.80	12.77	13.00	14.68	10.70	10.94	11.92	12.14	13.83
	12H	11.53	11.75	12.75	12.94	14.66	10.79	11.00	12.01	12.20	13.91
12H	4H	11.31	11.61	12.51	12.80	14.47	10.09	10.40	11.30	11.59	13.26
	6H	11.51	11.75	12.72	12.95	14.63	10.55	10.80	11.77	11.99	13.68
	8H	11.53	11.74	12.75	12.94	14.65	10.70	10.91	11.92	12.11	13.82