

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998182

Luminaire Tested: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998182
REPORT IS A COMBINATION OF REPORTS P983922 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2543.0 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	48	48	43
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	45	43	41	41	41	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	36	36	32
4	75	65	57	52	69	60	54	48	52	47	43	44	40	37	36	33	31	31	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	27	27	24
6	64	52	44	39	59	49	42	37	42	37	33	36	32	28	30	27	24	24	24	22
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22	22	22	19
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	20	20	17
9	51	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18	18	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9054	9054	9054	9054
5°	9075	9654	9110	7680
10°	8971	10539	9027	6332
15°	8753	11116	8875	5334
20°	8617	10438	8617	4636
25°	8342	8967	8380	4146
30°	7890	7049	8041	3755
35°	7490	4874	7616	3435
40°	7029	3680	7110	3181
45°	6462	3025	6567	2906
50°	5971	2654	5983	2661
55°	5412	2262	5446	2394
60°	4816	1890	4882	2089
65°	4284	1537	4362	1784
70°	3750	1205	3846	1438
75°	3149	875	3273	1043
80°	2459	555	2635	620
85°	1610	280	1737	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9360 cd/sqm

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	2.1
10°-20°	158.6	6.2
20°-30°	230.1	9.0
30°-40°	242.6	9.5
40°-50°	214.7	8.4
50°-60°	171.4	6.7
60°-70°	116.4	4.6
70°-80°	59.6	2.3
80°-90°	15.3	0.6
90°-100°	71.6	2.8
100°-110°	252.3	9.9
110°-120°	265.0	10.4
120°-130°	218.0	8.6
130°-140°	175.1	6.9
140°-150°	132.3	5.2
150°-160°	93.0	3.7
160°-170°	54.7	2.2
170°-180°	17.8	0.7
0°-30°	443.2	17.4
0°-40°	685.8	27.0
0°-60°	1071.9	42.2
0°-90°	1263.2	49.7
90°-120°	588.9	23.2
90°-150°	1114.3	43.8
90°-180°	1280.0	50.3
0°-180°	2543.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	572	572	572	572	572	
5°	572	639	575	508	572	54
15°	538	785	545	377	538	152
25°	483	654	485	302	483	221
35°	394	356	401	251	394	247
45°	296	215	301	206	296	230
55°	203	151	204	160	203	181
65°	120	93	123	108	120	120
75°	56	46	58	54	56	60
85°	11	12	12	9	11	13
90°	0	12	0	12	0	1
95°	12	40	12	40	12	13
105°	43	398	43	398	43	46
115°	76	524	76	524	76	75
125°	106	425	106	425	106	94
135°	124	352	124	352	124	96
145°	142	281	142	281	142	89
155°	162	236	162	236	162	74
165°	176	208	176	208	176	50
175°	183	187	183	187	183	17
180°	184	184	184	184	184	

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	575.1	576.4	578.6	579.0	583.4	586.9	590.9	590.9	592.2	591.8	588.3
5°	572.4	576.4	582.1	586.9	594.9	598.4	603.7	607.6	611.1	613.8	613.3
7.5°	568.0	575.1	583.4	592.7	603.2	609.4	616.8	623.9	628.7	633.1	636.2
10°	560.6	572.4	583.9	596.2	609.8	618.2	627.0	636.2	643.7	652.0	659.9
12.5°	550.5	567.6	581.7	597.9	614.6	623.9	637.9	645.0	659.5	680.6	686.3
15°	537.7	561.0	574.2	594.9	616.8	624.3	643.7	655.1	685.0	698.2	714.0
17.5°	525.8	551.8	569.4	593.1	614.6	629.2	648.1	671.4	696.4	715.3	732.9
20°	516.2	541.2	562.3	588.7	616.0	634.4	654.2	682.4	709.6	729.0	742.6
22.5°	494.2	526.3	550.9	580.4	613.3	638.8	657.7	688.5	718.0	729.8	741.7
25°	483.2	510.9	539.5	572.9	611.6	641.9	658.2	692.5	718.4	722.8	725.4
27.5°	463.0	494.2	527.6	565.8	611.1	636.6	657.3	688.5	709.2	706.1	698.2
30°	437.9	476.2	513.1	554.4	605.0	632.7	652.0	680.6	691.1	675.3	661.2
32.5°	419.4	455.5	496.4	544.3	597.9	624.3	643.2	665.6	667.8	639.3	615.5
35°	394.4	434.4	480.5	531.1	586.1	609.8	627.4	641.0	630.5	590.5	562.3
37.5°	372.0	411.5	460.8	512.2	569.8	593.1	607.2	609.4	583.4	548.3	506.9
40°	347.3	388.2	439.7	493.7	551.8	572.0	580.8	574.2	536.8	495.9	448.0
42.5°	322.7	363.2	418.6	474.0	528.9	546.1	549.6	531.5	485.8	437.9	382.5
45°	295.9	338.1	393.5	449.3	502.5	512.2	512.6	486.7	432.6	382.5	331.1
47.5°	273.9	313.0	368.0	423.8	468.7	475.3	472.6	442.7	383.8	327.5	282.7
50°	249.7	287.1	341.6	396.6	434.8	436.6	430.0	387.3	329.7	278.3	242.7
52.5°	223.8	261.6	311.7	364.5	398.8	396.1	383.4	337.7	283.6	240.9	213.7
55°	203.1	236.5	283.6	335.0	359.2	351.7	337.7	291.1	248.4	212.4	188.6
57.5°	180.3	209.7	255.9	300.7	314.8	307.8	293.7	250.2	210.6	183.3	167.5
60°	158.7	185.5	226.0	263.4	274.3	266.9	250.6	211.5	182.9	160.0	148.2
62.5°	138.9	162.2	196.1	230.4	234.8	227.3	213.2	181.6	157.0	138.9	130.1
65°	120.5	142.4	169.7	195.6	199.6	191.7	177.2	154.3	133.7	122.2	113.9
67.5°	102.4	120.0	144.2	163.1	165.3	157.8	146.0	127.5	114.8	102.4	96.3
70°	86.6	99.8	118.7	134.1	135.0	127.9	121.8	105.1	95.4	86.6	81.8
72.5°	71.2	80.5	95.0	106.4	106.8	102.4	96.7	86.2	77.8	71.7	66.8
75°	56.3	64.2	73.0	83.1	82.7	79.1	74.7	68.1	61.1	57.2	55.0
77.5°	43.1	47.9	55.0	61.6	61.6	59.8	57.2	52.3	47.9	44.0	41.8
80°	30.8	33.9	39.6	41.8	42.6	42.2	40.0	36.5	34.7	31.7	30.8
82.5°	19.8	22.0	24.6	26.8	28.1	27.3	26.8	25.1	22.4	21.5	20.7
85°	11.4	12.3	13.6	14.9	15.4	14.9	15.8	14.5	13.2	13.2	12.8
87.5°	4.8	5.3	6.2	6.2	6.6	6.6	6.2	6.6	6.6	6.2	5.7
90°	0.4	1.4	2.8	3.5	4.2	4.8	5.3	7.1	9.5	11.7	12.0
92.5°	5.3	7.4	10.2	12.0	14.8	16.8	18.7	28.3	41.7	53.7	54.4
95°	12.4	13.8	17.3	20.5	26.2	30.4	34.6	50.9	81.6	122.6	138.5
97.5°	18.4	20.5	24.4	29.0	35.3	40.1	44.9	65.7	108.5	174.6	225.8
100°	27.2	28.3	31.5	37.1	44.2	49.2	54.1	72.8	115.9	192.3	279.2
102.5°	35.3	36.0	39.2	44.9	52.3	57.2	62.2	79.2	116.3	185.5	281.0
105°	43.1	44.5	47.0	52.3	60.1	65.0	70.0	86.6	118.0	176.4	261.9
107.5°	51.6	52.7	55.1	60.1	67.9	72.8	77.8	94.0	121.9	171.4	244.2
110°	60.1	61.5	63.6	68.2	75.6	80.8	85.9	101.4	126.9	170.0	232.2

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	67.9	69.3	71.7	76.0	83.1	88.4	93.7	108.5	132.2	170.3	224.4
115°	76.0	77.8	79.9	84.1	91.2	96.0	100.7	115.9	137.5	171.8	219.1
117.5°	84.5	85.9	88.0	91.9	98.6	103.6	108.5	122.6	143.1	173.9	216.3
120°	92.2	93.7	95.8	99.0	106.0	111.0	115.9	129.7	148.8	176.0	213.8
122.5°	99.7	100.7	102.8	106.4	113.4	118.6	123.7	136.4	153.7	178.5	212.4
125°	106.0	107.1	109.2	113.4	120.5	125.4	130.4	143.1	159.0	180.9	210.6
127.5°	111.3	112.7	115.6	120.2	126.9	132.0	137.1	149.5	164.0	183.4	209.6
130°	115.9	117.3	120.9	125.8	132.9	137.9	142.8	155.1	168.6	186.2	208.9
132.5°	120.2	121.9	125.8	131.1	138.5	143.4	148.4	160.1	173.2	189.1	208.5
135°	124.4	125.8	130.1	135.4	143.5	148.4	153.4	164.7	177.1	191.2	208.2
137.5°	128.3	130.1	134.3	140.0	148.1	152.7	157.3	168.6	180.2	193.3	208.2
140°	132.9	134.3	138.5	144.2	152.0	156.6	161.2	171.8	182.7	194.7	207.8
142.5°	137.5	138.5	142.4	148.1	155.5	159.8	164.0	174.2	184.8	195.8	207.8
145°	142.1	143.5	147.0	152.3	159.4	163.3	167.2	176.7	186.6	196.5	207.1
147.5°	147.0	148.1	151.6	156.6	162.6	166.1	169.6	178.8	187.7	196.9	206.0
150°	152.0	153.0	155.9	160.5	165.8	169.0	172.1	180.2	188.4	196.5	205.0
152.5°	156.9	157.3	160.1	164.0	168.9	171.8	174.6	181.7	188.7	195.8	203.2
155°	161.5	161.9	164.0	167.9	171.8	174.4	177.1	183.1	189.1	195.1	201.1
157.5°	165.4	165.8	167.5	171.1	174.2	176.5	178.8	184.1	189.1	193.7	199.0
160°	169.3	169.6	171.1	173.9	176.7	178.6	180.6	184.8	189.1	192.6	196.9
162.5°	173.2	172.8	174.2	176.4	178.8	180.2	181.7	185.2	188.7	191.6	195.1
165°	176.0	175.6	176.4	178.5	180.2	181.3	182.4	185.5	188.0	190.1	192.6
167.5°	178.5	178.1	178.8	180.2	181.7	182.4	183.1	185.5	187.7	188.7	190.5
170°	180.9	180.2	180.6	181.7	182.4	182.9	183.4	185.2	187.0	187.7	188.7
172.5°	182.4	182.0	181.7	182.7	183.1	183.4	183.8	184.8	185.9	186.2	186.6
175°	183.4	183.1	182.7	183.4	183.4	183.6	183.8	184.5	185.2	184.8	185.2
177.5°	184.1	183.4	183.1	183.8	183.8	183.8	183.8	184.1	184.8	184.1	183.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	594.4	594.9	595.7	600.1	602.3	602.8	601.0	605.0	606.3	605.0	604.1
5°	622.6	625.2	630.5	636.2	635.7	636.2	638.8	641.5	642.3	638.8	640.1
7.5°	647.2	652.5	658.2	667.0	667.0	671.4	673.1	675.3	680.6	678.0	677.1
10°	675.3	682.4	692.9	707.0	707.4	711.8	716.2	723.2	725.4	723.7	724.6
12.5°	710.5	724.1	725.0	740.4	747.4	748.3	755.3	754.0	758.4	758.4	765.9
15°	725.9	747.0	758.9	773.8	778.2	772.9	778.6	784.8	785.2	785.2	784.8
17.5°	753.6	761.9	773.8	781.7	783.5	783.5	783.9	786.6	784.8	781.3	783.9
20°	759.3	762.8	767.2	766.3	767.2	762.8	758.4	754.0	754.5	752.3	758.9
22.5°	748.7	747.9	737.7	731.2	731.2	722.4	714.0	710.1	706.1	707.4	709.6
25°	722.4	708.7	696.4	686.7	684.6	670.5	659.0	655.5	648.9	654.2	655.1
27.5°	680.2	664.8	645.0	636.6	625.2	619.5	611.6	601.0	587.4	595.3	594.0
30°	634.9	612.0	595.7	575.5	557.5	556.2	541.2	523.6	516.6	516.6	520.6
32.5°	584.3	554.0	530.2	501.7	484.1	476.6	458.6	441.0	444.9	431.7	436.6
35°	525.4	485.4	455.5	427.8	414.6	405.8	382.5	372.8	362.3	356.1	367.6
37.5°	469.1	423.0	384.7	354.4	349.5	333.7	317.9	311.7	305.6	308.2	307.8
40°	400.5	359.6	325.3	301.6	293.3	285.8	275.2	267.8	263.8	266.0	266.4
42.5°	338.5	304.2	278.7	262.0	255.0	249.7	244.5	238.3	237.0	237.0	238.7
45°	290.6	262.5	245.3	231.7	227.7	223.8	219.8	217.2	216.3	214.6	215.9
47.5°	252.4	229.9	219.4	209.3	204.9	204.0	200.5	199.2	197.4	197.0	197.4
50°	220.3	206.2	196.5	190.8	187.7	186.4	184.7	182.0	181.1	183.3	182.5
52.5°	197.8	184.7	179.4	173.7	171.9	170.1	167.5	167.9	167.5	166.6	166.6
55°	175.4	167.1	161.8	157.4	157.0	155.2	153.0	152.1	151.7	150.8	152.1
57.5°	157.4	150.8	146.0	142.0	140.3	140.3	138.1	136.3	136.3	135.9	136.3
60°	139.4	132.8	129.7	125.7	124.4	124.0	122.7	121.8	120.5	120.5	120.5
62.5°	122.7	117.4	113.9	110.4	110.8	108.6	106.8	106.0	106.0	106.4	106.4
65°	106.8	103.3	98.9	95.8	95.0	94.5	93.6	93.2	91.9	92.8	92.8
67.5°	92.3	87.5	84.9	83.5	82.2	81.8	80.9	80.0	79.6	79.1	80.0
70°	77.8	73.9	71.7	70.8	69.5	69.0	68.6	67.3	67.7	68.1	68.6
72.5°	64.6	61.1	60.7	58.0	58.0	58.0	56.3	57.2	56.7	55.8	56.7
75°	51.0	49.2	48.4	47.0	47.5	47.0	46.6	45.3	45.3	45.7	46.2
77.5°	40.4	38.7	38.3	36.9	36.1	36.9	36.1	35.6	35.6	36.1	36.1
80°	29.9	29.0	27.7	27.7	27.7	27.3	27.3	27.3	26.8	26.4	26.8
82.5°	19.8	19.8	19.3	18.9	19.3	18.5	18.9	18.9	18.9	18.9	18.9
85°	12.8	12.3	12.3	11.9	11.9	11.9	12.3	11.4	11.4	11.9	11.9
87.5°	5.7	5.7	5.7	6.2	5.7	5.7	5.7	6.2	5.7	5.7	5.7
90°	11.7	11.3	10.6	11.3	11.5	11.7	11.7	11.7	11.7	11.7	11.7
92.5°	45.6	35.7	30.4	26.5	25.1	23.7	23.3	21.9	22.3	21.6	22.3
95°	121.2	92.6	71.0	56.2	52.3	48.4	43.8	41.0	39.9	40.3	39.9
97.5°	227.6	189.4	151.3	115.6	105.0	94.4	80.6	73.5	69.6	67.5	69.6
100°	330.1	322.7	278.8	230.4	209.0	187.7	158.3	143.1	132.9	126.5	132.9
102.5°	368.3	410.0	408.5	376.4	353.4	330.4	297.9	269.3	255.9	246.7	255.9
105°	355.9	429.4	469.3	473.9	468.1	462.3	440.4	418.4	403.2	398.3	403.2
107.5°	329.7	408.5	467.9	502.6	509.6	516.7	516.3	513.2	508.6	500.4	508.6
110°	305.4	379.9	443.2	488.4	502.9	517.4	532.6	539.3	542.5	542.1	542.5

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	288.4	353.8	413.8	463.0	480.2	497.3	519.9	532.2	539.0	541.4	539.0
115°	275.0	333.3	387.7	434.0	452.2	470.4	495.5	511.7	520.9	524.1	520.9
117.5°	265.8	316.3	365.1	408.2	425.5	442.8	468.6	485.9	495.5	498.0	495.5
120°	258.7	304.3	348.1	385.6	401.6	417.7	442.5	459.1	469.3	472.9	469.3
122.5°	252.7	294.7	334.0	369.0	383.1	397.2	418.8	435.1	443.9	446.7	443.9
125°	247.0	285.6	322.0	353.1	366.4	379.6	400.1	413.5	422.3	425.2	422.3
127.5°	241.7	276.4	309.9	339.6	352.0	364.4	382.4	395.1	402.9	405.0	402.9
130°	236.4	267.5	297.9	325.8	337.5	349.2	366.5	378.5	385.6	388.4	385.6
132.5°	232.2	259.1	286.6	311.7	322.5	333.3	350.2	362.3	368.6	371.1	368.6
135°	228.3	251.3	274.6	297.9	307.8	317.7	332.9	344.6	350.9	352.4	350.9
137.5°	225.5	244.9	265.1	284.1	293.0	301.8	316.3	326.6	332.2	334.3	332.2
140°	223.0	238.9	255.9	272.1	279.9	287.7	299.0	308.2	313.5	315.6	313.5
142.5°	220.5	234.0	247.7	261.2	267.4	273.5	284.1	292.3	296.9	296.9	296.9
145°	218.4	229.4	241.0	252.0	257.1	262.2	270.7	276.7	280.3	281.3	280.3
147.5°	216.3	225.8	235.4	244.2	248.1	252.0	259.4	264.4	266.8	267.5	266.8
150°	213.5	221.9	229.7	237.1	240.3	243.5	248.8	253.0	255.2	255.5	255.2
152.5°	211.0	218.1	225.1	231.1	233.8	236.4	240.3	243.9	245.3	245.3	245.3
155°	207.8	214.5	220.2	225.5	227.4	229.4	233.3	235.7	237.1	236.4	237.1
157.5°	205.0	210.3	215.2	219.8	221.4	223.0	225.8	228.0	228.7	228.7	228.7
160°	201.8	206.4	210.3	214.2	215.4	216.6	219.1	220.9	221.2	221.2	221.2
162.5°	199.0	202.5	205.7	208.9	209.8	210.6	213.1	214.2	214.5	214.2	214.5
165°	195.8	198.6	201.1	203.6	204.3	205.0	206.4	207.8	207.8	207.5	207.8
167.5°	192.6	194.7	196.9	198.6	199.3	200.0	200.7	201.4	201.4	201.1	201.4
170°	190.1	191.9	193.0	194.4	194.8	195.1	195.4	196.5	196.1	195.4	196.1
172.5°	187.7	188.7	189.4	190.5	190.6	190.8	191.2	191.6	191.2	190.8	191.2
175°	185.5	186.6	187.0	187.3	187.5	187.7	187.7	188.0	187.7	187.0	187.7
177.5°	184.1	184.8	184.8	185.2	185.2	185.2	185.2	185.2	184.8	184.1	184.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	606.3	603.2	600.6	601.0	603.2	601.5	597.1	591.3	589.1	586.5	589.1
5°	642.8	640.1	634.9	635.3	634.0	632.2	625.2	616.4	616.4	609.4	608.5
7.5°	678.8	674.9	671.4	670.5	665.6	662.1	656.0	643.7	638.8	630.5	625.6
10°	719.3	716.2	712.2	707.4	704.8	698.6	688.5	670.5	661.7	650.3	641.9
12.5°	760.2	759.7	750.9	741.3	740.8	731.2	724.1	699.9	688.1	672.7	652.9
15°	786.1	783.9	779.1	774.2	775.6	765.0	749.2	720.6	712.7	694.2	673.1
17.5°	785.7	785.7	784.4	783.5	782.2	779.1	770.3	751.4	738.6	715.3	695.5
20°	760.6	766.3	767.6	767.2	771.6	773.8	773.4	761.5	751.4	730.7	710.5
22.5°	710.5	723.7	729.4	732.9	742.1	747.0	758.4	754.0	751.4	736.0	718.8
25°	663.9	668.3	685.4	686.3	699.1	710.9	722.4	729.8	739.5	733.8	719.3
27.5°	603.7	613.8	626.1	635.3	637.9	662.1	681.0	695.1	717.1	718.8	714.0
30°	535.5	540.3	560.6	572.9	586.9	604.5	631.8	656.0	675.8	693.8	699.9
32.5°	452.4	472.2	484.1	499.0	511.3	542.5	576.0	607.2	630.0	660.4	673.6
35°	376.3	391.7	412.0	418.1	440.5	466.9	510.4	550.5	585.2	616.0	642.8
37.5°	313.5	325.8	347.3	357.0	370.2	404.0	440.5	490.2	532.0	569.8	603.2
40°	270.4	279.6	295.9	299.0	310.0	340.7	370.2	416.8	472.2	523.2	559.7
42.5°	240.9	245.3	256.3	260.3	267.3	288.0	314.4	358.3	409.8	462.5	514.0
45°	219.8	222.9	229.5	233.0	241.8	251.0	272.6	307.8	348.2	401.4	456.8
47.5°	200.9	204.9	207.5	209.7	214.6	224.7	238.7	264.7	303.4	352.2	405.8
50°	185.1	186.4	191.3	191.7	194.8	201.4	214.6	230.4	261.2	300.7	352.6
52.5°	169.3	170.6	173.7	176.7	178.1	183.3	192.1	205.3	228.2	259.4	305.6
55°	153.4	155.2	158.3	160.5	161.8	166.2	171.5	184.2	202.2	224.2	262.0
57.5°	137.6	141.6	142.4	143.8	146.0	150.8	155.6	163.1	177.2	197.4	225.1
60°	122.7	124.0	127.1	128.4	130.6	133.2	139.4	145.1	155.2	171.0	196.1
62.5°	107.3	110.4	111.7	113.0	114.8	117.8	121.8	127.9	136.7	149.5	169.3
65°	94.1	94.5	97.2	98.9	100.7	102.9	106.8	112.6	117.8	129.7	144.2
67.5°	81.3	82.2	83.1	84.9	87.1	89.3	92.8	95.8	102.4	110.4	121.8
70°	69.0	69.0	71.2	72.5	72.1	74.7	77.4	80.9	85.7	93.2	102.4
72.5°	58.0	57.6	59.4	59.8	60.7	62.4	64.2	67.7	70.3	76.1	83.1
75°	46.2	47.0	47.9	47.9	49.2	50.6	52.3	54.1	57.2	60.7	65.9
77.5°	36.5	36.5	37.4	37.8	39.1	38.7	40.4	42.2	44.4	47.5	51.4
80°	26.8	27.7	27.7	27.7	28.1	28.6	30.3	31.7	33.0	35.2	36.9
82.5°	18.9	18.9	19.8	19.8	19.8	20.7	20.7	21.1	22.0	23.3	24.6
85°	11.9	11.9	11.9	12.3	11.9	12.3	13.2	12.8	13.2	14.1	14.1
87.5°	5.7	5.7	5.7	5.7	5.7	6.2	5.7	6.2	6.6	6.6	6.6
90°	11.7	11.7	11.7	11.5	11.3	10.6	11.3	11.7	12.0	11.7	9.5
92.5°	21.9	23.3	23.7	25.1	26.5	30.4	35.7	45.6	54.4	53.7	41.7
95°	41.0	43.8	48.4	52.3	56.2	71.0	92.6	121.2	138.5	122.6	81.6
97.5°	73.5	80.6	94.4	105.0	115.6	151.3	189.4	227.6	225.8	174.6	108.5
100°	143.1	158.3	187.7	209.0	230.4	278.8	322.7	330.1	279.2	192.3	115.9
102.5°	269.3	297.9	330.4	353.4	376.4	408.5	410.0	368.3	281.0	185.5	116.3
105°	418.4	440.4	462.3	468.1	473.9	469.3	429.4	355.9	261.9	176.4	118.0
107.5°	513.2	516.3	516.7	509.6	502.6	467.9	408.5	329.7	244.2	171.4	121.9
110°	539.3	532.6	517.4	502.9	488.4	443.2	379.9	305.4	232.2	170.0	126.9

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	532.2	519.9	497.3	480.2	463.0	413.8	353.8	288.4	224.4	170.3	132.2
115°	511.7	495.5	470.4	452.2	434.0	387.7	333.3	275.0	219.1	171.8	137.5
117.5°	485.9	468.6	442.8	425.5	408.2	365.1	316.3	265.8	216.3	173.9	143.1
120°	459.1	442.5	417.7	401.6	385.6	348.1	304.3	258.7	213.8	176.0	148.8
122.5°	435.1	418.8	397.2	383.1	369.0	334.0	294.7	252.7	212.4	178.5	153.7
125°	413.5	400.1	379.6	366.4	353.1	322.0	285.6	247.0	210.6	180.9	159.0
127.5°	395.1	382.4	364.4	352.0	339.6	309.9	276.4	241.7	209.6	183.4	164.0
130°	378.5	366.5	349.2	337.5	325.8	297.9	267.5	236.4	208.9	186.2	168.6
132.5°	362.3	350.2	333.3	322.5	311.7	286.6	259.1	232.2	208.5	189.1	173.2
135°	344.6	332.9	317.7	307.8	297.9	274.6	251.3	228.3	208.2	191.2	177.1
137.5°	326.6	316.3	301.8	293.0	284.1	265.1	244.9	225.5	208.2	193.3	180.2
140°	308.2	299.0	287.7	279.9	272.1	255.9	238.9	223.0	207.8	194.7	182.7
142.5°	292.3	284.1	273.5	267.4	261.2	247.7	234.0	220.5	207.8	195.8	184.8
145°	276.7	270.7	262.2	257.1	252.0	241.0	229.4	218.4	207.1	196.5	186.6
147.5°	264.4	259.4	252.0	248.1	244.2	235.4	225.8	216.3	206.0	196.9	187.7
150°	253.0	248.8	243.5	240.3	237.1	229.7	221.9	213.5	205.0	196.5	188.4
152.5°	243.9	240.3	236.4	233.8	231.1	225.1	218.1	211.0	203.2	195.8	188.7
155°	235.7	233.3	229.4	227.4	225.5	220.2	214.5	207.8	201.1	195.1	189.1
157.5°	228.0	225.8	223.0	221.4	219.8	215.2	210.3	205.0	199.0	193.7	189.1
160°	220.9	219.1	216.6	215.4	214.2	210.3	206.4	201.8	196.9	192.6	189.1
162.5°	214.2	213.1	210.6	209.8	208.9	205.7	202.5	199.0	195.1	191.6	188.7
165°	207.8	206.4	205.0	204.3	203.6	201.1	198.6	195.8	192.6	190.1	188.0
167.5°	201.4	200.7	200.0	199.3	198.6	196.9	194.7	192.6	190.5	188.7	187.7
170°	196.5	195.4	195.1	194.8	194.4	193.0	191.9	190.1	188.7	187.7	187.0
172.5°	191.6	191.2	190.8	190.6	190.5	189.4	188.7	187.7	186.6	186.2	185.9
175°	188.0	187.7	187.7	187.5	187.3	187.0	186.6	185.5	185.2	184.8	185.2
177.5°	185.2	185.2	185.2	185.2	185.2	184.8	184.8	184.1	183.8	184.1	184.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	586.9	584.7	583.4	584.3	581.7	575.1	575.1	577.3	574.6	572.0	568.0
5°	603.2	598.8	596.2	595.7	589.6	579.0	576.8	574.6	568.9	562.8	556.2
7.5°	619.0	611.1	606.7	603.7	594.9	581.2	575.5	570.7	561.4	552.2	543.9
10°	632.2	620.8	615.5	610.7	599.3	582.1	572.9	564.1	552.2	540.3	529.8
12.5°	642.8	629.6	623.0	616.0	601.9	579.5	568.0	554.0	542.1	526.3	515.7
15°	660.4	633.1	627.0	620.4	605.9	575.1	561.0	545.2	528.9	507.8	496.4
17.5°	674.4	637.9	637.5	623.4	604.5	573.3	551.8	531.1	513.5	492.4	474.4
20°	682.8	645.4	638.4	623.9	600.1	561.4	539.0	516.2	497.3	471.8	453.7
22.5°	689.8	656.0	637.5	619.9	590.9	557.5	524.5	503.0	477.0	449.3	432.2
25°	692.5	658.2	638.8	618.6	584.3	546.1	508.7	485.4	456.4	431.3	408.0
27.5°	692.9	657.7	634.0	612.9	575.1	531.1	492.9	468.2	436.1	407.1	383.8
30°	688.5	652.9	631.4	608.5	566.3	517.5	473.5	446.3	412.0	382.9	358.8
32.5°	675.3	643.2	625.6	600.6	554.9	498.6	455.0	424.7	388.7	360.1	336.8
35°	653.3	631.4	612.0	588.7	539.9	481.0	436.6	401.0	364.5	337.2	315.2
37.5°	626.1	614.2	596.2	573.3	522.8	465.2	415.9	376.3	339.9	313.5	291.9
40°	589.1	592.2	574.6	554.0	502.5	443.6	389.1	351.3	317.0	292.4	271.3
42.5°	549.1	561.9	551.8	532.0	480.1	419.9	369.3	327.5	294.1	268.6	251.0
45°	506.0	528.0	521.9	507.4	456.8	394.8	341.2	300.7	271.3	246.6	231.3
47.5°	459.0	490.2	490.2	479.7	430.9	369.8	317.0	275.7	246.6	229.1	214.1
50°	411.1	446.3	452.0	444.9	401.8	341.2	287.5	250.2	225.1	208.0	197.0
52.5°	361.0	401.8	412.4	408.9	371.1	313.9	263.4	226.9	204.0	189.1	179.4
55°	313.0	360.5	372.0	373.3	338.1	284.0	236.5	204.4	182.5	172.3	164.0
57.5°	267.8	313.5	326.2	328.4	304.7	256.8	211.5	183.3	163.6	155.2	148.6
60°	229.1	267.3	284.0	288.9	268.2	225.1	188.2	160.9	146.0	138.1	131.9
62.5°	197.4	228.2	245.8	247.1	237.9	197.4	164.0	141.1	128.4	121.3	118.3
65°	166.6	194.3	204.9	210.2	202.7	171.0	141.6	122.7	112.6	106.4	103.3
67.5°	142.0	159.6	168.4	175.4	167.9	144.2	120.5	105.1	97.6	91.4	89.7
70°	116.5	131.0	137.6	144.6	138.1	120.0	102.9	88.8	82.2	77.4	75.2
72.5°	93.2	104.6	110.8	115.2	111.2	96.3	82.2	72.5	67.7	64.2	62.9
75°	73.9	81.8	85.3	88.4	86.6	75.2	66.4	58.5	54.1	51.0	50.1
77.5°	56.3	62.0	65.9	66.8	64.6	57.2	49.7	44.8	41.3	39.6	38.7
80°	40.0	43.5	45.7	47.0	44.8	41.8	36.5	33.0	29.9	27.7	27.3
82.5°	26.8	28.6	30.3	29.9	29.0	26.4	23.3	21.5	20.2	18.5	18.5
85°	15.4	15.8	16.7	17.1	16.7	14.9	13.2	12.3	11.4	10.1	10.1
87.5°	6.6	7.0	7.0	7.5	6.6	6.6	5.7	4.8	4.8	4.4	4.0
90°	7.1	5.3	4.8	4.2	3.5	2.8	1.4	0.4	1.4	2.8	3.5
92.5°	28.3	18.7	16.8	14.8	12.0	10.2	7.4	5.3	7.4	10.2	12.0
95°	50.9	34.6	30.4	26.2	20.5	17.3	13.8	12.4	13.8	17.3	20.5
97.5°	65.7	44.9	40.1	35.3	29.0	24.4	20.5	18.4	20.5	24.4	29.0
100°	72.8	54.1	49.2	44.2	37.1	31.5	28.3	27.2	28.3	31.5	37.1
102.5°	79.2	62.2	57.2	52.3	44.9	39.2	36.0	35.3	36.0	39.2	44.9
105°	86.6	70.0	65.0	60.1	52.3	47.0	44.5	43.1	44.5	47.0	52.3
107.5°	94.0	77.8	72.8	67.9	60.1	55.1	52.7	51.6	52.7	55.1	60.1
110°	101.4	85.9	80.8	75.6	68.2	63.6	61.5	60.1	61.5	63.6	68.2

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	108.5	93.7	88.4	83.1	76.0	71.7	69.3	67.9	69.3	71.7	76.0
115°	115.9	100.7	96.0	91.2	84.1	79.9	77.8	76.0	77.8	79.9	84.1
117.5°	122.6	108.5	103.6	98.6	91.9	88.0	85.9	84.5	85.9	88.0	91.9
120°	129.7	115.9	111.0	106.0	99.0	95.8	93.7	92.2	93.7	95.8	99.0
122.5°	136.4	123.7	118.6	113.4	106.4	102.8	100.7	99.7	100.7	102.8	106.4
125°	143.1	130.4	125.4	120.5	113.4	109.2	107.1	106.0	107.1	109.2	113.4
127.5°	149.5	137.1	132.0	126.9	120.2	115.6	112.7	111.3	112.7	115.6	120.2
130°	155.1	142.8	137.9	132.9	125.8	120.9	117.3	115.9	117.3	120.9	125.8
132.5°	160.1	148.4	143.4	138.5	131.1	125.8	121.9	120.2	121.9	125.8	131.1
135°	164.7	153.4	148.4	143.5	135.4	130.1	125.8	124.4	125.8	130.1	135.4
137.5°	168.6	157.3	152.7	148.1	140.0	134.3	130.1	128.3	130.1	134.3	140.0
140°	171.8	161.2	156.6	152.0	144.2	138.5	134.3	132.9	134.3	138.5	144.2
142.5°	174.2	164.0	159.8	155.5	148.1	142.4	138.5	137.5	138.5	142.4	148.1
145°	176.7	167.2	163.3	159.4	152.3	147.0	143.5	142.1	143.5	147.0	152.3
147.5°	178.8	169.6	166.1	162.6	156.6	151.6	148.1	147.0	148.1	151.6	156.6
150°	180.2	172.1	169.0	165.8	160.5	155.9	153.0	152.0	153.0	155.9	160.5
152.5°	181.7	174.6	171.8	168.9	164.0	160.1	157.3	156.9	157.3	160.1	164.0
155°	183.1	177.1	174.4	171.8	167.9	164.0	161.9	161.5	161.9	164.0	167.9
157.5°	184.1	178.8	176.5	174.2	171.1	167.5	165.8	165.4	165.8	167.5	171.1
160°	184.8	180.6	178.6	176.7	173.9	171.1	169.6	169.3	169.6	171.1	173.9
162.5°	185.2	181.7	180.2	178.8	176.4	174.2	172.8	173.2	172.8	174.2	176.4
165°	185.5	182.4	181.3	180.2	178.5	176.4	175.6	176.0	175.6	176.4	178.5
167.5°	185.5	183.1	182.4	181.7	180.2	178.8	178.1	178.5	178.1	178.8	180.2
170°	185.2	183.4	182.9	182.4	181.7	180.6	180.2	180.9	180.2	180.6	181.7
172.5°	184.8	183.8	183.4	183.1	182.7	181.7	182.0	182.4	182.0	181.7	182.7
175°	184.5	183.8	183.6	183.4	183.4	182.7	183.1	183.4	183.1	182.7	183.4
177.5°	184.1	183.8	183.8	183.8	183.8	183.1	183.4	184.1	183.4	183.1	183.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	565.8	568.0	567.6	563.2	558.4	554.4	546.9	547.8	545.2	545.6	548.3
5°	551.8	551.8	550.0	543.9	535.9	531.5	523.2	521.0	515.7	515.3	514.8
7.5°	536.8	534.6	532.4	523.6	514.0	506.9	495.5	492.9	487.6	484.1	482.3
10°	519.2	516.2	511.8	501.7	489.8	481.0	469.1	465.6	455.5	451.1	448.5
12.5°	499.9	498.1	491.1	482.7	463.4	453.7	436.6	440.1	430.0	421.2	419.9
15°	480.5	474.0	470.0	456.4	433.1	428.7	415.0	408.0	398.8	391.7	391.7
17.5°	461.6	451.5	442.7	428.2	411.1	398.8	388.7	385.1	373.7	366.7	365.4
20°	436.6	425.2	423.0	402.3	390.4	376.8	367.1	358.3	350.0	346.9	344.7
22.5°	412.8	399.7	396.1	378.5	366.7	353.0	343.4	337.2	331.1	328.9	324.9
25°	387.3	379.4	374.2	355.2	342.1	329.3	322.7	318.3	312.6	312.2	309.5
27.5°	362.7	355.2	350.0	331.9	322.3	310.4	305.1	300.3	297.2	295.9	294.6
30°	341.6	333.3	327.1	313.9	302.0	292.4	288.0	284.9	283.1	280.9	280.5
32.5°	318.3	313.5	305.1	295.0	285.8	276.5	273.9	271.7	269.1	268.2	267.8
35°	298.5	291.9	286.7	275.2	271.3	263.4	260.3	258.5	255.0	254.1	253.2
37.5°	279.2	273.0	267.3	260.3	252.8	248.4	246.6	244.0	242.3	242.7	241.8
40°	259.8	255.0	250.6	243.1	238.7	236.5	233.0	230.4	229.5	229.9	229.5
42.5°	240.9	236.5	233.9	228.2	223.8	221.6	219.4	216.8	218.1	218.1	219.4
45°	223.8	219.8	218.1	213.7	211.0	207.5	205.3	204.9	206.6	206.2	206.2
47.5°	206.2	204.9	202.7	198.7	195.2	193.0	192.6	192.6	194.3	195.2	194.8
50°	192.6	189.9	187.3	184.2	181.6	180.7	179.4	180.3	182.0	182.0	182.9
52.5°	175.4	173.7	172.8	170.1	168.4	168.4	168.4	168.8	170.1	171.5	171.0
55°	160.5	159.2	158.3	157.0	154.8	155.2	154.8	155.6	157.0	158.3	159.2
57.5°	144.6	144.2	143.3	141.1	141.1	140.7	142.0	142.4	144.6	145.5	146.8
60°	130.6	129.3	129.3	127.5	127.5	127.5	128.8	130.1	131.9	132.3	133.2
62.5°	115.6	115.6	115.2	113.9	113.9	115.2	115.6	117.4	118.3	118.3	119.6
65°	101.6	101.1	100.7	101.1	101.6	101.6	102.9	103.8	104.6	105.1	105.5
67.5°	87.5	87.1	87.9	87.5	88.4	90.1	89.7	91.0	92.3	92.3	92.8
70°	74.3	75.2	74.7	75.6	75.2	76.1	77.4	77.8	77.8	78.3	79.6
72.5°	62.0	62.0	62.0	61.6	62.0	62.9	63.8	64.2	65.1	65.5	66.8
75°	50.1	50.1	49.2	50.1	50.1	51.0	51.9	51.9	51.9	52.8	54.1
77.5°	37.8	38.3	37.8	38.7	38.7	39.1	40.0	39.6	40.4	40.9	41.3
80°	27.7	27.3	27.3	27.3	27.7	27.7	28.6	29.0	29.0	30.3	29.5
82.5°	17.6	18.0	17.6	18.0	18.0	18.5	18.0	18.5	18.9	19.8	19.3
85°	10.1	9.7	9.7	10.1	9.7	9.7	10.1	9.7	10.1	9.7	10.1
87.5°	4.0	3.5	3.5	3.5	3.5	3.1	3.1	2.6	2.6	2.6	2.2
90°	4.2	4.8	5.3	7.1	9.5	11.7	12.0	11.7	11.3	10.6	11.3
92.5°	14.8	16.8	18.7	28.3	41.7	53.7	54.4	45.6	35.7	30.4	26.5
95°	26.2	30.4	34.6	50.9	81.6	122.6	138.5	121.2	92.6	71.0	56.2
97.5°	35.3	40.1	44.9	65.7	108.5	174.6	225.8	227.6	189.4	151.3	115.6
100°	44.2	49.2	54.1	72.8	115.9	192.3	279.2	330.1	322.7	278.8	230.4
102.5°	52.3	57.2	62.2	79.2	116.3	185.5	281.0	368.3	410.0	408.5	376.4
105°	60.1	65.0	70.0	86.6	118.0	176.4	261.9	355.9	429.4	469.3	473.9
107.5°	67.9	72.8	77.8	94.0	121.9	171.4	244.2	329.7	408.5	467.9	502.6
110°	75.6	80.8	85.9	101.4	126.9	170.0	232.2	305.4	379.9	443.2	488.4

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	83.1	88.4	93.7	108.5	132.2	170.3	224.4	288.4	353.8	413.8	463.0
115°	91.2	96.0	100.7	115.9	137.5	171.8	219.1	275.0	333.3	387.7	434.0
117.5°	98.6	103.6	108.5	122.6	143.1	173.9	216.3	265.8	316.3	365.1	408.2
120°	106.0	111.0	115.9	129.7	148.8	176.0	213.8	258.7	304.3	348.1	385.6
122.5°	113.4	118.6	123.7	136.4	153.7	178.5	212.4	252.7	294.7	334.0	369.0
125°	120.5	125.4	130.4	143.1	159.0	180.9	210.6	247.0	285.6	322.0	353.1
127.5°	126.9	132.0	137.1	149.5	164.0	183.4	209.6	241.7	276.4	309.9	339.6
130°	132.9	137.9	142.8	155.1	168.6	186.2	208.9	236.4	267.5	297.9	325.8
132.5°	138.5	143.4	148.4	160.1	173.2	189.1	208.5	232.2	259.1	286.6	311.7
135°	143.5	148.4	153.4	164.7	177.1	191.2	208.2	228.3	251.3	274.6	297.9
137.5°	148.1	152.7	157.3	168.6	180.2	193.3	208.2	225.5	244.9	265.1	284.1
140°	152.0	156.6	161.2	171.8	182.7	194.7	207.8	223.0	238.9	255.9	272.1
142.5°	155.5	159.8	164.0	174.2	184.8	195.8	207.8	220.5	234.0	247.7	261.2
145°	159.4	163.3	167.2	176.7	186.6	196.5	207.1	218.4	229.4	241.0	252.0
147.5°	162.6	166.1	169.6	178.8	187.7	196.9	206.0	216.3	225.8	235.4	244.2
150°	165.8	169.0	172.1	180.2	188.4	196.5	205.0	213.5	221.9	229.7	237.1
152.5°	168.9	171.8	174.6	181.7	188.7	195.8	203.2	211.0	218.1	225.1	231.1
155°	171.8	174.4	177.1	183.1	189.1	195.1	201.1	207.8	214.5	220.2	225.5
157.5°	174.2	176.5	178.8	184.1	189.1	193.7	199.0	205.0	210.3	215.2	219.8
160°	176.7	178.6	180.6	184.8	189.1	192.6	196.9	201.8	206.4	210.3	214.2
162.5°	178.8	180.2	181.7	185.2	188.7	191.6	195.1	199.0	202.5	205.7	208.9
165°	180.2	181.3	182.4	185.5	188.0	190.1	192.6	195.8	198.6	201.1	203.6
167.5°	181.7	182.4	183.1	185.5	187.7	188.7	190.5	192.6	194.7	196.9	198.6
170°	182.4	182.9	183.4	185.2	187.0	187.7	188.7	190.1	191.9	193.0	194.4
172.5°	183.1	183.4	183.8	184.8	185.9	186.2	186.6	187.7	188.7	189.4	190.5
175°	183.4	183.6	183.8	184.5	185.2	184.8	185.2	185.5	186.6	187.0	187.3
177.5°	183.8	183.8	183.8	184.1	184.8	184.1	183.8	184.1	184.8	184.8	185.2
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	545.2	546.5	543.4	542.5	543.4	540.3	541.2	542.1	542.1	543.4	544.3
5°	513.5	511.8	508.7	507.8	506.9	508.2	507.4	508.7	509.1	512.2	512.6
7.5°	482.3	479.7	477.0	474.4	473.5	471.3	473.5	473.5	476.6	475.7	477.9
10°	445.4	444.9	441.4	440.1	438.3	434.8	439.7	438.3	440.5	444.5	445.4
12.5°	418.1	413.3	415.5	409.3	411.5	408.0	408.4	408.4	412.0	412.4	411.5
15°	392.2	388.2	382.5	379.9	378.5	376.8	382.5	382.9	380.3	386.5	384.3
17.5°	365.8	365.8	360.5	359.2	355.7	357.4	356.6	357.0	356.1	360.5	362.7
20°	342.9	340.7	339.0	339.4	335.0	334.1	333.3	334.1	337.2	340.3	341.2
22.5°	324.5	323.1	318.8	319.6	316.1	317.4	316.6	318.8	319.2	319.2	322.3
25°	306.9	305.1	305.6	303.8	302.5	302.5	301.2	302.5	304.2	305.1	305.6
27.5°	293.7	292.4	290.2	288.9	289.7	287.5	289.3	290.6	290.6	289.7	290.6
30°	277.9	278.7	278.7	274.3	276.1	275.2	276.5	277.4	277.4	277.9	277.0
32.5°	267.3	264.7	264.2	263.8	263.8	262.0	262.0	263.4	263.8	264.2	265.6
35°	253.2	253.2	251.0	252.4	250.6	251.0	250.6	251.0	251.9	250.6	251.9
37.5°	240.5	240.9	240.1	240.9	241.4	240.5	239.6	241.4	240.5	240.5	239.6
40°	229.5	229.1	229.5	229.5	229.5	229.9	229.1	229.1	229.1	228.2	227.3
42.5°	220.3	217.6	218.5	219.0	217.6	217.6	218.1	217.6	219.0	216.3	216.3
45°	207.1	206.2	206.6	206.6	207.5	206.2	207.1	207.5	206.2	205.8	204.9
47.5°	195.2	196.1	195.2	196.1	196.1	197.0	195.2	195.6	196.1	194.3	193.0
50°	183.3	183.3	184.7	184.2	184.7	183.8	183.8	183.3	183.8	182.9	181.6
52.5°	172.3	171.0	173.2	172.8	172.3	171.9	171.5	171.9	171.0	170.1	170.1
55°	158.7	158.7	160.0	160.5	160.5	159.6	158.7	159.2	158.7	158.3	157.8
57.5°	147.7	146.0	146.8	147.3	147.3	146.0	146.8	146.0	146.0	146.4	145.1
60°	133.7	133.7	132.8	134.1	134.1	133.2	133.2	133.7	132.8	132.3	131.9
62.5°	118.7	119.1	120.5	120.9	121.3	120.5	119.6	120.0	120.0	118.7	119.1
65°	106.0	106.8	108.6	108.2	107.3	107.7	106.8	107.3	106.0	106.4	105.1
67.5°	93.6	93.2	93.6	93.6	94.5	94.1	93.2	93.2	92.8	94.1	92.8
70°	80.5	80.5	80.5	80.5	80.9	81.3	80.5	79.6	80.0	79.1	78.7
72.5°	66.8	67.3	66.8	67.7	66.4	67.3	67.3	66.8	66.4	66.4	66.4
75°	54.1	55.0	53.6	54.1	53.6	54.5	54.1	54.1	53.2	52.8	53.2
77.5°	41.3	41.8	40.9	41.3	40.9	41.3	41.3	40.9	40.9	40.9	40.9
80°	29.5	29.9	29.5	29.0	28.6	29.5	28.6	29.0	29.5	29.0	29.9
82.5°	18.9	18.9	18.5	18.9	18.0	18.0	18.5	18.5	18.0	18.9	18.0
85°	9.2	9.2	10.1	9.2	8.8	8.8	8.8	9.2	8.8	9.7	9.2
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.6	1.8
90°	11.5	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.5
92.5°	25.1	23.7	23.3	21.9	22.3	21.6	22.3	21.9	23.3	23.7	25.1
95°	52.3	48.4	43.8	41.0	39.9	40.3	39.9	41.0	43.8	48.4	52.3
97.5°	105.0	94.4	80.6	73.5	69.6	67.5	69.6	73.5	80.6	94.4	105.0
100°	209.0	187.7	158.3	143.1	132.9	126.5	132.9	143.1	158.3	187.7	209.0
102.5°	353.4	330.4	297.9	269.3	255.9	246.7	255.9	269.3	297.9	330.4	353.4
105°	468.1	462.3	440.4	418.4	403.2	398.3	403.2	418.4	440.4	462.3	468.1
107.5°	509.6	516.7	516.3	513.2	508.6	500.4	508.6	513.2	516.3	516.7	509.6
110°	502.9	517.4	532.6	539.3	542.5	542.1	542.5	539.3	532.6	517.4	502.9

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	480.2	497.3	519.9	532.2	539.0	541.4	539.0	532.2	519.9	497.3	480.2
115°	452.2	470.4	495.5	511.7	520.9	524.1	520.9	511.7	495.5	470.4	452.2
117.5°	425.5	442.8	468.6	485.9	495.5	498.0	495.5	485.9	468.6	442.8	425.5
120°	401.6	417.7	442.5	459.1	469.3	472.9	469.3	459.1	442.5	417.7	401.6
122.5°	383.1	397.2	418.8	435.1	443.9	446.7	443.9	435.1	418.8	397.2	383.1
125°	366.4	379.6	400.1	413.5	422.3	425.2	422.3	413.5	400.1	379.6	366.4
127.5°	352.0	364.4	382.4	395.1	402.9	405.0	402.9	395.1	382.4	364.4	352.0
130°	337.5	349.2	366.5	378.5	385.6	388.4	385.6	378.5	366.5	349.2	337.5
132.5°	322.5	333.3	350.2	362.3	368.6	371.1	368.6	362.3	350.2	333.3	322.5
135°	307.8	317.7	332.9	344.6	350.9	352.4	350.9	344.6	332.9	317.7	307.8
137.5°	293.0	301.8	316.3	326.6	332.2	334.3	332.2	326.6	316.3	301.8	293.0
140°	279.9	287.7	299.0	308.2	313.5	315.6	313.5	308.2	299.0	287.7	279.9
142.5°	267.4	273.5	284.1	292.3	296.9	296.9	296.9	292.3	284.1	273.5	267.4
145°	257.1	262.2	270.7	276.7	280.3	281.3	280.3	276.7	270.7	262.2	257.1
147.5°	248.1	252.0	259.4	264.4	266.8	267.5	266.8	264.4	259.4	252.0	248.1
150°	240.3	243.5	248.8	253.0	255.2	255.5	255.2	253.0	248.8	243.5	240.3
152.5°	233.8	236.4	240.3	243.9	245.3	245.3	245.3	243.9	240.3	236.4	233.8
155°	227.4	229.4	233.3	235.7	237.1	236.4	237.1	235.7	233.3	229.4	227.4
157.5°	221.4	223.0	225.8	228.0	228.7	228.7	228.7	228.0	225.8	223.0	221.4
160°	215.4	216.6	219.1	220.9	221.2	221.2	221.2	220.9	219.1	216.6	215.4
162.5°	209.8	210.6	213.1	214.2	214.5	214.2	214.5	214.2	213.1	210.6	209.8
165°	204.3	205.0	206.4	207.8	207.8	207.5	207.8	207.8	206.4	205.0	204.3
167.5°	199.3	200.0	200.7	201.4	201.4	201.1	201.4	201.4	200.7	200.0	199.3
170°	194.8	195.1	195.4	196.5	196.1	195.4	196.1	196.5	195.4	195.1	194.8
172.5°	190.6	190.8	191.2	191.6	191.2	190.8	191.2	191.6	191.2	190.8	190.6
175°	187.5	187.7	187.7	188.0	187.7	187.0	187.7	188.0	187.7	187.7	187.5
177.5°	185.2	185.2	185.2	185.2	184.8	184.1	184.8	185.2	185.2	185.2	185.2
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	543.0	546.5	545.2	540.3	546.1	546.1	550.0	550.0	554.9	556.6	559.2
5°	512.2	514.8	517.0	514.8	518.8	525.0	528.5	531.5	538.1	540.8	544.7
7.5°	479.2	484.1	486.3	486.3	492.9	499.9	506.9	511.3	520.6	524.1	528.0
10°	447.1	452.8	457.2	456.8	467.8	472.2	481.0	491.1	500.3	505.6	511.3
12.5°	413.3	416.4	422.5	431.3	433.9	441.9	452.0	464.7	481.4	486.3	494.6
15°	385.1	393.5	398.3	402.3	408.4	415.9	426.9	439.2	455.9	466.5	475.3
17.5°	361.4	372.4	375.5	374.6	382.5	393.9	406.7	415.9	430.9	443.6	452.0
20°	342.1	346.5	351.7	353.9	360.1	372.4	384.7	395.3	407.6	417.7	427.3
22.5°	322.7	326.2	330.6	334.6	339.4	346.5	358.3	371.5	383.4	393.1	404.0
25°	306.9	309.1	313.0	316.1	321.4	326.2	334.6	349.1	363.2	368.9	378.5
27.5°	291.5	293.3	295.9	299.4	302.0	306.9	314.4	326.2	340.7	346.5	359.6
30°	277.9	279.2	281.8	283.6	284.9	290.6	296.3	305.6	316.6	324.5	334.1
32.5°	265.1	266.4	269.1	269.5	271.3	274.3	279.6	288.0	297.6	304.2	312.6
35°	251.0	251.9	254.6	255.4	256.8	259.4	263.4	269.5	278.3	283.1	290.6
37.5°	240.1	239.6	241.4	242.7	244.5	245.8	247.1	253.2	259.8	264.2	270.0
40°	228.2	227.3	227.7	229.5	230.4	232.1	232.1	238.3	242.7	246.2	250.6
42.5°	216.3	215.9	215.0	215.9	216.8	217.2	217.6	222.0	226.4	229.5	234.3
45°	204.4	204.0	203.1	203.6	203.6	204.4	205.8	207.5	210.6	213.2	215.9
47.5°	193.5	192.6	191.3	190.8	191.7	191.7	191.7	193.5	196.5	197.4	200.0
50°	182.0	180.7	178.9	178.1	178.1	177.6	178.5	178.9	181.6	182.5	184.7
52.5°	169.7	168.8	167.1	165.3	165.8	164.9	165.3	165.8	166.6	167.9	169.3
55°	157.4	155.6	154.3	153.9	152.6	152.6	151.2	153.0	152.6	153.0	154.8
57.5°	145.5	143.8	141.6	140.7	139.4	138.9	138.1	137.6	138.1	139.4	140.7
60°	131.5	130.6	129.3	127.9	127.1	125.7	124.9	124.9	124.4	124.4	124.9
62.5°	117.8	117.4	115.6	115.2	114.3	113.4	112.1	111.2	111.2	112.1	112.6
65°	104.6	104.2	102.9	102.4	100.2	99.4	98.9	98.5	97.6	97.6	97.6
67.5°	92.3	91.0	91.0	88.8	87.1	86.2	85.3	84.9	84.9	84.9	85.3
70°	78.7	78.7	77.4	76.1	74.3	74.7	73.4	72.1	72.1	71.2	71.7
72.5°	65.5	65.1	63.8	63.3	62.0	60.7	59.8	60.7	59.4	58.9	59.4
75°	52.8	52.3	51.4	50.6	51.0	49.7	48.4	47.9	47.9	47.0	47.0
77.5°	40.4	41.3	39.6	39.1	38.3	37.4	36.9	36.5	36.5	36.5	37.4
80°	28.1	28.6	28.6	27.7	28.1	26.8	26.8	26.8	25.5	25.9	26.4
82.5°	18.0	18.0	17.6	18.0	17.6	17.6	17.1	17.1	16.7	16.7	17.1
85°	10.1	9.7	9.2	10.1	9.7	9.7	9.2	9.2	9.2	9.2	9.2
87.5°	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5
90°	11.3	10.6	11.3	11.7	12.0	11.7	9.5	7.1	5.3	4.8	4.2
92.5°	26.5	30.4	35.7	45.6	54.4	53.7	41.7	28.3	18.7	16.8	14.8
95°	56.2	71.0	92.6	121.2	138.5	122.6	81.6	50.9	34.6	30.4	26.2
97.5°	115.6	151.3	189.4	227.6	225.8	174.6	108.5	65.7	44.9	40.1	35.3
100°	230.4	278.8	322.7	330.1	279.2	192.3	115.9	72.8	54.1	49.2	44.2
102.5°	376.4	408.5	410.0	368.3	281.0	185.5	116.3	79.2	62.2	57.2	52.3
105°	473.9	469.3	429.4	355.9	261.9	176.4	118.0	86.6	70.0	65.0	60.1
107.5°	502.6	467.9	408.5	329.7	244.2	171.4	121.9	94.0	77.8	72.8	67.9
110°	488.4	443.2	379.9	305.4	232.2	170.0	126.9	101.4	85.9	80.8	75.6

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	463.0	413.8	353.8	288.4	224.4	170.3	132.2	108.5	93.7	88.4	83.1
115°	434.0	387.7	333.3	275.0	219.1	171.8	137.5	115.9	100.7	96.0	91.2
117.5°	408.2	365.1	316.3	265.8	216.3	173.9	143.1	122.6	108.5	103.6	98.6
120°	385.6	348.1	304.3	258.7	213.8	176.0	148.8	129.7	115.9	111.0	106.0
122.5°	369.0	334.0	294.7	252.7	212.4	178.5	153.7	136.4	123.7	118.6	113.4
125°	353.1	322.0	285.6	247.0	210.6	180.9	159.0	143.1	130.4	125.4	120.5
127.5°	339.6	309.9	276.4	241.7	209.6	183.4	164.0	149.5	137.1	132.0	126.9
130°	325.8	297.9	267.5	236.4	208.9	186.2	168.6	155.1	142.8	137.9	132.9
132.5°	311.7	286.6	259.1	232.2	208.5	189.1	173.2	160.1	148.4	143.4	138.5
135°	297.9	274.6	251.3	228.3	208.2	191.2	177.1	164.7	153.4	148.4	143.5
137.5°	284.1	265.1	244.9	225.5	208.2	193.3	180.2	168.6	157.3	152.7	148.1
140°	272.1	255.9	238.9	223.0	207.8	194.7	182.7	171.8	161.2	156.6	152.0
142.5°	261.2	247.7	234.0	220.5	207.8	195.8	184.8	174.2	164.0	159.8	155.5
145°	252.0	241.0	229.4	218.4	207.1	196.5	186.6	176.7	167.2	163.3	159.4
147.5°	244.2	235.4	225.8	216.3	206.0	196.9	187.7	178.8	169.6	166.1	162.6
150°	237.1	229.7	221.9	213.5	205.0	196.5	188.4	180.2	172.1	169.0	165.8
152.5°	231.1	225.1	218.1	211.0	203.2	195.8	188.7	181.7	174.6	171.8	168.9
155°	225.5	220.2	214.5	207.8	201.1	195.1	189.1	183.1	177.1	174.4	171.8
157.5°	219.8	215.2	210.3	205.0	199.0	193.7	189.1	184.1	178.8	176.5	174.2
160°	214.2	210.3	206.4	201.8	196.9	192.6	189.1	184.8	180.6	178.6	176.7
162.5°	208.9	205.7	202.5	199.0	195.1	191.6	188.7	185.2	181.7	180.2	178.8
165°	203.6	201.1	198.6	195.8	192.6	190.1	188.0	185.5	182.4	181.3	180.2
167.5°	198.6	196.9	194.7	192.6	190.5	188.7	187.7	185.5	183.1	182.4	181.7
170°	194.4	193.0	191.9	190.1	188.7	187.7	187.0	185.2	183.4	182.9	182.4
172.5°	190.5	189.4	188.7	187.7	186.6	186.2	185.9	184.8	183.8	183.4	183.1
175°	187.3	187.0	186.6	185.5	185.2	184.8	185.2	184.5	183.8	183.6	183.4
177.5°	185.2	184.8	184.8	184.1	183.8	184.1	184.8	184.1	183.8	183.8	183.8
180°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	572.0	572.0	572.0	572.0
2.5°	561.4	561.4	568.0	575.1
5°	549.1	552.2	562.8	572.4
7.5°	537.3	542.5	555.7	568.0
10°	522.8	529.8	546.1	560.6
12.5°	508.7	515.3	534.2	550.5
15°	488.9	497.3	517.5	537.7
17.5°	469.1	477.5	502.1	525.8
20°	445.8	456.8	484.5	516.2
22.5°	424.3	437.9	468.7	494.2
25°	400.5	421.6	450.2	483.2
27.5°	379.4	400.5	429.5	463.0
30°	355.7	377.2	407.1	437.9
32.5°	332.8	352.6	381.6	419.4
35°	309.1	328.0	356.1	394.4
37.5°	287.5	306.0	336.8	372.0
40°	266.4	285.8	312.2	347.3
42.5°	246.6	263.8	287.5	322.7
45°	228.6	240.9	262.9	295.9
47.5°	209.7	220.7	240.9	273.9
50°	192.1	201.4	219.0	249.7
52.5°	175.0	182.9	199.2	223.8
55°	159.6	167.1	178.9	203.1
57.5°	143.8	149.5	160.9	180.3
60°	128.4	133.7	142.9	158.7
62.5°	113.0	117.4	126.2	138.9
65°	99.4	102.9	109.5	120.5
67.5°	86.2	88.4	93.6	102.4
70°	73.4	75.2	79.6	86.6
72.5°	59.8	61.6	66.4	71.2
75°	48.4	48.8	52.3	56.3
77.5°	37.8	37.4	40.0	43.1
80°	25.9	27.3	29.5	30.8
82.5°	17.6	18.0	18.9	19.8
85°	9.7	10.1	10.1	11.4
87.5°	4.0	4.4	4.4	4.8
90°	3.5	2.8	1.4	0.4
92.5°	12.0	10.2	7.4	5.3
95°	20.5	17.3	13.8	12.4
97.5°	29.0	24.4	20.5	18.4
100°	37.1	31.5	28.3	27.2
102.5°	44.9	39.2	36.0	35.3
105°	52.3	47.0	44.5	43.1
107.5°	60.1	55.1	52.7	51.6
110°	68.2	63.6	61.5	60.1

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	76.0	71.7	69.3	67.9
115°	84.1	79.9	77.8	76.0
117.5°	91.9	88.0	85.9	84.5
120°	99.0	95.8	93.7	92.2
122.5°	106.4	102.8	100.7	99.7
125°	113.4	109.2	107.1	106.0
127.5°	120.2	115.6	112.7	111.3
130°	125.8	120.9	117.3	115.9
132.5°	131.1	125.8	121.9	120.2
135°	135.4	130.1	125.8	124.4
137.5°	140.0	134.3	130.1	128.3
140°	144.2	138.5	134.3	132.9
142.5°	148.1	142.4	138.5	137.5
145°	152.3	147.0	143.5	142.1
147.5°	156.6	151.6	148.1	147.0
150°	160.5	155.9	153.0	152.0
152.5°	164.0	160.1	157.3	156.9
155°	167.9	164.0	161.9	161.5
157.5°	171.1	167.5	165.8	165.4
160°	173.9	171.1	169.6	169.3
162.5°	176.4	174.2	172.8	173.2
165°	178.5	176.4	175.6	176.0
167.5°	180.2	178.8	178.1	178.5
170°	181.7	180.6	180.2	180.9
172.5°	182.7	181.7	182.0	182.4
175°	183.4	182.7	183.1	183.4
177.5°	183.8	183.1	183.4	184.1
180°	183.8	183.8	183.8	183.8

TEST NUMBER: P998182

CATALOG NUMBER: SA2XXDIP-B290D330UB40-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.47	14.29	14.43	15.27	16.55	10.96	11.79	11.93	12.76	14.04
	3H	14.28	15.01	15.25	16.00	17.30	12.30	13.04	13.28	14.03	15.33
	4H	14.44	15.14	15.43	16.13	17.44	12.76	13.46	13.76	14.45	15.76
	6H	14.49	15.13	15.49	16.12	17.45	13.07	13.71	14.07	14.71	16.03
	8H	14.46	15.08	15.47	16.09	17.41	13.15	13.76	14.16	14.77	16.09
	12H	14.43	15.01	15.44	16.01	17.35	13.19	13.77	14.21	14.78	16.12
4H	2H	13.50	14.20	14.50	15.19	16.50	11.40	12.10	12.40	13.09	14.40
	3H	14.48	15.06	15.49	16.08	17.40	12.86	13.44	13.87	14.46	15.78
	4H	14.76	15.29	15.77	16.30	17.65	13.39	13.92	14.41	14.93	16.28
	6H	14.89	15.34	15.91	16.38	17.72	13.77	14.23	14.80	15.26	16.60
	8H	14.88	15.31	15.91	16.34	17.69	13.88	14.31	14.91	15.33	16.69
	12H	14.85	15.23	15.89	16.27	17.63	13.94	14.32	14.98	15.36	16.72
8H	4H	14.76	15.19	15.79	16.22	17.57	13.53	13.96	14.56	14.99	16.34
	6H	14.94	15.29	15.99	16.36	17.72	13.97	14.32	15.02	15.39	16.74
	8H	14.97	15.28	16.03	16.33	17.71	14.12	14.42	15.17	15.48	16.85
	12H	14.95	15.23	16.01	16.27	17.69	14.21	14.48	15.27	15.53	16.94
12H	4H	14.72	15.10	15.76	16.15	17.51	13.50	13.89	14.55	14.93	16.29
	6H	14.92	15.23	15.98	16.28	17.66	13.97	14.27	15.02	15.33	16.70
	8H	14.95	15.22	16.01	16.27	17.69	14.12	14.39	15.18	15.44	16.86