

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999295

Luminaire Tested: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999295
REPORT IS A COMBINATION OF REPORTS P987844 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7372.0 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999295

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999295

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	94	90	87	90	86	83	80	73	70	68	60	58	57	48	47	46
2	89	82	76	71	82	76	71	67	64	60	57	53	51	48	43	41	40
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	39	36	34
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	32	29	26
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	37	30	26	32	26	23	27	23	20	23	20	17
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26984	26984	26984
5°	27028	25673	25482
10°	26762	24349	23545
15°	26394	22786	21338
20°	25908	21009	19029
25°	25410	19186	16916
30°	24739	17410	14609
35°	24083	15619	12627
40°	23419	13860	10586
45°	22642	12045	8806
50°	21840	10295	7169
55°	21005	8545	5692
60°	20037	6834	4306
65°	18919	5209	3501
70°	17570	3780	2785
75°	15881	2882	2126
80°	13429	1953	1427
85°	9365	893	689

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22642 cd/sqm

TEST NUMBER: P999295

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.8	2.2
10°-20°	438.6	5.9
20°-30°	615.8	8.4
30°-40°	671.2	9.1
40°-50°	616.9	8.4
50°-60°	484.5	6.6
60°-70°	315.4	4.3
70°-80°	162.4	2.2
80°-90°	45.4	0.6
90°-100°	85.5	1.2
100°-110°	271.7	3.7
110°-120°	464.8	6.3
120°-130°	611.3	8.3
130°-140°	686.2	9.3
140°-150°	672.9	9.1
150°-160°	564.5	7.7
160°-170°	374.4	5.1
170°-180°	130.8	1.8
0°-30°	1214.2	16.5
0°-40°	1885.4	25.6
0°-60°	2986.8	40.5
0°-90°	3509.9	47.6
90°-120°	822.0	11.1
90°-150°	2792.4	37.9
90°-180°	3862.0	52.4
0°-180°	7372.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1705	1705	1705	1705	1705	
5°	1705	1697	1677	1691	1686	162
15°	1621	1604	1552	1523	1507	457
25°	1472	1422	1321	1257	1234	677
35°	1268	1190	1054	956	923	794
45°	1037	933	771	662	625	801
55°	788	668	501	409	380	704
65°	532	407	268	216	211	528
75°	284	176	123	113	111	300
85°	66	34	29	29	29	76
90°	1	15	41	38	40	7
95°	61	72	75	75	72	68
105°	251	254	256	259	259	265
115°	466	473	471	470	466	461
125°	678	689	685	682	681	606
135°	878	891	893	892	888	678
145°	1066	1074	1081	1082	1077	666
155°	1218	1222	1225	1231	1228	561
165°	1325	1324	1324	1332	1327	374
175°	1379	1376	1373	1381	1374	131
180°	1381	1381	1381	1381	1381	

TEST NUMBER: P999295

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1704.7	1704.7	1704.7	1704.7	1704.7
2.5°	1712.4	1704.7	1687.8	1703.2	1700.1
5°	1704.7	1697.0	1677.0	1690.8	1686.2
7.5°	1690.8	1681.6	1660.0	1666.2	1658.4
10°	1672.3	1661.5	1630.7	1626.1	1616.8
12.5°	1649.2	1635.3	1593.7	1584.4	1567.4
15°	1621.4	1604.5	1552.0	1522.7	1507.3
17.5°	1589.0	1564.3	1499.5	1465.6	1440.9
20°	1552.0	1521.1	1444.0	1405.4	1371.5
22.5°	1511.9	1476.4	1386.9	1334.5	1311.3
25°	1471.8	1422.4	1320.6	1257.3	1234.2
27.5°	1424.0	1371.5	1258.9	1186.4	1150.9
30°	1373.0	1314.4	1191.0	1112.3	1070.7
32.5°	1323.7	1252.7	1126.2	1033.6	995.1
35°	1268.1	1189.5	1053.7	956.5	922.6
37.5°	1214.1	1129.3	985.8	879.4	840.8
40°	1157.1	1064.5	914.8	805.3	765.2
42.5°	1098.4	999.7	843.9	729.7	691.1
45°	1036.7	933.4	771.4	661.8	624.8
47.5°	978.1	868.6	701.9	592.4	558.5
50°	913.3	803.8	634.1	527.6	495.2
52.5°	850.1	734.3	569.3	467.5	438.1
55°	788.3	668.0	501.4	408.8	379.5
57.5°	725.1	601.7	441.2	354.8	330.1
60°	660.3	536.9	378.0	299.3	274.6
62.5°	597.0	473.6	324.0	249.9	237.6
65°	532.2	407.3	268.4	216.0	211.4
67.5°	470.5	345.6	216.0	189.8	185.1
70°	405.7	285.4	179.0	163.5	157.4
72.5°	344.0	229.9	149.6	137.3	134.2
75°	283.9	175.9	123.4	112.6	111.1
77.5°	223.7	125.0	97.2	91.0	87.9
80°	168.2	89.5	74.1	67.9	67.9
82.5°	117.2	60.2	50.9	47.8	47.8
85°	66.3	33.9	29.3	29.3	29.3
87.5°	24.7	12.3	12.3	10.8	10.8
90°	1.2	15.2	40.8	38.5	39.6
92.5°	25.6	35.0	36.1	37.3	37.3
95°	60.6	72.3	74.6	74.6	72.3
97.5°	101.4	111.9	116.6	116.6	116.6
100°	148.0	157.4	160.9	160.9	159.7
102.5°	197.0	204.0	208.7	209.8	208.7
105°	250.6	254.1	256.5	258.8	258.8
107.5°	304.3	308.9	308.9	310.1	304.3
110°	355.5	362.5	362.5	362.5	359.0

TEST NUMBER: P999295

CATALOG NUMBER: SA2XXRDIP-B1005D1080UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	411.5	418.5	417.3	413.8	411.5
115°	466.3	473.3	471.0	469.8	466.3
117.5°	521.1	530.4	524.6	521.1	517.6
120°	575.9	585.2	575.9	575.9	572.4
122.5°	626.0	637.6	631.8	628.3	626.0
125°	678.4	688.9	685.4	681.9	680.8
127.5°	729.7	742.6	737.9	733.2	729.7
130°	777.5	792.7	790.4	788.0	783.4
132.5°	831.2	842.8	844.0	838.2	834.7
135°	877.8	890.6	892.9	891.8	888.3
137.5°	929.1	939.6	941.9	940.7	936.1
140°	974.5	985.0	990.9	990.9	986.2
142.5°	1021.2	1031.7	1035.2	1036.3	1031.7
145°	1065.5	1073.6	1080.6	1081.8	1077.1
147.5°	1105.1	1115.6	1120.3	1122.6	1117.9
150°	1145.9	1152.9	1157.6	1161.1	1157.6
152.5°	1182.0	1189.0	1194.9	1199.5	1194.9
155°	1218.2	1221.7	1225.2	1231.0	1227.5
157.5°	1249.7	1252.0	1254.3	1262.5	1256.6
160°	1277.6	1280.0	1281.1	1288.1	1283.5
162.5°	1303.3	1303.3	1304.4	1312.6	1306.8
165°	1325.4	1324.3	1324.3	1332.4	1326.6
167.5°	1345.2	1341.7	1341.7	1349.9	1344.1
170°	1360.4	1356.9	1355.7	1363.9	1356.9
172.5°	1370.9	1367.4	1366.2	1374.4	1367.4
175°	1379.0	1375.5	1373.2	1381.4	1374.4
177.5°	1383.7	1380.2	1377.9	1384.9	1377.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4

(END OF REPORT)