

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999312

Luminaire Tested: SA2XXRDIP-B1005D330UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999312
REPORT IS A COMBINATION OF REPORTS P987863 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D330UB27-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4738.4 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999312

CATALOG NUMBER: SA2XXRDIP-B1005D330UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999312

CATALOG NUMBER: SA2XXRDIP-B1005D330UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	104	99	96	92	98	95	91	88	85	83	81	77	75	73	69	68	67
2	95	88	82	77	90	84	78	74	76	72	68	69	65	62	62	60	57
3	87	78	71	65	83	74	68	62	68	62	58	61	57	54	56	52	50
4	80	69	62	56	76	66	59	54	61	55	50	55	51	47	50	46	43
5	74	62	54	48	70	60	52	47	55	49	44	50	45	41	46	42	38
6	68	56	48	42	65	54	47	41	50	43	39	45	40	36	42	37	34
7	64	51	43	38	60	49	42	37	45	39	35	42	36	33	38	34	31
8	59	47	39	34	56	45	38	33	42	35	31	38	33	29	35	31	28
9	55	43	36	30	53	41	34	30	38	32	28	35	30	27	33	28	25
10	52	40	33	28	49	38	32	27	36	30	26	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26631	26631	26631
5°	26675	25336	25148
10°	26411	24030	23237
15°	26047	22487	21058
20°	25567	20734	18779
25°	25077	18934	16694
30°	24414	17182	14417
35°	23768	15415	12462
40°	23111	13678	10448
45°	22344	11888	8691
50°	21553	10159	7075
55°	20731	8433	5617
60°	19773	6744	4250
65°	18674	5141	3455
70°	17340	3730	2747
75°	15669	2845	2098
80°	13253	1926	1409
85°	9252	881	680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22344 cd/sqm

TEST NUMBER: P999312

CATALOG NUMBER: SA2XXRDIP-B1005D330UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	3.3
10°-20°	432.8	9.1
20°-30°	607.7	12.8
30°-40°	662.4	14.0
40°-50°	608.8	12.8
50°-60°	478.1	10.1
60°-70°	311.2	6.6
70°-80°	160.2	3.4
80°-90°	42.1	0.9
90°-100°	74.3	1.6
100°-110°	251.1	5.3
110°-120°	263.9	5.6
120°-130°	217.0	4.6
130°-140°	174.4	3.7
140°-150°	131.7	2.8
150°-160°	92.6	2.0
160°-170°	54.5	1.2
170°-180°	17.7	0.4
0°-30°	1198.2	25.3
0°-40°	1860.7	39.3
0°-60°	2947.6	62.2
0°-90°	3461.2	73.0
90°-120°	589.2	12.4
90°-150°	1112.4	23.5
90°-180°	1277.0	26.9
0°-180°	4738.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1682	1682	1682	1682	1682	
5°	1682	1675	1655	1669	1664	160
15°	1600	1583	1532	1503	1488	451
25°	1452	1404	1303	1241	1218	668
35°	1252	1174	1040	944	910	783
45°	1023	921	761	653	617	790
55°	778	659	495	404	374	695
65°	525	402	265	213	209	521
75°	280	174	122	111	110	296
85°	66	34	29	29	29	75
90°	0	5	12	11	12	4
95°	12	30	138	52	40	13
105°	43	65	261	467	397	46
115°	76	96	218	451	522	75
125°	106	125	210	365	424	94
135°	124	148	208	307	351	96
145°	142	163	206	256	280	89
155°	161	174	200	227	236	74
165°	176	181	192	204	207	49
175°	183	183	185	187	186	17
180°	183	183	183	183	183	

TEST NUMBER: P999312

CATALOG NUMBER: SA2XXRDIP-B1005D330UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1682.4	1682.4	1682.4	1682.4	1682.4
2.5°	1690.0	1682.4	1665.6	1680.8	1677.8
5°	1682.4	1674.8	1655.0	1668.7	1664.1
7.5°	1668.7	1659.5	1638.2	1644.3	1636.7
10°	1650.4	1639.7	1609.3	1604.7	1595.6
12.5°	1627.6	1613.9	1572.7	1563.6	1546.9
15°	1600.1	1583.4	1531.6	1502.7	1487.5
17.5°	1568.2	1543.8	1479.9	1446.4	1422.0
20°	1531.6	1501.2	1425.1	1387.0	1353.5
22.5°	1492.1	1457.0	1368.7	1317.0	1294.1
25°	1452.5	1403.7	1303.3	1240.8	1218.0
27.5°	1405.3	1353.5	1242.4	1170.8	1135.8
30°	1355.0	1297.2	1175.4	1097.7	1056.6
32.5°	1306.3	1236.3	1111.4	1020.1	982.0
35°	1251.5	1173.8	1039.9	944.0	910.5
37.5°	1198.2	1114.5	972.9	867.8	829.8
40°	1141.9	1050.5	902.8	794.7	755.2
42.5°	1084.0	986.6	832.8	720.1	682.1
45°	1023.1	921.1	761.3	653.2	616.6
47.5°	965.3	857.2	692.7	584.6	551.1
50°	901.3	793.2	625.7	520.7	488.7
52.5°	838.9	724.7	561.8	461.3	432.4
55°	778.0	659.2	494.8	403.5	374.5
57.5°	715.6	593.8	435.4	350.2	325.8
60°	651.6	529.8	373.0	295.4	271.0
62.5°	589.2	467.4	319.7	246.6	234.5
65°	525.3	401.9	264.9	213.2	208.6
67.5°	464.4	341.0	213.2	187.3	182.7
70°	400.4	281.7	176.6	161.4	155.3
72.5°	339.5	226.9	147.7	135.5	132.5
75°	280.1	173.6	121.8	111.1	109.6
77.5°	220.8	123.3	95.9	89.8	86.8
80°	166.0	88.3	73.1	67.0	67.0
82.5°	115.7	59.4	50.2	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.4	12.2	12.2	10.7	10.7
90°	0.4	4.8	12.0	11.4	11.6
92.5°	5.3	16.8	54.3	25.0	21.5
95°	12.3	30.3	138.1	52.2	40.2
97.5°	18.3	40.0	225.1	104.6	67.3
100°	27.1	49.0	278.3	208.4	126.1
102.5°	35.2	57.0	280.1	352.3	245.9
105°	43.0	64.8	261.1	466.6	397.1
107.5°	51.4	72.6	243.4	508.0	498.9
110°	59.9	80.5	231.5	501.4	540.4

TEST NUMBER: P999312

CATALOG NUMBER: SA2XXRDIP-B1005D330UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	67.6	88.1	223.7	478.6	539.7
115°	75.7	95.6	218.4	450.8	522.5
117.5°	84.2	103.2	215.6	424.2	496.4
120°	92.0	110.6	213.1	400.4	471.4
122.5°	99.4	118.2	211.7	381.9	445.3
125°	105.7	125.0	210.0	365.2	423.8
127.5°	111.0	131.6	208.9	350.9	403.7
130°	115.6	137.4	208.2	336.5	387.2
132.5°	119.8	143.0	207.9	321.4	369.9
135°	124.0	148.0	207.5	306.8	351.3
137.5°	127.9	152.2	207.5	292.1	333.3
140°	132.5	156.1	207.2	279.0	314.6
142.5°	137.0	159.2	207.2	266.5	295.9
145°	141.6	162.8	206.5	256.3	280.4
147.5°	146.6	165.6	205.4	247.3	266.7
150°	151.5	168.4	204.3	239.6	254.7
152.5°	156.4	171.2	202.6	233.0	244.5
155°	161.0	173.8	200.5	226.8	235.7
157.5°	164.9	176.0	198.4	220.7	227.9
160°	168.8	178.1	196.2	214.8	220.5
162.5°	172.6	179.7	194.5	209.1	213.5
165°	175.5	180.8	192.0	203.6	206.8
167.5°	177.9	181.8	189.9	198.7	200.5
170°	180.4	182.3	188.1	194.2	194.8
172.5°	181.8	182.8	186.0	190.0	190.2
175°	182.8	183.0	184.6	186.9	186.4
177.5°	183.6	183.2	183.2	184.6	183.6
180°	183.2	183.2	183.2	183.2	183.2

(END OF REPORT)