

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999328

Luminaire Tested: SA2XXRDIP-B1005D330UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999328
REPORT IS A COMBINATION OF REPORTS P987879 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D330UB30-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4780.5 lumens
Efficiency: N/A
Efficacy: 67.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999328

CATALOG NUMBER: SA2XXRDIP-B1005D330UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999328

CATALOG NUMBER: SA2XXRDIP-B1005D330UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	104	99	96	92	98	95	91	88	86	83	81	77	75	73	69	68	67
2	95	88	82	77	90	84	78	74	76	72	68	69	65	62	62	60	57
3	87	78	71	65	83	74	68	62	68	62	58	61	57	54	56	52	50
4	80	69	62	56	76	66	59	54	61	55	50	55	51	47	50	46	43
5	74	62	54	48	70	60	52	47	55	49	44	50	45	41	46	42	38
6	68	56	48	42	65	54	47	41	50	43	39	46	40	36	42	37	34
7	64	51	43	38	60	49	42	37	45	39	35	42	36	33	38	34	31
8	59	47	39	34	56	45	38	33	42	35	31	38	33	29	35	31	28
9	55	43	36	30	53	41	34	30	38	32	28	35	30	27	33	28	25
10	52	40	33	28	49	38	32	27	36	30	26	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26869	26869	26869
5°	26912	25563	25373
10°	26648	24245	23445
15°	26282	22689	21246
20°	25798	20919	18947
25°	25301	19103	16843
30°	24634	17336	14546
35°	23981	15553	12573
40°	23317	13801	10541
45°	22545	11994	8768
50°	21747	10251	7139
55°	20917	8508	5668
60°	19952	6805	4287
65°	18841	5188	3486
70°	17496	3764	2772
75°	15814	2871	2117
80°	13365	1942	1421
85°	9337	890	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22545 cd/sqm

TEST NUMBER: P999328

CATALOG NUMBER: SA2XXRDIP-B1005D330UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	3.3
10°-20°	436.7	9.1
20°-30°	613.1	12.8
30°-40°	668.4	14.0
40°-50°	614.3	12.8
50°-60°	482.4	10.1
60°-70°	314.0	6.6
70°-80°	161.7	3.4
80°-90°	42.5	0.9
90°-100°	74.9	1.6
100°-110°	253.2	5.3
110°-120°	266.2	5.6
120°-130°	218.9	4.6
130°-140°	175.9	3.7
140°-150°	132.9	2.8
150°-160°	93.4	2.0
160°-170°	55.0	1.2
170°-180°	17.9	0.4
0°-30°	1209.0	25.3
0°-40°	1877.3	39.3
0°-60°	2974.0	62.2
0°-90°	3492.2	73.1
90°-120°	594.3	12.4
90°-150°	1122.0	23.5
90°-180°	1288.0	26.9
0°-180°	4780.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1697	1690	1670	1684	1679	161
15°	1614	1598	1545	1516	1501	455
25°	1466	1416	1315	1252	1229	674
35°	1263	1184	1049	952	919	790
45°	1032	929	768	659	622	797
55°	785	665	499	407	378	701
65°	530	406	267	215	210	525
75°	283	175	123	112	111	299
85°	66	34	29	29	29	76
90°	0	5	12	12	12	4
95°	12	31	139	53	40	13
105°	43	65	263	471	400	46
115°	76	96	220	455	527	76
125°	107	126	212	368	428	95
135°	125	149	209	310	354	97
145°	143	164	208	259	283	90
155°	162	175	202	229	238	75
165°	177	182	194	205	209	50
175°	184	185	186	188	188	18
180°	185	185	185	185	185	

TEST NUMBER: P999328

CATALOG NUMBER: SA2XXRDIP-B1005D330UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1697.4	1697.4	1697.4	1697.4	1697.4
2.5°	1705.1	1697.4	1680.5	1695.9	1692.8
5°	1697.4	1689.8	1669.8	1683.6	1679.0
7.5°	1683.6	1674.4	1652.9	1659.0	1651.4
10°	1665.2	1654.4	1623.7	1619.1	1609.9
12.5°	1642.1	1628.3	1586.8	1577.6	1560.7
15°	1614.5	1597.6	1545.4	1516.2	1500.8
17.5°	1582.2	1557.6	1493.1	1459.3	1434.8
20°	1545.4	1514.6	1437.8	1399.4	1365.6
22.5°	1505.4	1470.1	1381.0	1328.8	1305.7
25°	1465.5	1416.3	1314.9	1252.0	1228.9
27.5°	1417.9	1365.6	1253.5	1181.3	1146.0
30°	1367.2	1308.8	1185.9	1107.6	1066.1
32.5°	1318.0	1247.3	1121.4	1029.2	990.8
35°	1262.7	1184.4	1049.2	952.4	918.6
37.5°	1208.9	1124.5	981.6	875.6	837.2
40°	1152.1	1059.9	910.9	801.9	761.9
42.5°	1093.7	995.4	840.3	726.6	688.2
45°	1032.3	929.4	768.1	659.0	622.1
47.5°	973.9	864.8	698.9	589.9	556.1
50°	909.4	800.3	631.4	525.4	493.1
52.5°	846.4	731.2	566.8	465.5	436.3
55°	785.0	665.2	499.2	407.1	377.9
57.5°	722.0	599.1	439.3	353.3	328.7
60°	657.5	534.6	376.4	298.0	273.4
62.5°	594.5	471.6	322.6	248.9	236.6
65°	530.0	405.5	267.3	215.1	210.5
67.5°	468.5	344.1	215.1	188.9	184.3
70°	404.0	284.2	178.2	162.8	156.7
72.5°	342.6	228.9	149.0	136.7	133.6
75°	282.7	175.1	122.9	112.1	110.6
77.5°	222.7	124.4	96.8	90.6	87.6
80°	167.4	89.1	73.7	67.6	67.6
82.5°	116.7	59.9	50.7	47.6	47.6
85°	66.1	33.8	29.2	29.2	29.2
87.5°	24.6	12.3	12.3	10.8	10.8
90°	0.4	4.8	12.1	11.6	11.7
92.5°	5.3	16.8	54.7	25.2	21.7
95°	12.4	30.6	139.3	52.6	40.5
97.5°	18.5	40.3	227.1	105.6	67.9
100°	27.4	49.4	280.7	210.2	127.2
102.5°	35.5	57.6	282.5	355.3	248.0
105°	43.4	65.4	263.3	470.6	400.5
107.5°	51.9	73.2	245.5	512.4	503.2
110°	60.4	81.2	233.5	505.6	545.1



TEST NUMBER: P999328

CATALOG NUMBER: SA2XXRDIP-B1005D330UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	68.2	88.8	225.6	482.8	544.4
115°	76.4	96.5	220.3	454.7	527.0
117.5°	84.9	104.1	217.5	427.8	500.7
120°	92.7	111.6	215.0	403.8	475.5
122.5°	100.2	119.2	213.6	385.2	449.2
125°	106.6	126.2	211.8	368.3	427.5
127.5°	111.9	132.8	210.7	354.0	407.2
130°	116.6	138.6	210.0	339.4	390.5
132.5°	120.8	144.2	209.7	324.2	373.1
135°	125.1	149.2	209.3	309.6	354.3
137.5°	129.0	153.5	209.3	294.6	336.2
140°	133.6	157.4	208.9	281.5	317.3
142.5°	138.2	160.6	208.9	268.8	298.5
145°	142.8	164.2	208.2	258.6	282.9
147.5°	147.8	167.0	207.2	249.4	269.0
150°	152.8	169.9	206.1	241.6	256.9
152.5°	157.8	172.7	204.3	235.0	246.6
155°	162.4	175.4	202.2	228.6	237.7
157.5°	166.3	177.5	200.1	222.6	229.9
160°	170.2	179.6	197.9	216.6	222.4
162.5°	174.1	181.2	196.2	210.9	215.3
165°	177.0	182.3	193.7	205.4	208.6
167.5°	179.4	183.4	191.5	200.4	202.2
170°	181.9	183.9	189.8	195.8	196.5
172.5°	183.4	184.4	187.6	191.7	191.9
175°	184.4	184.6	186.2	188.5	188.0
177.5°	185.1	184.8	184.8	186.2	185.1
180°	184.8	184.8	184.8	184.8	184.8

(END OF REPORT)