

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998292

Luminaire Tested: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998292
REPORT IS A COMBINATION OF REPORTS P984032 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3818.0 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	37	36	35
2	86	79	73	69	78	72	67	63	58	54	51	45	42	40	33	31	30
3	79	70	63	57	71	63	57	53	51	47	43	40	37	35	29	27	26
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	19	18
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9148	9148	9148	9148
5°	9169	9753	9205	7760
10°	9062	10647	9120	6398
15°	8843	11230	8966	5389
20°	8706	10545	8706	4684
25°	8428	9060	8466	4189
30°	7971	7121	8124	3794
35°	7566	4924	7693	3471
40°	7102	3717	7183	3214
45°	6528	3056	6635	2936
50°	6033	2681	6043	2688
55°	5468	2286	5502	2418
60°	4867	1908	4934	2111
65°	4326	1552	4405	1802
70°	3789	1217	3885	1454
75°	3183	884	3306	1055
80°	2483	561	2659	626
85°	1624	282	1752	209

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9457 cd/sqm

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.0	1.4
10°-20°	160.2	4.2
20°-30°	232.5	6.1
30°-40°	245.1	6.4
40°-50°	216.9	5.7
50°-60°	173.2	4.5
60°-70°	117.6	3.1
70°-80°	60.2	1.6
80°-90°	16.8	0.4
90°-100°	56.2	1.5
100°-110°	178.7	4.7
110°-120°	305.8	8.0
120°-130°	402.1	10.5
130°-140°	451.4	11.8
140°-150°	442.6	11.6
150°-160°	371.3	9.7
160°-170°	246.2	6.4
170°-180°	86.1	2.3
0°-30°	447.8	11.7
0°-40°	692.9	18.1
0°-60°	1083.0	28.4
0°-90°	1277.6	33.5
90°-120°	540.7	14.2
90°-150°	1836.8	48.1
90°-180°	2540.0	66.5
0°-180°	3818.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	578	578	578	578	578	
5°	578	645	581	514	578	55
15°	543	793	551	381	543	153
25°	488	661	490	306	488	223
35°	398	360	405	254	398	249
45°	299	217	304	208	299	232
55°	205	152	206	161	205	183
65°	122	94	124	109	122	121
75°	57	46	59	55	57	61
85°	12	12	12	9	12	13
90°	1	26	1	26	1	3
95°	40	48	40	48	40	45
105°	165	170	165	170	165	174
115°	307	307	307	307	307	303
125°	446	448	446	448	446	399
135°	577	584	577	584	577	446
145°	701	708	701	708	701	438
155°	801	807	801	807	801	369
165°	872	873	872	873	872	246
175°	907	904	907	904	907	86
180°	909	909	909	909	909	

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	581.0	582.3	584.6	585.0	589.4	593.0	597.0	597.0	598.3	597.9	594.3
5°	578.3	582.3	588.1	593.0	601.0	604.5	609.9	613.9	617.4	620.1	619.6
7.5°	573.9	581.0	589.4	598.8	609.4	615.6	623.2	630.3	635.2	639.6	642.7
10°	566.3	578.3	589.9	602.3	616.1	624.5	633.4	642.7	650.3	658.7	666.7
12.5°	556.1	573.4	587.7	604.1	621.0	630.3	644.5	651.6	666.3	687.6	693.4
15°	543.2	566.8	580.1	601.0	623.2	630.7	650.3	661.8	692.0	705.4	721.4
17.5°	531.2	557.5	575.2	599.2	621.0	635.6	654.7	678.3	703.6	722.7	740.5
20°	521.5	546.8	568.1	594.8	622.3	641.0	661.0	689.4	716.9	736.5	750.2
22.5°	499.3	531.7	556.6	586.3	619.6	645.4	664.5	695.6	725.4	737.4	749.3
25°	488.2	516.1	545.0	578.8	617.9	648.5	665.0	699.6	725.8	730.2	732.9
27.5°	467.7	499.3	533.0	571.7	617.4	643.2	664.1	695.6	716.5	713.4	705.4
30°	442.4	481.1	518.4	560.1	611.2	639.2	658.7	687.6	698.3	682.3	668.1
32.5°	423.8	460.2	501.5	549.9	604.1	630.7	649.8	672.5	674.7	645.9	621.9
35°	398.4	438.9	485.5	536.6	592.1	616.1	633.9	647.6	637.0	596.5	568.1
37.5°	375.8	415.8	465.5	517.5	575.7	599.2	613.4	615.6	589.4	553.9	512.1
40°	350.9	392.2	444.2	498.8	557.5	577.9	586.8	580.1	542.4	501.0	452.6
42.5°	326.0	366.9	422.9	478.8	534.4	551.7	555.2	537.0	490.8	442.4	386.4
45°	298.9	341.6	397.5	454.0	507.7	517.5	517.9	491.7	437.1	386.4	334.5
47.5°	276.7	316.3	371.8	428.2	473.5	480.2	477.5	447.3	387.8	330.9	285.6
50°	252.3	290.1	345.1	400.7	439.3	441.1	434.4	391.3	333.1	281.2	245.2
52.5°	226.1	264.3	314.9	368.2	402.9	400.2	387.3	341.1	286.5	243.4	215.9
55°	205.2	239.0	286.5	338.5	362.9	355.4	341.1	294.1	251.0	214.5	190.6
57.5°	182.1	211.9	258.5	303.8	318.0	310.9	296.7	252.7	212.8	185.2	169.2
60°	160.4	187.4	228.3	266.1	277.2	269.6	253.2	213.7	184.8	161.7	149.7
62.5°	140.4	163.9	198.1	232.8	237.2	229.6	215.4	183.4	158.6	140.4	131.5
65°	121.7	143.9	171.5	197.7	201.7	193.7	179.0	155.9	135.0	123.5	115.0
67.5°	103.5	121.3	145.7	164.8	167.0	159.5	147.5	128.8	115.9	103.5	97.3
70°	87.5	100.8	119.9	135.5	136.4	129.3	123.0	106.2	96.4	87.5	82.6
72.5°	72.0	81.3	95.9	107.5	107.9	103.5	97.7	87.1	78.6	72.4	67.5
75°	56.9	64.9	73.7	84.0	83.5	80.0	75.5	68.8	61.7	57.7	55.5
77.5°	43.5	48.4	55.5	62.2	62.2	60.4	57.7	52.9	48.4	44.4	42.2
80°	31.1	34.2	40.0	42.2	43.1	42.6	40.4	36.9	35.1	32.0	31.1
82.5°	20.0	22.2	24.9	27.1	28.4	27.5	27.1	25.3	22.7	21.8	20.9
85°	11.5	12.4	13.8	15.1	15.5	15.1	16.0	14.7	13.3	13.3	12.9
87.5°	4.9	5.3	6.2	6.2	6.7	6.7	6.2	6.7	6.7	6.2	5.8
90°	0.8	2.8	4.9	6.9	9.0	10.0	11.9	15.6	19.3	23.1	26.8
92.5°	16.9	18.3	19.6	21.0	22.3	23.0	23.1	23.3	23.4	23.6	23.8
95°	39.9	41.6	43.3	45.0	46.7	47.5	47.7	48.0	48.4	48.7	49.1
97.5°	66.7	68.2	69.8	71.3	72.8	73.6	73.9	74.6	75.3	76.0	76.7
100°	97.4	98.8	100.1	101.5	102.8	103.5	103.8	104.3	104.8	105.3	105.8
102.5°	129.6	130.6	131.6	132.7	133.7	134.2	134.5	135.2	135.9	136.6	137.3
105°	164.9	165.4	165.9	166.4	166.9	167.2	167.4	167.7	168.0	168.4	168.7
107.5°	200.1	200.8	201.5	202.2	202.9	203.2	203.2	203.2	203.2	203.2	203.2
110°	233.9	234.9	235.9	237.0	238.0	238.5	238.5	238.5	238.5	238.5	238.5



TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	270.7	271.7	272.7	273.8	274.8	275.3	275.2	275.0	274.9	274.7	274.5
115°	306.7	307.7	308.7	309.8	310.8	311.3	311.1	310.8	310.5	310.1	309.8
117.5°	342.8	344.2	345.5	346.9	348.2	348.9	348.5	347.6	346.8	345.9	345.1
120°	378.8	380.2	381.5	382.9	384.2	384.9	384.2	382.9	381.5	380.2	378.8
122.5°	411.8	413.5	415.2	416.9	418.6	419.4	419.0	418.1	417.3	416.4	415.6
125°	446.3	447.8	449.4	450.9	452.4	453.2	452.9	452.4	451.9	451.4	450.9
127.5°	480.0	481.9	483.7	485.6	487.5	488.4	488.1	487.4	486.7	486.1	485.4
130°	511.5	513.7	515.9	518.1	520.3	521.4	521.2	520.9	520.6	520.2	519.9
132.5°	546.7	548.4	550.1	551.8	553.5	554.4	554.5	554.7	554.8	555.0	555.2
135°	577.4	579.3	581.1	583.0	584.9	585.8	586.0	586.3	586.7	587.0	587.4
137.5°	611.1	612.6	614.2	615.7	617.2	618.0	618.2	618.5	618.9	619.2	619.6
140°	641.0	642.5	644.1	645.6	647.1	647.9	648.3	649.2	650.1	650.9	651.8
142.5°	671.7	673.2	674.8	676.3	677.8	678.6	678.9	679.4	679.9	680.4	680.9
145°	700.8	702.0	703.2	704.4	705.6	706.2	706.7	707.7	708.8	709.8	710.8
147.5°	726.9	728.4	730.0	731.5	733.0	733.8	734.1	734.8	735.5	736.2	736.9
150°	753.8	754.8	755.8	756.9	757.9	758.4	758.7	759.4	760.1	760.7	761.4
152.5°	777.5	778.5	779.5	780.6	781.6	782.1	782.5	783.4	784.3	785.1	786.0
155°	801.3	801.8	802.3	802.8	803.3	803.6	803.9	804.4	804.9	805.4	805.9
157.5°	822.0	822.3	822.7	823.0	823.3	823.5	823.7	824.0	824.4	824.7	825.1
160°	840.4	840.7	841.1	841.4	841.7	841.9	842.0	842.2	842.3	842.5	842.7
162.5°	857.3	857.3	857.3	857.3	857.3	857.3	857.4	857.5	857.7	857.8	858.0
165°	871.8	871.6	871.5	871.3	871.2	871.1	871.1	871.1	871.1	871.1	871.1
167.5°	884.9	884.4	883.9	883.4	882.9	882.6	882.6	882.6	882.6	882.6	882.6
170°	894.8	894.3	893.8	893.3	892.8	892.5	892.4	892.3	892.1	892.0	891.8
172.5°	901.7	901.2	900.7	900.2	899.7	899.4	899.3	899.2	899.0	898.9	898.7
175°	907.1	906.6	906.1	905.6	905.1	904.8	904.6	904.3	904.0	903.6	903.3
177.5°	910.2	909.7	909.2	908.7	908.2	907.9	907.7	907.4	907.0	906.7	906.3
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	600.5	601.0	601.9	606.3	608.5	609.0	607.2	611.2	612.5	611.2	610.3
5°	629.0	631.6	637.0	642.7	642.3	642.7	645.4	648.1	649.0	645.4	646.7
7.5°	653.8	659.2	665.0	673.8	673.8	678.3	680.1	682.3	687.6	684.9	684.1
10°	682.3	689.4	700.0	714.3	714.7	719.1	723.6	730.7	732.9	731.1	732.0
12.5°	717.8	731.6	732.5	748.0	755.1	756.0	763.1	761.8	766.2	766.2	773.8
15°	733.4	754.7	766.7	781.8	786.2	780.9	786.7	792.9	793.3	793.3	792.9
17.5°	761.3	769.8	781.8	789.8	791.5	791.5	792.0	794.7	792.9	789.3	792.0
20°	767.1	770.7	775.1	774.2	775.1	770.7	766.2	761.8	762.2	760.0	766.7
22.5°	756.5	755.6	745.3	738.7	738.7	729.8	721.4	717.4	713.4	714.7	716.9
25°	729.8	716.0	703.6	693.8	691.6	677.4	665.8	662.3	655.6	661.0	661.8
27.5°	687.2	671.6	651.6	643.2	631.6	625.9	617.9	607.2	593.4	601.4	600.1
30°	641.4	618.3	601.9	581.4	563.2	561.9	546.8	529.0	521.9	521.9	525.9
32.5°	590.3	559.7	535.7	506.8	489.1	481.5	463.3	445.5	449.5	436.2	441.1
35°	530.8	490.4	460.2	432.2	418.9	410.0	386.4	376.7	366.0	359.8	371.3
37.5°	473.9	427.3	388.7	358.0	353.1	337.1	321.1	314.9	308.7	311.4	310.9
40°	404.7	363.3	328.7	304.7	296.3	288.7	278.1	270.5	266.5	268.7	269.2
42.5°	342.0	307.4	281.6	264.7	257.6	252.3	247.0	240.8	239.4	239.4	241.2
45°	293.6	265.2	247.9	234.1	230.1	226.1	222.1	219.4	218.5	216.8	218.1
47.5°	255.0	232.3	221.7	211.4	207.0	206.1	202.6	201.2	199.4	199.0	199.4
50°	222.5	208.3	198.6	192.8	189.7	188.3	186.6	183.9	183.0	185.2	184.3
52.5°	199.9	186.6	181.2	175.5	173.7	171.9	169.2	169.7	169.2	168.3	168.3
55°	177.2	168.8	163.5	159.0	158.6	156.8	154.6	153.7	153.2	152.4	153.7
57.5°	159.0	152.4	147.5	143.5	141.7	141.7	139.5	137.7	137.7	137.3	137.7
60°	140.8	134.1	131.0	127.0	125.7	125.3	123.9	123.0	121.7	121.7	121.7
62.5°	123.9	118.6	115.0	111.5	111.9	109.7	107.9	107.0	107.0	107.5	107.5
65°	107.9	104.4	99.9	96.8	95.9	95.5	94.6	94.2	92.8	93.7	93.7
67.5°	93.3	88.4	85.7	84.4	83.1	82.6	81.7	80.8	80.4	80.0	80.8
70°	78.6	74.6	72.4	71.5	70.2	69.7	69.3	68.0	68.4	68.8	69.3
72.5°	65.3	61.7	61.3	58.6	58.6	58.6	56.9	57.7	57.3	56.4	57.3
75°	51.5	49.7	48.9	47.5	48.0	47.5	47.1	45.8	45.8	46.2	46.6
77.5°	40.9	39.1	38.6	37.3	36.4	37.3	36.4	36.0	36.0	36.4	36.4
80°	30.2	29.3	28.0	28.0	28.0	27.5	27.5	27.5	27.1	26.7	27.1
82.5°	20.0	20.0	19.5	19.1	19.5	18.7	19.1	19.1	19.1	19.1	19.1
85°	12.9	12.4	12.4	12.0	12.0	12.0	12.4	11.5	11.5	12.0	12.0
87.5°	5.8	5.8	5.8	6.2	5.8	5.8	5.8	6.2	5.8	5.8	5.8
90°	26.5	26.1	25.8	25.5	25.3	25.4	25.6	25.7	25.9	26.1	25.9
92.5°	24.0	24.1	24.3	24.4	24.5	24.5	24.5	24.5	24.5	24.5	24.5
95°	49.1	49.1	49.1	49.1	49.1	48.9	48.6	48.2	47.9	47.5	47.9
97.5°	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7
100°	105.8	105.8	105.8	105.8	105.8	105.7	105.6	105.4	105.3	105.1	105.3
102.5°	137.5	137.6	137.8	137.9	138.0	137.9	137.8	137.6	137.5	137.3	137.5
105°	169.0	169.4	169.7	170.0	170.2	170.2	170.2	170.2	170.2	170.2	170.2
107.5°	203.4	203.6	203.7	203.9	204.0	203.6	202.7	201.8	201.0	200.1	201.0
110°	238.5	238.5	238.5	238.5	238.5	238.2	237.7	237.2	236.7	236.2	236.7

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	274.0	273.5	273.0	272.5	272.2	272.0	271.7	271.4	271.0	270.7	271.0
115°	309.6	309.4	309.3	309.1	309.0	308.7	308.2	307.7	307.2	306.7	307.2
117.5°	344.6	344.1	343.6	343.1	342.8	342.5	342.0	341.5	341.0	340.5	341.0
120°	378.8	378.8	378.8	378.8	378.8	378.5	378.0	377.5	377.0	376.5	377.0
122.5°	415.1	414.6	414.1	413.6	413.3	413.1	412.8	412.5	412.1	411.8	412.1
125°	450.4	449.9	449.4	448.9	448.6	448.5	448.3	448.2	448.0	447.8	448.0
127.5°	484.7	484.0	483.3	482.6	482.3	482.0	481.5	481.0	480.5	480.0	480.5
130°	519.6	519.2	518.9	518.6	518.4	518.1	517.4	516.7	516.0	515.3	516.0
132.5°	554.3	553.5	552.6	551.7	551.3	551.0	550.5	550.0	549.5	549.0	549.5
135°	587.2	587.0	586.9	586.7	586.6	586.3	585.8	585.3	584.8	584.3	584.8
137.5°	619.4	619.2	619.1	618.9	618.8	618.5	617.8	617.1	616.4	615.7	616.4
140°	651.8	651.8	651.8	651.8	651.8	651.5	650.8	650.1	649.4	648.7	649.4
142.5°	681.1	681.3	681.4	681.6	681.7	681.4	680.7	680.0	679.3	678.6	679.3
145°	711.0	711.2	711.3	711.5	711.6	711.3	710.6	709.9	709.2	708.5	709.2
147.5°	737.2	737.6	737.9	738.2	738.4	738.1	737.4	736.7	736.1	735.4	736.1
150°	761.9	762.4	762.9	763.4	763.7	763.4	762.9	762.4	761.9	761.4	761.9
152.5°	786.7	787.3	788.0	788.7	789.0	788.7	788.0	787.3	786.7	786.0	786.7
155°	806.7	807.6	808.4	809.3	809.7	809.4	808.9	808.4	807.9	807.4	807.9
157.5°	826.3	827.5	828.6	829.8	830.4	830.0	829.1	828.3	827.4	826.6	827.4
160°	843.7	844.7	845.8	846.8	847.3	847.0	846.3	845.6	844.9	844.2	844.9
162.5°	859.2	860.4	861.6	862.8	863.4	863.0	862.1	861.3	860.4	859.6	860.4
165°	872.3	873.5	874.6	875.8	876.4	876.0	875.1	874.3	873.4	872.6	873.4
167.5°	883.8	885.0	886.1	887.3	887.9	887.5	886.6	885.8	884.9	884.1	884.9
170°	893.0	894.2	895.3	896.5	897.1	896.6	895.6	894.5	893.5	892.5	893.5
172.5°	899.9	901.1	902.2	903.4	904.0	903.5	902.5	901.4	900.4	899.4	900.4
175°	904.5	905.7	906.9	908.1	908.7	908.2	907.1	906.1	905.0	904.0	905.0
177.5°	907.3	908.4	909.4	910.5	911.0	910.5	909.4	908.4	907.3	906.3	907.3
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	612.5	609.4	606.8	607.2	609.4	607.7	603.2	597.4	595.2	592.5	595.2
5°	649.4	646.7	641.4	641.9	640.5	638.7	631.6	622.8	622.8	615.6	614.8
7.5°	685.8	681.8	678.3	677.4	672.5	668.9	662.7	650.3	645.4	637.0	632.1
10°	726.7	723.6	719.6	714.7	712.0	705.8	695.6	677.4	668.5	657.0	648.5
12.5°	768.0	767.6	758.7	748.9	748.5	738.7	731.6	707.1	695.2	679.6	659.6
15°	794.2	792.0	787.1	782.2	783.5	772.9	756.9	728.0	720.0	701.4	680.1
17.5°	793.8	793.8	792.4	791.5	790.2	787.1	778.2	759.1	746.2	722.7	702.7
20°	768.4	774.2	775.6	775.1	779.6	781.8	781.3	769.3	759.1	738.2	717.8
22.5°	717.8	731.1	736.9	740.5	749.8	754.7	766.2	761.8	759.1	743.6	726.2
25°	670.7	675.2	692.5	693.4	706.3	718.3	729.8	737.4	747.1	741.4	726.7
27.5°	609.9	620.1	632.5	641.9	644.5	668.9	688.0	702.3	724.5	726.2	721.4
30°	541.0	545.9	566.3	578.8	593.0	610.8	638.3	662.7	682.7	700.9	707.1
32.5°	457.1	477.1	489.1	504.2	516.6	548.1	581.9	613.4	636.5	667.2	680.5
35°	380.2	395.8	416.2	422.4	445.1	471.7	515.7	556.1	591.2	622.3	649.4
37.5°	316.7	329.1	350.9	360.7	374.0	408.2	445.1	495.3	537.5	575.7	609.4
40°	273.2	282.5	298.9	302.0	313.2	344.2	374.0	421.1	477.1	528.6	565.5
42.5°	243.4	247.9	259.0	263.0	270.1	290.9	317.6	362.0	414.0	467.3	519.3
45°	222.1	225.2	231.9	235.4	244.3	253.6	275.4	310.9	351.8	405.5	461.5
47.5°	203.0	207.0	209.7	211.9	216.8	227.0	241.2	267.4	306.5	355.8	410.0
50°	187.0	188.3	193.2	193.7	196.8	203.4	216.8	232.8	263.8	303.8	356.2
52.5°	171.0	172.3	175.5	178.6	179.9	185.2	194.1	207.4	230.5	262.1	308.7
55°	155.0	156.8	159.9	162.1	163.5	167.9	173.2	186.1	204.3	226.5	264.7
57.5°	139.0	143.0	143.9	145.2	147.5	152.4	157.2	164.8	179.0	199.4	227.4
60°	123.9	125.3	128.4	129.7	131.9	134.6	140.8	146.6	156.8	172.8	198.1
62.5°	108.4	111.5	112.8	114.2	115.9	119.0	123.0	129.3	138.1	151.0	171.0
65°	95.1	95.5	98.2	99.9	101.7	103.9	107.9	113.7	119.0	131.0	145.7
67.5°	82.2	83.1	84.0	85.7	87.9	90.2	93.7	96.8	103.5	111.5	123.0
70°	69.7	69.7	72.0	73.3	72.8	75.5	78.2	81.7	86.6	94.2	103.5
72.5°	58.6	58.2	60.0	60.4	61.3	63.1	64.9	68.4	71.1	76.8	84.0
75°	46.6	47.5	48.4	48.4	49.7	51.1	52.9	54.6	57.7	61.3	66.6
77.5°	36.9	36.9	37.8	38.2	39.5	39.1	40.9	42.6	44.9	48.0	52.0
80°	27.1	28.0	28.0	28.0	28.4	28.9	30.6	32.0	33.3	35.5	37.3
82.5°	19.1	19.1	20.0	20.0	20.0	20.9	20.9	21.3	22.2	23.5	24.9
85°	12.0	12.0	12.0	12.4	12.0	12.4	13.3	12.9	13.3	14.2	14.2
87.5°	5.8	5.8	5.8	5.8	5.8	6.2	5.8	6.2	6.7	6.7	6.7
90°	25.7	25.6	25.4	25.3	25.5	25.8	26.1	26.5	26.8	23.1	19.3
92.5°	24.5	24.5	24.5	24.5	24.4	24.3	24.1	24.0	23.8	23.6	23.4
95°	48.2	48.6	48.9	49.1	49.1	49.1	49.1	49.1	49.1	48.7	48.4
97.5°	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.0	75.3
100°	105.4	105.6	105.7	105.8	105.8	105.8	105.8	105.8	105.8	105.3	104.8
102.5°	137.6	137.8	137.9	138.0	137.9	137.8	137.6	137.5	137.3	136.6	135.9
105°	170.2	170.2	170.2	170.2	170.0	169.7	169.4	169.0	168.7	168.4	168.0
107.5°	201.8	202.7	203.6	204.0	203.9	203.7	203.6	203.4	203.2	203.2	203.2
110°	237.2	237.7	238.2	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	271.4	271.7	272.0	272.2	272.5	273.0	273.5	274.0	274.5	274.7	274.9
115°	307.7	308.2	308.7	309.0	309.1	309.3	309.4	309.6	309.8	310.1	310.5
117.5°	341.5	342.0	342.5	342.8	343.1	343.6	344.1	344.6	345.1	345.9	346.8
120°	377.5	378.0	378.5	378.8	378.8	378.8	378.8	378.8	378.8	380.2	381.5
122.5°	412.5	412.8	413.1	413.3	413.6	414.1	414.6	415.1	415.6	416.4	417.3
125°	448.2	448.3	448.5	448.6	448.9	449.4	449.9	450.4	450.9	451.4	451.9
127.5°	481.0	481.5	482.0	482.3	482.6	483.3	484.0	484.7	485.4	486.1	486.7
130°	516.7	517.4	518.1	518.4	518.6	518.9	519.2	519.6	519.9	520.2	520.6
132.5°	550.0	550.5	551.0	551.3	551.7	552.6	553.5	554.3	555.2	555.0	554.8
135°	585.3	585.8	586.3	586.6	586.7	586.9	587.0	587.2	587.4	587.0	586.7
137.5°	617.1	617.8	618.5	618.8	618.9	619.1	619.2	619.4	619.6	619.2	618.9
140°	650.1	650.8	651.5	651.8	651.8	651.8	651.8	651.8	651.8	650.9	650.1
142.5°	680.0	680.7	681.4	681.7	681.6	681.4	681.3	681.1	680.9	680.4	679.9
145°	709.9	710.6	711.3	711.6	711.5	711.3	711.2	711.0	710.8	709.8	708.8
147.5°	736.7	737.4	738.1	738.4	738.2	737.9	737.6	737.2	736.9	736.2	735.5
150°	762.4	762.9	763.4	763.7	763.4	762.9	762.4	761.9	761.4	760.7	760.1
152.5°	787.3	788.0	788.7	789.0	788.7	788.0	787.3	786.7	786.0	785.1	784.3
155°	808.4	808.9	809.4	809.7	809.3	808.4	807.6	806.7	805.9	805.4	804.9
157.5°	828.3	829.1	830.0	830.4	829.8	828.6	827.5	826.3	825.1	824.7	824.4
160°	845.6	846.3	847.0	847.3	846.8	845.8	844.7	843.7	842.7	842.5	842.3
162.5°	861.3	862.1	863.0	863.4	862.8	861.6	860.4	859.2	858.0	857.8	857.7
165°	874.3	875.1	876.0	876.4	875.8	874.6	873.5	872.3	871.1	871.1	871.1
167.5°	885.8	886.6	887.5	887.9	887.3	886.1	885.0	883.8	882.6	882.6	882.6
170°	894.5	895.6	896.6	897.1	896.5	895.3	894.2	893.0	891.8	892.0	892.1
172.5°	901.4	902.5	903.5	904.0	903.4	902.2	901.1	899.9	898.7	898.9	899.0
175°	906.1	907.1	908.2	908.7	908.1	906.9	905.7	904.5	903.3	903.6	904.0
177.5°	908.4	909.4	910.5	911.0	910.5	909.4	908.4	907.3	906.3	906.7	907.0
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	593.0	590.8	589.4	590.3	587.7	581.0	581.0	583.2	580.6	577.9	573.9
5°	609.4	605.0	602.3	601.9	595.7	585.0	582.8	580.6	574.8	568.6	561.9
7.5°	625.4	617.4	613.0	609.9	601.0	587.2	581.4	576.6	567.2	557.9	549.5
10°	638.7	627.2	621.9	617.0	605.4	588.1	578.8	569.9	557.9	545.9	535.2
12.5°	649.4	636.1	629.4	622.3	608.1	585.4	573.9	559.7	547.7	531.7	521.0
15°	667.2	639.6	633.4	626.8	612.1	581.0	566.8	550.8	534.4	513.0	501.5
17.5°	681.4	644.5	644.1	629.9	610.8	579.2	557.5	536.6	518.8	497.5	479.3
20°	689.8	652.1	645.0	630.3	606.3	567.2	544.6	521.5	502.4	476.6	458.4
22.5°	696.9	662.7	644.1	626.3	597.0	563.2	529.9	508.2	481.9	454.0	436.6
25°	699.6	665.0	645.4	625.0	590.3	551.7	513.9	490.4	461.1	435.7	412.2
27.5°	700.0	664.5	640.5	619.2	581.0	536.6	497.9	473.1	440.6	411.3	387.8
30°	695.6	659.6	637.9	614.8	572.1	522.8	478.4	450.9	416.2	386.9	362.5
32.5°	682.3	649.8	632.1	606.8	560.6	503.7	459.7	429.1	392.7	363.8	340.2
35°	660.1	637.9	618.3	594.8	545.5	485.9	441.1	405.1	368.2	340.7	318.5
37.5°	632.5	620.5	602.3	579.2	528.1	470.0	420.2	380.2	343.4	316.7	294.9
40°	595.2	598.3	580.6	559.7	507.7	448.2	393.1	354.9	320.3	295.4	274.1
42.5°	554.8	567.7	557.5	537.5	485.1	424.2	373.1	330.9	297.2	271.4	253.6
45°	511.3	533.5	527.3	512.6	461.5	398.9	344.7	303.8	274.1	249.2	233.6
47.5°	463.7	495.3	495.3	484.6	435.3	373.6	320.3	278.5	249.2	231.4	216.3
50°	415.3	450.9	456.6	449.5	406.0	344.7	290.5	252.7	227.4	210.1	199.0
52.5°	364.7	406.0	416.6	413.1	374.9	317.2	266.1	229.2	206.1	191.0	181.2
55°	316.3	364.2	375.8	377.1	341.6	286.9	239.0	206.5	184.3	174.1	165.7
57.5°	270.5	316.7	329.6	331.8	307.8	259.4	213.7	185.2	165.2	156.8	150.1
60°	231.4	270.1	286.9	291.8	271.0	227.4	190.1	162.6	147.5	139.5	133.3
62.5°	199.4	230.5	248.3	249.6	240.3	199.4	165.7	142.6	129.7	122.6	119.5
65°	168.3	196.3	207.0	212.3	204.8	172.8	143.0	123.9	113.7	107.5	104.4
67.5°	143.5	161.2	170.1	177.2	169.7	145.7	121.7	106.2	98.6	92.4	90.6
70°	117.7	132.4	139.0	146.1	139.5	121.3	103.9	89.7	83.1	78.2	76.0
72.5°	94.2	105.7	111.9	116.4	112.4	97.3	83.1	73.3	68.4	64.9	63.5
75°	74.6	82.6	86.2	89.3	87.5	76.0	67.1	59.1	54.6	51.5	50.6
77.5°	56.9	62.6	66.6	67.5	65.3	57.7	50.2	45.3	41.8	40.0	39.1
80°	40.4	44.0	46.2	47.5	45.3	42.2	36.9	33.3	30.2	28.0	27.5
82.5°	27.1	28.9	30.6	30.2	29.3	26.7	23.5	21.8	20.4	18.7	18.7
85°	15.5	16.0	16.9	17.3	16.9	15.1	13.3	12.4	11.5	10.2	10.2
87.5°	6.7	7.1	7.1	7.6	6.7	6.7	5.8	4.9	4.9	4.4	4.0
90°	15.6	11.9	10.0	9.0	6.9	4.9	2.8	0.8	2.8	4.9	6.9
92.5°	23.3	23.1	23.0	22.3	21.0	19.6	18.3	16.9	18.3	19.6	21.0
95°	48.0	47.7	47.5	46.7	45.0	43.3	41.6	39.9	41.6	43.3	45.0
97.5°	74.6	73.9	73.6	72.8	71.3	69.8	68.2	66.7	68.2	69.8	71.3
100°	104.3	103.8	103.5	102.8	101.5	100.1	98.8	97.4	98.8	100.1	101.5
102.5°	135.2	134.5	134.2	133.7	132.7	131.6	130.6	129.6	130.6	131.6	132.7
105°	167.7	167.4	167.2	166.9	166.4	165.9	165.4	164.9	165.4	165.9	166.4
107.5°	203.2	203.2	203.2	202.9	202.2	201.5	200.8	200.1	200.8	201.5	202.2
110°	238.5	238.5	238.5	238.0	237.0	235.9	234.9	233.9	234.9	235.9	237.0

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	275.0	275.2	275.3	274.8	273.8	272.7	271.7	270.7	271.7	272.7	273.8
115°	310.8	311.1	311.3	310.8	309.8	308.7	307.7	306.7	307.7	308.7	309.8
117.5°	347.6	348.5	348.9	348.2	346.9	345.5	344.2	342.8	344.2	345.5	346.9
120°	382.9	384.2	384.9	384.2	382.9	381.5	380.2	378.8	380.2	381.5	382.9
122.5°	418.1	419.0	419.4	418.6	416.9	415.2	413.5	411.8	413.5	415.2	416.9
125°	452.4	452.9	453.2	452.4	450.9	449.4	447.8	446.3	447.8	449.4	450.9
127.5°	487.4	488.1	488.4	487.5	485.6	483.7	481.9	480.0	481.9	483.7	485.6
130°	520.9	521.2	521.4	520.3	518.1	515.9	513.7	511.5	513.7	515.9	518.1
132.5°	554.7	554.5	554.4	553.5	551.8	550.1	548.4	546.7	548.4	550.1	551.8
135°	586.3	586.0	585.8	584.9	583.0	581.1	579.3	577.4	579.3	581.1	583.0
137.5°	618.5	618.2	618.0	617.2	615.7	614.2	612.6	611.1	612.6	614.2	615.7
140°	649.2	648.3	647.9	647.1	645.6	644.1	642.5	641.0	642.5	644.1	645.6
142.5°	679.4	678.9	678.6	677.8	676.3	674.8	673.2	671.7	673.2	674.8	676.3
145°	707.7	706.7	706.2	705.6	704.4	703.2	702.0	700.8	702.0	703.2	704.4
147.5°	734.8	734.1	733.8	733.0	731.5	730.0	728.4	726.9	728.4	730.0	731.5
150°	759.4	758.7	758.4	757.9	756.9	755.8	754.8	753.8	754.8	755.8	756.9
152.5°	783.4	782.5	782.1	781.6	780.6	779.5	778.5	777.5	778.5	779.5	780.6
155°	804.4	803.9	803.6	803.3	802.8	802.3	801.8	801.3	801.8	802.3	802.8
157.5°	824.0	823.7	823.5	823.3	823.0	822.7	822.3	822.0	822.3	822.7	823.0
160°	842.2	842.0	841.9	841.7	841.4	841.1	840.7	840.4	840.7	841.1	841.4
162.5°	857.5	857.4	857.3	857.3	857.3	857.3	857.3	857.3	857.3	857.3	857.3
165°	871.1	871.1	871.1	871.2	871.3	871.5	871.6	871.8	871.6	871.5	871.3
167.5°	882.6	882.6	882.6	882.9	883.4	883.9	884.4	884.9	884.4	883.9	883.4
170°	892.3	892.4	892.5	892.8	893.3	893.8	894.3	894.8	894.3	893.8	893.3
172.5°	899.2	899.3	899.4	899.7	900.2	900.7	901.2	901.7	901.2	900.7	900.2
175°	904.3	904.6	904.8	905.1	905.6	906.1	906.6	907.1	906.6	906.1	905.6
177.5°	907.4	907.7	907.9	908.2	908.7	909.2	909.7	910.2	909.7	909.2	908.7
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	571.7	573.9	573.4	569.0	564.1	560.1	552.6	553.5	550.8	551.2	553.9
5°	557.5	557.5	555.7	549.5	541.5	537.0	528.6	526.4	521.0	520.6	520.1
7.5°	542.4	540.1	537.9	529.0	519.3	512.1	500.6	497.9	492.6	489.1	487.3
10°	524.6	521.5	517.0	506.8	494.8	485.9	473.9	470.4	460.2	455.7	453.1
12.5°	505.0	503.3	496.2	487.7	468.2	458.4	441.1	444.6	434.4	425.5	424.2
15°	485.5	478.8	474.8	461.1	437.5	433.1	419.3	412.2	402.9	395.8	395.8
17.5°	466.4	456.2	447.3	432.6	415.3	402.9	392.7	389.1	377.6	370.5	369.1
20°	441.1	429.5	427.3	406.4	394.4	380.7	370.9	362.0	353.6	350.5	348.2
22.5°	417.1	403.8	400.2	382.4	370.5	356.7	346.9	340.7	334.5	332.3	328.3
25°	391.3	383.3	378.0	358.9	345.6	332.7	326.0	321.6	315.8	315.4	312.7
27.5°	366.5	358.9	353.6	335.4	325.6	313.6	308.3	303.4	300.3	298.9	297.6
30°	345.1	336.7	330.5	317.2	305.2	295.4	290.9	287.8	286.1	283.8	283.4
32.5°	321.6	316.7	308.3	298.1	288.7	279.4	276.7	274.5	271.8	271.0	270.5
35°	301.6	294.9	289.6	278.1	274.1	266.1	263.0	261.2	257.6	256.7	255.9
37.5°	282.1	275.8	270.1	263.0	255.4	251.0	249.2	246.5	244.7	245.2	244.3
40°	262.5	257.6	253.2	245.6	241.2	239.0	235.4	232.8	231.9	232.3	231.9
42.5°	243.4	239.0	236.3	230.5	226.1	223.9	221.7	219.0	220.3	220.3	221.7
45°	226.1	222.1	220.3	215.9	213.2	209.7	207.4	207.0	208.8	208.3	208.3
47.5°	208.3	207.0	204.8	200.8	197.2	195.0	194.6	194.6	196.3	197.2	196.8
50°	194.6	191.9	189.2	186.1	183.4	182.6	181.2	182.1	183.9	183.9	184.8
52.5°	177.2	175.5	174.6	171.9	170.1	170.1	170.1	170.6	171.9	173.2	172.8
55°	162.1	160.8	159.9	158.6	156.4	156.8	156.4	157.2	158.6	159.9	160.8
57.5°	146.1	145.7	144.8	142.6	142.6	142.1	143.5	143.9	146.1	147.0	148.4
60°	131.9	130.6	130.6	128.8	128.8	128.8	130.1	131.5	133.3	133.7	134.6
62.5°	116.8	116.8	116.4	115.0	115.0	116.4	116.8	118.6	119.5	119.5	120.8
65°	102.6	102.2	101.7	102.2	102.6	102.6	103.9	104.8	105.7	106.2	106.6
67.5°	88.4	87.9	88.8	88.4	89.3	91.1	90.6	91.9	93.3	93.3	93.7
70°	75.1	76.0	75.5	76.4	76.0	76.8	78.2	78.6	78.6	79.1	80.4
72.5°	62.6	62.6	62.6	62.2	62.6	63.5	64.4	64.9	65.7	66.2	67.5
75°	50.6	50.6	49.7	50.6	50.6	51.5	52.4	52.4	52.4	53.3	54.6
77.5°	38.2	38.6	38.2	39.1	39.1	39.5	40.4	40.0	40.9	41.3	41.8
80°	28.0	27.5	27.5	27.5	28.0	28.0	28.9	29.3	29.3	30.6	29.8
82.5°	17.8	18.2	17.8	18.2	18.2	18.7	18.2	18.7	19.1	20.0	19.5
85°	10.2	9.8	9.8	10.2	9.8	9.8	10.2	9.8	10.2	9.8	10.2
87.5°	4.0	3.6	3.6	3.6	3.6	3.1	3.1	2.7	2.7	2.7	2.2
90°	9.0	10.0	11.9	15.6	19.3	23.1	26.8	26.5	26.1	25.8	25.5
92.5°	22.3	23.0	23.1	23.3	23.4	23.6	23.8	24.0	24.1	24.3	24.4
95°	46.7	47.5	47.7	48.0	48.4	48.7	49.1	49.1	49.1	49.1	49.1
97.5°	72.8	73.6	73.9	74.6	75.3	76.0	76.7	76.7	76.7	76.7	76.7
100°	102.8	103.5	103.8	104.3	104.8	105.3	105.8	105.8	105.8	105.8	105.8
102.5°	133.7	134.2	134.5	135.2	135.9	136.6	137.3	137.5	137.6	137.8	137.9
105°	166.9	167.2	167.4	167.7	168.0	168.4	168.7	169.0	169.4	169.7	170.0
107.5°	202.9	203.2	203.2	203.2	203.2	203.2	203.2	203.4	203.6	203.7	203.9
110°	238.0	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	274.8	275.3	275.2	275.0	274.9	274.7	274.5	274.0	273.5	273.0	272.5
115°	310.8	311.3	311.1	310.8	310.5	310.1	309.8	309.6	309.4	309.3	309.1
117.5°	348.2	348.9	348.5	347.6	346.8	345.9	345.1	344.6	344.1	343.6	343.1
120°	384.2	384.9	384.2	382.9	381.5	380.2	378.8	378.8	378.8	378.8	378.8
122.5°	418.6	419.4	419.0	418.1	417.3	416.4	415.6	415.1	414.6	414.1	413.6
125°	452.4	453.2	452.9	452.4	451.9	451.4	450.9	450.4	449.9	449.4	448.9
127.5°	487.5	488.4	488.1	487.4	486.7	486.1	485.4	484.7	484.0	483.3	482.6
130°	520.3	521.4	521.2	520.9	520.6	520.2	519.9	519.6	519.2	518.9	518.6
132.5°	553.5	554.4	554.5	554.7	554.8	555.0	555.2	554.3	553.5	552.6	551.7
135°	584.9	585.8	586.0	586.3	586.7	587.0	587.4	587.2	587.0	586.9	586.7
137.5°	617.2	618.0	618.2	618.5	618.9	619.2	619.6	619.4	619.2	619.1	618.9
140°	647.1	647.9	648.3	649.2	650.1	650.9	651.8	651.8	651.8	651.8	651.8
142.5°	677.8	678.6	678.9	679.4	679.9	680.4	680.9	681.1	681.3	681.4	681.6
145°	705.6	706.2	706.7	707.7	708.8	709.8	710.8	711.0	711.2	711.3	711.5
147.5°	733.0	733.8	734.1	734.8	735.5	736.2	736.9	737.2	737.6	737.9	738.2
150°	757.9	758.4	758.7	759.4	760.1	760.7	761.4	761.9	762.4	762.9	763.4
152.5°	781.6	782.1	782.5	783.4	784.3	785.1	786.0	786.7	787.3	788.0	788.7
155°	803.3	803.6	803.9	804.4	804.9	805.4	805.9	806.7	807.6	808.4	809.3
157.5°	823.3	823.5	823.7	824.0	824.4	824.7	825.1	826.3	827.5	828.6	829.8
160°	841.7	841.9	842.0	842.2	842.3	842.5	842.7	843.7	844.7	845.8	846.8
162.5°	857.3	857.3	857.4	857.5	857.7	857.8	858.0	859.2	860.4	861.6	862.8
165°	871.2	871.1	871.1	871.1	871.1	871.1	871.1	872.3	873.5	874.6	875.8
167.5°	882.9	882.6	882.6	882.6	882.6	882.6	882.6	883.8	885.0	886.1	887.3
170°	892.8	892.5	892.4	892.3	892.1	892.0	891.8	893.0	894.2	895.3	896.5
172.5°	899.7	899.4	899.3	899.2	899.0	898.9	898.7	899.9	901.1	902.2	903.4
175°	905.1	904.8	904.6	904.3	904.0	903.6	903.3	904.5	905.7	906.9	908.1
177.5°	908.2	907.9	907.7	907.4	907.0	906.7	906.3	907.3	908.4	909.4	910.5
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	550.8	552.1	549.0	548.1	549.0	545.9	546.8	547.7	547.7	549.0	549.9
5°	518.8	517.0	513.9	513.0	512.1	513.5	512.6	513.9	514.4	517.5	517.9
7.5°	487.3	484.6	481.9	479.3	478.4	476.2	478.4	478.4	481.5	480.6	482.8
10°	450.0	449.5	446.0	444.6	442.9	439.3	444.2	442.9	445.1	449.1	450.0
12.5°	422.4	417.5	419.8	413.5	415.8	412.2	412.7	412.7	416.2	416.6	415.8
15°	396.2	392.2	386.4	383.8	382.4	380.7	386.4	386.9	384.2	390.4	388.2
17.5°	369.6	369.6	364.2	362.9	359.3	361.1	360.2	360.7	359.8	364.2	366.5
20°	346.5	344.2	342.5	342.9	338.5	337.6	336.7	337.6	340.7	343.8	344.7
22.5°	327.8	326.5	322.0	322.9	319.4	320.7	319.8	322.0	322.5	322.5	325.6
25°	310.0	308.3	308.7	306.9	305.6	305.6	304.3	305.6	307.4	308.3	308.7
27.5°	296.7	295.4	293.2	291.8	292.7	290.5	292.3	293.6	293.6	292.7	293.6
30°	280.7	281.6	281.6	277.2	279.0	278.1	279.4	280.3	280.3	280.7	279.8
32.5°	270.1	267.4	267.0	266.5	266.5	264.7	264.7	266.1	266.5	267.0	268.3
35°	255.9	255.9	253.6	255.0	253.2	253.6	253.2	253.6	254.5	253.2	254.5
37.5°	243.0	243.4	242.5	243.4	243.9	243.0	242.1	243.9	243.0	243.0	242.1
40°	231.9	231.4	231.9	231.9	231.9	232.3	231.4	231.4	231.4	230.5	229.6
42.5°	222.5	219.9	220.8	221.2	219.9	219.9	220.3	219.9	221.2	218.5	218.5
45°	209.2	208.3	208.8	208.8	209.7	208.3	209.2	209.7	208.3	207.9	207.0
47.5°	197.2	198.1	197.2	198.1	198.1	199.0	197.2	197.7	198.1	196.3	195.0
50°	185.2	185.2	186.6	186.1	186.6	185.7	185.7	185.2	185.7	184.8	183.4
52.5°	174.1	172.8	175.0	174.6	174.1	173.7	173.2	173.7	172.8	171.9	171.9
55°	160.4	160.4	161.7	162.1	162.1	161.2	160.4	160.8	160.4	159.9	159.5
57.5°	149.2	147.5	148.4	148.8	148.8	147.5	148.4	147.5	147.5	147.9	146.6
60°	135.0	135.0	134.1	135.5	135.5	134.6	134.6	135.0	134.1	133.7	133.3
62.5°	119.9	120.4	121.7	122.2	122.6	121.7	120.8	121.3	121.3	119.9	120.4
65°	107.0	107.9	109.7	109.3	108.4	108.8	107.9	108.4	107.0	107.5	106.2
67.5°	94.6	94.2	94.6	94.6	95.5	95.1	94.2	94.2	93.7	95.1	93.7
70°	81.3	81.3	81.3	81.3	81.7	82.2	81.3	80.4	80.8	80.0	79.5
72.5°	67.5	68.0	67.5	68.4	67.1	68.0	68.0	67.5	67.1	67.1	67.1
75°	54.6	55.5	54.2	54.6	54.2	55.1	54.6	54.6	53.7	53.3	53.7
77.5°	41.8	42.2	41.3	41.8	41.3	41.8	41.8	41.3	41.3	41.3	41.3
80°	29.8	30.2	29.8	29.3	28.9	29.8	28.9	29.3	29.8	29.3	30.2
82.5°	19.1	19.1	18.7	19.1	18.2	18.2	18.7	18.7	18.2	19.1	18.2
85°	9.3	9.3	10.2	9.3	8.9	8.9	8.9	9.3	8.9	9.8	9.3
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.7	1.8
90°	25.3	25.4	25.6	25.7	25.9	26.1	25.9	25.7	25.6	25.4	25.3
92.5°	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5
95°	49.1	48.9	48.6	48.2	47.9	47.5	47.9	48.2	48.6	48.9	49.1
97.5°	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7
100°	105.8	105.7	105.6	105.4	105.3	105.1	105.3	105.4	105.6	105.7	105.8
102.5°	138.0	137.9	137.8	137.6	137.5	137.3	137.5	137.6	137.8	137.9	138.0
105°	170.2	170.2	170.2	170.2	170.2	170.2	170.2	170.2	170.2	170.2	170.2
107.5°	204.0	203.6	202.7	201.8	201.0	200.1	201.0	201.8	202.7	203.6	204.0
110°	238.5	238.2	237.7	237.2	236.7	236.2	236.7	237.2	237.7	238.2	238.5

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	272.2	272.0	271.7	271.4	271.0	270.7	271.0	271.4	271.7	272.0	272.2
115°	309.0	308.7	308.2	307.7	307.2	306.7	307.2	307.7	308.2	308.7	309.0
117.5°	342.8	342.5	342.0	341.5	341.0	340.5	341.0	341.5	342.0	342.5	342.8
120°	378.8	378.5	378.0	377.5	377.0	376.5	377.0	377.5	378.0	378.5	378.8
122.5°	413.3	413.1	412.8	412.5	412.1	411.8	412.1	412.5	412.8	413.1	413.3
125°	448.6	448.5	448.3	448.2	448.0	447.8	448.0	448.2	448.3	448.5	448.6
127.5°	482.3	482.0	481.5	481.0	480.5	480.0	480.5	481.0	481.5	482.0	482.3
130°	518.4	518.1	517.4	516.7	516.0	515.3	516.0	516.7	517.4	518.1	518.4
132.5°	551.3	551.0	550.5	550.0	549.5	549.0	549.5	550.0	550.5	551.0	551.3
135°	586.6	586.3	585.8	585.3	584.8	584.3	584.8	585.3	585.8	586.3	586.6
137.5°	618.8	618.5	617.8	617.1	616.4	615.7	616.4	617.1	617.8	618.5	618.8
140°	651.8	651.5	650.8	650.1	649.4	648.7	649.4	650.1	650.8	651.5	651.8
142.5°	681.7	681.4	680.7	680.0	679.3	678.6	679.3	680.0	680.7	681.4	681.7
145°	711.6	711.3	710.6	709.9	709.2	708.5	709.2	709.9	710.6	711.3	711.6
147.5°	738.4	738.1	737.4	736.7	736.1	735.4	736.1	736.7	737.4	738.1	738.4
150°	763.7	763.4	762.9	762.4	761.9	761.4	761.9	762.4	762.9	763.4	763.7
152.5°	789.0	788.7	788.0	787.3	786.7	786.0	786.7	787.3	788.0	788.7	789.0
155°	809.7	809.4	808.9	808.4	807.9	807.4	807.9	808.4	808.9	809.4	809.7
157.5°	830.4	830.0	829.1	828.3	827.4	826.6	827.4	828.3	829.1	830.0	830.4
160°	847.3	847.0	846.3	845.6	844.9	844.2	844.9	845.6	846.3	847.0	847.3
162.5°	863.4	863.0	862.1	861.3	860.4	859.6	860.4	861.3	862.1	863.0	863.4
165°	876.4	876.0	875.1	874.3	873.4	872.6	873.4	874.3	875.1	876.0	876.4
167.5°	887.9	887.5	886.6	885.8	884.9	884.1	884.9	885.8	886.6	887.5	887.9
170°	897.1	896.6	895.6	894.5	893.5	892.5	893.5	894.5	895.6	896.6	897.1
172.5°	904.0	903.5	902.5	901.4	900.4	899.4	900.4	901.4	902.5	903.5	904.0
175°	908.7	908.2	907.1	906.1	905.0	904.0	905.0	906.1	907.1	908.2	908.7
177.5°	911.0	910.5	909.4	908.4	907.3	906.3	907.3	908.4	909.4	910.5	911.0
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	548.6	552.1	550.8	545.9	551.7	551.7	555.7	555.7	560.6	562.3	565.0
5°	517.5	520.1	522.4	520.1	524.1	530.4	533.9	537.0	543.7	546.4	550.3
7.5°	484.2	489.1	491.3	491.3	497.9	505.0	512.1	516.6	525.9	529.5	533.5
10°	451.7	457.5	462.0	461.5	472.6	477.1	485.9	496.2	505.5	510.8	516.6
12.5°	417.5	420.6	426.9	435.7	438.4	446.4	456.6	469.5	486.4	491.3	499.7
15°	389.1	397.5	402.4	406.4	412.7	420.2	431.3	443.7	460.6	471.3	480.2
17.5°	365.1	376.2	379.3	378.4	386.4	398.0	410.9	420.2	435.3	448.2	456.6
20°	345.6	350.0	355.4	357.6	363.8	376.2	388.7	399.3	411.8	422.0	431.8
22.5°	326.0	329.6	334.0	338.0	342.9	350.0	362.0	375.3	387.3	397.1	408.2
25°	310.0	312.3	316.3	319.4	324.7	329.6	338.0	352.7	366.9	372.7	382.4
27.5°	294.5	296.3	298.9	302.5	305.2	310.0	317.6	329.6	344.2	350.0	363.3
30°	280.7	282.1	284.7	286.5	287.8	293.6	299.4	308.7	319.8	327.8	337.6
32.5°	267.8	269.2	271.8	272.3	274.1	277.2	282.5	290.9	300.7	307.4	315.8
35°	253.6	254.5	257.2	258.1	259.4	262.1	266.1	272.3	281.2	286.1	293.6
37.5°	242.5	242.1	243.9	245.2	247.0	248.3	249.6	255.9	262.5	267.0	272.7
40°	230.5	229.6	230.1	231.9	232.8	234.5	234.5	240.8	245.2	248.7	253.2
42.5°	218.5	218.1	217.2	218.1	219.0	219.4	219.9	224.3	228.8	231.9	236.8
45°	206.5	206.1	205.2	205.7	205.7	206.5	207.9	209.7	212.8	215.4	218.1
47.5°	195.4	194.6	193.2	192.8	193.7	193.7	193.7	195.4	198.6	199.4	202.1
50°	183.9	182.6	180.8	179.9	179.9	179.5	180.3	180.8	183.4	184.3	186.6
52.5°	171.5	170.6	168.8	167.0	167.5	166.6	167.0	167.5	168.3	169.7	171.0
55°	159.0	157.2	155.9	155.5	154.1	154.1	152.8	154.6	154.1	154.6	156.4
57.5°	147.0	145.2	143.0	142.1	140.8	140.4	139.5	139.0	139.5	140.8	142.1
60°	132.8	131.9	130.6	129.3	128.4	127.0	126.1	126.1	125.7	125.7	126.1
62.5°	119.0	118.6	116.8	116.4	115.5	114.6	113.3	112.4	112.4	113.3	113.7
65°	105.7	105.3	103.9	103.5	101.3	100.4	99.9	99.5	98.6	98.6	98.6
67.5°	93.3	91.9	91.9	89.7	87.9	87.1	86.2	85.7	85.7	85.7	86.2
70°	79.5	79.5	78.2	76.8	75.1	75.5	74.2	72.8	72.8	72.0	72.4
72.5°	66.2	65.7	64.4	64.0	62.6	61.3	60.4	61.3	60.0	59.5	60.0
75°	53.3	52.9	52.0	51.1	51.5	50.2	48.9	48.4	48.4	47.5	47.5
77.5°	40.9	41.8	40.0	39.5	38.6	37.8	37.3	36.9	36.9	36.9	37.8
80°	28.4	28.9	28.9	28.0	28.4	27.1	27.1	27.1	25.8	26.2	26.7
82.5°	18.2	18.2	17.8	18.2	17.8	17.8	17.3	17.3	16.9	16.9	17.3
85°	10.2	9.8	9.3	10.2	9.8	9.8	9.3	9.3	9.3	9.3	9.3
87.5°	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.1	3.6	3.6	3.6
90°	25.5	25.8	26.1	26.5	26.8	23.1	19.3	15.6	11.9	10.0	9.0
92.5°	24.4	24.3	24.1	24.0	23.8	23.6	23.4	23.3	23.1	23.0	22.3
95°	49.1	49.1	49.1	49.1	49.1	48.7	48.4	48.0	47.7	47.5	46.7
97.5°	76.7	76.7	76.7	76.7	76.7	76.0	75.3	74.6	73.9	73.6	72.8
100°	105.8	105.8	105.8	105.8	105.8	105.3	104.8	104.3	103.8	103.5	102.8
102.5°	137.9	137.8	137.6	137.5	137.3	136.6	135.9	135.2	134.5	134.2	133.7
105°	170.0	169.7	169.4	169.0	168.7	168.4	168.0	167.7	167.4	167.2	166.9
107.5°	203.9	203.7	203.6	203.4	203.2	203.2	203.2	203.2	203.2	203.2	202.9
110°	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.0

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	272.5	273.0	273.5	274.0	274.5	274.7	274.9	275.0	275.2	275.3	274.8
115°	309.1	309.3	309.4	309.6	309.8	310.1	310.5	310.8	311.1	311.3	310.8
117.5°	343.1	343.6	344.1	344.6	345.1	345.9	346.8	347.6	348.5	348.9	348.2
120°	378.8	378.8	378.8	378.8	378.8	380.2	381.5	382.9	384.2	384.9	384.2
122.5°	413.6	414.1	414.6	415.1	415.6	416.4	417.3	418.1	419.0	419.4	418.6
125°	448.9	449.4	449.9	450.4	450.9	451.4	451.9	452.4	452.9	453.2	452.4
127.5°	482.6	483.3	484.0	484.7	485.4	486.1	486.7	487.4	488.1	488.4	487.5
130°	518.6	518.9	519.2	519.6	519.9	520.2	520.6	520.9	521.2	521.4	520.3
132.5°	551.7	552.6	553.5	554.3	555.2	555.0	554.8	554.7	554.5	554.4	553.5
135°	586.7	586.9	587.0	587.2	587.4	587.0	586.7	586.3	586.0	585.8	584.9
137.5°	618.9	619.1	619.2	619.4	619.6	619.2	618.9	618.5	618.2	618.0	617.2
140°	651.8	651.8	651.8	651.8	651.8	650.9	650.1	649.2	648.3	647.9	647.1
142.5°	681.6	681.4	681.3	681.1	680.9	680.4	679.9	679.4	678.9	678.6	677.8
145°	711.5	711.3	711.2	711.0	710.8	709.8	708.8	707.7	706.7	706.2	705.6
147.5°	738.2	737.9	737.6	737.2	736.9	736.2	735.5	734.8	734.1	733.8	733.0
150°	763.4	762.9	762.4	761.9	761.4	760.7	760.1	759.4	758.7	758.4	757.9
152.5°	788.7	788.0	787.3	786.7	786.0	785.1	784.3	783.4	782.5	782.1	781.6
155°	809.3	808.4	807.6	806.7	805.9	805.4	804.9	804.4	803.9	803.6	803.3
157.5°	829.8	828.6	827.5	826.3	825.1	824.7	824.4	824.0	823.7	823.5	823.3
160°	846.8	845.8	844.7	843.7	842.7	842.5	842.3	842.2	842.0	841.9	841.7
162.5°	862.8	861.6	860.4	859.2	858.0	857.8	857.7	857.5	857.4	857.3	857.3
165°	875.8	874.6	873.5	872.3	871.1	871.1	871.1	871.1	871.1	871.1	871.2
167.5°	887.3	886.1	885.0	883.8	882.6	882.6	882.6	882.6	882.6	882.6	882.9
170°	896.5	895.3	894.2	893.0	891.8	892.0	892.1	892.3	892.4	892.5	892.8
172.5°	903.4	902.2	901.1	899.9	898.7	898.9	899.0	899.2	899.3	899.4	899.7
175°	908.1	906.9	905.7	904.5	903.3	903.6	904.0	904.3	904.6	904.8	905.1
177.5°	910.5	909.4	908.4	907.3	906.3	906.7	907.0	907.4	907.7	907.9	908.2
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	577.9	577.9	577.9	577.9
2.5°	567.2	567.2	573.9	581.0
5°	554.8	557.9	568.6	578.3
7.5°	542.8	548.1	561.5	573.9
10°	528.1	535.2	551.7	566.3
12.5°	513.9	520.6	539.7	556.1
15°	493.9	502.4	522.8	543.2
17.5°	473.9	482.4	507.3	531.2
20°	450.4	461.5	489.5	521.5
22.5°	428.6	442.4	473.5	499.3
25°	404.7	426.0	454.8	488.2
27.5°	383.3	404.7	434.0	467.7
30°	359.3	381.1	411.3	442.4
32.5°	336.3	356.2	385.6	423.8
35°	312.3	331.4	359.8	398.4
37.5°	290.5	309.2	340.2	375.8
40°	269.2	288.7	315.4	350.9
42.5°	249.2	266.5	290.5	326.0
45°	231.0	243.4	265.6	298.9
47.5°	211.9	223.0	243.4	276.7
50°	194.1	203.4	221.2	252.3
52.5°	176.8	184.8	201.2	226.1
55°	161.2	168.8	180.8	205.2
57.5°	145.2	151.0	162.6	182.1
60°	129.7	135.0	144.4	160.4
62.5°	114.2	118.6	127.5	140.4
65°	100.4	103.9	110.6	121.7
67.5°	87.1	89.3	94.6	103.5
70°	74.2	76.0	80.4	87.5
72.5°	60.4	62.2	67.1	72.0
75°	48.9	49.3	52.9	56.9
77.5°	38.2	37.8	40.4	43.5
80°	26.2	27.5	29.8	31.1
82.5°	17.8	18.2	19.1	20.0
85°	9.8	10.2	10.2	11.5
87.5°	4.0	4.4	4.4	4.9
90°	6.9	4.9	2.8	0.8
92.5°	21.0	19.6	18.3	16.9
95°	45.0	43.3	41.6	39.9
97.5°	71.3	69.8	68.2	66.7
100°	101.5	100.1	98.8	97.4
102.5°	132.7	131.6	130.6	129.6
105°	166.4	165.9	165.4	164.9
107.5°	202.2	201.5	200.8	200.1
110°	237.0	235.9	234.9	233.9

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	273.8	272.7	271.7	270.7
115°	309.8	308.7	307.7	306.7
117.5°	346.9	345.5	344.2	342.8
120°	382.9	381.5	380.2	378.8
122.5°	416.9	415.2	413.5	411.8
125°	450.9	449.4	447.8	446.3
127.5°	485.6	483.7	481.9	480.0
130°	518.1	515.9	513.7	511.5
132.5°	551.8	550.1	548.4	546.7
135°	583.0	581.1	579.3	577.4
137.5°	615.7	614.2	612.6	611.1
140°	645.6	644.1	642.5	641.0
142.5°	676.3	674.8	673.2	671.7
145°	704.4	703.2	702.0	700.8
147.5°	731.5	730.0	728.4	726.9
150°	756.9	755.8	754.8	753.8
152.5°	780.6	779.5	778.5	777.5
155°	802.8	802.3	801.8	801.3
157.5°	823.0	822.7	822.3	822.0
160°	841.4	841.1	840.7	840.4
162.5°	857.3	857.3	857.3	857.3
165°	871.3	871.5	871.6	871.8
167.5°	883.4	883.9	884.4	884.9
170°	893.3	893.8	894.3	894.8
172.5°	900.2	900.7	901.2	901.7
175°	905.6	906.1	906.6	907.1
177.5°	908.7	909.2	909.7	910.2
180°	908.7	908.7	908.7	908.7

TEST NUMBER: P998292

CATALOG NUMBER: SA2XXDIP-B290D725UB35-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.75	12.46	12.85	13.55	15.04	9.25	9.96	10.34	11.04	12.54
	3H	12.55	13.19	13.65	14.28	15.79	10.58	11.21	11.68	12.31	13.82
	4H	12.71	13.32	13.83	14.41	15.93	11.03	11.64	12.15	12.73	14.25
	6H	12.75	13.31	13.87	14.41	15.93	11.33	11.89	12.45	12.99	14.51
	8H	12.73	13.25	13.85	14.37	15.89	11.41	11.94	12.54	13.06	14.58
	12H	12.68	13.18	13.81	14.29	15.84	11.45	11.95	12.58	13.06	14.60
4H	2H	11.78	12.38	12.89	13.47	14.99	9.67	10.28	10.79	11.37	12.89
	3H	12.74	13.24	13.87	14.37	15.89	11.12	11.62	12.25	12.75	14.27
	4H	13.01	13.47	14.14	14.59	16.13	11.65	12.11	12.78	13.22	14.77
	6H	13.14	13.53	14.27	14.67	16.21	12.02	12.41	13.16	13.55	15.09
	8H	13.13	13.50	14.27	14.63	16.18	12.13	12.50	13.26	13.62	15.18
	12H	13.09	13.42	14.24	14.56	16.12	12.18	12.51	13.33	13.65	15.21
8H	4H	13.01	13.38	14.15	14.51	16.06	11.78	12.15	12.92	13.28	14.83
	6H	13.18	13.49	14.34	14.66	16.21	12.21	12.51	13.37	13.68	15.23
	8H	13.21	13.48	14.38	14.63	16.20	12.36	12.62	13.52	13.77	15.35
	12H	13.19	13.42	14.36	14.57	16.18	12.44	12.68	13.61	13.82	15.43
12H	4H	12.96	13.29	14.11	14.43	15.99	11.75	12.08	12.90	13.22	14.78
	6H	13.16	13.43	14.32	14.58	16.15	12.21	12.47	13.37	13.62	15.20
	8H	13.19	13.42	14.35	14.57	16.17	12.36	12.59	13.52	13.74	15.35