

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999376

Luminaire Tested: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999376
REPORT IS A COMBINATION OF REPORTS P987927 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5682.0 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67		
1	103	99	95	92	97	93	90	87	83	81	78	74	72	70	65	64	63	58		
2	94	87	82	77	89	83	78	73	74	70	67	66	63	60	58	56	54	51		
3	87	78	71	65	82	74	68	63	66	62	58	59	56	52	53	50	48	44		
4	80	70	62	57	75	66	60	54	60	54	50	54	50	46	48	45	42	39		
5	74	63	55	49	70	60	53	48	54	49	44	49	44	41	44	40	38	35		
6	69	57	49	44	65	55	47	42	50	44	39	45	40	37	40	37	34	31		
7	64	52	44	39	60	50	43	38	45	40	35	41	37	33	37	34	31	28		
8	60	48	40	35	57	46	39	34	42	36	32	38	33	30	35	31	28	26		
9	56	44	37	32	53	42	36	31	39	33	29	35	31	27	32	28	26	24		
10	53	41	34	29	50	39	33	28	36	30	27	33	28	25	30	26	24	22		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	34790	34790	34790	34790
5°	34870	36952	34991	29520
10°	34486	39056	34731	24377
15°	33737	39069	34309	18313
20°	32837	32295	33552	15109
25°	31746	20180	32433	12854
30°	30353	12920	31178	11065
35°	28658	9930	29585	9470
40°	26768	8347	27912	8283
45°	24749	7104	25784	6953
50°	22680	6036	23739	6014
55°	20390	5245	21487	5177
60°	18352	4000	19326	3952
65°	16452	3009	17430	3415
70°	14352	2404	15478	2783
75°	12133	1841	13241	2105
80°	9636	1253	10363	1381
85°	6681	647	7331	682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 31825 cd/sqm

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.5	3.7
10°-20°	581.9	10.2
20°-30°	748.9	13.2
30°-40°	710.4	12.5
40°-50°	608.9	10.7
50°-60°	463.7	8.2
60°-70°	292.4	5.1
70°-80°	145.9	2.6
80°-90°	39.4	0.7
90°-100°	41.6	0.7
100°-110°	132.4	2.3
110°-120°	226.5	4.0
120°-130°	297.9	5.2
130°-140°	334.4	5.9
140°-150°	327.9	5.8
150°-160°	275.1	4.8
160°-170°	182.4	3.2
170°-180°	63.8	1.1
0°-30°	1539.2	27.1
0°-40°	2249.6	39.6
0°-60°	3322.2	58.5
0°-90°	3799.9	66.9
90°-120°	400.5	7.0
90°-150°	1360.8	23.9
90°-180°	1882.0	33.1
0°-180°	5682.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2198	2198	2198	2198	2198	
5°	2199	2445	2207	1953	2199	209
15°	2072	2760	2108	1294	2072	583
25°	1839	1472	1879	938	1839	844
35°	1509	726	1558	692	1509	944
45°	1133	504	1181	493	1133	875
55°	765	350	806	345	765	690
65°	463	182	490	206	463	459
75°	217	96	237	110	217	235
85°	47	28	52	29	47	54
90°	1	19	1	19	1	5
95°	30	35	30	35	30	33
105°	122	126	122	126	122	129
115°	227	227	227	227	227	225
125°	331	332	331	332	331	295
135°	428	433	428	433	428	331
145°	519	525	519	525	519	324
155°	594	598	594	598	594	273
165°	646	646	646	646	646	182
175°	672	670	672	670	672	64
180°	673	673	673	673	673	

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2211.5	2220.7	2225.2	2231.4	2245.1	2254.3	2268.0	2271.1	2269.5	2275.7	2258.9
5°	2199.3	2219.1	2237.5	2252.7	2277.2	2292.5	2309.3	2329.1	2333.7	2356.6	2342.9
7.5°	2182.5	2211.5	2237.5	2268.0	2304.7	2324.5	2350.5	2381.0	2394.8	2422.3	2429.9
10°	2155.0	2196.2	2240.5	2272.6	2323.0	2358.1	2382.6	2431.4	2463.5	2504.7	2498.6
12.5°	2110.7	2164.2	2223.7	2277.2	2342.9	2365.8	2411.6	2462.0	2503.2	2541.4	2575.0
15°	2072.5	2133.6	2199.3	2265.0	2339.8	2382.6	2428.4	2494.1	2538.3	2605.5	2634.6
17.5°	2020.6	2098.5	2176.4	2249.7	2338.3	2387.1	2443.7	2507.8	2573.5	2637.6	2660.5
20°	1967.1	2051.1	2135.1	2234.4	2335.2	2382.6	2440.6	2520.0	2584.2	2634.6	2634.6
22.5°	1903.0	2005.3	2101.5	2196.2	2306.2	2374.9	2434.5	2527.7	2573.5	2584.2	2542.9
25°	1838.8	1941.2	2046.6	2164.2	2289.4	2350.5	2417.7	2504.7	2520.0	2477.3	2370.3
27.5°	1762.5	1877.0	1996.2	2122.9	2254.3	2330.6	2391.7	2449.8	2420.7	2306.2	2139.7
30°	1684.6	1808.3	1942.7	2063.4	2222.2	2292.5	2344.4	2361.2	2269.5	2083.2	1867.9
32.5°	1603.6	1724.3	1866.3	2011.4	2171.8	2239.0	2272.6	2228.3	2060.3	1825.1	1562.4
35°	1509.0	1644.9	1793.0	1944.2	2103.1	2153.5	2173.3	2064.9	1849.5	1545.6	1284.4
37.5°	1423.4	1559.4	1718.2	1872.4	2026.7	2054.2	2034.3	1864.8	1591.4	1290.6	1035.5
40°	1322.6	1467.7	1623.5	1796.1	1922.8	1930.5	1881.6	1661.7	1322.6	1040.1	882.8
42.5°	1229.5	1376.1	1531.9	1707.5	1803.7	1777.8	1712.1	1423.4	1104.2	896.5	769.8
45°	1133.2	1272.2	1440.2	1596.0	1664.7	1603.6	1504.4	1197.4	927.1	771.3	673.5
47.5°	1040.1	1169.9	1336.4	1486.0	1498.3	1429.5	1311.9	1003.4	803.4	678.1	598.7
50°	948.4	1078.3	1234.0	1357.8	1345.5	1250.8	1118.0	872.1	698.0	598.7	533.0
52.5°	856.8	974.4	1125.6	1223.4	1171.4	1079.8	948.4	739.2	609.4	522.3	471.9
55°	765.2	875.1	1005.0	1085.9	1003.4	898.0	804.9	633.8	528.4	458.2	420.0
57.5°	688.8	775.9	895.0	943.9	844.6	762.1	681.2	545.2	458.2	407.8	363.5
60°	604.8	684.2	782.0	811.0	708.7	641.5	572.7	461.2	392.5	348.2	319.2
62.5°	533.0	598.7	673.5	673.5	583.4	533.0	481.1	386.4	329.9	294.8	281.0
65°	462.8	510.1	563.6	557.5	481.1	436.8	395.6	319.2	276.4	252.0	238.3
67.5°	394.0	430.7	465.8	444.4	389.5	351.3	313.1	258.1	229.1	212.3	194.0
70°	331.4	360.4	378.8	358.9	303.9	271.9	244.4	207.7	184.8	163.4	152.7
72.5°	278.0	290.2	296.3	271.9	226.0	207.7	187.9	161.9	142.0	131.3	128.3
75°	216.9	227.6	223.0	204.7	166.5	152.7	137.5	119.1	114.5	108.4	105.4
77.5°	169.5	169.5	161.9	145.1	119.1	108.4	102.3	93.2	88.6	87.1	84.0
80°	120.7	119.1	114.5	96.2	80.9	74.8	74.8	68.7	67.2	64.1	64.1
82.5°	79.4	79.4	73.3	58.0	53.5	51.9	50.4	47.3	47.3	45.8	45.8
85°	47.3	44.3	36.7	32.1	30.5	30.5	29.0	27.5	29.0	27.5	27.5
87.5°	21.4	16.8	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
90°	0.6	2.1	3.6	5.1	6.6	7.4	8.8	11.6	14.3	17.1	19.9
92.5°	12.5	13.5	14.5	15.5	16.5	17.0	17.1	17.2	17.3	17.5	17.6
95°	29.5	30.8	32.0	33.3	34.6	35.2	35.3	35.6	35.9	36.1	36.4
97.5°	49.4	50.5	51.7	52.8	53.9	54.5	54.8	55.3	55.8	56.3	56.8
100°	72.1	73.1	74.1	75.2	76.2	76.7	76.9	77.3	77.6	78.0	78.4
102.5°	96.0	96.8	97.5	98.3	99.0	99.4	99.7	100.2	100.7	101.2	101.7
105°	122.1	122.5	122.9	123.2	123.6	123.8	123.9	124.2	124.5	124.7	125.0
107.5°	148.3	148.8	149.3	149.8	150.3	150.5	150.5	150.5	150.5	150.5	150.5
110°	173.3	174.1	174.8	175.6	176.3	176.7	176.7	176.7	176.7	176.7	176.7



TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	200.5	201.3	202.0	202.8	203.5	203.9	203.8	203.7	203.6	203.5	203.4
115°	227.2	228.0	228.7	229.5	230.2	230.6	230.5	230.2	230.0	229.7	229.5
117.5°	253.9	254.9	255.9	257.0	258.0	258.5	258.2	257.5	256.9	256.2	255.6
120°	280.6	281.6	282.6	283.7	284.7	285.2	284.7	283.7	282.6	281.6	280.6
122.5°	305.1	306.3	307.6	308.8	310.1	310.7	310.4	309.8	309.1	308.5	307.9
125°	330.6	331.7	332.9	334.0	335.1	335.7	335.5	335.1	334.8	334.4	334.0
127.5°	355.6	357.0	358.4	359.8	361.2	361.9	361.6	361.1	360.6	360.1	359.6
130°	378.9	380.5	382.2	383.8	385.5	386.3	386.2	385.9	385.7	385.4	385.2
132.5°	405.0	406.3	407.5	408.8	410.1	410.7	410.8	410.9	411.0	411.2	411.3
135°	427.8	429.2	430.6	431.9	433.3	434.0	434.1	434.4	434.7	434.9	435.2
137.5°	452.8	453.9	455.1	456.2	457.3	457.9	458.0	458.3	458.5	458.8	459.0
140°	474.9	476.0	477.2	478.3	479.4	480.0	480.3	481.0	481.6	482.3	482.9
142.5°	497.6	498.8	499.9	501.1	502.2	502.8	503.0	503.4	503.7	504.1	504.5
145°	519.2	520.1	521.0	521.9	522.8	523.2	523.6	524.3	525.1	525.8	526.6
147.5°	538.5	539.7	540.8	542.0	543.1	543.7	543.9	544.4	544.9	545.4	545.9
150°	558.4	559.2	559.9	560.7	561.4	561.8	562.1	562.6	563.1	563.6	564.1
152.5°	576.0	576.8	577.5	578.3	579.0	579.4	579.7	580.4	581.0	581.7	582.3
155°	593.6	594.0	594.4	594.8	595.2	595.4	595.6	596.0	596.3	596.7	597.1
157.5°	609.0	609.2	609.5	609.7	610.0	610.1	610.2	610.5	610.8	611.0	611.3
160°	622.6	622.9	623.1	623.4	623.7	623.8	623.9	624.0	624.1	624.2	624.3
162.5°	635.1	635.1	635.1	635.1	635.1	635.1	635.2	635.3	635.4	635.6	635.7
165°	645.9	645.8	645.6	645.5	645.4	645.3	645.3	645.3	645.3	645.3	645.3
167.5°	655.6	655.2	654.8	654.5	654.1	653.9	653.9	653.9	653.9	653.9	653.9
170°	663.0	662.6	662.2	661.9	661.5	661.3	661.2	661.1	661.0	660.8	660.7
172.5°	668.1	667.7	667.3	667.0	666.6	666.4	666.3	666.2	666.1	665.9	665.8
175°	672.0	671.6	671.2	670.9	670.5	670.3	670.2	669.9	669.7	669.4	669.2
177.5°	674.3	673.9	673.5	673.2	672.8	672.6	672.5	672.2	672.0	671.7	671.5
180°	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2275.7	2278.7	2283.3	2304.7	2307.7	2313.8	2310.8	2310.8	2312.3	2309.3	2310.8
5°	2373.4	2378.0	2400.9	2426.9	2433.0	2426.9	2434.5	2445.2	2445.2	2445.2	2442.1
7.5°	2465.0	2481.8	2507.8	2546.0	2553.6	2561.3	2575.0	2565.8	2568.9	2582.6	2578.1
10°	2553.6	2578.1	2607.1	2639.1	2655.9	2666.6	2672.7	2686.5	2718.6	2681.9	2695.7
12.5°	2637.6	2672.7	2703.3	2738.4	2750.6	2764.4	2769.0	2781.2	2781.2	2779.7	2790.3
15°	2692.6	2724.7	2752.2	2775.1	2778.1	2775.1	2772.0	2773.5	2778.1	2759.8	2770.5
17.5°	2704.8	2707.9	2717.0	2707.9	2709.4	2677.3	2659.0	2654.4	2611.7	2613.2	2648.3
20°	2645.3	2593.3	2579.6	2529.2	2498.6	2416.2	2413.1	2390.2	2300.1	2327.6	2321.5
22.5°	2481.8	2393.3	2275.7	2217.6	2188.6	2101.5	2034.3	1987.0	1954.9	1922.8	1909.1
25°	2266.5	2122.9	1956.4	1841.9	1825.1	1744.2	1620.4	1562.4	1493.7	1472.3	1509.0
27.5°	1988.5	1802.2	1614.3	1438.7	1406.6	1333.3	1270.7	1229.5	1150.0	1145.5	1148.5
30°	1611.3	1423.4	1266.1	1151.6	1072.2	1038.6	997.3	966.8	934.7	946.9	950.0
32.5°	1324.2	1145.5	998.8	937.8	901.1	879.7	844.6	824.7	811.0	806.4	804.9
35°	1052.3	933.2	867.5	807.9	786.6	771.3	745.3	736.1	723.9	725.5	725.5
37.5°	901.1	801.8	753.0	722.4	702.5	694.9	678.1	668.9	661.3	658.3	662.8
40°	777.4	708.7	678.1	650.6	633.8	630.8	621.6	610.9	601.7	603.3	607.9
42.5°	687.3	647.6	610.9	589.5	577.3	572.7	565.1	557.5	557.5	552.9	551.3
45°	615.5	583.4	552.9	533.0	525.4	519.3	510.1	508.6	502.5	504.0	505.5
47.5°	551.3	525.4	502.5	482.6	475.0	473.5	464.3	458.2	458.2	456.7	455.1
50°	493.3	467.3	447.5	436.8	426.1	423.1	421.5	420.0	416.9	416.9	418.5
52.5°	446.0	420.0	404.7	395.6	389.5	386.4	386.4	384.9	384.9	384.9	383.3
55°	394.0	372.7	360.4	357.4	354.3	352.8	351.3	348.2	346.7	349.7	346.7
57.5°	345.2	337.5	326.8	323.8	316.1	316.1	311.6	308.5	305.5	308.5	308.5
60°	307.0	296.3	290.2	281.0	274.9	268.8	261.2	259.6	256.6	255.1	253.5
62.5°	267.3	258.1	242.8	229.1	219.9	213.8	210.8	209.2	209.2	207.7	207.7
65°	223.0	201.6	194.0	189.4	187.9	186.3	183.3	181.7	183.3	181.7	183.3
67.5°	174.1	171.1	166.5	163.4	161.9	160.4	160.4	158.8	158.8	158.8	158.8
70°	151.2	143.6	142.0	139.0	139.0	137.5	137.5	137.5	137.5	135.9	139.0
72.5°	125.2	120.7	119.1	117.6	117.6	117.6	116.1	116.1	116.1	114.5	116.1
75°	102.3	100.8	97.7	97.7	96.2	97.7	96.2	96.2	94.7	96.2	96.2
77.5°	82.5	80.9	79.4	79.4	77.9	77.9	77.9	77.9	77.9	77.9	79.4
80°	62.6	61.1	59.6	61.1	59.6	61.1	59.6	59.6	61.1	59.6	59.6
82.5°	45.8	44.3	44.3	42.8	42.8	42.8	42.8	42.8	42.8	42.8	42.8
85°	27.5	26.0	26.0	27.5	26.0	27.5	26.0	26.0	26.0	27.5	27.5
87.5°	12.2	13.7	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	13.7
90°	19.6	19.4	19.1	18.8	18.7	18.8	18.9	19.0	19.2	19.3	19.2
92.5°	17.7	17.9	18.0	18.1	18.2	18.2	18.2	18.2	18.2	18.2	18.2
95°	36.4	36.4	36.4	36.4	36.4	36.3	36.0	35.7	35.5	35.2	35.5
97.5°	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8
100°	78.4	78.4	78.4	78.4	78.4	78.3	78.2	78.1	77.9	77.8	77.9
102.5°	101.8	102.0	102.1	102.2	102.3	102.2	102.1	102.0	101.8	101.7	101.8
105°	125.2	125.5	125.7	126.0	126.1	126.1	126.1	126.1	126.1	126.1	126.1
107.5°	150.6	150.8	150.9	151.0	151.1	150.8	150.2	149.5	148.9	148.3	148.9
110°	176.7	176.7	176.7	176.7	176.7	176.5	176.1	175.8	175.4	175.0	175.4

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	203.0	202.6	202.3	201.9	201.7	201.6	201.3	201.0	200.8	200.5	200.8
115°	229.4	229.2	229.1	229.0	228.9	228.7	228.3	228.0	227.6	227.2	227.6
117.5°	255.2	254.8	254.5	254.1	253.9	253.7	253.3	253.0	252.6	252.2	252.6
120°	280.6	280.6	280.6	280.6	280.6	280.4	280.0	279.7	279.3	278.9	279.3
122.5°	307.5	307.1	306.8	306.4	306.2	306.1	305.8	305.6	305.3	305.1	305.3
125°	333.6	333.2	332.9	332.5	332.3	332.2	332.1	332.0	331.9	331.8	331.9
127.5°	359.1	358.6	358.1	357.6	357.3	357.1	356.7	356.4	356.0	355.6	356.0
130°	384.9	384.7	384.4	384.1	384.0	383.8	383.3	382.8	382.3	381.8	382.3
132.5°	410.7	410.1	409.4	408.8	408.5	408.3	407.9	407.5	407.1	406.7	407.1
135°	435.1	434.9	434.8	434.7	434.6	434.4	434.0	433.7	433.3	432.9	433.3
137.5°	458.9	458.7	458.6	458.5	458.4	458.2	457.7	457.2	456.7	456.2	456.7
140°	482.9	482.9	482.9	482.9	482.9	482.6	482.1	481.6	481.1	480.6	481.1
142.5°	504.6	504.7	504.8	504.9	505.0	504.8	504.3	503.8	503.3	502.8	503.3
145°	526.7	526.9	527.0	527.1	527.2	526.9	526.4	525.9	525.4	524.9	525.4
147.5°	546.2	546.4	546.7	547.0	547.1	546.8	546.3	545.8	545.3	544.8	545.3
150°	564.5	564.9	565.2	565.6	565.8	565.6	565.2	564.9	564.5	564.1	564.5
152.5°	582.8	583.3	583.8	584.3	584.6	584.3	583.8	583.3	582.8	582.3	582.8
155°	597.7	598.3	599.0	599.6	599.9	599.7	599.3	599.0	598.6	598.2	598.6
157.5°	612.2	613.0	613.9	614.8	615.2	614.9	614.3	613.6	613.0	612.4	613.0
160°	625.1	625.8	626.6	627.3	627.7	627.5	627.0	626.5	626.0	625.5	626.0
162.5°	636.6	637.5	638.4	639.3	639.7	639.4	638.7	638.1	637.4	636.8	637.4
165°	646.2	647.1	648.0	648.9	649.3	649.0	648.4	647.7	647.1	646.5	647.1
167.5°	654.8	655.6	656.5	657.4	657.8	657.5	656.9	656.2	655.6	655.0	655.6
170°	661.6	662.5	663.4	664.3	664.7	664.3	663.6	662.8	662.1	661.3	662.1
172.5°	666.7	667.6	668.5	669.4	669.8	669.4	668.7	667.9	667.2	666.4	667.2
175°	670.1	671.0	671.9	672.8	673.2	672.8	672.1	671.3	670.6	669.8	670.6
177.5°	672.3	673.0	673.8	674.5	674.9	674.5	673.8	673.0	672.3	671.5	672.3
180°	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2316.9	2306.2	2303.1	2306.2	2303.1	2304.7	2294.0	2254.3	2265.0	2248.2	2257.3
5°	2448.2	2439.1	2419.2	2416.2	2413.1	2410.1	2394.8	2359.7	2345.9	2323.0	2321.5
7.5°	2573.5	2573.5	2558.2	2547.5	2533.8	2523.1	2503.2	2451.3	2429.9	2402.4	2387.1
10°	2697.2	2657.5	2674.3	2663.6	2630.0	2623.9	2587.2	2556.7	2515.4	2487.9	2463.5
12.5°	2785.8	2773.5	2758.3	2749.1	2739.9	2720.1	2695.7	2617.8	2596.4	2541.4	2513.9
15°	2782.7	2775.1	2779.7	2779.7	2776.6	2772.0	2752.2	2695.7	2659.0	2605.5	2558.2
17.5°	2633.0	2652.9	2672.7	2686.5	2717.0	2730.8	2749.1	2715.5	2692.6	2646.8	2596.4
20°	2371.9	2420.7	2478.8	2491.0	2518.5	2599.4	2636.1	2665.1	2674.3	2659.0	2617.8
22.5°	2008.4	2049.6	2190.1	2187.1	2226.8	2323.0	2429.9	2517.0	2585.7	2623.9	2608.6
25°	1573.1	1631.1	1706.0	1762.5	1892.3	2035.9	2168.7	2307.7	2426.9	2532.2	2558.2
27.5°	1189.8	1266.1	1325.7	1400.5	1466.2	1635.7	1806.8	2023.6	2162.6	2362.7	2466.6
30°	962.2	997.3	1056.9	1092.0	1124.1	1253.9	1447.9	1661.7	1906.0	2136.7	2315.4
32.5°	821.7	846.1	890.4	905.7	939.3	1026.3	1148.5	1344.0	1596.0	1875.5	2110.7
35°	737.7	763.6	772.8	786.6	814.0	869.0	953.0	1095.1	1322.6	1596.0	1877.0
37.5°	665.9	679.6	705.6	714.8	723.9	765.2	821.7	921.0	1072.2	1296.7	1608.2
40°	615.5	623.1	636.9	644.5	650.6	679.6	730.0	797.2	908.7	1079.8	1366.9
42.5°	562.0	571.2	580.4	589.5	597.2	620.1	650.6	714.8	789.6	919.4	1127.1
45°	510.1	516.2	526.9	533.0	543.7	562.0	589.5	633.8	701.0	783.5	951.5
47.5°	462.8	470.4	475.0	482.6	490.3	510.1	536.1	565.1	620.1	701.0	823.2
50°	420.0	429.2	435.3	436.8	442.9	461.2	482.6	514.7	549.8	612.4	719.3
52.5°	389.5	391.0	395.6	401.7	400.1	410.8	430.7	455.1	491.8	542.2	620.1
55°	354.3	358.9	362.0	363.5	363.5	372.7	383.3	406.3	435.3	476.5	542.2
57.5°	310.0	314.6	323.8	326.8	331.4	336.0	340.6	355.9	380.3	420.0	473.5
60°	264.2	267.3	276.4	282.5	285.6	297.8	303.9	316.1	329.9	358.9	409.3
62.5°	212.3	215.3	219.9	226.0	232.1	250.5	265.7	278.0	288.7	308.5	349.7
65°	184.8	186.3	189.4	190.9	192.4	200.1	213.8	230.6	250.5	265.7	290.2
67.5°	160.4	161.9	163.4	166.5	168.0	169.5	175.6	180.2	200.1	221.5	239.8
70°	137.5	140.5	142.0	142.0	143.6	146.6	149.7	155.8	161.9	172.6	195.5
72.5°	116.1	117.6	120.7	120.7	120.7	123.7	126.8	129.8	132.9	139.0	148.1
75°	96.2	99.3	99.3	99.3	100.8	100.8	103.9	106.9	110.0	114.5	117.6
77.5°	79.4	79.4	79.4	79.4	80.9	80.9	82.5	85.5	87.1	88.6	91.6
80°	59.6	61.1	61.1	61.1	62.6	62.6	62.6	65.7	67.2	67.2	70.3
82.5°	44.3	44.3	44.3	45.8	44.3	45.8	45.8	47.3	45.8	47.3	48.9
85°	27.5	27.5	27.5	29.0	29.0	29.0	29.0	29.0	29.0	29.0	30.5
87.5°	13.7	13.7	13.7	13.7	13.7	13.7	13.7	13.7	15.3	13.7	13.7
90°	19.0	18.9	18.8	18.7	18.8	19.1	19.4	19.6	19.9	17.1	14.3
92.5°	18.2	18.2	18.2	18.2	18.1	18.0	17.9	17.7	17.6	17.5	17.3
95°	35.7	36.0	36.3	36.4	36.4	36.4	36.4	36.4	36.4	36.1	35.9
97.5°	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.3	55.8
100°	78.1	78.2	78.3	78.4	78.4	78.4	78.4	78.4	78.4	78.0	77.6
102.5°	102.0	102.1	102.2	102.3	102.2	102.1	102.0	101.8	101.7	101.2	100.7
105°	126.1	126.1	126.1	126.1	126.0	125.7	125.5	125.2	125.0	124.7	124.5
107.5°	149.5	150.2	150.8	151.1	151.0	150.9	150.8	150.6	150.5	150.5	150.5
110°	175.8	176.1	176.5	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	201.0	201.3	201.6	201.7	201.9	202.3	202.6	203.0	203.4	203.5	203.6
115°	228.0	228.3	228.7	228.9	229.0	229.1	229.2	229.4	229.5	229.7	230.0
117.5°	253.0	253.3	253.7	253.9	254.1	254.5	254.8	255.2	255.6	256.2	256.9
120°	279.7	280.0	280.4	280.6	280.6	280.6	280.6	280.6	280.6	281.6	282.6
122.5°	305.6	305.8	306.1	306.2	306.4	306.8	307.1	307.5	307.9	308.5	309.1
125°	332.0	332.1	332.2	332.3	332.5	332.9	333.2	333.6	334.0	334.4	334.8
127.5°	356.4	356.7	357.1	357.3	357.6	358.1	358.6	359.1	359.6	360.1	360.6
130°	382.8	383.3	383.8	384.0	384.1	384.4	384.7	384.9	385.2	385.4	385.7
132.5°	407.5	407.9	408.3	408.5	408.8	409.4	410.1	410.7	411.3	411.2	411.0
135°	433.7	434.0	434.4	434.6	434.7	434.8	434.9	435.1	435.2	434.9	434.7
137.5°	457.2	457.7	458.2	458.4	458.5	458.6	458.7	458.9	459.0	458.8	458.5
140°	481.6	482.1	482.6	482.9	482.9	482.9	482.9	482.9	482.9	482.3	481.6
142.5°	503.8	504.3	504.8	505.0	504.9	504.8	504.7	504.6	504.5	504.1	503.7
145°	525.9	526.4	526.9	527.2	527.1	527.0	526.9	526.7	526.6	525.8	525.1
147.5°	545.8	546.3	546.8	547.1	547.0	546.7	546.4	546.2	545.9	545.4	544.9
150°	564.9	565.2	565.6	565.8	565.6	565.2	564.9	564.5	564.1	563.6	563.1
152.5°	583.3	583.8	584.3	584.6	584.3	583.8	583.3	582.8	582.3	581.7	581.0
155°	599.0	599.3	599.7	599.9	599.6	599.0	598.3	597.7	597.1	596.7	596.3
157.5°	613.6	614.3	614.9	615.2	614.8	613.9	613.0	612.2	611.3	611.0	610.8
160°	626.5	627.0	627.5	627.7	627.3	626.6	625.8	625.1	624.3	624.2	624.1
162.5°	638.1	638.7	639.4	639.7	639.3	638.4	637.5	636.6	635.7	635.6	635.4
165°	647.7	648.4	649.0	649.3	648.9	648.0	647.1	646.2	645.3	645.3	645.3
167.5°	656.2	656.9	657.5	657.8	657.4	656.5	655.6	654.8	653.9	653.9	653.9
170°	662.8	663.6	664.3	664.7	664.3	663.4	662.5	661.6	660.7	660.8	661.0
172.5°	667.9	668.7	669.4	669.8	669.4	668.5	667.6	666.7	665.8	665.9	666.1
175°	671.3	672.1	672.8	673.2	672.8	671.9	671.0	670.1	669.2	669.4	669.7
177.5°	673.0	673.8	674.5	674.9	674.5	673.8	673.0	672.3	671.5	671.7	672.0
180°	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2243.6	2235.9	2235.9	2231.4	2231.4	2206.9	2206.9	2214.6	2205.4	2194.7	2179.4
5°	2301.6	2284.8	2280.2	2274.1	2254.3	2223.7	2211.5	2206.9	2188.6	2165.7	2139.7
7.5°	2356.6	2329.1	2315.4	2301.6	2275.7	2232.9	2208.4	2191.6	2164.2	2129.0	2095.4
10°	2410.1	2374.9	2339.8	2323.0	2286.3	2232.9	2197.8	2170.3	2130.6	2083.2	2035.9
12.5°	2458.9	2385.6	2379.5	2345.9	2292.5	2231.4	2177.9	2138.2	2087.8	2032.8	1977.8
15°	2501.7	2426.9	2390.2	2359.7	2289.4	2213.0	2156.5	2107.6	2040.4	1977.8	1910.6
17.5°	2523.1	2442.1	2417.7	2367.3	2295.5	2196.2	2119.9	2060.3	1987.0	1912.2	1835.8
20°	2544.5	2449.8	2410.1	2374.9	2277.2	2164.2	2078.6	2009.9	1929.0	1840.4	1756.4
22.5°	2555.1	2449.8	2402.4	2353.5	2258.9	2129.0	2028.2	1947.3	1852.6	1762.5	1661.7
25°	2536.8	2440.6	2384.1	2333.7	2226.8	2086.3	1970.2	1878.6	1777.8	1675.4	1573.1
27.5°	2491.0	2419.2	2353.5	2301.6	2182.5	2031.3	1909.1	1805.2	1701.4	1586.8	1483.0
30°	2405.5	2373.4	2321.5	2263.4	2133.6	1982.4	1837.3	1730.4	1615.9	1501.3	1392.9
32.5°	2272.6	2300.1	2266.5	2216.1	2075.6	1915.2	1761.0	1652.5	1527.3	1403.6	1304.3
35°	2110.7	2208.4	2190.1	2155.0	2014.5	1843.4	1689.2	1557.8	1432.6	1307.4	1208.1
37.5°	1933.5	2081.7	2097.0	2075.6	1944.2	1770.1	1600.6	1472.3	1344.0	1217.2	1116.4
40°	1690.7	1918.3	1967.1	1976.3	1870.9	1681.5	1504.4	1379.1	1252.4	1128.7	1006.5
42.5°	1467.7	1754.8	1815.9	1854.1	1777.8	1594.5	1415.8	1276.8	1151.6	1040.1	917.9
45°	1258.5	1557.8	1657.1	1706.0	1672.4	1495.2	1310.4	1180.6	1066.0	963.7	846.1
47.5°	1043.1	1344.0	1483.0	1560.9	1560.9	1394.4	1209.6	1081.3	971.4	884.3	780.4
50°	899.6	1150.0	1293.6	1395.9	1423.4	1292.1	1118.0	992.7	888.9	794.2	714.8
52.5°	766.7	991.2	1110.3	1217.2	1296.7	1182.1	1015.6	902.6	800.3	711.7	649.1
55°	662.8	830.8	939.3	1056.9	1145.5	1070.6	916.4	806.4	717.8	644.5	591.1
57.5°	563.6	710.2	798.8	902.6	997.3	940.8	817.1	722.4	644.5	580.4	533.0
60°	479.6	598.7	667.4	748.4	866.0	826.3	723.9	636.9	574.3	516.2	476.5
62.5°	407.8	502.5	560.5	618.5	725.5	707.1	627.7	560.5	507.1	458.2	424.6
65°	334.5	412.4	458.2	508.6	594.1	601.7	537.6	490.3	441.4	398.6	368.1
67.5°	270.3	331.4	372.7	415.4	484.1	505.5	461.2	421.5	380.3	345.2	317.7
70°	218.4	261.2	291.7	325.3	381.8	407.8	384.9	357.4	323.8	294.8	270.3
72.5°	172.6	200.1	218.4	244.4	290.2	316.1	314.6	290.2	265.7	245.9	226.0
75°	126.8	148.1	163.4	180.2	216.9	241.3	247.4	236.7	212.3	197.0	181.7
77.5°	96.2	108.4	116.1	128.3	154.3	175.6	184.8	181.7	164.9	152.7	142.0
80°	73.3	76.4	79.4	84.0	105.4	125.2	131.3	129.8	120.7	116.1	103.9
82.5°	51.9	53.5	55.0	56.5	64.1	80.9	87.1	90.1	82.5	77.9	67.2
85°	30.5	32.1	32.1	35.1	36.7	41.2	51.9	51.9	50.4	44.3	42.8
87.5°	15.3	15.3	13.7	13.7	15.3	16.8	19.9	22.9	19.9	18.3	16.8
90°	11.6	8.8	7.4	6.6	5.1	3.6	2.1	0.6	2.1	3.6	5.1
92.5°	17.2	17.1	17.0	16.5	15.5	14.5	13.5	12.5	13.5	14.5	15.5
95°	35.6	35.3	35.2	34.6	33.3	32.0	30.8	29.5	30.8	32.0	33.3
97.5°	55.3	54.8	54.5	53.9	52.8	51.7	50.5	49.4	50.5	51.7	52.8
100°	77.3	76.9	76.7	76.2	75.2	74.1	73.1	72.1	73.1	74.1	75.2
102.5°	100.2	99.7	99.4	99.0	98.3	97.5	96.8	96.0	96.8	97.5	98.3
105°	124.2	123.9	123.8	123.6	123.2	122.9	122.5	122.1	122.5	122.9	123.2
107.5°	150.5	150.5	150.5	150.3	149.8	149.3	148.8	148.3	148.8	149.3	149.8
110°	176.7	176.7	176.7	176.3	175.6	174.8	174.1	173.3	174.1	174.8	175.6

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	203.7	203.8	203.9	203.5	202.8	202.0	201.3	200.5	201.3	202.0	202.8
115°	230.2	230.5	230.6	230.2	229.5	228.7	228.0	227.2	228.0	228.7	229.5
117.5°	257.5	258.2	258.5	258.0	257.0	255.9	254.9	253.9	254.9	255.9	257.0
120°	283.7	284.7	285.2	284.7	283.7	282.6	281.6	280.6	281.6	282.6	283.7
122.5°	309.8	310.4	310.7	310.1	308.8	307.6	306.3	305.1	306.3	307.6	308.8
125°	335.1	335.5	335.7	335.1	334.0	332.9	331.7	330.6	331.7	332.9	334.0
127.5°	361.1	361.6	361.9	361.2	359.8	358.4	357.0	355.6	357.0	358.4	359.8
130°	385.9	386.2	386.3	385.5	383.8	382.2	380.5	378.9	380.5	382.2	383.8
132.5°	410.9	410.8	410.7	410.1	408.8	407.5	406.3	405.0	406.3	407.5	408.8
135°	434.4	434.1	434.0	433.3	431.9	430.6	429.2	427.8	429.2	430.6	431.9
137.5°	458.3	458.0	457.9	457.3	456.2	455.1	453.9	452.8	453.9	455.1	456.2
140°	481.0	480.3	480.0	479.4	478.3	477.2	476.0	474.9	476.0	477.2	478.3
142.5°	503.4	503.0	502.8	502.2	501.1	499.9	498.8	497.6	498.8	499.9	501.1
145°	524.3	523.6	523.2	522.8	521.9	521.0	520.1	519.2	520.1	521.0	521.9
147.5°	544.4	543.9	543.7	543.1	542.0	540.8	539.7	538.5	539.7	540.8	542.0
150°	562.6	562.1	561.8	561.4	560.7	559.9	559.2	558.4	559.2	559.9	560.7
152.5°	580.4	579.7	579.4	579.0	578.3	577.5	576.8	576.0	576.8	577.5	578.3
155°	596.0	595.6	595.4	595.2	594.8	594.4	594.0	593.6	594.0	594.4	594.8
157.5°	610.5	610.2	610.1	610.0	609.7	609.5	609.2	609.0	609.2	609.5	609.7
160°	624.0	623.9	623.8	623.7	623.4	623.1	622.9	622.6	622.9	623.1	623.4
162.5°	635.3	635.2	635.1	635.1	635.1	635.1	635.1	635.1	635.1	635.1	635.1
165°	645.3	645.3	645.3	645.4	645.5	645.6	645.8	645.9	645.8	645.6	645.5
167.5°	653.9	653.9	653.9	654.1	654.5	654.8	655.2	655.6	655.2	654.8	654.5
170°	661.1	661.2	661.3	661.5	661.9	662.2	662.6	663.0	662.6	662.2	661.9
172.5°	666.2	666.3	666.4	666.6	667.0	667.3	667.7	668.1	667.7	667.3	667.0
175°	669.9	670.2	670.3	670.5	670.9	671.2	671.6	672.0	671.6	671.2	670.9
177.5°	672.2	672.5	672.6	672.8	673.2	673.5	673.9	674.3	673.9	673.5	673.2
180°	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2173.3	2174.8	2179.4	2165.7	2144.3	2135.1	2107.6	2103.1	2098.5	2098.5	2103.1
5°	2124.4	2118.3	2119.9	2093.9	2063.4	2045.0	2006.8	2013.0	1993.1	1980.9	1983.9
7.5°	2071.0	2054.2	2052.7	2019.1	1980.9	1947.3	1907.6	1898.4	1880.1	1858.7	1849.5
10°	2003.8	1991.6	1968.7	1930.5	1881.6	1854.1	1800.7	1768.6	1764.0	1731.9	1719.7
12.5°	1935.1	1913.7	1890.8	1837.3	1782.3	1738.0	1698.3	1663.2	1638.8	1611.3	1593.0
15°	1855.6	1829.7	1803.7	1747.2	1683.1	1638.8	1579.2	1527.3	1455.5	1399.0	1366.9
17.5°	1768.6	1739.6	1704.4	1641.8	1579.2	1518.1	1408.2	1347.1	1296.7	1263.1	1243.2
20°	1678.5	1646.4	1611.3	1548.7	1440.2	1333.3	1272.2	1224.9	1194.3	1160.7	1136.3
22.5°	1583.8	1550.2	1512.0	1414.3	1299.7	1224.9	1177.5	1133.2	1089.0	1070.6	1058.4
25°	1495.2	1464.7	1415.8	1282.9	1192.8	1124.1	1070.6	1041.6	1018.7	994.3	971.4
27.5°	1403.6	1347.1	1278.3	1166.8	1110.3	1040.1	1001.9	980.5	940.8	924.0	913.3
30°	1293.6	1231.0	1165.3	1085.9	1020.2	971.4	936.2	901.1	878.2	861.4	843.1
32.5°	1182.1	1122.6	1081.3	998.8	950.0	899.6	866.0	844.6	811.0	800.3	792.7
35°	1085.9	1035.5	998.8	931.6	885.8	840.0	815.6	783.5	762.1	742.3	730.0
37.5°	991.2	963.7	925.5	869.0	820.2	783.5	749.9	739.2	710.2	699.5	687.3
40°	925.5	884.3	852.2	803.4	762.1	722.4	701.0	676.6	656.7	639.9	635.3
42.5°	846.1	815.6	797.2	743.8	701.0	678.1	652.1	624.7	609.4	595.6	578.8
45°	786.6	759.1	733.1	690.3	652.1	623.1	600.2	581.9	555.9	549.8	523.9
47.5°	723.9	696.4	676.6	633.8	598.7	571.2	554.4	530.0	508.6	494.8	482.6
50°	661.3	638.4	620.1	583.4	552.9	523.9	500.9	476.5	467.3	444.4	436.8
52.5°	601.7	586.5	566.6	531.5	500.9	476.5	452.1	432.2	418.5	406.3	397.1
55°	551.3	526.9	517.7	479.6	453.6	427.6	406.3	394.0	377.2	369.6	362.0
57.5°	494.8	481.1	465.8	436.8	407.8	383.3	368.1	349.7	340.6	331.4	325.3
60°	446.0	426.1	413.9	389.5	363.5	340.6	326.8	313.1	300.9	293.2	281.0
62.5°	389.5	374.2	366.5	340.6	319.2	297.8	285.6	271.9	262.7	248.9	233.7
65°	340.6	328.4	319.2	297.8	278.0	258.1	245.9	229.1	216.9	209.2	207.7
67.5°	297.8	288.7	274.9	255.1	235.2	219.9	206.2	192.4	190.9	187.9	187.9
70°	250.5	241.3	233.7	212.3	195.5	178.7	175.6	171.1	166.5	164.9	161.9
72.5°	209.2	201.6	192.4	174.1	157.3	152.7	149.7	146.6	142.0	140.5	139.0
75°	169.5	158.8	152.7	135.9	131.3	128.3	125.2	120.7	117.6	116.1	113.0
77.5°	129.8	119.1	119.1	110.0	106.9	102.3	99.3	96.2	94.7	91.6	91.6
80°	91.6	91.6	88.6	84.0	79.4	77.9	73.3	71.8	70.3	71.8	68.7
82.5°	67.2	61.1	61.1	58.0	55.0	53.5	50.4	50.4	48.9	48.9	48.9
85°	38.2	38.2	36.7	33.6	32.1	32.1	30.5	30.5	29.0	29.0	27.5
87.5°	15.3	13.7	15.3	13.7	13.7	12.2	12.2	12.2	10.7	12.2	10.7
90°	6.6	7.4	8.8	11.6	14.3	17.1	19.9	19.6	19.4	19.1	18.8
92.5°	16.5	17.0	17.1	17.2	17.3	17.5	17.6	17.7	17.9	18.0	18.1
95°	34.6	35.2	35.3	35.6	35.9	36.1	36.4	36.4	36.4	36.4	36.4
97.5°	53.9	54.5	54.8	55.3	55.8	56.3	56.8	56.8	56.8	56.8	56.8
100°	76.2	76.7	76.9	77.3	77.6	78.0	78.4	78.4	78.4	78.4	78.4
102.5°	99.0	99.4	99.7	100.2	100.7	101.2	101.7	101.8	102.0	102.1	102.2
105°	123.6	123.8	123.9	124.2	124.5	124.7	125.0	125.2	125.5	125.7	126.0
107.5°	150.3	150.5	150.5	150.5	150.5	150.5	150.5	150.6	150.8	150.9	151.0
110°	176.3	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	203.5	203.9	203.8	203.7	203.6	203.5	203.4	203.0	202.6	202.3	201.9
115°	230.2	230.6	230.5	230.2	230.0	229.7	229.5	229.4	229.2	229.1	229.0
117.5°	258.0	258.5	258.2	257.5	256.9	256.2	255.6	255.2	254.8	254.5	254.1
120°	284.7	285.2	284.7	283.7	282.6	281.6	280.6	280.6	280.6	280.6	280.6
122.5°	310.1	310.7	310.4	309.8	309.1	308.5	307.9	307.5	307.1	306.8	306.4
125°	335.1	335.7	335.5	335.1	334.8	334.4	334.0	333.6	333.2	332.9	332.5
127.5°	361.2	361.9	361.6	361.1	360.6	360.1	359.6	359.1	358.6	358.1	357.6
130°	385.5	386.3	386.2	385.9	385.7	385.4	385.2	384.9	384.7	384.4	384.1
132.5°	410.1	410.7	410.8	410.9	411.0	411.2	411.3	410.7	410.1	409.4	408.8
135°	433.3	434.0	434.1	434.4	434.7	434.9	435.2	435.1	434.9	434.8	434.7
137.5°	457.3	457.9	458.0	458.3	458.5	458.8	459.0	458.9	458.7	458.6	458.5
140°	479.4	480.0	480.3	481.0	481.6	482.3	482.9	482.9	482.9	482.9	482.9
142.5°	502.2	502.8	503.0	503.4	503.7	504.1	504.5	504.6	504.7	504.8	504.9
145°	522.8	523.2	523.6	524.3	525.1	525.8	526.6	526.7	526.9	527.0	527.1
147.5°	543.1	543.7	543.9	544.4	544.9	545.4	545.9	546.2	546.4	546.7	547.0
150°	561.4	561.8	562.1	562.6	563.1	563.6	564.1	564.5	564.9	565.2	565.6
152.5°	579.0	579.4	579.7	580.4	581.0	581.7	582.3	582.8	583.3	583.8	584.3
155°	595.2	595.4	595.6	596.0	596.3	596.7	597.1	597.7	598.3	599.0	599.6
157.5°	610.0	610.1	610.2	610.5	610.8	611.0	611.3	612.2	613.0	613.9	614.8
160°	623.7	623.8	623.9	624.0	624.1	624.2	624.3	625.1	625.8	626.6	627.3
162.5°	635.1	635.1	635.2	635.3	635.4	635.6	635.7	636.6	637.5	638.4	639.3
165°	645.4	645.3	645.3	645.3	645.3	645.3	645.3	646.2	647.1	648.0	648.9
167.5°	654.1	653.9	653.9	653.9	653.9	653.9	653.9	654.8	655.6	656.5	657.4
170°	661.5	661.3	661.2	661.1	661.0	660.8	660.7	661.6	662.5	663.4	664.3
172.5°	666.6	666.4	666.3	666.2	666.1	665.9	665.8	666.7	667.6	668.5	669.4
175°	670.5	670.3	670.2	669.9	669.7	669.4	669.2	670.1	671.0	671.9	672.8
177.5°	672.8	672.6	672.5	672.2	672.0	671.7	671.5	672.3	673.0	673.8	674.5
180°	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2103.1	2100.0	2090.8	2093.9	2089.3	2089.3	2086.3	2086.3	2086.3	2093.9	2089.3
5°	1988.5	1977.8	1967.1	1962.6	1958.0	1953.4	1953.4	1951.9	1965.6	1962.6	1974.8
7.5°	1846.5	1843.4	1822.0	1822.0	1814.4	1811.4	1819.0	1820.5	1822.0	1825.1	1832.7
10°	1719.7	1712.1	1681.5	1684.6	1680.0	1673.9	1678.5	1675.4	1686.1	1689.2	1686.1
12.5°	1570.0	1556.3	1522.7	1505.9	1487.6	1473.8	1490.6	1478.4	1521.2	1533.4	1567.0
15°	1371.5	1345.5	1322.6	1322.6	1305.8	1293.6	1301.2	1315.0	1324.2	1337.9	1344.0
17.5°	1238.6	1227.9	1209.6	1198.9	1194.3	1189.8	1189.8	1195.9	1215.7	1214.2	1226.4
20°	1125.6	1119.5	1110.3	1096.6	1092.0	1089.0	1089.0	1089.0	1102.7	1114.9	1122.6
22.5°	1047.7	1043.1	1037.0	1018.7	1009.5	1006.5	1014.1	1018.7	1029.4	1038.6	1046.2
25°	969.8	959.1	948.4	942.3	937.8	937.8	940.8	942.3	946.9	951.5	960.7
27.5°	905.7	898.0	882.8	866.0	866.0	861.4	864.4	867.5	878.2	893.5	901.1
30°	833.9	832.4	826.3	820.2	814.0	811.0	817.1	821.7	823.2	830.8	830.8
32.5°	782.0	771.3	760.6	754.5	751.4	749.9	751.4	757.5	757.5	766.7	777.4
35°	730.0	723.9	713.2	702.5	699.5	691.9	698.0	704.1	714.8	719.3	723.9
37.5°	673.5	665.9	661.3	658.3	652.1	653.7	649.1	658.3	667.4	665.9	668.9
40°	630.8	617.0	603.3	601.7	600.2	598.7	598.7	600.2	606.3	612.4	621.6
42.5°	575.8	571.2	559.0	546.8	543.7	540.7	537.6	543.7	555.9	566.6	571.2
45°	519.3	513.2	510.1	500.9	494.8	493.3	490.3	497.9	508.6	513.2	516.2
47.5°	467.3	465.8	456.7	458.2	453.6	455.1	453.6	458.2	458.2	462.8	465.8
50°	432.2	427.6	423.1	420.0	415.4	415.4	413.9	415.4	421.5	427.6	426.1
52.5°	397.1	389.5	387.9	386.4	383.3	386.4	381.8	383.3	389.5	392.5	391.0
55°	355.9	354.3	351.3	348.2	346.7	345.2	345.2	345.2	351.3	355.9	357.4
57.5°	323.8	316.1	310.0	310.0	303.9	302.4	305.5	307.0	311.6	314.6	317.7
60°	279.5	276.4	267.3	262.7	253.5	252.0	252.0	258.1	265.7	276.4	279.5
62.5°	232.1	227.6	226.0	226.0	226.0	226.0	226.0	226.0	226.0	227.6	227.6
65°	206.2	207.7	206.2	204.7	206.2	206.2	204.7	204.7	204.7	206.2	207.7
67.5°	184.8	183.3	184.8	183.3	181.7	181.7	180.2	181.7	183.3	184.8	184.8
70°	160.4	160.4	158.8	160.4	158.8	157.3	155.8	155.8	158.8	160.4	160.4
72.5°	137.5	137.5	135.9	135.9	132.9	132.9	134.4	132.9	132.9	137.5	137.5
75°	114.5	113.0	111.5	111.5	110.0	110.0	110.0	108.4	111.5	111.5	113.0
77.5°	90.1	90.1	90.1	88.6	88.6	87.1	87.1	88.6	88.6	88.6	90.1
80°	68.7	68.7	68.7	67.2	65.7	65.7	65.7	65.7	65.7	67.2	65.7
82.5°	47.3	47.3	47.3	47.3	47.3	45.8	45.8	45.8	47.3	47.3	45.8
85°	29.0	27.5	29.0	29.0	27.5	29.0	27.5	27.5	26.0	26.0	27.5
87.5°	12.2	10.7	9.2	9.2	10.7	9.2	9.2	9.2	10.7	9.2	9.2
90°	18.7	18.8	18.9	19.0	19.2	19.3	19.2	19.0	18.9	18.8	18.7
92.5°	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2
95°	36.4	36.3	36.0	35.7	35.5	35.2	35.5	35.7	36.0	36.3	36.4
97.5°	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8
100°	78.4	78.3	78.2	78.1	77.9	77.8	77.9	78.1	78.2	78.3	78.4
102.5°	102.3	102.2	102.1	102.0	101.8	101.7	101.8	102.0	102.1	102.2	102.3
105°	126.1	126.1	126.1	126.1	126.1	126.1	126.1	126.1	126.1	126.1	126.1
107.5°	151.1	150.8	150.2	149.5	148.9	148.3	148.9	149.5	150.2	150.8	151.1
110°	176.7	176.5	176.1	175.8	175.4	175.0	175.4	175.8	176.1	176.5	176.7

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	201.7	201.6	201.3	201.0	200.8	200.5	200.8	201.0	201.3	201.6	201.7
115°	228.9	228.7	228.3	228.0	227.6	227.2	227.6	228.0	228.3	228.7	228.9
117.5°	253.9	253.7	253.3	253.0	252.6	252.2	252.6	253.0	253.3	253.7	253.9
120°	280.6	280.4	280.0	279.7	279.3	278.9	279.3	279.7	280.0	280.4	280.6
122.5°	306.2	306.1	305.8	305.6	305.3	305.1	305.3	305.6	305.8	306.1	306.2
125°	332.3	332.2	332.1	332.0	331.9	331.8	331.9	332.0	332.1	332.2	332.3
127.5°	357.3	357.1	356.7	356.4	356.0	355.6	356.0	356.4	356.7	357.1	357.3
130°	384.0	383.8	383.3	382.8	382.3	381.8	382.3	382.8	383.3	383.8	384.0
132.5°	408.5	408.3	407.9	407.5	407.1	406.7	407.1	407.5	407.9	408.3	408.5
135°	434.6	434.4	434.0	433.7	433.3	432.9	433.3	433.7	434.0	434.4	434.6
137.5°	458.4	458.2	457.7	457.2	456.7	456.2	456.7	457.2	457.7	458.2	458.4
140°	482.9	482.6	482.1	481.6	481.1	480.6	481.1	481.6	482.1	482.6	482.9
142.5°	505.0	504.8	504.3	503.8	503.3	502.8	503.3	503.8	504.3	504.8	505.0
145°	527.2	526.9	526.4	525.9	525.4	524.9	525.4	525.9	526.4	526.9	527.2
147.5°	547.1	546.8	546.3	545.8	545.3	544.8	545.3	545.8	546.3	546.8	547.1
150°	565.8	565.6	565.2	564.9	564.5	564.1	564.5	564.9	565.2	565.6	565.8
152.5°	584.6	584.3	583.8	583.3	582.8	582.3	582.8	583.3	583.8	584.3	584.6
155°	599.9	599.7	599.3	599.0	598.6	598.2	598.6	599.0	599.3	599.7	599.9
157.5°	615.2	614.9	614.3	613.6	613.0	612.4	613.0	613.6	614.3	614.9	615.2
160°	627.7	627.5	627.0	626.5	626.0	625.5	626.0	626.5	627.0	627.5	627.7
162.5°	639.7	639.4	638.7	638.1	637.4	636.8	637.4	638.1	638.7	639.4	639.7
165°	649.3	649.0	648.4	647.7	647.1	646.5	647.1	647.7	648.4	649.0	649.3
167.5°	657.8	657.5	656.9	656.2	655.6	655.0	655.6	656.2	656.9	657.5	657.8
170°	664.7	664.3	663.6	662.8	662.1	661.3	662.1	662.8	663.6	664.3	664.7
172.5°	669.8	669.4	668.7	667.9	667.2	666.4	667.2	667.9	668.7	669.4	669.8
175°	673.2	672.8	672.1	671.3	670.6	669.8	670.6	671.3	672.1	672.8	673.2
177.5°	674.9	674.5	673.8	673.0	672.3	671.5	672.3	673.0	673.8	674.5	674.9
180°	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2093.9	2101.5	2098.5	2081.7	2098.5	2103.1	2112.2	2121.4	2127.5	2136.7	2144.3
5°	1962.6	1977.8	1987.0	1977.8	2008.4	2013.0	2034.3	2046.6	2064.9	2080.2	2092.4
7.5°	1838.8	1851.1	1869.4	1872.4	1890.8	1912.2	1942.7	1973.2	2002.3	2017.5	2031.3
10°	1706.0	1727.4	1754.8	1748.7	1776.2	1809.8	1841.9	1890.8	1915.2	1942.7	1967.1
12.5°	1573.1	1586.8	1623.5	1635.7	1675.4	1701.4	1745.7	1776.2	1837.3	1869.4	1890.8
15°	1341.0	1397.5	1443.3	1498.3	1550.2	1599.1	1638.8	1693.8	1747.2	1771.6	1806.8
17.5°	1235.6	1261.5	1289.0	1316.5	1383.7	1470.8	1541.0	1600.6	1646.4	1678.5	1719.7
20°	1125.6	1151.6	1182.1	1208.1	1249.3	1311.9	1399.0	1501.3	1556.3	1589.9	1629.6
22.5°	1047.7	1072.2	1092.0	1114.9	1147.0	1192.8	1258.5	1385.2	1458.6	1499.8	1534.9
25°	963.7	994.3	1015.6	1032.4	1058.4	1108.8	1162.3	1234.0	1365.4	1397.5	1446.3
27.5°	905.7	914.8	939.3	965.2	991.2	1018.7	1073.7	1134.8	1223.4	1293.6	1353.2
30°	837.0	859.9	882.8	893.5	916.4	956.1	989.7	1055.4	1124.1	1179.1	1250.8
32.5°	785.0	798.8	814.0	840.0	861.4	888.9	922.5	977.5	1035.5	1070.6	1125.6
35°	727.0	736.1	768.2	778.9	800.3	827.8	861.4	904.2	966.8	994.3	1034.0
37.5°	672.0	693.4	702.5	727.0	746.8	774.3	798.8	847.6	888.9	921.0	957.6
40°	629.2	638.4	655.2	676.6	693.4	714.8	745.3	780.4	824.7	850.7	882.8
42.5°	577.3	584.9	606.3	618.5	646.0	665.9	684.2	727.0	766.7	786.6	818.6
45°	520.8	539.1	552.9	577.3	592.6	617.0	639.9	670.5	707.1	730.0	748.4
47.5°	471.9	490.3	504.0	526.9	551.3	562.0	586.5	618.5	652.1	670.5	696.4
50°	432.2	438.3	464.3	475.0	500.9	522.3	539.1	566.6	603.3	614.0	635.3
52.5°	394.0	398.6	415.4	429.2	452.1	470.4	491.8	517.7	548.3	565.1	581.9
55°	360.4	363.5	371.1	386.4	401.7	424.6	444.4	468.9	494.8	513.2	528.4
57.5°	322.3	328.4	334.5	343.6	358.9	380.3	401.7	424.6	446.0	458.2	478.0
60°	278.0	287.1	297.8	308.5	319.2	334.5	358.9	380.3	400.1	410.8	426.1
62.5°	230.6	248.9	258.1	270.3	279.5	293.2	311.6	336.0	349.7	363.5	375.7
65°	207.7	209.2	210.8	223.0	239.8	253.5	270.3	288.7	310.0	319.2	328.4
67.5°	184.8	186.3	189.4	190.9	197.0	212.3	230.6	250.5	267.3	273.4	282.5
70°	161.9	161.9	168.0	169.5	171.1	172.6	187.9	207.7	223.0	230.6	241.3
72.5°	137.5	139.0	142.0	143.6	146.6	149.7	154.3	164.9	183.3	190.9	203.1
75°	113.0	114.5	116.1	117.6	122.2	123.7	128.3	134.4	142.0	151.2	158.8
77.5°	90.1	90.1	91.6	94.7	97.7	99.3	103.9	106.9	110.0	114.5	120.7
80°	67.2	68.7	68.7	71.8	71.8	73.3	74.8	79.4	82.5	85.5	88.6
82.5°	45.8	48.9	48.9	48.9	50.4	51.9	53.5	53.5	56.5	58.0	62.6
85°	27.5	29.0	29.0	29.0	27.5	30.5	30.5	32.1	32.1	32.1	33.6
87.5°	10.7	9.2	10.7	10.7	10.7	12.2	10.7	10.7	12.2	13.7	13.7
90°	18.8	19.1	19.4	19.6	19.9	17.1	14.3	11.6	8.8	7.4	6.6
92.5°	18.1	18.0	17.9	17.7	17.6	17.5	17.3	17.2	17.1	17.0	16.5
95°	36.4	36.4	36.4	36.4	36.4	36.1	35.9	35.6	35.3	35.2	34.6
97.5°	56.8	56.8	56.8	56.8	56.8	56.3	55.8	55.3	54.8	54.5	53.9
100°	78.4	78.4	78.4	78.4	78.4	78.0	77.6	77.3	76.9	76.7	76.2
102.5°	102.2	102.1	102.0	101.8	101.7	101.2	100.7	100.2	99.7	99.4	99.0
105°	126.0	125.7	125.5	125.2	125.0	124.7	124.5	124.2	123.9	123.8	123.6
107.5°	151.0	150.9	150.8	150.6	150.5	150.5	150.5	150.5	150.5	150.5	150.3
110°	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.7	176.3

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	201.9	202.3	202.6	203.0	203.4	203.5	203.6	203.7	203.8	203.9	203.5
115°	229.0	229.1	229.2	229.4	229.5	229.7	230.0	230.2	230.5	230.6	230.2
117.5°	254.1	254.5	254.8	255.2	255.6	256.2	256.9	257.5	258.2	258.5	258.0
120°	280.6	280.6	280.6	280.6	280.6	281.6	282.6	283.7	284.7	285.2	284.7
122.5°	306.4	306.8	307.1	307.5	307.9	308.5	309.1	309.8	310.4	310.7	310.1
125°	332.5	332.9	333.2	333.6	334.0	334.4	334.8	335.1	335.5	335.7	335.1
127.5°	357.6	358.1	358.6	359.1	359.6	360.1	360.6	361.1	361.6	361.9	361.2
130°	384.1	384.4	384.7	384.9	385.2	385.4	385.7	385.9	386.2	386.3	385.5
132.5°	408.8	409.4	410.1	410.7	411.3	411.2	411.0	410.9	410.8	410.7	410.1
135°	434.7	434.8	434.9	435.1	435.2	434.9	434.7	434.4	434.1	434.0	433.3
137.5°	458.5	458.6	458.7	458.9	459.0	458.8	458.5	458.3	458.0	457.9	457.3
140°	482.9	482.9	482.9	482.9	482.9	482.3	481.6	481.0	480.3	480.0	479.4
142.5°	504.9	504.8	504.7	504.6	504.5	504.1	503.7	503.4	503.0	502.8	502.2
145°	527.1	527.0	526.9	526.7	526.6	525.8	525.1	524.3	523.6	523.2	522.8
147.5°	547.0	546.7	546.4	546.2	545.9	545.4	544.9	544.4	543.9	543.7	543.1
150°	565.6	565.2	564.9	564.5	564.1	563.6	563.1	562.6	562.1	561.8	561.4
152.5°	584.3	583.8	583.3	582.8	582.3	581.7	581.0	580.4	579.7	579.4	579.0
155°	599.6	599.0	598.3	597.7	597.1	596.7	596.3	596.0	595.6	595.4	595.2
157.5°	614.8	613.9	613.0	612.2	611.3	611.0	610.8	610.5	610.2	610.1	610.0
160°	627.3	626.6	625.8	625.1	624.3	624.2	624.1	624.0	623.9	623.8	623.7
162.5°	639.3	638.4	637.5	636.6	635.7	635.6	635.4	635.3	635.2	635.1	635.1
165°	648.9	648.0	647.1	646.2	645.3	645.3	645.3	645.3	645.3	645.3	645.4
167.5°	657.4	656.5	655.6	654.8	653.9	653.9	653.9	653.9	653.9	653.9	654.1
170°	664.3	663.4	662.5	661.6	660.7	660.8	661.0	661.1	661.2	661.3	661.5
172.5°	669.4	668.5	667.6	666.7	665.8	665.9	666.1	666.2	666.3	666.4	666.6
175°	672.8	671.9	671.0	670.1	669.2	669.4	669.7	669.9	670.2	670.3	670.5
177.5°	674.5	673.8	673.0	672.3	671.5	671.7	672.0	672.2	672.5	672.6	672.8
180°	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2	673.2

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2197.8	2197.8	2197.8	2197.8
2.5°	2158.0	2153.5	2181.0	2211.5
5°	2113.8	2121.4	2156.5	2199.3
7.5°	2067.9	2084.7	2126.0	2182.5
10°	2003.8	2034.3	2097.0	2155.0
12.5°	1941.2	1982.4	2042.0	2110.7
15°	1870.9	1916.7	1990.0	2072.5
17.5°	1793.0	1845.0	1930.5	2020.6
20°	1710.6	1779.3	1869.4	1967.1
22.5°	1618.9	1701.4	1794.6	1903.0
25°	1530.3	1620.4	1713.6	1838.8
27.5°	1443.3	1531.9	1635.7	1762.5
30°	1356.2	1437.2	1548.7	1684.6
32.5°	1263.1	1347.1	1464.7	1603.6
35°	1177.5	1261.5	1371.5	1509.0
37.5°	1085.9	1176.0	1281.4	1423.4
40°	979.0	1084.4	1186.7	1322.6
42.5°	890.4	1001.9	1101.2	1229.5
45°	820.2	925.5	1008.0	1133.2
47.5°	754.5	840.0	924.0	1040.1
50°	691.9	757.5	844.6	948.4
52.5°	627.7	684.2	759.1	856.8
55°	569.7	623.1	690.3	765.2
57.5°	516.2	554.4	621.6	688.8
60°	456.7	496.4	548.3	604.8
62.5°	406.3	436.8	485.7	533.0
65°	352.8	381.8	418.5	462.8
67.5°	303.9	329.9	358.9	394.0
70°	259.6	279.5	300.9	331.4
72.5°	212.3	233.7	253.5	278.0
75°	174.1	183.3	200.1	216.9
77.5°	134.4	146.6	155.8	169.5
80°	96.2	106.9	110.0	120.7
82.5°	64.1	70.3	76.4	79.4
85°	36.7	39.7	45.8	47.3
87.5°	13.7	15.3	18.3	21.4
90°	5.1	3.6	2.1	0.6
92.5°	15.5	14.5	13.5	12.5
95°	33.3	32.0	30.8	29.5
97.5°	52.8	51.7	50.5	49.4
100°	75.2	74.1	73.1	72.1
102.5°	98.3	97.5	96.8	96.0
105°	123.2	122.9	122.5	122.1
107.5°	149.8	149.3	148.8	148.3
110°	175.6	174.8	174.1	173.3

TEST NUMBER: P999376

CATALOG NUMBER: SA2XXRDIP-B1005D530UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	202.8	202.0	201.3	200.5
115°	229.5	228.7	228.0	227.2
117.5°	257.0	255.9	254.9	253.9
120°	283.7	282.6	281.6	280.6
122.5°	308.8	307.6	306.3	305.1
125°	334.0	332.9	331.7	330.6
127.5°	359.8	358.4	357.0	355.6
130°	383.8	382.2	380.5	378.9
132.5°	408.8	407.5	406.3	405.0
135°	431.9	430.6	429.2	427.8
137.5°	456.2	455.1	453.9	452.8
140°	478.3	477.2	476.0	474.9
142.5°	501.1	499.9	498.8	497.6
145°	521.9	521.0	520.1	519.2
147.5°	542.0	540.8	539.7	538.5
150°	560.7	559.9	559.2	558.4
152.5°	578.3	577.5	576.8	576.0
155°	594.8	594.4	594.0	593.6
157.5°	609.7	609.5	609.2	609.0
160°	623.4	623.1	622.9	622.6
162.5°	635.1	635.1	635.1	635.1
165°	645.5	645.6	645.8	645.9
167.5°	654.5	654.8	655.2	655.6
170°	661.9	662.2	662.6	663.0
172.5°	667.0	667.3	667.7	668.1
175°	670.9	671.2	671.6	672.0
177.5°	673.2	673.5	673.9	674.3
180°	673.2	673.2	673.2	673.2

(END OF REPORT)