

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999392

Luminaire Tested: SA2XXRDIP-B1005D725UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999392
REPORT IS A COMBINATION OF REPORTS P987943 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D725UB27-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6206.1 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999392

CATALOG NUMBER: SA2XXRDIP-B1005D725UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999392

CATALOG NUMBER: SA2XXRDIP-B1005D725UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61
1	100	95	92	88	92	89	86	83	77	74	72	65	64	62	55	54	53
2	91	84	78	73	85	78	73	69	68	64	61	58	55	53	49	47	45
3	84	74	67	62	77	69	63	58	60	56	52	52	48	45	44	41	39
4	77	66	58	53	71	62	55	50	54	49	45	47	43	39	40	37	34
5	71	59	51	45	66	56	49	43	49	43	39	42	38	34	36	33	30
6	65	53	45	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	60	48	41	35	56	46	39	34	40	34	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	24	28	24	22
9	53	40	33	28	49	38	31	27	34	28	25	30	25	22	26	22	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26631	26631	26631
5°	26675	25336	25148
10°	26411	24030	23237
15°	26047	22487	21058
20°	25567	20734	18779
25°	25077	18934	16694
30°	24414	17182	14417
35°	23768	15415	12462
40°	23111	13678	10448
45°	22344	11888	8691
50°	21553	10159	7075
55°	20731	8433	5617
60°	19773	6744	4250
65°	18674	5141	3455
70°	17340	3730	2747
75°	15669	2845	2098
80°	13253	1926	1409
85°	9252	881	680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22344 cd/sqm

TEST NUMBER: P999392

CATALOG NUMBER: SA2XXRDIP-B1005D725UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	2.5
10°-20°	432.8	7.0
20°-30°	607.7	9.8
30°-40°	662.4	10.7
40°-50°	608.8	9.8
50°-60°	478.1	7.7
60°-70°	311.2	5.0
70°-80°	160.2	2.6
80°-90°	43.4	0.7
90°-100°	159.5	2.6
100°-110°	539.3	8.7
110°-120°	566.9	9.1
120°-130°	466.2	7.5
130°-140°	374.6	6.0
140°-150°	283.0	4.6
150°-160°	198.9	3.2
160°-170°	117.1	1.9
170°-180°	38.1	0.6
0°-30°	1198.2	19.3
0°-40°	1860.7	30.0
0°-60°	2947.6	47.5
0°-90°	3462.5	55.8
90°-120°	1265.7	20.4
90°-150°	2389.4	38.5
90°-180°	2744.0	44.2
0°-180°	6206.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1682	1682	1682	1682	1682	
5°	1682	1675	1655	1669	1664	160
15°	1600	1583	1532	1503	1488	451
25°	1452	1404	1303	1241	1218	668
35°	1252	1174	1040	944	910	783
45°	1023	921	761	653	617	790
55°	778	659	495	404	374	695
65°	525	402	265	213	209	521
75°	280	174	122	111	110	296
85°	66	34	29	29	29	75
90°	1	10	26	25	25	5
95°	26	65	297	112	86	27
105°	92	139	561	1002	853	98
115°	163	205	469	968	1122	161
125°	227	269	451	784	910	202
135°	266	318	446	659	754	206
145°	304	350	444	551	602	191
155°	346	374	431	487	506	159
165°	377	388	412	437	444	106
175°	393	393	396	402	400	37
180°	394	394	394	394	394	

TEST NUMBER: P999392

CATALOG NUMBER: SA2XXRDIP-B1005D725UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1682.4	1682.4	1682.4	1682.4	1682.4
2.5°	1690.0	1682.4	1665.6	1680.8	1677.8
5°	1682.4	1674.8	1655.0	1668.7	1664.1
7.5°	1668.7	1659.5	1638.2	1644.3	1636.7
10°	1650.4	1639.7	1609.3	1604.7	1595.6
12.5°	1627.6	1613.9	1572.7	1563.6	1546.9
15°	1600.1	1583.4	1531.6	1502.7	1487.5
17.5°	1568.2	1543.8	1479.9	1446.4	1422.0
20°	1531.6	1501.2	1425.1	1387.0	1353.5
22.5°	1492.1	1457.0	1368.7	1317.0	1294.1
25°	1452.5	1403.7	1303.3	1240.8	1218.0
27.5°	1405.3	1353.5	1242.4	1170.8	1135.8
30°	1355.0	1297.2	1175.4	1097.7	1056.6
32.5°	1306.3	1236.3	1111.4	1020.1	982.0
35°	1251.5	1173.8	1039.9	944.0	910.5
37.5°	1198.2	1114.5	972.9	867.8	829.8
40°	1141.9	1050.5	902.8	794.7	755.2
42.5°	1084.0	986.6	832.8	720.1	682.1
45°	1023.1	921.1	761.3	653.2	616.6
47.5°	965.3	857.2	692.7	584.6	551.1
50°	901.3	793.2	625.7	520.7	488.7
52.5°	838.9	724.7	561.8	461.3	432.4
55°	778.0	659.2	494.8	403.5	374.5
57.5°	715.6	593.8	435.4	350.2	325.8
60°	651.6	529.8	373.0	295.4	271.0
62.5°	589.2	467.4	319.7	246.6	234.5
65°	525.3	401.9	264.9	213.2	208.6
67.5°	464.4	341.0	213.2	187.3	182.7
70°	400.4	281.7	176.6	161.4	155.3
72.5°	339.5	226.9	147.7	135.5	132.5
75°	280.1	173.6	121.8	111.1	109.6
77.5°	220.8	123.3	95.9	89.8	86.8
80°	166.0	88.3	73.1	67.0	67.0
82.5°	115.7	59.4	50.2	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.4	12.2	12.2	10.7	10.7
90°	0.8	10.2	25.7	24.6	25.0
92.5°	11.4	36.0	116.5	53.8	46.2
95°	26.5	65.1	296.7	112.0	86.3
97.5°	39.4	85.9	483.6	224.8	144.5
100°	58.3	105.2	597.8	447.6	270.9
102.5°	75.7	122.6	601.6	756.8	528.2
105°	92.3	139.2	560.8	1002.3	852.9
107.5°	110.5	155.9	522.9	1091.2	1071.6
110°	128.7	172.9	497.2	1076.9	1160.9



TEST NUMBER: P999392

CATALOG NUMBER: SA2XXRDIP-B1005D725UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	145.3	189.2	480.5	1028.1	1159.4
115°	162.7	205.4	469.2	968.3	1122.3
117.5°	180.9	221.7	463.1	911.2	1066.3
120°	197.5	237.6	457.8	860.0	1012.6
122.5°	213.4	253.9	454.8	820.4	956.6
125°	227.0	268.6	451.0	784.4	910.4
127.5°	238.4	282.6	448.8	753.8	867.3
130°	248.2	295.1	447.2	722.7	831.7
132.5°	257.3	307.2	446.5	690.6	794.6
135°	266.4	317.8	445.7	659.2	754.5
137.5°	274.7	327.0	445.7	627.3	715.9
140°	284.5	335.2	445.0	599.4	675.8
142.5°	294.4	342.0	445.0	572.4	635.7
145°	304.2	349.6	443.5	550.6	602.4
147.5°	314.8	355.6	441.2	531.2	572.9
150°	325.4	361.7	438.9	514.6	547.1
152.5°	336.0	367.8	435.1	500.6	525.2
155°	345.8	373.5	430.6	487.0	506.3
157.5°	354.2	378.0	426.1	474.1	489.6
160°	362.5	382.5	421.5	461.2	473.7
162.5°	370.8	386.0	417.7	449.1	458.6
165°	376.9	388.2	412.4	437.4	444.2
167.5°	382.2	390.5	407.9	426.8	430.6
170°	387.5	391.6	404.1	417.0	418.5
172.5°	390.5	392.8	399.6	408.3	408.7
175°	392.8	393.2	396.5	401.5	400.3
177.5°	394.3	393.5	393.5	396.5	394.3
180°	393.5	393.5	393.5	393.5	393.5

(END OF REPORT)