

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998349

Luminaire Tested: SA2XXDIP-B290D925UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998349
REPORT IS A COMBINATION OF REPORTS P984089 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D925UB30-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4447.0 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998349

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P998349

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18
5	64	53	45	40	57	48	41	36	37	33	29	28	25	22	19	17	16
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7280	7280	7280
5°	7292	6938	6890
10°	7232	6622	6491
15°	7127	6304	6072
20°	6983	5958	5675
25°	6840	5595	5278
30°	6661	5255	4863
35°	6491	4896	4455
40°	6282	4542	4069
45°	6074	4191	3690
50°	5847	3833	3296
55°	5609	3451	2925
60°	5341	3037	2537
65°	5044	2618	2132
70°	4673	2156	1721
75°	4156	1663	1328
80°	3529	1131	856
85°	2557	524	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6074 cd/sqm

TEST NUMBER: P998349

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.3	1.0
10°-20°	121.8	2.7
20°-30°	179.0	4.0
30°-40°	207.9	4.7
40°-50°	207.6	4.7
50°-60°	181.0	4.1
60°-70°	133.8	3.0
70°-80°	75.7	1.7
80°-90°	23.3	0.5
90°-100°	72.4	1.6
100°-110°	230.3	5.2
110°-120°	394.0	8.9
120°-130°	518.2	11.7
130°-140°	581.7	13.1
140°-150°	570.4	12.8
150°-160°	478.5	10.8
160°-170°	317.3	7.1
170°-180°	110.9	2.5
0°-30°	344.0	7.7
0°-40°	551.9	12.4
0°-60°	940.5	21.1
0°-90°	1173.3	26.4
90°-120°	696.7	15.7
90°-150°	2367.0	53.2
90°-180°	3274.0	73.6
0°-180°	4447.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	460	460	460	460	460	
5°	460	458	453	457	456	44
15°	438	435	429	431	429	123
25°	396	393	385	386	385	182
35°	342	337	330	328	326	213
45°	278	275	268	264	262	215
55°	210	208	202	197	195	188
65°	142	139	135	131	129	140
75°	74	73	71	68	69	79
85°	18	18	17	16	16	20
90°	1	13	35	33	34	4
95°	51	61	63	63	61	57
105°	212	215	217	219	219	224
115°	395	401	399	398	395	391
125°	575	584	581	578	577	514
135°	744	755	757	756	753	575
145°	903	910	916	917	913	564
155°	1033	1036	1038	1044	1040	475
165°	1124	1122	1122	1129	1124	317
175°	1169	1166	1164	1171	1165	111
180°	1171	1171	1171	1171	1171	

TEST NUMBER: P998349

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	459.9	459.9	459.9	459.9	459.9
2.5°	462.5	460.3	455.5	459.9	459.0
5°	459.9	458.1	453.2	456.8	455.9
7.5°	456.8	454.1	449.3	452.8	451.9
10°	451.9	448.8	443.5	447.1	445.7
12.5°	445.3	442.6	437.3	439.5	438.7
15°	437.8	435.1	429.4	431.1	428.9
17.5°	428.5	425.8	420.1	422.3	420.1
20°	418.3	415.7	409.5	410.8	409.0
22.5°	408.1	404.2	398.4	398.4	397.5
25°	396.2	392.7	385.1	386.0	385.1
27.5°	382.9	379.8	374.1	372.8	370.6
30°	369.7	366.1	359.5	358.2	356.4
32.5°	355.5	352.9	345.8	343.1	341.4
35°	341.8	337.4	330.3	327.7	325.5
37.5°	326.3	322.4	315.3	312.2	310.0
40°	310.4	306.9	299.8	295.8	294.1
42.5°	294.9	291.4	284.3	279.9	277.3
45°	278.1	275.0	268.4	263.5	261.8
47.5°	261.8	258.7	251.6	246.7	244.1
50°	244.5	242.3	236.1	229.9	227.7
52.5°	227.7	224.6	218.9	214.0	210.9
55°	210.5	207.8	202.5	197.2	195.0
57.5°	193.2	191.0	185.3	180.0	178.2
60°	176.0	174.2	168.0	163.2	161.8
62.5°	159.2	156.1	151.7	147.2	145.5
65°	141.9	139.3	134.9	130.9	128.7
67.5°	124.3	122.0	118.1	115.0	113.2
70°	107.9	106.1	102.1	99.1	97.3
72.5°	91.1	89.3	87.1	84.0	82.7
75°	74.3	73.4	71.2	68.5	69.4
77.5°	59.3	57.5	56.6	55.3	53.9
80°	44.2	43.8	42.9	41.6	40.7
82.5°	30.1	30.1	29.6	27.9	27.9
85°	18.1	17.7	17.2	15.9	15.5
87.5°	8.0	7.1	6.2	4.9	4.4
90°	1.0	12.8	34.6	32.6	33.6
92.5°	21.7	29.6	30.6	31.6	31.6
95°	51.4	61.3	63.2	63.2	61.3
97.5°	86.0	94.9	98.8	98.8	98.8
100°	125.5	133.4	136.4	136.4	135.4
102.5°	167.0	172.9	176.9	177.9	176.9
105°	212.4	215.4	217.4	219.4	219.4
107.5°	257.9	261.9	261.9	262.8	257.9
110°	301.4	307.3	307.3	307.3	304.3

TEST NUMBER: P998349

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	348.8	354.7	353.7	350.8	348.8
115°	395.2	401.2	399.2	398.2	395.2
117.5°	441.7	449.6	444.7	441.7	438.7
120°	488.1	496.0	488.1	488.1	485.2
122.5°	530.6	540.5	535.6	532.6	530.6
125°	575.1	584.0	581.0	578.0	577.1
127.5°	618.6	629.4	625.5	621.5	618.6
130°	659.1	671.9	669.9	668.0	664.0
132.5°	704.5	714.4	715.4	710.5	707.5
135°	744.1	754.9	756.9	755.9	752.9
137.5°	787.5	796.4	798.4	797.4	793.5
140°	826.1	835.0	839.9	839.9	835.9
142.5°	865.6	874.5	877.4	878.4	874.5
145°	903.1	910.1	916.0	917.0	913.0
147.5°	936.7	945.6	949.6	951.6	947.6
150°	971.3	977.2	981.2	984.2	981.2
152.5°	1002.0	1007.9	1012.8	1016.8	1012.8
155°	1032.6	1035.5	1038.5	1043.5	1040.5
157.5°	1059.3	1061.2	1063.2	1070.1	1065.2
160°	1083.0	1085.0	1085.9	1091.9	1087.9
162.5°	1104.7	1104.7	1105.7	1112.6	1107.7
165°	1123.5	1122.5	1122.5	1129.4	1124.5
167.5°	1140.3	1137.3	1137.3	1144.2	1139.3
170°	1153.1	1150.2	1149.2	1156.1	1150.2
172.5°	1162.0	1159.1	1158.1	1165.0	1159.1
175°	1168.9	1166.0	1164.0	1170.9	1165.0
177.5°	1172.9	1169.9	1168.0	1173.9	1168.0
180°	1170.9	1170.9	1170.9	1170.9	1170.9

TEST NUMBER: P998349

CATALOG NUMBER: SA2XXDIP-B290D925UB30-4F0-XX-W2A-F1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.39	10.08	10.53	11.20	12.78	10.18	10.86	11.31	11.99	13.56
	3H	10.72	11.33	11.86	12.46	14.05	11.79	12.40	12.93	13.54	15.13
	4H	11.11	11.70	12.27	12.83	14.42	12.37	12.95	13.53	14.09	15.68
	6H	11.32	11.86	12.49	13.00	14.60	12.77	13.30	13.93	14.44	16.04
	8H	11.35	11.86	12.51	13.01	14.61	12.87	13.38	14.03	14.53	16.13
	12H	11.33	11.82	12.50	12.96	14.58	12.91	13.39	14.08	14.54	16.16
4H	2H	9.84	10.42	11.00	11.56	13.15	10.49	11.07	11.65	12.20	13.80
	3H	11.34	11.83	12.51	12.99	14.59	12.25	12.73	13.42	13.90	15.50
	4H	11.84	12.29	13.01	13.44	15.06	12.92	13.37	14.09	14.52	16.14
	6H	12.13	12.52	13.31	13.69	15.30	13.41	13.79	14.58	14.96	16.58
	8H	12.19	12.54	13.36	13.71	15.34	13.55	13.90	14.72	15.07	16.70
	12H	12.18	12.50	13.37	13.68	15.31	13.60	13.92	14.79	15.10	16.74
8H	4H	12.00	12.36	13.17	13.52	15.15	12.99	13.35	14.17	14.51	16.15
	6H	12.38	12.67	13.57	13.88	15.51	13.56	13.85	14.75	15.06	16.68
	8H	12.48	12.73	13.68	13.92	15.57	13.74	14.00	14.94	15.18	16.83
	12H	12.50	12.73	13.70	13.91	15.59	13.83	14.06	15.03	15.24	16.92
12H	4H	11.97	12.30	13.16	13.47	15.11	12.95	13.27	14.14	14.45	16.08
	6H	12.39	12.65	13.59	13.83	15.48	13.55	13.80	14.74	14.99	16.63
	8H	12.50	12.72	13.70	13.91	15.59	13.73	13.96	14.93	15.14	16.82