

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999414

Luminaire Tested: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999414
REPORT IS A COMBINATION OF REPORTS P987965 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6288.2 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999414

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999414

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61
1	100	95	92	88	92	89	86	83	77	74	72	65	64	62	55	54	53
2	91	84	78	73	85	78	73	69	68	64	61	58	55	53	49	47	45
3	84	74	67	62	77	69	63	58	60	56	52	52	48	45	44	41	39
4	77	66	58	53	71	62	55	50	54	49	45	47	43	39	40	37	34
5	71	59	51	45	66	56	49	43	49	43	39	42	38	34	36	33	30
6	65	53	45	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	60	48	41	35	56	46	39	34	40	34	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	24	28	24	22
9	53	40	33	28	49	38	31	27	34	28	25	30	25	22	26	22	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26984	26984	26984
5°	27028	25673	25482
10°	26762	24349	23545
15°	26394	22786	21338
20°	25908	21009	19029
25°	25410	19186	16916
30°	24739	17410	14609
35°	24083	15619	12627
40°	23419	13860	10586
45°	22642	12045	8806
50°	21840	10295	7169
55°	21005	8545	5692
60°	20037	6834	4306
65°	18919	5209	3501
70°	17570	3780	2785
75°	15881	2882	2126
80°	13429	1953	1427
85°	9365	893	689

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22642 cd/sqm

TEST NUMBER: P999414

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.8	2.5
10°-20°	438.6	7.0
20°-30°	615.8	9.8
30°-40°	671.2	10.7
40°-50°	616.9	9.8
50°-60°	484.5	7.7
60°-70°	315.4	5.0
70°-80°	162.4	2.6
80°-90°	44.0	0.7
90°-100°	161.6	2.6
100°-110°	546.4	8.7
110°-120°	574.3	9.1
120°-130°	472.3	7.5
130°-140°	379.5	6.0
140°-150°	286.7	4.6
150°-160°	201.6	3.2
160°-170°	118.7	1.9
170°-180°	38.6	0.6
0°-30°	1214.2	19.3
0°-40°	1885.4	30.0
0°-60°	2986.8	47.5
0°-90°	3508.5	55.8
90°-120°	1282.3	20.4
90°-150°	2420.8	38.5
90°-180°	2780.0	44.2
0°-180°	6288.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1705	1705	1705	1705	1705	
5°	1705	1697	1677	1691	1686	162
15°	1621	1604	1552	1523	1507	457
25°	1472	1422	1321	1257	1234	677
35°	1268	1190	1054	956	923	794
45°	1037	933	771	662	625	801
55°	788	668	501	409	380	704
65°	532	407	268	216	211	528
75°	284	176	123	113	111	300
85°	66	34	29	29	29	76
90°	1	10	26	25	25	5
95°	27	66	300	113	87	28
105°	94	141	568	1015	864	99
115°	165	208	475	981	1137	163
125°	230	272	457	795	922	204
135°	270	322	452	668	764	208
145°	308	354	449	558	610	193
155°	350	378	436	493	513	161
165°	382	393	418	443	450	108
175°	398	398	402	407	406	38
180°	399	399	399	399	399	

TEST NUMBER: P999414

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1704.7	1704.7	1704.7	1704.7	1704.7
2.5°	1712.4	1704.7	1687.8	1703.2	1700.1
5°	1704.7	1697.0	1677.0	1690.8	1686.2
7.5°	1690.8	1681.6	1660.0	1666.2	1658.4
10°	1672.3	1661.5	1630.7	1626.1	1616.8
12.5°	1649.2	1635.3	1593.7	1584.4	1567.4
15°	1621.4	1604.5	1552.0	1522.7	1507.3
17.5°	1589.0	1564.3	1499.5	1465.6	1440.9
20°	1552.0	1521.1	1444.0	1405.4	1371.5
22.5°	1511.9	1476.4	1386.9	1334.5	1311.3
25°	1471.8	1422.4	1320.6	1257.3	1234.2
27.5°	1424.0	1371.5	1258.9	1186.4	1150.9
30°	1373.0	1314.4	1191.0	1112.3	1070.7
32.5°	1323.7	1252.7	1126.2	1033.6	995.1
35°	1268.1	1189.5	1053.7	956.5	922.6
37.5°	1214.1	1129.3	985.8	879.4	840.8
40°	1157.1	1064.5	914.8	805.3	765.2
42.5°	1098.4	999.7	843.9	729.7	691.1
45°	1036.7	933.4	771.4	661.8	624.8
47.5°	978.1	868.6	701.9	592.4	558.5
50°	913.3	803.8	634.1	527.6	495.2
52.5°	850.1	734.3	569.3	467.5	438.1
55°	788.3	668.0	501.4	408.8	379.5
57.5°	725.1	601.7	441.2	354.8	330.1
60°	660.3	536.9	378.0	299.3	274.6
62.5°	597.0	473.6	324.0	249.9	237.6
65°	532.2	407.3	268.4	216.0	211.4
67.5°	470.5	345.6	216.0	189.8	185.1
70°	405.7	285.4	179.0	163.5	157.4
72.5°	344.0	229.9	149.6	137.3	134.2
75°	283.9	175.9	123.4	112.6	111.1
77.5°	223.7	125.0	97.2	91.0	87.9
80°	168.2	89.5	74.1	67.9	67.9
82.5°	117.2	60.2	50.9	47.8	47.8
85°	66.3	33.9	29.3	29.3	29.3
87.5°	24.7	12.3	12.3	10.8	10.8
90°	0.8	10.4	26.1	24.9	25.3
92.5°	11.5	36.4	118.1	54.4	46.8
95°	26.8	65.9	300.5	113.4	87.4
97.5°	39.9	87.1	489.9	227.7	146.4
100°	59.0	106.6	605.7	453.5	274.5
102.5°	76.7	124.2	609.5	766.7	535.2
105°	93.5	141.0	568.1	1015.4	864.1
107.5°	111.9	158.0	529.8	1105.6	1085.6
110°	130.3	175.2	503.7	1091.0	1176.1



TEST NUMBER: P999414

CATALOG NUMBER: SA2XXRDIP-B1005D725UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	147.2	191.7	486.9	1041.6	1174.6
115°	164.8	208.2	475.4	981.0	1137.0
117.5°	183.2	224.6	469.2	923.1	1080.3
120°	200.1	240.8	463.9	871.4	1025.8
122.5°	216.2	257.2	460.8	831.1	969.1
125°	230.0	272.2	457.0	794.6	922.3
127.5°	241.5	286.4	454.7	763.6	878.6
130°	251.5	299.0	453.1	732.2	842.6
132.5°	260.7	311.2	452.4	699.6	805.0
135°	269.9	322.0	451.6	667.8	764.4
137.5°	278.3	331.2	451.6	635.6	725.3
140°	288.3	339.6	450.8	607.2	684.7
142.5°	298.2	346.5	450.8	580.0	644.0
145°	308.2	354.2	449.3	557.8	610.3
147.5°	318.9	360.4	447.0	538.2	580.4
150°	329.7	366.5	444.7	521.4	554.3
152.5°	340.4	372.6	440.9	507.2	532.1
155°	350.4	378.4	436.3	493.4	512.9
157.5°	358.8	383.0	431.7	480.4	496.1
160°	367.2	387.6	427.1	467.3	480.0
162.5°	375.7	391.0	423.2	455.0	464.6
165°	381.8	393.3	417.9	443.2	450.1
167.5°	387.2	395.6	413.3	432.4	436.3
170°	392.5	396.8	409.4	422.4	424.0
172.5°	395.6	397.9	404.8	413.6	414.0
175°	397.9	398.3	401.7	406.7	405.6
177.5°	399.4	398.7	398.7	401.7	399.4
180°	398.7	398.7	398.7	398.7	398.7

(END OF REPORT)