

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999420

Luminaire Tested: SA2XXRDIP-B1005D725UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999420
REPORT IS A COMBINATION OF REPORTS P987971 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D725UB40-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6226.1 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999420

CATALOG NUMBER: SA2XXRDIP-B1005D725UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999420

CATALOG NUMBER: SA2XXRDIP-B1005D725UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61
1	100	95	92	88	92	89	86	83	77	74	72	65	64	62	55	54	53
2	91	84	78	73	85	78	73	69	68	64	61	58	55	53	49	47	45
3	84	74	67	62	77	69	63	58	60	56	52	52	48	45	44	41	39
4	77	66	58	53	71	62	55	50	54	49	45	47	43	39	40	37	34
5	71	59	51	45	66	56	49	43	49	43	39	42	38	34	36	33	30
6	65	53	45	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	60	48	41	35	56	46	39	34	40	34	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	24	28	24	22
9	53	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26715	26715	26715
5°	26759	25416	25228
10°	26494	24106	23311
15°	26130	22559	21124
20°	25649	20799	18839
25°	25156	18994	16748
30°	24492	17236	14463
35°	23844	15464	12501
40°	23184	13722	10481
45°	22417	11925	8719
50°	21623	10191	7098
55°	20797	8460	5635
60°	19836	6765	4264
65°	18731	5159	3465
70°	17396	3742	2756
75°	15719	2854	2105
80°	13293	1932	1413
85°	9281	884	682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22417 cd/sqm

TEST NUMBER: P999420

CATALOG NUMBER: SA2XXRDIP-B1005D725UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.2	2.5
10°-20°	434.2	7.0
20°-30°	609.6	9.8
30°-40°	664.5	10.7
40°-50°	610.8	9.8
50°-60°	479.7	7.7
60°-70°	312.2	5.0
70°-80°	160.7	2.6
80°-90°	43.6	0.7
90°-100°	160.1	2.6
100°-110°	541.1	8.7
110°-120°	568.7	9.1
120°-130°	467.7	7.5
130°-140°	375.8	6.0
140°-150°	283.9	4.6
150°-160°	199.6	3.2
160°-170°	117.5	1.9
170°-180°	38.2	0.6
0°-30°	1202.0	19.3
0°-40°	1866.6	30.0
0°-60°	2957.0	47.5
0°-90°	3473.5	55.8
90°-120°	1269.9	20.4
90°-150°	2397.3	38.5
90°-180°	2753.0	44.2
0°-180°	6226.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1688	1688	1688	1688	1688	
5°	1688	1680	1660	1674	1669	160
15°	1605	1588	1536	1508	1492	452
25°	1457	1408	1307	1245	1222	670
35°	1256	1178	1043	947	913	786
45°	1026	924	764	655	619	793
55°	780	661	496	405	376	697
65°	527	403	266	214	209	522
75°	281	174	122	112	110	297
85°	66	34	29	29	29	75
90°	1	10	26	25	25	5
95°	27	65	298	112	87	27
105°	93	140	563	1006	856	98
115°	163	206	471	972	1126	162
125°	228	270	452	787	913	202
135°	267	319	447	661	757	206
145°	305	351	445	552	604	191
155°	347	375	432	489	508	160
165°	378	390	414	439	446	107
175°	394	394	398	403	402	37
180°	395	395	395	395	395	

TEST NUMBER: P999420

CATALOG NUMBER: SA2XXRDIP-B1005D725UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1687.7	1687.7	1687.7	1687.7	1687.7
2.5°	1695.4	1687.7	1670.9	1686.2	1683.1
5°	1687.7	1680.1	1660.2	1674.0	1669.4
7.5°	1674.0	1664.8	1643.4	1649.5	1641.9
10°	1655.6	1644.9	1614.4	1609.8	1600.7
12.5°	1632.7	1619.0	1577.7	1568.6	1551.8
15°	1605.2	1588.4	1536.5	1507.5	1492.2
17.5°	1573.2	1548.7	1484.6	1451.0	1426.5
20°	1536.5	1506.0	1429.6	1391.4	1357.8
22.5°	1496.8	1461.7	1373.1	1321.2	1298.2
25°	1457.1	1408.2	1307.4	1244.8	1221.9
27.5°	1409.7	1357.8	1246.3	1174.5	1139.4
30°	1359.3	1301.3	1179.1	1101.2	1060.0
32.5°	1310.5	1240.2	1115.0	1023.3	985.1
35°	1255.5	1177.6	1043.2	947.0	913.4
37.5°	1202.0	1118.0	976.0	870.6	832.4
40°	1145.5	1053.9	905.7	797.3	757.6
42.5°	1087.5	989.7	835.5	722.4	684.2
45°	1026.4	924.0	763.7	655.2	618.6
47.5°	968.3	859.9	694.9	586.5	552.9
50°	904.2	795.7	627.7	522.4	490.3
52.5°	841.6	727.0	563.6	462.8	433.8
55°	780.5	661.3	496.4	404.7	375.7
57.5°	717.9	595.7	436.8	351.3	326.9
60°	653.7	531.5	374.2	296.3	271.9
62.5°	591.1	468.9	320.7	247.4	235.2
65°	526.9	403.2	265.8	213.8	209.2
67.5°	465.8	342.1	213.8	187.9	183.3
70°	401.7	282.6	177.2	161.9	155.8
72.5°	340.6	227.6	148.2	135.9	132.9
75°	281.0	174.1	122.2	111.5	110.0
77.5°	221.5	123.7	96.2	90.1	87.1
80°	166.5	88.6	73.3	67.2	67.2
82.5°	116.1	59.6	50.4	47.3	47.3
85°	65.7	33.6	29.0	29.0	29.0
87.5°	24.4	12.2	12.2	10.7	10.7
90°	0.8	10.2	25.8	24.7	25.1
92.5°	11.4	36.0	116.9	53.9	46.3
95°	26.6	65.3	297.6	112.4	86.6
97.5°	39.5	86.2	485.2	225.5	145.0
100°	58.5	105.6	599.8	449.1	271.8
102.5°	75.9	123.0	603.6	759.2	530.0
105°	92.6	139.7	562.6	1005.6	855.7
107.5°	110.9	156.4	524.6	1094.8	1075.1
110°	129.1	173.5	498.8	1080.4	1164.7



TEST NUMBER: P999420

CATALOG NUMBER: SA2XXRDIP-B1005D725UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	145.8	189.8	482.1	1031.4	1163.2
115°	163.2	206.2	470.7	971.5	1126.0
117.5°	181.5	222.4	464.7	914.1	1069.8
120°	198.2	238.4	459.3	862.8	1015.9
122.5°	214.1	254.7	456.3	823.0	959.7
125°	227.8	269.5	452.5	787.0	913.4
127.5°	239.2	283.6	450.2	756.2	870.1
130°	249.0	296.1	448.7	725.0	834.4
132.5°	258.1	308.2	448.0	692.8	797.2
135°	267.3	318.9	447.2	661.3	757.0
137.5°	275.6	328.0	447.2	629.4	718.2
140°	285.5	336.4	446.4	601.3	678.0
142.5°	295.3	343.2	446.4	574.4	637.8
145°	305.2	350.8	444.9	552.3	604.4
147.5°	315.8	356.8	442.6	533.0	574.8
150°	326.5	363.0	440.4	516.3	548.9
152.5°	337.1	369.0	436.6	502.2	526.9
155°	347.0	374.7	432.0	488.6	507.9
157.5°	355.3	379.2	427.5	475.7	491.2
160°	363.7	383.8	422.9	462.8	475.3
162.5°	372.0	387.2	419.1	450.6	460.1
165°	378.1	389.5	413.8	438.8	445.7
167.5°	383.4	391.8	409.2	428.2	432.0
170°	388.7	393.0	405.4	418.4	419.9
172.5°	391.8	394.0	400.9	409.6	410.0
175°	394.1	394.5	397.8	402.8	401.6
177.5°	395.6	394.8	394.8	397.8	395.6
180°	394.8	394.8	394.8	394.8	394.8

(END OF REPORT)