

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999447

Luminaire Tested: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999447
REPORT IS A COMBINATION OF REPORTS P987998 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6768.0 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999447

CATALOG NUMBER: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999447

CATALOG NUMBER: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	58	58	58
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	50	50	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	43	43	38
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	37	37	33
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	34	32	32	32	29
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	28	28	25
6	64	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	25	25	22
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23	23	23	20
8	56	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	20	20	18
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19	19	19	16
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26869	26869	26869
5°	26912	25563	25373
10°	26648	24245	23445
15°	26282	22689	21246
20°	25798	20919	18947
25°	25301	19103	16843
30°	24634	17336	14546
35°	23981	15553	12573
40°	23317	13801	10541
45°	22545	11994	8768
50°	21747	10251	7139
55°	20917	8508	5668
60°	19952	6805	4287
65°	18841	5188	3486
70°	17496	3764	2772
75°	15814	2871	2117
80°	13365	1942	1421
85°	9337	890	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22545 cd/sqm

TEST NUMBER: P999447

CATALOG NUMBER: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	2.4
10°-20°	436.7	6.5
20°-30°	613.1	9.1
30°-40°	668.4	9.9
40°-50°	614.3	9.1
50°-60°	482.4	7.1
60°-70°	314.0	4.6
70°-80°	161.7	2.4
80°-90°	44.6	0.7
90°-100°	72.4	1.1
100°-110°	230.3	3.4
110°-120°	394.0	5.8
120°-130°	518.2	7.7
130°-140°	581.7	8.6
140°-150°	570.4	8.4
150°-160°	478.5	7.1
160°-170°	317.3	4.7
170°-180°	110.9	1.6
0°-30°	1209.0	17.9
0°-40°	1877.3	27.7
0°-60°	2974.0	43.9
0°-90°	3494.3	51.6
90°-120°	696.7	10.3
90°-150°	2367.0	35.0
90°-180°	3274.0	48.4
0°-180°	6768.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1697	1690	1670	1684	1679	161
15°	1614	1598	1545	1516	1501	455
25°	1466	1416	1315	1252	1229	674
35°	1263	1184	1049	952	919	790
45°	1032	929	768	659	622	797
55°	785	665	499	407	378	701
65°	530	406	267	215	210	525
75°	283	175	123	112	111	299
85°	66	34	29	29	29	76
90°	1	13	35	33	34	7
95°	51	61	63	63	61	57
105°	212	215	217	219	219	224
115°	395	401	399	398	395	391
125°	575	584	581	578	577	514
135°	744	755	757	756	753	575
145°	903	910	916	917	913	564
155°	1033	1036	1038	1044	1040	475
165°	1124	1122	1122	1129	1124	317
175°	1169	1166	1164	1171	1165	111
180°	1171	1171	1171	1171	1171	

TEST NUMBER: P999447

CATALOG NUMBER: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1697.4	1697.4	1697.4	1697.4	1697.4
2.5°	1705.1	1697.4	1680.5	1695.9	1692.8
5°	1697.4	1689.8	1669.8	1683.6	1679.0
7.5°	1683.6	1674.4	1652.9	1659.0	1651.4
10°	1665.2	1654.4	1623.7	1619.1	1609.9
12.5°	1642.1	1628.3	1586.8	1577.6	1560.7
15°	1614.5	1597.6	1545.4	1516.2	1500.8
17.5°	1582.2	1557.6	1493.1	1459.3	1434.8
20°	1545.4	1514.6	1437.8	1399.4	1365.6
22.5°	1505.4	1470.1	1381.0	1328.8	1305.7
25°	1465.5	1416.3	1314.9	1252.0	1228.9
27.5°	1417.9	1365.6	1253.5	1181.3	1146.0
30°	1367.2	1308.8	1185.9	1107.6	1066.1
32.5°	1318.0	1247.3	1121.4	1029.2	990.8
35°	1262.7	1184.4	1049.2	952.4	918.6
37.5°	1208.9	1124.5	981.6	875.6	837.2
40°	1152.1	1059.9	910.9	801.9	761.9
42.5°	1093.7	995.4	840.3	726.6	688.2
45°	1032.3	929.4	768.1	659.0	622.1
47.5°	973.9	864.8	698.9	589.9	556.1
50°	909.4	800.3	631.4	525.4	493.1
52.5°	846.4	731.2	566.8	465.5	436.3
55°	785.0	665.2	499.2	407.1	377.9
57.5°	722.0	599.1	439.3	353.3	328.7
60°	657.5	534.6	376.4	298.0	273.4
62.5°	594.5	471.6	322.6	248.9	236.6
65°	530.0	405.5	267.3	215.1	210.5
67.5°	468.5	344.1	215.1	188.9	184.3
70°	404.0	284.2	178.2	162.8	156.7
72.5°	342.6	228.9	149.0	136.7	133.6
75°	282.7	175.1	122.9	112.1	110.6
77.5°	222.7	124.4	96.8	90.6	87.6
80°	167.4	89.1	73.7	67.6	67.6
82.5°	116.7	59.9	50.7	47.6	47.6
85°	66.1	33.8	29.2	29.2	29.2
87.5°	24.6	12.3	12.3	10.8	10.8
90°	1.0	12.8	34.6	32.6	33.6
92.5°	21.7	29.6	30.6	31.6	31.6
95°	51.4	61.3	63.2	63.2	61.3
97.5°	86.0	94.9	98.8	98.8	98.8
100°	125.5	133.4	136.4	136.4	135.4
102.5°	167.0	172.9	176.9	177.9	176.9
105°	212.4	215.4	217.4	219.4	219.4
107.5°	257.9	261.9	261.9	262.8	257.9
110°	301.4	307.3	307.3	307.3	304.3

TEST NUMBER: P999447

CATALOG NUMBER: SA2XXRDIP-B1005D925UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	348.8	354.7	353.7	350.8	348.8
115°	395.2	401.2	399.2	398.2	395.2
117.5°	441.7	449.6	444.7	441.7	438.7
120°	488.1	496.0	488.1	488.1	485.2
122.5°	530.6	540.5	535.6	532.6	530.6
125°	575.1	584.0	581.0	578.0	577.1
127.5°	618.6	629.4	625.5	621.5	618.6
130°	659.1	671.9	669.9	668.0	664.0
132.5°	704.5	714.4	715.4	710.5	707.5
135°	744.1	754.9	756.9	755.9	752.9
137.5°	787.5	796.4	798.4	797.4	793.5
140°	826.1	835.0	839.9	839.9	835.9
142.5°	865.6	874.5	877.4	878.4	874.5
145°	903.1	910.1	916.0	917.0	913.0
147.5°	936.7	945.6	949.6	951.6	947.6
150°	971.3	977.2	981.2	984.2	981.2
152.5°	1002.0	1007.9	1012.8	1016.8	1012.8
155°	1032.6	1035.5	1038.5	1043.5	1040.5
157.5°	1059.3	1061.2	1063.2	1070.1	1065.2
160°	1083.0	1085.0	1085.9	1091.9	1087.9
162.5°	1104.7	1104.7	1105.7	1112.6	1107.7
165°	1123.5	1122.5	1122.5	1129.4	1124.5
167.5°	1140.3	1137.3	1137.3	1144.2	1139.3
170°	1153.1	1150.2	1149.2	1156.1	1150.2
172.5°	1162.0	1159.1	1158.1	1165.0	1159.1
175°	1168.9	1166.0	1164.0	1170.9	1165.0
177.5°	1172.9	1169.9	1168.0	1173.9	1168.0
180°	1170.9	1170.9	1170.9	1170.9	1170.9

(END OF REPORT)