

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999459

Luminaire Tested: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999459
REPORT IS A COMBINATION OF REPORTS P988010 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6729.0 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999459

CATALOG NUMBER: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999459

CATALOG NUMBER: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	34	32
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28
6	64	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23
8	56	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26715	26715	26715
5°	26759	25416	25228
10°	26494	24106	23311
15°	26130	22559	21124
20°	25649	20799	18839
25°	25156	18994	16748
30°	24492	17236	14463
35°	23844	15464	12501
40°	23184	13722	10481
45°	22417	11925	8719
50°	21623	10191	7098
55°	20797	8460	5635
60°	19836	6765	4264
65°	18731	5159	3465
70°	17396	3742	2756
75°	15719	2854	2105
80°	13293	1932	1413
85°	9281	884	682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22417 cd/sqm

TEST NUMBER: P999459

CATALOG NUMBER: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.2	2.4
10°-20°	434.2	6.5
20°-30°	609.6	9.1
30°-40°	664.5	9.9
40°-50°	610.8	9.1
50°-60°	479.7	7.1
60°-70°	312.2	4.6
70°-80°	160.7	2.4
80°-90°	44.4	0.7
90°-100°	72.0	1.1
100°-110°	228.9	3.4
110°-120°	391.7	5.8
120°-130°	515.2	7.7
130°-140°	578.3	8.6
140°-150°	567.1	8.4
150°-160°	475.7	7.1
160°-170°	315.5	4.7
170°-180°	110.3	1.6
0°-30°	1202.0	17.9
0°-40°	1866.6	27.7
0°-60°	2957.0	43.9
0°-90°	3474.3	51.6
90°-120°	692.7	10.3
90°-150°	2353.2	35.0
90°-180°	3255.0	48.4
0°-180°	6729.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1688	1688	1688	1688	1688	
5°	1688	1680	1660	1674	1669	160
15°	1605	1588	1536	1508	1492	452
25°	1457	1408	1307	1245	1222	670
35°	1256	1178	1043	947	913	786
45°	1026	924	764	655	619	793
55°	780	661	496	405	376	697
65°	527	403	266	214	209	522
75°	281	174	122	112	110	297
85°	66	34	29	29	29	75
90°	1	13	34	32	33	7
95°	51	61	63	63	61	57
105°	211	214	216	218	218	223
115°	393	399	397	396	393	389
125°	572	581	578	575	574	511
135°	740	750	752	752	749	572
145°	898	905	911	912	908	561
155°	1027	1030	1032	1037	1034	473
165°	1117	1116	1116	1123	1118	315
175°	1162	1159	1157	1164	1158	110
180°	1164	1164	1164	1164	1164	

TEST NUMBER: P999459

CATALOG NUMBER: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1687.7	1687.7	1687.7	1687.7	1687.7
2.5°	1695.4	1687.7	1670.9	1686.2	1683.1
5°	1687.7	1680.1	1660.2	1674.0	1669.4
7.5°	1674.0	1664.8	1643.4	1649.5	1641.9
10°	1655.6	1644.9	1614.4	1609.8	1600.7
12.5°	1632.7	1619.0	1577.7	1568.6	1551.8
15°	1605.2	1588.4	1536.5	1507.5	1492.2
17.5°	1573.2	1548.7	1484.6	1451.0	1426.5
20°	1536.5	1506.0	1429.6	1391.4	1357.8
22.5°	1496.8	1461.7	1373.1	1321.2	1298.2
25°	1457.1	1408.2	1307.4	1244.8	1221.9
27.5°	1409.7	1357.8	1246.3	1174.5	1139.4
30°	1359.3	1301.3	1179.1	1101.2	1060.0
32.5°	1310.5	1240.2	1115.0	1023.3	985.1
35°	1255.5	1177.6	1043.2	947.0	913.4
37.5°	1202.0	1118.0	976.0	870.6	832.4
40°	1145.5	1053.9	905.7	797.3	757.6
42.5°	1087.5	989.7	835.5	722.4	684.2
45°	1026.4	924.0	763.7	655.2	618.6
47.5°	968.3	859.9	694.9	586.5	552.9
50°	904.2	795.7	627.7	522.4	490.3
52.5°	841.6	727.0	563.6	462.8	433.8
55°	780.5	661.3	496.4	404.7	375.7
57.5°	717.9	595.7	436.8	351.3	326.9
60°	653.7	531.5	374.2	296.3	271.9
62.5°	591.1	468.9	320.7	247.4	235.2
65°	526.9	403.2	265.8	213.8	209.2
67.5°	465.8	342.1	213.8	187.9	183.3
70°	401.7	282.6	177.2	161.9	155.8
72.5°	340.6	227.6	148.2	135.9	132.9
75°	281.0	174.1	122.2	111.5	110.0
77.5°	221.5	123.7	96.2	90.1	87.1
80°	166.5	88.6	73.3	67.2	67.2
82.5°	116.1	59.6	50.4	47.3	47.3
85°	65.7	33.6	29.0	29.0	29.0
87.5°	24.4	12.2	12.2	10.7	10.7
90°	1.0	12.8	34.4	32.4	33.4
92.5°	21.6	29.5	30.5	31.4	31.4
95°	51.1	60.9	62.9	62.9	60.9
97.5°	85.5	94.3	98.2	98.2	98.2
100°	124.8	132.6	135.6	135.6	134.6
102.5°	166.0	171.9	175.8	176.8	175.8
105°	211.2	214.2	216.1	218.1	218.1
107.5°	256.4	260.3	260.3	261.3	256.4
110°	299.6	305.5	305.5	305.5	302.6



TEST NUMBER: P999459

CATALOG NUMBER: SA2XXRDIP-B1005D925UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	346.8	352.7	351.7	348.7	346.8
115°	393.0	398.8	396.9	395.9	393.0
117.5°	439.1	447.0	442.1	439.1	436.2
120°	485.3	493.2	485.3	485.3	482.4
122.5°	527.5	537.4	532.5	529.5	527.5
125°	571.7	580.6	577.6	574.7	573.7
127.5°	615.0	625.8	621.9	617.9	615.0
130°	655.3	668.0	666.1	664.1	660.2
132.5°	700.4	710.3	711.2	706.3	703.4
135°	739.7	750.5	752.5	751.5	748.6
137.5°	783.0	791.8	793.8	792.8	788.9
140°	821.3	830.1	835.0	835.0	831.1
142.5°	860.6	869.4	872.4	873.3	869.4
145°	897.9	904.8	910.7	911.7	907.7
147.5°	931.3	940.1	944.1	946.0	942.1
150°	965.7	971.6	975.5	978.5	975.5
152.5°	996.1	1002.0	1006.9	1010.9	1006.9
155°	1026.6	1029.5	1032.5	1037.4	1034.5
157.5°	1053.1	1055.1	1057.0	1063.9	1059.0
160°	1076.7	1078.7	1079.6	1085.5	1081.6
162.5°	1098.3	1098.3	1099.3	1106.2	1101.3
165°	1117.0	1116.0	1116.0	1122.9	1118.0
167.5°	1133.7	1130.7	1130.7	1137.6	1132.7
170°	1146.4	1143.5	1142.5	1149.4	1143.5
172.5°	1155.3	1152.3	1151.4	1158.2	1152.3
175°	1162.2	1159.2	1157.3	1164.1	1158.2
177.5°	1166.1	1163.1	1161.2	1167.1	1161.2
180°	1164.1	1164.1	1164.1	1164.1	1164.1

(END OF REPORT)