

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999493

Luminaire Tested: SA2XXRDIP-B290D1080UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999493
REPORT IS A COMBINATION OF REPORTS P988044 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D1080UB35-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4875.0 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999493

CATALOG NUMBER: SA2XXRDIP-B290D1080UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999493

CATALOG NUMBER: SA2XXRDIP-B290D1080UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	19	18
4	70	60	52	47	61	53	47	42	41	36	33	29	27	24	19	17	16
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11
8	50	39	31	26	44	35	28	24	27	22	19	20	17	14	13	11	10
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9
10	43	32	25	21	38	29	23	19	22	18	15	17	14	12	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7766	7766	7766
5°	7778	7388	7334
10°	7702	7007	6776
15°	7596	6558	6141
20°	7457	6047	5476
25°	7313	5522	4868
30°	7121	5011	4204
35°	6932	4494	3634
40°	6740	3989	3046
45°	6517	3467	2534
50°	6284	2963	2063
55°	6046	2459	1638
60°	5765	1967	1239
65°	5446	1500	1007
70°	5058	1088	801
75°	4570	829	612
80°	3864	561	410
85°	2698	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6517 cd/sqm

TEST NUMBER: P999493

CATALOG NUMBER: SA2XXRDIP-B290D1080UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	0.9
10°-20°	126.2	2.6
20°-30°	177.2	3.6
30°-40°	193.2	4.0
40°-50°	177.6	3.6
50°-60°	139.4	2.9
60°-70°	90.8	1.9
70°-80°	46.7	1.0
80°-90°	15.9	0.3
90°-100°	85.5	1.8
100°-110°	271.7	5.6
110°-120°	464.8	9.5
120°-130°	611.3	12.5
130°-140°	686.2	14.1
140°-150°	672.9	13.8
150°-160°	564.5	11.6
160°-170°	374.4	7.7
170°-180°	130.8	2.7
0°-30°	349.4	7.2
0°-40°	542.6	11.1
0°-60°	859.6	17.6
0°-90°	1013.0	20.8
90°-120°	822.0	16.9
90°-150°	2792.4	57.3
90°-180°	3862.0	79.2
0°-180°	4875.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	491	491	491	491	491	
5°	491	488	483	487	485	47
15°	467	462	447	438	434	131
25°	424	409	380	362	355	195
35°	365	342	303	275	266	228
45°	298	269	222	190	180	230
55°	227	192	144	118	109	203
65°	153	117	77	62	61	152
75°	82	51	36	32	32	86
85°	19	10	8	8	8	22
90°	1	15	41	38	40	5
95°	61	72	75	75	72	68
105°	251	254	256	259	259	265
115°	466	473	471	470	466	461
125°	678	689	685	682	681	606
135°	878	891	893	892	888	678
145°	1066	1074	1081	1082	1077	666
155°	1218	1222	1225	1231	1228	561
165°	1325	1324	1324	1332	1327	374
175°	1379	1376	1373	1381	1374	131
180°	1381	1381	1381	1381	1381	

TEST NUMBER: P999493

CATALOG NUMBER: SA2XXRDIP-B290D1080UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	490.6	490.6	490.6	490.6	490.6
2.5°	492.8	490.6	485.7	490.2	489.3
5°	490.6	488.4	482.6	486.6	485.3
7.5°	486.6	483.9	477.7	479.5	477.3
10°	481.3	478.2	469.3	468.0	465.3
12.5°	474.6	470.6	458.6	456.0	451.1
15°	466.6	461.7	446.7	438.2	433.8
17.5°	457.3	450.2	431.6	421.8	414.7
20°	446.7	437.8	415.6	404.5	394.7
22.5°	435.1	424.9	399.1	384.1	377.4
25°	423.6	409.4	380.1	361.9	355.2
27.5°	409.8	394.7	362.3	341.4	331.2
30°	395.2	378.3	342.8	320.1	308.1
32.5°	380.9	360.5	324.1	297.5	286.4
35°	365.0	342.3	303.2	275.3	265.5
37.5°	349.4	325.0	283.7	253.1	242.0
40°	333.0	306.4	263.3	231.8	220.2
42.5°	316.1	287.7	242.9	210.0	198.9
45°	298.4	268.6	222.0	190.5	179.8
47.5°	281.5	250.0	202.0	170.5	160.7
50°	262.8	231.3	182.5	151.8	142.5
52.5°	244.6	211.3	163.8	134.5	126.1
55°	226.9	192.2	144.3	117.7	109.2
57.5°	208.7	173.2	127.0	102.1	95.0
60°	190.0	154.5	108.8	86.1	79.0
62.5°	171.8	136.3	93.2	71.9	68.4
65°	153.2	117.2	77.3	62.2	60.8
67.5°	135.4	99.5	62.2	54.6	53.3
70°	116.8	82.1	51.5	47.1	45.3
72.5°	99.0	66.2	43.1	39.5	38.6
75°	81.7	50.6	35.5	32.4	32.0
77.5°	64.4	36.0	28.0	26.2	25.3
80°	48.4	25.8	21.3	19.5	19.5
82.5°	33.7	17.3	14.7	13.8	13.8
85°	19.1	9.8	8.4	8.4	8.4
87.5°	7.1	3.6	3.6	3.1	3.1
90°	1.2	15.2	40.8	38.5	39.6
92.5°	25.6	35.0	36.1	37.3	37.3
95°	60.6	72.3	74.6	74.6	72.3
97.5°	101.4	111.9	116.6	116.6	116.6
100°	148.0	157.4	160.9	160.9	159.7
102.5°	197.0	204.0	208.7	209.8	208.7
105°	250.6	254.1	256.5	258.8	258.8
107.5°	304.3	308.9	308.9	310.1	304.3
110°	355.5	362.5	362.5	362.5	359.0

TEST NUMBER: P999493

CATALOG NUMBER: SA2XXRDIP-B290D1080UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	411.5	418.5	417.3	413.8	411.5
115°	466.3	473.3	471.0	469.8	466.3
117.5°	521.1	530.4	524.6	521.1	517.6
120°	575.9	585.2	575.9	575.9	572.4
122.5°	626.0	637.6	631.8	628.3	626.0
125°	678.4	688.9	685.4	681.9	680.8
127.5°	729.7	742.6	737.9	733.2	729.7
130°	777.5	792.7	790.4	788.0	783.4
132.5°	831.2	842.8	844.0	838.2	834.7
135°	877.8	890.6	892.9	891.8	888.3
137.5°	929.1	939.6	941.9	940.7	936.1
140°	974.5	985.0	990.9	990.9	986.2
142.5°	1021.2	1031.7	1035.2	1036.3	1031.7
145°	1065.5	1073.6	1080.6	1081.8	1077.1
147.5°	1105.1	1115.6	1120.3	1122.6	1117.9
150°	1145.9	1152.9	1157.6	1161.1	1157.6
152.5°	1182.0	1189.0	1194.9	1199.5	1194.9
155°	1218.2	1221.7	1225.2	1231.0	1227.5
157.5°	1249.7	1252.0	1254.3	1262.5	1256.6
160°	1277.6	1280.0	1281.1	1288.1	1283.5
162.5°	1303.3	1303.3	1304.4	1312.6	1306.8
165°	1325.4	1324.3	1324.3	1332.4	1326.6
167.5°	1345.2	1341.7	1341.7	1349.9	1344.1
170°	1360.4	1356.9	1355.7	1363.9	1356.9
172.5°	1370.9	1367.4	1366.2	1374.4	1367.4
175°	1379.0	1375.5	1373.2	1381.4	1374.4
177.5°	1383.7	1380.2	1377.9	1384.9	1377.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4

(END OF REPORT)