

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998436

Luminaire Tested: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998436
REPORT IS A COMBINATION OF REPORTS P984179 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3286.0 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	102	97	94	90	95	92	89	86	81	79	76	71	70	68	62	61	60
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	50	47	44
4	78	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34
6	67	55	47	41	63	52	45	40	47	41	37	42	37	34	37	34	31
7	62	50	42	36	58	47	40	35	43	37	33	38	34	30	34	30	27
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	32	28	25
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	23
10	51	39	31	27	48	37	30	26	33	28	24	30	26	22	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15188	15188	15188	15188
5°	15226	16194	15283	12885
10°	15048	17679	15142	10622
15°	14683	18647	14887	8948
20°	14455	17508	14455	7777
25°	13993	15041	14057	6954
30°	13236	11824	13488	6300
35°	12565	8176	12774	5763
40°	11791	6173	11927	5336
45°	10841	5073	11018	4875
50°	10017	4452	10037	4463
55°	9078	3794	9140	4015
60°	8078	3169	8190	3505
65°	7185	2577	7316	2993
70°	6293	2022	6453	2413
75°	5281	1468	5488	1751
80°	4120	931	4415	1039
85°	2712	468	2924	348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15700 cd/sqm

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	2.8
10°-20°	266.0	8.1
20°-30°	386.1	11.7
30°-40°	407.0	12.4
40°-50°	360.1	11.0
50°-60°	287.6	8.8
60°-70°	195.3	5.9
70°-80°	99.9	3.0
80°-90°	24.8	0.8
90°-100°	25.8	0.8
100°-110°	82.1	2.5
110°-120°	140.6	4.3
120°-130°	184.8	5.6
130°-140°	207.5	6.3
140°-150°	203.5	6.2
150°-160°	170.7	5.2
160°-170°	113.2	3.4
170°-180°	39.6	1.2
0°-30°	743.5	22.6
0°-40°	1150.4	35.0
0°-60°	1798.1	54.7
0°-90°	2118.2	64.5
90°-120°	248.5	7.6
90°-150°	844.3	25.7
90°-180°	1168.0	35.5
0°-180°	3286.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	960	960	960	960	960	
5°	960	1072	964	853	960	91
15°	902	1317	914	632	902	255
25°	810	1097	814	507	810	371
35°	662	597	673	421	662	414
45°	496	360	504	346	496	385
55°	341	253	343	268	341	304
65°	202	156	206	181	202	201
75°	94	77	98	92	94	101
85°	19	20	21	15	19	22
90°	0	12	0	12	0	2
95°	18	22	18	22	18	20
105°	76	78	76	78	76	80
115°	141	141	141	141	141	139
125°	205	206	205	206	205	183
135°	265	269	265	269	265	205
145°	322	326	322	326	322	201
155°	368	371	368	371	368	170
165°	401	401	401	401	401	113
175°	417	416	417	416	417	40
180°	418	418	418	418	418	

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	964.7	966.9	970.6	971.3	978.7	984.6	991.2	991.2	993.4	992.7	986.8
5°	960.3	966.9	976.5	984.6	997.9	1003.8	1012.6	1019.3	1025.2	1029.6	1028.9
7.5°	952.9	964.7	978.7	994.2	1011.9	1022.2	1034.8	1046.6	1054.7	1062.0	1067.2
10°	940.3	960.3	979.4	1000.1	1023.0	1037.0	1051.7	1067.2	1079.7	1093.8	1107.0
12.5°	923.4	952.1	975.7	1003.0	1031.1	1046.6	1070.2	1082.0	1106.3	1141.7	1151.3
15°	902.0	941.1	963.2	997.9	1034.8	1047.3	1079.7	1098.9	1149.1	1171.2	1197.7
17.5°	882.1	925.6	955.1	994.9	1031.1	1055.4	1087.1	1126.2	1168.2	1200.0	1229.5
20°	865.9	907.9	943.3	987.5	1033.3	1064.3	1097.4	1144.6	1190.4	1222.8	1245.7
22.5°	829.0	882.8	924.1	973.5	1028.9	1071.6	1103.3	1155.0	1204.4	1224.3	1244.2
25°	810.5	857.0	904.9	961.0	1025.9	1076.8	1104.1	1161.6	1205.1	1212.5	1216.9
27.5°	776.6	829.0	885.0	949.2	1025.2	1067.9	1102.6	1155.0	1189.6	1184.5	1171.2
30°	734.6	798.7	860.7	930.0	1014.8	1061.3	1093.8	1141.7	1159.4	1132.8	1109.2
32.5°	703.6	764.1	832.7	913.1	1003.0	1047.3	1079.0	1116.6	1120.3	1072.4	1032.5
35°	661.6	728.7	806.1	890.9	983.1	1023.0	1052.5	1075.3	1057.6	990.5	943.3
37.5°	623.9	690.3	772.9	859.2	955.8	994.9	1018.5	1022.2	978.7	919.7	850.4
40°	582.6	651.2	737.5	828.2	925.6	959.5	974.3	963.2	900.5	831.9	751.5
42.5°	541.3	609.2	702.1	795.1	887.2	916.0	921.9	891.7	815.0	734.6	641.6
45°	496.4	567.2	660.1	753.8	843.0	859.2	860.0	816.4	725.7	641.6	555.4
47.5°	459.5	525.1	617.3	711.0	786.2	797.3	792.8	742.7	643.9	549.5	474.2
50°	418.9	481.6	573.1	665.2	729.4	732.4	721.3	649.8	553.1	466.9	407.1
52.5°	375.4	438.8	522.9	611.4	668.9	664.5	643.1	566.4	475.7	404.2	358.4
55°	340.7	396.8	475.7	562.0	602.6	590.0	566.4	488.2	416.7	356.2	316.4
57.5°	302.4	351.8	429.2	504.5	528.1	516.3	492.7	419.7	353.3	307.5	281.0
60°	266.2	311.2	379.1	441.8	460.2	447.7	420.4	354.8	306.8	268.5	248.5
62.5°	233.1	272.1	328.9	386.5	393.8	381.3	357.7	304.6	263.3	233.1	218.3
65°	202.1	239.0	284.7	328.2	334.8	321.6	297.2	258.9	224.2	205.0	191.0
67.5°	171.8	201.3	241.9	273.6	277.3	264.8	244.9	213.9	192.5	171.8	161.5
70°	145.3	167.4	199.1	224.9	226.4	214.6	204.3	176.3	160.0	145.3	137.2
72.5°	119.5	135.0	159.3	178.5	179.2	171.8	162.3	144.6	130.5	120.2	112.1
75°	94.4	107.7	122.4	139.4	138.7	132.8	125.4	114.3	102.5	95.9	92.2
77.5°	72.3	80.4	92.2	103.3	103.3	100.3	95.9	87.8	80.4	73.8	70.1
80°	51.6	56.8	66.4	70.1	71.5	70.8	67.1	61.2	58.3	53.1	51.6
82.5°	33.2	36.9	41.3	45.0	47.2	45.7	45.0	42.0	37.6	36.1	34.7
85°	19.2	20.7	22.9	25.1	25.8	25.1	26.6	24.3	22.1	22.1	21.4
87.5°	8.1	8.9	10.3	10.3	11.1	11.1	10.3	11.1	11.1	10.3	9.6
90°	0.4	1.3	2.3	3.2	4.1	4.6	5.5	7.2	8.9	10.6	12.3
92.5°	7.8	8.4	9.0	9.7	10.3	10.6	10.6	10.7	10.8	10.8	10.9
95°	18.3	19.1	19.9	20.7	21.5	21.9	22.0	22.1	22.3	22.4	22.6
97.5°	30.7	31.4	32.1	32.8	33.5	33.8	34.0	34.3	34.6	34.9	35.2
100°	44.8	45.4	46.0	46.7	47.3	47.6	47.7	47.9	48.2	48.4	48.6
102.5°	59.6	60.1	60.5	61.0	61.5	61.7	61.9	62.2	62.5	62.8	63.1
105°	75.8	76.0	76.2	76.5	76.7	76.8	76.9	77.0	77.2	77.3	77.5
107.5°	92.0	92.3	92.6	92.9	93.2	93.4	93.4	93.4	93.4	93.4	93.4
110°	107.5	108.0	108.4	108.9	109.4	109.6	109.6	109.6	109.6	109.6	109.6

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	124.4	124.9	125.3	125.8	126.3	126.5	126.5	126.4	126.3	126.3	126.2
115°	141.0	141.5	141.9	142.4	142.9	143.1	143.0	142.9	142.7	142.6	142.4
117.5°	157.6	158.2	158.8	159.5	160.1	160.4	160.2	159.8	159.4	159.0	158.6
120°	174.1	174.7	175.3	176.0	176.6	176.9	176.6	176.0	175.3	174.7	174.1
122.5°	189.3	190.1	190.9	191.6	192.4	192.8	192.6	192.2	191.8	191.4	191.0
125°	205.1	205.8	206.5	207.2	207.9	208.3	208.2	208.0	207.7	207.5	207.3
127.5°	220.7	221.5	222.4	223.2	224.1	224.5	224.3	224.0	223.7	223.4	223.1
130°	235.1	236.1	237.1	238.2	239.2	239.7	239.6	239.5	239.3	239.2	239.0
132.5°	251.3	252.1	252.9	253.7	254.5	254.9	254.9	255.0	255.1	255.1	255.2
135°	265.4	266.3	267.1	268.0	268.9	269.3	269.4	269.5	269.7	269.8	270.0
137.5°	280.9	281.6	282.3	283.0	283.7	284.1	284.2	284.3	284.5	284.6	284.8
140°	294.7	295.4	296.1	296.8	297.5	297.9	298.1	298.5	298.8	299.2	299.6
142.5°	308.8	309.5	310.2	310.9	311.6	312.0	312.1	312.3	312.6	312.8	313.0
145°	322.2	322.7	323.3	323.8	324.3	324.6	324.8	325.3	325.8	326.3	326.8
147.5°	334.2	334.9	335.6	336.3	337.0	337.3	337.5	337.8	338.1	338.4	338.7
150°	346.5	347.0	347.4	347.9	348.4	348.6	348.8	349.1	349.4	349.7	350.0
152.5°	357.4	357.9	358.3	358.8	359.3	359.5	359.7	360.1	360.5	360.9	361.3
155°	368.4	368.6	368.8	369.1	369.3	369.4	369.5	369.8	370.0	370.3	370.5
157.5°	377.9	378.1	378.2	378.4	378.5	378.6	378.7	378.8	379.0	379.1	379.3
160°	386.3	386.5	386.6	386.8	386.9	387.0	387.0	387.1	387.2	387.3	387.4
162.5°	394.1	394.1	394.1	394.1	394.1	394.1	394.1	394.2	394.3	394.3	394.4
165°	400.8	400.7	400.6	400.5	400.4	400.4	400.4	400.4	400.4	400.4	400.4
167.5°	406.8	406.6	406.3	406.1	405.8	405.7	405.7	405.7	405.7	405.7	405.7
170°	411.4	411.2	410.9	410.7	410.4	410.3	410.3	410.2	410.1	410.0	409.9
172.5°	414.5	414.3	414.1	413.8	413.6	413.5	413.5	413.4	413.3	413.2	413.1
175°	417.0	416.8	416.5	416.3	416.0	415.9	415.8	415.7	415.5	415.4	415.2
177.5°	418.4	418.2	417.9	417.7	417.4	417.3	417.2	417.1	416.9	416.8	416.6
180°	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	997.1	997.9	999.3	1006.7	1010.4	1011.1	1008.2	1014.8	1017.1	1014.8	1013.4
5°	1044.3	1048.8	1057.6	1067.2	1066.5	1067.2	1071.6	1076.1	1077.5	1071.6	1073.8
7.5°	1085.6	1094.5	1104.1	1118.8	1118.8	1126.2	1129.2	1132.8	1141.7	1137.3	1135.8
10°	1132.8	1144.6	1162.3	1185.9	1186.7	1194.1	1201.4	1213.2	1216.9	1214.0	1215.4
12.5°	1191.8	1214.7	1216.2	1242.0	1253.8	1255.3	1267.1	1264.9	1272.2	1272.2	1284.8
15°	1217.7	1253.1	1273.0	1298.0	1305.4	1296.6	1306.2	1316.5	1317.2	1317.2	1316.5
17.5°	1264.1	1278.1	1298.0	1311.3	1314.3	1314.3	1315.0	1319.4	1316.5	1310.6	1315.0
20°	1273.7	1279.6	1287.0	1285.5	1287.0	1279.6	1272.2	1264.9	1265.6	1261.9	1273.0
22.5°	1256.0	1254.5	1237.6	1226.5	1226.5	1211.8	1197.7	1191.1	1184.5	1186.7	1190.4
25°	1211.8	1188.9	1168.2	1152.0	1148.3	1124.7	1105.6	1099.7	1088.6	1097.4	1098.9
27.5°	1141.0	1115.1	1082.0	1067.9	1048.8	1039.2	1025.9	1008.2	985.3	998.6	996.4
30°	1065.0	1026.6	999.3	965.4	935.2	933.0	907.9	878.4	866.6	866.6	873.2
32.5°	980.2	929.3	889.5	841.5	812.0	799.5	769.2	739.7	746.4	724.3	732.4
35°	881.3	814.2	764.1	717.6	695.5	680.7	641.6	625.4	607.7	597.4	616.6
37.5°	786.9	709.5	645.3	594.4	586.3	559.8	533.2	522.9	512.6	517.0	516.3
40°	671.9	603.3	545.8	505.9	491.9	479.4	461.7	449.2	442.5	446.2	446.9
42.5°	567.9	510.4	467.6	439.6	427.8	418.9	410.1	399.7	397.5	397.5	400.5
45°	487.5	440.3	411.5	388.7	382.0	375.4	368.8	364.3	362.9	359.9	362.1
47.5°	423.3	385.7	368.0	351.1	343.7	342.2	336.3	334.1	331.1	330.4	331.1
50°	369.5	345.9	329.7	320.1	314.9	312.7	309.8	305.3	303.9	307.5	306.1
52.5°	331.9	309.8	300.9	291.3	288.4	285.4	281.0	281.7	281.0	279.5	279.5
55°	294.3	280.3	271.4	264.0	263.3	260.3	256.7	255.2	254.4	253.0	255.2
57.5°	264.0	253.0	244.9	238.2	235.3	235.3	231.6	228.6	228.6	227.9	228.6
60°	233.8	222.7	217.6	210.9	208.7	208.0	205.8	204.3	202.1	202.1	202.1
62.5°	205.8	196.9	191.0	185.1	185.9	182.2	179.2	177.7	177.7	178.5	178.5
65°	179.2	173.3	165.9	160.8	159.3	158.6	157.1	156.4	154.1	155.6	155.6
67.5°	154.9	146.8	142.3	140.1	137.9	137.2	135.7	134.2	133.5	132.8	134.2
70°	130.5	123.9	120.2	118.7	116.5	115.8	115.1	112.8	113.6	114.3	115.1
72.5°	108.4	102.5	101.8	97.4	97.4	97.4	94.4	95.9	95.1	93.7	95.1
75°	85.6	82.6	81.1	78.9	79.7	78.9	78.2	76.0	76.0	76.7	77.4
77.5°	67.9	64.9	64.2	62.0	60.5	62.0	60.5	59.7	59.7	60.5	60.5
80°	50.2	48.7	46.5	46.5	46.5	45.7	45.7	45.7	45.0	44.3	45.0
82.5°	33.2	33.2	32.5	31.7	32.5	31.0	31.7	31.7	31.7	31.7	31.7
85°	21.4	20.7	20.7	19.9	19.9	19.9	20.7	19.2	19.2	19.9	19.9
87.5°	9.6	9.6	9.6	10.3	9.6	9.6	9.6	10.3	9.6	9.6	9.6
90°	12.1	12.0	11.8	11.7	11.6	11.6	11.7	11.8	11.9	12.0	11.9
92.5°	11.0	11.1	11.2	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3
95°	22.6	22.6	22.6	22.6	22.6	22.5	22.4	22.2	22.1	21.9	22.1
97.5°	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2
100°	48.6	48.6	48.6	48.6	48.6	48.6	48.5	48.4	48.4	48.3	48.4
102.5°	63.2	63.2	63.3	63.4	63.4	63.4	63.3	63.2	63.2	63.1	63.2
105°	77.7	77.9	78.0	78.2	78.3	78.3	78.3	78.3	78.3	78.3	78.3
107.5°	93.5	93.6	93.7	93.8	93.8	93.6	93.2	92.8	92.4	92.0	92.4
110°	109.6	109.6	109.6	109.6	109.6	109.5	109.3	109.0	108.8	108.6	108.8

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	126.0	125.7	125.5	125.2	125.1	125.0	124.9	124.7	124.6	124.4	124.6
115°	142.3	142.3	142.2	142.1	142.1	142.0	141.7	141.5	141.2	141.0	141.2
117.5°	158.4	158.2	157.9	157.7	157.6	157.5	157.2	157.0	156.7	156.5	156.7
120°	174.1	174.1	174.1	174.1	174.1	174.0	173.8	173.5	173.3	173.1	173.3
122.5°	190.8	190.6	190.3	190.1	190.0	189.9	189.8	189.6	189.5	189.3	189.5
125°	207.1	206.8	206.6	206.3	206.2	206.2	206.1	206.0	206.0	205.9	206.0
127.5°	222.8	222.5	222.2	221.9	221.7	221.6	221.4	221.1	220.9	220.7	220.9
130°	238.8	238.7	238.5	238.4	238.3	238.1	237.8	237.5	237.2	236.9	237.2
132.5°	254.8	254.4	254.0	253.6	253.4	253.3	253.1	252.8	252.6	252.4	252.6
135°	269.9	269.9	269.8	269.7	269.7	269.6	269.3	269.1	268.8	268.6	268.8
137.5°	284.7	284.7	284.6	284.5	284.5	284.3	284.0	283.7	283.3	283.0	283.3
140°	299.6	299.6	299.6	299.6	299.6	299.4	299.1	298.8	298.5	298.2	298.5
142.5°	313.1	313.2	313.3	313.4	313.4	313.2	312.9	312.6	312.3	312.0	312.3
145°	326.9	326.9	327.0	327.1	327.1	326.9	326.6	326.3	326.0	325.7	326.0
147.5°	338.9	339.0	339.2	339.3	339.4	339.2	338.9	338.6	338.3	338.0	338.3
150°	350.2	350.5	350.7	351.0	351.1	351.0	350.7	350.5	350.2	350.0	350.2
152.5°	361.6	361.9	362.2	362.5	362.7	362.5	362.2	361.9	361.6	361.3	361.6
155°	370.9	371.3	371.6	372.0	372.2	372.1	371.9	371.6	371.4	371.2	371.4
157.5°	379.8	380.4	380.9	381.4	381.7	381.5	381.1	380.8	380.4	380.0	380.4
160°	387.9	388.3	388.8	389.3	389.5	389.3	389.0	388.7	388.4	388.1	388.4
162.5°	395.0	395.5	396.1	396.6	396.9	396.7	396.3	395.9	395.5	395.1	395.5
165°	401.0	401.5	402.1	402.6	402.9	402.7	402.3	401.9	401.5	401.1	401.5
167.5°	406.3	406.8	407.4	407.9	408.2	408.0	407.6	407.2	406.8	406.4	406.8
170°	410.5	411.0	411.6	412.1	412.4	412.2	411.7	411.2	410.8	410.3	410.8
172.5°	413.7	414.2	414.8	415.3	415.6	415.4	414.9	414.4	414.0	413.5	414.0
175°	415.8	416.3	416.9	417.4	417.7	417.5	417.0	416.5	416.1	415.6	416.1
177.5°	417.1	417.6	418.1	418.6	418.8	418.6	418.1	417.6	417.1	416.6	417.1
180°	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	1017.1	1011.9	1007.5	1008.2	1011.9	1008.9	1001.6	992.0	988.3	983.9	988.3
5°	1078.3	1073.8	1065.0	1065.7	1063.5	1060.6	1048.8	1034.0	1034.0	1022.2	1020.7
7.5°	1138.7	1132.1	1126.2	1124.7	1116.6	1110.7	1100.4	1079.7	1071.6	1057.6	1049.5
10°	1206.6	1201.4	1194.8	1186.7	1182.3	1171.9	1155.0	1124.7	1110.0	1090.8	1076.8
12.5°	1275.2	1274.4	1259.7	1243.5	1242.7	1226.5	1214.7	1174.1	1154.2	1128.4	1095.2
15°	1318.7	1315.0	1306.9	1298.8	1301.0	1283.3	1256.7	1208.8	1195.5	1164.6	1129.2
17.5°	1318.0	1318.0	1315.7	1314.3	1312.1	1306.9	1292.1	1260.4	1239.0	1200.0	1166.8
20°	1275.9	1285.5	1287.7	1287.0	1294.4	1298.0	1297.3	1277.4	1260.4	1225.8	1191.8
22.5°	1191.8	1214.0	1223.6	1229.5	1244.9	1253.1	1272.2	1264.9	1260.4	1234.6	1205.9
25°	1113.7	1121.0	1149.8	1151.3	1172.7	1192.6	1211.8	1224.3	1240.5	1230.9	1206.6
27.5°	1012.6	1029.6	1050.2	1065.7	1070.2	1110.7	1142.4	1166.0	1202.9	1205.9	1197.7
30°	898.3	906.4	940.3	961.0	984.6	1014.1	1059.8	1100.4	1133.6	1163.8	1174.1
32.5°	758.9	792.1	812.0	837.1	857.7	910.1	966.2	1018.5	1056.9	1107.8	1129.9
35°	631.3	657.1	691.1	701.4	739.0	783.3	856.3	923.4	981.6	1033.3	1078.3
37.5°	525.9	546.5	582.6	598.9	621.0	677.8	739.0	822.3	892.4	955.8	1011.9
40°	453.6	469.1	496.4	501.5	520.0	571.6	621.0	699.2	792.1	877.7	938.9
42.5°	404.2	411.5	430.0	436.6	448.4	483.1	527.3	601.1	687.4	775.9	862.2
45°	368.8	373.9	385.0	390.9	405.6	421.1	457.3	516.3	584.1	673.4	766.3
47.5°	337.0	343.7	348.1	351.8	359.9	376.9	400.5	444.0	508.9	590.8	680.7
50°	310.5	312.7	320.8	321.6	326.7	337.8	359.9	386.5	438.1	504.5	591.5
52.5°	283.9	286.2	291.3	296.5	298.7	307.5	322.3	344.4	382.8	435.1	512.6
55°	257.4	260.3	265.5	269.2	271.4	278.8	287.6	309.0	339.3	376.1	439.6
57.5°	230.8	237.5	239.0	241.2	244.9	253.0	261.1	273.6	297.2	331.1	377.6
60°	205.8	208.0	213.1	215.4	219.0	223.5	233.8	243.4	260.3	286.9	328.9
62.5°	180.0	185.1	187.3	189.5	192.5	197.7	204.3	214.6	229.4	250.8	283.9
65°	157.8	158.6	163.0	165.9	168.9	172.6	179.2	188.8	197.7	217.6	241.9
67.5°	136.4	137.9	139.4	142.3	146.0	149.7	155.6	160.8	171.8	185.1	204.3
70°	115.8	115.8	119.5	121.7	121.0	125.4	129.8	135.7	143.8	156.4	171.8
72.5°	97.4	96.6	99.6	100.3	101.8	104.7	107.7	113.6	118.0	127.6	139.4
75°	77.4	78.9	80.4	80.4	82.6	84.8	87.8	90.7	95.9	101.8	110.6
77.5°	61.2	61.2	62.7	63.4	65.6	64.9	67.9	70.8	74.5	79.7	86.3
80°	45.0	46.5	46.5	46.5	47.2	47.9	50.9	53.1	55.3	59.0	62.0
82.5°	31.7	31.7	33.2	33.2	33.2	34.7	34.7	35.4	36.9	39.1	41.3
85°	19.9	19.9	19.9	20.7	19.9	20.7	22.1	21.4	22.1	23.6	23.6
87.5°	9.6	9.6	9.6	9.6	9.6	10.3	9.6	10.3	11.1	11.1	11.1
90°	11.8	11.7	11.6	11.6	11.7	11.8	12.0	12.1	12.3	10.6	8.9
92.5°	11.3	11.3	11.3	11.3	11.3	11.2	11.1	11.0	10.9	10.8	10.8
95°	22.2	22.4	22.5	22.6	22.6	22.6	22.6	22.6	22.6	22.4	22.3
97.5°	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	34.9	34.6
100°	48.4	48.5	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.4	48.2
102.5°	63.2	63.3	63.4	63.4	63.4	63.3	63.2	63.2	63.1	62.8	62.5
105°	78.3	78.3	78.3	78.3	78.2	78.0	77.9	77.7	77.5	77.3	77.2
107.5°	92.8	93.2	93.6	93.8	93.8	93.7	93.6	93.5	93.4	93.4	93.4
110°	109.0	109.3	109.5	109.6	109.6	109.6	109.6	109.6	109.6	109.6	109.6

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	124.7	124.9	125.0	125.1	125.2	125.5	125.7	126.0	126.2	126.3	126.3
115°	141.5	141.7	142.0	142.1	142.1	142.2	142.3	142.3	142.4	142.6	142.7
117.5°	157.0	157.2	157.5	157.6	157.7	157.9	158.2	158.4	158.6	159.0	159.4
120°	173.5	173.8	174.0	174.1	174.1	174.1	174.1	174.1	174.1	174.7	175.3
122.5°	189.6	189.8	189.9	190.0	190.1	190.3	190.6	190.8	191.0	191.4	191.8
125°	206.0	206.1	206.2	206.2	206.3	206.6	206.8	207.1	207.3	207.5	207.7
127.5°	221.1	221.4	221.6	221.7	221.9	222.2	222.5	222.8	223.1	223.4	223.7
130°	237.5	237.8	238.1	238.3	238.4	238.5	238.7	238.8	239.0	239.2	239.3
132.5°	252.8	253.1	253.3	253.4	253.6	254.0	254.4	254.8	255.2	255.1	255.1
135°	269.1	269.3	269.6	269.7	269.7	269.8	269.9	269.9	270.0	269.8	269.7
137.5°	283.7	284.0	284.3	284.5	284.5	284.6	284.7	284.7	284.8	284.6	284.5
140°	298.8	299.1	299.4	299.6	299.6	299.6	299.6	299.6	299.6	299.2	298.8
142.5°	312.6	312.9	313.2	313.4	313.4	313.3	313.2	313.1	313.0	312.8	312.6
145°	326.3	326.6	326.9	327.1	327.1	327.0	326.9	326.9	326.8	326.3	325.8
147.5°	338.6	338.9	339.2	339.4	339.3	339.2	339.0	338.9	338.7	338.4	338.1
150°	350.5	350.7	351.0	351.1	351.0	350.7	350.5	350.2	350.0	349.7	349.4
152.5°	361.9	362.2	362.5	362.7	362.5	362.2	361.9	361.6	361.3	360.9	360.5
155°	371.6	371.9	372.1	372.2	372.0	371.6	371.3	370.9	370.5	370.3	370.0
157.5°	380.8	381.1	381.5	381.7	381.4	380.9	380.4	379.8	379.3	379.1	379.0
160°	388.7	389.0	389.3	389.5	389.3	388.8	388.3	387.9	387.4	387.3	387.2
162.5°	395.9	396.3	396.7	396.9	396.6	396.1	395.5	395.0	394.4	394.3	394.3
165°	401.9	402.3	402.7	402.9	402.6	402.1	401.5	401.0	400.4	400.4	400.4
167.5°	407.2	407.6	408.0	408.2	407.9	407.4	406.8	406.3	405.7	405.7	405.7
170°	411.2	411.7	412.2	412.4	412.1	411.6	411.0	410.5	409.9	410.0	410.1
172.5°	414.4	414.9	415.4	415.6	415.3	414.8	414.2	413.7	413.1	413.2	413.3
175°	416.5	417.0	417.5	417.7	417.4	416.9	416.3	415.8	415.2	415.4	415.5
177.5°	417.6	418.1	418.6	418.8	418.6	418.1	417.6	417.1	416.6	416.8	416.9
180°	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	984.6	980.9	978.7	980.2	975.7	964.7	964.7	968.4	963.9	959.5	952.9
5°	1011.9	1004.5	1000.1	999.3	989.0	971.3	967.6	963.9	954.4	944.0	933.0
7.5°	1038.4	1025.2	1017.8	1012.6	997.9	975.0	965.4	957.3	941.8	926.3	912.3
10°	1060.6	1041.4	1032.5	1024.4	1005.2	976.5	961.0	946.2	926.3	906.4	888.7
12.5°	1078.3	1056.1	1045.1	1033.3	1009.7	972.1	952.9	929.3	909.4	882.8	865.1
15°	1107.8	1062.0	1051.7	1040.7	1016.3	964.7	941.1	914.5	887.2	851.8	832.7
17.5°	1131.4	1070.2	1069.4	1045.8	1014.1	961.7	925.6	890.9	861.4	826.0	795.8
20°	1145.4	1082.7	1070.9	1046.6	1006.7	941.8	904.2	865.9	834.1	791.4	761.1
22.5°	1157.2	1100.4	1069.4	1039.9	991.2	935.2	879.9	843.7	800.2	753.8	725.0
25°	1161.6	1104.1	1071.6	1037.7	980.2	916.0	853.3	814.2	765.6	723.5	684.4
27.5°	1162.3	1103.3	1063.5	1028.1	964.7	890.9	826.8	785.5	731.6	683.0	643.9
30°	1155.0	1095.2	1059.1	1020.7	949.9	868.1	794.3	748.6	691.1	642.4	601.8
32.5°	1132.8	1079.0	1049.5	1007.5	930.8	836.4	763.3	712.5	652.0	604.0	564.9
35°	1096.0	1059.1	1026.6	987.5	905.7	806.9	732.4	672.6	611.4	565.7	528.8
37.5°	1050.2	1030.3	1000.1	961.7	876.9	780.3	697.7	631.3	570.1	525.9	489.7
40°	988.3	993.4	963.9	929.3	843.0	744.2	652.7	589.3	531.8	490.5	455.1
42.5°	921.2	942.6	925.6	892.4	805.4	704.3	619.5	549.5	493.4	450.6	421.1
45°	848.9	885.8	875.4	851.1	766.3	662.3	572.3	504.5	455.1	413.8	387.9
47.5°	770.0	822.3	822.3	804.6	722.8	620.3	531.8	462.4	413.8	384.3	359.2
50°	689.6	748.6	758.2	746.4	674.1	572.3	482.3	419.7	377.6	348.9	330.4
52.5°	605.5	674.1	691.8	685.9	622.5	526.6	441.8	380.6	342.2	317.1	300.9
55°	525.1	604.8	623.9	626.2	567.2	476.4	396.8	343.0	306.1	289.1	275.1
57.5°	449.2	525.9	547.2	550.9	511.1	430.7	354.8	307.5	274.4	260.3	249.3
60°	384.3	448.4	476.4	484.6	449.9	377.6	315.7	269.9	244.9	231.6	221.3
62.5°	331.1	382.8	412.3	414.5	399.0	331.1	275.1	236.7	215.4	203.6	198.4
65°	279.5	326.0	343.7	352.5	340.0	286.9	237.5	205.8	188.8	178.5	173.3
67.5°	238.2	267.7	282.5	294.3	281.7	241.9	202.1	176.3	163.7	153.4	150.5
70°	195.4	219.8	230.8	242.6	231.6	201.3	172.6	149.0	137.9	129.8	126.1
72.5°	156.4	175.5	185.9	193.2	186.6	161.5	137.9	121.7	113.6	107.7	105.5
75°	123.9	137.2	143.1	148.2	145.3	126.1	111.4	98.1	90.7	85.6	84.1
77.5°	94.4	104.0	110.6	112.1	108.4	95.9	83.3	75.2	69.3	66.4	64.9
80°	67.1	73.0	76.7	78.9	75.2	70.1	61.2	55.3	50.2	46.5	45.7
82.5°	45.0	47.9	50.9	50.2	48.7	44.3	39.1	36.1	33.9	31.0	31.0
85°	25.8	26.6	28.0	28.8	28.0	25.1	22.1	20.7	19.2	17.0	17.0
87.5°	11.1	11.8	11.8	12.5	11.1	11.1	9.6	8.1	8.1	7.4	6.6
90°	7.2	5.5	4.6	4.1	3.2	2.3	1.3	0.4	1.3	2.3	3.2
92.5°	10.7	10.6	10.6	10.3	9.7	9.0	8.4	7.8	8.4	9.0	9.7
95°	22.1	22.0	21.9	21.5	20.7	19.9	19.1	18.3	19.1	19.9	20.7
97.5°	34.3	34.0	33.8	33.5	32.8	32.1	31.4	30.7	31.4	32.1	32.8
100°	47.9	47.7	47.6	47.3	46.7	46.0	45.4	44.8	45.4	46.0	46.7
102.5°	62.2	61.9	61.7	61.5	61.0	60.5	60.1	59.6	60.1	60.5	61.0
105°	77.0	76.9	76.8	76.7	76.5	76.2	76.0	75.8	76.0	76.2	76.5
107.5°	93.4	93.4	93.4	93.2	92.9	92.6	92.3	92.0	92.3	92.6	92.9
110°	109.6	109.6	109.6	109.4	108.9	108.4	108.0	107.5	108.0	108.4	108.9

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	126.4	126.5	126.5	126.3	125.8	125.3	124.9	124.4	124.9	125.3	125.8
115°	142.9	143.0	143.1	142.9	142.4	141.9	141.5	141.0	141.5	141.9	142.4
117.5°	159.8	160.2	160.4	160.1	159.5	158.8	158.2	157.6	158.2	158.8	159.5
120°	176.0	176.6	176.9	176.6	176.0	175.3	174.7	174.1	174.7	175.3	176.0
122.5°	192.2	192.6	192.8	192.4	191.6	190.9	190.1	189.3	190.1	190.9	191.6
125°	208.0	208.2	208.3	207.9	207.2	206.5	205.8	205.1	205.8	206.5	207.2
127.5°	224.0	224.3	224.5	224.1	223.2	222.4	221.5	220.7	221.5	222.4	223.2
130°	239.5	239.6	239.7	239.2	238.2	237.1	236.1	235.1	236.1	237.1	238.2
132.5°	255.0	254.9	254.9	254.5	253.7	252.9	252.1	251.3	252.1	252.9	253.7
135°	269.5	269.4	269.3	268.9	268.0	267.1	266.3	265.4	266.3	267.1	268.0
137.5°	284.3	284.2	284.1	283.7	283.0	282.3	281.6	280.9	281.6	282.3	283.0
140°	298.5	298.1	297.9	297.5	296.8	296.1	295.4	294.7	295.4	296.1	296.8
142.5°	312.3	312.1	312.0	311.6	310.9	310.2	309.5	308.8	309.5	310.2	310.9
145°	325.3	324.8	324.6	324.3	323.8	323.3	322.7	322.2	322.7	323.3	323.8
147.5°	337.8	337.5	337.3	337.0	336.3	335.6	334.9	334.2	334.9	335.6	336.3
150°	349.1	348.8	348.6	348.4	347.9	347.4	347.0	346.5	347.0	347.4	347.9
152.5°	360.1	359.7	359.5	359.3	358.8	358.3	357.9	357.4	357.9	358.3	358.8
155°	369.8	369.5	369.4	369.3	369.1	368.8	368.6	368.4	368.6	368.8	369.1
157.5°	378.8	378.7	378.6	378.5	378.4	378.2	378.1	377.9	378.1	378.2	378.4
160°	387.1	387.0	387.0	386.9	386.8	386.6	386.5	386.3	386.5	386.6	386.8
162.5°	394.2	394.1	394.1	394.1	394.1	394.1	394.1	394.1	394.1	394.1	394.1
165°	400.4	400.4	400.4	400.4	400.5	400.6	400.7	400.8	400.7	400.6	400.5
167.5°	405.7	405.7	405.7	405.8	406.1	406.3	406.6	406.8	406.6	406.3	406.1
170°	410.2	410.3	410.3	410.4	410.7	410.9	411.2	411.4	411.2	410.9	410.7
172.5°	413.4	413.5	413.5	413.6	413.8	414.1	414.3	414.5	414.3	414.1	413.8
175°	415.7	415.8	415.9	416.0	416.3	416.5	416.8	417.0	416.8	416.5	416.3
177.5°	417.1	417.2	417.3	417.4	417.7	417.9	418.2	418.4	418.2	417.9	417.7
180°	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	949.2	952.9	952.1	944.8	936.7	930.0	917.5	919.0	914.5	915.3	919.7
5°	925.6	925.6	922.6	912.3	899.0	891.7	877.7	874.0	865.1	864.4	863.6
7.5°	900.5	896.8	893.1	878.4	862.2	850.4	831.2	826.8	817.9	812.0	809.1
10°	871.0	865.9	858.5	841.5	821.6	806.9	786.9	781.0	764.1	756.7	752.3
12.5°	838.6	835.6	823.8	809.8	777.4	761.1	732.4	738.3	721.3	706.6	704.3
15°	806.1	795.1	788.4	765.6	726.5	719.1	696.2	684.4	668.9	657.1	657.1
17.5°	774.4	757.4	742.7	718.4	689.6	668.9	652.0	646.1	626.9	615.1	612.9
20°	732.4	713.2	709.5	674.8	654.9	632.1	615.8	601.1	587.1	581.9	578.2
22.5°	692.5	670.4	664.5	635.0	615.1	592.2	576.0	565.7	555.4	551.7	545.0
25°	649.8	636.5	627.6	595.9	573.8	552.4	541.3	534.0	524.4	523.6	519.2
27.5°	608.5	595.9	587.1	556.8	540.6	520.7	511.8	503.7	498.6	496.4	494.1
30°	573.1	559.0	548.7	526.6	506.7	490.5	483.1	477.9	475.0	471.3	470.5
32.5°	534.0	525.9	511.8	494.9	479.4	463.9	459.5	455.8	451.4	449.9	449.2
35°	500.8	489.7	480.9	461.7	455.1	441.8	436.6	433.7	427.8	426.3	424.8
37.5°	468.3	458.0	448.4	436.6	424.1	416.7	413.8	409.3	406.4	407.1	405.6
40°	435.9	427.8	420.4	407.9	400.5	396.8	390.9	386.5	385.0	385.7	385.0
42.5°	404.2	396.8	392.4	382.8	375.4	371.7	368.0	363.6	365.8	365.8	368.0
45°	375.4	368.8	365.8	358.4	354.0	348.1	344.4	343.7	346.6	345.9	345.9
47.5°	345.9	343.7	340.0	333.4	327.5	323.8	323.0	323.0	326.0	327.5	326.7
50°	323.0	318.6	314.2	309.0	304.6	303.1	300.9	302.4	305.3	305.3	306.8
52.5°	294.3	291.3	289.8	285.4	282.5	282.5	282.5	283.2	285.4	287.6	286.9
55°	269.2	267.0	265.5	263.3	259.6	260.3	259.6	261.1	263.3	265.5	267.0
57.5°	242.6	241.9	240.4	236.7	236.7	236.0	238.2	239.0	242.6	244.1	246.3
60°	219.0	216.8	216.8	213.9	213.9	213.9	216.1	218.3	221.3	222.0	223.5
62.5°	194.0	194.0	193.2	191.0	191.0	193.2	194.0	196.9	198.4	198.4	200.6
65°	170.4	169.6	168.9	169.6	170.4	170.4	172.6	174.1	175.5	176.3	177.0
67.5°	146.8	146.0	147.5	146.8	148.2	151.2	150.5	152.7	154.9	154.9	155.6
70°	124.6	126.1	125.4	126.9	126.1	127.6	129.8	130.5	130.5	131.3	133.5
72.5°	104.0	104.0	104.0	103.3	104.0	105.5	106.9	107.7	109.2	109.9	112.1
75°	84.1	84.1	82.6	84.1	84.1	85.6	87.0	87.0	87.0	88.5	90.7
77.5°	63.4	64.2	63.4	64.9	64.9	65.6	67.1	66.4	67.9	68.6	69.3
80°	46.5	45.7	45.7	45.7	46.5	46.5	47.9	48.7	48.7	50.9	49.4
82.5°	29.5	30.2	29.5	30.2	30.2	31.0	30.2	31.0	31.7	33.2	32.5
85°	17.0	16.2	16.2	17.0	16.2	16.2	17.0	16.2	17.0	16.2	17.0
87.5°	6.6	5.9	5.9	5.9	5.9	5.2	5.2	4.4	4.4	4.4	3.7
90°	4.1	4.6	5.5	7.2	8.9	10.6	12.3	12.1	12.0	11.8	11.7
92.5°	10.3	10.6	10.6	10.7	10.8	10.8	10.9	11.0	11.1	11.2	11.3
95°	21.5	21.9	22.0	22.1	22.3	22.4	22.6	22.6	22.6	22.6	22.6
97.5°	33.5	33.8	34.0	34.3	34.6	34.9	35.2	35.2	35.2	35.2	35.2
100°	47.3	47.6	47.7	47.9	48.2	48.4	48.6	48.6	48.6	48.6	48.6
102.5°	61.5	61.7	61.9	62.2	62.5	62.8	63.1	63.2	63.2	63.3	63.4
105°	76.7	76.8	76.9	77.0	77.2	77.3	77.5	77.7	77.9	78.0	78.2
107.5°	93.2	93.4	93.4	93.4	93.4	93.4	93.4	93.5	93.6	93.7	93.8
110°	109.4	109.6	109.6	109.6	109.6	109.6	109.6	109.6	109.6	109.6	109.6

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	126.3	126.5	126.5	126.4	126.3	126.3	126.2	126.0	125.7	125.5	125.2
115°	142.9	143.1	143.0	142.9	142.7	142.6	142.4	142.3	142.3	142.2	142.1
117.5°	160.1	160.4	160.2	159.8	159.4	159.0	158.6	158.4	158.2	157.9	157.7
120°	176.6	176.9	176.6	176.0	175.3	174.7	174.1	174.1	174.1	174.1	174.1
122.5°	192.4	192.8	192.6	192.2	191.8	191.4	191.0	190.8	190.6	190.3	190.1
125°	207.9	208.3	208.2	208.0	207.7	207.5	207.3	207.1	206.8	206.6	206.3
127.5°	224.1	224.5	224.3	224.0	223.7	223.4	223.1	222.8	222.5	222.2	221.9
130°	239.2	239.7	239.6	239.5	239.3	239.2	239.0	238.8	238.7	238.5	238.4
132.5°	254.5	254.9	254.9	255.0	255.1	255.1	255.2	254.8	254.4	254.0	253.6
135°	268.9	269.3	269.4	269.5	269.7	269.8	270.0	269.9	269.9	269.8	269.7
137.5°	283.7	284.1	284.2	284.3	284.5	284.6	284.8	284.7	284.7	284.6	284.5
140°	297.5	297.9	298.1	298.5	298.8	299.2	299.6	299.6	299.6	299.6	299.6
142.5°	311.6	312.0	312.1	312.3	312.6	312.8	313.0	313.1	313.2	313.3	313.4
145°	324.3	324.6	324.8	325.3	325.8	326.3	326.8	326.9	326.9	327.0	327.1
147.5°	337.0	337.3	337.5	337.8	338.1	338.4	338.7	338.9	339.0	339.2	339.3
150°	348.4	348.6	348.8	349.1	349.4	349.7	350.0	350.2	350.5	350.7	351.0
152.5°	359.3	359.5	359.7	360.1	360.5	360.9	361.3	361.6	361.9	362.2	362.5
155°	369.3	369.4	369.5	369.8	370.0	370.3	370.5	370.9	371.3	371.6	372.0
157.5°	378.5	378.6	378.7	378.8	379.0	379.1	379.3	379.8	380.4	380.9	381.4
160°	386.9	387.0	387.0	387.1	387.2	387.3	387.4	387.9	388.3	388.8	389.3
162.5°	394.1	394.1	394.1	394.2	394.3	394.3	394.4	395.0	395.5	396.1	396.6
165°	400.4	400.4	400.4	400.4	400.4	400.4	400.4	401.0	401.5	402.1	402.6
167.5°	405.8	405.7	405.7	405.7	405.7	405.7	405.7	406.3	406.8	407.4	407.9
170°	410.4	410.3	410.3	410.2	410.1	410.0	409.9	410.5	411.0	411.6	412.1
172.5°	413.6	413.5	413.5	413.4	413.3	413.2	413.1	413.7	414.2	414.8	415.3
175°	416.0	415.9	415.8	415.7	415.5	415.4	415.2	415.8	416.3	416.9	417.4
177.5°	417.4	417.3	417.2	417.1	416.9	416.8	416.6	417.1	417.6	418.1	418.6
180°	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	914.5	916.7	911.6	910.1	911.6	906.4	907.9	909.4	909.4	911.6	913.1
5°	861.4	858.5	853.3	851.8	850.4	852.6	851.1	853.3	854.1	859.2	860.0
7.5°	809.1	804.6	800.2	795.8	794.3	790.6	794.3	794.3	799.5	798.0	801.7
10°	747.1	746.4	740.5	738.3	735.3	729.4	737.5	735.3	739.0	745.6	747.1
12.5°	701.4	693.3	697.0	686.6	690.3	684.4	685.2	685.2	691.1	691.8	690.3
15°	657.9	651.2	641.6	637.2	635.0	632.1	641.6	642.4	638.0	648.3	644.6
17.5°	613.6	613.6	604.8	602.6	596.7	599.6	598.1	598.9	597.4	604.8	608.5
20°	575.3	571.6	568.6	569.4	562.0	560.5	559.0	560.5	565.7	570.8	572.3
22.5°	544.3	542.1	534.7	536.2	530.3	532.5	531.0	534.7	535.4	535.4	540.6
25°	514.8	511.8	512.6	509.6	507.4	507.4	505.2	507.4	510.4	511.8	512.6
27.5°	492.7	490.5	486.8	484.6	486.0	482.3	485.3	487.5	487.5	486.0	487.5
30°	466.1	467.6	467.6	460.2	463.2	461.7	463.9	465.4	465.4	466.1	464.6
32.5°	448.4	444.0	443.3	442.5	442.5	439.6	439.6	441.8	442.5	443.3	445.5
35°	424.8	424.8	421.1	423.3	420.4	421.1	420.4	421.1	422.6	420.4	422.6
37.5°	403.4	404.2	402.7	404.2	404.9	403.4	402.0	404.9	403.4	403.4	402.0
40°	385.0	384.3	385.0	385.0	385.0	385.7	384.3	384.3	384.3	382.8	381.3
42.5°	369.5	365.1	366.6	367.3	365.1	365.1	365.8	365.1	367.3	362.9	362.9
45°	347.4	345.9	346.6	346.6	348.1	345.9	347.4	348.1	345.9	345.2	343.7
47.5°	327.5	328.9	327.5	328.9	328.9	330.4	327.5	328.2	328.9	326.0	323.8
50°	307.5	307.5	309.8	309.0	309.8	308.3	308.3	307.5	308.3	306.8	304.6
52.5°	289.1	286.9	290.6	289.8	289.1	288.4	287.6	288.4	286.9	285.4	285.4
55°	266.2	266.2	268.5	269.2	269.2	267.7	266.2	267.0	266.2	265.5	264.8
57.5°	247.8	244.9	246.3	247.1	247.1	244.9	246.3	244.9	244.9	245.6	243.4
60°	224.2	224.2	222.7	224.9	224.9	223.5	223.5	224.2	222.7	222.0	221.3
62.5°	199.1	199.9	202.1	202.8	203.6	202.1	200.6	201.3	201.3	199.1	199.9
65°	177.7	179.2	182.2	181.4	180.0	180.7	179.2	180.0	177.7	178.5	176.3
67.5°	157.1	156.4	157.1	157.1	158.6	157.8	156.4	156.4	155.6	157.8	155.6
70°	135.0	135.0	135.0	135.0	135.7	136.4	135.0	133.5	134.2	132.8	132.0
72.5°	112.1	112.8	112.1	113.6	111.4	112.8	112.8	112.1	111.4	111.4	111.4
75°	90.7	92.2	90.0	90.7	90.0	91.5	90.7	90.7	89.2	88.5	89.2
77.5°	69.3	70.1	68.6	69.3	68.6	69.3	69.3	68.6	68.6	68.6	68.6
80°	49.4	50.2	49.4	48.7	47.9	49.4	47.9	48.7	49.4	48.7	50.2
82.5°	31.7	31.7	31.0	31.7	30.2	30.2	31.0	31.0	30.2	31.7	30.2
85°	15.5	15.5	17.0	15.5	14.8	14.8	14.8	15.5	14.8	16.2	15.5
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.4	3.0
90°	11.6	11.6	11.7	11.8	11.9	12.0	11.9	11.8	11.7	11.6	11.6
92.5°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3
95°	22.6	22.5	22.4	22.2	22.1	21.9	22.1	22.2	22.4	22.5	22.6
97.5°	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2
100°	48.6	48.6	48.5	48.4	48.4	48.3	48.4	48.4	48.5	48.6	48.6
102.5°	63.4	63.4	63.3	63.2	63.2	63.1	63.2	63.2	63.3	63.4	63.4
105°	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3
107.5°	93.8	93.6	93.2	92.8	92.4	92.0	92.4	92.8	93.2	93.6	93.8
110°	109.6	109.5	109.3	109.0	108.8	108.6	108.8	109.0	109.3	109.5	109.6

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	125.1	125.0	124.9	124.7	124.6	124.4	124.6	124.7	124.9	125.0	125.1
115°	142.1	142.0	141.7	141.5	141.2	141.0	141.2	141.5	141.7	142.0	142.1
117.5°	157.6	157.5	157.2	157.0	156.7	156.5	156.7	157.0	157.2	157.5	157.6
120°	174.1	174.0	173.8	173.5	173.3	173.1	173.3	173.5	173.8	174.0	174.1
122.5°	190.0	189.9	189.8	189.6	189.5	189.3	189.5	189.6	189.8	189.9	190.0
125°	206.2	206.2	206.1	206.0	206.0	205.9	206.0	206.0	206.1	206.2	206.2
127.5°	221.7	221.6	221.4	221.1	220.9	220.7	220.9	221.1	221.4	221.6	221.7
130°	238.3	238.1	237.8	237.5	237.2	236.9	237.2	237.5	237.8	238.1	238.3
132.5°	253.4	253.3	253.1	252.8	252.6	252.4	252.6	252.8	253.1	253.3	253.4
135°	269.7	269.6	269.3	269.1	268.8	268.6	268.8	269.1	269.3	269.6	269.7
137.5°	284.5	284.3	284.0	283.7	283.3	283.0	283.3	283.7	284.0	284.3	284.5
140°	299.6	299.4	299.1	298.8	298.5	298.2	298.5	298.8	299.1	299.4	299.6
142.5°	313.4	313.2	312.9	312.6	312.3	312.0	312.3	312.6	312.9	313.2	313.4
145°	327.1	326.9	326.6	326.3	326.0	325.7	326.0	326.3	326.6	326.9	327.1
147.5°	339.4	339.2	338.9	338.6	338.3	338.0	338.3	338.6	338.9	339.2	339.4
150°	351.1	351.0	350.7	350.5	350.2	350.0	350.2	350.5	350.7	351.0	351.1
152.5°	362.7	362.5	362.2	361.9	361.6	361.3	361.6	361.9	362.2	362.5	362.7
155°	372.2	372.1	371.9	371.6	371.4	371.2	371.4	371.6	371.9	372.1	372.2
157.5°	381.7	381.5	381.1	380.8	380.4	380.0	380.4	380.8	381.1	381.5	381.7
160°	389.5	389.3	389.0	388.7	388.4	388.1	388.4	388.7	389.0	389.3	389.5
162.5°	396.9	396.7	396.3	395.9	395.5	395.1	395.5	395.9	396.3	396.7	396.9
165°	402.9	402.7	402.3	401.9	401.5	401.1	401.5	401.9	402.3	402.7	402.9
167.5°	408.2	408.0	407.6	407.2	406.8	406.4	406.8	407.2	407.6	408.0	408.2
170°	412.4	412.2	411.7	411.2	410.8	410.3	410.8	411.2	411.7	412.2	412.4
172.5°	415.6	415.4	414.9	414.4	414.0	413.5	414.0	414.4	414.9	415.4	415.6
175°	417.7	417.5	417.0	416.5	416.1	415.6	416.1	416.5	417.0	417.5	417.7
177.5°	418.8	418.6	418.1	417.6	417.1	416.6	417.1	417.6	418.1	418.6	418.8
180°	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	910.8	916.7	914.5	906.4	916.0	916.0	922.6	922.6	930.8	933.7	938.1
5°	859.2	863.6	867.3	863.6	870.3	880.6	886.5	891.7	902.7	907.2	913.8
7.5°	803.9	812.0	815.7	815.7	826.8	838.6	850.4	857.7	873.2	879.1	885.8
10°	750.1	759.7	767.0	766.3	784.7	792.1	806.9	823.8	839.3	848.2	857.7
12.5°	693.3	698.4	708.8	723.5	727.9	741.2	758.2	779.6	807.6	815.7	829.7
15°	646.1	660.1	668.2	674.8	685.2	697.7	716.1	736.8	764.8	782.5	797.3
17.5°	606.2	624.7	629.8	628.4	641.6	660.8	682.2	697.7	722.8	744.2	758.2
20°	573.8	581.2	590.0	593.7	604.0	624.7	645.3	663.0	683.7	700.7	716.9
22.5°	541.3	547.2	554.6	561.3	569.4	581.2	601.1	623.2	643.1	659.3	677.8
25°	514.8	518.5	525.1	530.3	539.1	547.2	561.3	585.6	609.2	618.8	635.0
27.5°	489.0	491.9	496.4	502.3	506.7	514.8	527.3	547.2	571.6	581.2	603.3
30°	466.1	468.3	472.8	475.7	477.9	487.5	497.1	512.6	531.0	544.3	560.5
32.5°	444.7	446.9	451.4	452.1	455.1	460.2	469.1	483.1	499.3	510.4	524.4
35°	421.1	422.6	427.0	428.5	430.7	435.1	441.8	452.1	466.9	475.0	487.5
37.5°	402.7	402.0	404.9	407.1	410.1	412.3	414.5	424.8	435.9	443.3	452.8
40°	382.8	381.3	382.0	385.0	386.5	389.4	389.4	399.7	407.1	413.0	420.4
42.5°	362.9	362.1	360.7	362.1	363.6	364.3	365.1	372.5	379.8	385.0	393.1
45°	343.0	342.2	340.7	341.5	341.5	343.0	345.2	348.1	353.3	357.7	362.1
47.5°	324.5	323.0	320.8	320.1	321.6	321.6	321.6	324.5	329.7	331.1	335.6
50°	305.3	303.1	300.2	298.7	298.7	298.0	299.4	300.2	304.6	306.1	309.8
52.5°	284.7	283.2	280.3	277.3	278.0	276.6	277.3	278.0	279.5	281.7	283.9
55°	264.0	261.1	258.9	258.1	255.9	255.9	253.7	256.7	255.9	256.7	259.6
57.5°	244.1	241.2	237.5	236.0	233.8	233.1	231.6	230.8	231.6	233.8	236.0
60°	220.5	219.0	216.8	214.6	213.1	210.9	209.5	209.5	208.7	208.7	209.5
62.5°	197.7	196.9	194.0	193.2	191.8	190.3	188.1	186.6	186.6	188.1	188.8
65°	175.5	174.8	172.6	171.8	168.2	166.7	165.9	165.2	163.7	163.7	163.7
67.5°	154.9	152.7	152.7	149.0	146.0	144.6	143.1	142.3	142.3	142.3	143.1
70°	132.0	132.0	129.8	127.6	124.6	125.4	123.2	121.0	121.0	119.5	120.2
72.5°	109.9	109.2	106.9	106.2	104.0	101.8	100.3	101.8	99.6	98.8	99.6
75°	88.5	87.8	86.3	84.8	85.6	83.3	81.1	80.4	80.4	78.9	78.9
77.5°	67.9	69.3	66.4	65.6	64.2	62.7	62.0	61.2	61.2	61.2	62.7
80°	47.2	47.9	47.9	46.5	47.2	45.0	45.0	45.0	42.8	43.5	44.3
82.5°	30.2	30.2	29.5	30.2	29.5	29.5	28.8	28.8	28.0	28.0	28.8
85°	17.0	16.2	15.5	17.0	16.2	16.2	15.5	15.5	15.5	15.5	15.5
87.5°	3.7	4.4	4.4	4.4	4.4	5.2	5.2	5.2	5.9	5.9	5.9
90°	11.7	11.8	12.0	12.1	12.3	10.6	8.9	7.2	5.5	4.6	4.1
92.5°	11.3	11.2	11.1	11.0	10.9	10.8	10.8	10.7	10.6	10.6	10.3
95°	22.6	22.6	22.6	22.6	22.6	22.4	22.3	22.1	22.0	21.9	21.5
97.5°	35.2	35.2	35.2	35.2	35.2	34.9	34.6	34.3	34.0	33.8	33.5
100°	48.6	48.6	48.6	48.6	48.6	48.4	48.2	47.9	47.7	47.6	47.3
102.5°	63.4	63.3	63.2	63.2	63.1	62.8	62.5	62.2	61.9	61.7	61.5
105°	78.2	78.0	77.9	77.7	77.5	77.3	77.2	77.0	76.9	76.8	76.7
107.5°	93.8	93.7	93.6	93.5	93.4	93.4	93.4	93.4	93.4	93.4	93.2
110°	109.6	109.6	109.6	109.6	109.6	109.6	109.6	109.6	109.6	109.6	109.4

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	125.2	125.5	125.7	126.0	126.2	126.3	126.3	126.4	126.5	126.5	126.3
115°	142.1	142.2	142.3	142.3	142.4	142.6	142.7	142.9	143.0	143.1	142.9
117.5°	157.7	157.9	158.2	158.4	158.6	159.0	159.4	159.8	160.2	160.4	160.1
120°	174.1	174.1	174.1	174.1	174.1	174.7	175.3	176.0	176.6	176.9	176.6
122.5°	190.1	190.3	190.6	190.8	191.0	191.4	191.8	192.2	192.6	192.8	192.4
125°	206.3	206.6	206.8	207.1	207.3	207.5	207.7	208.0	208.2	208.3	207.9
127.5°	221.9	222.2	222.5	222.8	223.1	223.4	223.7	224.0	224.3	224.5	224.1
130°	238.4	238.5	238.7	238.8	239.0	239.2	239.3	239.5	239.6	239.7	239.2
132.5°	253.6	254.0	254.4	254.8	255.2	255.1	255.1	255.0	254.9	254.9	254.5
135°	269.7	269.8	269.9	269.9	270.0	269.8	269.7	269.5	269.4	269.3	268.9
137.5°	284.5	284.6	284.7	284.7	284.8	284.6	284.5	284.3	284.2	284.1	283.7
140°	299.6	299.6	299.6	299.6	299.6	299.2	298.8	298.5	298.1	297.9	297.5
142.5°	313.4	313.3	313.2	313.1	313.0	312.8	312.6	312.3	312.1	312.0	311.6
145°	327.1	327.0	326.9	326.9	326.8	326.3	325.8	325.3	324.8	324.6	324.3
147.5°	339.3	339.2	339.0	338.9	338.7	338.4	338.1	337.8	337.5	337.3	337.0
150°	351.0	350.7	350.5	350.2	350.0	349.7	349.4	349.1	348.8	348.6	348.4
152.5°	362.5	362.2	361.9	361.6	361.3	360.9	360.5	360.1	359.7	359.5	359.3
155°	372.0	371.6	371.3	370.9	370.5	370.3	370.0	369.8	369.5	369.4	369.3
157.5°	381.4	380.9	380.4	379.8	379.3	379.1	379.0	378.8	378.7	378.6	378.5
160°	389.3	388.8	388.3	387.9	387.4	387.3	387.2	387.1	387.0	387.0	386.9
162.5°	396.6	396.1	395.5	395.0	394.4	394.3	394.3	394.2	394.1	394.1	394.1
165°	402.6	402.1	401.5	401.0	400.4	400.4	400.4	400.4	400.4	400.4	400.4
167.5°	407.9	407.4	406.8	406.3	405.7	405.7	405.7	405.7	405.7	405.7	405.8
170°	412.1	411.6	411.0	410.5	409.9	410.0	410.1	410.2	410.3	410.3	410.4
172.5°	415.3	414.8	414.2	413.7	413.1	413.2	413.3	413.4	413.5	413.5	413.6
175°	417.4	416.9	416.3	415.8	415.2	415.4	415.5	415.7	415.8	415.9	416.0
177.5°	418.6	418.1	417.6	417.1	416.6	416.8	416.9	417.1	417.2	417.3	417.4
180°	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7	417.7

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	959.5	959.5	959.5	959.5
2.5°	941.8	941.8	952.9	964.7
5°	921.2	926.3	944.0	960.3
7.5°	901.3	910.1	932.2	952.9
10°	876.9	888.7	916.0	940.3
12.5°	853.3	864.4	896.1	923.4
15°	820.1	834.1	868.1	902.0
17.5°	786.9	801.0	842.3	882.1
20°	747.9	766.3	812.8	865.9
22.5°	711.7	734.6	786.2	829.0
25°	671.9	707.3	755.2	810.5
27.5°	636.5	671.9	720.6	776.6
30°	596.7	632.8	683.0	734.6
32.5°	558.3	591.5	640.2	703.6
35°	518.5	550.2	597.4	661.6
37.5°	482.3	513.3	564.9	623.9
40°	446.9	479.4	523.6	582.6
42.5°	413.8	442.5	482.3	541.3
45°	383.5	404.2	441.0	496.4
47.5°	351.8	370.2	404.2	459.5
50°	322.3	337.8	367.3	418.9
52.5°	293.5	306.8	334.1	375.4
55°	267.7	280.3	300.2	340.7
57.5°	241.2	250.8	269.9	302.4
60°	215.4	224.2	239.7	266.2
62.5°	189.5	196.9	211.7	233.1
65°	166.7	172.6	183.6	202.1
67.5°	144.6	148.2	157.1	171.8
70°	123.2	126.1	133.5	145.3
72.5°	100.3	103.3	111.4	119.5
75°	81.1	81.9	87.8	94.4
77.5°	63.4	62.7	67.1	72.3
80°	43.5	45.7	49.4	51.6
82.5°	29.5	30.2	31.7	33.2
85°	16.2	17.0	17.0	19.2
87.5°	6.6	7.4	7.4	8.1
90°	3.2	2.3	1.3	0.4
92.5°	9.7	9.0	8.4	7.8
95°	20.7	19.9	19.1	18.3
97.5°	32.8	32.1	31.4	30.7
100°	46.7	46.0	45.4	44.8
102.5°	61.0	60.5	60.1	59.6
105°	76.5	76.2	76.0	75.8
107.5°	92.9	92.6	92.3	92.0
110°	108.9	108.4	108.0	107.5

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	125.8	125.3	124.9	124.4
115°	142.4	141.9	141.5	141.0
117.5°	159.5	158.8	158.2	157.6
120°	176.0	175.3	174.7	174.1
122.5°	191.6	190.9	190.1	189.3
125°	207.2	206.5	205.8	205.1
127.5°	223.2	222.4	221.5	220.7
130°	238.2	237.1	236.1	235.1
132.5°	253.7	252.9	252.1	251.3
135°	268.0	267.1	266.3	265.4
137.5°	283.0	282.3	281.6	280.9
140°	296.8	296.1	295.4	294.7
142.5°	310.9	310.2	309.5	308.8
145°	323.8	323.3	322.7	322.2
147.5°	336.3	335.6	334.9	334.2
150°	347.9	347.4	347.0	346.5
152.5°	358.8	358.3	357.9	357.4
155°	369.1	368.8	368.6	368.4
157.5°	378.4	378.2	378.1	377.9
160°	386.8	386.6	386.5	386.3
162.5°	394.1	394.1	394.1	394.1
165°	400.5	400.6	400.7	400.8
167.5°	406.1	406.3	406.6	406.8
170°	410.7	410.9	411.2	411.4
172.5°	413.8	414.1	414.3	414.5
175°	416.3	416.5	416.8	417.0
177.5°	417.7	417.9	418.2	418.4
180°	417.7	417.7	417.7	417.7

TEST NUMBER: P998436

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.55	17.51	17.38	18.36	19.41	14.04	15.00	14.87	15.85	16.90
	3H	17.37	18.23	18.21	19.09	20.17	15.40	16.26	16.24	17.11	18.19
	4H	17.54	18.35	18.40	19.22	20.31	15.86	16.67	16.72	17.54	18.63
	6H	17.59	18.34	18.46	19.21	20.31	16.17	16.92	17.05	17.79	18.90
	8H	17.57	18.29	18.45	19.17	20.28	16.26	16.97	17.14	17.86	18.96
	12H	17.54	18.22	18.43	19.10	20.23	16.31	16.98	17.19	17.86	18.99
4H	2H	16.60	17.41	17.47	18.28	19.37	14.50	15.31	15.37	16.18	17.27
	3H	17.59	18.27	18.47	19.16	20.27	15.97	16.64	16.85	17.54	18.65
	4H	17.87	18.49	18.76	19.38	20.51	16.51	17.12	17.40	18.02	19.15
	6H	18.01	18.54	18.91	19.45	20.59	16.89	17.42	17.80	18.34	19.47
	8H	18.01	18.50	18.91	19.41	20.56	17.01	17.50	17.91	18.41	19.56
	12H	17.98	18.42	18.90	19.35	20.50	17.07	17.51	17.99	18.44	19.59
8H	4H	17.89	18.38	18.79	19.29	20.44	16.66	17.15	17.56	18.06	19.21
	6H	18.07	18.48	19.00	19.43	20.58	17.10	17.50	18.03	18.46	19.60
	8H	18.10	18.46	19.04	19.41	20.57	17.25	17.61	18.19	18.55	19.72
	12H	18.09	18.41	19.04	19.35	20.56	17.34	17.66	18.29	18.60	19.81
12H	4H	17.85	18.30	18.78	19.23	20.38	16.64	17.08	17.56	18.01	19.16
	6H	18.05	18.41	18.99	19.36	20.52	17.10	17.46	18.04	18.40	19.57
	8H	18.09	18.41	19.03	19.34	20.56	17.26	17.58	18.20	18.51	19.73