

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998439

Luminaire Tested: SA2XXDIP-B485D330UB27-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998439
REPORT IS A COMBINATION OF REPORTS P984182 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D330UB27-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3110.0 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998439

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P998439

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	97	92	88	84	90	86	82	78	73	70	68	62	60	58	51	50	48
2	88	80	73	67	81	74	68	63	63	59	55	53	50	47	44	42	39
3	80	69	61	55	74	65	57	52	55	50	45	47	42	39	39	36	33
4	73	61	53	46	67	57	49	43	49	43	38	41	37	33	34	31	28
5	67	54	46	39	61	51	43	37	43	37	33	37	32	28	31	27	24
6	61	49	40	34	57	45	38	32	39	33	28	33	28	25	28	24	21
7	57	44	35	29	52	41	33	28	35	29	25	30	25	22	25	21	18
8	53	40	32	26	49	37	30	25	32	26	22	28	23	19	23	19	16
9	49	36	28	23	45	34	27	22	29	24	19	25	21	17	21	18	15
10	46	33	26	21	42	31	24	20	27	21	17	23	19	15	20	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8052	8052	8052
5°	8089	7708	7665
10°	8035	7442	7332
15°	7921	7166	6992
20°	7777	6876	6670
25°	7636	6597	6376
30°	7440	6315	6085
35°	7240	6043	5873
40°	7027	5809	5661
45°	6827	5595	5476
50°	6612	5398	5294
55°	6384	5190	5108
60°	6108	4972	4913
65°	5819	4722	4689
70°	5491	4454	4447
75°	5074	4184	4219
80°	4415	3905	3984
85°	3743	3641	3779

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6827 cd/sqm

TEST NUMBER: P998439

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.2	1.6
10°-20°	138.3	4.4
20°-30°	209.6	6.7
30°-40°	255.2	8.2
40°-50°	274.6	8.8
50°-60°	266.6	8.6
60°-70°	232.9	7.5
70°-80°	179.2	5.8
80°-90°	121.2	3.9
90°-100°	108.6	3.5
100°-110°	142.6	4.6
110°-120°	180.5	5.8
120°-130°	207.1	6.7
130°-140°	216.8	7.0
140°-150°	205.0	6.6
150°-160°	170.7	5.5
160°-170°	113.2	3.6
170°-180°	39.6	1.3
0°-30°	396.1	12.7
0°-40°	651.3	20.9
0°-60°	1192.5	38.3
0°-90°	1725.8	55.5
90°-120°	431.7	13.9
90°-150°	1060.7	34.1
90°-180°	1384.0	44.5
0°-180°	3110.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	509	509	509	509	509	
5°	510	508	504	508	507	48
15°	487	488	488	495	494	137
25°	442	448	454	463	465	203
35°	381	394	408	424	429	238
45°	313	332	358	381	388	241
55°	240	266	304	331	341	214
65°	164	200	243	274	283	163
75°	91	132	179	211	220	96
85°	26	72	119	150	161	28
90°	8	55	110	138	148	6
95°	24	62	107	135	144	25
105°	80	102	141	168	176	84
115°	144	154	187	208	216	142
125°	207	210	232	251	258	185
135°	266	270	278	293	298	206
145°	322	325	327	332	334	201
155°	368	369	370	372	371	170
165°	401	400	400	403	401	113
175°	417	416	415	418	416	40
180°	418	418	418	418	418	

TEST NUMBER: P998439

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	508.7	508.7	508.7	508.7	508.7
2.5°	512.4	510.2	505.0	508.7	507.2
5°	510.2	508.0	503.5	508.0	507.2
7.5°	506.5	505.0	501.3	506.5	505.7
10°	502.1	500.6	498.4	504.3	503.5
12.5°	494.7	495.4	493.9	499.8	499.1
15°	486.6	488.1	488.1	494.7	493.9
17.5°	476.3	479.2	481.4	488.1	488.1
20°	465.9	469.6	472.6	480.7	480.7
22.5°	454.9	459.3	463.7	471.8	473.3
25°	442.3	447.5	454.1	463.0	465.2
27.5°	427.6	435.7	443.1	454.1	455.6
30°	412.9	422.4	432.0	443.8	446.0
32.5°	396.6	407.7	419.5	433.5	437.9
35°	381.2	393.7	407.7	423.9	429.1
37.5°	364.2	378.2	395.9	413.6	418.8
40°	347.2	363.5	383.4	402.5	409.2
42.5°	331.0	347.2	370.8	392.2	398.8
45°	312.6	332.5	358.3	381.2	388.5
47.5°	294.9	316.3	345.8	369.4	377.5
50°	276.5	299.3	332.5	357.6	365.7
52.5°	258.8	283.1	318.5	344.3	353.1
55°	239.6	266.1	304.5	331.0	340.6
57.5°	221.2	250.7	289.0	317.7	327.3
60°	201.3	233.0	275.0	303.0	313.3
62.5°	183.6	216.7	258.8	289.0	298.6
65°	163.7	199.8	243.3	273.5	283.1
67.5°	146.0	183.6	227.8	258.0	268.4
70°	126.8	165.1	210.9	242.6	251.4
72.5°	109.1	148.9	195.4	226.3	237.4
75°	90.7	132.0	179.1	210.9	220.4
77.5°	73.0	115.7	163.7	195.4	205.7
80°	55.3	100.3	148.2	179.1	189.5
82.5°	40.5	84.8	133.4	164.4	174.0
85°	26.5	72.2	119.4	150.4	160.7
87.5°	16.2	60.5	107.6	137.9	147.4
90°	7.8	54.7	109.6	138.4	147.7
92.5°	14.4	56.3	101.6	130.7	139.6
95°	24.2	62.4	107.4	135.4	143.5
97.5°	35.9	70.7	114.8	142.1	150.9
100°	50.0	80.0	122.3	149.6	157.4
102.5°	64.0	90.5	131.7	158.5	166.3
105°	79.5	101.9	140.9	167.5	175.6
107.5°	95.7	114.8	151.6	177.1	183.4
110°	110.4	127.3	163.4	187.0	194.1

TEST NUMBER: P998439

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	127.3	141.2	174.9	197.3	204.8
115°	143.9	154.2	186.6	208.5	215.5
117.5°	159.8	168.5	197.7	218.8	225.1
120°	176.3	182.1	208.8	229.4	236.5
122.5°	191.5	195.7	221.2	240.1	246.1
125°	206.6	209.8	232.4	251.2	257.5
127.5°	222.2	225.2	243.7	260.8	266.4
130°	236.6	240.4	255.2	272.2	276.7
132.5°	252.8	255.6	267.0	282.2	287.1
135°	266.1	270.0	278.1	293.3	298.1
137.5°	281.6	284.8	289.2	302.9	306.6
140°	295.4	297.9	301.1	312.9	315.9
142.5°	309.5	312.0	313.0	322.2	324.5
145°	322.2	324.6	326.8	331.5	333.8
147.5°	334.2	337.3	338.7	340.1	340.9
150°	346.5	348.6	350.0	351.1	350.0
152.5°	357.4	359.5	361.3	362.7	361.3
155°	368.4	369.4	370.5	372.2	371.2
157.5°	377.9	378.6	379.3	381.7	380.0
160°	386.3	387.0	387.4	389.5	388.1
162.5°	394.1	394.1	394.4	396.9	395.1
165°	400.8	400.4	400.4	402.9	401.1
167.5°	406.8	405.7	405.7	408.2	406.4
170°	411.4	410.3	409.9	412.4	410.3
172.5°	414.5	413.5	413.1	415.6	413.5
175°	417.0	415.9	415.2	417.7	415.6
177.5°	418.4	417.3	416.6	418.8	416.6
180°	417.7	417.7	417.7	417.7	417.7

TEST NUMBER: P998439

CATALOG NUMBER: SA2XXDIP-B485D330UB27-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.94	13.91	13.84	14.83	16.02	16.01	16.98	16.91	17.91	19.09
	3H	14.41	15.29	15.31	16.22	17.43	18.61	19.49	19.52	20.42	21.63
	4H	14.89	15.72	15.81	16.66	17.88	19.87	20.70	20.79	21.64	22.86
	6H	15.18	15.95	16.11	16.90	18.13	21.17	21.94	22.10	22.89	24.12
	8H	15.24	15.98	16.18	16.94	18.17	21.83	22.57	22.77	23.53	24.76
	12H	15.26	15.96	16.21	16.92	18.18	22.56	23.27	23.51	24.22	25.48
4H	2H	14.00	14.84	14.93	15.78	16.99	16.35	17.19	17.28	18.13	19.35
	3H	15.72	16.43	16.65	17.39	18.63	19.15	19.86	20.09	20.83	22.07
	4H	16.34	17.00	17.29	17.96	19.22	20.57	21.23	21.52	22.19	23.45
	6H	16.76	17.33	17.72	18.32	19.58	22.05	22.62	23.01	23.61	24.86
	8H	16.87	17.41	17.84	18.39	19.66	22.81	23.34	23.77	24.33	25.60
	12H	16.92	17.41	17.91	18.41	19.69	23.64	24.13	24.63	25.13	26.40
8H	4H	17.14	17.68	18.10	18.66	19.93	20.73	21.26	21.69	22.24	23.52
	6H	17.78	18.23	18.77	19.25	20.52	22.36	22.81	23.35	23.83	25.10
	8H	18.00	18.40	19.00	19.41	20.70	23.25	23.66	24.25	24.66	25.95
	12H	18.14	18.50	19.14	19.50	20.83	24.25	24.61	25.25	25.61	26.94
12H	4H	17.34	17.83	18.33	18.83	20.11	20.71	21.20	21.69	22.19	23.47
	6H	18.11	18.52	19.11	19.53	20.81	22.39	22.79	23.38	23.80	25.09
	8H	18.42	18.78	19.42	19.78	21.12	23.32	23.68	24.32	24.68	26.01