

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998460

Luminaire Tested: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998460
REPORT IS A COMBINATION OF REPORTS P984203 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3314.0 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	102	97	94	90	95	92	89	86	81	79	76	71	70	68	62	61	60
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	50	47	44
4	78	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34
6	67	55	47	41	63	52	45	40	47	41	37	42	37	34	37	34	31
7	62	50	42	36	58	47	40	35	43	37	33	38	34	30	34	30	27
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	32	28	25
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	23
10	51	39	31	27	48	37	30	26	33	28	24	30	26	22	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15318	15318	15318	15318
5°	15354	16332	15413	12993
10°	15176	17829	15272	10713
15°	14809	18805	15014	9023
20°	14577	17657	14577	7843
25°	14112	15170	14178	7013
30°	13348	11925	13604	6353
35°	12671	8246	12882	5813
40°	11892	6226	12028	5382
45°	10933	5116	11112	4916
50°	10103	4491	10120	4501
55°	9156	3826	9217	4049
60°	8148	3196	8260	3535
65°	7245	2599	7376	3018
70°	6344	2040	6505	2434
75°	5326	1481	5533	1765
80°	4160	938	4455	1047
85°	2726	473	2938	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15834 cd/sqm

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	2.8
10°-20°	268.3	8.1
20°-30°	389.3	11.7
30°-40°	410.4	12.4
40°-50°	363.2	11.0
50°-60°	290.0	8.8
60°-70°	197.0	5.9
70°-80°	100.8	3.0
80°-90°	25.0	0.8
90°-100°	26.1	0.8
100°-110°	82.9	2.5
110°-120°	141.8	4.3
120°-130°	186.4	5.6
130°-140°	209.3	6.3
140°-150°	205.2	6.2
150°-160°	172.1	5.2
160°-170°	114.2	3.4
170°-180°	39.9	1.2
0°-30°	749.8	22.6
0°-40°	1160.2	35.0
0°-60°	1813.4	54.7
0°-90°	2136.2	64.5
90°-120°	250.7	7.6
90°-150°	851.6	25.7
90°-180°	1178.0	35.5
0°-180°	3314.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	968	968	968	968	968	
5°	968	1081	972	860	968	92
15°	910	1328	922	637	910	257
25°	817	1107	821	512	817	374
35°	667	602	678	425	667	417
45°	501	363	509	349	501	388
55°	344	255	346	270	344	307
65°	204	157	208	182	204	203
75°	95	77	99	92	95	102
85°	19	20	21	15	19	23
90°	0	12	0	12	0	2
95°	18	22	18	22	18	21
105°	76	79	76	79	76	81
115°	142	142	142	142	142	141
125°	207	208	207	208	207	185
135°	268	271	268	271	268	207
145°	325	328	325	328	325	203
155°	372	374	372	374	372	171
165°	404	405	404	405	404	114
175°	421	419	421	419	421	40
180°	421	421	421	421	421	

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	972.9	975.1	978.8	979.6	987.0	993.0	999.7	999.7	1001.9	1001.2	995.2
5°	968.4	975.1	984.8	993.0	1006.4	1012.3	1021.2	1027.9	1033.9	1038.3	1037.6
7.5°	961.0	972.9	987.0	1002.6	1020.5	1030.9	1043.5	1055.4	1063.6	1071.1	1076.3
10°	948.3	968.4	987.8	1008.6	1031.6	1045.8	1060.7	1076.3	1088.9	1103.1	1116.4
12.5°	931.2	960.2	984.0	1011.6	1039.8	1055.4	1079.3	1091.2	1115.7	1151.4	1161.1
15°	909.7	949.1	971.4	1006.4	1043.5	1056.2	1088.9	1108.3	1158.8	1181.2	1207.9
17.5°	889.6	933.5	963.2	1003.4	1039.8	1064.4	1096.4	1135.8	1178.2	1210.2	1239.9
20°	873.2	915.6	951.3	995.9	1042.1	1073.3	1106.8	1154.4	1200.5	1233.2	1256.3
22.5°	836.0	890.3	932.0	981.8	1037.6	1080.7	1112.7	1164.8	1214.6	1234.7	1254.8
25°	817.4	864.3	912.6	969.2	1034.6	1085.9	1113.5	1171.5	1215.4	1222.8	1227.3
27.5°	783.2	836.0	892.6	957.3	1033.9	1077.0	1112.0	1164.8	1199.7	1194.5	1181.2
30°	740.8	805.5	868.0	937.9	1023.5	1070.3	1103.1	1151.4	1169.3	1142.5	1118.7
32.5°	709.6	770.6	839.7	920.8	1011.6	1056.2	1088.2	1126.1	1129.8	1081.5	1041.3
35°	667.2	734.9	813.0	898.5	991.5	1031.6	1061.4	1084.5	1066.6	998.9	951.3
37.5°	629.3	696.2	779.5	866.5	964.0	1003.4	1027.2	1030.9	987.0	927.5	857.6
40°	587.6	656.8	743.8	835.3	933.5	967.7	982.6	971.4	908.2	839.0	757.9
42.5°	545.9	614.4	708.1	801.8	894.8	923.8	929.7	899.3	821.9	740.8	647.1
45°	500.6	572.0	665.7	760.2	850.2	866.5	867.3	823.4	731.9	647.1	560.1
47.5°	463.4	529.6	622.6	717.0	792.9	804.0	799.6	749.0	649.3	554.1	478.3
50°	422.5	485.7	577.9	670.9	735.6	738.6	727.4	655.3	557.8	470.8	410.6
52.5°	378.6	442.6	527.4	616.6	674.6	670.2	648.6	571.2	479.7	407.6	361.5
55°	343.6	400.2	479.7	566.8	607.7	595.0	571.2	492.4	420.2	359.3	319.1
57.5°	305.0	354.8	432.9	508.8	532.6	520.7	496.9	423.2	356.3	310.2	283.4
60°	268.5	313.9	382.3	445.5	464.1	451.5	424.0	357.8	309.4	270.7	250.7
62.5°	235.0	274.5	331.7	389.8	397.2	384.5	360.7	307.2	265.5	235.0	220.2
65°	203.8	241.0	287.1	331.0	337.7	324.3	299.8	261.1	226.1	206.8	192.6
67.5°	173.3	203.1	244.0	275.9	279.7	267.0	246.9	215.7	194.1	173.3	162.9
70°	146.5	168.8	200.8	226.9	228.3	216.4	206.0	177.8	161.4	146.5	138.3
72.5°	120.5	136.1	160.7	180.0	180.7	173.3	163.6	145.8	131.7	121.2	113.1
75°	95.2	108.6	123.5	140.6	139.8	133.9	126.4	115.3	103.4	96.7	93.0
77.5°	72.9	81.1	93.0	104.1	104.1	101.2	96.7	88.5	81.1	74.4	70.7
80°	52.1	57.3	66.9	70.7	72.1	71.4	67.7	61.7	58.8	53.6	52.1
82.5°	33.5	37.2	41.7	45.4	47.6	46.1	45.4	42.4	37.9	36.4	35.0
85°	19.3	20.8	23.1	25.3	26.0	25.3	26.8	24.5	22.3	22.3	21.6
87.5°	8.2	8.9	10.4	10.4	11.2	11.2	10.4	11.2	11.2	10.4	9.7
90°	0.4	1.3	2.3	3.2	4.1	4.6	5.5	7.2	8.9	10.7	12.4
92.5°	7.8	8.4	9.1	9.7	10.4	10.7	10.7	10.8	10.9	10.9	11.0
95°	18.5	19.3	20.1	20.8	21.6	22.0	22.1	22.3	22.4	22.6	22.8
97.5°	30.9	31.6	32.3	33.0	33.7	34.1	34.3	34.6	34.9	35.3	35.6
100°	45.1	45.7	46.4	47.0	47.7	48.0	48.1	48.4	48.6	48.9	49.1
102.5°	60.1	60.6	61.0	61.5	62.0	62.2	62.4	62.7	63.0	63.3	63.6
105°	76.4	76.6	76.9	77.1	77.4	77.5	77.6	77.7	77.9	78.0	78.2
107.5°	92.8	93.1	93.4	93.7	94.0	94.2	94.2	94.2	94.2	94.2	94.2
110°	108.4	108.9	109.4	109.9	110.4	110.6	110.6	110.6	110.6	110.6	110.6

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	125.5	126.0	126.4	126.9	127.4	127.6	127.6	127.5	127.4	127.4	127.3
115°	142.2	142.7	143.1	143.6	144.1	144.3	144.2	144.1	143.9	143.8	143.6
117.5°	158.9	159.5	160.2	160.8	161.5	161.8	161.6	161.2	160.8	160.4	160.0
120°	175.6	176.2	176.9	177.5	178.2	178.5	178.2	177.5	176.9	176.2	175.6
122.5°	190.9	191.7	192.5	193.3	194.1	194.5	194.3	193.9	193.5	193.1	192.7
125°	206.9	207.6	208.3	209.0	209.7	210.1	210.0	209.7	209.5	209.2	209.0
127.5°	222.5	223.4	224.3	225.2	226.1	226.5	226.3	226.0	225.7	225.3	225.0
130°	237.1	238.1	239.1	240.2	241.2	241.7	241.6	241.5	241.3	241.2	241.0
132.5°	253.5	254.3	255.1	255.8	256.6	257.0	257.0	257.1	257.2	257.3	257.4
135°	267.7	268.6	269.4	270.3	271.2	271.6	271.7	271.8	272.0	272.1	272.3
137.5°	283.3	284.0	284.7	285.4	286.1	286.5	286.6	286.7	286.9	287.0	287.2
140°	297.2	297.9	298.6	299.3	300.0	300.4	300.6	301.0	301.4	301.8	302.2
142.5°	311.4	312.1	312.8	313.5	314.2	314.6	314.7	315.0	315.2	315.5	315.7
145°	324.9	325.5	326.0	326.6	327.1	327.4	327.6	328.1	328.6	329.1	329.6
147.5°	337.0	337.7	338.4	339.1	339.8	340.2	340.4	340.7	341.0	341.3	341.6
150°	349.5	350.0	350.4	350.9	351.4	351.6	351.8	352.1	352.4	352.7	353.0
152.5°	360.5	361.0	361.4	361.9	362.4	362.6	362.8	363.2	363.6	364.0	364.4
155°	371.5	371.7	372.0	372.2	372.5	372.6	372.7	372.9	373.2	373.4	373.6
157.5°	381.1	381.3	381.4	381.6	381.7	381.8	381.9	382.0	382.2	382.3	382.5
160°	389.6	389.8	389.9	390.1	390.2	390.3	390.3	390.4	390.5	390.6	390.7
162.5°	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.6	397.7	397.7	397.8
165°	404.2	404.1	404.1	404.0	403.9	403.9	403.9	403.9	403.9	403.9	403.9
167.5°	410.3	410.1	409.8	409.6	409.3	409.2	409.2	409.2	409.2	409.2	409.2
170°	414.9	414.7	414.4	414.2	413.9	413.8	413.8	413.7	413.6	413.6	413.5
172.5°	418.1	417.9	417.6	417.4	417.1	417.0	417.0	416.9	416.8	416.8	416.7
175°	420.6	420.4	420.1	419.9	419.6	419.5	419.4	419.3	419.1	419.0	418.8
177.5°	422.0	421.8	421.5	421.3	421.0	420.9	420.8	420.7	420.5	420.4	420.2
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1005.6	1006.4	1007.8	1015.3	1019.0	1019.7	1016.8	1023.5	1025.7	1023.5	1022.0
5°	1053.2	1057.7	1066.6	1076.3	1075.5	1076.3	1080.7	1085.2	1086.7	1080.7	1083.0
7.5°	1094.9	1103.8	1113.5	1128.3	1128.3	1135.8	1138.8	1142.5	1151.4	1146.9	1145.4
10°	1142.5	1154.4	1172.2	1196.0	1196.8	1204.2	1211.6	1223.5	1227.3	1224.3	1225.8
12.5°	1202.0	1225.0	1226.5	1252.6	1264.5	1265.9	1277.8	1275.6	1283.1	1283.1	1295.7
15°	1228.0	1263.7	1283.8	1309.1	1316.5	1307.6	1317.3	1327.7	1328.4	1328.4	1327.7
17.5°	1274.9	1289.0	1309.1	1322.5	1325.4	1325.4	1326.2	1330.7	1327.7	1321.7	1326.2
20°	1284.5	1290.5	1297.9	1296.4	1297.9	1290.5	1283.1	1275.6	1276.4	1272.6	1283.8
22.5°	1266.7	1265.2	1248.1	1236.9	1236.9	1222.1	1207.9	1201.2	1194.5	1196.8	1200.5
25°	1222.1	1199.0	1178.2	1161.8	1158.1	1134.3	1115.0	1109.0	1097.8	1106.8	1108.3
27.5°	1150.7	1124.6	1091.2	1077.0	1057.7	1048.0	1034.6	1016.8	993.7	1007.1	1004.9
30°	1074.0	1035.4	1007.8	973.6	943.1	940.9	915.6	885.9	874.0	874.0	880.7
32.5°	988.5	937.2	897.0	848.7	818.9	806.3	775.8	746.0	752.7	730.4	738.6
35°	888.8	821.2	770.6	723.7	701.4	686.5	647.1	630.7	612.9	602.5	621.8
37.5°	793.6	715.5	650.8	599.5	591.3	564.5	537.8	527.4	516.9	521.4	520.7
40°	677.6	608.4	550.4	510.2	496.1	483.5	465.6	453.0	446.3	450.0	450.7
42.5°	572.7	514.7	471.6	443.3	431.4	422.5	413.6	403.1	400.9	400.9	403.9
45°	491.7	444.0	415.0	392.0	385.3	378.6	371.9	367.4	365.9	363.0	365.2
47.5°	426.9	389.0	371.2	354.0	346.6	345.1	339.2	336.9	334.0	333.2	334.0
50°	372.6	348.8	332.5	322.8	317.6	315.4	312.4	307.9	306.4	310.2	308.7
52.5°	334.7	312.4	303.5	293.8	290.8	287.8	283.4	284.1	283.4	281.9	281.9
55°	296.8	282.6	273.7	266.3	265.5	262.6	258.8	257.4	256.6	255.1	257.4
57.5°	266.3	255.1	246.9	240.2	237.3	237.3	233.6	230.6	230.6	229.8	230.6
60°	235.8	224.6	219.4	212.7	210.5	209.8	207.5	206.0	203.8	203.8	203.8
62.5°	207.5	198.6	192.6	186.7	187.4	183.7	180.7	179.3	179.3	180.0	180.0
65°	180.7	174.8	167.4	162.1	160.7	159.9	158.4	157.7	155.5	156.9	156.9
67.5°	156.2	148.0	143.6	141.3	139.1	138.3	136.9	135.4	134.6	133.9	135.4
70°	131.7	125.0	121.2	119.8	117.5	116.8	116.0	113.8	114.5	115.3	116.0
72.5°	109.3	103.4	102.6	98.2	98.2	98.2	95.2	96.7	95.9	94.5	95.9
75°	86.3	83.3	81.8	79.6	80.3	79.6	78.8	76.6	76.6	77.4	78.1
77.5°	68.4	65.5	64.7	62.5	61.0	62.5	61.0	60.2	60.2	61.0	61.0
80°	50.6	49.1	46.9	46.9	46.9	46.1	46.1	46.1	45.4	44.6	45.4
82.5°	33.5	33.5	32.7	32.0	32.7	31.2	32.0	32.0	32.0	32.0	32.0
85°	21.6	20.8	20.8	20.1	20.1	20.1	20.8	19.3	19.3	20.1	20.1
87.5°	9.7	9.7	9.7	10.4	9.7	9.7	9.7	10.4	9.7	9.7	9.7
90°	12.2	12.1	11.9	11.8	11.7	11.7	11.8	11.9	12.0	12.1	12.0
92.5°	11.1	11.2	11.3	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
95°	22.8	22.8	22.8	22.8	22.8	22.7	22.5	22.4	22.2	22.0	22.2
97.5°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6
100°	49.1	49.1	49.1	49.1	49.1	49.1	49.0	48.9	48.8	48.7	48.8
102.5°	63.7	63.8	63.9	64.0	64.0	64.0	63.9	63.8	63.7	63.6	63.7
105°	78.4	78.5	78.7	78.8	78.9	78.9	78.9	78.9	78.9	78.9	78.9
107.5°	94.3	94.4	94.5	94.6	94.6	94.4	94.0	93.6	93.2	92.8	93.2
110°	110.6	110.6	110.6	110.6	110.6	110.5	110.2	110.0	109.7	109.5	109.7

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	127.1	126.8	126.6	126.3	126.2	126.1	126.0	125.8	125.7	125.5	125.7
115°	143.5	143.5	143.4	143.3	143.3	143.2	142.9	142.7	142.4	142.2	142.4
117.5°	159.8	159.5	159.3	159.0	158.9	158.8	158.5	158.3	158.0	157.8	158.0
120°	175.6	175.6	175.6	175.6	175.6	175.5	175.3	175.0	174.8	174.6	174.8
122.5°	192.5	192.2	192.0	191.7	191.6	191.5	191.4	191.2	191.1	190.9	191.1
125°	208.8	208.6	208.3	208.1	208.0	208.0	207.9	207.8	207.7	207.6	207.7
127.5°	224.7	224.4	224.1	223.8	223.6	223.5	223.2	223.0	222.7	222.5	222.7
130°	240.8	240.7	240.5	240.4	240.3	240.1	239.8	239.5	239.2	238.9	239.2
132.5°	257.0	256.6	256.2	255.8	255.6	255.5	255.2	255.0	254.7	254.5	254.7
135°	272.2	272.2	272.1	272.0	272.0	271.9	271.6	271.4	271.1	270.9	271.1
137.5°	287.1	287.1	287.0	286.9	286.9	286.7	286.4	286.1	285.8	285.5	285.8
140°	302.2	302.2	302.2	302.2	302.2	302.0	301.7	301.4	301.1	300.8	301.1
142.5°	315.8	315.8	315.9	316.0	316.0	315.8	315.5	315.2	314.9	314.6	314.9
145°	329.7	329.7	329.8	329.9	329.9	329.7	329.4	329.1	328.8	328.5	328.8
147.5°	341.8	342.0	342.1	342.3	342.4	342.2	341.9	341.6	341.2	340.9	341.2
150°	353.2	353.5	353.7	354.0	354.1	354.0	353.7	353.5	353.2	353.0	353.2
152.5°	364.7	365.0	365.3	365.6	365.8	365.6	365.3	365.0	364.7	364.4	364.7
155°	374.0	374.4	374.8	375.2	375.4	375.3	375.0	374.8	374.5	374.3	374.5
157.5°	383.1	383.6	384.2	384.7	385.0	384.8	384.4	384.0	383.6	383.2	383.6
160°	391.2	391.6	392.1	392.6	392.8	392.6	392.3	392.0	391.7	391.4	391.7
162.5°	398.4	398.9	399.5	400.0	400.3	400.1	399.7	399.3	398.9	398.5	398.9
165°	404.4	405.0	405.5	406.0	406.3	406.1	405.7	405.4	405.0	404.6	405.0
167.5°	409.8	410.3	410.9	411.4	411.7	411.5	411.1	410.7	410.3	409.9	410.3
170°	414.0	414.6	415.1	415.6	415.9	415.7	415.2	414.7	414.3	413.8	414.3
172.5°	417.2	417.8	418.3	418.8	419.1	418.9	418.4	417.9	417.5	417.0	417.5
175°	419.4	419.9	420.5	421.0	421.3	421.1	420.6	420.1	419.6	419.1	419.6
177.5°	420.7	421.1	421.6	422.1	422.3	422.1	421.6	421.1	420.7	420.2	420.7
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1025.7	1020.5	1016.0	1016.8	1020.5	1017.5	1010.1	1000.4	996.7	992.2	996.7
5°	1087.4	1083.0	1074.0	1074.8	1072.6	1069.6	1057.7	1042.8	1042.8	1030.9	1029.4
7.5°	1148.4	1141.7	1135.8	1134.3	1126.1	1120.2	1109.7	1088.9	1080.7	1066.6	1058.4
10°	1216.9	1211.6	1205.0	1196.8	1192.3	1181.9	1164.8	1134.3	1119.4	1100.1	1085.9
12.5°	1286.0	1285.3	1270.4	1254.0	1253.3	1236.9	1225.0	1184.1	1164.0	1138.0	1104.5
15°	1329.9	1326.2	1318.0	1309.8	1312.1	1294.2	1267.4	1219.1	1205.7	1174.5	1138.8
17.5°	1329.2	1329.2	1326.9	1325.4	1323.2	1318.0	1303.1	1271.2	1249.6	1210.2	1176.7
20°	1286.8	1296.4	1298.7	1297.9	1305.4	1309.1	1308.3	1288.3	1271.2	1236.2	1202.0
22.5°	1202.0	1224.3	1234.0	1239.9	1255.5	1263.7	1283.1	1275.6	1271.2	1245.1	1216.1
25°	1123.1	1130.6	1159.6	1161.1	1182.6	1202.7	1222.1	1234.7	1251.1	1241.4	1216.9
27.5°	1021.2	1038.3	1059.2	1074.8	1079.3	1120.2	1152.1	1175.9	1213.1	1216.1	1207.9
30°	905.9	914.1	948.3	969.2	993.0	1022.7	1068.8	1109.7	1143.2	1173.7	1184.1
32.5°	765.4	798.8	818.9	844.2	865.0	917.8	974.4	1027.2	1065.9	1117.2	1139.5
35°	636.7	662.7	696.9	707.4	745.3	789.9	863.5	931.2	990.0	1042.1	1087.4
37.5°	530.3	551.2	587.6	604.0	626.3	683.6	745.3	829.3	900.0	964.0	1020.5
40°	457.4	473.1	500.6	505.8	524.4	576.4	626.3	705.1	798.8	885.1	946.9
42.5°	407.6	415.0	433.6	440.3	452.2	487.2	531.8	606.2	693.2	782.5	869.5
45°	371.9	377.1	388.3	394.2	409.1	424.7	461.2	520.7	589.1	679.1	772.8
47.5°	339.9	346.6	351.1	354.8	363.0	380.1	403.9	447.8	513.2	595.8	686.5
50°	313.1	315.4	323.6	324.3	329.5	340.7	363.0	389.8	441.8	508.8	596.5
52.5°	286.4	288.6	293.8	299.0	301.2	310.2	325.0	347.4	386.0	438.8	516.9
55°	259.6	262.6	267.8	271.5	273.7	281.2	290.1	311.7	342.1	379.3	443.3
57.5°	232.8	239.5	241.0	243.2	246.9	255.1	263.3	275.9	299.8	334.0	380.8
60°	207.5	209.8	215.0	217.2	220.9	225.4	235.8	245.5	262.6	289.3	331.7
62.5°	181.5	186.7	188.9	191.2	194.1	199.3	206.0	216.4	231.3	252.9	286.4
65°	159.2	159.9	164.4	167.4	170.3	174.0	180.7	190.4	199.3	219.4	244.0
67.5°	137.6	139.1	140.6	143.6	147.3	151.0	156.9	162.1	173.3	186.7	206.0
70°	116.8	116.8	120.5	122.7	122.0	126.4	130.9	136.9	145.0	157.7	173.3
72.5°	98.2	97.4	100.4	101.2	102.6	105.6	108.6	114.5	119.0	128.7	140.6
75°	78.1	79.6	81.1	81.1	83.3	85.5	88.5	91.5	96.7	102.6	111.6
77.5°	61.7	61.7	63.2	64.0	66.2	65.5	68.4	71.4	75.1	80.3	87.0
80°	45.4	46.9	46.9	46.9	47.6	48.3	51.3	53.6	55.8	59.5	62.5
82.5°	32.0	32.0	33.5	33.5	33.5	35.0	35.0	35.7	37.2	39.4	41.7
85°	20.1	20.1	20.1	20.8	20.1	20.8	22.3	21.6	22.3	23.8	23.8
87.5°	9.7	9.7	9.7	9.7	9.7	10.4	9.7	10.4	11.2	11.2	11.2
90°	11.9	11.8	11.7	11.7	11.8	11.9	12.1	12.2	12.4	10.7	8.9
92.5°	11.4	11.4	11.4	11.4	11.4	11.3	11.2	11.1	11.0	10.9	10.9
95°	22.4	22.5	22.7	22.8	22.8	22.8	22.8	22.8	22.8	22.6	22.4
97.5°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.3	34.9
100°	48.9	49.0	49.1	49.1	49.1	49.1	49.1	49.1	49.1	48.9	48.6
102.5°	63.8	63.9	64.0	64.0	64.0	63.9	63.8	63.7	63.6	63.3	63.0
105°	78.9	78.9	78.9	78.9	78.8	78.7	78.5	78.4	78.2	78.0	77.9
107.5°	93.6	94.0	94.4	94.6	94.6	94.5	94.4	94.3	94.2	94.2	94.2
110°	110.0	110.2	110.5	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	125.8	126.0	126.1	126.2	126.3	126.6	126.8	127.1	127.3	127.4	127.4
115°	142.7	142.9	143.2	143.3	143.3	143.4	143.5	143.5	143.6	143.8	143.9
117.5°	158.3	158.5	158.8	158.9	159.0	159.3	159.5	159.8	160.0	160.4	160.8
120°	175.0	175.3	175.5	175.6	175.6	175.6	175.6	175.6	175.6	176.2	176.9
122.5°	191.2	191.4	191.5	191.6	191.7	192.0	192.2	192.5	192.7	193.1	193.5
125°	207.8	207.9	208.0	208.0	208.1	208.3	208.6	208.8	209.0	209.2	209.5
127.5°	223.0	223.2	223.5	223.6	223.8	224.1	224.4	224.7	225.0	225.3	225.7
130°	239.5	239.8	240.1	240.3	240.4	240.5	240.7	240.8	241.0	241.2	241.3
132.5°	255.0	255.2	255.5	255.6	255.8	256.2	256.6	257.0	257.4	257.3	257.2
135°	271.4	271.6	271.9	272.0	272.0	272.1	272.2	272.2	272.3	272.1	272.0
137.5°	286.1	286.4	286.7	286.9	286.9	287.0	287.1	287.1	287.2	287.0	286.9
140°	301.4	301.7	302.0	302.2	302.2	302.2	302.2	302.2	302.2	301.8	301.4
142.5°	315.2	315.5	315.8	316.0	316.0	315.9	315.8	315.8	315.7	315.5	315.2
145°	329.1	329.4	329.7	329.9	329.9	329.8	329.7	329.7	329.6	329.1	328.6
147.5°	341.6	341.9	342.2	342.4	342.3	342.1	342.0	341.8	341.6	341.3	341.0
150°	353.5	353.7	354.0	354.1	354.0	353.7	353.5	353.2	353.0	352.7	352.4
152.5°	365.0	365.3	365.6	365.8	365.6	365.3	365.0	364.7	364.4	364.0	363.6
155°	374.8	375.0	375.3	375.4	375.2	374.8	374.4	374.0	373.6	373.4	373.2
157.5°	384.0	384.4	384.8	385.0	384.7	384.2	383.6	383.1	382.5	382.3	382.2
160°	392.0	392.3	392.6	392.8	392.6	392.1	391.6	391.2	390.7	390.6	390.5
162.5°	399.3	399.7	400.1	400.3	400.0	399.5	398.9	398.4	397.8	397.7	397.7
165°	405.4	405.7	406.1	406.3	406.0	405.5	405.0	404.4	403.9	403.9	403.9
167.5°	410.7	411.1	411.5	411.7	411.4	410.9	410.3	409.8	409.2	409.2	409.2
170°	414.7	415.2	415.7	415.9	415.6	415.1	414.6	414.0	413.5	413.6	413.6
172.5°	417.9	418.4	418.9	419.1	418.8	418.3	417.8	417.2	416.7	416.8	416.8
175°	420.1	420.6	421.1	421.3	421.0	420.5	419.9	419.4	418.8	419.0	419.1
177.5°	421.1	421.6	422.1	422.3	422.1	421.6	421.1	420.7	420.2	420.4	420.5
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	993.0	989.3	987.0	988.5	984.0	972.9	972.9	976.6	972.1	967.7	961.0
5°	1020.5	1013.1	1008.6	1007.8	997.4	979.6	975.9	972.1	962.5	952.1	940.9
7.5°	1047.3	1033.9	1026.4	1021.2	1006.4	983.3	973.6	965.5	949.8	934.2	920.1
10°	1069.6	1050.2	1041.3	1033.1	1013.8	984.8	969.2	954.3	934.2	914.1	896.3
12.5°	1087.4	1065.1	1054.0	1042.1	1018.3	980.3	961.0	937.2	917.1	890.3	872.5
15°	1117.2	1071.1	1060.7	1049.5	1025.0	972.9	949.1	922.3	894.8	859.1	839.7
17.5°	1141.0	1079.3	1078.5	1054.7	1022.7	969.9	933.5	898.5	868.8	833.1	802.6
20°	1155.1	1091.9	1080.0	1055.4	1015.3	949.8	911.9	873.2	841.2	798.1	767.6
22.5°	1167.0	1109.7	1078.5	1048.8	999.7	943.1	887.4	850.9	807.0	760.2	731.2
25°	1171.5	1113.5	1080.7	1046.5	988.5	923.8	860.6	821.2	772.1	729.7	690.2
27.5°	1172.2	1112.7	1072.6	1036.9	972.9	898.5	833.8	792.1	737.8	688.8	649.3
30°	1164.8	1104.5	1068.1	1029.4	958.0	875.5	801.1	755.0	696.9	647.8	606.9
32.5°	1142.5	1088.2	1058.4	1016.0	938.7	843.5	769.8	718.5	657.5	609.2	569.7
35°	1105.3	1068.1	1035.4	995.9	913.4	813.7	738.6	678.3	616.6	570.5	533.3
37.5°	1059.2	1039.1	1008.6	969.9	884.4	786.9	703.6	636.7	575.0	530.3	493.9
40°	996.7	1001.9	972.1	937.2	850.2	750.5	658.3	594.3	536.3	494.6	458.9
42.5°	929.0	950.6	933.5	900.0	812.2	710.3	624.8	554.1	497.6	454.5	424.7
45°	856.1	893.3	882.9	858.3	772.8	667.9	577.2	508.8	458.9	417.3	391.2
47.5°	776.5	829.3	829.3	811.5	728.9	625.5	536.3	466.4	417.3	387.5	362.2
50°	695.5	755.0	764.6	752.7	679.8	577.2	486.4	423.2	380.8	351.8	333.2
52.5°	610.7	679.8	697.7	691.7	627.8	531.1	445.5	383.8	345.1	319.8	303.5
55°	529.6	609.9	629.3	631.5	572.0	480.5	400.2	345.9	308.7	291.6	277.4
57.5°	453.0	530.3	551.9	555.6	515.5	434.4	357.8	310.2	276.7	262.6	251.4
60°	387.5	452.2	480.5	488.7	453.7	380.8	318.3	272.2	246.9	233.6	223.1
62.5°	334.0	386.0	415.8	418.0	402.4	334.0	277.4	238.8	217.2	205.3	200.1
65°	281.9	328.8	346.6	355.5	342.9	289.3	239.5	207.5	190.4	180.0	174.8
67.5°	240.2	270.0	284.9	296.8	284.1	244.0	203.8	177.8	165.1	154.7	151.7
70°	197.1	221.7	232.8	244.7	233.6	203.1	174.0	150.2	139.1	130.9	127.2
72.5°	157.7	177.0	187.4	194.9	188.2	162.9	139.1	122.7	114.5	108.6	106.4
75°	125.0	138.3	144.3	149.5	146.5	127.2	112.3	98.9	91.5	86.3	84.8
77.5°	95.2	104.9	111.6	113.1	109.3	96.7	84.0	75.9	69.9	66.9	65.5
80°	67.7	73.6	77.4	79.6	75.9	70.7	61.7	55.8	50.6	46.9	46.1
82.5°	45.4	48.3	51.3	50.6	49.1	44.6	39.4	36.4	34.2	31.2	31.2
85°	26.0	26.8	28.3	29.0	28.3	25.3	22.3	20.8	19.3	17.1	17.1
87.5°	11.2	11.9	11.9	12.6	11.2	11.2	9.7	8.2	8.2	7.4	6.7
90°	7.2	5.5	4.6	4.1	3.2	2.3	1.3	0.4	1.3	2.3	3.2
92.5°	10.8	10.7	10.7	10.4	9.7	9.1	8.4	7.8	8.4	9.1	9.7
95°	22.3	22.1	22.0	21.6	20.8	20.1	19.3	18.5	19.3	20.1	20.8
97.5°	34.6	34.3	34.1	33.7	33.0	32.3	31.6	30.9	31.6	32.3	33.0
100°	48.4	48.1	48.0	47.7	47.0	46.4	45.7	45.1	45.7	46.4	47.0
102.5°	62.7	62.4	62.2	62.0	61.5	61.0	60.6	60.1	60.6	61.0	61.5
105°	77.7	77.6	77.5	77.4	77.1	76.9	76.6	76.4	76.6	76.9	77.1
107.5°	94.2	94.2	94.2	94.0	93.7	93.4	93.1	92.8	93.1	93.4	93.7
110°	110.6	110.6	110.6	110.4	109.9	109.4	108.9	108.4	108.9	109.4	109.9

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	127.5	127.6	127.6	127.4	126.9	126.4	126.0	125.5	126.0	126.4	126.9
115°	144.1	144.2	144.3	144.1	143.6	143.1	142.7	142.2	142.7	143.1	143.6
117.5°	161.2	161.6	161.8	161.5	160.8	160.2	159.5	158.9	159.5	160.2	160.8
120°	177.5	178.2	178.5	178.2	177.5	176.9	176.2	175.6	176.2	176.9	177.5
122.5°	193.9	194.3	194.5	194.1	193.3	192.5	191.7	190.9	191.7	192.5	193.3
125°	209.7	210.0	210.1	209.7	209.0	208.3	207.6	206.9	207.6	208.3	209.0
127.5°	226.0	226.3	226.5	226.1	225.2	224.3	223.4	222.5	223.4	224.3	225.2
130°	241.5	241.6	241.7	241.2	240.2	239.1	238.1	237.1	238.1	239.1	240.2
132.5°	257.1	257.0	257.0	256.6	255.8	255.1	254.3	253.5	254.3	255.1	255.8
135°	271.8	271.7	271.6	271.2	270.3	269.4	268.6	267.7	268.6	269.4	270.3
137.5°	286.7	286.6	286.5	286.1	285.4	284.7	284.0	283.3	284.0	284.7	285.4
140°	301.0	300.6	300.4	300.0	299.3	298.6	297.9	297.2	297.9	298.6	299.3
142.5°	315.0	314.7	314.6	314.2	313.5	312.8	312.1	311.4	312.1	312.8	313.5
145°	328.1	327.6	327.4	327.1	326.6	326.0	325.5	324.9	325.5	326.0	326.6
147.5°	340.7	340.4	340.2	339.8	339.1	338.4	337.7	337.0	337.7	338.4	339.1
150°	352.1	351.8	351.6	351.4	350.9	350.4	350.0	349.5	350.0	350.4	350.9
152.5°	363.2	362.8	362.6	362.4	361.9	361.4	361.0	360.5	361.0	361.4	361.9
155°	372.9	372.7	372.6	372.5	372.2	372.0	371.7	371.5	371.7	372.0	372.2
157.5°	382.0	381.9	381.8	381.7	381.6	381.4	381.3	381.1	381.3	381.4	381.6
160°	390.4	390.3	390.3	390.2	390.1	389.9	389.8	389.6	389.8	389.9	390.1
162.5°	397.6	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5	397.5
165°	403.9	403.9	403.9	403.9	404.0	404.1	404.1	404.2	404.1	404.1	404.0
167.5°	409.2	409.2	409.2	409.3	409.6	409.8	410.1	410.3	410.1	409.8	409.6
170°	413.7	413.8	413.8	413.9	414.2	414.4	414.7	414.9	414.7	414.4	414.2
172.5°	416.9	417.0	417.0	417.1	417.4	417.6	417.9	418.1	417.9	417.6	417.4
175°	419.3	419.4	419.5	419.6	419.9	420.1	420.4	420.6	420.4	420.1	419.9
177.5°	420.7	420.8	420.9	421.0	421.3	421.5	421.8	422.0	421.8	421.5	421.3
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	957.3	961.0	960.2	952.8	944.6	937.9	925.3	926.8	922.3	923.1	927.5
5°	933.5	933.5	930.5	920.1	906.7	899.3	885.1	881.4	872.5	871.7	871.0
7.5°	908.2	904.5	900.7	885.9	869.5	857.6	838.3	833.8	824.9	818.9	815.9
10°	878.4	873.2	865.8	848.7	828.6	813.7	793.6	787.7	770.6	763.1	758.7
12.5°	845.7	842.7	830.8	816.7	784.0	767.6	738.6	744.5	727.4	712.6	710.3
15°	813.0	801.8	795.1	772.1	732.6	725.2	702.1	690.2	674.6	662.7	662.7
17.5°	781.0	763.9	749.0	724.5	695.5	674.6	657.5	651.6	632.2	620.3	618.1
20°	738.6	719.3	715.5	680.6	660.5	637.4	621.1	606.2	592.1	586.9	583.1
22.5°	698.4	676.1	670.2	640.4	620.3	597.3	580.9	570.5	560.1	556.4	549.7
25°	655.3	641.9	633.0	601.0	578.7	557.1	545.9	538.5	528.8	528.1	523.6
27.5°	613.6	601.0	592.1	561.6	545.2	525.1	516.2	508.0	502.8	500.6	498.3
30°	577.9	563.8	553.4	531.1	511.0	494.6	487.2	482.0	479.0	475.3	474.5
32.5°	538.5	530.3	516.2	499.1	483.5	467.8	463.4	459.7	455.2	453.7	453.0
35°	505.0	493.9	485.0	465.6	458.9	445.5	440.3	437.4	431.4	429.9	428.4
37.5°	472.3	461.9	452.2	440.3	427.7	420.2	417.3	412.8	409.8	410.6	409.1
40°	439.6	431.4	424.0	411.3	403.9	400.2	394.2	389.8	388.3	389.0	388.3
42.5°	407.6	400.2	395.7	386.0	378.6	374.9	371.2	366.7	368.9	368.9	371.2
45°	378.6	371.9	368.9	361.5	357.0	351.1	347.4	346.6	349.6	348.8	348.8
47.5°	348.8	346.6	342.9	336.2	330.2	326.5	325.8	325.8	328.8	330.2	329.5
50°	325.8	321.3	316.9	311.7	307.2	305.7	303.5	305.0	307.9	307.9	309.4
52.5°	296.8	293.8	292.3	287.8	284.9	284.9	284.9	285.6	287.8	290.1	289.3
55°	271.5	269.3	267.8	265.5	261.8	262.6	261.8	263.3	265.5	267.8	269.3
57.5°	244.7	244.0	242.5	238.8	238.8	238.0	240.2	241.0	244.7	246.2	248.4
60°	220.9	218.7	218.7	215.7	215.7	215.7	217.9	220.2	223.1	223.9	225.4
62.5°	195.6	195.6	194.9	192.6	192.6	194.9	195.6	198.6	200.1	200.1	202.3
65°	171.8	171.1	170.3	171.1	171.8	171.8	174.0	175.5	177.0	177.8	178.5
67.5°	148.0	147.3	148.8	148.0	149.5	152.5	151.7	154.0	156.2	156.2	156.9
70°	125.7	127.2	126.4	127.9	127.2	128.7	130.9	131.7	131.7	132.4	134.6
72.5°	104.9	104.9	104.9	104.1	104.9	106.4	107.9	108.6	110.1	110.8	113.1
75°	84.8	84.8	83.3	84.8	84.8	86.3	87.8	87.8	87.8	89.3	91.5
77.5°	64.0	64.7	64.0	65.5	65.5	66.2	67.7	66.9	68.4	69.2	69.9
80°	46.9	46.1	46.1	46.1	46.9	46.9	48.3	49.1	49.1	51.3	49.8
82.5°	29.8	30.5	29.8	30.5	30.5	31.2	30.5	31.2	32.0	33.5	32.7
85°	17.1	16.4	16.4	17.1	16.4	16.4	17.1	16.4	17.1	16.4	17.1
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	4.1	4.6	5.5	7.2	8.9	10.7	12.4	12.2	12.1	11.9	11.8
92.5°	10.4	10.7	10.7	10.8	10.9	10.9	11.0	11.1	11.2	11.3	11.4
95°	21.6	22.0	22.1	22.3	22.4	22.6	22.8	22.8	22.8	22.8	22.8
97.5°	33.7	34.1	34.3	34.6	34.9	35.3	35.6	35.6	35.6	35.6	35.6
100°	47.7	48.0	48.1	48.4	48.6	48.9	49.1	49.1	49.1	49.1	49.1
102.5°	62.0	62.2	62.4	62.7	63.0	63.3	63.6	63.7	63.8	63.9	64.0
105°	77.4	77.5	77.6	77.7	77.9	78.0	78.2	78.4	78.5	78.7	78.8
107.5°	94.0	94.2	94.2	94.2	94.2	94.2	94.2	94.3	94.4	94.5	94.6
110°	110.4	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	127.4	127.6	127.6	127.5	127.4	127.4	127.3	127.1	126.8	126.6	126.3
115°	144.1	144.3	144.2	144.1	143.9	143.8	143.6	143.5	143.5	143.4	143.3
117.5°	161.5	161.8	161.6	161.2	160.8	160.4	160.0	159.8	159.5	159.3	159.0
120°	178.2	178.5	178.2	177.5	176.9	176.2	175.6	175.6	175.6	175.6	175.6
122.5°	194.1	194.5	194.3	193.9	193.5	193.1	192.7	192.5	192.2	192.0	191.7
125°	209.7	210.1	210.0	209.7	209.5	209.2	209.0	208.8	208.6	208.3	208.1
127.5°	226.1	226.5	226.3	226.0	225.7	225.3	225.0	224.7	224.4	224.1	223.8
130°	241.2	241.7	241.6	241.5	241.3	241.2	241.0	240.8	240.7	240.5	240.4
132.5°	256.6	257.0	257.0	257.1	257.2	257.3	257.4	257.0	256.6	256.2	255.8
135°	271.2	271.6	271.7	271.8	272.0	272.1	272.3	272.2	272.2	272.1	272.0
137.5°	286.1	286.5	286.6	286.7	286.9	287.0	287.2	287.1	287.1	287.0	286.9
140°	300.0	300.4	300.6	301.0	301.4	301.8	302.2	302.2	302.2	302.2	302.2
142.5°	314.2	314.6	314.7	315.0	315.2	315.5	315.7	315.8	315.8	315.9	316.0
145°	327.1	327.4	327.6	328.1	328.6	329.1	329.6	329.7	329.7	329.8	329.9
147.5°	339.8	340.2	340.4	340.7	341.0	341.3	341.6	341.8	342.0	342.1	342.3
150°	351.4	351.6	351.8	352.1	352.4	352.7	353.0	353.2	353.5	353.7	354.0
152.5°	362.4	362.6	362.8	363.2	363.6	364.0	364.4	364.7	365.0	365.3	365.6
155°	372.5	372.6	372.7	372.9	373.2	373.4	373.6	374.0	374.4	374.8	375.2
157.5°	381.7	381.8	381.9	382.0	382.2	382.3	382.5	383.1	383.6	384.2	384.7
160°	390.2	390.3	390.3	390.4	390.5	390.6	390.7	391.2	391.6	392.1	392.6
162.5°	397.5	397.5	397.5	397.6	397.7	397.7	397.8	398.4	398.9	399.5	400.0
165°	403.9	403.9	403.9	403.9	403.9	403.9	403.9	404.4	405.0	405.5	406.0
167.5°	409.3	409.2	409.2	409.2	409.2	409.2	409.2	409.8	410.3	410.9	411.4
170°	413.9	413.8	413.8	413.7	413.6	413.6	413.5	414.0	414.6	415.1	415.6
172.5°	417.1	417.0	417.0	416.9	416.8	416.8	416.7	417.2	417.8	418.3	418.8
175°	419.6	419.5	419.4	419.3	419.1	419.0	418.8	419.4	419.9	420.5	421.0
177.5°	421.0	420.9	420.8	420.7	420.5	420.4	420.2	420.7	421.1	421.6	422.1
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	922.3	924.5	919.3	917.8	919.3	914.1	915.6	917.1	917.1	919.3	920.8
5°	868.8	865.8	860.6	859.1	857.6	859.8	858.3	860.6	861.3	866.5	867.3
7.5°	815.9	811.5	807.0	802.6	801.1	797.4	801.1	801.1	806.3	804.8	808.5
10°	753.5	752.7	746.8	744.5	741.6	735.6	743.8	741.6	745.3	752.0	753.5
12.5°	707.4	699.2	702.9	692.5	696.2	690.2	691.0	691.0	696.9	697.7	696.2
15°	663.5	656.8	647.1	642.6	640.4	637.4	647.1	647.8	643.4	653.8	650.1
17.5°	618.8	618.8	609.9	607.7	601.7	604.7	603.2	604.0	602.5	609.9	613.6
20°	580.2	576.4	573.5	574.2	566.8	565.3	563.8	565.3	570.5	575.7	577.2
22.5°	548.9	546.7	539.3	540.7	534.8	537.0	535.5	539.3	540.0	540.0	545.2
25°	519.2	516.2	516.9	514.0	511.7	511.7	509.5	511.7	514.7	516.2	516.9
27.5°	496.9	494.6	490.9	488.7	490.2	486.4	489.4	491.7	491.7	490.2	491.7
30°	470.1	471.6	471.6	464.1	467.1	465.6	467.8	469.3	469.3	470.1	468.6
32.5°	452.2	447.8	447.0	446.3	446.3	443.3	443.3	445.5	446.3	447.0	449.3
35°	428.4	428.4	424.7	426.9	424.0	424.7	424.0	424.7	426.2	424.0	426.2
37.5°	406.9	407.6	406.1	407.6	408.3	406.9	405.4	408.3	406.9	406.9	405.4
40°	388.3	387.5	388.3	388.3	388.3	389.0	387.5	387.5	387.5	386.0	384.5
42.5°	372.6	368.2	369.7	370.4	368.2	368.2	368.9	368.2	370.4	365.9	365.9
45°	350.3	348.8	349.6	349.6	351.1	348.8	350.3	351.1	348.8	348.1	346.6
47.5°	330.2	331.7	330.2	331.7	331.7	333.2	330.2	331.0	331.7	328.8	326.5
50°	310.2	310.2	312.4	311.7	312.4	310.9	310.9	310.2	310.9	309.4	307.2
52.5°	291.6	289.3	293.1	292.3	291.6	290.8	290.1	290.8	289.3	287.8	287.8
55°	268.5	268.5	270.7	271.5	271.5	270.0	268.5	269.3	268.5	267.8	267.0
57.5°	249.9	246.9	248.4	249.2	249.2	246.9	248.4	246.9	246.9	247.7	245.5
60°	226.1	226.1	224.6	226.9	226.9	225.4	225.4	226.1	224.6	223.9	223.1
62.5°	200.8	201.6	203.8	204.5	205.3	203.8	202.3	203.1	203.1	200.8	201.6
65°	179.3	180.7	183.7	183.0	181.5	182.2	180.7	181.5	179.3	180.0	177.8
67.5°	158.4	157.7	158.4	158.4	159.9	159.2	157.7	157.7	156.9	159.2	156.9
70°	136.1	136.1	136.1	136.1	136.9	137.6	136.1	134.6	135.4	133.9	133.1
72.5°	113.1	113.8	113.1	114.5	112.3	113.8	113.8	113.1	112.3	112.3	112.3
75°	91.5	93.0	90.7	91.5	90.7	92.2	91.5	91.5	90.0	89.3	90.0
77.5°	69.9	70.7	69.2	69.9	69.2	69.9	69.9	69.2	69.2	69.2	69.2
80°	49.8	50.6	49.8	49.1	48.3	49.8	48.3	49.1	49.8	49.1	50.6
82.5°	32.0	32.0	31.2	32.0	30.5	30.5	31.2	31.2	30.5	32.0	30.5
85°	15.6	15.6	17.1	15.6	14.9	14.9	14.9	15.6	14.9	16.4	15.6
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	11.7	11.7	11.8	11.9	12.0	12.1	12.0	11.9	11.8	11.7	11.7
92.5°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
95°	22.8	22.7	22.5	22.4	22.2	22.0	22.2	22.4	22.5	22.7	22.8
97.5°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6
100°	49.1	49.1	49.0	48.9	48.8	48.7	48.8	48.9	49.0	49.1	49.1
102.5°	64.0	64.0	63.9	63.8	63.7	63.6	63.7	63.8	63.9	64.0	64.0
105°	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9	78.9
107.5°	94.6	94.4	94.0	93.6	93.2	92.8	93.2	93.6	94.0	94.4	94.6
110°	110.6	110.5	110.2	110.0	109.7	109.5	109.7	110.0	110.2	110.5	110.6

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	126.2	126.1	126.0	125.8	125.7	125.5	125.7	125.8	126.0	126.1	126.2
115°	143.3	143.2	142.9	142.7	142.4	142.2	142.4	142.7	142.9	143.2	143.3
117.5°	158.9	158.8	158.5	158.3	158.0	157.8	158.0	158.3	158.5	158.8	158.9
120°	175.6	175.5	175.3	175.0	174.8	174.6	174.8	175.0	175.3	175.5	175.6
122.5°	191.6	191.5	191.4	191.2	191.1	190.9	191.1	191.2	191.4	191.5	191.6
125°	208.0	208.0	207.9	207.8	207.7	207.6	207.7	207.8	207.9	208.0	208.0
127.5°	223.6	223.5	223.2	223.0	222.7	222.5	222.7	223.0	223.2	223.5	223.6
130°	240.3	240.1	239.8	239.5	239.2	238.9	239.2	239.5	239.8	240.1	240.3
132.5°	255.6	255.5	255.2	255.0	254.7	254.5	254.7	255.0	255.2	255.5	255.6
135°	272.0	271.9	271.6	271.4	271.1	270.9	271.1	271.4	271.6	271.9	272.0
137.5°	286.9	286.7	286.4	286.1	285.8	285.5	285.8	286.1	286.4	286.7	286.9
140°	302.2	302.0	301.7	301.4	301.1	300.8	301.1	301.4	301.7	302.0	302.2
142.5°	316.0	315.8	315.5	315.2	314.9	314.6	314.9	315.2	315.5	315.8	316.0
145°	329.9	329.7	329.4	329.1	328.8	328.5	328.8	329.1	329.4	329.7	329.9
147.5°	342.4	342.2	341.9	341.6	341.2	340.9	341.2	341.6	341.9	342.2	342.4
150°	354.1	354.0	353.7	353.5	353.2	353.0	353.2	353.5	353.7	354.0	354.1
152.5°	365.8	365.6	365.3	365.0	364.7	364.4	364.7	365.0	365.3	365.6	365.8
155°	375.4	375.3	375.0	374.8	374.5	374.3	374.5	374.8	375.0	375.3	375.4
157.5°	385.0	384.8	384.4	384.0	383.6	383.2	383.6	384.0	384.4	384.8	385.0
160°	392.8	392.6	392.3	392.0	391.7	391.4	391.7	392.0	392.3	392.6	392.8
162.5°	400.3	400.1	399.7	399.3	398.9	398.5	398.9	399.3	399.7	400.1	400.3
165°	406.3	406.1	405.7	405.4	405.0	404.6	405.0	405.4	405.7	406.1	406.3
167.5°	411.7	411.5	411.1	410.7	410.3	409.9	410.3	410.7	411.1	411.5	411.7
170°	415.9	415.7	415.2	414.7	414.3	413.8	414.3	414.7	415.2	415.7	415.9
172.5°	419.1	418.9	418.4	417.9	417.5	417.0	417.5	417.9	418.4	418.9	419.1
175°	421.3	421.1	420.6	420.1	419.6	419.1	419.6	420.1	420.6	421.1	421.3
177.5°	422.3	422.1	421.6	421.1	420.7	420.2	420.7	421.1	421.6	422.1	422.3
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	918.6	924.5	922.3	914.1	923.8	923.8	930.5	930.5	938.7	941.6	946.1
5°	866.5	871.0	874.7	871.0	877.7	888.1	894.0	899.3	910.4	914.9	921.6
7.5°	810.7	818.9	822.6	822.6	833.8	845.7	857.6	865.0	880.7	886.6	893.3
10°	756.4	766.1	773.6	772.8	791.4	798.8	813.7	830.8	846.4	855.4	865.0
12.5°	699.2	704.4	714.8	729.7	734.1	747.5	764.6	786.2	814.5	822.6	836.8
15°	651.6	665.7	673.9	680.6	691.0	703.6	722.2	743.1	771.3	789.2	804.0
17.5°	611.4	630.0	635.2	633.7	647.1	666.4	688.0	703.6	728.9	750.5	764.6
20°	578.7	586.1	595.0	598.8	609.2	630.0	650.8	668.7	689.5	706.6	723.0
22.5°	545.9	551.9	559.3	566.0	574.2	586.1	606.2	628.5	648.6	665.0	683.6
25°	519.2	522.9	529.6	534.8	543.7	551.9	566.0	590.6	614.4	624.0	640.4
27.5°	493.1	496.1	500.6	506.5	511.0	519.2	531.8	551.9	576.4	586.1	608.4
30°	470.1	472.3	476.8	479.7	482.0	491.7	501.3	516.9	535.5	548.9	565.3
32.5°	448.5	450.7	455.2	455.9	458.9	464.1	473.1	487.2	503.6	514.7	528.8
35°	424.7	426.2	430.7	432.1	434.4	438.8	445.5	455.9	470.8	479.0	491.7
37.5°	406.1	405.4	408.3	410.6	413.6	415.8	418.0	428.4	439.6	447.0	456.7
40°	386.0	384.5	385.3	388.3	389.8	392.7	392.7	403.1	410.6	416.5	424.0
42.5°	365.9	365.2	363.7	365.2	366.7	367.4	368.2	375.6	383.1	388.3	396.4
45°	345.9	345.1	343.6	344.4	344.4	345.9	348.1	351.1	356.3	360.7	365.2
47.5°	327.3	325.8	323.6	322.8	324.3	324.3	324.3	327.3	332.5	334.0	338.4
50°	307.9	305.7	302.7	301.2	301.2	300.5	302.0	302.7	307.2	308.7	312.4
52.5°	287.1	285.6	282.6	279.7	280.4	278.9	279.7	280.4	281.9	284.1	286.4
55°	266.3	263.3	261.1	260.3	258.1	258.1	255.9	258.8	258.1	258.8	261.8
57.5°	246.2	243.2	239.5	238.0	235.8	235.0	233.6	232.8	233.6	235.8	238.0
60°	222.4	220.9	218.7	216.4	215.0	212.7	211.2	211.2	210.5	210.5	211.2
62.5°	199.3	198.6	195.6	194.9	193.4	191.9	189.7	188.2	188.2	189.7	190.4
65°	177.0	176.3	174.0	173.3	169.6	168.1	167.4	166.6	165.1	165.1	165.1
67.5°	156.2	154.0	154.0	150.2	147.3	145.8	144.3	143.6	143.6	143.6	144.3
70°	133.1	133.1	130.9	128.7	125.7	126.4	124.2	122.0	122.0	120.5	121.2
72.5°	110.8	110.1	107.9	107.1	104.9	102.6	101.2	102.6	100.4	99.7	100.4
75°	89.3	88.5	87.0	85.5	86.3	84.0	81.8	81.1	81.1	79.6	79.6
77.5°	68.4	69.9	66.9	66.2	64.7	63.2	62.5	61.7	61.7	61.7	63.2
80°	47.6	48.3	48.3	46.9	47.6	45.4	45.4	45.4	43.1	43.9	44.6
82.5°	30.5	30.5	29.8	30.5	29.8	29.8	29.0	29.0	28.3	28.3	29.0
85°	17.1	16.4	15.6	17.1	16.4	16.4	15.6	15.6	15.6	15.6	15.6
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	11.8	11.9	12.1	12.2	12.4	10.7	8.9	7.2	5.5	4.6	4.1
92.5°	11.4	11.3	11.2	11.1	11.0	10.9	10.9	10.8	10.7	10.7	10.4
95°	22.8	22.8	22.8	22.8	22.8	22.6	22.4	22.3	22.1	22.0	21.6
97.5°	35.6	35.6	35.6	35.6	35.6	35.3	34.9	34.6	34.3	34.1	33.7
100°	49.1	49.1	49.1	49.1	49.1	48.9	48.6	48.4	48.1	48.0	47.7
102.5°	64.0	63.9	63.8	63.7	63.6	63.3	63.0	62.7	62.4	62.2	62.0
105°	78.8	78.7	78.5	78.4	78.2	78.0	77.9	77.7	77.6	77.5	77.4
107.5°	94.6	94.5	94.4	94.3	94.2	94.2	94.2	94.2	94.2	94.2	94.0
110°	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.4

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	126.3	126.6	126.8	127.1	127.3	127.4	127.4	127.5	127.6	127.6	127.4
115°	143.3	143.4	143.5	143.5	143.6	143.8	143.9	144.1	144.2	144.3	144.1
117.5°	159.0	159.3	159.5	159.8	160.0	160.4	160.8	161.2	161.6	161.8	161.5
120°	175.6	175.6	175.6	175.6	175.6	176.2	176.9	177.5	178.2	178.5	178.2
122.5°	191.7	192.0	192.2	192.5	192.7	193.1	193.5	193.9	194.3	194.5	194.1
125°	208.1	208.3	208.6	208.8	209.0	209.2	209.5	209.7	210.0	210.1	209.7
127.5°	223.8	224.1	224.4	224.7	225.0	225.3	225.7	226.0	226.3	226.5	226.1
130°	240.4	240.5	240.7	240.8	241.0	241.2	241.3	241.5	241.6	241.7	241.2
132.5°	255.8	256.2	256.6	257.0	257.4	257.3	257.2	257.1	257.0	257.0	256.6
135°	272.0	272.1	272.2	272.2	272.3	272.1	272.0	271.8	271.7	271.6	271.2
137.5°	286.9	287.0	287.1	287.1	287.2	287.0	286.9	286.7	286.6	286.5	286.1
140°	302.2	302.2	302.2	302.2	302.2	301.8	301.4	301.0	300.6	300.4	300.0
142.5°	316.0	315.9	315.8	315.8	315.7	315.5	315.2	315.0	314.7	314.6	314.2
145°	329.9	329.8	329.7	329.7	329.6	329.1	328.6	328.1	327.6	327.4	327.1
147.5°	342.3	342.1	342.0	341.8	341.6	341.3	341.0	340.7	340.4	340.2	339.8
150°	354.0	353.7	353.5	353.2	353.0	352.7	352.4	352.1	351.8	351.6	351.4
152.5°	365.6	365.3	365.0	364.7	364.4	364.0	363.6	363.2	362.8	362.6	362.4
155°	375.2	374.8	374.4	374.0	373.6	373.4	373.2	372.9	372.7	372.6	372.5
157.5°	384.7	384.2	383.6	383.1	382.5	382.3	382.2	382.0	381.9	381.8	381.7
160°	392.6	392.1	391.6	391.2	390.7	390.6	390.5	390.4	390.3	390.3	390.2
162.5°	400.0	399.5	398.9	398.4	397.8	397.7	397.7	397.6	397.5	397.5	397.5
165°	406.0	405.5	405.0	404.4	403.9	403.9	403.9	403.9	403.9	403.9	403.9
167.5°	411.4	410.9	410.3	409.8	409.2	409.2	409.2	409.2	409.2	409.2	409.3
170°	415.6	415.1	414.6	414.0	413.5	413.6	413.6	413.7	413.8	413.8	413.9
172.5°	418.8	418.3	417.8	417.2	416.7	416.8	416.8	416.9	417.0	417.0	417.1
175°	421.0	420.5	419.9	419.4	418.8	419.0	419.1	419.3	419.4	419.5	419.6
177.5°	422.1	421.6	421.1	420.7	420.2	420.4	420.5	420.7	420.8	420.9	421.0
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	967.7	967.7	967.7	967.7
2.5°	949.8	949.8	961.0	972.9
5°	929.0	934.2	952.1	968.4
7.5°	908.9	917.8	940.2	961.0
10°	884.4	896.3	923.8	948.3
12.5°	860.6	871.7	903.7	931.2
15°	827.1	841.2	875.5	909.7
17.5°	793.6	807.8	849.4	889.6
20°	754.2	772.8	819.7	873.2
22.5°	717.8	740.8	792.9	836.0
25°	677.6	713.3	761.6	817.4
27.5°	641.9	677.6	726.7	783.2
30°	601.7	638.2	688.8	740.8
32.5°	563.1	596.5	645.6	709.6
35°	522.9	554.9	602.5	667.2
37.5°	486.4	517.7	569.7	629.3
40°	450.7	483.5	528.1	587.6
42.5°	417.3	446.3	486.4	545.9
45°	386.8	407.6	444.8	500.6
47.5°	354.8	373.4	407.6	463.4
50°	325.0	340.7	370.4	422.5
52.5°	296.0	309.4	336.9	378.6
55°	270.0	282.6	302.7	343.6
57.5°	243.2	252.9	272.2	305.0
60°	217.2	226.1	241.7	268.5
62.5°	191.2	198.6	213.5	235.0
65°	168.1	174.0	185.2	203.8
67.5°	145.8	149.5	158.4	173.3
70°	124.2	127.2	134.6	146.5
72.5°	101.2	104.1	112.3	120.5
75°	81.8	82.6	88.5	95.2
77.5°	64.0	63.2	67.7	72.9
80°	43.9	46.1	49.8	52.1
82.5°	29.8	30.5	32.0	33.5
85°	16.4	17.1	17.1	19.3
87.5°	6.7	7.4	7.4	8.2
90°	3.2	2.3	1.3	0.4
92.5°	9.7	9.1	8.4	7.8
95°	20.8	20.1	19.3	18.5
97.5°	33.0	32.3	31.6	30.9
100°	47.0	46.4	45.7	45.1
102.5°	61.5	61.0	60.6	60.1
105°	77.1	76.9	76.6	76.4
107.5°	93.7	93.4	93.1	92.8
110°	109.9	109.4	108.9	108.4



TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	126.9	126.4	126.0	125.5
115°	143.6	143.1	142.7	142.2
117.5°	160.8	160.2	159.5	158.9
120°	177.5	176.9	176.2	175.6
122.5°	193.3	192.5	191.7	190.9
125°	209.0	208.3	207.6	206.9
127.5°	225.2	224.3	223.4	222.5
130°	240.2	239.1	238.1	237.1
132.5°	255.8	255.1	254.3	253.5
135°	270.3	269.4	268.6	267.7
137.5°	285.4	284.7	284.0	283.3
140°	299.3	298.6	297.9	297.2
142.5°	313.5	312.8	312.1	311.4
145°	326.6	326.0	325.5	324.9
147.5°	339.1	338.4	337.7	337.0
150°	350.9	350.4	350.0	349.5
152.5°	361.9	361.4	361.0	360.5
155°	372.2	372.0	371.7	371.5
157.5°	381.6	381.4	381.3	381.1
160°	390.1	389.9	389.8	389.6
162.5°	397.5	397.5	397.5	397.5
165°	404.0	404.1	404.1	404.2
167.5°	409.6	409.8	410.1	410.3
170°	414.2	414.4	414.7	414.9
172.5°	417.4	417.6	417.9	418.1
175°	419.9	420.1	420.4	420.6
177.5°	421.3	421.5	421.8	422.0
180°	421.3	421.3	421.3	421.3

TEST NUMBER: P998460

CATALOG NUMBER: SA2XXDIP-B485D330UB30-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.58	17.54	17.41	18.39	19.44	14.07	15.03	14.90	15.88	16.93
	3H	17.40	18.26	18.24	19.11	20.19	15.42	16.29	16.27	17.14	18.22
	4H	17.57	18.38	18.43	19.25	20.34	15.89	16.70	16.75	17.57	18.66
	6H	17.62	18.37	18.49	19.24	20.34	16.20	16.95	17.08	17.82	18.92
	8H	17.60	18.31	18.48	19.20	20.31	16.29	17.00	17.17	17.89	18.99
	12H	17.57	18.25	18.45	19.13	20.26	16.34	17.01	17.22	17.89	19.02
4H	2H	16.63	17.44	17.50	18.31	19.40	14.53	15.34	15.39	16.20	17.30
	3H	17.62	18.30	18.50	19.19	20.30	16.00	16.67	16.87	17.57	18.68
	4H	17.90	18.52	18.79	19.41	20.54	16.54	17.15	17.43	18.04	19.18
	6H	18.04	18.57	18.94	19.48	20.62	16.92	17.45	17.83	18.37	19.50
	8H	18.04	18.53	18.94	19.44	20.59	17.04	17.53	17.94	18.44	19.59
	12H	18.01	18.45	18.93	19.38	20.53	17.10	17.54	18.02	18.47	19.62
8H	4H	17.92	18.41	18.82	19.32	20.47	16.69	17.18	17.59	18.09	19.24
	6H	18.10	18.51	19.03	19.46	20.61	17.13	17.53	18.06	18.49	19.63
	8H	18.13	18.49	19.07	19.44	20.60	17.28	17.64	18.22	18.58	19.75
	12H	18.12	18.44	19.06	19.38	20.59	17.37	17.69	18.32	18.63	19.84
12H	4H	17.88	18.32	18.80	19.25	20.41	16.67	17.11	17.59	18.04	19.19
	6H	18.08	18.44	19.02	19.39	20.55	17.13	17.49	18.07	18.43	19.60
	8H	18.12	18.43	19.06	19.37	20.59	17.29	17.61	18.23	18.54	19.76