

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999538

Luminaire Tested: SA2XXRDIP-B290D330UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999538
REPORT IS A COMBINATION OF REPORTS P988091 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D330UB40-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2281.5 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999538

CATALOG NUMBER: SA2XXRDIP-B290D330UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999538

CATALOG NUMBER: SA2XXRDIP-B290D330UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	97	93	89	86	88	85	82	79	71	68	66	57	56	55	45	44	43
2	88	81	76	71	81	75	70	66	62	59	56	51	48	46	40	39	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	40	36	34	32
4	74	64	56	51	68	59	52	47	49	45	41	41	37	34	33	30	28
5	68	57	49	44	62	53	46	41	44	39	35	37	33	30	30	27	25
6	63	51	44	38	58	47	41	36	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	37	31	27	30	26	23	25	22	20
8	54	42	35	30	50	39	33	28	33	28	24	28	24	21	23	20	18
9	50	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7688	7688	7688
5°	7701	7315	7261
10°	7625	6937	6709
15°	7521	6492	6080
20°	7382	5987	5422
25°	7241	5467	4820
30°	7049	4961	4163
35°	6862	4450	3598
40°	6673	3950	3016
45°	6452	3432	2509
50°	6222	2934	2043
55°	5985	2435	1621
60°	5708	1947	1226
65°	5393	1485	997
70°	5006	1077	793
75°	4526	822	607
80°	3824	556	406
85°	2670	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6452 cd/sqm

TEST NUMBER: P999538

CATALOG NUMBER: SA2XXRDIP-B290D330UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	2.0
10°-20°	125.0	5.5
20°-30°	175.5	7.7
30°-40°	191.3	8.4
40°-50°	175.8	7.7
50°-60°	138.0	6.1
60°-70°	89.9	3.9
70°-80°	46.3	2.0
80°-90°	13.0	0.6
90°-100°	74.5	3.3
100°-110°	251.9	11.0
110°-120°	264.8	11.6
120°-130°	217.7	9.5
130°-140°	174.9	7.7
140°-150°	132.2	5.8
150°-160°	92.9	4.1
160°-170°	54.7	2.4
170°-180°	17.8	0.8
0°-30°	346.0	15.2
0°-40°	537.2	23.5
0°-60°	851.1	37.3
0°-90°	1000.2	43.8
90°-120°	591.1	25.9
90°-150°	1115.9	48.9
90°-180°	1281.0	56.1
0°-180°	2281.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	486	486	486	486	486	
5°	486	484	478	482	480	46
15°	462	457	442	434	430	130
25°	419	405	376	358	352	193
35°	361	339	300	272	263	226
45°	295	266	220	189	178	228
55°	225	190	143	116	108	201
65°	152	116	76	62	60	150
75°	81	50	35	32	32	86
85°	19	10	8	8	8	22
90°	0	5	12	12	12	2
95°	12	30	138	52	40	13
105°	43	65	262	468	398	46
115°	76	96	219	452	524	75
125°	106	125	211	366	425	94
135°	124	148	208	308	352	96
145°	142	163	207	257	281	89
155°	162	174	201	227	236	74
165°	176	181	193	204	208	50
175°	183	184	185	188	187	17
180°	184	184	184	184	184	

TEST NUMBER: P999538

CATALOG NUMBER: SA2XXRDIP-B290D330UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	485.7	485.7	485.7	485.7	485.7
2.5°	487.9	485.7	480.9	485.3	484.4
5°	485.7	483.5	477.8	481.8	480.5
7.5°	481.8	479.2	473.0	474.8	472.6
10°	476.5	473.4	464.6	463.3	460.7
12.5°	469.9	466.0	454.1	451.5	446.6
15°	462.0	457.2	442.2	433.9	429.5
17.5°	452.8	445.7	427.3	417.6	410.6
20°	442.2	433.4	411.5	400.5	390.8
22.5°	430.8	420.7	395.2	380.2	373.7
25°	419.4	405.3	376.3	358.3	351.7
27.5°	405.7	390.8	358.7	338.0	327.9
30°	391.2	374.5	339.4	316.9	305.1
32.5°	377.2	356.9	320.9	294.5	283.5
35°	361.3	338.9	300.2	272.5	262.9
37.5°	346.0	321.8	280.9	250.6	239.6
40°	329.7	303.3	260.7	229.5	218.0
42.5°	313.0	284.9	240.5	207.9	196.9
45°	295.4	266.0	219.8	188.6	178.0
47.5°	278.7	247.5	200.0	168.8	159.1
50°	260.2	229.0	180.7	150.3	141.1
52.5°	242.2	209.2	162.2	133.2	124.8
55°	224.6	190.3	142.9	116.5	108.1
57.5°	206.6	171.4	125.7	101.1	94.1
60°	188.1	153.0	107.7	85.3	78.2
62.5°	170.1	135.0	92.3	71.2	67.7
65°	151.7	116.1	76.5	61.5	60.2
67.5°	134.1	98.5	61.5	54.1	52.8
70°	115.6	81.3	51.0	46.6	44.8
72.5°	98.0	65.5	42.6	39.1	38.2
75°	80.9	50.1	35.2	32.1	31.7
77.5°	63.7	35.6	27.7	25.9	25.1
80°	47.9	25.5	21.1	19.3	19.3
82.5°	33.4	17.1	14.5	13.6	13.6
85°	18.9	9.7	8.4	8.4	8.4
87.5°	7.0	3.5	3.5	3.1	3.1
90°	0.4	4.8	12.0	11.5	11.7
92.5°	5.3	16.8	54.4	25.1	21.6
95°	12.4	30.4	138.5	52.3	40.3
97.5°	18.4	40.1	225.8	105.0	67.5
100°	27.2	49.2	279.2	209.0	126.5
102.5°	35.3	57.2	281.0	353.4	246.7
105°	43.1	65.0	261.9	468.1	398.3
107.5°	51.6	72.8	244.2	509.6	500.4
110°	60.1	80.8	232.2	502.9	542.1

TEST NUMBER: P999538

CATALOG NUMBER: SA2XXRDIP-B290D330UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	67.9	88.4	224.4	480.2	541.4
115°	76.0	96.0	219.1	452.2	524.1
117.5°	84.5	103.6	216.3	425.5	498.0
120°	92.2	111.0	213.8	401.6	472.9
122.5°	99.7	118.6	212.4	383.1	446.7
125°	106.0	125.4	210.6	366.4	425.2
127.5°	111.3	132.0	209.6	352.0	405.0
130°	115.9	137.9	208.9	337.5	388.4
132.5°	120.2	143.4	208.5	322.5	371.1
135°	124.4	148.4	208.2	307.8	352.4
137.5°	128.3	152.7	208.2	293.0	334.3
140°	132.9	156.6	207.8	279.9	315.6
142.5°	137.5	159.8	207.8	267.4	296.9
145°	142.1	163.3	207.1	257.1	281.3
147.5°	147.0	166.1	206.0	248.1	267.5
150°	152.0	169.0	205.0	240.3	255.5
152.5°	156.9	171.8	203.2	233.8	245.3
155°	161.5	174.4	201.1	227.4	236.4
157.5°	165.4	176.5	199.0	221.4	228.7
160°	169.3	178.6	196.9	215.4	221.2
162.5°	173.2	180.2	195.1	209.8	214.2
165°	176.0	181.3	192.6	204.3	207.5
167.5°	178.5	182.4	190.5	199.3	201.1
170°	180.9	182.9	188.7	194.8	195.4
172.5°	182.4	183.4	186.6	190.6	190.8
175°	183.4	183.6	185.2	187.5	187.0
177.5°	184.1	183.8	183.8	185.2	184.1
180°	183.8	183.8	183.8	183.8	183.8

(END OF REPORT)