

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999549

Luminaire Tested: SA2XXRDIP-B290D530UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999549
REPORT IS A COMBINATION OF REPORTS P988102 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D530UB27-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2875.0 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999549

CATALOG NUMBER: SA2XXRDIP-B290D530UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999549

CATALOG NUMBER: SA2XXRDIP-B290D530UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	38	37	36
2	86	79	74	69	78	72	67	63	58	55	52	45	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	47	44	40	38	35	30	28	27
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23
5	67	55	48	42	60	51	44	39	41	36	33	33	29	26	24	22	20
6	61	50	42	36	55	45	39	34	37	32	28	30	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	20	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	16	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	17	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7666	7666	7666
5°	7679	7293	7239
10°	7603	6918	6689
15°	7498	6473	6062
20°	7360	5968	5406
25°	7218	5451	4805
30°	7029	4945	4151
35°	6843	4437	3587
40°	6653	3938	3008
45°	6432	3421	2502
50°	6206	2924	2037
55°	5969	2427	1617
60°	5693	1942	1223
65°	5375	1481	994
70°	4993	1073	791
75°	4509	820	605
80°	3816	553	406
85°	2656	253	195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6432 cd/sqm

TEST NUMBER: P999549

CATALOG NUMBER: SA2XXRDIP-B290D530UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.4	1.6
10°-20°	124.6	4.3
20°-30°	174.9	6.1
30°-40°	190.7	6.6
40°-50°	175.3	6.1
50°-60°	137.6	4.8
60°-70°	89.6	3.1
70°-80°	46.1	1.6
80°-90°	13.7	0.5
90°-100°	41.5	1.4
100°-110°	132.0	4.6
110°-120°	225.9	7.9
120°-130°	297.1	10.3
130°-140°	333.5	11.6
140°-150°	327.1	11.4
150°-160°	274.3	9.5
160°-170°	182.0	6.3
170°-180°	63.6	2.2
0°-30°	344.9	12.0
0°-40°	535.6	18.6
0°-60°	848.5	29.5
0°-90°	997.9	34.7
90°-120°	399.5	13.9
90°-150°	1357.2	47.2
90°-180°	1877.0	65.3
0°-180°	2875.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	484	484	484	484	484	
5°	484	482	476	480	479	46
15°	461	456	441	433	428	130
25°	418	404	375	357	351	192
35°	360	338	299	272	262	225
45°	294	265	219	188	178	227
55°	224	190	142	116	108	200
65°	151	116	76	61	60	150
75°	81	50	35	32	32	85
85°	19	10	8	8	8	22
90°	1	7	20	19	19	3
95°	30	35	36	36	35	33
105°	122	124	125	126	126	129
115°	227	230	229	228	227	224
125°	330	335	333	331	331	295
135°	427	433	434	433	432	330
145°	518	522	525	526	524	324
155°	592	594	596	598	597	273
165°	644	644	644	648	645	182
175°	670	669	667	671	668	64
180°	671	671	671	671	671	

TEST NUMBER: P999549

CATALOG NUMBER: SA2XXRDIP-B290D530UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	484.3	484.3	484.3	484.3	484.3
2.5°	486.5	484.3	479.5	483.8	483.0
5°	484.3	482.1	476.4	480.3	479.0
7.5°	480.3	477.7	471.6	473.3	471.1
10°	475.1	472.0	463.3	461.9	459.3
12.5°	468.5	464.6	452.7	450.1	445.3
15°	460.6	455.8	440.9	432.6	428.2
17.5°	451.4	444.4	426.0	416.4	409.3
20°	440.9	432.1	410.2	399.3	389.6
22.5°	429.5	419.4	394.0	379.1	372.5
25°	418.1	404.1	375.2	357.2	350.6
27.5°	404.5	389.6	357.6	337.0	326.9
30°	390.1	373.4	338.3	316.0	304.2
32.5°	376.0	355.9	319.9	293.6	282.7
35°	360.3	337.9	299.3	271.7	262.1
37.5°	344.9	320.8	280.1	249.8	238.9
40°	328.7	302.4	259.9	228.8	217.4
42.5°	312.0	284.0	239.7	207.3	196.3
45°	294.5	265.2	219.1	188.0	177.5
47.5°	277.9	246.7	199.4	168.3	158.7
50°	259.5	228.3	180.1	149.9	140.7
52.5°	241.5	208.6	161.7	132.8	124.5
55°	224.0	189.8	142.4	116.1	107.8
57.5°	206.0	170.9	125.3	100.8	93.8
60°	187.6	152.5	107.4	85.0	78.0
62.5°	169.6	134.5	92.0	71.0	67.5
65°	151.2	115.7	76.3	61.4	60.0
67.5°	133.7	98.2	61.4	53.9	52.6
70°	115.3	81.1	50.8	46.5	44.7
72.5°	97.7	65.3	42.5	39.0	38.1
75°	80.6	50.0	35.1	32.0	31.6
77.5°	63.5	35.5	27.6	25.9	25.0
80°	47.8	25.4	21.0	19.3	19.3
82.5°	33.3	17.1	14.5	13.6	13.6
85°	18.8	9.6	8.3	8.3	8.3
87.5°	7.0	3.5	3.5	3.1	3.1
90°	0.6	7.4	19.8	18.7	19.3
92.5°	12.5	17.0	17.6	18.1	18.1
95°	29.5	35.1	36.3	36.3	35.1
97.5°	49.3	54.4	56.7	56.7	56.7
100°	72.0	76.5	78.2	78.2	77.6
102.5°	95.8	99.2	101.4	102.0	101.4
105°	121.8	123.5	124.6	125.8	125.8
107.5°	147.9	150.1	150.1	150.7	147.9
110°	172.8	176.2	176.2	176.2	174.5

TEST NUMBER: P999549

CATALOG NUMBER: SA2XXRDIP-B290D530UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	200.0	203.4	202.8	201.1	200.0
115°	226.6	230.0	228.9	228.3	226.6
117.5°	253.3	257.8	255.0	253.3	251.6
120°	279.9	284.4	279.9	279.9	278.2
122.5°	304.3	309.9	307.1	305.4	304.3
125°	329.7	334.8	333.1	331.4	330.9
127.5°	354.7	360.9	358.6	356.4	354.7
130°	377.9	385.3	384.1	383.0	380.7
132.5°	404.0	409.6	410.2	407.4	405.7
135°	426.6	432.9	434.0	433.4	431.7
137.5°	451.6	456.7	457.8	457.2	455.0
140°	473.7	478.8	481.6	481.6	479.3
142.5°	496.3	501.4	503.1	503.7	501.4
145°	517.9	521.8	525.2	525.8	523.5
147.5°	537.1	542.2	544.5	545.6	543.3
150°	556.9	560.3	562.6	564.3	562.6
152.5°	574.5	577.9	580.7	583.0	580.7
155°	592.1	593.8	595.5	598.3	596.6
157.5°	607.4	608.5	609.6	613.6	610.8
160°	621.0	622.1	622.7	626.1	623.8
162.5°	633.4	633.4	634.0	638.0	635.1
165°	644.2	643.6	643.6	647.6	644.8
167.5°	653.8	652.1	652.1	656.1	653.3
170°	661.2	659.5	658.9	662.9	659.5
172.5°	666.3	664.6	664.0	668.0	664.6
175°	670.3	668.6	667.4	671.4	668.0
177.5°	672.5	670.8	669.7	673.1	669.7
180°	671.4	671.4	671.4	671.4	671.4

(END OF REPORT)