

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998542

Luminaire Tested: SA2XXDIP-B485D530UB40-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998542
REPORT IS A COMBINATION OF REPORTS P984285 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D530UB40-4F0-XX-W2A-D4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4009.3 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998542

CATALOG NUMBER: SA2XXDIP-B485D530UB40-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P998542

CATALOG NUMBER: SA2XXDIP-B485D530UB40-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	95	90	86	82	86	82	79	75	68	65	63	54	52	51	42	41	40
2	86	78	71	66	78	71	65	61	59	54	51	47	44	41	36	34	32
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	17	15
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8078	8078	8078
5°	8113	7733	7689
10°	8059	7464	7356
15°	7946	7188	7014
20°	7802	6896	6690
25°	7660	6618	6395
30°	7461	6336	6104
35°	7260	6063	5891
40°	7049	5826	5678
45°	6849	5612	5493
50°	6631	5415	5310
55°	6403	5205	5125
60°	6127	4986	4929
65°	5837	4736	4704
70°	5509	4467	4462
75°	5091	4198	4232
80°	4431	3916	3996
85°	3757	3653	3791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6849 cd/sqm

TEST NUMBER: P998542

CATALOG NUMBER: SA2XXDIP-B485D530UB40-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	1.2
10°-20°	138.7	3.5
20°-30°	210.2	5.2
30°-40°	256.0	6.4
40°-50°	275.4	6.9
50°-60°	267.5	6.7
60°-70°	233.6	5.8
70°-80°	179.8	4.5
80°-90°	122.3	3.1
90°-100°	202.9	5.1
100°-110°	465.7	11.6
110°-120°	465.8	11.6
120°-130°	372.4	9.3
130°-140°	290.7	7.2
140°-150°	214.1	5.3
150°-160°	149.4	3.7
160°-170°	88.0	2.2
170°-180°	28.6	0.7
0°-30°	397.3	9.9
0°-40°	653.3	16.3
0°-60°	1196.2	29.8
0°-90°	1731.8	43.2
90°-120°	1134.3	28.3
90°-150°	2011.5	50.2
90°-180°	2277.0	56.8
0°-180°	4009.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	510	510	510	510	510	
5°	512	510	505	510	509	49
15°	488	490	490	496	496	137
25°	444	449	456	464	467	204
35°	382	395	409	425	430	239
45°	314	334	359	382	390	242
55°	240	267	305	332	342	215
65°	164	200	244	274	284	163
75°	91	132	180	212	221	96
85°	27	72	120	151	161	28
90°	8	58	117	146	155	7
95°	26	90	308	197	187	25
105°	73	130	485	842	738	78
115°	125	165	397	794	918	124
125°	172	203	364	634	736	153
135°	201	239	343	519	596	155
145°	228	263	333	418	460	144
155°	260	280	323	366	380	120
165°	283	292	310	328	334	80
175°	295	295	298	302	301	28
180°	296	296	296	296	296	

TEST NUMBER: P998542

CATALOG NUMBER: SA2XXDIP-B485D530UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	510.3	510.3	510.3	510.3	510.3
2.5°	514.0	511.7	506.6	510.3	508.8
5°	511.7	509.5	505.1	509.5	508.8
7.5°	508.0	506.6	502.9	508.0	507.3
10°	503.6	502.1	499.9	505.8	505.1
12.5°	496.2	497.0	495.5	501.4	500.7
15°	488.1	489.6	489.6	496.2	495.5
17.5°	477.7	480.7	482.9	489.6	489.6
20°	467.4	471.1	474.0	482.2	482.2
22.5°	456.3	460.7	465.2	473.3	474.8
25°	443.7	448.9	455.5	464.4	466.6
27.5°	428.9	437.1	444.4	455.5	457.0
30°	414.1	423.7	433.4	445.2	447.4
32.5°	397.9	409.0	420.8	434.8	439.3
35°	382.3	394.9	409.0	425.2	430.4
37.5°	365.3	379.4	397.1	414.9	420.0
40°	348.3	364.6	384.5	403.8	410.4
42.5°	332.0	348.3	372.0	393.4	400.1
45°	313.6	333.5	359.4	382.3	389.7
47.5°	295.8	317.3	346.8	370.5	378.6
50°	277.3	300.2	333.5	358.7	366.8
52.5°	259.6	284.0	319.5	345.4	354.2
55°	240.3	267.0	305.4	332.0	341.7
57.5°	221.9	251.4	289.9	318.7	328.3
60°	201.9	233.7	275.8	303.9	314.3
62.5°	184.1	217.4	259.6	289.9	299.5
65°	164.2	200.4	244.0	274.4	284.0
67.5°	146.4	184.1	228.5	258.8	269.2
70°	127.2	165.7	211.5	243.3	252.2
72.5°	109.4	149.4	196.0	227.0	238.1
75°	91.0	132.4	179.7	211.5	221.1
77.5°	73.2	116.1	164.2	196.0	206.3
80°	55.5	100.6	148.6	179.7	190.1
82.5°	40.7	85.0	133.9	164.9	174.5
85°	26.6	72.5	119.8	150.9	161.2
87.5°	16.3	60.6	108.0	138.3	147.9
90°	8.0	58.0	116.9	145.7	154.9
92.5°	15.2	72.9	178.5	160.2	163.4
95°	25.8	89.6	307.8	197.2	186.8
97.5°	34.8	101.5	443.1	276.0	224.7
100°	49.0	111.5	523.0	437.5	312.9
102.5°	61.2	120.8	520.6	663.7	500.2
105°	73.0	129.6	484.7	842.2	738.1
107.5°	86.7	138.4	451.1	903.2	896.5
110°	99.6	147.5	427.4	886.3	957.6

TEST NUMBER: P998542

CATALOG NUMBER: SA2XXDIP-B485D530UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	112.1	156.9	409.7	844.6	951.3
115°	125.2	165.4	396.8	793.8	917.5
117.5°	138.0	174.6	387.0	745.6	869.6
120°	150.5	183.6	378.6	701.4	824.0
122.5°	162.5	193.6	371.9	666.3	775.3
125°	172.0	203.2	363.8	634.2	735.5
127.5°	180.5	213.0	357.7	605.3	697.2
130°	187.9	222.3	352.2	576.8	664.5
132.5°	194.7	231.4	347.1	547.4	631.5
135°	200.8	239.4	342.8	518.7	596.2
137.5°	207.0	246.2	339.1	489.6	561.3
140°	214.4	251.8	335.7	463.4	525.2
142.5°	221.8	256.9	334.2	438.8	490.0
145°	228.5	262.6	333.0	417.8	460.5
147.5°	236.4	267.1	331.3	399.6	433.2
150°	244.4	271.6	329.6	386.5	410.9
152.5°	252.3	276.2	326.8	376.0	394.4
155°	259.7	280.4	323.4	365.7	380.2
157.5°	266.0	283.9	320.0	356.0	367.7
160°	272.2	287.3	316.6	346.4	355.8
162.5°	278.5	289.8	313.7	337.3	344.4
165°	283.0	291.6	309.7	328.5	333.6
167.5°	287.0	293.2	306.3	320.5	323.4
170°	291.0	294.2	303.5	313.2	314.3
172.5°	293.3	295.0	300.1	306.6	306.9
175°	295.0	295.2	297.8	301.5	300.6
177.5°	296.1	295.5	295.5	297.8	296.1
180°	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P998542

CATALOG NUMBER: SA2XXDIP-B485D530UB40-4F0-XX-W2A-D4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.81	12.66	12.82	13.68	15.04	14.89	15.73	15.89	16.75	18.11
	3H	13.27	14.04	14.28	15.06	16.45	17.48	18.24	18.49	19.27	20.65
	4H	13.75	14.47	14.77	15.51	16.89	18.73	19.45	19.75	20.49	21.87
	6H	14.03	14.70	15.07	15.74	17.14	20.02	20.70	21.06	21.73	23.13
	8H	14.09	14.73	15.13	15.78	17.18	20.68	21.32	21.72	22.38	23.77
	12H	14.10	14.72	15.15	15.76	17.18	21.41	22.02	22.45	23.07	24.49
4H	2H	12.86	13.59	13.89	14.62	16.01	15.22	15.94	16.25	16.97	18.36
	3H	14.57	15.18	15.61	16.24	17.64	18.01	18.62	19.05	19.68	21.08
	4H	15.19	15.76	16.24	16.81	18.23	19.42	19.99	20.47	21.04	22.46
	6H	15.60	16.10	16.66	17.17	18.59	20.89	21.38	21.94	22.46	23.87
	8H	15.71	16.17	16.77	17.24	18.68	21.65	22.11	22.70	23.17	24.61
	12H	15.75	16.18	16.83	17.26	18.70	22.47	22.89	23.55	23.98	25.41
8H	4H	15.98	16.44	17.03	17.51	18.94	19.56	20.03	20.62	21.09	22.53
	6H	16.61	17.00	17.69	18.11	19.54	21.19	21.58	22.27	22.69	24.12
	8H	16.83	17.18	17.92	18.27	19.72	22.08	22.43	23.17	23.52	24.97
	12H	16.97	17.27	18.06	18.36	19.84	23.08	23.38	24.17	24.47	25.96
12H	4H	16.18	16.60	17.25	17.68	19.12	19.54	19.96	20.61	21.04	22.48
	6H	16.94	17.29	18.03	18.38	19.83	21.22	21.56	22.30	22.65	24.10
	8H	17.25	17.55	18.34	18.64	20.13	22.15	22.45	23.24	23.54	25.03