

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999570

Luminaire Tested: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P999570  
REPORT IS A COMBINATION OF REPORTS P988123 AND P1007351  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-F  
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}  
{m-EER=0.792}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3138.0 lumens  
Efficiency: N/A  
Efficacy: 110.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')  
CIE Type: Semi-Indirect

Input Watts (W): 28.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P999570

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-F

### Luminous Intensity Polar Plot



TEST NUMBER: P999570

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80  |     |     |     | 70 |    |    |    | 50 |    |    |    | 30 |    |    |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 103 | 103 | 103 | 103 | 93 | 93 | 93 | 93 | 73 | 73 | 73 | 56 | 56 | 56 | 40 | 40 | 40 |
| 1   | 94  | 90  | 86  | 83  | 85 | 81 | 78 | 75 | 65 | 63 | 61 | 50 | 48 | 47 | 36 | 35 | 34 |
| 2   | 86  | 79  | 73  | 68  | 77 | 71 | 66 | 62 | 57 | 54 | 51 | 44 | 42 | 40 | 32 | 30 | 29 |
| 3   | 79  | 70  | 63  | 57  | 70 | 63 | 57 | 52 | 51 | 46 | 43 | 39 | 36 | 34 | 28 | 27 | 25 |
| 4   | 72  | 62  | 54  | 48  | 65 | 56 | 50 | 45 | 45 | 40 | 37 | 35 | 32 | 29 | 26 | 24 | 22 |
| 5   | 66  | 55  | 47  | 42  | 59 | 50 | 43 | 38 | 40 | 36 | 32 | 31 | 28 | 25 | 23 | 21 | 19 |
| 6   | 61  | 49  | 42  | 36  | 55 | 45 | 38 | 33 | 36 | 31 | 28 | 28 | 25 | 22 | 21 | 19 | 17 |
| 7   | 56  | 45  | 37  | 32  | 51 | 41 | 34 | 29 | 33 | 28 | 25 | 26 | 22 | 20 | 19 | 17 | 15 |
| 8   | 52  | 40  | 33  | 28  | 47 | 37 | 30 | 26 | 30 | 25 | 22 | 24 | 20 | 18 | 18 | 15 | 14 |
| 9   | 49  | 37  | 30  | 25  | 44 | 34 | 27 | 23 | 28 | 23 | 19 | 22 | 18 | 16 | 16 | 14 | 12 |
| 10  | 45  | 34  | 27  | 22  | 41 | 31 | 25 | 21 | 25 | 21 | 18 | 20 | 17 | 14 | 15 | 13 | 11 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 7766 | 7766 | 7766 |
| 5°  | 7778 | 7388 | 7334 |
| 10° | 7702 | 7007 | 6776 |
| 15° | 7596 | 6558 | 6141 |
| 20° | 7457 | 6047 | 5476 |
| 25° | 7313 | 5522 | 4868 |
| 30° | 7121 | 5011 | 4204 |
| 35° | 6932 | 4494 | 3634 |
| 40° | 6740 | 3989 | 3046 |
| 45° | 6517 | 3467 | 2534 |
| 50° | 6284 | 2963 | 2063 |
| 55° | 6046 | 2459 | 1638 |
| 60° | 5765 | 1967 | 1239 |
| 65° | 5446 | 1500 | 1007 |
| 70° | 5058 | 1088 | 801  |
| 75° | 4570 | 829  | 612  |
| 80° | 3864 | 561  | 410  |
| 85° | 2698 | 256  | 198  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6517 cd/sqm

TEST NUMBER: P999570

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-F

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 46.0   | 1.5       |
| 10°-20°   | 126.2  | 4.0       |
| 20°-30°   | 177.2  | 5.6       |
| 30°-40°   | 193.2  | 6.2       |
| 40°-50°   | 177.6  | 5.7       |
| 50°-60°   | 139.4  | 4.4       |
| 60°-70°   | 90.8   | 2.9       |
| 70°-80°   | 46.7   | 1.5       |
| 80°-90°   | 13.2   | 0.4       |
| 90°-100°  | 23.9   | 0.8       |
| 100°-110° | 89.2   | 2.8       |
| 110°-120° | 236.6  | 7.5       |
| 120°-130° | 392.4  | 12.5      |
| 130°-140° | 416.9  | 13.3      |
| 140°-150° | 387.4  | 12.3      |
| 150°-160° | 311.5  | 9.9       |
| 160°-170° | 200.7  | 6.4       |
| 170°-180° | 69.1   | 2.2       |
| 0°-30°    | 349.4  | 11.1      |
| 0°-40°    | 542.6  | 17.3      |
| 0°-60°    | 859.6  | 27.4      |
| 0°-90°    | 1010.3 | 32.2      |
| 90°-120°  | 349.8  | 11.1      |
| 90°-150°  | 1546.5 | 49.3      |
| 90°-180°  | 2128.0 | 67.8      |
| 0°-180°   | 3138.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°  | 22.5° | 45° | 67.5° | 90° | Flux |
|------|-----|-------|-----|-------|-----|------|
| 0°   | 491 | 491   | 491 | 491   | 491 |      |
| 5°   | 491 | 488   | 483 | 487   | 485 | 47   |
| 15°  | 467 | 462   | 447 | 438   | 434 | 131  |
| 25°  | 424 | 409   | 380 | 362   | 355 | 195  |
| 35°  | 365 | 342   | 303 | 275   | 266 | 228  |
| 45°  | 298 | 269   | 222 | 190   | 180 | 230  |
| 55°  | 227 | 192   | 144 | 118   | 109 | 203  |
| 65°  | 153 | 117   | 77  | 62    | 61  | 152  |
| 75°  | 82  | 51    | 36  | 32    | 32  | 86   |
| 85°  | 19  | 10    | 8   | 8     | 8   | 22   |
| 90°  | 0   | 6     | 10  | 13    | 14  | 3    |
| 95°  | 34  | 17    | 20  | 23    | 23  | 40   |
| 105° | 160 | 175   | 32  | 38    | 40  | 171  |
| 115° | 302 | 311   | 324 | 81    | 43  | 297  |
| 125° | 427 | 434   | 444 | 447   | 449 | 381  |
| 135° | 528 | 537   | 541 | 547   | 546 | 408  |
| 145° | 613 | 612   | 621 | 625   | 622 | 383  |
| 155° | 675 | 670   | 676 | 680   | 675 | 311  |
| 165° | 711 | 708   | 710 | 713   | 710 | 201  |
| 175° | 727 | 724   | 725 | 728   | 723 | 69   |
| 180° | 726 | 726   | 726 | 726   | 726 |      |

TEST NUMBER: P999570

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-F

**CANDELA DISTRIBUTION (FULL):**

|        | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|--------|-------|-------|-------|-------|-------|
| 0°     | 490.6 | 490.6 | 490.6 | 490.6 | 490.6 |
| 2.5°   | 492.8 | 490.6 | 485.7 | 490.2 | 489.3 |
| 5°     | 490.6 | 488.4 | 482.6 | 486.6 | 485.3 |
| 7.5°   | 486.6 | 483.9 | 477.7 | 479.5 | 477.3 |
| 10°    | 481.3 | 478.2 | 469.3 | 468.0 | 465.3 |
| 12.5°  | 474.6 | 470.6 | 458.6 | 456.0 | 451.1 |
| 15°    | 466.6 | 461.7 | 446.7 | 438.2 | 433.8 |
| 17.5°  | 457.3 | 450.2 | 431.6 | 421.8 | 414.7 |
| 20°    | 446.7 | 437.8 | 415.6 | 404.5 | 394.7 |
| 22.5°  | 435.1 | 424.9 | 399.1 | 384.1 | 377.4 |
| 25°    | 423.6 | 409.4 | 380.1 | 361.9 | 355.2 |
| 27.5°  | 409.8 | 394.7 | 362.3 | 341.4 | 331.2 |
| 30°    | 395.2 | 378.3 | 342.8 | 320.1 | 308.1 |
| 32.5°  | 380.9 | 360.5 | 324.1 | 297.5 | 286.4 |
| 35°    | 365.0 | 342.3 | 303.2 | 275.3 | 265.5 |
| 37.5°  | 349.4 | 325.0 | 283.7 | 253.1 | 242.0 |
| 40°    | 333.0 | 306.4 | 263.3 | 231.8 | 220.2 |
| 42.5°  | 316.1 | 287.7 | 242.9 | 210.0 | 198.9 |
| 45°    | 298.4 | 268.6 | 222.0 | 190.5 | 179.8 |
| 47.5°  | 281.5 | 250.0 | 202.0 | 170.5 | 160.7 |
| 50°    | 262.8 | 231.3 | 182.5 | 151.8 | 142.5 |
| 52.5°  | 244.6 | 211.3 | 163.8 | 134.5 | 126.1 |
| 55°    | 226.9 | 192.2 | 144.3 | 117.7 | 109.2 |
| 57.5°  | 208.7 | 173.2 | 127.0 | 102.1 | 95.0  |
| 60°    | 190.0 | 154.5 | 108.8 | 86.1  | 79.0  |
| 62.5°  | 171.8 | 136.3 | 93.2  | 71.9  | 68.4  |
| 65°    | 153.2 | 117.2 | 77.3  | 62.2  | 60.8  |
| 67.5°  | 135.4 | 99.5  | 62.2  | 54.6  | 53.3  |
| 70°    | 116.8 | 82.1  | 51.5  | 47.1  | 45.3  |
| 72.5°  | 99.0  | 66.2  | 43.1  | 39.5  | 38.6  |
| 75°    | 81.7  | 50.6  | 35.5  | 32.4  | 32.0  |
| 77.5°  | 64.4  | 36.0  | 28.0  | 26.2  | 25.3  |
| 80°    | 48.4  | 25.8  | 21.3  | 19.5  | 19.5  |
| 82.5°  | 33.7  | 17.3  | 14.7  | 13.8  | 13.8  |
| 85°    | 19.1  | 9.8   | 8.4   | 8.4   | 8.4   |
| 87.5°  | 7.1   | 3.6   | 3.6   | 3.1   | 3.1   |
| 90°    | 0.5   | 6.3   | 10.5  | 13.1  | 14.2  |
| 92.5°  | 13.1  | 11.0  | 12.6  | 13.7  | 14.2  |
| 95°    | 34.1  | 16.8  | 20.5  | 23.1  | 22.6  |
| 97.5°  | 61.4  | 18.4  | 26.8  | 28.4  | 28.9  |
| 100°   | 93.0  | 21.0  | 29.9  | 34.1  | 35.2  |
| 102.5° | 127.6 | 126.6 | 31.0  | 36.8  | 38.3  |
| 105°   | 159.6 | 175.4 | 32.0  | 37.8  | 39.9  |
| 107.5° | 196.9 | 210.1 | 33.1  | 38.9  | 41.0  |
| 110°   | 232.6 | 243.7 | 91.9  | 39.4  | 41.5  |

TEST NUMBER: P999570

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-F

**CANDELA DISTRIBUTION (continued):**

|        | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|--------|-------|-------|-------|-------|-------|
| 112.5° | 266.3 | 275.7 | 266.8 | 40.4  | 42.0  |
| 115°   | 302.0 | 310.9 | 324.0 | 80.9  | 43.1  |
| 117.5° | 333.0 | 343.5 | 352.4 | 277.3 | 139.7 |
| 120°   | 367.6 | 375.5 | 384.9 | 391.2 | 320.4 |
| 122.5° | 397.0 | 405.4 | 415.9 | 419.1 | 419.6 |
| 125°   | 427.0 | 433.8 | 443.8 | 447.4 | 449.0 |
| 127.5° | 454.3 | 461.6 | 469.5 | 474.7 | 475.3 |
| 130°   | 480.0 | 488.4 | 494.2 | 500.0 | 499.4 |
| 132.5° | 506.3 | 513.1 | 518.9 | 523.6 | 523.1 |
| 135°   | 528.3 | 536.7 | 541.4 | 546.7 | 545.6 |
| 137.5° | 551.4 | 557.7 | 563.0 | 568.2 | 566.7 |
| 140°   | 574.0 | 578.2 | 584.0 | 588.7 | 586.1 |
| 142.5° | 592.9 | 596.6 | 603.4 | 607.6 | 605.0 |
| 145°   | 612.9 | 612.3 | 621.3 | 624.9 | 622.3 |
| 147.5° | 630.2 | 628.6 | 637.5 | 640.2 | 638.1 |
| 150°   | 647.0 | 643.3 | 651.7 | 654.9 | 652.3 |
| 152.5° | 661.2 | 657.0 | 664.9 | 668.0 | 664.3 |
| 155°   | 674.8 | 670.1 | 676.4 | 679.6 | 675.4 |
| 157.5° | 685.9 | 681.7 | 686.4 | 690.1 | 685.9 |
| 160°   | 695.3 | 692.2 | 695.3 | 698.5 | 694.8 |
| 162.5° | 703.7 | 700.6 | 703.2 | 706.9 | 702.1 |
| 165°   | 711.1 | 707.9 | 709.5 | 713.2 | 709.5 |
| 167.5° | 716.8 | 713.7 | 715.3 | 718.9 | 714.2 |
| 170°   | 721.6 | 718.4 | 719.5 | 723.2 | 718.4 |
| 172.5° | 724.7 | 721.6 | 722.6 | 726.3 | 721.6 |
| 175°   | 727.4 | 723.7 | 724.7 | 728.4 | 723.2 |
| 177.5° | 728.4 | 724.7 | 725.3 | 728.9 | 724.2 |
| 180°   | 725.8 | 725.8 | 725.8 | 725.8 | 725.8 |

(END OF REPORT)