

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999585

Luminaire Tested: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999585
REPORT IS A COMBINATION OF REPORTS P988138 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3898.0 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	36	36	28
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	32	32	31	31	31	24
2	85	78	73	68	76	70	66	62	56	52	50	42	40	38	29	28	27	27	27	21
3	78	69	63	57	70	62	57	52	49	45	42	37	35	33	26	25	23	23	23	19
4	72	62	54	49	64	56	49	44	44	40	36	34	31	28	24	22	21	21	21	16
5	66	55	47	42	59	50	43	38	40	35	31	30	27	25	22	20	18	18	18	15
6	61	49	42	36	54	45	38	33	36	31	28	28	24	22	20	18	16	16	16	13
7	56	45	37	32	50	40	34	29	33	28	24	25	22	20	18	16	15	15	15	12
8	52	41	33	28	47	37	30	26	30	25	22	23	20	18	17	15	13	13	13	11
9	48	37	30	25	43	34	28	23	27	23	20	21	18	16	16	14	12	12	12	10
10	45	34	27	23	41	31	25	21	25	21	18	20	17	14	15	13	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9984	9984	9984	9984
5°	10008	10604	10043	8472
10°	9898	11209	9968	6996
15°	9683	11212	9847	5256
20°	9425	9268	9629	4336
25°	9110	5791	9307	3688
30°	8712	3709	8948	3175
35°	8225	2850	8491	2718
40°	7683	2395	8011	2377
45°	7102	2038	7399	1996
50°	6509	1733	6813	1726
55°	5851	1506	6166	1486
60°	5268	1148	5547	1134
65°	4721	865	5002	980
70°	4119	690	4443	798
75°	3479	528	3798	605
80°	2762	359	2978	395
85°	1921	186	2105	195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9134 cd/sqm

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.8	1.5
10°-20°	167.0	4.3
20°-30°	214.9	5.5
30°-40°	203.9	5.2
40°-50°	174.7	4.5
50°-60°	133.1	3.4
60°-70°	83.9	2.2
70°-80°	41.9	1.1
80°-90°	12.4	0.3
90°-100°	31.6	0.8
100°-110°	117.7	3.0
110°-120°	312.1	8.0
120°-130°	517.6	13.3
130°-140°	549.8	14.1
140°-150°	511.0	13.1
150°-160°	410.8	10.5
160°-170°	264.7	6.8
170°-180°	91.1	2.3
0°-30°	441.7	11.3
0°-40°	645.6	16.6
0°-60°	953.4	24.5
0°-90°	1091.7	28.0
90°-120°	461.3	11.8
90°-150°	2039.7	52.3
90°-180°	2806.0	72.0
0°-180°	3898.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	631	631	631	631	631	
5°	631	702	633	561	631	60
15°	595	792	605	371	595	167
25°	528	422	539	269	528	242
35°	433	208	447	199	433	271
45°	325	145	339	142	325	251
55°	220	100	231	99	220	198
65°	133	52	141	59	133	132
75°	62	28	68	32	62	67
85°	14	8	15	8	14	15
90°	1	19	1	19	1	3
95°	45	30	45	30	45	53
105°	211	53	211	53	211	225
115°	398	57	398	57	398	392
125°	563	592	563	592	563	502
135°	697	720	697	720	697	538
145°	808	821	808	821	808	506
155°	890	891	890	891	890	410
165°	938	936	938	936	938	265
175°	959	954	959	954	959	91
180°	957	957	957	957	957	

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	634.7	637.3	638.6	640.4	644.3	647.0	650.9	651.8	651.3	653.1	648.3
5°	631.2	636.9	642.1	646.5	653.5	657.9	662.7	668.4	669.8	676.3	672.4
7.5°	626.4	634.7	642.1	650.9	661.4	667.1	674.6	683.3	687.3	695.2	697.4
10°	618.5	630.3	643.0	652.2	666.7	676.8	683.8	697.8	707.0	718.8	717.1
12.5°	605.8	621.1	638.2	653.5	672.4	679.0	692.1	706.6	718.4	729.4	739.0
15°	594.8	612.3	631.2	650.0	671.5	683.8	696.9	715.8	728.5	747.8	756.1
17.5°	579.9	602.3	624.6	645.6	671.1	685.1	701.3	719.7	738.6	757.0	763.6
20°	564.6	588.7	612.8	641.3	670.2	683.8	700.4	723.2	741.6	756.1	756.1
22.5°	546.1	575.5	603.1	630.3	661.9	681.6	698.7	725.4	738.6	741.6	729.8
25°	527.7	557.1	587.3	621.1	657.0	674.6	693.9	718.8	723.2	711.0	680.3
27.5°	505.8	538.7	572.9	609.3	647.0	668.9	686.4	703.1	694.7	661.9	614.1
30°	483.5	519.0	557.5	592.2	637.8	657.9	672.8	677.6	651.3	597.9	536.1
32.5°	460.2	494.9	535.6	577.3	623.3	642.6	652.2	639.5	591.3	523.8	448.4
35°	433.1	472.1	514.6	558.0	603.6	618.0	623.7	592.6	530.8	443.6	368.6
37.5°	408.5	447.5	493.1	537.4	581.6	589.5	583.8	535.2	456.7	370.4	297.2
40°	379.6	421.2	465.9	515.5	551.8	554.0	540.0	476.9	379.6	298.5	253.3
42.5°	352.8	394.9	439.6	490.0	517.7	510.2	491.4	408.5	316.9	257.3	220.9
45°	325.2	365.1	413.3	458.0	477.8	460.2	431.7	343.6	266.1	221.4	193.3
47.5°	298.5	335.8	383.5	426.5	430.0	410.3	376.5	288.0	230.6	194.6	171.8
50°	272.2	309.5	354.2	389.7	386.2	359.0	320.8	250.3	200.3	171.8	153.0
52.5°	245.9	279.6	323.0	351.1	336.2	309.9	272.2	212.1	174.9	149.9	135.4
55°	219.6	251.2	288.4	311.6	288.0	257.7	231.0	181.9	151.7	131.5	120.5
57.5°	197.7	222.7	256.9	270.9	242.4	218.7	195.5	156.5	131.5	117.0	104.3
60°	173.6	196.4	224.4	232.7	203.4	184.1	164.4	132.4	112.6	99.9	91.6
62.5°	153.0	171.8	193.3	193.3	167.4	153.0	138.1	110.9	94.7	84.6	80.7
65°	132.8	146.4	161.7	160.0	138.1	125.4	113.5	91.6	79.3	72.3	68.4
67.5°	113.1	123.6	133.7	127.6	111.8	100.8	89.9	74.1	65.7	60.9	55.7
70°	95.1	103.4	108.7	103.0	87.2	78.0	70.1	59.6	53.0	46.9	43.8
72.5°	79.8	83.3	85.0	78.0	64.9	59.6	53.9	46.5	40.8	37.7	36.8
75°	62.2	65.3	64.0	58.7	47.8	43.8	39.4	34.2	32.9	31.1	30.2
77.5°	48.7	48.7	46.5	41.6	34.2	31.1	29.4	26.7	25.4	25.0	24.1
80°	34.6	34.2	32.9	27.6	23.2	21.5	21.5	19.7	19.3	18.4	18.4
82.5°	22.8	22.8	21.0	16.7	15.3	14.9	14.5	13.6	13.6	13.1	13.1
85°	13.6	12.7	10.5	9.2	8.8	8.8	8.3	7.9	8.3	7.9	7.9
87.5°	6.1	4.8	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.7	2.4	4.1	5.8	7.5	8.3	8.9	10.2	11.4	12.7	13.9
92.5°	17.3	16.7	16.1	15.4	14.8	14.5	14.7	15.2	15.7	16.1	16.6
95°	45.0	39.9	34.9	29.8	24.7	22.2	22.7	23.8	24.9	25.9	27.0
97.5°	81.0	68.4	55.8	43.1	30.5	24.2	25.4	27.9	30.4	32.8	35.3
100°	122.6	101.5	80.4	59.3	38.2	27.7	29.0	31.6	34.3	36.9	39.5
102.5°	168.3	168.0	167.7	167.4	167.1	166.9	152.9	124.9	96.9	68.9	40.9
105°	210.6	215.2	219.8	224.4	229.0	231.3	210.3	168.3	126.3	84.3	42.3
107.5°	259.7	263.6	267.4	271.3	275.2	277.1	251.2	199.3	147.4	95.5	43.6
110°	306.8	310.0	313.3	316.5	319.8	321.4	299.2	254.7	210.2	165.7	121.2

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	351.2	354.0	356.7	359.5	362.2	363.6	362.3	359.7	357.1	354.5	351.9
115°	398.3	400.9	403.5	406.2	408.8	410.1	412.0	415.9	419.7	423.6	427.4
117.5°	439.1	442.2	445.3	448.4	451.5	453.0	454.3	456.9	459.6	462.2	464.8
120°	484.9	487.2	489.5	491.8	494.1	495.2	496.6	499.4	502.1	504.9	507.7
122.5°	523.6	526.1	528.5	531.0	533.5	534.7	536.2	539.3	542.4	545.5	548.6
125°	563.1	565.1	567.1	569.1	571.1	572.1	573.6	576.5	579.4	582.4	585.3
127.5°	599.1	601.3	603.4	605.6	607.7	608.8	610.0	612.3	614.6	616.9	619.2
130°	633.1	635.6	638.0	640.5	643.0	644.2	645.0	646.7	648.4	650.1	651.8
132.5°	667.7	669.7	671.7	673.7	675.7	676.7	677.5	679.2	680.9	682.6	684.3
135°	696.8	699.3	701.7	704.2	706.7	707.9	708.6	710.0	711.3	712.7	714.1
137.5°	727.3	729.1	731.0	732.8	734.7	735.6	736.4	737.9	739.4	741.0	742.5
140°	757.1	758.3	759.5	760.8	762.0	762.6	763.4	765.1	766.8	768.5	770.2
142.5°	782.0	783.1	784.2	785.3	786.4	786.9	787.9	789.9	791.9	793.9	795.9
145°	808.3	808.1	808.0	807.8	807.7	807.6	808.9	811.5	814.2	816.8	819.4
147.5°	831.2	830.7	830.3	829.8	829.3	829.1	830.4	833.0	835.7	838.3	840.9
150°	853.3	852.2	851.2	850.1	849.0	848.5	849.7	852.2	854.7	857.1	859.6
152.5°	872.1	870.9	869.6	868.4	867.1	866.5	867.7	870.0	872.3	874.6	876.9
155°	890.1	888.7	887.3	885.9	884.5	883.8	884.7	886.6	888.4	890.3	892.1
157.5°	904.6	903.4	902.2	900.9	899.7	899.1	899.8	901.2	902.5	903.9	905.3
160°	917.1	916.2	915.2	914.3	913.4	912.9	913.4	914.3	915.2	916.2	917.1
162.5°	928.2	927.3	926.3	925.4	924.5	924.0	924.4	925.2	925.9	926.7	927.5
165°	937.9	937.0	936.0	935.1	934.2	933.7	933.9	934.4	934.9	935.3	935.8
167.5°	945.5	944.6	943.6	942.7	941.8	941.3	941.5	942.0	942.5	942.9	943.4
170°	951.7	950.8	949.9	949.0	948.1	947.6	947.7	948.0	948.3	948.6	948.9
172.5°	955.9	955.0	954.0	953.1	952.2	951.7	951.9	952.2	952.5	952.8	953.1
175°	959.3	958.2	957.2	956.1	955.0	954.5	954.7	955.0	955.3	955.6	955.9
177.5°	960.7	959.6	958.6	957.5	956.4	955.9	956.0	956.1	956.3	956.4	956.6
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	653.1	654.0	655.3	661.4	662.3	664.1	663.2	663.2	663.6	662.7	663.2
5°	681.1	682.5	689.0	696.5	698.2	696.5	698.7	701.7	701.7	701.7	700.9
7.5°	707.4	712.3	719.7	730.7	732.9	735.1	739.0	736.4	737.3	741.2	739.9
10°	732.9	739.9	748.2	757.4	762.2	765.3	767.1	771.0	780.2	769.7	773.6
12.5°	757.0	767.1	775.8	785.9	789.4	793.4	794.7	798.2	798.2	797.7	800.8
15°	772.8	782.0	789.9	796.4	797.3	796.4	795.5	796.0	797.3	792.0	795.1
17.5°	776.3	777.1	779.8	777.1	777.6	768.4	763.1	761.8	749.5	750.0	760.0
20°	759.2	744.3	740.3	725.9	717.1	693.4	692.5	686.0	660.1	668.0	666.2
22.5°	712.3	686.8	653.1	636.4	628.1	603.1	583.8	570.3	561.0	551.8	547.9
25°	650.5	609.3	561.5	528.6	523.8	500.6	465.1	448.4	428.7	422.5	433.1
27.5°	570.7	517.2	463.3	412.9	403.7	382.7	364.7	352.8	330.1	328.7	329.6
30°	462.4	408.5	363.4	330.5	307.7	298.1	286.2	277.5	268.3	271.8	272.6
32.5°	380.0	328.7	286.7	269.1	258.6	252.5	242.4	236.7	232.7	231.4	231.0
35°	302.0	267.8	249.0	231.9	225.7	221.4	213.9	211.3	207.8	208.2	208.2
37.5°	258.6	230.1	216.1	207.3	201.6	199.4	194.6	192.0	189.8	188.9	190.2
40°	223.1	203.4	194.6	186.7	181.9	181.0	178.4	175.3	172.7	173.1	174.5
42.5°	197.2	185.8	175.3	169.2	165.7	164.4	162.2	160.0	160.0	158.7	158.2
45°	176.6	167.4	158.7	153.0	150.8	149.0	146.4	146.0	144.2	144.6	145.1
47.5°	158.2	150.8	144.2	138.5	136.3	135.9	133.2	131.5	131.5	131.1	130.6
50°	141.6	134.1	128.4	125.4	122.3	121.4	121.0	120.5	119.7	119.7	120.1
52.5°	128.0	120.5	116.2	113.5	111.8	110.9	110.9	110.5	110.5	110.5	110.0
55°	113.1	106.9	103.4	102.6	101.7	101.3	100.8	99.9	99.5	100.4	99.5
57.5°	99.1	96.9	93.8	92.9	90.7	90.7	89.4	88.5	87.7	88.5	88.5
60°	88.1	85.0	83.3	80.7	78.9	77.1	75.0	74.5	73.6	73.2	72.8
62.5°	76.7	74.1	69.7	65.7	63.1	61.4	60.5	60.0	60.0	59.6	59.6
65°	64.0	57.9	55.7	54.4	53.9	53.5	52.6	52.2	52.6	52.2	52.6
67.5°	50.0	49.1	47.8	46.9	46.5	46.0	46.0	45.6	45.6	45.6	45.6
70°	43.4	41.2	40.8	39.9	39.9	39.4	39.4	39.4	39.4	39.0	39.9
72.5°	35.9	34.6	34.2	33.8	33.8	33.8	33.3	33.3	33.3	32.9	33.3
75°	29.4	28.9	28.1	28.1	27.6	28.1	27.6	27.6	27.2	27.6	27.6
77.5°	23.7	23.2	22.8	22.8	22.4	22.4	22.4	22.4	22.4	22.4	22.8
80°	18.0	17.5	17.1	17.5	17.1	17.5	17.1	17.1	17.5	17.1	17.1
82.5°	13.1	12.7	12.7	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
85°	7.9	7.5	7.5	7.9	7.5	7.9	7.5	7.5	7.5	7.9	7.9
87.5°	3.5	3.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.9
90°	14.7	15.4	16.2	16.9	17.3	17.5	17.8	18.1	18.4	18.7	18.4
92.5°	16.9	17.2	17.5	17.8	18.0	18.1	18.2	18.4	18.5	18.7	18.5
95°	27.8	28.6	29.3	30.1	30.5	30.4	30.3	30.1	30.0	29.8	30.0
97.5°	35.8	36.2	36.7	37.2	37.4	37.5	37.6	37.8	37.9	38.1	37.9
100°	40.7	41.9	43.2	44.4	45.0	45.2	45.5	45.8	46.1	46.4	46.1
102.5°	42.6	44.3	46.0	47.7	48.5	48.7	49.2	49.7	50.1	50.6	50.1
105°	44.0	45.7	47.4	49.1	49.9	50.2	50.8	51.4	52.0	52.6	52.0
107.5°	45.3	47.0	48.7	50.4	51.3	51.6	52.2	52.8	53.4	54.0	53.4
110°	105.8	90.4	75.0	59.6	51.9	52.2	52.8	53.5	54.1	54.7	54.1

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	285.5	219.2	152.8	86.5	53.3	53.5	54.0	54.5	54.9	55.4	54.9
115°	356.1	284.9	213.6	142.3	106.7	101.2	90.1	79.0	67.9	56.8	67.9
117.5°	442.8	420.8	398.7	376.7	365.7	345.5	305.2	264.9	224.5	184.2	224.5
120°	509.5	511.4	513.2	515.1	516.0	505.6	484.8	464.1	443.3	422.5	443.3
122.5°	549.5	550.4	551.3	552.2	552.7	552.8	552.9	553.1	553.2	553.4	553.2
125°	586.4	587.4	588.5	589.6	590.1	590.3	590.8	591.3	591.7	592.2	591.7
127.5°	620.8	622.3	623.9	625.4	626.2	626.3	626.4	626.6	626.7	626.9	626.7
130°	653.5	655.2	656.9	658.6	659.4	659.3	659.2	659.0	658.9	658.7	658.9
132.5°	685.7	687.1	688.5	689.9	690.6	690.5	690.4	690.2	690.1	689.9	690.1
135°	715.7	717.2	718.8	720.3	721.1	720.9	720.6	720.3	720.0	719.7	720.0
137.5°	744.1	745.6	747.2	748.7	749.5	749.3	748.8	748.3	747.9	747.4	747.9
140°	771.6	773.0	774.4	775.8	776.5	776.1	775.3	774.6	773.8	773.0	773.8
142.5°	797.1	798.3	799.6	800.8	801.4	801.0	800.2	799.5	798.7	797.9	798.7
145°	820.5	821.6	822.7	823.8	824.3	823.9	823.1	822.4	821.6	820.8	821.6
147.5°	841.7	842.4	843.2	843.9	844.3	844.0	843.4	842.8	842.2	841.6	842.2
150°	860.5	861.4	862.3	863.2	863.7	863.3	862.6	861.8	861.1	860.3	861.1
152.5°	877.8	878.8	879.7	880.6	881.1	880.6	879.5	878.4	877.3	876.2	877.3
155°	893.0	894.0	894.9	895.8	896.3	895.7	894.5	893.2	892.0	890.8	892.0
157.5°	906.4	907.4	908.5	909.6	910.1	909.5	908.3	907.0	905.8	904.6	905.8
160°	918.0	918.9	919.8	920.7	921.2	920.7	919.6	918.5	917.5	916.4	917.5
162.5°	928.6	929.6	930.7	931.8	932.3	931.6	930.2	928.9	927.5	926.1	927.5
165°	936.9	937.9	939.0	940.1	940.6	940.1	939.0	937.9	936.9	935.8	936.9
167.5°	944.5	945.5	946.6	947.7	948.2	947.5	946.1	944.8	943.4	942.0	943.4
170°	950.0	951.1	952.2	953.3	953.8	953.1	951.7	950.4	949.0	947.6	949.0
172.5°	954.2	955.2	956.3	957.4	957.9	957.2	955.8	954.5	953.1	951.7	953.1
175°	957.0	958.0	959.1	960.2	960.7	959.9	958.4	956.9	955.3	953.8	955.3
177.5°	957.7	958.7	959.8	960.9	961.4	960.7	959.3	958.0	956.6	955.2	956.6
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	664.9	661.9	661.0	661.9	661.0	661.4	658.4	647.0	650.0	645.2	647.8
5°	702.6	700.0	694.3	693.4	692.5	691.7	687.3	677.2	673.3	666.7	666.2
7.5°	738.6	738.6	734.2	731.1	727.2	724.1	718.4	703.5	697.4	689.5	685.1
10°	774.1	762.7	767.5	764.4	754.8	753.0	742.5	733.7	721.9	714.0	707.0
12.5°	799.5	796.0	791.6	789.0	786.3	780.6	773.6	751.3	745.1	729.4	721.5
15°	798.6	796.4	797.7	797.7	796.9	795.5	789.9	773.6	763.1	747.8	734.2
17.5°	755.7	761.4	767.1	771.0	779.8	783.7	789.0	779.3	772.8	759.6	745.1
20°	680.7	694.7	711.4	714.9	722.8	746.0	756.5	764.9	767.5	763.1	751.3
22.5°	576.4	588.2	628.6	627.7	639.1	666.7	697.4	722.4	742.1	753.0	748.6
25°	451.5	468.1	489.6	505.8	543.1	584.3	622.4	662.3	696.5	726.7	734.2
27.5°	341.5	363.4	380.5	401.9	420.8	469.4	518.5	580.8	620.7	678.1	707.9
30°	276.1	286.2	303.3	313.4	322.6	359.9	415.5	476.9	547.0	613.2	664.5
32.5°	235.8	242.8	255.5	259.9	269.6	294.6	329.6	385.7	458.0	538.3	605.8
35°	211.7	219.2	221.8	225.7	233.6	249.4	273.5	314.3	379.6	458.0	538.7
37.5°	191.1	195.1	202.5	205.1	207.8	219.6	235.8	264.3	307.7	372.1	461.6
40°	176.6	178.8	182.8	185.0	186.7	195.1	209.5	228.8	260.8	309.9	392.3
42.5°	161.3	163.9	166.6	169.2	171.4	178.0	186.7	205.1	226.6	263.9	323.5
45°	146.4	148.2	151.2	153.0	156.0	161.3	169.2	181.9	201.2	224.9	273.1
47.5°	132.8	135.0	136.3	138.5	140.7	146.4	153.9	162.2	178.0	201.2	236.3
50°	120.5	123.2	124.9	125.4	127.1	132.4	138.5	147.7	157.8	175.8	206.4
52.5°	111.8	112.2	113.5	115.3	114.8	117.9	123.6	130.6	141.1	155.6	178.0
55°	101.7	103.0	103.9	104.3	104.3	106.9	110.0	116.6	124.9	136.8	155.6
57.5°	89.0	90.3	92.9	93.8	95.1	96.4	97.7	102.1	109.1	120.5	135.9
60°	75.8	76.7	79.3	81.1	82.0	85.5	87.2	90.7	94.7	103.0	117.5
62.5°	60.9	61.8	63.1	64.9	66.6	71.9	76.3	79.8	82.8	88.5	100.4
65°	53.0	53.5	54.4	54.8	55.2	57.4	61.4	66.2	71.9	76.3	83.3
67.5°	46.0	46.5	46.9	47.8	48.2	48.7	50.4	51.7	57.4	63.6	68.8
70°	39.4	40.3	40.8	40.8	41.2	42.1	43.0	44.7	46.5	49.5	56.1
72.5°	33.3	33.8	34.6	34.6	34.6	35.5	36.4	37.3	38.1	39.9	42.5
75°	27.6	28.5	28.5	28.5	28.9	28.9	29.8	30.7	31.6	32.9	33.8
77.5°	22.8	22.8	22.8	22.8	23.2	23.2	23.7	24.5	25.0	25.4	26.3
80°	17.1	17.5	17.5	17.5	18.0	18.0	18.0	18.8	19.3	19.3	20.2
82.5°	12.7	12.7	12.7	13.1	12.7	13.1	13.1	13.6	13.1	13.6	14.0
85°	7.9	7.9	7.9	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.8
87.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	4.4	3.9	3.9
90°	18.1	17.8	17.5	17.3	16.9	16.2	15.4	14.7	13.9	12.7	11.4
92.5°	18.4	18.2	18.1	18.0	17.8	17.5	17.2	16.9	16.6	16.1	15.7
95°	30.1	30.3	30.4	30.5	30.1	29.3	28.6	27.8	27.0	25.9	24.9
97.5°	37.8	37.6	37.5	37.4	37.2	36.7	36.2	35.8	35.3	32.8	30.4
100°	45.8	45.5	45.2	45.0	44.4	43.2	41.9	40.7	39.5	36.9	34.3
102.5°	49.7	49.2	48.7	48.5	47.7	46.0	44.3	42.6	40.9	68.9	96.9
105°	51.4	50.8	50.2	49.9	49.1	47.4	45.7	44.0	42.3	84.3	126.3
107.5°	52.8	52.2	51.6	51.3	50.4	48.7	47.0	45.3	43.6	95.5	147.4
110°	53.5	52.8	52.2	51.9	59.6	75.0	90.4	105.8	121.2	165.7	210.2

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	54.5	54.0	53.5	53.3	86.5	152.8	219.2	285.5	351.9	354.5	357.1
115°	79.0	90.1	101.2	106.7	142.3	213.6	284.9	356.1	427.4	423.6	419.7
117.5°	264.9	305.2	345.5	365.7	376.7	398.7	420.8	442.8	464.8	462.2	459.6
120°	464.1	484.8	505.6	516.0	515.1	513.2	511.4	509.5	507.7	504.9	502.1
122.5°	553.1	552.9	552.8	552.7	552.2	551.3	550.4	549.5	548.6	545.5	542.4
125°	591.3	590.8	590.3	590.1	589.6	588.5	587.4	586.4	585.3	582.4	579.4
127.5°	626.6	626.4	626.3	626.2	625.4	623.9	622.3	620.8	619.2	616.9	614.6
130°	659.0	659.2	659.3	659.4	658.6	656.9	655.2	653.5	651.8	650.1	648.4
132.5°	690.2	690.4	690.5	690.6	689.9	688.5	687.1	685.7	684.3	682.6	680.9
135°	720.3	720.6	720.9	721.1	720.3	718.8	717.2	715.7	714.1	712.7	711.3
137.5°	748.3	748.8	749.3	749.5	748.7	747.2	745.6	744.1	742.5	741.0	739.4
140°	774.6	775.3	776.1	776.5	775.8	774.4	773.0	771.6	770.2	768.5	766.8
142.5°	799.5	800.2	801.0	801.4	800.8	799.6	798.3	797.1	795.9	793.9	791.9
145°	822.4	823.1	823.9	824.3	823.8	822.7	821.6	820.5	819.4	816.8	814.2
147.5°	842.8	843.4	844.0	844.3	843.9	843.2	842.4	841.7	840.9	838.3	835.7
150°	861.8	862.6	863.3	863.7	863.2	862.3	861.4	860.5	859.6	857.1	854.7
152.5°	878.4	879.5	880.6	881.1	880.6	879.7	878.8	877.8	876.9	874.6	872.3
155°	893.2	894.5	895.7	896.3	895.8	894.9	894.0	893.0	892.1	890.3	888.4
157.5°	907.0	908.3	909.5	910.1	909.6	908.5	907.4	906.4	905.3	903.9	902.5
160°	918.5	919.6	920.7	921.2	920.7	919.8	918.9	918.0	917.1	916.2	915.2
162.5°	928.9	930.2	931.6	932.3	931.8	930.7	929.6	928.6	927.5	926.7	925.9
165°	937.9	939.0	940.1	940.6	940.1	939.0	937.9	936.9	935.8	935.3	934.9
167.5°	944.8	946.1	947.5	948.2	947.7	946.6	945.5	944.5	943.4	942.9	942.5
170°	950.4	951.7	953.1	953.8	953.3	952.2	951.1	950.0	948.9	948.6	948.3
172.5°	954.5	955.8	957.2	957.9	957.4	956.3	955.2	954.2	953.1	952.8	952.5
175°	956.9	958.4	959.9	960.7	960.2	959.1	958.0	957.0	955.9	955.6	955.3
177.5°	958.0	959.3	960.7	961.4	960.9	959.8	958.7	957.7	956.6	956.4	956.3
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	643.9	641.7	641.7	640.4	640.4	633.4	633.4	635.6	632.9	629.9	625.5
5°	660.5	655.7	654.4	652.7	647.0	638.2	634.7	633.4	628.1	621.5	614.1
7.5°	676.3	668.4	664.5	660.5	653.1	640.8	633.8	629.0	621.1	611.0	601.4
10°	691.7	681.6	671.5	666.7	656.2	640.8	630.7	622.9	611.5	597.9	584.3
12.5°	705.7	684.7	682.9	673.3	657.9	640.4	625.0	613.6	599.2	583.4	567.6
15°	718.0	696.5	686.0	677.2	657.0	635.1	618.9	604.9	585.6	567.6	548.3
17.5°	724.1	700.9	693.9	679.4	658.8	630.3	608.4	591.3	570.3	548.8	526.9
20°	730.2	703.1	691.7	681.6	653.5	621.1	596.6	576.8	553.6	528.2	504.1
22.5°	733.3	703.1	689.5	675.5	648.3	611.0	582.1	558.9	531.7	505.8	476.9
25°	728.0	700.4	684.2	669.8	639.1	598.7	565.4	539.1	510.2	480.8	451.5
27.5°	714.9	694.3	675.5	660.5	626.4	583.0	547.9	518.1	488.3	455.4	425.6
30°	690.4	681.1	666.2	649.6	612.3	568.9	527.3	496.6	463.7	430.9	399.7
32.5°	652.2	660.1	650.5	636.0	595.7	549.7	505.4	474.3	438.3	402.8	374.3
35°	605.8	633.8	628.6	618.5	578.1	529.1	484.8	447.1	411.1	375.2	346.7
37.5°	554.9	597.4	601.8	595.7	558.0	508.0	459.4	422.5	385.7	349.3	320.4
40°	485.2	550.5	564.6	567.2	536.9	482.6	431.7	395.8	359.4	323.9	288.9
42.5°	421.2	503.6	521.2	532.1	510.2	457.6	406.3	366.4	330.5	298.5	263.4
45°	361.2	447.1	475.6	489.6	480.0	429.1	376.1	338.8	305.9	276.6	242.8
47.5°	299.4	385.7	425.6	448.0	448.0	400.2	347.1	310.3	278.8	253.8	224.0
50°	258.2	330.1	371.3	400.6	408.5	370.8	320.8	284.9	255.1	227.9	205.1
52.5°	220.0	284.5	318.7	349.3	372.1	339.3	291.5	259.0	229.7	204.3	186.3
55°	190.2	238.4	269.6	303.3	328.7	307.3	263.0	231.4	206.0	185.0	169.6
57.5°	161.7	203.8	229.2	259.0	286.2	270.0	234.5	207.3	185.0	166.6	153.0
60°	137.6	171.8	191.5	214.8	248.5	237.1	207.8	182.8	164.8	148.2	136.8
62.5°	117.0	144.2	160.9	177.5	208.2	202.9	180.1	160.9	145.5	131.5	121.9
65°	96.0	118.3	131.5	146.0	170.5	172.7	154.3	140.7	126.7	114.4	105.6
67.5°	77.6	95.1	106.9	119.2	138.9	145.1	132.4	121.0	109.1	99.1	91.2
70°	62.7	75.0	83.7	93.4	109.6	117.0	110.5	102.6	92.9	84.6	77.6
72.5°	49.5	57.4	62.7	70.1	83.3	90.7	90.3	83.3	76.3	70.6	64.9
75°	36.4	42.5	46.9	51.7	62.2	69.3	71.0	67.9	60.9	56.5	52.2
77.5°	27.6	31.1	33.3	36.8	44.3	50.4	53.0	52.2	47.3	43.8	40.8
80°	21.0	21.9	22.8	24.1	30.2	35.9	37.7	37.3	34.6	33.3	29.8
82.5°	14.9	15.3	15.8	16.2	18.4	23.2	25.0	25.9	23.7	22.4	19.3
85°	8.8	9.2	9.2	10.1	10.5	11.8	14.9	14.9	14.5	12.7	12.3
87.5°	4.4	4.4	3.9	3.9	4.4	4.8	5.7	6.6	5.7	5.3	4.8
90°	10.2	8.9	8.3	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.2	14.7	14.5	14.8	15.4	16.1	16.7	17.3	16.7	16.1	15.4
95°	23.8	22.7	22.2	24.7	29.8	34.9	39.9	45.0	39.9	34.9	29.8
97.5°	27.9	25.4	24.2	30.5	43.1	55.8	68.4	81.0	68.4	55.8	43.1
100°	31.6	29.0	27.7	38.2	59.3	80.4	101.5	122.6	101.5	80.4	59.3
102.5°	124.9	152.9	166.9	167.1	167.4	167.7	168.0	168.3	168.0	167.7	167.4
105°	168.3	210.3	231.3	229.0	224.4	219.8	215.2	210.6	215.2	219.8	224.4
107.5°	199.3	251.2	277.1	275.2	271.3	267.4	263.6	259.7	263.6	267.4	271.3
110°	254.7	299.2	321.4	319.8	316.5	313.3	310.0	306.8	310.0	313.3	316.5

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	359.7	362.3	363.6	362.2	359.5	356.7	354.0	351.2	354.0	356.7	359.5
115°	415.9	412.0	410.1	408.8	406.2	403.5	400.9	398.3	400.9	403.5	406.2
117.5°	456.9	454.3	453.0	451.5	448.4	445.3	442.2	439.1	442.2	445.3	448.4
120°	499.4	496.6	495.2	494.1	491.8	489.5	487.2	484.9	487.2	489.5	491.8
122.5°	539.3	536.2	534.7	533.5	531.0	528.5	526.1	523.6	526.1	528.5	531.0
125°	576.5	573.6	572.1	571.1	569.1	567.1	565.1	563.1	565.1	567.1	569.1
127.5°	612.3	610.0	608.8	607.7	605.6	603.4	601.3	599.1	601.3	603.4	605.6
130°	646.7	645.0	644.2	643.0	640.5	638.0	635.6	633.1	635.6	638.0	640.5
132.5°	679.2	677.5	676.7	675.7	673.7	671.7	669.7	667.7	669.7	671.7	673.7
135°	710.0	708.6	707.9	706.7	704.2	701.7	699.3	696.8	699.3	701.7	704.2
137.5°	737.9	736.4	735.6	734.7	732.8	731.0	729.1	727.3	729.1	731.0	732.8
140°	765.1	763.4	762.6	762.0	760.8	759.5	758.3	757.1	758.3	759.5	760.8
142.5°	789.9	787.9	786.9	786.4	785.3	784.2	783.1	782.0	783.1	784.2	785.3
145°	811.5	808.9	807.6	807.7	807.8	808.0	808.1	808.3	808.1	808.0	807.8
147.5°	833.0	830.4	829.1	829.3	829.8	830.3	830.7	831.2	830.7	830.3	829.8
150°	852.2	849.7	848.5	849.0	850.1	851.2	852.2	853.3	852.2	851.2	850.1
152.5°	870.0	867.7	866.5	867.1	868.4	869.6	870.9	872.1	870.9	869.6	868.4
155°	886.6	884.7	883.8	884.5	885.9	887.3	888.7	890.1	888.7	887.3	885.9
157.5°	901.2	899.8	899.1	899.7	900.9	902.2	903.4	904.6	903.4	902.2	900.9
160°	914.3	913.4	912.9	913.4	914.3	915.2	916.2	917.1	916.2	915.2	914.3
162.5°	925.2	924.4	924.0	924.5	925.4	926.3	927.3	928.2	927.3	926.3	925.4
165°	934.4	933.9	933.7	934.2	935.1	936.0	937.0	937.9	937.0	936.0	935.1
167.5°	942.0	941.5	941.3	941.8	942.7	943.6	944.6	945.5	944.6	943.6	942.7
170°	948.0	947.7	947.6	948.1	949.0	949.9	950.8	951.7	950.8	949.9	949.0
172.5°	952.2	951.9	951.7	952.2	953.1	954.0	955.0	955.9	955.0	954.0	953.1
175°	955.0	954.7	954.5	955.0	956.1	957.2	958.2	959.3	958.2	957.2	956.1
177.5°	956.1	956.0	955.9	956.4	957.5	958.6	959.6	960.7	959.6	958.6	957.5
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	623.7	624.2	625.5	621.5	615.4	612.8	604.9	603.6	602.3	602.3	603.6
5°	609.7	607.9	608.4	600.9	592.2	586.9	576.0	577.7	572.0	568.5	569.4
7.5°	594.4	589.5	589.1	579.5	568.5	558.9	547.5	544.8	539.6	533.4	530.8
10°	575.1	571.6	565.0	554.0	540.0	532.1	516.8	507.6	506.3	497.1	493.5
12.5°	555.4	549.2	542.6	527.3	511.5	498.8	487.4	477.3	470.3	462.4	457.2
15°	532.6	525.1	517.7	501.4	483.0	470.3	453.2	438.3	417.7	401.5	392.3
17.5°	507.6	499.2	489.2	471.2	453.2	435.7	404.1	386.6	372.1	362.5	356.8
20°	481.7	472.5	462.4	444.5	413.3	382.7	365.1	351.5	342.8	333.1	326.1
22.5°	454.5	444.9	433.9	405.9	373.0	351.5	337.9	325.2	312.5	307.3	303.8
25°	429.1	420.3	406.3	368.2	342.3	322.6	307.3	298.9	292.4	285.3	278.8
27.5°	402.8	386.6	366.9	334.9	318.7	298.5	287.5	281.4	270.0	265.2	262.1
30°	371.3	353.3	334.4	311.6	292.8	278.8	268.7	258.6	252.0	247.2	242.0
32.5°	339.3	322.2	310.3	286.7	272.6	258.2	248.5	242.4	232.7	229.7	227.5
35°	311.6	297.2	286.7	267.4	254.2	241.1	234.1	224.9	218.7	213.0	209.5
37.5°	284.5	276.6	265.6	249.4	235.4	224.9	215.2	212.1	203.8	200.8	197.2
40°	265.6	253.8	244.6	230.6	218.7	207.3	201.2	194.2	188.5	183.7	182.3
42.5°	242.8	234.1	228.8	213.5	201.2	194.6	187.2	179.3	174.9	170.9	166.1
45°	225.7	217.8	210.4	198.1	187.2	178.8	172.3	167.0	159.5	157.8	150.3
47.5°	207.8	199.9	194.2	181.9	171.8	163.9	159.1	152.1	146.0	142.0	138.5
50°	189.8	183.2	178.0	167.4	158.7	150.3	143.8	136.8	134.1	127.6	125.4
52.5°	172.7	168.3	162.6	152.5	143.8	136.8	129.7	124.0	120.1	116.6	114.0
55°	158.2	151.2	148.6	137.6	130.2	122.7	116.6	113.1	108.3	106.1	103.9
57.5°	142.0	138.1	133.7	125.4	117.0	110.0	105.6	100.4	97.7	95.1	93.4
60°	128.0	122.3	118.8	111.8	104.3	97.7	93.8	89.9	86.3	84.2	80.7
62.5°	111.8	107.4	105.2	97.7	91.6	85.5	82.0	78.0	75.4	71.4	67.1
65°	97.7	94.2	91.6	85.5	79.8	74.1	70.6	65.7	62.2	60.0	59.6
67.5°	85.5	82.8	78.9	73.2	67.5	63.1	59.2	55.2	54.8	53.9	53.9
70°	71.9	69.3	67.1	60.9	56.1	51.3	50.4	49.1	47.8	47.3	46.5
72.5°	60.0	57.9	55.2	50.0	45.1	43.8	43.0	42.1	40.8	40.3	39.9
75°	48.7	45.6	43.8	39.0	37.7	36.8	35.9	34.6	33.8	33.3	32.4
77.5°	37.3	34.2	34.2	31.6	30.7	29.4	28.5	27.6	27.2	26.3	26.3
80°	26.3	26.3	25.4	24.1	22.8	22.4	21.0	20.6	20.2	20.6	19.7
82.5°	19.3	17.5	17.5	16.7	15.8	15.3	14.5	14.5	14.0	14.0	14.0
85°	11.0	11.0	10.5	9.6	9.2	9.2	8.8	8.8	8.3	8.3	7.9
87.5°	4.4	3.9	4.4	3.9	3.9	3.5	3.5	3.5	3.1	3.5	3.1
90°	7.5	8.3	8.9	10.2	11.4	12.7	13.9	14.7	15.4	16.2	16.9
92.5°	14.8	14.5	14.7	15.2	15.7	16.1	16.6	16.9	17.2	17.5	17.8
95°	24.7	22.2	22.7	23.8	24.9	25.9	27.0	27.8	28.6	29.3	30.1
97.5°	30.5	24.2	25.4	27.9	30.4	32.8	35.3	35.8	36.2	36.7	37.2
100°	38.2	27.7	29.0	31.6	34.3	36.9	39.5	40.7	41.9	43.2	44.4
102.5°	167.1	166.9	152.9	124.9	96.9	68.9	40.9	42.6	44.3	46.0	47.7
105°	229.0	231.3	210.3	168.3	126.3	84.3	42.3	44.0	45.7	47.4	49.1
107.5°	275.2	277.1	251.2	199.3	147.4	95.5	43.6	45.3	47.0	48.7	50.4
110°	319.8	321.4	299.2	254.7	210.2	165.7	121.2	105.8	90.4	75.0	59.6

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	362.2	363.6	362.3	359.7	357.1	354.5	351.9	285.5	219.2	152.8	86.5
115°	408.8	410.1	412.0	415.9	419.7	423.6	427.4	356.1	284.9	213.6	142.3
117.5°	451.5	453.0	454.3	456.9	459.6	462.2	464.8	442.8	420.8	398.7	376.7
120°	494.1	495.2	496.6	499.4	502.1	504.9	507.7	509.5	511.4	513.2	515.1
122.5°	533.5	534.7	536.2	539.3	542.4	545.5	548.6	549.5	550.4	551.3	552.2
125°	571.1	572.1	573.6	576.5	579.4	582.4	585.3	586.4	587.4	588.5	589.6
127.5°	607.7	608.8	610.0	612.3	614.6	616.9	619.2	620.8	622.3	623.9	625.4
130°	643.0	644.2	645.0	646.7	648.4	650.1	651.8	653.5	655.2	656.9	658.6
132.5°	675.7	676.7	677.5	679.2	680.9	682.6	684.3	685.7	687.1	688.5	689.9
135°	706.7	707.9	708.6	710.0	711.3	712.7	714.1	715.7	717.2	718.8	720.3
137.5°	734.7	735.6	736.4	737.9	739.4	741.0	742.5	744.1	745.6	747.2	748.7
140°	762.0	762.6	763.4	765.1	766.8	768.5	770.2	771.6	773.0	774.4	775.8
142.5°	786.4	786.9	787.9	789.9	791.9	793.9	795.9	797.1	798.3	799.6	800.8
145°	807.7	807.6	808.9	811.5	814.2	816.8	819.4	820.5	821.6	822.7	823.8
147.5°	829.3	829.1	830.4	833.0	835.7	838.3	840.9	841.7	842.4	843.2	843.9
150°	849.0	848.5	849.7	852.2	854.7	857.1	859.6	860.5	861.4	862.3	863.2
152.5°	867.1	866.5	867.7	870.0	872.3	874.6	876.9	877.8	878.8	879.7	880.6
155°	884.5	883.8	884.7	886.6	888.4	890.3	892.1	893.0	894.0	894.9	895.8
157.5°	899.7	899.1	899.8	901.2	902.5	903.9	905.3	906.4	907.4	908.5	909.6
160°	913.4	912.9	913.4	914.3	915.2	916.2	917.1	918.0	918.9	919.8	920.7
162.5°	924.5	924.0	924.4	925.2	925.9	926.7	927.5	928.6	929.6	930.7	931.8
165°	934.2	933.7	933.9	934.4	934.9	935.3	935.8	936.9	937.9	939.0	940.1
167.5°	941.8	941.3	941.5	942.0	942.5	942.9	943.4	944.5	945.5	946.6	947.7
170°	948.1	947.6	947.7	948.0	948.3	948.6	948.9	950.0	951.1	952.2	953.3
172.5°	952.2	951.7	951.9	952.2	952.5	952.8	953.1	954.2	955.2	956.3	957.4
175°	955.0	954.5	954.7	955.0	955.3	955.6	955.9	957.0	958.0	959.1	960.2
177.5°	956.4	955.9	956.0	956.1	956.3	956.4	956.6	957.7	958.7	959.8	960.9
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	603.6	602.7	600.1	600.9	599.6	599.6	598.7	598.7	598.7	600.9	599.6
5°	570.7	567.6	564.6	563.2	561.9	560.6	560.6	560.2	564.1	563.2	566.7
7.5°	529.9	529.1	522.9	522.9	520.7	519.8	522.0	522.5	522.9	523.8	526.0
10°	493.5	491.4	482.6	483.5	482.2	480.4	481.7	480.8	483.9	484.8	483.9
12.5°	450.6	446.6	437.0	432.2	426.9	423.0	427.8	424.3	436.6	440.1	449.7
15°	393.6	386.2	379.6	379.6	374.8	371.3	373.4	377.4	380.0	384.0	385.7
17.5°	355.5	352.4	347.1	344.1	342.8	341.5	341.5	343.2	348.9	348.5	352.0
20°	323.0	321.3	318.7	314.7	313.4	312.5	312.5	312.5	316.5	320.0	322.2
22.5°	300.7	299.4	297.6	292.4	289.7	288.9	291.0	292.4	295.4	298.1	300.2
25°	278.3	275.3	272.2	270.4	269.1	269.1	270.0	270.4	271.8	273.1	275.7
27.5°	259.9	257.7	253.3	248.5	248.5	247.2	248.1	249.0	252.0	256.4	258.6
30°	239.3	238.9	237.1	235.4	233.6	232.7	234.5	235.8	236.3	238.4	238.4
32.5°	224.4	221.4	218.3	216.5	215.7	215.2	215.7	217.4	217.4	220.0	223.1
35°	209.5	207.8	204.7	201.6	200.8	198.6	200.3	202.1	205.1	206.4	207.8
37.5°	193.3	191.1	189.8	188.9	187.2	187.6	186.3	188.9	191.5	191.1	192.0
40°	181.0	177.1	173.1	172.7	172.3	171.8	171.8	172.3	174.0	175.8	178.4
42.5°	165.2	163.9	160.4	156.9	156.0	155.2	154.3	156.0	159.5	162.6	163.9
45°	149.0	147.3	146.4	143.8	142.0	141.6	140.7	142.9	146.0	147.3	148.2
47.5°	134.1	133.7	131.1	131.5	130.2	130.6	130.2	131.5	131.5	132.8	133.7
50°	124.0	122.7	121.4	120.5	119.2	119.2	118.8	119.2	121.0	122.7	122.3
52.5°	114.0	111.8	111.3	110.9	110.0	110.9	109.6	110.0	111.8	112.6	112.2
55°	102.1	101.7	100.8	99.9	99.5	99.1	99.1	99.1	100.8	102.1	102.6
57.5°	92.9	90.7	89.0	89.0	87.2	86.8	87.7	88.1	89.4	90.3	91.2
60°	80.2	79.3	76.7	75.4	72.8	72.3	72.3	74.1	76.3	79.3	80.2
62.5°	66.6	65.3	64.9	64.9	64.9	64.9	64.9	64.9	64.9	65.3	65.3
65°	59.2	59.6	59.2	58.7	59.2	59.2	58.7	58.7	58.7	59.2	59.6
67.5°	53.0	52.6	53.0	52.6	52.2	52.2	51.7	52.2	52.6	53.0	53.0
70°	46.0	46.0	45.6	46.0	45.6	45.1	44.7	44.7	45.6	46.0	46.0
72.5°	39.4	39.4	39.0	39.0	38.1	38.1	38.6	38.1	38.1	39.4	39.4
75°	32.9	32.4	32.0	32.0	31.6	31.6	31.6	31.1	32.0	32.0	32.4
77.5°	25.9	25.9	25.9	25.4	25.4	25.0	25.0	25.4	25.4	25.4	25.9
80°	19.7	19.7	19.7	19.3	18.8	18.8	18.8	18.8	18.8	19.3	18.8
82.5°	13.6	13.6	13.6	13.6	13.6	13.1	13.1	13.1	13.6	13.6	13.1
85°	8.3	7.9	8.3	8.3	7.9	8.3	7.9	7.9	7.5	7.5	7.9
87.5°	3.5	3.1	2.6	2.6	3.1	2.6	2.6	2.6	3.1	2.6	2.6
90°	17.3	17.5	17.8	18.1	18.4	18.7	18.4	18.1	17.8	17.5	17.3
92.5°	18.0	18.1	18.2	18.4	18.5	18.7	18.5	18.4	18.2	18.1	18.0
95°	30.5	30.4	30.3	30.1	30.0	29.8	30.0	30.1	30.3	30.4	30.5
97.5°	37.4	37.5	37.6	37.8	37.9	38.1	37.9	37.8	37.6	37.5	37.4
100°	45.0	45.2	45.5	45.8	46.1	46.4	46.1	45.8	45.5	45.2	45.0
102.5°	48.5	48.7	49.2	49.7	50.1	50.6	50.1	49.7	49.2	48.7	48.5
105°	49.9	50.2	50.8	51.4	52.0	52.6	52.0	51.4	50.8	50.2	49.9
107.5°	51.3	51.6	52.2	52.8	53.4	54.0	53.4	52.8	52.2	51.6	51.3
110°	51.9	52.2	52.8	53.5	54.1	54.7	54.1	53.5	52.8	52.2	51.9

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	53.3	53.5	54.0	54.5	54.9	55.4	54.9	54.5	54.0	53.5	53.3
115°	106.7	101.2	90.1	79.0	67.9	56.8	67.9	79.0	90.1	101.2	106.7
117.5°	365.7	345.5	305.2	264.9	224.5	184.2	224.5	264.9	305.2	345.5	365.7
120°	516.0	505.6	484.8	464.1	443.3	422.5	443.3	464.1	484.8	505.6	516.0
122.5°	552.7	552.8	552.9	553.1	553.2	553.4	553.2	553.1	552.9	552.8	552.7
125°	590.1	590.3	590.8	591.3	591.7	592.2	591.7	591.3	590.8	590.3	590.1
127.5°	626.2	626.3	626.4	626.6	626.7	626.9	626.7	626.6	626.4	626.3	626.2
130°	659.4	659.3	659.2	659.0	658.9	658.7	658.9	659.0	659.2	659.3	659.4
132.5°	690.6	690.5	690.4	690.2	690.1	689.9	690.1	690.2	690.4	690.5	690.6
135°	721.1	720.9	720.6	720.3	720.0	719.7	720.0	720.3	720.6	720.9	721.1
137.5°	749.5	749.3	748.8	748.3	747.9	747.4	747.9	748.3	748.8	749.3	749.5
140°	776.5	776.1	775.3	774.6	773.8	773.0	773.8	774.6	775.3	776.1	776.5
142.5°	801.4	801.0	800.2	799.5	798.7	797.9	798.7	799.5	800.2	801.0	801.4
145°	824.3	823.9	823.1	822.4	821.6	820.8	821.6	822.4	823.1	823.9	824.3
147.5°	844.3	844.0	843.4	842.8	842.2	841.6	842.2	842.8	843.4	844.0	844.3
150°	863.7	863.3	862.6	861.8	861.1	860.3	861.1	861.8	862.6	863.3	863.7
152.5°	881.1	880.6	879.5	878.4	877.3	876.2	877.3	878.4	879.5	880.6	881.1
155°	896.3	895.7	894.5	893.2	892.0	890.8	892.0	893.2	894.5	895.7	896.3
157.5°	910.1	909.5	908.3	907.0	905.8	904.6	905.8	907.0	908.3	909.5	910.1
160°	921.2	920.7	919.6	918.5	917.5	916.4	917.5	918.5	919.6	920.7	921.2
162.5°	932.3	931.6	930.2	928.9	927.5	926.1	927.5	928.9	930.2	931.6	932.3
165°	940.6	940.1	939.0	937.9	936.9	935.8	936.9	937.9	939.0	940.1	940.6
167.5°	948.2	947.5	946.1	944.8	943.4	942.0	943.4	944.8	946.1	947.5	948.2
170°	953.8	953.1	951.7	950.4	949.0	947.6	949.0	950.4	951.7	953.1	953.8
172.5°	957.9	957.2	955.8	954.5	953.1	951.7	953.1	954.5	955.8	957.2	957.9
175°	960.7	959.9	958.4	956.9	955.3	953.8	955.3	956.9	958.4	959.9	960.7
177.5°	961.4	960.7	959.3	958.0	956.6	955.2	956.6	958.0	959.3	960.7	961.4
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	600.9	603.1	602.3	597.4	602.3	603.6	606.2	608.8	610.6	613.2	615.4
5°	563.2	567.6	570.3	567.6	576.4	577.7	583.8	587.3	592.6	597.0	600.5
7.5°	527.7	531.2	536.5	537.4	542.6	548.8	557.5	566.3	574.6	579.0	583.0
10°	489.6	495.7	503.6	501.9	509.8	519.4	528.6	542.6	549.7	557.5	564.6
12.5°	451.5	455.4	465.9	469.4	480.8	488.3	501.0	509.8	527.3	536.5	542.6
15°	384.8	401.1	414.2	430.0	444.9	458.9	470.3	486.1	501.4	508.5	518.5
17.5°	354.6	362.1	369.9	377.8	397.1	422.1	442.3	459.4	472.5	481.7	493.5
20°	323.0	330.5	339.3	346.7	358.5	376.5	401.5	430.9	446.6	456.3	467.7
22.5°	300.7	307.7	313.4	320.0	329.2	342.3	361.2	397.6	418.6	430.4	440.5
25°	276.6	285.3	291.5	296.3	303.8	318.2	333.6	354.2	391.9	401.1	415.1
27.5°	259.9	262.6	269.6	277.0	284.5	292.4	308.1	325.7	351.1	371.3	388.4
30°	240.2	246.8	253.3	256.4	263.0	274.4	284.0	302.9	322.6	338.4	359.0
32.5°	225.3	229.2	233.6	241.1	247.2	255.1	264.7	280.5	297.2	307.3	323.0
35°	208.6	211.3	220.5	223.5	229.7	237.6	247.2	259.5	277.5	285.3	296.7
37.5°	192.9	199.0	201.6	208.6	214.3	222.2	229.2	243.3	255.1	264.3	274.8
40°	180.6	183.2	188.0	194.2	199.0	205.1	213.9	224.0	236.7	244.1	253.3
42.5°	165.7	167.9	174.0	177.5	185.4	191.1	196.4	208.6	220.0	225.7	234.9
45°	149.5	154.7	158.7	165.7	170.1	177.1	183.7	192.4	202.9	209.5	214.8
47.5°	135.4	140.7	144.6	151.2	158.2	161.3	168.3	177.5	187.2	192.4	199.9
50°	124.0	125.8	133.2	136.3	143.8	149.9	154.7	162.6	173.1	176.2	182.3
52.5°	113.1	114.4	119.2	123.2	129.7	135.0	141.1	148.6	157.4	162.2	167.0
55°	103.4	104.3	106.5	110.9	115.3	121.9	127.6	134.6	142.0	147.3	151.7
57.5°	92.5	94.2	96.0	98.6	103.0	109.1	115.3	121.9	128.0	131.5	137.2
60°	79.8	82.4	85.5	88.5	91.6	96.0	103.0	109.1	114.8	117.9	122.3
62.5°	66.2	71.4	74.1	77.6	80.2	84.2	89.4	96.4	100.4	104.3	107.8
65°	59.6	60.0	60.5	64.0	68.8	72.8	77.6	82.8	89.0	91.6	94.2
67.5°	53.0	53.5	54.4	54.8	56.5	60.9	66.2	71.9	76.7	78.5	81.1
70°	46.5	46.5	48.2	48.7	49.1	49.5	53.9	59.6	64.0	66.2	69.3
72.5°	39.4	39.9	40.8	41.2	42.1	43.0	44.3	47.3	52.6	54.8	58.3
75°	32.4	32.9	33.3	33.8	35.1	35.5	36.8	38.6	40.8	43.4	45.6
77.5°	25.9	25.9	26.3	27.2	28.1	28.5	29.8	30.7	31.6	32.9	34.6
80°	19.3	19.7	19.7	20.6	20.6	21.0	21.5	22.8	23.7	24.5	25.4
82.5°	13.1	14.0	14.0	14.0	14.5	14.9	15.3	15.3	16.2	16.7	18.0
85°	7.9	8.3	8.3	8.3	7.9	8.8	8.8	9.2	9.2	9.2	9.6
87.5°	3.1	2.6	3.1	3.1	3.1	3.5	3.1	3.1	3.5	3.9	3.9
90°	16.9	16.2	15.4	14.7	13.9	12.7	11.4	10.2	8.9	8.3	7.5
92.5°	17.8	17.5	17.2	16.9	16.6	16.1	15.7	15.2	14.7	14.5	14.8
95°	30.1	29.3	28.6	27.8	27.0	25.9	24.9	23.8	22.7	22.2	24.7
97.5°	37.2	36.7	36.2	35.8	35.3	32.8	30.4	27.9	25.4	24.2	30.5
100°	44.4	43.2	41.9	40.7	39.5	36.9	34.3	31.6	29.0	27.7	38.2
102.5°	47.7	46.0	44.3	42.6	40.9	68.9	96.9	124.9	152.9	166.9	167.1
105°	49.1	47.4	45.7	44.0	42.3	84.3	126.3	168.3	210.3	231.3	229.0
107.5°	50.4	48.7	47.0	45.3	43.6	95.5	147.4	199.3	251.2	277.1	275.2
110°	59.6	75.0	90.4	105.8	121.2	165.7	210.2	254.7	299.2	321.4	319.8

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	86.5	152.8	219.2	285.5	351.9	354.5	357.1	359.7	362.3	363.6	362.2
115°	142.3	213.6	284.9	356.1	427.4	423.6	419.7	415.9	412.0	410.1	408.8
117.5°	376.7	398.7	420.8	442.8	464.8	462.2	459.6	456.9	454.3	453.0	451.5
120°	515.1	513.2	511.4	509.5	507.7	504.9	502.1	499.4	496.6	495.2	494.1
122.5°	552.2	551.3	550.4	549.5	548.6	545.5	542.4	539.3	536.2	534.7	533.5
125°	589.6	588.5	587.4	586.4	585.3	582.4	579.4	576.5	573.6	572.1	571.1
127.5°	625.4	623.9	622.3	620.8	619.2	616.9	614.6	612.3	610.0	608.8	607.7
130°	658.6	656.9	655.2	653.5	651.8	650.1	648.4	646.7	645.0	644.2	643.0
132.5°	689.9	688.5	687.1	685.7	684.3	682.6	680.9	679.2	677.5	676.7	675.7
135°	720.3	718.8	717.2	715.7	714.1	712.7	711.3	710.0	708.6	707.9	706.7
137.5°	748.7	747.2	745.6	744.1	742.5	741.0	739.4	737.9	736.4	735.6	734.7
140°	775.8	774.4	773.0	771.6	770.2	768.5	766.8	765.1	763.4	762.6	762.0
142.5°	800.8	799.6	798.3	797.1	795.9	793.9	791.9	789.9	787.9	786.9	786.4
145°	823.8	822.7	821.6	820.5	819.4	816.8	814.2	811.5	808.9	807.6	807.7
147.5°	843.9	843.2	842.4	841.7	840.9	838.3	835.7	833.0	830.4	829.1	829.3
150°	863.2	862.3	861.4	860.5	859.6	857.1	854.7	852.2	849.7	848.5	849.0
152.5°	880.6	879.7	878.8	877.8	876.9	874.6	872.3	870.0	867.7	866.5	867.1
155°	895.8	894.9	894.0	893.0	892.1	890.3	888.4	886.6	884.7	883.8	884.5
157.5°	909.6	908.5	907.4	906.4	905.3	903.9	902.5	901.2	899.8	899.1	899.7
160°	920.7	919.8	918.9	918.0	917.1	916.2	915.2	914.3	913.4	912.9	913.4
162.5°	931.8	930.7	929.6	928.6	927.5	926.7	925.9	925.2	924.4	924.0	924.5
165°	940.1	939.0	937.9	936.9	935.8	935.3	934.9	934.4	933.9	933.7	934.2
167.5°	947.7	946.6	945.5	944.5	943.4	942.9	942.5	942.0	941.5	941.3	941.8
170°	953.3	952.2	951.1	950.0	948.9	948.6	948.3	948.0	947.7	947.6	948.1
172.5°	957.4	956.3	955.2	954.2	953.1	952.8	952.5	952.2	951.9	951.7	952.2
175°	960.2	959.1	958.0	957.0	955.9	955.6	955.3	955.0	954.7	954.5	955.0
177.5°	960.9	959.8	958.7	957.7	956.6	956.4	956.3	956.1	956.0	955.9	956.4
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	630.7	630.7	630.7	630.7
2.5°	619.3	618.0	625.9	634.7
5°	606.6	608.8	618.9	631.2
7.5°	593.5	598.3	610.1	626.4
10°	575.1	583.8	601.8	618.5
12.5°	557.1	568.9	586.0	605.8
15°	536.9	550.1	571.1	594.8
17.5°	514.6	529.5	554.0	579.9
20°	490.9	510.6	536.5	564.6
22.5°	464.6	488.3	515.0	546.1
25°	439.2	465.1	491.8	527.7
27.5°	414.2	439.6	469.4	505.8
30°	389.2	412.5	444.5	483.5
32.5°	362.5	386.6	420.3	460.2
35°	337.9	362.1	393.6	433.1
37.5°	311.6	337.5	367.8	408.5
40°	281.0	311.2	340.6	379.6
42.5°	255.5	287.5	316.0	352.8
45°	235.4	265.6	289.3	325.2
47.5°	216.5	241.1	265.2	298.5
50°	198.6	217.4	242.4	272.2
52.5°	180.1	196.4	217.8	245.9
55°	163.5	178.8	198.1	219.6
57.5°	148.2	159.1	178.4	197.7
60°	131.1	142.5	157.4	173.6
62.5°	116.6	125.4	139.4	153.0
65°	101.3	109.6	120.1	132.8
67.5°	87.2	94.7	103.0	113.1
70°	74.5	80.2	86.3	95.1
72.5°	60.9	67.1	72.8	79.8
75°	50.0	52.6	57.4	62.2
77.5°	38.6	42.1	44.7	48.7
80°	27.6	30.7	31.6	34.6
82.5°	18.4	20.2	21.9	22.8
85°	10.5	11.4	13.1	13.6
87.5°	3.9	4.4	5.3	6.1
90°	5.8	4.1	2.4	0.7
92.5°	15.4	16.1	16.7	17.3
95°	29.8	34.9	39.9	45.0
97.5°	43.1	55.8	68.4	81.0
100°	59.3	80.4	101.5	122.6
102.5°	167.4	167.7	168.0	168.3
105°	224.4	219.8	215.2	210.6
107.5°	271.3	267.4	263.6	259.7
110°	316.5	313.3	310.0	306.8

TEST NUMBER: P999585

CATALOG NUMBER: SA2XXRDIP-B290D725UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	359.5	356.7	354.0	351.2
115°	406.2	403.5	400.9	398.3
117.5°	448.4	445.3	442.2	439.1
120°	491.8	489.5	487.2	484.9
122.5°	531.0	528.5	526.1	523.6
125°	569.1	567.1	565.1	563.1
127.5°	605.6	603.4	601.3	599.1
130°	640.5	638.0	635.6	633.1
132.5°	673.7	671.7	669.7	667.7
135°	704.2	701.7	699.3	696.8
137.5°	732.8	731.0	729.1	727.3
140°	760.8	759.5	758.3	757.1
142.5°	785.3	784.2	783.1	782.0
145°	807.8	808.0	808.1	808.3
147.5°	829.8	830.3	830.7	831.2
150°	850.1	851.2	852.2	853.3
152.5°	868.4	869.6	870.9	872.1
155°	885.9	887.3	888.7	890.1
157.5°	900.9	902.2	903.4	904.6
160°	914.3	915.2	916.2	917.1
162.5°	925.4	926.3	927.3	928.2
165°	935.1	936.0	937.0	937.9
167.5°	942.7	943.6	944.6	945.5
170°	949.0	949.9	950.8	951.7
172.5°	953.1	954.0	955.0	955.9
175°	956.1	957.2	958.2	959.3
177.5°	957.5	958.6	959.6	960.7
180°	957.2	957.2	957.2	957.2

(END OF REPORT)