

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998610

Luminaire Tested: SA2XXDIP-B485D725UB50-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998610
REPORT IS A COMBINATION OF REPORTS P984353 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D725UB50-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4317.0 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998610

CATALOG NUMBER: SA2XXDIP-B485D725UB50-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P998610

CATALOG NUMBER: SA2XXDIP-B485D725UB50-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	94	89	85	81	85	81	77	74	66	63	61	52	50	48	39	37	36
2	85	77	71	65	77	70	65	60	57	53	49	45	42	39	33	31	30
3	77	68	60	54	70	61	55	49	50	45	41	39	36	33	29	27	25
4	71	59	51	45	64	54	47	42	44	39	34	35	31	28	26	23	21
5	65	53	44	38	58	48	41	35	39	34	29	31	27	24	23	20	18
6	59	47	39	33	54	43	36	30	35	30	25	28	24	21	21	18	16
7	55	42	34	29	49	39	32	27	32	26	22	25	21	18	19	16	14
8	51	38	31	25	46	35	28	23	29	23	20	23	19	16	17	15	12
9	47	35	27	22	43	32	25	21	26	21	17	21	17	14	16	13	11
10	44	32	25	20	40	29	23	18	24	19	16	19	15	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7812	7812	7812
5°	7847	7478	7437
10°	7795	7220	7114
15°	7684	6952	6784
20°	7545	6669	6470
25°	7408	6401	6186
30°	7216	6127	5904
35°	7023	5863	5698
40°	6819	5635	5491
45°	6622	5428	5312
50°	6414	5238	5135
55°	6193	5035	4955
60°	5926	4824	4767
65°	5645	4580	4548
70°	5327	4319	4315
75°	4923	4060	4092
80°	4279	3789	3864
85°	3630	3534	3666

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6622 cd/sqm

TEST NUMBER: P998610

CATALOG NUMBER: SA2XXDIP-B485D725UB50-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	1.1
10°-20°	134.2	3.1
20°-30°	203.3	4.7
30°-40°	247.6	5.7
40°-50°	266.4	6.2
50°-60°	258.7	6.0
60°-70°	225.9	5.2
70°-80°	173.9	4.0
80°-90°	118.9	2.8
90°-100°	134.1	3.1
100°-110°	229.7	5.3
110°-120°	331.4	7.7
120°-130°	406.4	9.4
130°-140°	441.1	10.2
140°-150°	425.2	9.8
150°-160°	355.4	8.2
160°-170°	235.7	5.5
170°-180°	82.4	1.9
0°-30°	384.3	8.9
0°-40°	631.8	14.6
0°-60°	1156.9	26.8
0°-90°	1675.5	38.8
90°-120°	695.3	16.1
90°-150°	1968.0	45.6
90°-180°	2641.0	61.2
0°-180°	4317.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	494	494	494	494	494	
5°	495	493	488	493	492	47
15°	472	474	474	480	479	133
25°	429	434	441	449	451	197
35°	370	382	396	411	416	231
45°	303	323	348	370	377	234
55°	232	258	295	321	330	208
65°	159	194	236	265	275	158
75°	88	128	174	204	214	93
85°	26	70	116	146	156	27
90°	8	58	120	147	157	7
95°	44	85	129	156	164	47
105°	161	184	223	249	257	171
115°	296	309	339	360	366	293
125°	428	435	456	473	479	383
135°	553	561	570	584	588	428
145°	671	676	680	685	686	419
155°	767	769	771	775	773	353
165°	834	834	834	839	835	235
175°	868	866	865	870	865	82
180°	870	870	870	870	870	

TEST NUMBER: P998610

CATALOG NUMBER: SA2XXDIP-B485D725UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	493.5	493.5	493.5	493.5	493.5
2.5°	497.1	494.9	489.9	493.5	492.1
5°	494.9	492.8	488.5	492.8	492.1
7.5°	491.3	489.9	486.3	491.3	490.6
10°	487.1	485.6	483.5	489.2	488.5
12.5°	479.9	480.6	479.2	484.9	484.2
15°	472.0	473.5	473.5	479.9	479.2
17.5°	462.0	464.9	467.0	473.5	473.5
20°	452.0	455.6	458.4	466.3	466.3
22.5°	441.3	445.6	449.9	457.7	459.2
25°	429.1	434.1	440.6	449.2	451.3
27.5°	414.8	422.7	429.8	440.6	442.0
30°	400.5	409.8	419.1	430.6	432.7
32.5°	384.8	395.5	407.0	420.5	424.8
35°	369.8	381.9	395.5	411.2	416.3
37.5°	353.3	366.9	384.1	401.2	406.2
40°	336.9	352.6	371.9	390.5	396.9
42.5°	321.1	336.9	359.7	380.5	386.9
45°	303.2	322.6	347.6	369.8	376.9
47.5°	286.1	306.8	335.4	358.3	366.2
50°	268.2	290.4	322.6	346.9	354.7
52.5°	251.0	274.6	309.0	334.0	342.6
55°	232.4	258.2	295.4	321.1	330.4
57.5°	214.6	243.2	280.4	308.3	317.6
60°	195.3	226.0	266.8	294.0	304.0
62.5°	178.1	210.3	251.0	280.4	289.7
65°	158.8	193.8	236.0	265.3	274.6
67.5°	141.6	178.1	221.0	250.3	260.3
70°	123.0	160.2	204.5	235.3	243.9
72.5°	105.9	144.5	189.5	219.6	230.3
75°	88.0	128.0	173.8	204.5	213.8
77.5°	70.8	112.3	158.8	189.5	199.5
80°	53.6	97.3	143.8	173.8	183.8
82.5°	39.3	82.2	129.5	159.5	168.8
85°	25.7	70.1	115.9	145.9	155.9
87.5°	15.7	58.6	104.4	133.7	143.0
90°	7.9	58.1	120.1	147.2	156.6
92.5°	22.5	66.3	110.8	139.4	147.9
95°	43.9	84.8	129.2	156.4	163.5
97.5°	68.9	106.3	150.6	177.1	185.7
100°	98.2	130.6	172.8	199.3	206.4
102.5°	128.3	156.3	197.9	224.4	231.5
105°	161.4	184.3	223.0	249.4	257.3
107.5°	195.2	215.2	251.0	276.0	280.3
110°	226.7	245.5	280.5	303.4	309.0

TEST NUMBER: P998610

CATALOG NUMBER: SA2XXDIP-B485D725UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	262.0	277.8	309.9	330.6	337.1
115°	296.5	308.7	339.4	360.2	365.8
117.5°	330.2	341.8	368.2	387.5	392.4
120°	364.7	373.4	396.2	416.2	421.9
122.5°	396.2	404.4	427.1	444.2	449.2
125°	428.5	435.2	455.8	472.9	478.7
127.5°	460.8	468.2	484.6	499.5	503.7
130°	490.9	499.8	513.3	529.0	531.8
132.5°	524.7	531.3	542.8	555.6	559.1
135°	553.3	561.4	570.1	584.4	587.9
137.5°	585.6	592.2	597.3	610.2	612.2
140°	614.3	620.2	625.2	636.7	638.1
142.5°	643.6	649.5	651.7	661.1	661.7
145°	670.8	675.9	680.4	685.4	686.0
147.5°	695.8	702.4	705.3	707.5	706.7
150°	721.4	725.9	728.8	731.0	728.8
152.5°	744.2	748.6	752.3	755.2	752.3
155°	767.0	769.2	771.4	775.0	772.8
157.5°	786.8	788.2	789.7	794.8	791.2
160°	804.4	805.9	806.6	811.0	808.1
162.5°	820.5	820.5	821.3	826.4	822.7
165°	834.5	833.7	833.7	838.9	835.2
167.5°	847.0	844.7	844.7	849.9	846.2
170°	856.5	854.3	853.6	858.7	854.3
172.5°	863.1	860.9	860.2	865.3	860.9
175°	868.2	866.0	864.6	869.7	865.3
177.5°	871.2	869.0	867.5	871.9	867.5
180°	869.7	869.7	869.7	869.7	869.7

TEST NUMBER: P998610

CATALOG NUMBER: SA2XXDIP-B485D725UB50-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.23	12.04	12.27	13.09	14.51	14.31	15.12	15.35	16.17	17.59
	3H	12.69	13.42	13.74	14.48	15.91	16.89	17.62	17.94	18.68	20.12
	4H	13.16	13.86	14.22	14.92	16.36	18.15	18.84	19.20	19.90	21.34
	6H	13.45	14.09	14.51	15.15	16.61	19.44	20.08	20.51	21.14	22.60
	8H	13.50	14.11	14.58	15.20	16.65	20.10	20.71	21.17	21.79	23.24
	12H	13.52	14.10	14.60	15.17	16.65	20.82	21.40	21.90	22.48	23.95
4H	2H	12.28	12.97	13.34	14.03	15.48	14.63	15.33	15.70	16.39	17.83
	3H	13.98	14.57	15.05	15.65	17.11	17.42	18.00	18.49	19.09	20.55
	4H	14.60	15.14	15.68	16.22	17.70	18.83	19.37	19.91	20.45	21.93
	6H	15.01	15.48	16.10	16.58	18.05	20.30	20.77	21.38	21.87	23.34
	8H	15.12	15.56	16.21	16.65	18.14	21.06	21.49	22.14	22.59	24.08
	12H	15.16	15.56	16.27	16.67	18.16	21.88	22.28	22.99	23.39	24.88
8H	4H	15.39	15.83	16.47	16.92	18.41	18.97	19.41	20.06	20.51	21.99
	6H	16.02	16.39	17.13	17.52	19.01	20.60	20.97	21.71	22.10	23.59
	8H	16.24	16.56	17.35	17.68	19.18	21.49	21.81	22.61	22.93	24.43
	12H	16.37	16.66	17.49	17.77	19.31	22.48	22.77	23.60	23.88	25.42
12H	4H	15.58	15.98	16.69	17.09	18.58	18.95	19.34	20.05	20.45	21.94
	6H	16.35	16.68	17.47	17.79	19.30	20.63	20.95	21.74	22.07	23.57
	8H	16.65	16.94	17.77	18.05	19.59	21.55	21.84	22.67	22.95	24.49