

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999652

Luminaire Tested: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999652
REPORT IS A COMBINATION OF REPORTS P988205 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4610.2 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999652

CATALOG NUMBER: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999652

CATALOG NUMBER: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30
1	92	88	84	81	81	78	75	72	59	58	56	43	41	40	27	26	26
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22
3	76	68	61	55	67	60	54	50	46	42	39	33	31	29	22	20	19
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	19	18	17
5	64	53	46	40	57	47	41	36	37	32	29	27	24	22	17	16	15
6	59	48	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	13	12	10
9	47	35	28	23	41	32	26	21	25	20	17	18	15	13	12	11	9
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7766	7766	7766
5°	7778	7388	7334
10°	7702	7007	6776
15°	7596	6558	6141
20°	7457	6047	5476
25°	7313	5522	4868
30°	7121	5011	4204
35°	6932	4494	3634
40°	6740	3989	3046
45°	6517	3467	2534
50°	6284	2963	2063
55°	6046	2459	1638
60°	5765	1967	1239
65°	5446	1500	1007
70°	5058	1088	801
75°	4570	829	612
80°	3864	561	410
85°	2698	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6517 cd/sqm

TEST NUMBER: P999652

CATALOG NUMBER: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	1.0
10°-20°	126.2	2.7
20°-30°	177.2	3.8
30°-40°	193.2	4.2
40°-50°	177.6	3.9
50°-60°	139.4	3.0
60°-70°	90.8	2.0
70°-80°	46.7	1.0
80°-90°	15.2	0.3
90°-100°	209.2	4.5
100°-110°	707.2	15.3
110°-120°	743.4	16.1
120°-130°	611.3	13.3
130°-140°	491.2	10.7
140°-150°	371.1	8.0
150°-160°	260.9	5.7
160°-170°	153.6	3.3
170°-180°	50.0	1.1
0°-30°	349.4	7.6
0°-40°	542.6	11.8
0°-60°	859.6	18.6
0°-90°	1012.3	22.0
90°-120°	1659.8	36.0
90°-150°	3133.4	68.0
90°-180°	3598.0	78.0
0°-180°	4610.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	491	491	491	491	491	
5°	491	488	483	487	485	47
15°	467	462	447	438	434	131
25°	424	409	380	362	355	195
35°	365	342	303	275	266	228
45°	298	269	222	190	180	230
55°	227	192	144	118	109	203
65°	153	117	77	62	61	152
75°	82	51	36	32	32	86
85°	19	10	8	8	8	22
90°	1	13	34	32	33	3
95°	35	85	389	147	113	36
105°	121	183	735	1314	1118	129
115°	213	269	615	1270	1472	212
125°	298	352	592	1029	1194	265
135°	349	417	584	864	989	270
145°	399	458	582	722	790	250
155°	454	490	565	639	664	209
165°	494	509	541	574	582	139
175°	515	516	520	526	525	49
180°	516	516	516	516	516	

TEST NUMBER: P999652

CATALOG NUMBER: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	490.6	490.6	490.6	490.6	490.6
2.5°	492.8	490.6	485.7	490.2	489.3
5°	490.6	488.4	482.6	486.6	485.3
7.5°	486.6	483.9	477.7	479.5	477.3
10°	481.3	478.2	469.3	468.0	465.3
12.5°	474.6	470.6	458.6	456.0	451.1
15°	466.6	461.7	446.7	438.2	433.8
17.5°	457.3	450.2	431.6	421.8	414.7
20°	446.7	437.8	415.6	404.5	394.7
22.5°	435.1	424.9	399.1	384.1	377.4
25°	423.6	409.4	380.1	361.9	355.2
27.5°	409.8	394.7	362.3	341.4	331.2
30°	395.2	378.3	342.8	320.1	308.1
32.5°	380.9	360.5	324.1	297.5	286.4
35°	365.0	342.3	303.2	275.3	265.5
37.5°	349.4	325.0	283.7	253.1	242.0
40°	333.0	306.4	263.3	231.8	220.2
42.5°	316.1	287.7	242.9	210.0	198.9
45°	298.4	268.6	222.0	190.5	179.8
47.5°	281.5	250.0	202.0	170.5	160.7
50°	262.8	231.3	182.5	151.8	142.5
52.5°	244.6	211.3	163.8	134.5	126.1
55°	226.9	192.2	144.3	117.7	109.2
57.5°	208.7	173.2	127.0	102.1	95.0
60°	190.0	154.5	108.8	86.1	79.0
62.5°	171.8	136.3	93.2	71.9	68.4
65°	153.2	117.2	77.3	62.2	60.8
67.5°	135.4	99.5	62.2	54.6	53.3
70°	116.8	82.1	51.5	47.1	45.3
72.5°	99.0	66.2	43.1	39.5	38.6
75°	81.7	50.6	35.5	32.4	32.0
77.5°	64.4	36.0	28.0	26.2	25.3
80°	48.4	25.8	21.3	19.5	19.5
82.5°	33.7	17.3	14.7	13.8	13.8
85°	19.1	9.8	8.4	8.4	8.4
87.5°	7.1	3.6	3.6	3.1	3.1
90°	1.0	13.4	33.7	32.2	32.7
92.5°	14.9	47.2	152.8	70.4	60.5
95°	34.7	85.4	389.0	146.9	113.1
97.5°	51.6	112.6	634.1	294.8	189.5
100°	76.4	137.9	784.0	587.0	355.3
102.5°	99.2	160.8	788.9	992.4	692.7
105°	121.1	182.6	735.4	1314.4	1118.4
107.5°	144.9	204.4	685.7	1431.1	1405.2
110°	168.7	226.8	652.0	1412.2	1522.3

TEST NUMBER: P999652

CATALOG NUMBER: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	190.5	248.1	630.2	1348.2	1520.3
115°	213.4	269.4	615.3	1269.8	1471.7
117.5°	237.2	290.8	607.3	1194.8	1398.3
120°	259.0	311.6	600.4	1127.8	1327.8
122.5°	279.8	333.0	596.4	1075.7	1254.4
125°	297.7	352.3	591.5	1028.6	1193.8
127.5°	312.6	370.6	588.5	988.4	1137.3
130°	325.5	387.0	586.5	947.8	1090.6
132.5°	337.4	402.9	585.5	905.6	1042.0
135°	349.3	416.8	584.5	864.4	989.4
137.5°	360.2	428.7	584.5	822.7	938.8
140°	373.1	439.6	583.5	786.0	886.2
142.5°	386.0	448.6	583.5	750.8	833.6
145°	398.9	458.5	581.5	722.0	789.9
147.5°	412.8	466.4	578.6	696.7	751.2
150°	426.7	474.4	575.6	674.8	717.5
152.5°	440.6	482.3	570.6	656.4	688.7
155°	453.5	489.8	564.7	638.6	663.9
157.5°	464.4	495.6	558.7	621.8	642.1
160°	475.3	501.6	552.8	604.8	621.2
162.5°	486.3	506.1	547.8	589.0	601.4
165°	494.2	509.1	540.8	573.6	582.5
167.5°	501.1	512.1	534.9	559.7	564.7
170°	508.1	513.6	529.9	546.8	548.8
172.5°	512.1	515.0	524.0	535.4	535.9
175°	515.0	515.5	520.0	526.5	525.0
177.5°	517.0	516.0	516.0	520.0	517.0
180°	516.0	516.0	516.0	516.0	516.0

(END OF REPORT)