

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998617

Luminaire Tested: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998617
REPORT IS A COMBINATION OF REPORTS P984360 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5668.0 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28
4	73	63	55	49	66	57	51	46	47	42	39	38	34	31	29	26	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15188	15188	15188	15188
5°	15226	16194	15283	12885
10°	15048	17679	15142	10622
15°	14683	18647	14887	8948
20°	14455	17508	14455	7777
25°	13993	15041	14057	6954
30°	13236	11824	13488	6300
35°	12565	8176	12774	5763
40°	11791	6173	11927	5336
45°	10841	5073	11018	4875
50°	10017	4452	10037	4463
55°	9078	3794	9140	4015
60°	8078	3169	8190	3505
65°	7185	2577	7316	2993
70°	6293	2022	6453	2413
75°	5281	1468	5488	1751
80°	4120	931	4415	1039
85°	2712	468	2924	348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15700 cd/sqm

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.6
10°-20°	266.0	4.7
20°-30°	386.1	6.8
30°-40°	407.0	7.2
40°-50°	360.1	6.4
50°-60°	287.6	5.1
60°-70°	195.3	3.4
70°-80°	99.9	1.8
80°-90°	26.9	0.5
90°-100°	198.6	3.5
100°-110°	699.4	12.3
110°-120°	734.5	13.0
120°-130°	604.3	10.7
130°-140°	485.4	8.6
140°-150°	366.7	6.5
150°-160°	257.8	4.5
160°-170°	151.7	2.7
170°-180°	49.4	0.9
0°-30°	743.5	13.1
0°-40°	1150.4	20.3
0°-60°	1798.1	31.7
0°-90°	2120.3	37.4
90°-120°	1632.5	28.8
90°-150°	3088.8	54.5
90°-180°	3548.0	62.6
0°-180°	5668.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	960	960	960	960	960	
5°	960	1072	964	853	960	91
15°	902	1317	914	632	902	255
25°	810	1097	814	507	810	371
35°	662	597	673	421	662	414
45°	496	360	504	346	496	385
55°	341	253	343	268	341	304
65°	202	156	206	181	202	201
75°	94	77	98	92	94	101
85°	19	20	21	15	19	22
90°	1	32	1	32	1	3
95°	34	112	34	112	34	35
105°	120	1104	120	1104	120	127
115°	211	1453	211	1453	211	209
125°	294	1179	294	1179	294	261
135°	345	977	345	977	345	266
145°	394	780	394	780	394	247
155°	448	655	448	655	448	206
165°	488	575	488	575	488	138
175°	508	518	508	518	508	48
180°	509	509	509	509	509	

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	964.7	966.9	970.6	971.3	978.7	984.6	991.2	991.2	993.4	992.7	986.8
5°	960.3	966.9	976.5	984.6	997.9	1003.8	1012.6	1019.3	1025.2	1029.6	1028.9
7.5°	952.9	964.7	978.7	994.2	1011.9	1022.2	1034.8	1046.6	1054.7	1062.0	1067.2
10°	940.3	960.3	979.4	1000.1	1023.0	1037.0	1051.7	1067.2	1079.7	1093.8	1107.0
12.5°	923.4	952.1	975.7	1003.0	1031.1	1046.6	1070.2	1082.0	1106.3	1141.7	1151.3
15°	902.0	941.1	963.2	997.9	1034.8	1047.3	1079.7	1098.9	1149.1	1171.2	1197.7
17.5°	882.1	925.6	955.1	994.9	1031.1	1055.4	1087.1	1126.2	1168.2	1200.0	1229.5
20°	865.9	907.9	943.3	987.5	1033.3	1064.3	1097.4	1144.6	1190.4	1222.8	1245.7
22.5°	829.0	882.8	924.1	973.5	1028.9	1071.6	1103.3	1155.0	1204.4	1224.3	1244.2
25°	810.5	857.0	904.9	961.0	1025.9	1076.8	1104.1	1161.6	1205.1	1212.5	1216.9
27.5°	776.6	829.0	885.0	949.2	1025.2	1067.9	1102.6	1155.0	1189.6	1184.5	1171.2
30°	734.6	798.7	860.7	930.0	1014.8	1061.3	1093.8	1141.7	1159.4	1132.8	1109.2
32.5°	703.6	764.1	832.7	913.1	1003.0	1047.3	1079.0	1116.6	1120.3	1072.4	1032.5
35°	661.6	728.7	806.1	890.9	983.1	1023.0	1052.5	1075.3	1057.6	990.5	943.3
37.5°	623.9	690.3	772.9	859.2	955.8	994.9	1018.5	1022.2	978.7	919.7	850.4
40°	582.6	651.2	737.5	828.2	925.6	959.5	974.3	963.2	900.5	831.9	751.5
42.5°	541.3	609.2	702.1	795.1	887.2	916.0	921.9	891.7	815.0	734.6	641.6
45°	496.4	567.2	660.1	753.8	843.0	859.2	860.0	816.4	725.7	641.6	555.4
47.5°	459.5	525.1	617.3	711.0	786.2	797.3	792.8	742.7	643.9	549.5	474.2
50°	418.9	481.6	573.1	665.2	729.4	732.4	721.3	649.8	553.1	466.9	407.1
52.5°	375.4	438.8	522.9	611.4	668.9	664.5	643.1	566.4	475.7	404.2	358.4
55°	340.7	396.8	475.7	562.0	602.6	590.0	566.4	488.2	416.7	356.2	316.4
57.5°	302.4	351.8	429.2	504.5	528.1	516.3	492.7	419.7	353.3	307.5	281.0
60°	266.2	311.2	379.1	441.8	460.2	447.7	420.4	354.8	306.8	268.5	248.5
62.5°	233.1	272.1	328.9	386.5	393.8	381.3	357.7	304.6	263.3	233.1	218.3
65°	202.1	239.0	284.7	328.2	334.8	321.6	297.2	258.9	224.2	205.0	191.0
67.5°	171.8	201.3	241.9	273.6	277.3	264.8	244.9	213.9	192.5	171.8	161.5
70°	145.3	167.4	199.1	224.9	226.4	214.6	204.3	176.3	160.0	145.3	137.2
72.5°	119.5	135.0	159.3	178.5	179.2	171.8	162.3	144.6	130.5	120.2	112.1
75°	94.4	107.7	122.4	139.4	138.7	132.8	125.4	114.3	102.5	95.9	92.2
77.5°	72.3	80.4	92.2	103.3	103.3	100.3	95.9	87.8	80.4	73.8	70.1
80°	51.6	56.8	66.4	70.1	71.5	70.8	67.1	61.2	58.3	53.1	51.6
82.5°	33.2	36.9	41.3	45.0	47.2	45.7	45.0	42.0	37.6	36.1	34.7
85°	19.2	20.7	22.9	25.1	25.8	25.1	26.6	24.3	22.1	22.1	21.4
87.5°	8.1	8.9	10.3	10.3	11.1	11.1	10.3	11.1	11.1	10.3	9.6
90°	1.0	3.9	7.8	9.8	11.8	13.2	14.7	19.6	26.5	32.3	33.3
92.5°	14.7	20.6	28.4	33.3	41.1	46.5	51.9	78.4	115.6	148.9	150.9
95°	34.3	38.2	48.0	56.8	72.5	84.2	96.0	141.1	226.3	340.0	384.0
97.5°	50.9	56.8	67.6	80.3	98.0	111.2	124.4	182.2	300.8	484.0	626.0
100°	75.4	78.4	87.2	102.9	122.5	136.2	149.9	201.8	321.3	532.9	774.0
102.5°	98.0	99.9	108.7	124.4	145.0	158.7	172.4	219.4	322.3	514.3	778.8
105°	119.5	123.4	130.3	145.0	166.5	180.2	194.0	240.0	327.2	488.9	725.9
107.5°	143.0	146.0	152.8	166.5	188.1	201.8	215.5	260.6	338.0	475.1	677.0
110°	166.5	170.5	176.3	189.1	209.7	223.9	238.1	281.2	351.7	471.2	643.7

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	188.1	192.0	198.9	210.6	230.2	244.9	259.6	300.8	366.4	472.2	622.1
115°	210.6	215.5	221.4	233.2	252.8	266.0	279.2	321.3	381.1	476.1	607.4
117.5°	234.1	238.1	243.9	254.7	273.3	287.0	300.8	340.0	396.8	482.0	599.6
120°	255.7	259.6	265.5	274.3	293.9	307.6	321.3	359.5	412.4	487.9	592.7
122.5°	276.3	279.2	285.1	294.9	314.5	328.7	342.9	378.2	426.2	494.7	588.8
125°	293.9	296.8	302.7	314.5	334.1	347.8	361.5	396.8	440.9	501.6	583.9
127.5°	308.6	312.5	320.4	333.1	351.7	365.9	380.1	414.4	454.6	508.5	581.0
130°	321.3	325.3	335.1	348.8	368.4	382.1	395.8	430.1	467.3	516.3	579.0
132.5°	333.1	338.0	348.8	363.5	384.0	397.8	411.5	443.8	480.0	524.1	578.0
135°	344.8	348.8	360.5	375.2	397.8	411.5	425.2	456.5	490.8	530.0	577.0
137.5°	355.6	360.5	372.3	388.0	410.5	423.2	436.0	467.3	499.6	535.9	577.0
140°	368.4	372.3	384.0	399.7	421.3	434.0	446.7	476.1	506.5	539.8	576.1
142.5°	381.1	384.0	394.8	410.5	431.1	442.8	454.6	483.0	512.4	542.7	576.1
145°	393.8	397.8	407.5	422.2	441.8	452.6	463.4	489.8	517.3	544.7	574.1
147.5°	407.5	410.5	420.3	434.0	450.7	460.4	470.2	495.7	520.2	545.7	571.2
150°	421.3	424.2	432.0	444.8	459.5	468.3	477.1	499.6	522.2	544.7	568.2
152.5°	435.0	436.0	443.8	454.6	468.3	476.2	484.0	503.6	523.2	542.7	563.3
155°	447.7	448.7	454.6	465.4	476.1	483.4	490.8	507.5	524.1	540.8	557.4
157.5°	458.5	459.5	464.4	474.2	483.0	489.4	495.7	510.4	524.1	536.9	551.6
160°	469.3	470.2	474.2	482.0	489.8	495.2	500.6	512.4	524.1	533.9	545.7
162.5°	480.0	479.1	483.0	488.9	495.7	499.6	503.6	513.4	523.2	531.0	540.8
165°	487.9	486.9	488.9	494.7	499.6	502.6	505.5	514.3	521.2	527.1	533.9
167.5°	494.7	493.8	495.7	499.6	503.6	505.6	507.5	514.3	520.2	523.2	528.1
170°	501.6	499.6	500.6	503.6	505.5	507.0	508.5	513.4	518.3	520.2	523.2
172.5°	505.5	504.5	503.6	506.5	507.5	508.4	509.4	512.4	515.3	516.3	517.3
175°	508.5	507.5	506.5	508.5	508.5	509.0	509.4	511.4	513.4	512.4	513.4
177.5°	510.4	508.5	507.5	509.4	509.4	509.4	509.4	510.4	512.4	510.4	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	997.1	997.9	999.3	1006.7	1010.4	1011.1	1008.2	1014.8	1017.1	1014.8	1013.4
5°	1044.3	1048.8	1057.6	1067.2	1066.5	1067.2	1071.6	1076.1	1077.5	1071.6	1073.8
7.5°	1085.6	1094.5	1104.1	1118.8	1118.8	1126.2	1129.2	1132.8	1141.7	1137.3	1135.8
10°	1132.8	1144.6	1162.3	1185.9	1186.7	1194.1	1201.4	1213.2	1216.9	1214.0	1215.4
12.5°	1191.8	1214.7	1216.2	1242.0	1253.8	1255.3	1267.1	1264.9	1272.2	1272.2	1284.8
15°	1217.7	1253.1	1273.0	1298.0	1305.4	1296.6	1306.2	1316.5	1317.2	1317.2	1316.5
17.5°	1264.1	1278.1	1298.0	1311.3	1314.3	1314.3	1315.0	1319.4	1316.5	1310.6	1315.0
20°	1273.7	1279.6	1287.0	1285.5	1287.0	1279.6	1272.2	1264.9	1265.6	1261.9	1273.0
22.5°	1256.0	1254.5	1237.6	1226.5	1226.5	1211.8	1197.7	1191.1	1184.5	1186.7	1190.4
25°	1211.8	1188.9	1168.2	1152.0	1148.3	1124.7	1105.6	1099.7	1088.6	1097.4	1098.9
27.5°	1141.0	1115.1	1082.0	1067.9	1048.8	1039.2	1025.9	1008.2	985.3	998.6	996.4
30°	1065.0	1026.6	999.3	965.4	935.2	933.0	907.9	878.4	866.6	866.6	873.2
32.5°	980.2	929.3	889.5	841.5	812.0	799.5	769.2	739.7	746.4	724.3	732.4
35°	881.3	814.2	764.1	717.6	695.5	680.7	641.6	625.4	607.7	597.4	616.6
37.5°	786.9	709.5	645.3	594.4	586.3	559.8	533.2	522.9	512.6	517.0	516.3
40°	671.9	603.3	545.8	505.9	491.9	479.4	461.7	449.2	442.5	446.2	446.9
42.5°	567.9	510.4	467.6	439.6	427.8	418.9	410.1	399.7	397.5	397.5	400.5
45°	487.5	440.3	411.5	388.7	382.0	375.4	368.8	364.3	362.9	359.9	362.1
47.5°	423.3	385.7	368.0	351.1	343.7	342.2	336.3	334.1	331.1	330.4	331.1
50°	369.5	345.9	329.7	320.1	314.9	312.7	309.8	305.3	303.9	307.5	306.1
52.5°	331.9	309.8	300.9	291.3	288.4	285.4	281.0	281.7	281.0	279.5	279.5
55°	294.3	280.3	271.4	264.0	263.3	260.3	256.7	255.2	254.4	253.0	255.2
57.5°	264.0	253.0	244.9	238.2	235.3	235.3	231.6	228.6	228.6	227.9	228.6
60°	233.8	222.7	217.6	210.9	208.7	208.0	205.8	204.3	202.1	202.1	202.1
62.5°	205.8	196.9	191.0	185.1	185.9	182.2	179.2	177.7	177.7	178.5	178.5
65°	179.2	173.3	165.9	160.8	159.3	158.6	157.1	156.4	154.1	155.6	155.6
67.5°	154.9	146.8	142.3	140.1	137.9	137.2	135.7	134.2	133.5	132.8	134.2
70°	130.5	123.9	120.2	118.7	116.5	115.8	115.1	112.8	113.6	114.3	115.1
72.5°	108.4	102.5	101.8	97.4	97.4	97.4	94.4	95.9	95.1	93.7	95.1
75°	85.6	82.6	81.1	78.9	79.7	78.9	78.2	76.0	76.0	76.7	77.4
77.5°	67.9	64.9	64.2	62.0	60.5	62.0	60.5	59.7	59.7	60.5	60.5
80°	50.2	48.7	46.5	46.5	46.5	45.7	45.7	45.7	45.0	44.3	45.0
82.5°	33.2	33.2	32.5	31.7	32.5	31.0	31.7	31.7	31.7	31.7	31.7
85°	21.4	20.7	20.7	19.9	19.9	19.9	20.7	19.2	19.2	19.9	19.9
87.5°	9.6	9.6	9.6	10.3	9.6	9.6	9.6	10.3	9.6	9.6	9.6
90°	32.3	31.3	29.4	31.3	31.8	32.3	32.3	32.3	32.3	32.3	32.3
92.5°	126.4	98.9	84.3	73.5	69.6	65.6	64.7	60.7	61.7	59.8	61.7
95°	336.0	256.7	196.9	155.8	145.0	134.2	121.5	113.6	110.7	111.7	110.7
97.5°	630.9	525.1	419.3	320.4	291.0	261.6	223.4	203.8	193.0	187.1	193.0
100°	915.0	894.5	773.0	638.8	579.5	520.2	438.9	396.8	368.4	350.7	368.4
102.5°	1020.8	1136.4	1132.5	1043.4	979.7	916.0	825.9	746.5	709.3	683.8	709.3
105°	986.5	1190.3	1301.0	1313.8	1297.6	1281.4	1220.7	1159.9	1117.8	1104.1	1117.8
107.5°	914.0	1132.5	1297.1	1393.1	1412.7	1432.3	1431.3	1422.5	1409.8	1387.2	1409.8
110°	846.4	1053.2	1228.5	1353.9	1394.1	1434.3	1476.4	1495.0	1503.8	1502.8	1503.8

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	799.4	980.7	1147.2	1283.4	1330.9	1378.4	1441.1	1475.4	1494.0	1500.9	1494.0
115°	762.2	923.8	1074.7	1203.1	1253.6	1304.0	1373.5	1418.6	1444.1	1452.9	1444.1
117.5°	736.7	876.8	1012.0	1131.5	1179.5	1227.5	1299.1	1347.1	1373.5	1380.4	1373.5
120°	717.1	843.5	965.0	1068.8	1113.4	1158.0	1226.6	1272.6	1301.0	1310.8	1301.0
122.5°	700.5	817.1	925.8	1022.8	1062.0	1101.2	1160.9	1206.0	1230.5	1238.3	1230.5
125°	684.8	791.6	892.5	978.7	1015.4	1052.2	1109.0	1146.2	1170.7	1178.6	1170.7
127.5°	670.1	766.1	859.2	941.5	975.8	1010.1	1060.0	1095.3	1116.8	1122.7	1116.8
130°	655.4	741.6	825.9	903.3	935.6	967.9	1015.9	1049.2	1068.8	1076.7	1068.8
132.5°	643.7	718.1	794.5	864.1	894.0	923.8	970.9	1004.2	1021.8	1028.7	1021.8
135°	632.9	696.6	761.2	825.9	853.3	880.7	922.9	955.2	972.8	976.7	972.8
137.5°	625.0	678.9	734.8	787.7	812.2	836.7	876.8	905.2	920.9	926.8	920.9
140°	618.2	662.3	709.3	754.4	776.0	797.5	828.8	854.3	869.0	874.9	869.0
142.5°	611.3	648.6	686.8	724.0	741.2	758.3	787.7	810.2	822.9	822.9	822.9
145°	605.4	635.8	668.1	698.5	712.7	726.9	750.4	767.1	776.9	779.8	776.9
147.5°	599.6	626.0	652.5	677.0	687.8	698.5	719.1	732.8	739.7	741.6	739.7
150°	591.7	615.2	636.8	657.4	666.2	675.0	689.7	701.5	707.3	708.3	707.3
152.5°	584.9	604.5	624.1	640.7	648.0	655.4	666.2	676.0	679.9	679.9	679.9
155°	576.1	594.7	610.3	625.0	630.4	635.8	646.6	653.4	657.4	655.4	657.4
157.5°	568.2	582.9	596.6	609.4	613.8	618.2	626.0	631.9	633.9	633.9	633.9
160°	559.4	572.1	582.9	593.7	597.1	600.5	607.4	612.3	613.3	613.3	613.3
162.5°	551.6	561.4	570.2	579.0	581.4	583.9	590.7	593.7	594.7	593.7	594.7
165°	542.7	550.6	557.4	564.3	566.2	568.2	572.1	576.1	576.1	575.1	576.1
167.5°	533.9	539.8	545.7	550.6	552.6	554.5	556.5	558.4	558.4	557.4	558.4
170°	527.1	532.0	534.9	538.8	539.8	540.8	541.8	544.7	543.7	541.8	543.7
172.5°	520.2	523.2	525.1	528.1	528.6	529.0	530.0	531.0	530.0	529.0	530.0
175°	514.3	517.3	518.3	519.2	519.7	520.2	520.2	521.2	520.2	518.3	520.2
177.5°	510.4	512.4	512.4	513.4	513.4	513.4	513.4	513.4	512.4	510.4	512.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	1017.1	1011.9	1007.5	1008.2	1011.9	1008.9	1001.6	992.0	988.3	983.9	988.3
5°	1078.3	1073.8	1065.0	1065.7	1063.5	1060.6	1048.8	1034.0	1034.0	1022.2	1020.7
7.5°	1138.7	1132.1	1126.2	1124.7	1116.6	1110.7	1100.4	1079.7	1071.6	1057.6	1049.5
10°	1206.6	1201.4	1194.8	1186.7	1182.3	1171.9	1155.0	1124.7	1110.0	1090.8	1076.8
12.5°	1275.2	1274.4	1259.7	1243.5	1242.7	1226.5	1214.7	1174.1	1154.2	1128.4	1095.2
15°	1318.7	1315.0	1306.9	1298.8	1301.0	1283.3	1256.7	1208.8	1195.5	1164.6	1129.2
17.5°	1318.0	1318.0	1315.7	1314.3	1312.1	1306.9	1292.1	1260.4	1239.0	1200.0	1166.8
20°	1275.9	1285.5	1287.7	1287.0	1294.4	1298.0	1297.3	1277.4	1260.4	1225.8	1191.8
22.5°	1191.8	1214.0	1223.6	1229.5	1244.9	1253.1	1272.2	1264.9	1260.4	1234.6	1205.9
25°	1113.7	1121.0	1149.8	1151.3	1172.7	1192.6	1211.8	1224.3	1240.5	1230.9	1206.6
27.5°	1012.6	1029.6	1050.2	1065.7	1070.2	1110.7	1142.4	1166.0	1202.9	1205.9	1197.7
30°	898.3	906.4	940.3	961.0	984.6	1014.1	1059.8	1100.4	1133.6	1163.8	1174.1
32.5°	758.9	792.1	812.0	837.1	857.7	910.1	966.2	1018.5	1056.9	1107.8	1129.9
35°	631.3	657.1	691.1	701.4	739.0	783.3	856.3	923.4	981.6	1033.3	1078.3
37.5°	525.9	546.5	582.6	598.9	621.0	677.8	739.0	822.3	892.4	955.8	1011.9
40°	453.6	469.1	496.4	501.5	520.0	571.6	621.0	699.2	792.1	877.7	938.9
42.5°	404.2	411.5	430.0	436.6	448.4	483.1	527.3	601.1	687.4	775.9	862.2
45°	368.8	373.9	385.0	390.9	405.6	421.1	457.3	516.3	584.1	673.4	766.3
47.5°	337.0	343.7	348.1	351.8	359.9	376.9	400.5	444.0	508.9	590.8	680.7
50°	310.5	312.7	320.8	321.6	326.7	337.8	359.9	386.5	438.1	504.5	591.5
52.5°	283.9	286.2	291.3	296.5	298.7	307.5	322.3	344.4	382.8	435.1	512.6
55°	257.4	260.3	265.5	269.2	271.4	278.8	287.6	309.0	339.3	376.1	439.6
57.5°	230.8	237.5	239.0	241.2	244.9	253.0	261.1	273.6	297.2	331.1	377.6
60°	205.8	208.0	213.1	215.4	219.0	223.5	233.8	243.4	260.3	286.9	328.9
62.5°	180.0	185.1	187.3	189.5	192.5	197.7	204.3	214.6	229.4	250.8	283.9
65°	157.8	158.6	163.0	165.9	168.9	172.6	179.2	188.8	197.7	217.6	241.9
67.5°	136.4	137.9	139.4	142.3	146.0	149.7	155.6	160.8	171.8	185.1	204.3
70°	115.8	115.8	119.5	121.7	121.0	125.4	129.8	135.7	143.8	156.4	171.8
72.5°	97.4	96.6	99.6	100.3	101.8	104.7	107.7	113.6	118.0	127.6	139.4
75°	77.4	78.9	80.4	80.4	82.6	84.8	87.8	90.7	95.9	101.8	110.6
77.5°	61.2	61.2	62.7	63.4	65.6	64.9	67.9	70.8	74.5	79.7	86.3
80°	45.0	46.5	46.5	46.5	47.2	47.9	50.9	53.1	55.3	59.0	62.0
82.5°	31.7	31.7	33.2	33.2	33.2	34.7	34.7	35.4	36.9	39.1	41.3
85°	19.9	19.9	19.9	20.7	19.9	20.7	22.1	21.4	22.1	23.6	23.6
87.5°	9.6	9.6	9.6	9.6	9.6	10.3	9.6	10.3	11.1	11.1	11.1
90°	32.3	32.3	32.3	31.8	31.3	29.4	31.3	32.3	33.3	32.3	26.5
92.5°	60.7	64.7	65.6	69.6	73.5	84.3	98.9	126.4	150.9	148.9	115.6
95°	113.6	121.5	134.2	145.0	155.8	196.9	256.7	336.0	384.0	340.0	226.3
97.5°	203.8	223.4	261.6	291.0	320.4	419.3	525.1	630.9	626.0	484.0	300.8
100°	396.8	438.9	520.2	579.5	638.8	773.0	894.5	915.0	774.0	532.9	321.3
102.5°	746.5	825.9	916.0	979.7	1043.4	1132.5	1136.4	1020.8	778.8	514.3	322.3
105°	1159.9	1220.7	1281.4	1297.6	1313.8	1301.0	1190.3	986.5	725.9	488.9	327.2
107.5°	1422.5	1431.3	1432.3	1412.7	1393.1	1297.1	1132.5	914.0	677.0	475.1	338.0
110°	1495.0	1476.4	1434.3	1394.1	1353.9	1228.5	1053.2	846.4	643.7	471.2	351.7

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1475.4	1441.1	1378.4	1330.9	1283.4	1147.2	980.7	799.4	622.1	472.2	366.4
115°	1418.6	1373.5	1304.0	1253.6	1203.1	1074.7	923.8	762.2	607.4	476.1	381.1
117.5°	1347.1	1299.1	1227.5	1179.5	1131.5	1012.0	876.8	736.7	599.6	482.0	396.8
120°	1272.6	1226.6	1158.0	1113.4	1068.8	965.0	843.5	717.1	592.7	487.9	412.4
122.5°	1206.0	1160.9	1101.2	1062.0	1022.8	925.8	817.1	700.5	588.8	494.7	426.2
125°	1146.2	1109.0	1052.2	1015.4	978.7	892.5	791.6	684.8	583.9	501.6	440.9
127.5°	1095.3	1060.0	1010.1	975.8	941.5	859.2	766.1	670.1	581.0	508.5	454.6
130°	1049.2	1015.9	967.9	935.6	903.3	825.9	741.6	655.4	579.0	516.3	467.3
132.5°	1004.2	970.9	923.8	894.0	864.1	794.5	718.1	643.7	578.0	524.1	480.0
135°	955.2	922.9	880.7	853.3	825.9	761.2	696.6	632.9	577.0	530.0	490.8
137.5°	905.2	876.8	836.7	812.2	787.7	734.8	678.9	625.0	577.0	535.9	499.6
140°	854.3	828.8	797.5	776.0	754.4	709.3	662.3	618.2	576.1	539.8	506.5
142.5°	810.2	787.7	758.3	741.2	724.0	686.8	648.6	611.3	576.1	542.7	512.4
145°	767.1	750.4	726.9	712.7	698.5	668.1	635.8	605.4	574.1	544.7	517.3
147.5°	732.8	719.1	698.5	687.8	677.0	652.5	626.0	599.6	571.2	545.7	520.2
150°	701.5	689.7	675.0	666.2	657.4	636.8	615.2	591.7	568.2	544.7	522.2
152.5°	676.0	666.2	655.4	648.0	640.7	624.1	604.5	584.9	563.3	542.7	523.2
155°	653.4	646.6	635.8	630.4	625.0	610.3	594.7	576.1	557.4	540.8	524.1
157.5°	631.9	626.0	618.2	613.8	609.4	596.6	582.9	568.2	551.6	536.9	524.1
160°	612.3	607.4	600.5	597.1	593.7	582.9	572.1	559.4	545.7	533.9	524.1
162.5°	593.7	590.7	583.9	581.4	579.0	570.2	561.4	551.6	540.8	531.0	523.2
165°	576.1	572.1	568.2	566.2	564.3	557.4	550.6	542.7	533.9	527.1	521.2
167.5°	558.4	556.5	554.5	552.6	550.6	545.7	539.8	533.9	528.1	523.2	520.2
170°	544.7	541.8	540.8	539.8	538.8	534.9	532.0	527.1	523.2	520.2	518.3
172.5°	531.0	530.0	529.0	528.6	528.1	525.1	523.2	520.2	517.3	516.3	515.3
175°	521.2	520.2	520.2	519.7	519.2	518.3	517.3	514.3	513.4	512.4	513.4
177.5°	513.4	513.4	513.4	513.4	513.4	512.4	512.4	510.4	509.4	510.4	512.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	984.6	980.9	978.7	980.2	975.7	964.7	964.7	968.4	963.9	959.5	952.9
5°	1011.9	1004.5	1000.1	999.3	989.0	971.3	967.6	963.9	954.4	944.0	933.0
7.5°	1038.4	1025.2	1017.8	1012.6	997.9	975.0	965.4	957.3	941.8	926.3	912.3
10°	1060.6	1041.4	1032.5	1024.4	1005.2	976.5	961.0	946.2	926.3	906.4	888.7
12.5°	1078.3	1056.1	1045.1	1033.3	1009.7	972.1	952.9	929.3	909.4	882.8	865.1
15°	1107.8	1062.0	1051.7	1040.7	1016.3	964.7	941.1	914.5	887.2	851.8	832.7
17.5°	1131.4	1070.2	1069.4	1045.8	1014.1	961.7	925.6	890.9	861.4	826.0	795.8
20°	1145.4	1082.7	1070.9	1046.6	1006.7	941.8	904.2	865.9	834.1	791.4	761.1
22.5°	1157.2	1100.4	1069.4	1039.9	991.2	935.2	879.9	843.7	800.2	753.8	725.0
25°	1161.6	1104.1	1071.6	1037.7	980.2	916.0	853.3	814.2	765.6	723.5	684.4
27.5°	1162.3	1103.3	1063.5	1028.1	964.7	890.9	826.8	785.5	731.6	683.0	643.9
30°	1155.0	1095.2	1059.1	1020.7	949.9	868.1	794.3	748.6	691.1	642.4	601.8
32.5°	1132.8	1079.0	1049.5	1007.5	930.8	836.4	763.3	712.5	652.0	604.0	564.9
35°	1096.0	1059.1	1026.6	987.5	905.7	806.9	732.4	672.6	611.4	565.7	528.8
37.5°	1050.2	1030.3	1000.1	961.7	876.9	780.3	697.7	631.3	570.1	525.9	489.7
40°	988.3	993.4	963.9	929.3	843.0	744.2	652.7	589.3	531.8	490.5	455.1
42.5°	921.2	942.6	925.6	892.4	805.4	704.3	619.5	549.5	493.4	450.6	421.1
45°	848.9	885.8	875.4	851.1	766.3	662.3	572.3	504.5	455.1	413.8	387.9
47.5°	770.0	822.3	822.3	804.6	722.8	620.3	531.8	462.4	413.8	384.3	359.2
50°	689.6	748.6	758.2	746.4	674.1	572.3	482.3	419.7	377.6	348.9	330.4
52.5°	605.5	674.1	691.8	685.9	622.5	526.6	441.8	380.6	342.2	317.1	300.9
55°	525.1	604.8	623.9	626.2	567.2	476.4	396.8	343.0	306.1	289.1	275.1
57.5°	449.2	525.9	547.2	550.9	511.1	430.7	354.8	307.5	274.4	260.3	249.3
60°	384.3	448.4	476.4	484.6	449.9	377.6	315.7	269.9	244.9	231.6	221.3
62.5°	331.1	382.8	412.3	414.5	399.0	331.1	275.1	236.7	215.4	203.6	198.4
65°	279.5	326.0	343.7	352.5	340.0	286.9	237.5	205.8	188.8	178.5	173.3
67.5°	238.2	267.7	282.5	294.3	281.7	241.9	202.1	176.3	163.7	153.4	150.5
70°	195.4	219.8	230.8	242.6	231.6	201.3	172.6	149.0	137.9	129.8	126.1
72.5°	156.4	175.5	185.9	193.2	186.6	161.5	137.9	121.7	113.6	107.7	105.5
75°	123.9	137.2	143.1	148.2	145.3	126.1	111.4	98.1	90.7	85.6	84.1
77.5°	94.4	104.0	110.6	112.1	108.4	95.9	83.3	75.2	69.3	66.4	64.9
80°	67.1	73.0	76.7	78.9	75.2	70.1	61.2	55.3	50.2	46.5	45.7
82.5°	45.0	47.9	50.9	50.2	48.7	44.3	39.1	36.1	33.9	31.0	31.0
85°	25.8	26.6	28.0	28.8	28.0	25.1	22.1	20.7	19.2	17.0	17.0
87.5°	11.1	11.8	11.8	12.5	11.1	11.1	9.6	8.1	8.1	7.4	6.6
90°	19.6	14.7	13.2	11.8	9.8	7.8	3.9	1.0	3.9	7.8	9.8
92.5°	78.4	51.9	46.5	41.1	33.3	28.4	20.6	14.7	20.6	28.4	33.3
95°	141.1	96.0	84.2	72.5	56.8	48.0	38.2	34.3	38.2	48.0	56.8
97.5°	182.2	124.4	111.2	98.0	80.3	67.6	56.8	50.9	56.8	67.6	80.3
100°	201.8	149.9	136.2	122.5	102.9	87.2	78.4	75.4	78.4	87.2	102.9
102.5°	219.4	172.4	158.7	145.0	124.4	108.7	99.9	98.0	99.9	108.7	124.4
105°	240.0	194.0	180.2	166.5	145.0	130.3	123.4	119.5	123.4	130.3	145.0
107.5°	260.6	215.5	201.8	188.1	166.5	152.8	146.0	143.0	146.0	152.8	166.5
110°	281.2	238.1	223.9	209.7	189.1	176.3	170.5	166.5	170.5	176.3	189.1

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	300.8	259.6	244.9	230.2	210.6	198.9	192.0	188.1	192.0	198.9	210.6
115°	321.3	279.2	266.0	252.8	233.2	221.4	215.5	210.6	215.5	221.4	233.2
117.5°	340.0	300.8	287.0	273.3	254.7	243.9	238.1	234.1	238.1	243.9	254.7
120°	359.5	321.3	307.6	293.9	274.3	265.5	259.6	255.7	259.6	265.5	274.3
122.5°	378.2	342.9	328.7	314.5	294.9	285.1	279.2	276.3	279.2	285.1	294.9
125°	396.8	361.5	347.8	334.1	314.5	302.7	296.8	293.9	296.8	302.7	314.5
127.5°	414.4	380.1	365.9	351.7	333.1	320.4	312.5	308.6	312.5	320.4	333.1
130°	430.1	395.8	382.1	368.4	348.8	335.1	325.3	321.3	325.3	335.1	348.8
132.5°	443.8	411.5	397.8	384.0	363.5	348.8	338.0	333.1	338.0	348.8	363.5
135°	456.5	425.2	411.5	397.8	375.2	360.5	348.8	344.8	348.8	360.5	375.2
137.5°	467.3	436.0	423.2	410.5	388.0	372.3	360.5	355.6	360.5	372.3	388.0
140°	476.1	446.7	434.0	421.3	399.7	384.0	372.3	368.4	372.3	384.0	399.7
142.5°	483.0	454.6	442.8	431.1	410.5	394.8	384.0	381.1	384.0	394.8	410.5
145°	489.8	463.4	452.6	441.8	422.2	407.5	397.8	393.8	397.8	407.5	422.2
147.5°	495.7	470.2	460.4	450.7	434.0	420.3	410.5	407.5	410.5	420.3	434.0
150°	499.6	477.1	468.3	459.5	444.8	432.0	424.2	421.3	424.2	432.0	444.8
152.5°	503.6	484.0	476.2	468.3	454.6	443.8	436.0	435.0	436.0	443.8	454.6
155°	507.5	490.8	483.4	476.1	465.4	454.6	448.7	447.7	448.7	454.6	465.4
157.5°	510.4	495.7	489.4	483.0	474.2	464.4	459.5	458.5	459.5	464.4	474.2
160°	512.4	500.6	495.2	489.8	482.0	474.2	470.2	469.3	470.2	474.2	482.0
162.5°	513.4	503.6	499.6	495.7	488.9	483.0	479.1	480.0	479.1	483.0	488.9
165°	514.3	505.5	502.6	499.6	494.7	488.9	486.9	487.9	486.9	488.9	494.7
167.5°	514.3	507.5	505.6	503.6	499.6	495.7	493.8	494.7	493.8	495.7	499.6
170°	513.4	508.5	507.0	505.5	503.6	500.6	499.6	501.6	499.6	500.6	503.6
172.5°	512.4	509.4	508.4	507.5	506.5	503.6	504.5	505.5	504.5	503.6	506.5
175°	511.4	509.4	509.0	508.5	508.5	506.5	507.5	508.5	507.5	506.5	508.5
177.5°	510.4	509.4	509.4	509.4	509.4	507.5	508.5	510.4	508.5	507.5	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	949.2	952.9	952.1	944.8	936.7	930.0	917.5	919.0	914.5	915.3	919.7
5°	925.6	925.6	922.6	912.3	899.0	891.7	877.7	874.0	865.1	864.4	863.6
7.5°	900.5	896.8	893.1	878.4	862.2	850.4	831.2	826.8	817.9	812.0	809.1
10°	871.0	865.9	858.5	841.5	821.6	806.9	786.9	781.0	764.1	756.7	752.3
12.5°	838.6	835.6	823.8	809.8	777.4	761.1	732.4	738.3	721.3	706.6	704.3
15°	806.1	795.1	788.4	765.6	726.5	719.1	696.2	684.4	668.9	657.1	657.1
17.5°	774.4	757.4	742.7	718.4	689.6	668.9	652.0	646.1	626.9	615.1	612.9
20°	732.4	713.2	709.5	674.8	654.9	632.1	615.8	601.1	587.1	581.9	578.2
22.5°	692.5	670.4	664.5	635.0	615.1	592.2	576.0	565.7	555.4	551.7	545.0
25°	649.8	636.5	627.6	595.9	573.8	552.4	541.3	534.0	524.4	523.6	519.2
27.5°	608.5	595.9	587.1	556.8	540.6	520.7	511.8	503.7	498.6	496.4	494.1
30°	573.1	559.0	548.7	526.6	506.7	490.5	483.1	477.9	475.0	471.3	470.5
32.5°	534.0	525.9	511.8	494.9	479.4	463.9	459.5	455.8	451.4	449.9	449.2
35°	500.8	489.7	480.9	461.7	455.1	441.8	436.6	433.7	427.8	426.3	424.8
37.5°	468.3	458.0	448.4	436.6	424.1	416.7	413.8	409.3	406.4	407.1	405.6
40°	435.9	427.8	420.4	407.9	400.5	396.8	390.9	386.5	385.0	385.7	385.0
42.5°	404.2	396.8	392.4	382.8	375.4	371.7	368.0	363.6	365.8	365.8	368.0
45°	375.4	368.8	365.8	358.4	354.0	348.1	344.4	343.7	346.6	345.9	345.9
47.5°	345.9	343.7	340.0	333.4	327.5	323.8	323.0	323.0	326.0	327.5	326.7
50°	323.0	318.6	314.2	309.0	304.6	303.1	300.9	302.4	305.3	305.3	306.8
52.5°	294.3	291.3	289.8	285.4	282.5	282.5	282.5	283.2	285.4	287.6	286.9
55°	269.2	267.0	265.5	263.3	259.6	260.3	259.6	261.1	263.3	265.5	267.0
57.5°	242.6	241.9	240.4	236.7	236.7	236.0	238.2	239.0	242.6	244.1	246.3
60°	219.0	216.8	216.8	213.9	213.9	213.9	216.1	218.3	221.3	222.0	223.5
62.5°	194.0	194.0	193.2	191.0	191.0	193.2	194.0	196.9	198.4	198.4	200.6
65°	170.4	169.6	168.9	169.6	170.4	170.4	172.6	174.1	175.5	176.3	177.0
67.5°	146.8	146.0	147.5	146.8	148.2	151.2	150.5	152.7	154.9	154.9	155.6
70°	124.6	126.1	125.4	126.9	126.1	127.6	129.8	130.5	130.5	131.3	133.5
72.5°	104.0	104.0	104.0	103.3	104.0	105.5	106.9	107.7	109.2	109.9	112.1
75°	84.1	84.1	82.6	84.1	84.1	85.6	87.0	87.0	87.0	88.5	90.7
77.5°	63.4	64.2	63.4	64.9	64.9	65.6	67.1	66.4	67.9	68.6	69.3
80°	46.5	45.7	45.7	45.7	46.5	46.5	47.9	48.7	48.7	50.9	49.4
82.5°	29.5	30.2	29.5	30.2	30.2	31.0	30.2	31.0	31.7	33.2	32.5
85°	17.0	16.2	16.2	17.0	16.2	16.2	17.0	16.2	17.0	16.2	17.0
87.5°	6.6	5.9	5.9	5.9	5.9	5.2	5.2	4.4	4.4	4.4	3.7
90°	11.8	13.2	14.7	19.6	26.5	32.3	33.3	32.3	31.3	29.4	31.3
92.5°	41.1	46.5	51.9	78.4	115.6	148.9	150.9	126.4	98.9	84.3	73.5
95°	72.5	84.2	96.0	141.1	226.3	340.0	384.0	336.0	256.7	196.9	155.8
97.5°	98.0	111.2	124.4	182.2	300.8	484.0	626.0	630.9	525.1	419.3	320.4
100°	122.5	136.2	149.9	201.8	321.3	532.9	774.0	915.0	894.5	773.0	638.8
102.5°	145.0	158.7	172.4	219.4	322.3	514.3	778.8	1020.8	1136.4	1132.5	1043.4
105°	166.5	180.2	194.0	240.0	327.2	488.9	725.9	986.5	1190.3	1301.0	1313.8
107.5°	188.1	201.8	215.5	260.6	338.0	475.1	677.0	914.0	1132.5	1297.1	1393.1
110°	209.7	223.9	238.1	281.2	351.7	471.2	643.7	846.4	1053.2	1228.5	1353.9

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	230.2	244.9	259.6	300.8	366.4	472.2	622.1	799.4	980.7	1147.2	1283.4
115°	252.8	266.0	279.2	321.3	381.1	476.1	607.4	762.2	923.8	1074.7	1203.1
117.5°	273.3	287.0	300.8	340.0	396.8	482.0	599.6	736.7	876.8	1012.0	1131.5
120°	293.9	307.6	321.3	359.5	412.4	487.9	592.7	717.1	843.5	965.0	1068.8
122.5°	314.5	328.7	342.9	378.2	426.2	494.7	588.8	700.5	817.1	925.8	1022.8
125°	334.1	347.8	361.5	396.8	440.9	501.6	583.9	684.8	791.6	892.5	978.7
127.5°	351.7	365.9	380.1	414.4	454.6	508.5	581.0	670.1	766.1	859.2	941.5
130°	368.4	382.1	395.8	430.1	467.3	516.3	579.0	655.4	741.6	825.9	903.3
132.5°	384.0	397.8	411.5	443.8	480.0	524.1	578.0	643.7	718.1	794.5	864.1
135°	397.8	411.5	425.2	456.5	490.8	530.0	577.0	632.9	696.6	761.2	825.9
137.5°	410.5	423.2	436.0	467.3	499.6	535.9	577.0	625.0	678.9	734.8	787.7
140°	421.3	434.0	446.7	476.1	506.5	539.8	576.1	618.2	662.3	709.3	754.4
142.5°	431.1	442.8	454.6	483.0	512.4	542.7	576.1	611.3	648.6	686.8	724.0
145°	441.8	452.6	463.4	489.8	517.3	544.7	574.1	605.4	635.8	668.1	698.5
147.5°	450.7	460.4	470.2	495.7	520.2	545.7	571.2	599.6	626.0	652.5	677.0
150°	459.5	468.3	477.1	499.6	522.2	544.7	568.2	591.7	615.2	636.8	657.4
152.5°	468.3	476.2	484.0	503.6	523.2	542.7	563.3	584.9	604.5	624.1	640.7
155°	476.1	483.4	490.8	507.5	524.1	540.8	557.4	576.1	594.7	610.3	625.0
157.5°	483.0	489.4	495.7	510.4	524.1	536.9	551.6	568.2	582.9	596.6	609.4
160°	489.8	495.2	500.6	512.4	524.1	533.9	545.7	559.4	572.1	582.9	593.7
162.5°	495.7	499.6	503.6	513.4	523.2	531.0	540.8	551.6	561.4	570.2	579.0
165°	499.6	502.6	505.5	514.3	521.2	527.1	533.9	542.7	550.6	557.4	564.3
167.5°	503.6	505.6	507.5	514.3	520.2	523.2	528.1	533.9	539.8	545.7	550.6
170°	505.5	507.0	508.5	513.4	518.3	520.2	523.2	527.1	532.0	534.9	538.8
172.5°	507.5	508.4	509.4	512.4	515.3	516.3	517.3	520.2	523.2	525.1	528.1
175°	508.5	509.0	509.4	511.4	513.4	512.4	513.4	514.3	517.3	518.3	519.2
177.5°	509.4	509.4	509.4	510.4	512.4	510.4	509.4	510.4	512.4	512.4	513.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	914.5	916.7	911.6	910.1	911.6	906.4	907.9	909.4	909.4	911.6	913.1
5°	861.4	858.5	853.3	851.8	850.4	852.6	851.1	853.3	854.1	859.2	860.0
7.5°	809.1	804.6	800.2	795.8	794.3	790.6	794.3	794.3	799.5	798.0	801.7
10°	747.1	746.4	740.5	738.3	735.3	729.4	737.5	735.3	739.0	745.6	747.1
12.5°	701.4	693.3	697.0	686.6	690.3	684.4	685.2	685.2	691.1	691.8	690.3
15°	657.9	651.2	641.6	637.2	635.0	632.1	641.6	642.4	638.0	648.3	644.6
17.5°	613.6	613.6	604.8	602.6	596.7	599.6	598.1	598.9	597.4	604.8	608.5
20°	575.3	571.6	568.6	569.4	562.0	560.5	559.0	560.5	565.7	570.8	572.3
22.5°	544.3	542.1	534.7	536.2	530.3	532.5	531.0	534.7	535.4	535.4	540.6
25°	514.8	511.8	512.6	509.6	507.4	507.4	505.2	507.4	510.4	511.8	512.6
27.5°	492.7	490.5	486.8	484.6	486.0	482.3	485.3	487.5	487.5	486.0	487.5
30°	466.1	467.6	467.6	460.2	463.2	461.7	463.9	465.4	465.4	466.1	464.6
32.5°	448.4	444.0	443.3	442.5	442.5	439.6	439.6	441.8	442.5	443.3	445.5
35°	424.8	424.8	421.1	423.3	420.4	421.1	420.4	421.1	422.6	420.4	422.6
37.5°	403.4	404.2	402.7	404.2	404.9	403.4	402.0	404.9	403.4	403.4	402.0
40°	385.0	384.3	385.0	385.0	385.0	385.7	384.3	384.3	384.3	382.8	381.3
42.5°	369.5	365.1	366.6	367.3	365.1	365.1	365.8	365.1	367.3	362.9	362.9
45°	347.4	345.9	346.6	346.6	348.1	345.9	347.4	348.1	345.9	345.2	343.7
47.5°	327.5	328.9	327.5	328.9	328.9	330.4	327.5	328.2	328.9	326.0	323.8
50°	307.5	307.5	309.8	309.0	309.8	308.3	308.3	307.5	308.3	306.8	304.6
52.5°	289.1	286.9	290.6	289.8	289.1	288.4	287.6	288.4	286.9	285.4	285.4
55°	266.2	266.2	268.5	269.2	269.2	267.7	266.2	267.0	266.2	265.5	264.8
57.5°	247.8	244.9	246.3	247.1	247.1	244.9	246.3	244.9	244.9	245.6	243.4
60°	224.2	224.2	222.7	224.9	224.9	223.5	223.5	224.2	222.7	222.0	221.3
62.5°	199.1	199.9	202.1	202.8	203.6	202.1	200.6	201.3	201.3	199.1	199.9
65°	177.7	179.2	182.2	181.4	180.0	180.7	179.2	180.0	177.7	178.5	176.3
67.5°	157.1	156.4	157.1	157.1	158.6	157.8	156.4	156.4	155.6	157.8	155.6
70°	135.0	135.0	135.0	135.0	135.7	136.4	135.0	133.5	134.2	132.8	132.0
72.5°	112.1	112.8	112.1	113.6	111.4	112.8	112.8	112.1	111.4	111.4	111.4
75°	90.7	92.2	90.0	90.7	90.0	91.5	90.7	90.7	89.2	88.5	89.2
77.5°	69.3	70.1	68.6	69.3	68.6	69.3	69.3	68.6	68.6	68.6	68.6
80°	49.4	50.2	49.4	48.7	47.9	49.4	47.9	48.7	49.4	48.7	50.2
82.5°	31.7	31.7	31.0	31.7	30.2	30.2	31.0	31.0	30.2	31.7	30.2
85°	15.5	15.5	17.0	15.5	14.8	14.8	14.8	15.5	14.8	16.2	15.5
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.4	3.0
90°	31.8	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	31.8
92.5°	69.6	65.6	64.7	60.7	61.7	59.8	61.7	60.7	64.7	65.6	69.6
95°	145.0	134.2	121.5	113.6	110.7	111.7	110.7	113.6	121.5	134.2	145.0
97.5°	291.0	261.6	223.4	203.8	193.0	187.1	193.0	203.8	223.4	261.6	291.0
100°	579.5	520.2	438.9	396.8	368.4	350.7	368.4	396.8	438.9	520.2	579.5
102.5°	979.7	916.0	825.9	746.5	709.3	683.8	709.3	746.5	825.9	916.0	979.7
105°	1297.6	1281.4	1220.7	1159.9	1117.8	1104.1	1117.8	1159.9	1220.7	1281.4	1297.6
107.5°	1412.7	1432.3	1431.3	1422.5	1409.8	1387.2	1409.8	1422.5	1431.3	1432.3	1412.7
110°	1394.1	1434.3	1476.4	1495.0	1503.8	1502.8	1503.8	1495.0	1476.4	1434.3	1394.1

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1330.9	1378.4	1441.1	1475.4	1494.0	1500.9	1494.0	1475.4	1441.1	1378.4	1330.9
115°	1253.6	1304.0	1373.5	1418.6	1444.1	1452.9	1444.1	1418.6	1373.5	1304.0	1253.6
117.5°	1179.5	1227.5	1299.1	1347.1	1373.5	1380.4	1373.5	1347.1	1299.1	1227.5	1179.5
120°	1113.4	1158.0	1226.6	1272.6	1301.0	1310.8	1301.0	1272.6	1226.6	1158.0	1113.4
122.5°	1062.0	1101.2	1160.9	1206.0	1230.5	1238.3	1230.5	1206.0	1160.9	1101.2	1062.0
125°	1015.4	1052.2	1109.0	1146.2	1170.7	1178.6	1170.7	1146.2	1109.0	1052.2	1015.4
127.5°	975.8	1010.1	1060.0	1095.3	1116.8	1122.7	1116.8	1095.3	1060.0	1010.1	975.8
130°	935.6	967.9	1015.9	1049.2	1068.8	1076.7	1068.8	1049.2	1015.9	967.9	935.6
132.5°	894.0	923.8	970.9	1004.2	1021.8	1028.7	1021.8	1004.2	970.9	923.8	894.0
135°	853.3	880.7	922.9	955.2	972.8	976.7	972.8	955.2	922.9	880.7	853.3
137.5°	812.2	836.7	876.8	905.2	920.9	926.8	920.9	905.2	876.8	836.7	812.2
140°	776.0	797.5	828.8	854.3	869.0	874.9	869.0	854.3	828.8	797.5	776.0
142.5°	741.2	758.3	787.7	810.2	822.9	822.9	822.9	810.2	787.7	758.3	741.2
145°	712.7	726.9	750.4	767.1	776.9	779.8	776.9	767.1	750.4	726.9	712.7
147.5°	687.8	698.5	719.1	732.8	739.7	741.6	739.7	732.8	719.1	698.5	687.8
150°	666.2	675.0	689.7	701.5	707.3	708.3	707.3	701.5	689.7	675.0	666.2
152.5°	648.0	655.4	666.2	676.0	679.9	679.9	679.9	676.0	666.2	655.4	648.0
155°	630.4	635.8	646.6	653.4	657.4	655.4	657.4	653.4	646.6	635.8	630.4
157.5°	613.8	618.2	626.0	631.9	633.9	633.9	633.9	631.9	626.0	618.2	613.8
160°	597.1	600.5	607.4	612.3	613.3	613.3	613.3	612.3	607.4	600.5	597.1
162.5°	581.4	583.9	590.7	593.7	594.7	593.7	594.7	593.7	590.7	583.9	581.4
165°	566.2	568.2	572.1	576.1	576.1	575.1	576.1	576.1	572.1	568.2	566.2
167.5°	552.6	554.5	556.5	558.4	558.4	557.4	558.4	558.4	556.5	554.5	552.6
170°	539.8	540.8	541.8	544.7	543.7	541.8	543.7	544.7	541.8	540.8	539.8
172.5°	528.6	529.0	530.0	531.0	530.0	529.0	530.0	531.0	530.0	529.0	528.6
175°	519.7	520.2	520.2	521.2	520.2	518.3	520.2	521.2	520.2	520.2	519.7
177.5°	513.4	513.4	513.4	513.4	512.4	510.4	512.4	513.4	513.4	513.4	513.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	910.8	916.7	914.5	906.4	916.0	916.0	922.6	922.6	930.8	933.7	938.1
5°	859.2	863.6	867.3	863.6	870.3	880.6	886.5	891.7	902.7	907.2	913.8
7.5°	803.9	812.0	815.7	815.7	826.8	838.6	850.4	857.7	873.2	879.1	885.8
10°	750.1	759.7	767.0	766.3	784.7	792.1	806.9	823.8	839.3	848.2	857.7
12.5°	693.3	698.4	708.8	723.5	727.9	741.2	758.2	779.6	807.6	815.7	829.7
15°	646.1	660.1	668.2	674.8	685.2	697.7	716.1	736.8	764.8	782.5	797.3
17.5°	606.2	624.7	629.8	628.4	641.6	660.8	682.2	697.7	722.8	744.2	758.2
20°	573.8	581.2	590.0	593.7	604.0	624.7	645.3	663.0	683.7	700.7	716.9
22.5°	541.3	547.2	554.6	561.3	569.4	581.2	601.1	623.2	643.1	659.3	677.8
25°	514.8	518.5	525.1	530.3	539.1	547.2	561.3	585.6	609.2	618.8	635.0
27.5°	489.0	491.9	496.4	502.3	506.7	514.8	527.3	547.2	571.6	581.2	603.3
30°	466.1	468.3	472.8	475.7	477.9	487.5	497.1	512.6	531.0	544.3	560.5
32.5°	444.7	446.9	451.4	452.1	455.1	460.2	469.1	483.1	499.3	510.4	524.4
35°	421.1	422.6	427.0	428.5	430.7	435.1	441.8	452.1	466.9	475.0	487.5
37.5°	402.7	402.0	404.9	407.1	410.1	412.3	414.5	424.8	435.9	443.3	452.8
40°	382.8	381.3	382.0	385.0	386.5	389.4	389.4	399.7	407.1	413.0	420.4
42.5°	362.9	362.1	360.7	362.1	363.6	364.3	365.1	372.5	379.8	385.0	393.1
45°	343.0	342.2	340.7	341.5	341.5	343.0	345.2	348.1	353.3	357.7	362.1
47.5°	324.5	323.0	320.8	320.1	321.6	321.6	321.6	324.5	329.7	331.1	335.6
50°	305.3	303.1	300.2	298.7	298.7	298.0	299.4	300.2	304.6	306.1	309.8
52.5°	284.7	283.2	280.3	277.3	278.0	276.6	277.3	278.0	279.5	281.7	283.9
55°	264.0	261.1	258.9	258.1	255.9	255.9	253.7	256.7	255.9	256.7	259.6
57.5°	244.1	241.2	237.5	236.0	233.8	233.1	231.6	230.8	231.6	233.8	236.0
60°	220.5	219.0	216.8	214.6	213.1	210.9	209.5	209.5	208.7	208.7	209.5
62.5°	197.7	196.9	194.0	193.2	191.8	190.3	188.1	186.6	186.6	188.1	188.8
65°	175.5	174.8	172.6	171.8	168.2	166.7	165.9	165.2	163.7	163.7	163.7
67.5°	154.9	152.7	152.7	149.0	146.0	144.6	143.1	142.3	142.3	142.3	143.1
70°	132.0	132.0	129.8	127.6	124.6	125.4	123.2	121.0	121.0	119.5	120.2
72.5°	109.9	109.2	106.9	106.2	104.0	101.8	100.3	101.8	99.6	98.8	99.6
75°	88.5	87.8	86.3	84.8	85.6	83.3	81.1	80.4	80.4	78.9	78.9
77.5°	67.9	69.3	66.4	65.6	64.2	62.7	62.0	61.2	61.2	61.2	62.7
80°	47.2	47.9	47.9	46.5	47.2	45.0	45.0	45.0	42.8	43.5	44.3
82.5°	30.2	30.2	29.5	30.2	29.5	29.5	28.8	28.8	28.0	28.0	28.8
85°	17.0	16.2	15.5	17.0	16.2	16.2	15.5	15.5	15.5	15.5	15.5
87.5°	3.7	4.4	4.4	4.4	4.4	5.2	5.2	5.2	5.9	5.9	5.9
90°	31.3	29.4	31.3	32.3	33.3	32.3	26.5	19.6	14.7	13.2	11.8
92.5°	73.5	84.3	98.9	126.4	150.9	148.9	115.6	78.4	51.9	46.5	41.1
95°	155.8	196.9	256.7	336.0	384.0	340.0	226.3	141.1	96.0	84.2	72.5
97.5°	320.4	419.3	525.1	630.9	626.0	484.0	300.8	182.2	124.4	111.2	98.0
100°	638.8	773.0	894.5	915.0	774.0	532.9	321.3	201.8	149.9	136.2	122.5
102.5°	1043.4	1132.5	1136.4	1020.8	778.8	514.3	322.3	219.4	172.4	158.7	145.0
105°	1313.8	1301.0	1190.3	986.5	725.9	488.9	327.2	240.0	194.0	180.2	166.5
107.5°	1393.1	1297.1	1132.5	914.0	677.0	475.1	338.0	260.6	215.5	201.8	188.1
110°	1353.9	1228.5	1053.2	846.4	643.7	471.2	351.7	281.2	238.1	223.9	209.7

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1283.4	1147.2	980.7	799.4	622.1	472.2	366.4	300.8	259.6	244.9	230.2
115°	1203.1	1074.7	923.8	762.2	607.4	476.1	381.1	321.3	279.2	266.0	252.8
117.5°	1131.5	1012.0	876.8	736.7	599.6	482.0	396.8	340.0	300.8	287.0	273.3
120°	1068.8	965.0	843.5	717.1	592.7	487.9	412.4	359.5	321.3	307.6	293.9
122.5°	1022.8	925.8	817.1	700.5	588.8	494.7	426.2	378.2	342.9	328.7	314.5
125°	978.7	892.5	791.6	684.8	583.9	501.6	440.9	396.8	361.5	347.8	334.1
127.5°	941.5	859.2	766.1	670.1	581.0	508.5	454.6	414.4	380.1	365.9	351.7
130°	903.3	825.9	741.6	655.4	579.0	516.3	467.3	430.1	395.8	382.1	368.4
132.5°	864.1	794.5	718.1	643.7	578.0	524.1	480.0	443.8	411.5	397.8	384.0
135°	825.9	761.2	696.6	632.9	577.0	530.0	490.8	456.5	425.2	411.5	397.8
137.5°	787.7	734.8	678.9	625.0	577.0	535.9	499.6	467.3	436.0	423.2	410.5
140°	754.4	709.3	662.3	618.2	576.1	539.8	506.5	476.1	446.7	434.0	421.3
142.5°	724.0	686.8	648.6	611.3	576.1	542.7	512.4	483.0	454.6	442.8	431.1
145°	698.5	668.1	635.8	605.4	574.1	544.7	517.3	489.8	463.4	452.6	441.8
147.5°	677.0	652.5	626.0	599.6	571.2	545.7	520.2	495.7	470.2	460.4	450.7
150°	657.4	636.8	615.2	591.7	568.2	544.7	522.2	499.6	477.1	468.3	459.5
152.5°	640.7	624.1	604.5	584.9	563.3	542.7	523.2	503.6	484.0	476.2	468.3
155°	625.0	610.3	594.7	576.1	557.4	540.8	524.1	507.5	490.8	483.4	476.1
157.5°	609.4	596.6	582.9	568.2	551.6	536.9	524.1	510.4	495.7	489.4	483.0
160°	593.7	582.9	572.1	559.4	545.7	533.9	524.1	512.4	500.6	495.2	489.8
162.5°	579.0	570.2	561.4	551.6	540.8	531.0	523.2	513.4	503.6	499.6	495.7
165°	564.3	557.4	550.6	542.7	533.9	527.1	521.2	514.3	505.5	502.6	499.6
167.5°	550.6	545.7	539.8	533.9	528.1	523.2	520.2	514.3	507.5	505.6	503.6
170°	538.8	534.9	532.0	527.1	523.2	520.2	518.3	513.4	508.5	507.0	505.5
172.5°	528.1	525.1	523.2	520.2	517.3	516.3	515.3	512.4	509.4	508.4	507.5
175°	519.2	518.3	517.3	514.3	513.4	512.4	513.4	511.4	509.4	509.0	508.5
177.5°	513.4	512.4	512.4	510.4	509.4	510.4	512.4	510.4	509.4	509.4	509.4
180°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	959.5	959.5	959.5	959.5
2.5°	941.8	941.8	952.9	964.7
5°	921.2	926.3	944.0	960.3
7.5°	901.3	910.1	932.2	952.9
10°	876.9	888.7	916.0	940.3
12.5°	853.3	864.4	896.1	923.4
15°	820.1	834.1	868.1	902.0
17.5°	786.9	801.0	842.3	882.1
20°	747.9	766.3	812.8	865.9
22.5°	711.7	734.6	786.2	829.0
25°	671.9	707.3	755.2	810.5
27.5°	636.5	671.9	720.6	776.6
30°	596.7	632.8	683.0	734.6
32.5°	558.3	591.5	640.2	703.6
35°	518.5	550.2	597.4	661.6
37.5°	482.3	513.3	564.9	623.9
40°	446.9	479.4	523.6	582.6
42.5°	413.8	442.5	482.3	541.3
45°	383.5	404.2	441.0	496.4
47.5°	351.8	370.2	404.2	459.5
50°	322.3	337.8	367.3	418.9
52.5°	293.5	306.8	334.1	375.4
55°	267.7	280.3	300.2	340.7
57.5°	241.2	250.8	269.9	302.4
60°	215.4	224.2	239.7	266.2
62.5°	189.5	196.9	211.7	233.1
65°	166.7	172.6	183.6	202.1
67.5°	144.6	148.2	157.1	171.8
70°	123.2	126.1	133.5	145.3
72.5°	100.3	103.3	111.4	119.5
75°	81.1	81.9	87.8	94.4
77.5°	63.4	62.7	67.1	72.3
80°	43.5	45.7	49.4	51.6
82.5°	29.5	30.2	31.7	33.2
85°	16.2	17.0	17.0	19.2
87.5°	6.6	7.4	7.4	8.1
90°	9.8	7.8	3.9	1.0
92.5°	33.3	28.4	20.6	14.7
95°	56.8	48.0	38.2	34.3
97.5°	80.3	67.6	56.8	50.9
100°	102.9	87.2	78.4	75.4
102.5°	124.4	108.7	99.9	98.0
105°	145.0	130.3	123.4	119.5
107.5°	166.5	152.8	146.0	143.0
110°	189.1	176.3	170.5	166.5



TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	210.6	198.9	192.0	188.1
115°	233.2	221.4	215.5	210.6
117.5°	254.7	243.9	238.1	234.1
120°	274.3	265.5	259.6	255.7
122.5°	294.9	285.1	279.2	276.3
125°	314.5	302.7	296.8	293.9
127.5°	333.1	320.4	312.5	308.6
130°	348.8	335.1	325.3	321.3
132.5°	363.5	348.8	338.0	333.1
135°	375.2	360.5	348.8	344.8
137.5°	388.0	372.3	360.5	355.6
140°	399.7	384.0	372.3	368.4
142.5°	410.5	394.8	384.0	381.1
145°	422.2	407.5	397.8	393.8
147.5°	434.0	420.3	410.5	407.5
150°	444.8	432.0	424.2	421.3
152.5°	454.6	443.8	436.0	435.0
155°	465.4	454.6	448.7	447.7
157.5°	474.2	464.4	459.5	458.5
160°	482.0	474.2	470.2	469.3
162.5°	488.9	483.0	479.1	480.0
165°	494.7	488.9	486.9	487.9
167.5°	499.6	495.7	493.8	494.7
170°	503.6	500.6	499.6	501.6
172.5°	506.5	503.6	504.5	505.5
175°	508.5	506.5	507.5	508.5
177.5°	509.4	507.5	508.5	510.4
180°	509.4	509.4	509.4	509.4

TEST NUMBER: P998617

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.99	14.73	15.06	15.79	17.23	11.48	12.22	12.55	13.28	14.73
	3H	14.79	15.45	15.87	16.52	17.98	12.82	13.48	13.89	14.55	16.01
	4H	14.96	15.58	16.04	16.65	18.12	13.28	13.90	14.36	14.97	16.44
	6H	15.00	15.57	16.09	16.65	18.12	13.58	14.15	14.67	15.23	16.71
	8H	14.97	15.52	16.07	16.61	18.08	13.66	14.20	14.75	15.29	16.77
	12H	14.93	15.45	16.03	16.53	18.03	13.70	14.21	14.80	15.30	16.80
4H	2H	14.02	14.64	15.11	15.71	17.18	11.92	12.54	13.01	13.61	15.08
	3H	14.99	15.51	16.08	16.61	18.09	13.36	13.88	14.46	14.98	16.46
	4H	15.26	15.73	16.36	16.83	18.33	13.89	14.37	15.00	15.46	16.96
	6H	15.38	15.79	16.49	16.90	18.40	14.27	14.67	15.38	15.79	17.28
	8H	15.38	15.76	16.49	16.86	18.37	14.38	14.76	15.49	15.86	17.37
	12H	15.34	15.68	16.46	16.80	18.31	14.43	14.77	15.55	15.89	17.40
8H	4H	15.26	15.64	16.37	16.74	18.25	14.03	14.41	15.14	15.51	17.02
	6H	15.43	15.75	16.56	16.89	18.40	14.46	14.77	15.59	15.92	17.43
	8H	15.46	15.74	16.60	16.87	18.39	14.61	14.88	15.75	16.01	17.54
	12H	15.44	15.68	16.58	16.81	18.37	14.69	14.94	15.84	16.06	17.62
12H	4H	15.21	15.55	16.34	16.67	18.19	14.00	14.34	15.12	15.46	16.97
	6H	15.41	15.69	16.55	16.81	18.34	14.46	14.73	15.60	15.86	17.39
	8H	15.44	15.68	16.58	16.80	18.37	14.61	14.85	15.75	15.97	17.54