

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998618

Luminaire Tested: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998618
REPORT IS A COMBINATION OF REPORTS P984361 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5575.0 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998618

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D

Luminous Intensity Polar Plot



TEST NUMBER: P998618

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	93	88	84	80	83	79	76	72	62	60	58	47	45	44	33	32	31
2	84	76	70	65	75	69	63	59	54	50	47	41	38	36	28	27	25
3	76	67	59	53	68	60	54	48	47	43	39	36	32	30	25	23	21
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	22	20	18
5	64	52	44	38	57	47	40	35	37	32	28	28	24	22	20	17	15
6	58	46	38	33	52	42	35	30	33	28	24	25	22	19	18	15	13
7	54	42	34	28	48	38	31	26	30	25	21	23	19	16	16	14	12
8	50	38	30	25	45	34	27	23	27	22	19	21	17	14	15	12	10
9	46	34	27	22	41	31	25	20	25	20	16	19	15	13	13	11	9
10	43	31	24	19	39	28	22	18	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8052	8052	8052
5°	8089	7708	7665
10°	8035	7442	7332
15°	7921	7166	6992
20°	7777	6876	6670
25°	7636	6597	6376
30°	7440	6315	6085
35°	7240	6043	5873
40°	7027	5809	5661
45°	6827	5595	5476
50°	6612	5398	5294
55°	6384	5190	5108
60°	6108	4972	4913
65°	5819	4722	4689
70°	5491	4454	4447
75°	5074	4184	4219
80°	4415	3905	3984
85°	3743	3641	3779

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6827 cd/sqm

TEST NUMBER: P998618

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.2	0.9
10°-20°	138.3	2.5
20°-30°	209.6	3.8
30°-40°	255.2	4.6
40°-50°	274.6	4.9
50°-60°	266.6	4.8
60°-70°	232.9	4.2
70°-80°	179.2	3.2
80°-90°	122.2	2.2
90°-100°	123.7	2.2
100°-110°	212.8	3.8
110°-120°	443.8	8.0
120°-130°	692.1	12.4
130°-140°	720.9	12.9
140°-150°	662.9	11.9
150°-160°	531.6	9.5
160°-170°	342.6	6.1
170°-180°	117.9	2.1
0°-30°	396.1	7.1
0°-40°	651.3	11.7
0°-60°	1192.5	21.4
0°-90°	1726.8	31.0
90°-120°	780.2	14.0
90°-150°	2856.0	51.2
90°-180°	3848.0	69.0
0°-180°	5575.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	509	509	509	509	509	
5°	510	508	504	508	507	48
15°	487	488	488	495	494	137
25°	442	448	454	463	465	203
35°	381	394	408	424	429	238
45°	313	332	358	381	388	241
55°	240	266	304	331	341	214
65°	164	200	243	274	283	163
75°	91	132	179	211	220	96
85°	26	72	119	150	161	28
90°	8	61	115	149	160	8
95°	64	69	120	152	160	74
105°	276	324	118	154	165	295
115°	518	542	597	204	148	510
125°	730	742	783	809	818	652
135°	902	917	932	957	961	697
145°	1046	1045	1060	1071	1070	654
155°	1152	1144	1155	1160	1153	531
165°	1214	1208	1211	1217	1211	343
175°	1242	1235	1237	1243	1234	118
180°	1239	1239	1239	1239	1239	

TEST NUMBER: P998618

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	508.7	508.7	508.7	508.7	508.7
2.5°	512.4	510.2	505.0	508.7	507.2
5°	510.2	508.0	503.5	508.0	507.2
7.5°	506.5	505.0	501.3	506.5	505.7
10°	502.1	500.6	498.4	504.3	503.5
12.5°	494.7	495.4	493.9	499.8	499.1
15°	486.6	488.1	488.1	494.7	493.9
17.5°	476.3	479.2	481.4	488.1	488.1
20°	465.9	469.6	472.6	480.7	480.7
22.5°	454.9	459.3	463.7	471.8	473.3
25°	442.3	447.5	454.1	463.0	465.2
27.5°	427.6	435.7	443.1	454.1	455.6
30°	412.9	422.4	432.0	443.8	446.0
32.5°	396.6	407.7	419.5	433.5	437.9
35°	381.2	393.7	407.7	423.9	429.1
37.5°	364.2	378.2	395.9	413.6	418.8
40°	347.2	363.5	383.4	402.5	409.2
42.5°	331.0	347.2	370.8	392.2	398.8
45°	312.6	332.5	358.3	381.2	388.5
47.5°	294.9	316.3	345.8	369.4	377.5
50°	276.5	299.3	332.5	357.6	365.7
52.5°	258.8	283.1	318.5	344.3	353.1
55°	239.6	266.1	304.5	331.0	340.6
57.5°	221.2	250.7	289.0	317.7	327.3
60°	201.3	233.0	275.0	303.0	313.3
62.5°	183.6	216.7	258.8	289.0	298.6
65°	163.7	199.8	243.3	273.5	283.1
67.5°	146.0	183.6	227.8	258.0	268.4
70°	126.8	165.1	210.9	242.6	251.4
72.5°	109.1	148.9	195.4	226.3	237.4
75°	90.7	132.0	179.1	210.9	220.4
77.5°	73.0	115.7	163.7	195.4	205.7
80°	55.3	100.3	148.2	179.1	189.5
82.5°	40.5	84.8	133.4	164.4	174.0
85°	26.5	72.2	119.4	150.4	160.7
87.5°	16.2	60.5	107.6	137.9	147.4
90°	8.3	60.9	115.2	149.2	159.9
92.5°	29.0	64.5	112.2	142.7	152.5
95°	64.2	69.2	119.8	152.2	160.1
97.5°	110.1	68.3	125.3	155.3	165.0
100°	163.9	68.3	124.8	159.3	169.2
102.5°	222.2	244.8	121.5	157.8	168.6
105°	276.2	324.5	118.1	153.7	165.4
107.5°	339.9	380.0	114.7	149.6	161.3
110°	400.0	433.6	210.7	144.6	156.3

TEST NUMBER: P998618

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	457.4	485.3	504.1	141.2	152.1
115°	518.3	541.8	597.3	204.4	148.0
117.5°	570.5	594.3	640.6	534.5	307.0
120°	629.7	646.1	691.8	723.1	610.2
122.5°	679.9	694.9	740.2	765.4	773.0
125°	730.3	741.9	782.6	808.7	818.0
127.5°	776.9	788.6	822.0	849.5	856.9
130°	820.8	834.4	859.7	887.3	892.3
132.5°	865.6	876.5	897.4	922.5	927.5
135°	902.5	916.8	932.3	956.8	960.9
137.5°	941.9	952.7	965.3	988.3	990.8
140°	980.5	986.9	998.3	1018.2	1018.1
142.5°	1012.7	1018.3	1030.0	1045.9	1045.2
145°	1046.1	1045.2	1060.4	1071.1	1070.3
147.5°	1075.7	1073.0	1088.2	1093.4	1092.0
150°	1104.4	1098.1	1112.4	1117.8	1113.3
152.5°	1128.6	1121.4	1134.8	1140.2	1134.0
155°	1151.9	1143.8	1154.6	1159.9	1152.8
157.5°	1170.7	1163.5	1171.6	1177.9	1170.7
160°	1186.8	1181.5	1186.8	1192.2	1185.9
162.5°	1201.2	1195.8	1200.3	1206.6	1198.5
165°	1213.7	1208.4	1211.0	1217.3	1211.0
167.5°	1223.6	1218.2	1220.9	1227.2	1219.1
170°	1231.7	1226.3	1228.1	1234.3	1226.3
172.5°	1237.0	1231.7	1233.5	1239.7	1231.7
175°	1241.5	1235.2	1237.0	1243.3	1234.3
177.5°	1243.3	1237.0	1237.9	1244.2	1236.1
180°	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P998618

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.40	11.14	11.50	12.24	13.76	13.48	14.22	14.57	15.32	16.83
	3H	11.86	12.52	12.96	13.63	15.16	16.06	16.73	17.16	17.83	19.37
	4H	12.33	12.96	13.44	14.07	15.61	17.31	17.94	18.42	19.05	20.59
	6H	12.60	13.19	13.73	14.30	15.85	18.60	19.18	19.72	20.30	21.85
	8H	12.66	13.22	13.79	14.35	15.89	19.25	19.81	20.38	20.94	22.48
	12H	12.67	13.20	13.80	14.32	15.89	19.97	20.51	21.11	21.63	23.19
4H	2H	11.44	12.08	12.56	13.18	14.72	13.79	14.43	14.92	15.54	17.08
	3H	13.14	13.67	14.27	14.81	16.36	16.58	17.11	17.70	18.25	19.80
	4H	13.76	14.25	14.89	15.37	16.94	17.99	18.48	19.12	19.61	21.18
	6H	14.16	14.59	15.30	15.74	17.30	19.45	19.88	20.59	21.02	22.58
	8H	14.27	14.67	15.41	15.81	17.39	20.20	20.60	21.34	21.74	23.32
	12H	14.31	14.67	15.46	15.82	17.41	21.03	21.39	22.18	22.54	24.13
8H	4H	14.54	14.94	15.67	16.08	17.65	18.12	18.52	19.26	19.66	21.24
	6H	15.16	15.50	16.32	16.68	18.25	19.75	20.08	20.91	21.26	22.84
	8H	15.38	15.68	16.55	16.84	18.43	20.64	20.93	21.80	22.09	23.68
	12H	15.51	15.77	16.68	16.93	18.56	21.62	21.88	22.79	23.04	24.67
12H	4H	14.73	15.09	15.88	16.24	17.83	18.09	18.46	19.25	19.61	21.19
	6H	15.50	15.79	16.66	16.95	18.54	19.77	20.06	20.93	21.22	22.82
	8H	15.79	16.05	16.96	17.21	18.84	20.69	20.95	21.86	22.11	23.74