

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999657

Luminaire Tested: SA2XXRDIP-B290D925UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999657
REPORT IS A COMBINATION OF REPORTS P988210 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D925UB40-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4257.0 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999657

CATALOG NUMBER: SA2XXRDIP-B290D925UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999657

CATALOG NUMBER: SA2XXRDIP-B290D925UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	92	88	84	81	82	78	75	73	60	58	57	44	42	41	28	28	27
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20
4	70	60	53	47	62	54	47	43	42	37	34	31	28	26	20	19	17
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	18	17	15
6	59	48	40	35	52	43	36	32	34	29	25	25	22	19	17	15	14
7	55	43	36	30	48	39	32	28	30	26	22	23	19	17	15	13	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7688	7688	7688
5°	7701	7315	7261
10°	7625	6937	6709
15°	7521	6492	6080
20°	7382	5987	5422
25°	7241	5467	4820
30°	7049	4961	4163
35°	6862	4450	3598
40°	6673	3950	3016
45°	6452	3432	2509
50°	6222	2934	2043
55°	5985	2435	1621
60°	5708	1947	1226
65°	5393	1485	997
70°	5006	1077	793
75°	4526	822	607
80°	3824	556	406
85°	2670	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6452 cd/sqm

TEST NUMBER: P999657

CATALOG NUMBER: SA2XXRDIP-B290D925UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	1.1
10°-20°	125.0	2.9
20°-30°	175.5	4.1
30°-40°	191.3	4.5
40°-50°	175.8	4.1
50°-60°	138.0	3.2
60°-70°	89.9	2.1
70°-80°	46.3	1.1
80°-90°	15.1	0.4
90°-100°	72.0	1.7
100°-110°	228.9	5.4
110°-120°	391.7	9.2
120°-130°	515.2	12.1
130°-140°	578.3	13.6
140°-150°	567.1	13.3
150°-160°	475.7	11.2
160°-170°	315.5	7.4
170°-180°	110.3	2.6
0°-30°	346.0	8.1
0°-40°	537.2	12.6
0°-60°	851.1	20.0
0°-90°	1002.3	23.5
90°-120°	692.7	16.3
90°-150°	2353.2	55.3
90°-180°	3255.0	76.5
0°-180°	4257.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	486	486	486	486	486	
5°	486	484	478	482	480	46
15°	462	457	442	434	430	130
25°	419	405	376	358	352	193
35°	361	339	300	272	263	226
45°	295	266	220	189	178	228
55°	225	190	143	116	108	201
65°	152	116	76	62	60	150
75°	81	50	35	32	32	86
85°	19	10	8	8	8	22
90°	1	13	34	32	33	4
95°	51	61	63	63	61	57
105°	211	214	216	218	218	223
115°	393	399	397	396	393	389
125°	572	581	578	575	574	511
135°	740	750	752	752	749	572
145°	898	905	911	912	908	561
155°	1027	1030	1032	1037	1034	473
165°	1117	1116	1116	1123	1118	315
175°	1162	1159	1157	1164	1158	110
180°	1164	1164	1164	1164	1164	

TEST NUMBER: P999657

CATALOG NUMBER: SA2XXRDIP-B290D925UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	485.7	485.7	485.7	485.7	485.7
2.5°	487.9	485.7	480.9	485.3	484.4
5°	485.7	483.5	477.8	481.8	480.5
7.5°	481.8	479.2	473.0	474.8	472.6
10°	476.5	473.4	464.6	463.3	460.7
12.5°	469.9	466.0	454.1	451.5	446.6
15°	462.0	457.2	442.2	433.9	429.5
17.5°	452.8	445.7	427.3	417.6	410.6
20°	442.2	433.4	411.5	400.5	390.8
22.5°	430.8	420.7	395.2	380.2	373.7
25°	419.4	405.3	376.3	358.3	351.7
27.5°	405.7	390.8	358.7	338.0	327.9
30°	391.2	374.5	339.4	316.9	305.1
32.5°	377.2	356.9	320.9	294.5	283.5
35°	361.3	338.9	300.2	272.5	262.9
37.5°	346.0	321.8	280.9	250.6	239.6
40°	329.7	303.3	260.7	229.5	218.0
42.5°	313.0	284.9	240.5	207.9	196.9
45°	295.4	266.0	219.8	188.6	178.0
47.5°	278.7	247.5	200.0	168.8	159.1
50°	260.2	229.0	180.7	150.3	141.1
52.5°	242.2	209.2	162.2	133.2	124.8
55°	224.6	190.3	142.9	116.5	108.1
57.5°	206.6	171.4	125.7	101.1	94.1
60°	188.1	153.0	107.7	85.3	78.2
62.5°	170.1	135.0	92.3	71.2	67.7
65°	151.7	116.1	76.5	61.5	60.2
67.5°	134.1	98.5	61.5	54.1	52.8
70°	115.6	81.3	51.0	46.6	44.8
72.5°	98.0	65.5	42.6	39.1	38.2
75°	80.9	50.1	35.2	32.1	31.7
77.5°	63.7	35.6	27.7	25.9	25.1
80°	47.9	25.5	21.1	19.3	19.3
82.5°	33.4	17.1	14.5	13.6	13.6
85°	18.9	9.7	8.4	8.4	8.4
87.5°	7.0	3.5	3.5	3.1	3.1
90°	1.0	12.8	34.4	32.4	33.4
92.5°	21.6	29.5	30.5	31.4	31.4
95°	51.1	60.9	62.9	62.9	60.9
97.5°	85.5	94.3	98.2	98.2	98.2
100°	124.8	132.6	135.6	135.6	134.6
102.5°	166.0	171.9	175.8	176.8	175.8
105°	211.2	214.2	216.1	218.1	218.1
107.5°	256.4	260.3	260.3	261.3	256.4
110°	299.6	305.5	305.5	305.5	302.6

TEST NUMBER: P999657

CATALOG NUMBER: SA2XXRDIP-B290D925UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	346.8	352.7	351.7	348.7	346.8
115°	393.0	398.8	396.9	395.9	393.0
117.5°	439.1	447.0	442.1	439.1	436.2
120°	485.3	493.2	485.3	485.3	482.4
122.5°	527.5	537.4	532.5	529.5	527.5
125°	571.7	580.6	577.6	574.7	573.7
127.5°	615.0	625.8	621.9	617.9	615.0
130°	655.3	668.0	666.1	664.1	660.2
132.5°	700.4	710.3	711.2	706.3	703.4
135°	739.7	750.5	752.5	751.5	748.6
137.5°	783.0	791.8	793.8	792.8	788.9
140°	821.3	830.1	835.0	835.0	831.1
142.5°	860.6	869.4	872.4	873.3	869.4
145°	897.9	904.8	910.7	911.7	907.7
147.5°	931.3	940.1	944.1	946.0	942.1
150°	965.7	971.6	975.5	978.5	975.5
152.5°	996.1	1002.0	1006.9	1010.9	1006.9
155°	1026.6	1029.5	1032.5	1037.4	1034.5
157.5°	1053.1	1055.1	1057.0	1063.9	1059.0
160°	1076.7	1078.7	1079.6	1085.5	1081.6
162.5°	1098.3	1098.3	1099.3	1106.2	1101.3
165°	1117.0	1116.0	1116.0	1122.9	1118.0
167.5°	1133.7	1130.7	1130.7	1137.6	1132.7
170°	1146.4	1143.5	1142.5	1149.4	1143.5
172.5°	1155.3	1152.3	1151.4	1158.2	1152.3
175°	1162.2	1159.2	1157.3	1164.1	1158.2
177.5°	1166.1	1163.1	1161.2	1167.1	1161.2
180°	1164.1	1164.1	1164.1	1164.1	1164.1

(END OF REPORT)