

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998619

Luminaire Tested: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998619
REPORT IS A COMBINATION OF REPORTS P984362 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5189.0 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998619

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P998619

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	93	88	84	80	84	80	76	73	63	61	59	48	47	45	34	33	32
2	84	77	70	65	76	69	64	59	55	51	48	42	39	37	30	28	26
3	77	67	59	53	69	60	54	49	48	43	40	37	33	31	26	24	22
4	70	59	51	45	62	53	46	41	42	37	33	32	29	26	23	21	19
5	64	52	44	38	57	47	40	35	38	32	28	29	25	22	21	18	16
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14
7	54	42	34	28	49	38	31	26	30	25	21	23	20	17	17	14	12
8	50	38	30	25	45	34	28	23	28	23	19	21	18	15	15	13	11
9	47	34	27	22	42	31	25	20	25	20	17	20	16	13	14	12	10
10	43	31	24	20	39	29	22	18	23	18	15	18	14	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8052	8052	8052
5°	8089	7708	7665
10°	8035	7442	7332
15°	7921	7166	6992
20°	7777	6876	6670
25°	7636	6597	6376
30°	7440	6315	6085
35°	7240	6043	5873
40°	7027	5809	5661
45°	6827	5595	5476
50°	6612	5398	5294
55°	6384	5190	5108
60°	6108	4972	4913
65°	5819	4722	4689
70°	5491	4454	4447
75°	5074	4184	4219
80°	4415	3905	3984
85°	3743	3641	3779

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6827 cd/sqm

TEST NUMBER: P998619

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.2	0.9
10°-20°	138.3	2.7
20°-30°	209.6	4.0
30°-40°	255.2	4.9
40°-50°	274.6	5.3
50°-60°	266.6	5.1
60°-70°	232.9	4.5
70°-80°	179.2	3.5
80°-90°	123.3	2.4
90°-100°	154.6	3.0
100°-110°	288.7	5.6
110°-120°	430.5	8.3
120°-130°	535.8	10.3
130°-140°	585.9	11.3
140°-150°	566.9	10.9
150°-160°	474.2	9.1
160°-170°	314.5	6.1
170°-180°	109.9	2.1
0°-30°	396.1	7.6
0°-40°	651.3	12.6
0°-60°	1192.5	23.0
0°-90°	1727.9	33.3
90°-120°	873.8	16.8
90°-150°	2562.4	49.4
90°-180°	3461.0	66.7
0°-180°	5189.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	509	509	509	509	509	
5°	510	508	504	508	507	48
15°	487	488	488	495	494	137
25°	442	448	454	463	465	203
35°	381	394	408	424	429	238
45°	313	332	358	381	388	241
55°	240	266	304	331	341	214
65°	164	200	243	274	283	163
75°	91	132	179	211	220	96
85°	26	72	119	150	161	28
90°	8	63	132	159	169	8
95°	57	101	148	176	182	61
105°	214	239	279	307	315	227
115°	395	409	440	461	466	390
125°	572	580	601	618	624	511
135°	738	749	758	773	776	571
145°	895	902	908	913	913	559
155°	1023	1026	1029	1034	1031	471
165°	1114	1113	1113	1119	1114	314
175°	1159	1156	1154	1161	1155	110
180°	1161	1161	1161	1161	1161	

TEST NUMBER: P998619

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	508.7	508.7	508.7	508.7	508.7
2.5°	512.4	510.2	505.0	508.7	507.2
5°	510.2	508.0	503.5	508.0	507.2
7.5°	506.5	505.0	501.3	506.5	505.7
10°	502.1	500.6	498.4	504.3	503.5
12.5°	494.7	495.4	493.9	499.8	499.1
15°	486.6	488.1	488.1	494.7	493.9
17.5°	476.3	479.2	481.4	488.1	488.1
20°	465.9	469.6	472.6	480.7	480.7
22.5°	454.9	459.3	463.7	471.8	473.3
25°	442.3	447.5	454.1	463.0	465.2
27.5°	427.6	435.7	443.1	454.1	455.6
30°	412.9	422.4	432.0	443.8	446.0
32.5°	396.6	407.7	419.5	433.5	437.9
35°	381.2	393.7	407.7	423.9	429.1
37.5°	364.2	378.2	395.9	413.6	418.8
40°	347.2	363.5	383.4	402.5	409.2
42.5°	331.0	347.2	370.8	392.2	398.8
45°	312.6	332.5	358.3	381.2	388.5
47.5°	294.9	316.3	345.8	369.4	377.5
50°	276.5	299.3	332.5	357.6	365.7
52.5°	258.8	283.1	318.5	344.3	353.1
55°	239.6	266.1	304.5	331.0	340.6
57.5°	221.2	250.7	289.0	317.7	327.3
60°	201.3	233.0	275.0	303.0	313.3
62.5°	183.6	216.7	258.8	289.0	298.6
65°	163.7	199.8	243.3	273.5	283.1
67.5°	146.0	183.6	227.8	258.0	268.4
70°	126.8	165.1	210.9	242.6	251.4
72.5°	109.1	148.9	195.4	226.3	237.4
75°	90.7	132.0	179.1	210.9	220.4
77.5°	73.0	115.7	163.7	195.4	205.7
80°	55.3	100.3	148.2	179.1	189.5
82.5°	40.5	84.8	133.4	164.4	174.0
85°	26.5	72.2	119.4	150.4	160.7
87.5°	16.2	60.5	107.6	137.9	147.4
90°	8.4	62.8	131.6	159.1	169.0
92.5°	28.1	75.1	121.1	150.7	159.6
95°	56.8	101.2	147.5	175.5	182.3
97.5°	90.4	130.9	177.5	204.8	213.6
100°	129.6	164.6	208.9	236.2	243.3
102.5°	169.9	200.2	243.9	271.4	278.5
105°	214.3	238.6	278.9	306.6	314.7
107.5°	259.3	280.9	317.7	343.8	347.0
110°	301.6	322.3	358.4	382.0	387.1

TEST NUMBER: P998619

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	348.6	366.3	399.3	419.9	426.1
115°	394.6	408.7	439.9	461.1	466.2
117.5°	440.0	453.7	479.8	499.0	503.4
120°	486.0	496.8	518.5	539.1	544.3
122.5°	528.1	538.6	561.0	578.0	582.7
125°	571.5	580.3	601.0	617.9	623.6
127.5°	614.6	624.6	640.5	655.1	658.8
130°	654.7	666.7	680.2	696.0	697.9
132.5°	699.8	708.8	720.9	733.0	735.9
135°	738.2	748.9	758.3	772.8	775.8
137.5°	781.3	790.1	795.7	808.8	810.0
140°	819.5	827.6	834.0	845.8	846.2
142.5°	858.6	866.7	869.7	879.5	879.2
145°	895.1	902.0	907.9	913.3	913.0
147.5°	928.4	937.3	941.2	943.8	942.1
150°	962.7	968.6	972.5	975.5	972.5
152.5°	993.1	999.0	1003.9	1007.8	1003.9
155°	1023.4	1026.4	1029.3	1034.2	1031.3
157.5°	1049.9	1051.8	1053.8	1060.7	1055.8
160°	1073.4	1075.4	1076.3	1082.2	1078.3
162.5°	1094.9	1094.9	1095.9	1102.8	1097.9
165°	1113.5	1112.6	1112.6	1119.4	1114.5
167.5°	1130.2	1127.3	1127.3	1134.1	1129.2
170°	1142.9	1140.0	1139.0	1145.9	1140.0
172.5°	1151.7	1148.8	1147.8	1154.7	1148.8
175°	1158.6	1155.7	1153.7	1160.6	1154.7
177.5°	1162.5	1159.6	1157.6	1163.5	1157.6
180°	1160.6	1160.6	1160.6	1160.6	1160.6

TEST NUMBER: P998619

CATALOG NUMBER: SA2XXDIP-B485D925UB27-4F0-XX-W2A-D1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.70	11.46	11.78	12.54	14.03	13.77	14.53	14.85	15.61	17.10
	3H	12.15	12.84	13.24	13.93	15.43	16.35	17.04	17.44	18.13	19.64
	4H	12.62	13.27	13.72	14.37	15.88	17.60	18.25	18.70	19.35	20.86
	6H	12.90	13.50	14.01	14.60	16.12	18.89	19.50	20.00	20.59	22.12
	8H	12.96	13.53	14.07	14.65	16.16	19.55	20.12	20.66	21.24	22.76
	12H	12.97	13.52	14.09	14.62	16.17	20.27	20.82	21.39	21.93	23.47
4H	2H	11.74	12.39	12.84	13.48	14.99	14.09	14.74	15.20	15.84	17.35
	3H	13.44	13.99	14.55	15.11	16.63	16.87	17.42	17.99	18.54	20.07
	4H	14.05	14.56	15.17	15.67	17.22	18.29	18.79	19.40	19.91	21.45
	6H	14.46	14.90	15.59	16.04	17.57	19.75	20.19	20.87	21.32	22.86
	8H	14.57	14.98	15.69	16.11	17.66	20.50	20.91	21.63	22.04	23.59
	12H	14.61	14.98	15.75	16.12	17.68	21.33	21.70	22.47	22.84	24.40
8H	4H	14.84	15.25	15.96	16.37	17.93	18.42	18.83	19.55	19.96	21.51
	6H	15.46	15.81	16.61	16.98	18.52	20.05	20.39	21.19	21.56	23.11
	8H	15.69	15.99	16.83	17.13	18.70	20.94	21.24	22.09	22.39	23.95
	12H	15.81	16.08	16.97	17.23	18.83	21.93	22.19	23.08	23.34	24.94
12H	4H	15.03	15.40	16.17	16.54	18.10	18.39	18.77	19.53	19.90	21.46
	6H	15.80	16.10	16.95	17.25	18.82	20.07	20.37	21.22	21.52	23.09
	8H	16.10	16.36	17.25	17.51	19.11	21.00	21.26	22.15	22.41	24.01