

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999695

Luminaire Tested: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999695
REPORT IS A COMBINATION OF REPORTS P988250 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5509.0 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999695

CATALOG NUMBER: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999695

CATALOG NUMBER: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28
3	78	69	62	57	70	63	57	52	50	46	42	38	35	33	27	26	24
4	72	61	54	48	64	56	49	44	44	40	36	34	31	29	25	23	21
5	66	55	47	41	59	50	43	38	40	35	31	31	27	25	22	20	19
6	61	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	33	28	24	25	22	19	19	16	15
8	52	40	33	28	47	37	30	26	30	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	16	16	14	12
10	45	33	27	22	41	31	24	20	25	20	17	20	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12939	12939	12939
5°	12960	12308	12218
10°	12831	11675	11289
15°	12655	10925	10231
20°	12421	10072	9124
25°	12184	9199	8111
30°	11861	8347	7004
35°	11547	7489	6054
40°	11229	6645	5076
45°	10857	5774	4223
50°	10472	4936	3437
55°	10072	4097	2730
60°	9607	3276	2065
65°	9072	2498	1678
70°	8423	1812	1334
75°	7613	1383	1020
80°	6435	936	683
85°	4492	430	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10857 cd/sqm

TEST NUMBER: P999695

CATALOG NUMBER: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.6	1.4
10°-20°	210.3	3.8
20°-30°	295.2	5.4
30°-40°	321.8	5.8
40°-50°	295.8	5.4
50°-60°	232.3	4.2
60°-70°	151.2	2.7
70°-80°	77.8	1.4
80°-90°	23.8	0.4
90°-100°	84.6	1.5
100°-110°	269.0	4.9
110°-120°	460.3	8.4
120°-130°	605.3	11.0
130°-140°	679.5	12.3
140°-150°	666.3	12.1
150°-160°	558.9	10.1
160°-170°	370.7	6.7
170°-180°	129.6	2.4
0°-30°	582.1	10.6
0°-40°	904.0	16.4
0°-60°	1432.1	26.0
0°-90°	1684.9	30.6
90°-120°	813.9	14.8
90°-150°	2764.9	50.2
90°-180°	3824.0	69.4
0°-180°	5509.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	817	817	817	817	817	
5°	817	814	804	811	808	78
15°	777	769	744	730	723	219
25°	706	682	633	603	592	325
35°	608	570	505	459	442	381
45°	497	448	370	317	300	384
55°	378	320	240	196	182	338
65°	255	195	129	104	101	253
75°	136	84	59	54	53	144
85°	32	16	14	14	14	36
90°	1	15	40	38	39	5
95°	60	72	74	74	72	67
105°	248	252	254	256	256	262
115°	462	469	466	465	462	457
125°	672	682	679	675	674	600
135°	869	882	884	883	880	672
145°	1055	1063	1070	1071	1066	659
155°	1206	1210	1213	1219	1215	555
165°	1312	1311	1311	1319	1314	370
175°	1366	1362	1360	1368	1361	130
180°	1368	1368	1368	1368	1368	

TEST NUMBER: P999695

CATALOG NUMBER: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	817.4	817.4	817.4	817.4	817.4
2.5°	821.1	817.4	809.2	816.6	815.1
5°	817.4	813.7	804.0	810.7	808.5
7.5°	810.7	806.3	795.9	798.9	795.2
10°	801.8	796.6	781.9	779.6	775.2
12.5°	790.7	784.1	764.1	759.7	751.5
15°	777.4	769.3	744.1	730.1	722.7
17.5°	761.9	750.0	719.0	702.7	690.9
20°	744.1	729.3	692.3	673.9	657.6
22.5°	724.9	707.9	665.0	639.8	628.7
25°	705.7	682.0	633.2	602.8	591.8
27.5°	682.7	657.6	603.6	568.8	551.8
30°	658.3	630.2	571.0	533.3	513.3
32.5°	634.7	600.6	540.0	495.6	477.1
35°	608.0	570.3	505.2	458.6	442.3
37.5°	582.1	541.5	472.7	421.6	403.1
40°	554.8	510.4	438.6	386.1	366.9
42.5°	526.7	479.3	404.6	349.9	331.4
45°	497.1	447.5	369.8	317.3	299.6
47.5°	469.0	416.4	336.6	284.0	267.8
50°	437.9	385.4	304.0	253.0	237.4
52.5°	407.6	352.1	272.9	224.1	210.1
55°	378.0	320.3	240.4	196.0	182.0
57.5°	347.7	288.5	211.6	170.1	158.3
60°	316.6	257.4	181.2	143.5	131.7
62.5°	286.3	227.1	155.3	119.8	113.9
65°	255.2	195.3	128.7	103.6	101.3
67.5°	225.6	165.7	103.6	91.0	88.8
70°	194.5	136.8	85.8	78.4	75.4
72.5°	165.0	110.2	71.7	65.8	64.4
75°	136.1	84.3	59.2	54.0	53.3
77.5°	107.3	59.9	46.6	43.6	42.2
80°	80.6	42.9	35.5	32.5	32.5
82.5°	56.2	28.8	24.4	22.9	22.9
85°	31.8	16.3	14.1	14.1	14.1
87.5°	11.8	5.9	5.9	5.2	5.2
90°	1.2	15.0	40.4	38.1	39.2
92.5°	25.4	34.6	35.8	36.9	36.9
95°	60.0	71.6	73.9	73.9	71.6
97.5°	100.4	110.8	115.4	115.4	115.4
100°	146.6	155.8	159.3	159.3	158.1
102.5°	195.1	202.0	206.6	207.8	206.6
105°	248.2	251.6	253.9	256.2	256.2
107.5°	301.3	305.9	305.9	307.0	301.3
110°	352.0	359.0	359.0	359.0	355.5

TEST NUMBER: P999695

CATALOG NUMBER: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	407.5	414.4	413.2	409.8	407.5
115°	461.7	468.6	466.3	465.2	461.7
117.5°	516.0	525.2	519.4	516.0	512.5
120°	570.2	579.4	570.2	570.2	566.7
122.5°	619.8	631.4	625.6	622.1	619.8
125°	671.8	682.2	678.7	675.2	674.1
127.5°	722.6	735.3	730.6	726.0	722.6
130°	769.9	784.9	782.6	780.3	775.7
132.5°	823.0	834.5	835.7	829.9	826.5
135°	869.2	881.9	884.2	883.0	879.5
137.5°	919.9	930.3	932.6	931.5	926.9
140°	965.0	975.4	981.1	981.1	976.5
142.5°	1011.1	1021.5	1025.0	1026.1	1021.5
145°	1055.0	1063.1	1070.0	1071.2	1066.5
147.5°	1094.2	1104.6	1109.2	1111.6	1106.9
150°	1134.6	1141.6	1146.2	1149.6	1146.2
152.5°	1170.4	1177.3	1183.1	1187.7	1183.1
155°	1206.2	1209.7	1213.1	1218.9	1215.4
157.5°	1237.4	1239.7	1242.0	1250.1	1244.3
160°	1265.1	1267.4	1268.5	1275.5	1270.8
162.5°	1290.5	1290.5	1291.6	1299.7	1293.9
165°	1312.4	1311.2	1311.2	1319.3	1313.5
167.5°	1332.0	1328.6	1328.6	1336.6	1330.9
170°	1347.0	1343.6	1342.4	1350.5	1343.6
172.5°	1357.4	1353.9	1352.8	1360.9	1353.9
175°	1365.5	1362.0	1359.7	1367.8	1360.9
177.5°	1370.1	1366.6	1364.3	1371.3	1364.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8

(END OF REPORT)