

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999723

Luminaire Tested: SA2XXRDIP-B485D330UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999723
REPORT IS A COMBINATION OF REPORTS P988278 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D330UB30-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2869.0 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999723

CATALOG NUMBER: SA2XXRDIP-B485D330UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999723

CATALOG NUMBER: SA2XXRDIP-B485D330UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	55
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	49	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13007	13007	13007
5°	13028	12374	12283
10°	12900	11736	11349
15°	12723	10983	10285
20°	12488	10128	9173
25°	12247	9249	8154
30°	11924	8392	7042
35°	11610	7529	6086
40°	11287	6682	5104
45°	10913	5806	4245
50°	10527	4962	3456
55°	10126	4119	2743
60°	9659	3294	2076
65°	9122	2511	1688
70°	8471	1823	1343
75°	7653	1390	1024
80°	6475	941	687
85°	4520	430	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10913 cd/sqm

TEST NUMBER: P999723

CATALOG NUMBER: SA2XXRDIP-B485D330UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	2.7
10°-20°	211.4	7.4
20°-30°	296.8	10.3
30°-40°	323.6	11.3
40°-50°	297.4	10.4
50°-60°	233.5	8.1
60°-70°	152.0	5.3
70°-80°	78.3	2.7
80°-90°	21.2	0.7
90°-100°	26.1	0.9
100°-110°	82.8	2.9
110°-120°	141.8	4.9
120°-130°	186.4	6.5
130°-140°	209.3	7.3
140°-150°	205.2	7.2
150°-160°	172.1	6.0
160°-170°	114.2	4.0
170°-180°	39.9	1.4
0°-30°	585.3	20.4
0°-40°	908.8	31.7
0°-60°	1439.7	50.2
0°-90°	1691.2	58.9
90°-120°	250.7	8.7
90°-150°	851.6	29.7
90°-180°	1178.0	41.1
0°-180°	2869.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	822	822	822	822	822	
5°	822	818	808	815	813	78
15°	782	773	748	734	726	220
25°	709	686	637	606	595	326
35°	611	573	508	461	445	383
45°	500	450	372	319	301	386
55°	380	322	242	197	183	340
65°	257	196	129	104	102	254
75°	137	85	60	54	54	145
85°	32	16	14	14	14	37
90°	0	5	12	12	12	3
95°	18	22	23	23	22	21
105°	76	78	78	79	79	81
115°	142	144	144	143	142	141
125°	207	210	209	208	208	185
135°	268	272	272	272	271	207
145°	325	327	330	330	328	203
155°	372	373	374	375	374	171
165°	404	404	404	406	405	114
175°	421	420	419	421	419	40
180°	421	421	421	421	421	

TEST NUMBER: P999723

CATALOG NUMBER: SA2XXRDIP-B485D330UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	821.7	821.7	821.7	821.7	821.7
2.5°	825.5	821.7	813.6	821.0	819.5
5°	821.7	818.0	808.3	815.0	812.8
7.5°	815.0	810.6	800.2	803.1	799.4
10°	806.1	800.9	786.0	783.8	779.3
12.5°	795.0	788.3	768.2	763.7	755.5
15°	781.6	773.4	748.1	734.0	726.5
17.5°	766.0	754.1	722.8	706.5	694.6
20°	748.1	733.2	696.1	677.5	661.1
22.5°	728.8	711.7	668.5	643.3	632.1
25°	709.4	685.6	636.6	606.1	594.9
27.5°	686.4	661.1	606.8	571.9	554.8
30°	661.8	633.6	574.1	536.2	516.1
32.5°	638.1	603.8	542.9	498.2	479.7
35°	611.3	573.4	507.9	461.1	444.7
37.5°	585.3	544.4	475.2	423.9	405.3
40°	557.7	513.1	441.0	388.2	368.9
42.5°	529.5	481.9	406.8	351.7	333.2
45°	499.7	449.9	371.8	319.0	301.2
47.5°	471.5	418.7	338.4	285.6	269.2
50°	440.2	387.4	305.6	254.3	238.7
52.5°	409.8	354.0	274.4	225.3	211.2
55°	380.0	322.0	241.7	197.1	182.9
57.5°	349.5	290.0	212.7	171.0	159.1
60°	318.3	258.8	182.2	144.3	132.4
62.5°	287.8	228.3	156.2	120.5	114.5
65°	256.6	196.3	129.4	104.1	101.9
67.5°	226.8	166.6	104.1	91.5	89.2
70°	195.6	137.6	86.3	78.8	75.9
72.5°	165.8	110.8	72.1	66.2	64.7
75°	136.8	84.8	59.5	54.3	53.5
77.5°	107.8	60.2	46.8	43.9	42.4
80°	81.1	43.1	35.7	32.7	32.7
82.5°	56.5	29.0	24.5	23.1	23.1
85°	32.0	16.4	14.1	14.1	14.1
87.5°	11.9	5.9	5.9	5.2	5.2
90°	0.4	4.6	12.4	11.7	12.1
92.5°	7.8	10.7	11.0	11.4	11.4
95°	18.5	22.0	22.8	22.8	22.0
97.5°	30.9	34.1	35.6	35.6	35.6
100°	45.1	48.0	49.1	49.1	48.7
102.5°	60.1	62.2	63.6	64.0	63.6
105°	76.4	77.5	78.2	78.9	78.9
107.5°	92.8	94.2	94.2	94.6	92.8
110°	108.4	110.6	110.6	110.6	109.5

TEST NUMBER: P999723

CATALOG NUMBER: SA2XXRDIP-B485D330UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	125.5	127.6	127.3	126.2	125.5
115°	142.2	144.3	143.6	143.3	142.2
117.5°	158.9	161.8	160.0	158.9	157.8
120°	175.6	178.5	175.6	175.6	174.6
122.5°	190.9	194.5	192.7	191.6	190.9
125°	206.9	210.1	209.0	208.0	207.6
127.5°	222.5	226.5	225.0	223.6	222.5
130°	237.1	241.7	241.0	240.3	238.9
132.5°	253.5	257.0	257.4	255.6	254.5
135°	267.7	271.6	272.3	272.0	270.9
137.5°	283.3	286.5	287.2	286.9	285.5
140°	297.2	300.4	302.2	302.2	300.8
142.5°	311.4	314.6	315.7	316.0	314.6
145°	324.9	327.4	329.6	329.9	328.5
147.5°	337.0	340.2	341.6	342.4	340.9
150°	349.5	351.6	353.0	354.1	353.0
152.5°	360.5	362.6	364.4	365.8	364.4
155°	371.5	372.6	373.6	375.4	374.3
157.5°	381.1	381.8	382.5	385.0	383.2
160°	389.6	390.3	390.7	392.8	391.4
162.5°	397.5	397.5	397.8	400.3	398.5
165°	404.2	403.9	403.9	406.3	404.6
167.5°	410.3	409.2	409.2	411.7	409.9
170°	414.9	413.8	413.5	415.9	413.8
172.5°	418.1	417.0	416.7	419.1	417.0
175°	420.6	419.5	418.8	421.3	419.1
177.5°	422.0	420.9	420.2	422.3	420.2
180°	421.3	421.3	421.3	421.3	421.3

(END OF REPORT)