

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998658

Luminaire Tested: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998658
REPORT IS A COMBINATION OF REPORTS P984401 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5381.0 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	46	46	46
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	42	41	40
2	88	80	75	70	79	73	69	64	60	57	54	48	46	44	37	36	34
3	80	71	64	59	73	65	59	54	54	49	46	43	40	37	33	31	30
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26
5	67	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18
8	53	42	34	29	49	38	32	27	32	27	23	26	23	20	21	18	16
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15231	15231	15231	15231
5°	15268	16241	15327	12921
10°	15091	17729	15185	10653
15°	14726	18701	14929	8974
20°	14495	17558	14495	7799
25°	14033	15085	14096	6975
30°	13274	11858	13526	6317
35°	12599	8200	12810	5780
40°	11826	6191	11961	5351
45°	10872	5087	11049	4890
50°	10046	4465	10063	4476
55°	9105	3805	9164	4027
60°	8102	3179	8214	3514
65°	7206	2585	7337	3001
70°	6310	2027	6470	2420
75°	5298	1472	5505	1755
80°	4136	933	4431	1043
85°	2712	470	2924	348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15745 cd/sqm

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.7	1.7
10°-20°	266.8	5.0
20°-30°	387.2	7.2
30°-40°	408.1	7.6
40°-50°	361.2	6.7
50°-60°	288.4	5.4
60°-70°	195.9	3.6
70°-80°	100.2	1.9
80°-90°	27.0	0.5
90°-100°	72.0	1.3
100°-110°	228.9	4.3
110°-120°	391.7	7.3
120°-130°	515.2	9.6
130°-140°	578.3	10.7
140°-150°	567.1	10.5
150°-160°	475.7	8.8
160°-170°	315.5	5.9
170°-180°	110.3	2.0
0°-30°	745.6	13.9
0°-40°	1153.7	21.4
0°-60°	1803.2	33.5
0°-90°	2126.3	39.5
90°-120°	692.7	12.9
90°-150°	2353.2	43.7
90°-180°	3255.0	60.5
0°-180°	5381.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	962	962	962	962	962	
5°	963	1075	967	855	963	91
15°	905	1321	917	634	905	255
25°	813	1101	816	509	813	372
35°	663	599	674	422	663	415
45°	498	361	506	347	498	386
55°	342	254	344	268	342	305
65°	203	156	206	181	203	201
75°	95	77	98	92	95	102
85°	19	20	21	15	19	22
90°	1	33	1	33	1	4
95°	51	61	51	61	51	57
105°	211	218	211	218	211	223
115°	393	393	393	393	393	389
125°	572	574	572	574	572	511
135°	740	749	740	749	740	572
145°	898	908	898	908	898	561
155°	1027	1034	1027	1034	1027	473
165°	1117	1118	1117	1118	1117	315
175°	1162	1158	1162	1158	1162	110
180°	1164	1164	1164	1164	1164	

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	967.4	969.6	973.3	974.1	981.5	987.4	994.0	994.0	996.3	995.5	989.6
5°	963.0	969.6	979.3	987.4	1000.7	1006.6	1015.5	1022.2	1028.1	1032.5	1031.8
7.5°	955.6	967.4	981.5	997.0	1014.8	1025.1	1037.7	1049.5	1057.7	1065.0	1070.2
10°	943.0	963.0	982.2	1002.9	1025.8	1039.9	1054.7	1070.2	1082.8	1096.9	1110.2
12.5°	926.0	954.8	978.5	1005.9	1034.0	1049.5	1073.2	1085.0	1109.4	1144.9	1154.5
15°	904.6	943.8	965.9	1000.7	1037.7	1050.3	1082.8	1102.0	1152.3	1174.5	1201.1
17.5°	884.6	928.2	957.8	997.7	1034.0	1058.4	1090.2	1129.4	1171.6	1203.4	1232.9
20°	868.3	910.5	946.0	990.3	1036.2	1067.3	1100.6	1147.9	1193.7	1226.3	1249.2
22.5°	831.3	885.3	926.7	976.3	1031.8	1074.7	1106.5	1158.2	1207.8	1227.8	1247.7
25°	812.8	859.4	907.5	963.7	1028.8	1079.8	1107.2	1164.9	1208.5	1215.9	1220.4
27.5°	778.8	831.3	887.5	951.9	1028.1	1071.0	1105.7	1158.2	1193.0	1187.8	1174.5
30°	736.7	801.0	863.1	932.7	1017.7	1064.3	1096.9	1144.9	1162.7	1136.1	1112.4
32.5°	705.6	766.2	835.0	915.6	1005.9	1050.3	1082.1	1119.8	1123.5	1075.4	1035.5
35°	663.4	730.7	808.4	893.5	985.9	1025.8	1055.4	1078.4	1060.6	993.3	946.0
37.5°	625.7	692.3	775.1	861.7	958.5	997.7	1021.4	1025.1	981.5	922.3	852.8
40°	584.3	653.1	739.6	830.6	928.2	962.2	977.0	965.9	903.1	834.3	753.7
42.5°	542.9	610.9	704.1	797.3	889.8	918.6	924.5	894.2	817.3	736.7	643.5
45°	497.8	568.8	662.0	755.9	845.4	861.7	862.4	818.8	727.8	643.5	556.9
47.5°	460.8	526.6	619.1	713.0	788.4	799.5	795.1	744.8	645.7	551.0	475.6
50°	420.1	483.0	574.7	667.1	731.5	734.4	723.3	651.6	554.7	468.2	408.3
52.5°	376.5	440.1	524.4	613.1	670.8	666.4	644.9	568.0	477.1	405.3	359.5
55°	341.7	397.9	477.1	563.6	604.3	591.7	568.0	489.6	417.9	357.2	317.3
57.5°	303.2	352.8	430.5	505.9	529.6	517.7	494.1	420.8	354.3	308.4	281.8
60°	267.0	312.1	380.2	443.0	461.5	448.9	421.6	355.8	307.7	269.2	249.3
62.5°	233.7	272.9	329.9	387.6	395.0	382.4	358.7	305.5	264.0	233.7	218.9
65°	202.7	239.6	285.5	329.1	335.8	322.5	298.1	259.6	224.8	205.6	191.6
67.5°	172.3	201.9	242.6	274.4	278.1	265.5	245.6	214.5	193.0	172.3	162.0
70°	145.7	167.9	199.7	225.6	227.1	215.2	204.9	176.8	160.5	145.7	137.6
72.5°	119.8	135.4	159.8	179.0	179.7	172.3	162.7	145.0	130.9	120.6	112.4
75°	94.7	108.0	122.8	139.8	139.0	133.1	125.7	114.6	102.8	96.2	92.5
77.5°	72.5	80.6	92.5	103.5	103.5	100.6	96.2	88.0	80.6	74.0	70.3
80°	51.8	57.0	66.6	70.3	71.7	71.0	67.3	61.4	58.4	53.3	51.8
82.5°	33.3	37.0	41.4	45.1	47.3	45.9	45.1	42.2	37.7	36.2	34.8
85°	19.2	20.7	22.9	25.1	25.9	25.1	26.6	24.4	22.2	22.2	21.4
87.5°	8.1	8.9	10.4	10.4	11.1	11.1	10.4	11.1	11.1	10.4	9.6
90°	1.0	3.6	6.2	8.9	11.5	12.8	15.2	20.0	24.8	29.6	34.4
92.5°	21.6	23.4	25.1	26.9	28.6	29.5	29.6	29.8	30.1	30.3	30.5
95°	51.1	53.3	55.5	57.6	59.8	60.9	61.1	61.6	62.0	62.5	62.9
97.5°	85.5	87.5	89.4	91.4	93.3	94.3	94.7	95.6	96.5	97.3	98.2
100°	124.8	126.5	128.3	130.0	131.7	132.6	132.9	133.6	134.3	134.9	135.6
102.5°	166.0	167.3	168.6	169.9	171.2	171.9	172.3	173.2	174.1	174.9	175.8
105°	211.2	211.9	212.5	213.2	213.9	214.2	214.4	214.8	215.3	215.7	216.1
107.5°	256.4	257.3	258.1	259.0	259.9	260.3	260.3	260.3	260.3	260.3	260.3
110°	299.6	300.9	302.2	303.5	304.8	305.5	305.5	305.5	305.5	305.5	305.5

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	346.8	348.1	349.4	350.7	352.0	352.7	352.6	352.4	352.1	351.9	351.7
115°	393.0	394.3	395.6	396.9	398.2	398.8	398.6	398.2	397.7	397.3	396.9
117.5°	439.1	440.9	442.6	444.4	446.1	447.0	446.5	445.4	444.3	443.2	442.1
120°	485.3	487.1	488.8	490.6	492.3	493.2	492.3	490.6	488.8	487.1	485.3
122.5°	527.5	529.7	531.9	534.1	536.3	537.4	536.9	535.8	534.7	533.6	532.5
125°	571.7	573.7	575.7	577.6	579.6	580.6	580.3	579.6	578.9	578.3	577.6
127.5°	615.0	617.4	619.8	622.2	624.6	625.8	625.4	624.5	623.6	622.8	621.9
130°	655.3	658.1	660.9	663.8	666.6	668.0	667.8	667.4	666.9	666.5	666.1
132.5°	700.4	702.6	704.8	707.0	709.2	710.3	710.4	710.6	710.8	711.0	711.2
135°	739.7	742.1	744.5	746.9	749.3	750.5	750.7	751.2	751.6	752.1	752.5
137.5°	783.0	785.0	786.9	788.9	790.8	791.8	792.0	792.5	792.9	793.4	793.8
140°	821.3	823.3	825.2	827.2	829.1	830.1	830.6	831.7	832.8	833.9	835.0
142.5°	860.6	862.6	864.5	866.5	868.4	869.4	869.7	870.4	871.1	871.7	872.4
145°	897.9	899.4	901.0	902.5	904.0	904.8	905.5	906.8	908.1	909.4	910.7
147.5°	931.3	933.3	935.2	937.2	939.1	940.1	940.5	941.4	942.3	943.2	944.1
150°	965.7	967.0	968.3	969.6	970.9	971.6	972.0	972.9	973.8	974.6	975.5
152.5°	996.1	997.4	998.7	1000.0	1001.3	1002.0	1002.5	1003.6	1004.7	1005.8	1006.9
155°	1026.6	1027.2	1027.9	1028.5	1029.2	1029.5	1029.8	1030.5	1031.2	1031.8	1032.5
157.5°	1053.1	1053.5	1054.0	1054.4	1054.9	1055.1	1055.3	1055.7	1056.2	1056.6	1057.0
160°	1076.7	1077.1	1077.6	1078.0	1078.5	1078.7	1078.8	1079.0	1079.2	1079.4	1079.6
162.5°	1098.3	1098.3	1098.3	1098.3	1098.3	1098.3	1098.4	1098.6	1098.9	1099.1	1099.3
165°	1117.0	1116.8	1116.6	1116.3	1116.1	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0
167.5°	1133.7	1133.0	1132.4	1131.7	1131.0	1130.7	1130.7	1130.7	1130.7	1130.7	1130.7
170°	1146.4	1145.8	1145.1	1144.5	1143.8	1143.5	1143.4	1143.2	1142.9	1142.7	1142.5
172.5°	1155.3	1154.6	1154.0	1153.3	1152.6	1152.3	1152.2	1152.0	1151.8	1151.6	1151.4
175°	1162.2	1161.5	1160.9	1160.2	1159.5	1159.2	1159.0	1158.6	1158.1	1157.7	1157.3
177.5°	1166.1	1165.4	1164.8	1164.1	1163.4	1163.1	1162.9	1162.5	1162.0	1161.6	1161.2
180°	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	1000.0	1000.7	1002.2	1009.6	1013.3	1014.0	1011.1	1017.7	1019.9	1017.7	1016.2
5°	1047.3	1051.7	1060.6	1070.2	1069.5	1070.2	1074.7	1079.1	1080.6	1074.7	1076.9
7.5°	1088.7	1097.6	1107.2	1122.0	1122.0	1129.4	1132.4	1136.1	1144.9	1140.5	1139.0
10°	1136.1	1147.9	1165.6	1189.3	1190.0	1197.4	1204.8	1216.7	1220.4	1217.4	1218.9
12.5°	1195.2	1218.2	1219.6	1245.5	1257.3	1258.8	1270.7	1268.4	1275.8	1275.8	1288.4
15°	1221.1	1256.6	1276.6	1301.7	1309.1	1300.2	1309.9	1320.2	1321.0	1321.0	1320.2
17.5°	1267.7	1281.8	1301.7	1315.0	1318.0	1318.0	1318.7	1323.2	1320.2	1314.3	1318.7
20°	1277.3	1283.2	1290.6	1289.2	1290.6	1283.2	1275.8	1268.4	1269.2	1265.5	1276.6
22.5°	1259.6	1258.1	1241.1	1230.0	1230.0	1215.2	1201.1	1194.5	1187.8	1190.0	1193.7
25°	1215.2	1192.3	1171.6	1155.3	1151.6	1127.9	1108.7	1102.8	1091.7	1100.6	1102.0
27.5°	1144.2	1118.3	1085.0	1071.0	1051.7	1042.1	1028.8	1011.1	988.1	1001.4	999.2
30°	1068.0	1029.5	1002.2	968.2	937.8	935.6	910.5	880.9	869.1	869.1	875.7
32.5°	983.0	931.9	892.0	843.9	814.3	801.7	771.4	741.8	748.5	726.3	734.4
35°	883.8	816.5	766.2	719.6	697.5	682.7	643.5	627.2	609.4	599.1	618.3
37.5°	789.2	711.5	647.2	596.1	588.0	561.4	534.7	524.4	514.0	518.5	517.7
40°	673.8	605.0	547.3	507.4	493.3	480.8	463.0	450.4	443.8	447.5	448.2
42.5°	569.5	511.8	468.9	440.8	429.0	420.1	411.2	400.9	398.7	398.7	401.6
45°	488.9	441.6	412.7	389.8	383.1	376.5	369.8	365.4	363.9	360.9	363.2
47.5°	424.5	386.8	369.1	352.1	344.7	343.2	337.3	335.0	332.1	331.3	332.1
50°	370.5	346.9	330.6	321.0	315.8	313.6	310.6	306.2	304.7	308.4	306.9
52.5°	332.8	310.6	301.8	292.1	289.2	286.2	281.8	282.5	281.8	280.3	280.3
55°	295.1	281.1	272.2	264.8	264.0	261.1	257.4	255.9	255.2	253.7	255.9
57.5°	264.8	253.7	245.6	238.9	235.9	235.9	232.2	229.3	229.3	228.5	229.3
60°	234.5	223.4	218.2	211.5	209.3	208.6	206.4	204.9	202.7	202.7	202.7
62.5°	206.4	197.5	191.6	185.6	186.4	182.7	179.7	178.2	178.2	179.0	179.0
65°	179.7	173.8	166.4	161.2	159.8	159.0	157.5	156.8	154.6	156.1	156.1
67.5°	155.3	147.2	142.7	140.5	138.3	137.6	136.1	134.6	133.9	133.1	134.6
70°	130.9	124.3	120.6	119.1	116.9	116.1	115.4	113.2	113.9	114.6	115.4
72.5°	108.7	102.8	102.1	97.6	97.6	97.6	94.7	96.2	95.4	93.9	95.4
75°	85.8	82.8	81.4	79.1	79.9	79.1	78.4	76.2	76.2	76.9	77.7
77.5°	68.0	65.1	64.3	62.1	60.6	62.1	60.6	59.9	59.9	60.6	60.6
80°	50.3	48.8	46.6	46.6	46.6	45.9	45.9	45.9	45.1	44.4	45.1
82.5°	33.3	33.3	32.5	31.8	32.5	31.1	31.8	31.8	31.8	31.8	31.8
85°	21.4	20.7	20.7	20.0	20.0	20.0	20.7	19.2	19.2	20.0	20.0
87.5°	9.6	9.6	9.6	10.4	9.6	9.6	9.6	10.4	9.6	9.6	9.6
90°	34.0	33.5	33.1	32.6	32.4	32.5	32.7	33.0	33.2	33.4	33.2
92.5°	30.7	30.9	31.1	31.3	31.4	31.4	31.4	31.4	31.4	31.4	31.4
95°	62.9	62.9	62.9	62.9	62.9	62.7	62.2	61.8	61.3	60.9	61.3
97.5°	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2
100°	135.6	135.6	135.6	135.6	135.6	135.5	135.3	135.0	134.8	134.6	134.8
102.5°	176.0	176.2	176.5	176.7	176.8	176.7	176.5	176.2	176.0	175.8	176.0
105°	216.5	217.0	217.4	217.9	218.1	218.1	218.1	218.1	218.1	218.1	218.1
107.5°	260.5	260.7	261.0	261.2	261.3	260.8	259.7	258.6	257.5	256.4	257.5
110°	305.5	305.5	305.5	305.5	305.5	305.2	304.5	303.9	303.2	302.6	303.2

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	351.0	350.4	349.7	349.0	348.7	348.5	348.1	347.6	347.2	346.8	347.2
115°	396.7	396.5	396.2	396.0	395.9	395.6	394.9	394.3	393.6	393.0	393.6
117.5°	441.4	440.8	440.1	439.4	439.1	438.8	438.1	437.5	436.8	436.2	436.8
120°	485.3	485.3	485.3	485.3	485.3	485.0	484.3	483.7	483.0	482.4	483.0
122.5°	531.8	531.2	530.5	529.8	529.5	529.3	528.8	528.4	527.9	527.5	527.9
125°	577.0	576.3	575.7	575.0	574.7	574.6	574.4	574.1	573.9	573.7	573.9
127.5°	621.0	620.1	619.2	618.3	617.9	617.6	616.9	616.3	615.6	615.0	615.6
130°	665.7	665.2	664.8	664.3	664.1	663.7	662.8	661.9	661.1	660.2	661.1
132.5°	710.1	709.0	707.9	706.8	706.3	706.0	705.3	704.7	704.0	703.4	704.0
135°	752.3	752.1	751.8	751.6	751.5	751.2	750.5	749.9	749.2	748.6	749.2
137.5°	793.6	793.4	793.1	792.9	792.8	792.4	791.5	790.6	789.8	788.9	789.8
140°	835.0	835.0	835.0	835.0	835.0	834.6	833.7	832.8	832.0	831.1	832.0
142.5°	872.6	872.8	873.0	873.2	873.3	872.9	872.0	871.1	870.3	869.4	870.3
145°	910.9	911.1	911.4	911.6	911.7	911.3	910.4	909.5	908.6	907.7	908.6
147.5°	944.5	944.9	945.4	945.8	946.0	945.6	944.7	943.8	943.0	942.1	943.0
150°	976.2	976.8	977.5	978.2	978.5	978.2	977.5	976.8	976.2	975.5	976.2
152.5°	1007.8	1008.7	1009.6	1010.5	1010.9	1010.5	1009.6	1008.7	1007.8	1006.9	1007.8
155°	1033.6	1034.7	1035.8	1036.9	1037.4	1037.1	1036.4	1035.8	1035.1	1034.5	1035.1
157.5°	1058.5	1060.1	1061.6	1063.1	1063.9	1063.4	1062.3	1061.2	1060.1	1059.0	1060.1
160°	1080.9	1082.2	1083.5	1084.8	1085.5	1085.1	1084.2	1083.3	1082.5	1081.6	1082.5
162.5°	1100.8	1102.4	1103.9	1105.4	1106.2	1105.7	1104.6	1103.5	1102.4	1101.3	1102.4
165°	1117.5	1119.1	1120.6	1122.1	1122.9	1122.4	1121.3	1120.2	1119.1	1118.0	1119.1
167.5°	1132.2	1133.8	1135.3	1136.8	1137.6	1137.1	1136.0	1134.9	1133.8	1132.7	1133.8
170°	1144.0	1145.6	1147.1	1148.6	1149.4	1148.7	1147.4	1146.1	1144.8	1143.5	1144.8
172.5°	1152.9	1154.4	1155.9	1157.4	1158.2	1157.5	1156.2	1154.9	1153.6	1152.3	1153.6
175°	1158.8	1160.3	1161.8	1163.3	1164.1	1163.4	1162.1	1160.8	1159.5	1158.2	1159.5
177.5°	1162.5	1163.8	1165.1	1166.4	1167.1	1166.4	1165.1	1163.8	1162.5	1161.2	1162.5
180°	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	1019.9	1014.8	1010.3	1011.1	1014.8	1011.8	1004.4	994.8	991.1	986.6	991.1
5°	1081.3	1076.9	1068.0	1068.7	1066.5	1063.6	1051.7	1036.9	1036.9	1025.1	1023.6
7.5°	1142.0	1135.3	1129.4	1127.9	1119.8	1113.9	1103.5	1082.8	1074.7	1060.6	1052.5
10°	1210.0	1204.8	1198.2	1190.0	1185.6	1175.3	1158.2	1127.9	1113.1	1093.9	1079.8
12.5°	1278.8	1278.1	1263.3	1247.0	1246.3	1230.0	1218.2	1177.5	1157.5	1131.6	1098.3
15°	1322.4	1318.7	1310.6	1302.5	1304.7	1286.9	1260.3	1212.2	1198.9	1167.9	1132.4
17.5°	1321.7	1321.7	1319.5	1318.0	1315.8	1310.6	1295.8	1264.0	1242.6	1203.4	1170.1
20°	1279.5	1289.2	1291.4	1290.6	1298.0	1301.7	1301.0	1281.0	1264.0	1229.2	1195.2
22.5°	1195.2	1217.4	1227.0	1232.9	1248.5	1256.6	1275.8	1268.4	1264.0	1238.1	1209.3
25°	1116.8	1124.2	1153.1	1154.5	1176.0	1196.0	1215.2	1227.8	1244.0	1234.4	1210.0
27.5°	1015.5	1032.5	1053.2	1068.7	1073.2	1113.9	1145.7	1169.3	1206.3	1209.3	1201.1
30°	900.9	909.0	943.0	963.7	987.4	1017.0	1062.8	1103.5	1136.8	1167.1	1177.5
32.5°	761.1	794.3	814.3	839.5	860.2	912.7	968.9	1021.4	1059.9	1110.9	1133.1
35°	633.1	659.0	693.0	703.4	741.1	785.5	858.7	926.0	984.4	1036.2	1081.3
37.5°	527.3	548.1	584.3	600.6	622.8	679.7	741.1	824.7	894.9	958.5	1014.8
40°	454.9	470.4	497.8	502.9	521.4	573.2	622.8	701.2	794.3	880.1	941.5
42.5°	405.3	412.7	431.2	437.9	449.7	484.4	528.8	602.8	689.3	778.1	864.6
45°	369.8	375.0	386.1	392.0	406.8	422.3	458.6	517.7	585.8	675.3	768.5
47.5°	338.0	344.7	349.1	352.8	360.9	377.9	401.6	445.2	510.3	592.4	682.7
50°	311.4	313.6	321.7	322.5	327.7	338.7	360.9	387.6	439.3	505.9	593.2
52.5°	284.8	287.0	292.1	297.3	299.5	308.4	323.2	345.4	383.9	436.4	514.0
55°	258.1	261.1	266.3	270.0	272.2	279.6	288.5	309.9	340.2	377.2	440.8
57.5°	231.5	238.2	239.6	241.9	245.6	253.7	261.8	274.4	298.1	332.1	378.7
60°	206.4	208.6	213.7	216.0	219.7	224.1	234.5	244.1	261.1	287.7	329.9
62.5°	180.5	185.6	187.9	190.1	193.0	198.2	204.9	215.2	230.0	251.5	284.8
65°	158.3	159.0	163.5	166.4	169.4	173.1	179.7	189.3	198.2	218.2	242.6
67.5°	136.8	138.3	139.8	142.7	146.4	150.1	156.1	161.2	172.3	185.6	204.9
70°	116.1	116.1	119.8	122.0	121.3	125.7	130.2	136.1	144.2	156.8	172.3
72.5°	97.6	96.9	99.8	100.6	102.1	105.0	108.0	113.9	118.3	128.0	139.8
75°	77.7	79.1	80.6	80.6	82.8	85.1	88.0	91.0	96.2	102.1	110.9
77.5°	61.4	61.4	62.9	63.6	65.8	65.1	68.0	71.0	74.7	79.9	86.5
80°	45.1	46.6	46.6	46.6	47.3	48.1	51.0	53.3	55.5	59.2	62.1
82.5°	31.8	31.8	33.3	33.3	33.3	34.8	34.8	35.5	37.0	39.2	41.4
85°	20.0	20.0	20.0	20.7	20.0	20.7	22.2	21.4	22.2	23.7	23.7
87.5°	9.6	9.6	9.6	9.6	9.6	10.4	9.6	10.4	11.1	11.1	11.1
90°	33.0	32.7	32.5	32.4	32.6	33.1	33.5	34.0	34.4	29.6	24.8
92.5°	31.4	31.4	31.4	31.4	31.3	31.1	30.9	30.7	30.5	30.3	30.1
95°	61.8	62.2	62.7	62.9	62.9	62.9	62.9	62.9	62.9	62.5	62.0
97.5°	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	97.3	96.5
100°	135.0	135.3	135.5	135.6	135.6	135.6	135.6	135.6	135.6	134.9	134.3
102.5°	176.2	176.5	176.7	176.8	176.7	176.5	176.2	176.0	175.8	174.9	174.1
105°	218.1	218.1	218.1	218.1	217.9	217.4	217.0	216.5	216.1	215.7	215.3
107.5°	258.6	259.7	260.8	261.3	261.2	261.0	260.7	260.5	260.3	260.3	260.3
110°	303.9	304.5	305.2	305.5	305.5	305.5	305.5	305.5	305.5	305.5	305.5

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	347.6	348.1	348.5	348.7	349.0	349.7	350.4	351.0	351.7	351.9	352.1
115°	394.3	394.9	395.6	395.9	396.0	396.2	396.5	396.7	396.9	397.3	397.7
117.5°	437.5	438.1	438.8	439.1	439.4	440.1	440.8	441.4	442.1	443.2	444.3
120°	483.7	484.3	485.0	485.3	485.3	485.3	485.3	485.3	485.3	487.1	488.8
122.5°	528.4	528.8	529.3	529.5	529.8	530.5	531.2	531.8	532.5	533.6	534.7
125°	574.1	574.4	574.6	574.7	575.0	575.7	576.3	577.0	577.6	578.3	578.9
127.5°	616.3	616.9	617.6	617.9	618.3	619.2	620.1	621.0	621.9	622.8	623.6
130°	661.9	662.8	663.7	664.1	664.3	664.8	665.2	665.7	666.1	666.5	666.9
132.5°	704.7	705.3	706.0	706.3	706.8	707.9	709.0	710.1	711.2	711.0	710.8
135°	749.9	750.5	751.2	751.5	751.6	751.8	752.1	752.3	752.5	752.1	751.6
137.5°	790.6	791.5	792.4	792.8	792.9	793.1	793.4	793.6	793.8	793.4	792.9
140°	832.8	833.7	834.6	835.0	835.0	835.0	835.0	835.0	835.0	833.9	832.8
142.5°	871.1	872.0	872.9	873.3	873.2	873.0	872.8	872.6	872.4	871.7	871.1
145°	909.5	910.4	911.3	911.7	911.6	911.4	911.1	910.9	910.7	909.4	908.1
147.5°	943.8	944.7	945.6	946.0	945.8	945.4	944.9	944.5	944.1	943.2	942.3
150°	976.8	977.5	978.2	978.5	978.2	977.5	976.8	976.2	975.5	974.6	973.8
152.5°	1008.7	1009.6	1010.5	1010.9	1010.5	1009.6	1008.7	1007.8	1006.9	1005.8	1004.7
155°	1035.8	1036.4	1037.1	1037.4	1036.9	1035.8	1034.7	1033.6	1032.5	1031.8	1031.2
157.5°	1061.2	1062.3	1063.4	1063.9	1063.1	1061.6	1060.1	1058.5	1057.0	1056.6	1056.2
160°	1083.3	1084.2	1085.1	1085.5	1084.8	1083.5	1082.2	1080.9	1079.6	1079.4	1079.2
162.5°	1103.5	1104.6	1105.7	1106.2	1105.4	1103.9	1102.4	1100.8	1099.3	1099.1	1098.9
165°	1120.2	1121.3	1122.4	1122.9	1122.1	1120.6	1119.1	1117.5	1116.0	1116.0	1116.0
167.5°	1134.9	1136.0	1137.1	1137.6	1136.8	1135.3	1133.8	1132.2	1130.7	1130.7	1130.7
170°	1146.1	1147.4	1148.7	1149.4	1148.6	1147.1	1145.6	1144.0	1142.5	1142.7	1142.9
172.5°	1154.9	1156.2	1157.5	1158.2	1157.4	1155.9	1154.4	1152.9	1151.4	1151.6	1151.8
175°	1160.8	1162.1	1163.4	1164.1	1163.3	1161.8	1160.3	1158.8	1157.3	1157.7	1158.1
177.5°	1163.8	1165.1	1166.4	1167.1	1166.4	1165.1	1163.8	1162.5	1161.2	1161.6	1162.0
180°	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	987.4	983.7	981.5	983.0	978.5	967.4	967.4	971.1	966.7	962.2	955.6
5°	1014.8	1007.4	1002.9	1002.2	991.8	974.1	970.4	966.7	957.1	946.7	935.6
7.5°	1041.4	1028.1	1020.7	1015.5	1000.7	977.8	968.2	960.0	944.5	929.0	914.9
10°	1063.6	1044.3	1035.5	1027.3	1008.1	979.3	963.7	948.9	929.0	909.0	891.2
12.5°	1081.3	1059.1	1048.0	1036.2	1012.5	974.8	955.6	931.9	911.9	885.3	867.6
15°	1110.9	1065.0	1054.7	1043.6	1019.2	967.4	943.8	917.1	889.8	854.3	835.0
17.5°	1134.6	1073.2	1072.4	1048.8	1017.0	964.5	928.2	893.5	863.9	828.4	798.0
20°	1148.6	1085.8	1073.9	1049.5	1009.6	944.5	906.8	868.3	836.5	793.6	763.3
22.5°	1160.5	1103.5	1072.4	1042.9	994.0	937.8	882.4	846.1	802.5	755.9	727.0
25°	1164.9	1107.2	1074.7	1040.6	983.0	918.6	855.7	816.5	767.7	725.6	686.4
27.5°	1165.6	1106.5	1066.5	1031.0	967.4	893.5	829.1	787.7	733.7	684.9	645.7
30°	1158.2	1098.3	1062.1	1023.6	952.6	870.5	796.6	750.7	693.0	644.2	603.5
32.5°	1136.1	1082.1	1052.5	1010.3	933.4	838.7	765.5	714.5	653.8	605.7	566.5
35°	1099.1	1062.1	1029.5	990.3	908.3	809.1	734.4	674.5	613.1	567.3	530.3
37.5°	1053.2	1033.2	1002.9	964.5	879.4	782.5	699.7	633.1	571.7	527.3	491.1
40°	991.1	996.3	966.7	931.9	845.4	746.3	654.6	591.0	533.3	491.8	456.3
42.5°	923.8	945.2	928.2	894.9	807.7	706.3	621.3	551.0	494.8	451.9	422.3
45°	851.3	888.3	877.9	853.5	768.5	664.2	573.9	505.9	456.3	414.9	389.0
47.5°	772.2	824.7	824.7	806.9	724.8	622.0	533.3	463.7	414.9	385.3	360.2
50°	691.5	750.7	760.3	748.5	676.0	573.9	483.7	420.8	378.7	349.8	331.3
52.5°	607.2	676.0	693.8	687.8	624.2	528.1	443.0	381.6	343.2	318.0	301.8
55°	526.6	606.5	625.7	627.9	568.8	477.8	397.9	343.9	306.9	289.9	275.9
57.5°	450.4	527.3	548.8	552.5	512.6	431.9	355.8	308.4	275.1	261.1	250.0
60°	385.3	449.7	477.8	485.9	451.2	378.7	316.6	270.7	245.6	232.2	221.9
62.5°	332.1	383.9	413.4	415.7	400.1	332.1	275.9	237.4	216.0	204.1	199.0
65°	280.3	326.9	344.7	353.5	341.0	287.7	238.2	206.4	189.3	179.0	173.8
67.5°	238.9	268.5	283.3	295.1	282.5	242.6	202.7	176.8	164.2	153.8	150.9
70°	196.0	220.4	231.5	243.3	232.2	201.9	173.1	149.4	138.3	130.2	126.5
72.5°	156.8	176.0	186.4	193.8	187.1	162.0	138.3	122.0	113.9	108.0	105.8
75°	124.3	137.6	143.5	148.7	145.7	126.5	111.7	98.4	91.0	85.8	84.3
77.5°	94.7	104.3	110.9	112.4	108.7	96.2	83.6	75.4	69.5	66.6	65.1
80°	67.3	73.2	76.9	79.1	75.4	70.3	61.4	55.5	50.3	46.6	45.9
82.5°	45.1	48.1	51.0	50.3	48.8	44.4	39.2	36.2	34.0	31.1	31.1
85°	25.9	26.6	28.1	28.8	28.1	25.1	22.2	20.7	19.2	17.0	17.0
87.5°	11.1	11.8	11.8	12.6	11.1	11.1	9.6	8.1	8.1	7.4	6.7
90°	20.0	15.2	12.8	11.5	8.9	6.2	3.6	1.0	3.6	6.2	8.9
92.5°	29.8	29.6	29.5	28.6	26.9	25.1	23.4	21.6	23.4	25.1	26.9
95°	61.6	61.1	60.9	59.8	57.6	55.5	53.3	51.1	53.3	55.5	57.6
97.5°	95.6	94.7	94.3	93.3	91.4	89.4	87.5	85.5	87.5	89.4	91.4
100°	133.6	132.9	132.6	131.7	130.0	128.3	126.5	124.8	126.5	128.3	130.0
102.5°	173.2	172.3	171.9	171.2	169.9	168.6	167.3	166.0	167.3	168.6	169.9
105°	214.8	214.4	214.2	213.9	213.2	212.5	211.9	211.2	211.9	212.5	213.2
107.5°	260.3	260.3	260.3	259.9	259.0	258.1	257.3	256.4	257.3	258.1	259.0
110°	305.5	305.5	305.5	304.8	303.5	302.2	300.9	299.6	300.9	302.2	303.5

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	352.4	352.6	352.7	352.0	350.7	349.4	348.1	346.8	348.1	349.4	350.7
115°	398.2	398.6	398.8	398.2	396.9	395.6	394.3	393.0	394.3	395.6	396.9
117.5°	445.4	446.5	447.0	446.1	444.4	442.6	440.9	439.1	440.9	442.6	444.4
120°	490.6	492.3	493.2	492.3	490.6	488.8	487.1	485.3	487.1	488.8	490.6
122.5°	535.8	536.9	537.4	536.3	534.1	531.9	529.7	527.5	529.7	531.9	534.1
125°	579.6	580.3	580.6	579.6	577.6	575.7	573.7	571.7	573.7	575.7	577.6
127.5°	624.5	625.4	625.8	624.6	622.2	619.8	617.4	615.0	617.4	619.8	622.2
130°	667.4	667.8	668.0	666.6	663.8	660.9	658.1	655.3	658.1	660.9	663.8
132.5°	710.6	710.4	710.3	709.2	707.0	704.8	702.6	700.4	702.6	704.8	707.0
135°	751.2	750.7	750.5	749.3	746.9	744.5	742.1	739.7	742.1	744.5	746.9
137.5°	792.5	792.0	791.8	790.8	788.9	786.9	785.0	783.0	785.0	786.9	788.9
140°	831.7	830.6	830.1	829.1	827.2	825.2	823.3	821.3	823.3	825.2	827.2
142.5°	870.4	869.7	869.4	868.4	866.5	864.5	862.6	860.6	862.6	864.5	866.5
145°	906.8	905.5	904.8	904.0	902.5	901.0	899.4	897.9	899.4	901.0	902.5
147.5°	941.4	940.5	940.1	939.1	937.2	935.2	933.3	931.3	933.3	935.2	937.2
150°	972.9	972.0	971.6	970.9	969.6	968.3	967.0	965.7	967.0	968.3	969.6
152.5°	1003.6	1002.5	1002.0	1001.3	1000.0	998.7	997.4	996.1	997.4	998.7	1000.0
155°	1030.5	1029.8	1029.5	1029.2	1028.5	1027.9	1027.2	1026.6	1027.2	1027.9	1028.5
157.5°	1055.7	1055.3	1055.1	1054.9	1054.4	1054.0	1053.5	1053.1	1053.5	1054.0	1054.4
160°	1079.0	1078.8	1078.7	1078.5	1078.0	1077.6	1077.1	1076.7	1077.1	1077.6	1078.0
162.5°	1098.6	1098.4	1098.3	1098.3	1098.3	1098.3	1098.3	1098.3	1098.3	1098.3	1098.3
165°	1116.0	1116.0	1116.0	1116.1	1116.3	1116.6	1116.8	1117.0	1116.8	1116.6	1116.3
167.5°	1130.7	1130.7	1130.7	1131.0	1131.7	1132.4	1133.0	1133.7	1133.0	1132.4	1131.7
170°	1143.2	1143.4	1143.5	1143.8	1144.5	1145.1	1145.8	1146.4	1145.8	1145.1	1144.5
172.5°	1152.0	1152.2	1152.3	1152.6	1153.3	1154.0	1154.6	1155.3	1154.6	1154.0	1153.3
175°	1158.6	1159.0	1159.2	1159.5	1160.2	1160.9	1161.5	1162.2	1161.5	1160.9	1160.2
177.5°	1162.5	1162.9	1163.1	1163.4	1164.1	1164.8	1165.4	1166.1	1165.4	1164.8	1164.1
180°	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	951.9	955.6	954.8	947.5	939.3	932.7	920.1	921.6	917.1	917.9	922.3
5°	928.2	928.2	925.3	914.9	901.6	894.2	880.1	876.4	867.6	866.8	866.1
7.5°	903.1	899.4	895.7	880.9	864.6	852.8	833.5	829.1	820.2	814.3	811.4
10°	873.5	868.3	860.9	843.9	823.9	809.1	789.2	783.3	766.2	758.8	754.4
12.5°	840.9	838.0	826.2	812.1	779.6	763.3	734.4	740.4	723.3	708.6	706.3
15°	808.4	797.3	790.7	767.7	728.5	721.1	698.2	686.4	670.8	659.0	659.0
17.5°	776.6	759.6	744.8	720.4	691.5	670.8	653.8	647.9	628.7	616.8	614.6
20°	734.4	715.2	711.5	676.8	656.8	633.9	617.6	602.8	588.7	583.6	579.9
22.5°	694.5	672.3	666.4	636.8	616.8	593.9	577.6	567.3	556.9	553.2	546.6
25°	651.6	638.3	629.4	597.6	575.4	554.0	542.9	535.5	525.9	525.1	520.7
27.5°	610.2	597.6	588.7	558.4	542.1	522.2	513.3	505.2	500.0	497.8	495.5
30°	574.7	560.6	550.3	528.1	508.1	491.8	484.4	479.3	476.3	472.6	471.9
32.5°	535.5	527.3	513.3	496.3	480.8	465.2	460.8	457.1	452.6	451.2	450.4
35°	502.2	491.1	482.2	463.0	456.3	443.0	437.9	434.9	429.0	427.5	426.0
37.5°	469.7	459.3	449.7	437.9	425.3	417.9	414.9	410.5	407.5	408.3	406.8
40°	437.1	429.0	421.6	409.0	401.6	397.9	392.0	387.6	386.1	386.8	386.1
42.5°	405.3	397.9	393.5	383.9	376.5	372.8	369.1	364.6	366.9	366.9	369.1
45°	376.5	369.8	366.9	359.5	355.0	349.1	345.4	344.7	347.6	346.9	346.9
47.5°	346.9	344.7	341.0	334.3	328.4	324.7	324.0	324.0	326.9	328.4	327.7
50°	324.0	319.5	315.1	309.9	305.5	304.0	301.8	303.2	306.2	306.2	307.7
52.5°	295.1	292.1	290.7	286.2	283.3	283.3	283.3	284.0	286.2	288.5	287.7
55°	270.0	267.7	266.3	264.0	260.3	261.1	260.3	261.8	264.0	266.3	267.7
57.5°	243.3	242.6	241.1	237.4	237.4	236.7	238.9	239.6	243.3	244.8	247.0
60°	219.7	217.4	217.4	214.5	214.5	214.5	216.7	218.9	221.9	222.6	224.1
62.5°	194.5	194.5	193.8	191.6	191.6	193.8	194.5	197.5	199.0	199.0	201.2
65°	170.9	170.1	169.4	170.1	170.9	170.9	173.1	174.5	176.0	176.8	177.5
67.5°	147.2	146.4	147.9	147.2	148.7	151.6	150.9	153.1	155.3	155.3	156.1
70°	125.0	126.5	125.7	127.2	126.5	128.0	130.2	130.9	130.9	131.7	133.9
72.5°	104.3	104.3	104.3	103.5	104.3	105.8	107.2	108.0	109.5	110.2	112.4
75°	84.3	84.3	82.8	84.3	84.3	85.8	87.3	87.3	87.3	88.8	91.0
77.5°	63.6	64.3	63.6	65.1	65.1	65.8	67.3	66.6	68.0	68.8	69.5
80°	46.6	45.9	45.9	45.9	46.6	46.6	48.1	48.8	48.8	51.0	49.6
82.5°	29.6	30.3	29.6	30.3	30.3	31.1	30.3	31.1	31.8	33.3	32.5
85°	17.0	16.3	16.3	17.0	16.3	16.3	17.0	16.3	17.0	16.3	17.0
87.5°	6.7	5.9	5.9	5.9	5.9	5.2	5.2	4.4	4.4	4.4	3.7
90°	11.5	12.8	15.2	20.0	24.8	29.6	34.4	34.0	33.5	33.1	32.6
92.5°	28.6	29.5	29.6	29.8	30.1	30.3	30.5	30.7	30.9	31.1	31.3
95°	59.8	60.9	61.1	61.6	62.0	62.5	62.9	62.9	62.9	62.9	62.9
97.5°	93.3	94.3	94.7	95.6	96.5	97.3	98.2	98.2	98.2	98.2	98.2
100°	131.7	132.6	132.9	133.6	134.3	134.9	135.6	135.6	135.6	135.6	135.6
102.5°	171.2	171.9	172.3	173.2	174.1	174.9	175.8	176.0	176.2	176.5	176.7
105°	213.9	214.2	214.4	214.8	215.3	215.7	216.1	216.5	217.0	217.4	217.9
107.5°	259.9	260.3	260.3	260.3	260.3	260.3	260.3	260.5	260.7	261.0	261.2
110°	304.8	305.5	305.5	305.5	305.5	305.5	305.5	305.5	305.5	305.5	305.5

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	352.0	352.7	352.6	352.4	352.1	351.9	351.7	351.0	350.4	349.7	349.0
115°	398.2	398.8	398.6	398.2	397.7	397.3	396.9	396.7	396.5	396.2	396.0
117.5°	446.1	447.0	446.5	445.4	444.3	443.2	442.1	441.4	440.8	440.1	439.4
120°	492.3	493.2	492.3	490.6	488.8	487.1	485.3	485.3	485.3	485.3	485.3
122.5°	536.3	537.4	536.9	535.8	534.7	533.6	532.5	531.8	531.2	530.5	529.8
125°	579.6	580.6	580.3	579.6	578.9	578.3	577.6	577.0	576.3	575.7	575.0
127.5°	624.6	625.8	625.4	624.5	623.6	622.8	621.9	621.0	620.1	619.2	618.3
130°	666.6	668.0	667.8	667.4	666.9	666.5	666.1	665.7	665.2	664.8	664.3
132.5°	709.2	710.3	710.4	710.6	710.8	711.0	711.2	710.1	709.0	707.9	706.8
135°	749.3	750.5	750.7	751.2	751.6	752.1	752.5	752.3	752.1	751.8	751.6
137.5°	790.8	791.8	792.0	792.5	792.9	793.4	793.8	793.6	793.4	793.1	792.9
140°	829.1	830.1	830.6	831.7	832.8	833.9	835.0	835.0	835.0	835.0	835.0
142.5°	868.4	869.4	869.7	870.4	871.1	871.7	872.4	872.6	872.8	873.0	873.2
145°	904.0	904.8	905.5	906.8	908.1	909.4	910.7	910.9	911.1	911.4	911.6
147.5°	939.1	940.1	940.5	941.4	942.3	943.2	944.1	944.5	944.9	945.4	945.8
150°	970.9	971.6	972.0	972.9	973.8	974.6	975.5	976.2	976.8	977.5	978.2
152.5°	1001.3	1002.0	1002.5	1003.6	1004.7	1005.8	1006.9	1007.8	1008.7	1009.6	1010.5
155°	1029.2	1029.5	1029.8	1030.5	1031.2	1031.8	1032.5	1033.6	1034.7	1035.8	1036.9
157.5°	1054.9	1055.1	1055.3	1055.7	1056.2	1056.6	1057.0	1058.5	1060.1	1061.6	1063.1
160°	1078.5	1078.7	1078.8	1079.0	1079.2	1079.4	1079.6	1080.9	1082.2	1083.5	1084.8
162.5°	1098.3	1098.3	1098.4	1098.6	1098.9	1099.1	1099.3	1100.8	1102.4	1103.9	1105.4
165°	1116.1	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1117.5	1119.1	1120.6	1122.1
167.5°	1131.0	1130.7	1130.7	1130.7	1130.7	1130.7	1130.7	1132.2	1133.8	1135.3	1136.8
170°	1143.8	1143.5	1143.4	1143.2	1142.9	1142.7	1142.5	1144.0	1145.6	1147.1	1148.6
172.5°	1152.6	1152.3	1152.2	1152.0	1151.8	1151.6	1151.4	1152.9	1154.4	1155.9	1157.4
175°	1159.5	1159.2	1159.0	1158.6	1158.1	1157.7	1157.3	1158.8	1160.3	1161.8	1163.3
177.5°	1163.4	1163.1	1162.9	1162.5	1162.0	1161.6	1161.2	1162.5	1163.8	1165.1	1166.4
180°	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	917.1	919.3	914.2	912.7	914.2	909.0	910.5	911.9	911.9	914.2	915.6
5°	863.9	860.9	855.7	854.3	852.8	855.0	853.5	855.7	856.5	861.7	862.4
7.5°	811.4	806.9	802.5	798.0	796.6	792.9	796.6	796.6	801.7	800.3	804.0
10°	749.2	748.5	742.6	740.4	737.4	731.5	739.6	737.4	741.1	747.8	749.2
12.5°	703.4	695.2	698.9	688.6	692.3	686.4	687.1	687.1	693.0	693.8	692.3
15°	659.7	653.1	643.5	639.0	636.8	633.9	643.5	644.2	639.8	650.1	646.4
17.5°	615.4	615.4	606.5	604.3	598.4	601.3	599.8	600.6	599.1	606.5	610.2
20°	576.9	573.2	570.2	571.0	563.6	562.1	560.6	562.1	567.3	572.5	573.9
22.5°	545.8	543.6	536.2	537.7	531.8	534.0	532.5	536.2	537.0	537.0	542.1
25°	516.3	513.3	514.0	511.1	508.9	508.9	506.6	508.9	511.8	513.3	514.0
27.5°	494.1	491.8	488.1	485.9	487.4	483.7	486.7	488.9	488.9	487.4	488.9
30°	467.4	468.9	468.9	461.5	464.5	463.0	465.2	466.7	466.7	467.4	466.0
32.5°	449.7	445.2	444.5	443.8	443.8	440.8	440.8	443.0	443.8	444.5	446.7
35°	426.0	426.0	422.3	424.5	421.6	422.3	421.6	422.3	423.8	421.6	423.8
37.5°	404.6	405.3	403.8	405.3	406.1	404.6	403.1	406.1	404.6	404.6	403.1
40°	386.1	385.3	386.1	386.1	386.1	386.8	385.3	385.3	385.3	383.9	382.4
42.5°	370.5	366.1	367.6	368.3	366.1	366.1	366.9	366.1	368.3	363.9	363.9
45°	348.4	346.9	347.6	347.6	349.1	346.9	348.4	349.1	346.9	346.1	344.7
47.5°	328.4	329.9	328.4	329.9	329.9	331.3	328.4	329.1	329.9	326.9	324.7
50°	308.4	308.4	310.6	309.9	310.6	309.2	309.2	308.4	309.2	307.7	305.5
52.5°	289.9	287.7	291.4	290.7	289.9	289.2	288.5	289.2	287.7	286.2	286.2
55°	267.0	267.0	269.2	270.0	270.0	268.5	267.0	267.7	267.0	266.3	265.5
57.5°	248.5	245.6	247.0	247.8	247.8	245.6	247.0	245.6	245.6	246.3	244.1
60°	224.8	224.8	223.4	225.6	225.6	224.1	224.1	224.8	223.4	222.6	221.9
62.5°	199.7	200.4	202.7	203.4	204.1	202.7	201.2	201.9	201.9	199.7	200.4
65°	178.2	179.7	182.7	181.9	180.5	181.2	179.7	180.5	178.2	179.0	176.8
67.5°	157.5	156.8	157.5	157.5	159.0	158.3	156.8	156.8	156.1	158.3	156.1
70°	135.4	135.4	135.4	135.4	136.1	136.8	135.4	133.9	134.6	133.1	132.4
72.5°	112.4	113.2	112.4	113.9	111.7	113.2	113.2	112.4	111.7	111.7	111.7
75°	91.0	92.5	90.2	91.0	90.2	91.7	91.0	91.0	89.5	88.8	89.5
77.5°	69.5	70.3	68.8	69.5	68.8	69.5	69.5	68.8	68.8	68.8	68.8
80°	49.6	50.3	49.6	48.8	48.1	49.6	48.1	48.8	49.6	48.8	50.3
82.5°	31.8	31.8	31.1	31.8	30.3	30.3	31.1	31.1	30.3	31.8	30.3
85°	15.5	15.5	17.0	15.5	14.8	14.8	14.8	15.5	14.8	16.3	15.5
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.4	3.0
90°	32.4	32.5	32.7	33.0	33.2	33.4	33.2	33.0	32.7	32.5	32.4
92.5°	31.4	31.4	31.4	31.4	31.4	31.4	31.4	31.4	31.4	31.4	31.4
95°	62.9	62.7	62.2	61.8	61.3	60.9	61.3	61.8	62.2	62.7	62.9
97.5°	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2
100°	135.6	135.5	135.3	135.0	134.8	134.6	134.8	135.0	135.3	135.5	135.6
102.5°	176.8	176.7	176.5	176.2	176.0	175.8	176.0	176.2	176.5	176.7	176.8
105°	218.1	218.1	218.1	218.1	218.1	218.1	218.1	218.1	218.1	218.1	218.1
107.5°	261.3	260.8	259.7	258.6	257.5	256.4	257.5	258.6	259.7	260.8	261.3
110°	305.5	305.2	304.5	303.9	303.2	302.6	303.2	303.9	304.5	305.2	305.5

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	348.7	348.5	348.1	347.6	347.2	346.8	347.2	347.6	348.1	348.5	348.7
115°	395.9	395.6	394.9	394.3	393.6	393.0	393.6	394.3	394.9	395.6	395.9
117.5°	439.1	438.8	438.1	437.5	436.8	436.2	436.8	437.5	438.1	438.8	439.1
120°	485.3	485.0	484.3	483.7	483.0	482.4	483.0	483.7	484.3	485.0	485.3
122.5°	529.5	529.3	528.8	528.4	527.9	527.5	527.9	528.4	528.8	529.3	529.5
125°	574.7	574.6	574.4	574.1	573.9	573.7	573.9	574.1	574.4	574.6	574.7
127.5°	617.9	617.6	616.9	616.3	615.6	615.0	615.6	616.3	616.9	617.6	617.9
130°	664.1	663.7	662.8	661.9	661.1	660.2	661.1	661.9	662.8	663.7	664.1
132.5°	706.3	706.0	705.3	704.7	704.0	703.4	704.0	704.7	705.3	706.0	706.3
135°	751.5	751.2	750.5	749.9	749.2	748.6	749.2	749.9	750.5	751.2	751.5
137.5°	792.8	792.4	791.5	790.6	789.8	788.9	789.8	790.6	791.5	792.4	792.8
140°	835.0	834.6	833.7	832.8	832.0	831.1	832.0	832.8	833.7	834.6	835.0
142.5°	873.3	872.9	872.0	871.1	870.3	869.4	870.3	871.1	872.0	872.9	873.3
145°	911.7	911.3	910.4	909.5	908.6	907.7	908.6	909.5	910.4	911.3	911.7
147.5°	946.0	945.6	944.7	943.8	943.0	942.1	943.0	943.8	944.7	945.6	946.0
150°	978.5	978.2	977.5	976.8	976.2	975.5	976.2	976.8	977.5	978.2	978.5
152.5°	1010.9	1010.5	1009.6	1008.7	1007.8	1006.9	1007.8	1008.7	1009.6	1010.5	1010.9
155°	1037.4	1037.1	1036.4	1035.8	1035.1	1034.5	1035.1	1035.8	1036.4	1037.1	1037.4
157.5°	1063.9	1063.4	1062.3	1061.2	1060.1	1059.0	1060.1	1061.2	1062.3	1063.4	1063.9
160°	1085.5	1085.1	1084.2	1083.3	1082.5	1081.6	1082.5	1083.3	1084.2	1085.1	1085.5
162.5°	1106.2	1105.7	1104.6	1103.5	1102.4	1101.3	1102.4	1103.5	1104.6	1105.7	1106.2
165°	1122.9	1122.4	1121.3	1120.2	1119.1	1118.0	1119.1	1120.2	1121.3	1122.4	1122.9
167.5°	1137.6	1137.1	1136.0	1134.9	1133.8	1132.7	1133.8	1134.9	1136.0	1137.1	1137.6
170°	1149.4	1148.7	1147.4	1146.1	1144.8	1143.5	1144.8	1146.1	1147.4	1148.7	1149.4
172.5°	1158.2	1157.5	1156.2	1154.9	1153.6	1152.3	1153.6	1154.9	1156.2	1157.5	1158.2
175°	1164.1	1163.4	1162.1	1160.8	1159.5	1158.2	1159.5	1160.8	1162.1	1163.4	1164.1
177.5°	1167.1	1166.4	1165.1	1163.8	1162.5	1161.2	1162.5	1163.8	1165.1	1166.4	1167.1
180°	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	913.4	919.3	917.1	909.0	918.6	918.6	925.3	925.3	933.4	936.4	940.8
5°	861.7	866.1	869.8	866.1	872.7	883.1	889.0	894.2	905.3	909.7	916.4
7.5°	806.2	814.3	818.0	818.0	829.1	840.9	852.8	860.2	875.7	881.6	888.3
10°	752.2	761.8	769.2	768.5	787.0	794.3	809.1	826.2	841.7	850.6	860.2
12.5°	695.2	700.4	710.8	725.6	730.0	743.3	760.3	781.8	809.9	818.0	832.1
15°	647.9	662.0	670.1	676.8	687.1	699.7	718.2	738.9	767.0	784.7	799.5
17.5°	608.0	626.5	631.6	630.2	643.5	662.7	684.1	699.7	724.8	746.3	760.3
20°	575.4	582.8	591.7	595.4	605.7	626.5	647.2	664.9	685.6	702.6	718.9
22.5°	542.9	548.8	556.2	562.8	571.0	582.8	602.8	625.0	644.9	661.2	679.7
25°	516.3	520.0	526.6	531.8	540.7	548.8	562.8	587.3	610.9	620.5	636.8
27.5°	490.4	493.3	497.8	503.7	508.1	516.3	528.8	548.8	573.2	582.8	605.0
30°	467.4	469.7	474.1	477.1	479.3	488.9	498.5	514.0	532.5	545.8	562.1
32.5°	446.0	448.2	452.6	453.4	456.3	461.5	470.4	484.4	500.7	511.8	525.9
35°	422.3	423.8	428.2	429.7	431.9	436.4	443.0	453.4	468.2	476.3	488.9
37.5°	403.8	403.1	406.1	408.3	411.2	413.4	415.7	426.0	437.1	444.5	454.1
40°	383.9	382.4	383.1	386.1	387.6	390.5	390.5	400.9	408.3	414.2	421.6
42.5°	363.9	363.2	361.7	363.2	364.6	365.4	366.1	373.5	380.9	386.1	394.2
45°	343.9	343.2	341.7	342.4	342.4	343.9	346.1	349.1	354.3	358.7	363.2
47.5°	325.4	324.0	321.7	321.0	322.5	322.5	322.5	325.4	330.6	332.1	336.5
50°	306.2	304.0	301.0	299.5	299.5	298.8	300.3	301.0	305.5	306.9	310.6
52.5°	285.5	284.0	281.1	278.1	278.8	277.4	278.1	278.8	280.3	282.5	284.8
55°	264.8	261.8	259.6	258.9	256.6	256.6	254.4	257.4	256.6	257.4	260.3
57.5°	244.8	241.9	238.2	236.7	234.5	233.7	232.2	231.5	232.2	234.5	236.7
60°	221.1	219.7	217.4	215.2	213.7	211.5	210.1	210.1	209.3	209.3	210.1
62.5°	198.2	197.5	194.5	193.8	192.3	190.8	188.6	187.1	187.1	188.6	189.3
65°	176.0	175.3	173.1	172.3	168.6	167.2	166.4	165.7	164.2	164.2	164.2
67.5°	155.3	153.1	153.1	149.4	146.4	145.0	143.5	142.7	142.7	142.7	143.5
70°	132.4	132.4	130.2	128.0	125.0	125.7	123.5	121.3	121.3	119.8	120.6
72.5°	110.2	109.5	107.2	106.5	104.3	102.1	100.6	102.1	99.8	99.1	99.8
75°	88.8	88.0	86.5	85.1	85.8	83.6	81.4	80.6	80.6	79.1	79.1
77.5°	68.0	69.5	66.6	65.8	64.3	62.9	62.1	61.4	61.4	61.4	62.9
80°	47.3	48.1	48.1	46.6	47.3	45.1	45.1	45.1	42.9	43.6	44.4
82.5°	30.3	30.3	29.6	30.3	29.6	29.6	28.8	28.8	28.1	28.1	28.8
85°	17.0	16.3	15.5	17.0	16.3	16.3	15.5	15.5	15.5	15.5	15.5
87.5°	3.7	4.4	4.4	4.4	4.4	5.2	5.2	5.2	5.9	5.9	5.9
90°	32.6	33.1	33.5	34.0	34.4	29.6	24.8	20.0	15.2	12.8	11.5
92.5°	31.3	31.1	30.9	30.7	30.5	30.3	30.1	29.8	29.6	29.5	28.6
95°	62.9	62.9	62.9	62.9	62.9	62.5	62.0	61.6	61.1	60.9	59.8
97.5°	98.2	98.2	98.2	98.2	98.2	97.3	96.5	95.6	94.7	94.3	93.3
100°	135.6	135.6	135.6	135.6	135.6	134.9	134.3	133.6	132.9	132.6	131.7
102.5°	176.7	176.5	176.2	176.0	175.8	174.9	174.1	173.2	172.3	171.9	171.2
105°	217.9	217.4	217.0	216.5	216.1	215.7	215.3	214.8	214.4	214.2	213.9
107.5°	261.2	261.0	260.7	260.5	260.3	260.3	260.3	260.3	260.3	260.3	259.9
110°	305.5	305.5	305.5	305.5	305.5	305.5	305.5	305.5	305.5	305.5	304.8

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	349.0	349.7	350.4	351.0	351.7	351.9	352.1	352.4	352.6	352.7	352.0
115°	396.0	396.2	396.5	396.7	396.9	397.3	397.7	398.2	398.6	398.8	398.2
117.5°	439.4	440.1	440.8	441.4	442.1	443.2	444.3	445.4	446.5	447.0	446.1
120°	485.3	485.3	485.3	485.3	485.3	487.1	488.8	490.6	492.3	493.2	492.3
122.5°	529.8	530.5	531.2	531.8	532.5	533.6	534.7	535.8	536.9	537.4	536.3
125°	575.0	575.7	576.3	577.0	577.6	578.3	578.9	579.6	580.3	580.6	579.6
127.5°	618.3	619.2	620.1	621.0	621.9	622.8	623.6	624.5	625.4	625.8	624.6
130°	664.3	664.8	665.2	665.7	666.1	666.5	666.9	667.4	667.8	668.0	666.6
132.5°	706.8	707.9	709.0	710.1	711.2	711.0	710.8	710.6	710.4	710.3	709.2
135°	751.6	751.8	752.1	752.3	752.5	752.1	751.6	751.2	750.7	750.5	749.3
137.5°	792.9	793.1	793.4	793.6	793.8	793.4	792.9	792.5	792.0	791.8	790.8
140°	835.0	835.0	835.0	835.0	835.0	833.9	832.8	831.7	830.6	830.1	829.1
142.5°	873.2	873.0	872.8	872.6	872.4	871.7	871.1	870.4	869.7	869.4	868.4
145°	911.6	911.4	911.1	910.9	910.7	909.4	908.1	906.8	905.5	904.8	904.0
147.5°	945.8	945.4	944.9	944.5	944.1	943.2	942.3	941.4	940.5	940.1	939.1
150°	978.2	977.5	976.8	976.2	975.5	974.6	973.8	972.9	972.0	971.6	970.9
152.5°	1010.5	1009.6	1008.7	1007.8	1006.9	1005.8	1004.7	1003.6	1002.5	1002.0	1001.3
155°	1036.9	1035.8	1034.7	1033.6	1032.5	1031.8	1031.2	1030.5	1029.8	1029.5	1029.2
157.5°	1063.1	1061.6	1060.1	1058.5	1057.0	1056.6	1056.2	1055.7	1055.3	1055.1	1054.9
160°	1084.8	1083.5	1082.2	1080.9	1079.6	1079.4	1079.2	1079.0	1078.8	1078.7	1078.5
162.5°	1105.4	1103.9	1102.4	1100.8	1099.3	1099.1	1098.9	1098.6	1098.4	1098.3	1098.3
165°	1122.1	1120.6	1119.1	1117.5	1116.0	1116.0	1116.0	1116.0	1116.0	1116.0	1116.1
167.5°	1136.8	1135.3	1133.8	1132.2	1130.7	1130.7	1130.7	1130.7	1130.7	1130.7	1131.0
170°	1148.6	1147.1	1145.6	1144.0	1142.5	1142.7	1142.9	1143.2	1143.4	1143.5	1143.8
172.5°	1157.4	1155.9	1154.4	1152.9	1151.4	1151.6	1151.8	1152.0	1152.2	1152.3	1152.6
175°	1163.3	1161.8	1160.3	1158.8	1157.3	1157.7	1158.1	1158.6	1159.0	1159.2	1159.5
177.5°	1166.4	1165.1	1163.8	1162.5	1161.2	1161.6	1162.0	1162.5	1162.9	1163.1	1163.4
180°	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1	1164.1

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	962.2	962.2	962.2	962.2
2.5°	944.5	944.5	955.6	967.4
5°	923.8	929.0	946.7	963.0
7.5°	903.8	912.7	934.9	955.6
10°	879.4	891.2	918.6	943.0
12.5°	855.7	866.8	898.6	926.0
15°	822.5	836.5	870.5	904.6
17.5°	789.2	803.2	844.6	884.6
20°	750.0	768.5	815.1	868.3
22.5°	713.7	736.7	788.4	831.3
25°	673.8	709.3	757.4	812.8
27.5°	638.3	673.8	722.6	778.8
30°	598.4	634.6	684.9	736.7
32.5°	559.9	593.2	642.0	705.6
35°	520.0	551.8	599.1	663.4
37.5°	483.7	514.8	566.5	625.7
40°	448.2	480.8	525.1	584.3
42.5°	414.9	443.8	483.7	542.9
45°	384.6	405.3	442.3	497.8
47.5°	352.8	371.3	405.3	460.8
50°	323.2	338.7	368.3	420.1
52.5°	294.4	307.7	335.0	376.5
55°	268.5	281.1	301.0	341.7
57.5°	241.9	251.5	270.7	303.2
60°	216.0	224.8	240.4	267.0
62.5°	190.1	197.5	212.3	233.7
65°	167.2	173.1	184.2	202.7
67.5°	145.0	148.7	157.5	172.3
70°	123.5	126.5	133.9	145.7
72.5°	100.6	103.5	111.7	119.8
75°	81.4	82.1	88.0	94.7
77.5°	63.6	62.9	67.3	72.5
80°	43.6	45.9	49.6	51.8
82.5°	29.6	30.3	31.8	33.3
85°	16.3	17.0	17.0	19.2
87.5°	6.7	7.4	7.4	8.1
90°	8.9	6.2	3.6	1.0
92.5°	26.9	25.1	23.4	21.6
95°	57.6	55.5	53.3	51.1
97.5°	91.4	89.4	87.5	85.5
100°	130.0	128.3	126.5	124.8
102.5°	169.9	168.6	167.3	166.0
105°	213.2	212.5	211.9	211.2
107.5°	259.0	258.1	257.3	256.4
110°	303.5	302.2	300.9	299.6

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	350.7	349.4	348.1	346.8
115°	396.9	395.6	394.3	393.0
117.5°	444.4	442.6	440.9	439.1
120°	490.6	488.8	487.1	485.3
122.5°	534.1	531.9	529.7	527.5
125°	577.6	575.7	573.7	571.7
127.5°	622.2	619.8	617.4	615.0
130°	663.8	660.9	658.1	655.3
132.5°	707.0	704.8	702.6	700.4
135°	746.9	744.5	742.1	739.7
137.5°	788.9	786.9	785.0	783.0
140°	827.2	825.2	823.3	821.3
142.5°	866.5	864.5	862.6	860.6
145°	902.5	901.0	899.4	897.9
147.5°	937.2	935.2	933.3	931.3
150°	969.6	968.3	967.0	965.7
152.5°	1000.0	998.7	997.4	996.1
155°	1028.5	1027.9	1027.2	1026.6
157.5°	1054.4	1054.0	1053.5	1053.1
160°	1078.0	1077.6	1077.1	1076.7
162.5°	1098.3	1098.3	1098.3	1098.3
165°	1116.3	1116.6	1116.8	1117.0
167.5°	1131.7	1132.4	1133.0	1133.7
170°	1144.5	1145.1	1145.8	1146.4
172.5°	1153.3	1154.0	1154.6	1155.3
175°	1160.2	1160.9	1161.5	1162.2
177.5°	1164.1	1164.8	1165.4	1166.1
180°	1164.1	1164.1	1164.1	1164.1

TEST NUMBER: P998658

CATALOG NUMBER: SA2XXDIP-B485D925UB40-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.24	14.99	15.29	16.04	17.45	11.73	12.48	12.78	13.53	14.95
	3H	15.04	15.71	16.10	16.77	18.21	13.07	13.74	14.13	14.80	16.23
	4H	15.21	15.84	16.28	16.90	18.34	13.53	14.16	14.59	15.22	16.66
	6H	15.25	15.83	16.32	16.89	18.35	13.83	14.41	14.91	15.47	16.93
	8H	15.22	15.78	16.31	16.86	18.31	13.91	14.46	14.99	15.54	16.99
	12H	15.18	15.71	16.27	16.78	18.25	13.95	14.47	15.03	15.55	17.02
4H	2H	14.27	14.90	15.34	15.96	17.40	12.16	12.80	13.24	13.86	15.30
	3H	15.24	15.77	16.32	16.85	18.31	13.61	14.14	14.70	15.23	16.69
	4H	15.51	15.99	16.60	17.07	18.55	14.15	14.63	15.23	15.71	17.18
	6H	15.63	16.05	16.73	17.15	18.62	14.52	14.93	15.62	16.03	17.50
	8H	15.63	16.02	16.73	17.11	18.60	14.63	15.01	15.72	16.11	17.59
	12H	15.59	15.94	16.70	17.05	18.54	14.68	15.03	15.79	16.14	17.63
8H	4H	15.51	15.90	16.61	16.99	18.48	14.28	14.67	15.38	15.76	17.25
	6H	15.69	16.01	16.80	17.14	18.62	14.71	15.03	15.83	16.16	17.65
	8H	15.72	15.99	16.84	17.11	18.61	14.86	15.14	15.98	16.26	17.76
	12H	15.69	15.94	16.82	17.05	18.59	14.95	15.19	16.08	16.31	17.85
12H	4H	15.46	15.81	16.58	16.92	18.41	14.25	14.60	15.36	15.71	17.20
	6H	15.66	15.94	16.79	17.06	18.56	14.71	14.99	15.83	16.11	17.61
	8H	15.69	15.94	16.82	17.05	18.59	14.86	15.11	15.99	16.22	17.76