

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999729

Luminaire Tested: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999729
REPORT IS A COMBINATION OF REPORTS P988284 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2882.0 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999729

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999729

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	55
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	49	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13069	13069	13069
5°	13090	12434	12342
10°	12961	11793	11403
15°	12784	11036	10334
20°	12548	10176	9216
25°	12306	9292	8192
30°	11982	8432	7075
35°	11665	7564	6115
40°	11342	6713	5127
45°	10966	5834	4265
50°	10577	4986	3472
55°	10174	4138	2757
60°	9704	3310	2086
65°	9165	2523	1696
70°	8510	1831	1348
75°	7692	1397	1030
80°	6499	946	692
85°	4534	433	334

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10966 cd/sqm

TEST NUMBER: P999729

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	2.7
10°-20°	212.4	7.4
20°-30°	298.2	10.3
30°-40°	325.1	11.3
40°-50°	298.8	10.4
50°-60°	234.7	8.1
60°-70°	152.7	5.3
70°-80°	78.6	2.7
80°-90°	21.3	0.7
90°-100°	26.2	0.9
100°-110°	83.2	2.9
110°-120°	142.4	4.9
120°-130°	187.2	6.5
130°-140°	210.2	7.3
140°-150°	206.1	7.2
150°-160°	172.9	6.0
160°-170°	114.7	4.0
170°-180°	40.1	1.4
0°-30°	588.0	20.4
0°-40°	913.1	31.7
0°-60°	1446.5	50.2
0°-90°	1699.2	59.0
90°-120°	251.7	8.7
90°-150°	855.2	29.7
90°-180°	1183.0	41.0
0°-180°	2882.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	826	826	826	826	826	
5°	826	822	812	819	817	78
15°	785	777	752	738	730	221
25°	713	689	640	609	598	328
35°	614	576	510	463	447	384
45°	502	452	374	320	303	388
55°	382	324	243	198	184	341
65°	258	197	130	105	102	256
75°	138	85	60	54	54	145
85°	32	16	14	14	14	37
90°	0	5	12	12	12	3
95°	19	22	23	23	22	21
105°	77	78	78	79	79	81
115°	143	145	144	144	143	141
125°	208	211	210	209	208	186
135°	269	273	274	273	272	208
145°	326	329	331	331	330	204
155°	373	374	375	377	376	172
165°	406	406	406	408	406	115
175°	422	421	421	423	421	40
180°	423	423	423	423	423	

TEST NUMBER: P999729

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	825.6	825.6	825.6	825.6	825.6
2.5°	829.4	825.6	817.4	824.9	823.4
5°	825.6	821.9	812.2	818.9	816.7
7.5°	818.9	814.4	804.0	806.9	803.2
10°	809.9	804.7	789.8	787.5	783.0
12.5°	798.7	792.0	771.8	767.3	759.1
15°	785.3	777.1	751.7	737.5	730.0
17.5°	769.6	757.6	726.2	709.8	697.9
20°	751.7	736.7	699.4	680.7	664.2
22.5°	732.2	715.0	671.7	646.3	635.1
25°	712.8	688.9	639.6	608.9	597.7
27.5°	689.6	664.2	609.7	574.6	557.4
30°	665.0	636.6	576.8	538.7	518.5
32.5°	641.1	606.7	545.4	500.6	481.9
35°	614.2	576.1	510.3	463.2	446.8
37.5°	588.0	546.9	477.4	425.9	407.2
40°	560.4	515.5	443.1	390.0	370.6
42.5°	532.0	484.2	408.7	353.4	334.7
45°	502.1	452.0	373.6	320.5	302.6
47.5°	473.7	420.7	340.0	286.9	270.5
50°	442.3	389.3	307.1	255.5	239.8
52.5°	411.7	355.7	275.7	226.4	212.2
55°	381.8	323.5	242.8	198.0	183.8
57.5°	351.2	291.4	213.7	171.8	159.9
60°	319.8	260.0	183.1	145.0	133.0
62.5°	289.2	229.4	156.9	121.0	115.1
65°	257.8	197.3	130.0	104.6	102.4
67.5°	227.9	167.4	104.6	91.9	89.7
70°	196.5	138.2	86.7	79.2	76.2
72.5°	166.6	111.3	72.5	66.5	65.0
75°	137.5	85.2	59.8	54.5	53.8
77.5°	108.3	60.5	47.1	44.1	42.6
80°	81.4	43.3	35.9	32.9	32.9
82.5°	56.8	29.1	24.7	23.2	23.2
85°	32.1	16.4	14.2	14.2	14.2
87.5°	12.0	6.0	6.0	5.2	5.2
90°	0.4	4.6	12.5	11.8	12.1
92.5°	7.9	10.7	11.1	11.4	11.4
95°	18.6	22.1	22.8	22.8	22.1
97.5°	31.1	34.3	35.7	35.7	35.7
100°	45.3	48.2	49.3	49.3	48.9
102.5°	60.3	62.5	63.9	64.3	63.9
105°	76.8	77.8	78.5	79.3	79.3
107.5°	93.2	94.6	94.6	95.0	93.2
110°	108.9	111.0	111.0	111.0	110.0



TEST NUMBER: P999729

CATALOG NUMBER: SA2XXRDIP-B485D330UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	126.0	128.2	127.8	126.7	126.0
115°	142.8	144.9	144.2	143.9	142.8
117.5°	159.6	162.4	160.7	159.6	158.5
120°	176.4	179.2	176.4	176.4	175.3
122.5°	191.7	195.3	193.5	192.4	191.7
125°	207.8	211.0	209.9	208.9	208.5
127.5°	223.5	227.4	226.0	224.6	223.5
130°	238.1	242.8	242.1	241.3	239.9
132.5°	254.6	258.1	258.5	256.7	255.6
135°	268.8	272.8	273.5	273.1	272.0
137.5°	284.5	287.8	288.5	288.1	286.7
140°	298.5	301.7	303.5	303.5	302.0
142.5°	312.7	316.0	317.0	317.4	316.0
145°	326.3	328.8	331.0	331.3	329.9
147.5°	338.4	341.7	343.1	343.8	342.4
150°	350.9	353.1	354.5	355.6	354.5
152.5°	362.0	364.2	365.9	367.4	365.9
155°	373.1	374.1	375.2	377.0	375.9
157.5°	382.7	383.4	384.1	386.6	384.9
160°	391.3	392.0	392.4	394.5	393.1
162.5°	399.1	399.1	399.5	402.0	400.2
165°	405.9	405.6	405.6	408.1	406.3
167.5°	412.0	410.9	410.9	413.4	411.6
170°	416.6	415.6	415.2	417.7	415.6
172.5°	419.8	418.8	418.4	420.9	418.8
175°	422.3	421.3	420.6	423.1	420.9
177.5°	423.8	422.7	422.0	424.1	422.0
180°	423.1	423.1	423.1	423.1	423.1

(END OF REPORT)